

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937907

Luminaire Tested: SQ4-FB-125U-050D-B50-1D-UNV-W2A-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937907
REPORT IS A COMBINATION OF REPORTS P933605 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-050D-B50-1D-UNV-W2A-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9270.8 lumens
Efficiency: N/A
Efficacy: 129.8 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 71.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937907

CATALOG NUMBER: SQ4-FB-125U-050D-B50-1D-UNV-W2A-W-6

Luminous Intensity Polar Plot



TEST NUMBER: P937907

CATALOG NUMBER: SQ4-FB-125U-050D-B50-1D-UNV-W2A-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24		
1	92	88	84	80	81	78	75	72	60	58	56	44	42	41	28	28	27	20		
2	83	76	70	65	74	68	63	58	52	49	46	38	36	34	25	23	22	16		
3	76	66	59	54	67	59	53	48	46	42	38	33	30	28	21	20	19	13		
4	69	58	51	45	61	52	46	41	40	36	32	29	26	24	19	17	16	11		
5	63	52	44	38	56	46	39	34	36	31	27	26	23	20	17	15	13	10		
6	58	46	38	33	51	41	34	29	32	27	23	23	20	17	15	13	12	8		
7	53	41	34	28	47	37	30	26	29	24	20	21	18	15	14	12	10	7		
8	49	37	30	25	44	33	27	22	26	21	18	19	16	13	12	10	9	6		
9	46	34	27	22	40	30	24	20	24	19	16	17	14	12	11	9	8	6		
10	42	31	24	19	38	28	21	17	22	17	14	16	13	10	10	9	7	5		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1808	1808	1808
5°	1765	2088	2429
10°	1600	3044	4027
15°	1359	3975	4864
20°	1107	4606	4957
25°	923	4819	4856
30°	778	4848	4847
35°	688	4766	4972
40°	599	4660	5101
45°	542	4582	5122
50°	496	4512	5037
55°	475	4410	4814
60°	486	4214	4461
65°	505	3917	3976
70°	536	3414	3359
75°	592	2780	2622
80°	641	1925	1766
85°	560	1021	905

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5122 cd/sqm

TEST NUMBER: P937907

CATALOG NUMBER: SQ4-FB-125U-050D-B50-1D-UNV-W2A-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.8	0.4
10°-20°	167.5	1.8
20°-30°	293.0	3.2
30°-40°	377.2	4.1
40°-50°	421.3	4.5
50°-60°	403.5	4.4
60°-70°	319.8	3.4
70°-80°	188.0	2.0
80°-90°	56.4	0.6
90°-100°	526.8	5.7
100°-110°	1385.1	14.9
110°-120°	1436.2	15.5
120°-130°	1152.0	12.4
130°-140°	903.9	9.7
140°-150°	693.8	7.5
150°-160°	499.6	5.4
160°-170°	305.7	3.3
170°-180°	103.3	1.1
0°-30°	498.3	5.4
0°-40°	875.5	9.4
0°-60°	1700.2	18.3
0°-90°	2264.4	24.4
90°-120°	3348.1	36.1
90°-150°	6097.8	65.8
90°-180°	7006.0	75.6
0°-180°	9270.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	292	292	292	292	292	
5°	285	305	344	389	403	26
15°	213	394	663	804	830	59
25°	136	446	790	825	826	63
35°	92	427	744	786	817	57
45°	63	340	658	754	787	49
55°	45	216	558	648	666	41
65°	36	115	414	466	472	35
75°	26	70	227	250	251	28
85°	9	22	56	62	63	10
90°	7	20	55	28	28	7
95°	70	273	908	468	318	77
105°	250	378	1531	2325	2169	265
115°	443	538	1227	2447	2793	438
125°	616	691	1116	1885	2224	547
135°	735	809	1081	1522	1726	569
145°	852	907	1067	1298	1400	534
155°	963	990	1067	1172	1206	443
165°	1039	1053	1067	1109	1123	293
175°	1081	1081	1074	1088	1088	103
180°	1081	1081	1081	1081	1081	

TEST NUMBER: P937907

CATALOG NUMBER: SQ4-FB-125U-050D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	292.2	292.2	292.2	292.2	292.2	292.2	292.2	292.2	292.2	292.2	292.2
2.5°	292.2	292.2	294.0	295.0	296.9	297.9	299.7	301.6	307.2	308.1	310.0
5°	284.7	288.4	300.7	305.3	318.5	336.3	343.8	356.0	381.4	388.9	393.7
7.5°	273.4	281.9	311.9	319.4	352.3	399.3	419.0	445.3	485.7	505.5	521.5
10°	255.5	273.4	326.9	344.8	398.4	469.7	506.4	543.0	604.1	631.3	641.7
12.5°	235.8	265.0	342.9	367.3	444.4	548.6	592.8	633.3	702.7	739.4	745.0
15°	213.2	252.7	357.9	393.7	493.2	614.4	663.2	713.1	777.9	804.2	810.8
17.5°	193.5	243.3	372.0	409.7	530.8	673.6	723.4	764.8	817.3	835.2	839.9
20°	169.1	228.3	381.4	430.3	570.3	716.8	764.8	796.7	832.4	843.7	845.6
22.5°	151.2	212.3	387.0	437.8	596.5	743.1	783.5	808.8	833.3	837.1	838.0
25°	136.3	194.5	386.1	446.3	619.1	759.1	790.1	808.8	822.9	824.8	824.8
27.5°	122.2	174.8	382.4	448.1	636.1	762.9	787.3	800.4	807.0	810.8	810.8
30°	109.9	156.0	372.9	444.4	643.5	759.1	778.9	785.4	791.9	797.6	800.4
32.5°	100.5	138.1	358.8	436.8	644.5	749.7	763.8	767.6	776.9	790.1	794.8
35°	92.1	120.3	342.9	426.6	638.9	734.7	744.0	747.9	766.6	786.3	792.9
37.5°	83.6	107.1	322.2	408.7	630.4	716.8	723.4	730.0	759.1	782.6	790.1
40°	75.2	95.8	297.9	388.9	617.3	695.2	700.9	711.1	749.7	776.9	784.5
42.5°	68.6	86.4	271.5	368.3	600.3	670.8	679.2	694.2	738.4	767.6	776.0
45°	63.0	77.1	243.3	340.1	578.7	645.4	657.6	678.3	725.3	753.5	760.9
47.5°	57.3	70.4	214.2	310.9	555.3	620.1	636.1	659.5	707.4	734.7	741.2
50°	52.6	63.9	185.1	279.9	529.9	592.8	611.6	636.1	684.9	710.2	718.7
52.5°	48.8	58.3	157.8	249.0	500.7	564.6	586.3	611.6	657.6	682.1	687.7
55°	45.1	53.5	134.3	216.0	470.6	534.5	558.1	582.4	627.6	648.2	652.0
57.5°	43.2	49.8	114.6	185.1	438.7	500.7	527.1	549.6	591.9	607.8	611.6
60°	40.4	47.0	99.6	158.8	404.0	468.8	491.4	513.9	549.6	562.7	565.5
62.5°	37.5	45.1	88.4	133.4	368.3	431.2	453.7	474.5	504.5	513.9	517.6
65°	35.7	43.2	79.9	114.6	331.7	391.7	414.3	432.2	456.5	466.0	467.8
67.5°	33.8	41.4	73.3	98.6	295.0	352.3	369.2	386.1	404.9	414.3	415.3
70°	31.0	39.4	67.6	87.3	257.4	307.2	321.3	339.1	354.2	358.8	361.7
72.5°	29.1	36.6	63.9	78.9	218.9	263.9	277.1	287.5	300.7	305.3	305.3
75°	26.3	32.9	60.1	70.4	179.4	216.0	227.3	237.7	248.0	249.9	247.0
77.5°	23.4	29.1	51.7	59.2	140.0	171.0	180.4	186.1	194.5	196.3	197.3
80°	19.7	25.4	40.4	46.0	101.4	125.9	132.4	137.2	144.7	144.7	146.5
82.5°	15.0	19.7	29.1	32.9	68.6	86.4	92.1	94.9	99.6	99.6	99.6
85°	9.4	12.2	18.8	21.6	41.4	52.6	56.4	57.3	61.1	62.0	62.0
87.5°	4.7	6.5	12.2	13.2	21.6	27.3	27.3	29.1	29.1	28.2	27.3
90°	7.3	13.1	18.9	20.3	31.8	47.4	55.1	48.9	36.7	27.6	27.6
92.5°	29.0	78.4	127.7	140.0	196.8	272.5	310.5	272.1	195.4	137.9	132.3
95°	69.7	159.9	250.1	272.7	484.3	766.4	907.5	809.8	614.4	467.8	451.2
97.5°	120.4	200.0	279.6	299.5	652.3	1122.8	1357.9	1296.2	1172.7	1080.1	1048.5
100°	159.6	231.8	304.0	322.0	713.5	1235.5	1496.5	1500.9	1510.0	1516.7	1479.1
102.5°	193.0	260.3	327.7	344.6	741.6	1270.9	1535.6	1614.2	1771.6	1889.6	1857.4
105°	249.6	306.6	363.6	377.9	762.3	1275.0	1531.3	1707.6	2060.3	2324.8	2307.4
107.5°	307.6	360.7	413.9	427.2	766.3	1218.2	1444.2	1690.3	2182.2	2551.1	2555.3
110°	346.7	394.7	442.7	454.8	760.4	1167.9	1371.7	1646.6	2196.7	2609.2	2627.2

TEST NUMBER: P937907

CATALOG NUMBER: SQ4-FB-125U-050D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	385.2	430.9	476.7	488.2	760.6	1124.0	1305.6	1587.1	2150.0	2572.1	2599.9
115°	443.2	485.4	527.7	538.3	767.7	1073.6	1226.6	1497.8	2040.0	2446.7	2485.2
117.5°	500.5	538.9	577.2	586.8	781.9	1042.1	1172.2	1416.9	1906.3	2273.4	2315.9
120°	533.9	570.0	606.1	615.1	793.5	1031.4	1150.4	1374.0	1821.1	2156.5	2198.0
122.5°	566.6	603.0	639.4	648.5	810.2	1025.9	1133.8	1335.2	1737.8	2039.8	2080.6
125°	616.5	649.8	682.9	691.3	832.8	1021.3	1115.7	1286.7	1628.7	1885.3	1922.9
127.5°	657.2	690.7	724.2	732.6	855.3	1018.7	1100.4	1247.3	1541.0	1761.2	1793.0
130°	678.9	715.1	751.1	760.2	871.6	1020.2	1094.6	1225.3	1486.7	1682.9	1712.2
132.5°	701.4	737.6	773.6	782.7	885.0	1021.3	1089.5	1206.5	1440.6	1616.1	1642.3
135°	734.8	767.7	800.5	808.8	899.4	1020.4	1080.8	1178.8	1374.8	1521.9	1544.5
137.5°	768.9	801.5	834.1	842.2	921.2	1026.7	1079.3	1162.2	1327.9	1452.2	1470.7
140°	797.2	827.2	857.1	864.6	934.5	1027.7	1074.3	1145.8	1289.0	1396.3	1413.7
142.5°	818.9	846.7	874.4	881.3	945.7	1031.4	1074.3	1137.1	1262.9	1357.2	1372.1
145°	852.3	876.5	900.7	906.7	960.2	1031.4	1067.0	1118.5	1221.3	1298.4	1309.7
147.5°	885.7	909.2	932.8	938.7	981.4	1038.5	1067.0	1107.4	1188.4	1249.1	1258.5
150°	907.5	928.8	950.0	955.3	992.6	1042.2	1067.0	1101.2	1169.6	1220.8	1228.4
152.5°	929.9	946.0	962.2	966.2	999.8	1044.6	1067.0	1096.1	1154.5	1198.3	1204.0
155°	963.3	975.3	987.1	990.1	1015.7	1049.9	1067.0	1090.3	1136.7	1171.5	1175.3
157.5°	988.0	999.6	1011.1	1014.0	1031.7	1055.2	1067.0	1085.0	1121.2	1148.3	1150.9
160°	1004.6	1013.7	1022.7	1025.0	1039.0	1057.7	1067.0	1082.5	1113.4	1136.7	1138.2
162.5°	1021.3	1028.1	1034.9	1036.6	1046.7	1060.3	1067.0	1080.1	1106.1	1125.8	1127.2
165°	1039.4	1045.6	1051.8	1053.3	1057.8	1063.9	1067.0	1076.3	1095.1	1109.1	1110.6
167.5°	1056.2	1059.1	1062.0	1062.7	1066.5	1071.7	1074.3	1080.5	1092.7	1101.8	1102.5
170°	1067.0	1069.9	1072.8	1073.5	1073.8	1074.1	1074.3	1080.5	1092.7	1101.8	1101.8
172.5°	1072.8	1073.4	1074.1	1074.3	1074.3	1074.3	1074.3	1079.1	1088.8	1096.0	1095.5
175°	1080.8	1080.8	1080.8	1080.8	1078.7	1075.8	1074.3	1077.4	1083.5	1088.1	1088.1
177.5°	1080.8	1080.8	1080.8	1080.8	1079.1	1076.8	1075.7	1078.1	1083.0	1086.6	1086.0
180°	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8

TEST NUMBER: P937907

CATALOG NUMBER: SQ4-FB-125U-050D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	292.2	292.2
2.5°	311.9	310.0
5°	401.2	403.0
7.5°	540.2	539.3
10°	671.7	680.1
12.5°	767.6	769.4
15°	825.8	829.6
17.5°	848.4	849.3
20°	849.3	847.4
22.5°	838.9	837.1
25°	826.8	825.8
27.5°	815.5	816.4
30°	810.8	813.6
32.5°	810.8	815.5
35°	812.7	817.3
37.5°	811.7	817.3
40°	807.9	814.5
42.5°	797.6	802.3
45°	781.7	787.3
47.5°	760.9	764.8
50°	734.7	738.4
52.5°	701.8	702.7
55°	662.3	666.1
57.5°	620.1	621.0
60°	573.1	575.9
62.5°	523.3	523.3
65°	470.6	472.5
67.5°	416.2	420.9
70°	360.8	361.7
72.5°	306.3	306.3
75°	249.9	250.9
77.5°	196.3	196.3
80°	145.6	146.5
82.5°	100.5	102.4
85°	63.0	63.0
87.5°	29.1	26.3
90°	27.6	27.6
92.5°	110.4	88.4
95°	384.8	318.4
97.5°	922.1	795.8
100°	1328.6	1178.1
102.5°	1728.4	1599.5
105°	2238.1	2168.8
107.5°	2572.0	2588.9
110°	2699.4	2771.6

TEST NUMBER: P937907

CATALOG NUMBER: SQ4-FB-125U-050D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2710.7	2821.7
115°	2638.9	2792.7
117.5°	2486.5	2657.0
120°	2363.7	2529.4
122.5°	2244.0	2407.5
125°	2073.5	2224.0
127.5°	1920.0	2047.0
130°	1829.6	1946.9
132.5°	1747.5	1852.6
135°	1635.1	1725.7
137.5°	1544.8	1619.0
140°	1483.0	1552.3
142.5°	1431.7	1491.4
145°	1354.9	1400.0
147.5°	1295.9	1333.3
150°	1258.8	1289.0
152.5°	1226.9	1249.8
155°	1190.5	1205.6
157.5°	1161.5	1172.2
160°	1144.3	1150.4
162.5°	1133.0	1138.8
165°	1116.8	1122.9
167.5°	1105.0	1107.6
170°	1101.8	1101.8
172.5°	1093.2	1091.0
175°	1088.1	1088.1
177.5°	1083.4	1080.8
180°	1080.8	1080.8

(END OF REPORT)