

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937903

Luminaire Tested: SQ4-FB-125U-050D-B40-1D-UNV-W2A-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937903
REPORT IS A COMBINATION OF REPORTS P933605 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-050D-B40-1D-UNV-W2A-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9479.3 lumens
Efficiency: N/A
Efficacy: 132.8 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 71.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937903

CATALOG NUMBER: SQ4-FB-125U-050D-B40-1D-UNV-W2A-W-6

Luminous Intensity Polar Plot



TEST NUMBER: P937903

CATALOG NUMBER: SQ4-FB-125U-050D-B40-1D-UNV-W2A-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24		
1	92	88	84	80	81	78	75	72	60	58	56	44	42	41	28	28	27	20		
2	83	76	70	65	74	68	63	58	52	49	46	38	36	34	25	23	22	16		
3	76	66	59	54	67	59	53	48	46	42	38	33	30	28	21	20	19	13		
4	69	58	51	45	61	52	46	41	40	36	32	29	26	24	19	17	16	11		
5	63	52	44	38	56	46	39	34	36	31	27	26	23	20	17	15	13	10		
6	58	46	38	33	51	41	34	29	32	27	23	23	20	17	15	13	12	8		
7	53	41	34	28	47	37	30	26	29	24	20	21	18	15	14	12	10	7		
8	49	37	30	25	44	33	27	22	26	21	18	19	16	13	12	10	9	6		
9	46	34	27	22	40	30	24	20	24	19	16	17	14	12	11	9	8	6		
10	42	31	24	19	38	28	21	17	22	17	14	16	13	10	10	9	7	5		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1848	1848	1848
5°	1805	2135	2484
10°	1637	3112	4118
15°	1390	4064	4973
20°	1132	4710	5068
25°	943	4927	4965
30°	795	4957	4956
35°	703	4873	5084
40°	612	4765	5217
45°	554	4685	5237
50°	508	4613	5150
55°	486	4508	4922
60°	498	4308	4562
65°	516	4005	4065
70°	548	3490	3436
75°	605	2843	2681
80°	657	1969	1806
85°	572	1044	925

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5237 cd/sqm

TEST NUMBER: P937903

CATALOG NUMBER: SQ4-FB-125U-050D-B40-1D-UNV-W2A-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.6	0.4
10°-20°	171.3	1.8
20°-30°	299.6	3.2
30°-40°	385.6	4.1
40°-50°	430.7	4.5
50°-60°	412.6	4.4
60°-70°	327.0	3.4
70°-80°	192.3	2.0
80°-90°	57.6	0.6
90°-100°	538.7	5.7
100°-110°	1416.2	14.9
110°-120°	1468.5	15.5
120°-130°	1177.9	12.4
130°-140°	924.2	9.7
140°-150°	709.4	7.5
150°-160°	510.9	5.4
160°-170°	312.6	3.3
170°-180°	105.6	1.1
0°-30°	509.5	5.4
0°-40°	895.1	9.4
0°-60°	1738.5	18.3
0°-90°	2315.3	24.4
90°-120°	3423.4	36.1
90°-150°	6234.9	65.8
90°-180°	7164.0	75.6
0°-180°	9479.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	299	299	299	299	299	
5°	291	312	352	398	412	27
15°	218	402	678	822	848	61
25°	139	456	808	843	844	64
35°	94	436	761	804	836	59
45°	64	348	672	770	805	50
55°	46	221	571	663	681	42
65°	36	117	424	476	483	36
75°	27	72	232	256	256	28
85°	10	22	58	63	64	10
90°	7	21	56	28	28	7
95°	71	279	928	478	326	79
105°	255	386	1566	2377	2218	271
115°	453	550	1254	2502	2855	448
125°	630	707	1141	1928	2274	560
135°	751	827	1105	1556	1764	581
145°	871	927	1091	1328	1431	546
155°	985	1012	1091	1198	1233	453
165°	1063	1077	1091	1134	1148	300
175°	1105	1105	1098	1113	1113	105
180°	1105	1105	1105	1105	1105	

TEST NUMBER: P937903

CATALOG NUMBER: SQ4-FB-125U-050D-B40-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	298.7	298.7	298.7	298.7	298.7	298.7	298.7	298.7	298.7	298.7	298.7
2.5°	298.7	298.7	300.6	301.6	303.6	304.5	306.5	308.4	314.1	315.1	317.0
5°	291.1	294.9	307.4	312.2	325.7	343.9	351.5	364.0	390.0	397.7	402.5
7.5°	279.5	288.2	318.9	326.6	360.2	408.3	428.4	455.3	496.6	516.8	533.2
10°	261.3	279.5	334.2	352.6	407.3	480.3	517.8	555.2	617.7	645.5	656.1
12.5°	241.1	270.9	350.6	375.6	454.4	561.0	606.1	647.5	718.5	756.0	761.7
15°	218.0	258.4	366.0	402.5	504.3	628.2	678.1	729.1	795.4	822.3	829.0
17.5°	197.9	248.8	380.4	418.9	542.7	688.7	739.6	782.0	835.7	854.0	858.7
20°	173.0	233.4	390.0	440.0	583.1	733.0	782.0	814.6	851.1	862.7	864.6
22.5°	154.6	217.1	395.8	447.6	610.0	759.8	801.1	827.0	852.1	855.9	856.8
25°	139.3	198.8	394.8	456.3	633.1	776.1	807.8	827.0	841.5	843.4	843.4
27.5°	124.9	178.7	391.0	458.2	650.4	780.0	805.0	818.4	825.1	829.0	829.0
30°	112.4	159.5	381.3	454.4	658.0	776.1	796.4	803.1	809.7	815.6	818.4
32.5°	102.8	141.2	366.9	446.7	658.9	766.6	781.0	784.8	794.4	807.8	812.7
35°	94.2	123.0	350.6	436.1	653.2	751.2	760.8	764.7	783.9	804.0	810.7
37.5°	85.5	109.5	329.5	417.9	644.5	733.0	739.6	746.4	776.1	800.2	807.8
40°	76.9	98.0	304.5	397.7	631.2	710.8	716.6	727.1	766.6	794.4	802.1
42.5°	70.1	88.3	277.6	376.6	613.8	685.9	694.5	709.9	755.0	784.8	793.4
45°	64.4	78.8	248.8	347.7	591.7	659.9	672.4	693.5	741.6	770.4	778.0
47.5°	58.6	72.0	219.0	317.9	567.7	634.0	650.4	674.3	723.3	751.2	757.9
50°	53.8	65.3	189.3	286.2	541.8	606.1	625.3	650.4	700.3	726.2	734.9
52.5°	49.9	59.6	161.4	254.6	512.0	577.3	599.5	625.3	672.4	697.4	703.2
55°	46.1	54.7	137.3	220.9	481.2	546.5	570.6	595.5	641.7	662.8	666.7
57.5°	44.2	50.9	117.2	189.3	448.6	512.0	538.9	561.9	605.2	621.5	625.3
60°	41.4	48.0	101.8	162.4	413.0	479.3	502.4	525.4	561.9	575.4	578.3
62.5°	38.4	46.1	90.3	136.4	376.6	440.9	463.9	485.1	515.8	525.4	529.3
65°	36.5	44.2	81.7	117.2	339.1	400.5	423.6	441.9	466.8	476.4	478.4
67.5°	34.6	42.3	75.0	100.8	301.6	360.2	377.5	394.8	414.0	423.6	424.6
70°	31.7	40.3	69.1	89.3	263.2	314.1	328.5	346.8	362.1	366.9	369.9
72.5°	29.8	37.4	65.3	80.7	223.9	269.9	283.3	293.9	307.4	312.2	312.2
75°	26.9	33.6	61.5	72.0	183.5	220.9	232.4	243.0	253.6	255.6	252.6
77.5°	24.0	29.8	52.8	60.5	143.2	174.9	184.4	190.2	198.8	200.7	201.7
80°	20.2	26.0	41.4	47.1	103.7	128.7	135.4	140.3	147.9	147.9	149.8
82.5°	15.4	20.2	29.8	33.6	70.1	88.3	94.2	97.0	101.8	101.8	101.8
85°	9.6	12.5	19.2	22.1	42.3	53.8	57.7	58.6	62.5	63.4	63.4
87.5°	4.8	6.7	12.5	13.5	22.1	27.9	27.9	29.8	29.8	28.8	27.9
90°	7.4	13.4	19.3	20.7	32.6	48.4	56.3	50.0	37.5	28.2	28.2
92.5°	29.7	80.1	130.5	143.2	201.2	278.7	317.4	278.2	199.8	141.0	135.3
95°	71.2	163.5	255.7	278.9	495.2	783.7	927.9	828.0	628.2	478.4	461.4
97.5°	123.1	204.5	285.9	306.3	667.0	1148.0	1388.5	1325.3	1199.1	1104.4	1072.1
100°	163.2	237.0	310.9	329.3	729.5	1263.3	1530.1	1534.7	1543.9	1550.8	1512.3
102.5°	197.3	266.2	335.1	352.3	758.3	1299.5	1570.1	1650.5	1811.4	1932.1	1899.1
105°	255.2	313.5	371.8	386.4	779.5	1303.7	1565.7	1746.0	2106.6	2377.1	2359.3
107.5°	314.5	368.8	423.3	436.8	783.5	1245.6	1476.7	1728.3	2231.3	2608.5	2612.8
110°	354.5	403.6	452.7	465.0	777.5	1194.1	1402.5	1683.7	2246.1	2667.9	2686.3

TEST NUMBER: P937903

CATALOG NUMBER: SQ4-FB-125U-050D-B40-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	393.8	440.6	487.4	499.2	777.8	1149.2	1335.0	1622.7	2198.3	2630.0	2658.3
115°	453.1	496.3	539.6	550.4	785.0	1097.8	1254.2	1531.4	2085.9	2501.7	2541.1
117.5°	511.8	551.0	590.2	600.0	799.5	1065.5	1198.5	1448.7	1949.2	2324.5	2368.0
120°	545.9	582.8	619.7	629.0	811.4	1054.6	1176.3	1404.9	1862.1	2205.0	2247.4
122.5°	579.3	616.5	653.8	663.1	828.5	1049.0	1159.3	1365.2	1776.9	2085.6	2127.4
125°	630.4	664.4	698.3	706.8	851.5	1044.3	1140.7	1315.6	1665.3	1927.7	1966.2
127.5°	671.9	706.2	740.5	749.1	874.5	1041.6	1125.2	1275.3	1575.7	1800.8	1833.3
130°	694.2	731.1	768.0	777.3	891.2	1043.1	1119.2	1252.9	1520.2	1720.7	1750.7
132.5°	717.2	754.2	791.0	800.3	904.9	1044.3	1114.0	1233.7	1473.0	1652.4	1679.3
135°	751.3	784.9	818.5	826.9	919.7	1043.3	1105.1	1205.3	1405.8	1556.1	1579.2
137.5°	786.2	819.5	852.8	861.1	941.9	1049.7	1103.6	1188.3	1357.7	1484.8	1503.7
140°	815.1	845.7	876.4	884.0	955.5	1050.8	1098.4	1171.6	1318.0	1427.7	1445.5
142.5°	837.3	865.7	894.1	901.1	966.9	1054.6	1098.4	1162.7	1291.3	1387.7	1403.0
145°	871.4	896.2	920.9	927.1	981.7	1054.6	1091.0	1143.6	1248.8	1327.6	1339.2
147.5°	905.6	929.7	953.8	959.8	1003.5	1061.9	1091.0	1132.3	1215.1	1277.2	1286.8
150°	927.9	949.7	971.3	976.8	1014.9	1065.6	1091.0	1125.9	1195.9	1248.3	1256.0
152.5°	950.8	967.3	983.8	987.9	1022.3	1068.1	1091.0	1120.8	1180.5	1225.3	1231.1
155°	985.0	997.2	1009.3	1012.4	1038.6	1073.5	1091.0	1114.8	1162.2	1197.9	1201.8
157.5°	1010.2	1022.0	1033.9	1036.8	1054.9	1079.0	1091.0	1109.4	1146.4	1174.1	1176.8
160°	1027.2	1036.5	1045.7	1048.0	1062.3	1081.4	1091.0	1106.8	1138.5	1162.2	1163.8
162.5°	1044.3	1051.2	1058.1	1059.9	1070.3	1084.1	1091.0	1104.4	1131.0	1151.1	1152.6
165°	1062.8	1069.1	1075.4	1077.0	1081.6	1087.8	1091.0	1100.5	1119.7	1134.1	1135.6
167.5°	1079.9	1082.9	1085.8	1086.6	1090.5	1095.8	1098.4	1104.7	1117.3	1126.6	1127.3
170°	1091.0	1094.0	1096.9	1097.7	1098.0	1098.2	1098.4	1104.7	1117.3	1126.6	1126.6
172.5°	1096.9	1097.6	1098.2	1098.4	1098.4	1098.4	1098.4	1103.4	1113.2	1120.7	1120.1
175°	1105.1	1105.1	1105.1	1105.1	1102.9	1100.0	1098.4	1101.6	1107.9	1112.6	1112.6
177.5°	1105.1	1105.1	1105.1	1105.1	1103.4	1101.0	1099.9	1102.4	1107.3	1111.0	1110.4
180°	1105.1	1105.1	1105.1	1105.1	1105.1	1105.1	1105.1	1105.1	1105.1	1105.1	1105.1

TEST NUMBER: P937903

CATALOG NUMBER: SQ4-FB-125U-050D-B40-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	298.7	298.7
2.5°	318.9	317.0
5°	410.2	412.1
7.5°	552.4	551.4
10°	686.8	695.4
12.5°	784.8	786.7
15°	844.4	848.2
17.5°	867.4	868.4
20°	868.4	866.5
22.5°	857.8	855.9
25°	845.4	844.4
27.5°	833.8	834.8
30°	829.0	831.9
32.5°	829.0	833.8
35°	830.9	835.7
37.5°	830.0	835.7
40°	826.1	832.9
42.5°	815.6	820.3
45°	799.2	805.0
47.5°	778.0	782.0
50°	751.2	755.0
52.5°	717.6	718.5
55°	677.2	681.1
57.5°	634.0	635.0
60°	586.0	588.9
62.5°	535.1	535.1
65°	481.2	483.1
67.5°	425.5	430.3
70°	368.9	369.9
72.5°	313.1	313.1
75°	255.6	256.5
77.5°	200.7	200.7
80°	148.9	149.8
82.5°	102.8	104.7
85°	64.4	64.4
87.5°	29.8	26.9
90°	28.2	28.2
92.5°	112.9	90.4
95°	393.5	325.6
97.5°	942.9	813.7
100°	1358.5	1204.5
102.5°	1767.2	1635.4
105°	2288.5	2217.6
107.5°	2629.9	2647.1
110°	2760.1	2834.0

TEST NUMBER: P937903

CATALOG NUMBER: SQ4-FB-125U-050D-B40-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2771.7	2885.2
115°	2698.3	2855.4
117.5°	2542.4	2716.8
120°	2416.8	2586.2
122.5°	2294.5	2461.6
125°	2120.1	2274.0
127.5°	1963.2	2093.1
130°	1870.7	1990.7
132.5°	1786.8	1894.2
135°	1671.8	1764.5
137.5°	1579.6	1655.4
140°	1516.3	1587.2
142.5°	1463.9	1524.9
145°	1385.3	1431.4
147.5°	1325.1	1363.3
150°	1287.1	1318.0
152.5°	1254.5	1277.9
155°	1217.2	1232.7
157.5°	1187.6	1198.5
160°	1170.1	1176.3
162.5°	1158.5	1164.4
165°	1141.9	1148.1
167.5°	1129.9	1132.5
170°	1126.6	1126.6
172.5°	1117.8	1115.5
175°	1112.6	1112.6
177.5°	1107.8	1105.1
180°	1105.1	1105.1

(END OF REPORT)