

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938005

Luminaire Tested: SQ4-FB-125U-075D-B50-1D-UNV-W2A-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938005
REPORT IS A COMBINATION OF REPORTS P933590 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-075D-B50-1D-UNV-W2A-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20762.8 lumens
Efficiency: N/A
Efficacy: 124.5 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 166.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938005

CATALOG NUMBER: SQ4-FB-125U-075D-B50-1D-UNV-W2A-W-12

Luminous Intensity Polar Plot



TEST NUMBER: P938005

CATALOG NUMBER: SQ4-FB-125U-075D-B50-1D-UNV-W2A-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33			
1	94	89	85	82	84	80	77	74	64	62	60	49	47	46	35	34	33	27			
2	85	77	71	66	76	70	65	60	55	52	49	42	40	38	30	29	27	22			
3	77	68	60	54	69	61	55	50	49	44	40	37	34	31	26	24	23	18			
4	70	59	52	46	63	54	47	42	43	38	34	33	29	26	23	21	19	15			
5	64	53	45	39	57	48	41	35	38	33	29	29	25	23	21	18	16	13			
6	59	47	39	33	53	42	35	30	34	29	25	26	22	19	19	16	14	11			
7	54	42	34	29	49	38	31	26	31	25	22	23	20	17	17	14	12	10			
8	50	38	30	25	45	34	28	23	28	23	19	21	18	15	15	13	11	8			
9	47	34	27	22	42	31	25	20	25	20	17	19	16	13	14	12	10	7			
10	43	31	24	19	39	28	22	18	23	18	15	18	14	12	13	10	9	7			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2695	2695	2695
5°	2634	3116	3623
10°	2390	4544	6007
15°	2032	5938	7253
20°	1655	6882	7392
25°	1381	7204	7242
30°	1165	7251	7228
35°	1031	7133	7415
40°	899	6978	7608
45°	814	6866	7638
50°	748	6765	7512
55°	717	6616	7178
60°	735	6329	6653
65°	766	5890	5930
70°	818	5140	5010
75°	910	4195	3909
80°	1000	2913	2634
85°	907	1548	1348

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 7638 cd/sqm

TEST NUMBER: P938005

CATALOG NUMBER: SQ4-FB-125U-075D-B50-1D-UNV-W2A-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.7	0.5
10°-20°	499.6	2.4
20°-30°	873.9	4.2
30°-40°	1125.0	5.4
40°-50°	1256.5	6.1
50°-60°	1203.5	5.8
60°-70°	953.8	4.6
70°-80°	560.8	2.7
80°-90°	164.0	0.8
90°-100°	1053.7	5.1
100°-110°	2770.2	13.3
110°-120°	2872.4	13.8
120°-130°	2304.0	11.1
130°-140°	1807.8	8.7
140°-150°	1387.6	6.7
150°-160°	999.3	4.8
160°-170°	611.4	2.9
170°-180°	206.6	1.0
0°-30°	1486.2	7.2
0°-40°	2611.2	12.6
0°-60°	5071.2	24.4
0°-90°	6749.8	32.5
90°-120°	6696.3	32.3
90°-150°	12195.7	58.7
90°-180°	14013.0	67.5
0°-180°	20762.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	871	871	871	871	871	
5°	849	911	1026	1160	1202	78
15°	636	1174	1978	2399	2474	177
25°	406	1331	2357	2460	2463	187
35°	275	1272	2219	2345	2438	171
45°	188	1014	1962	2247	2348	145
55°	134	644	1664	1934	1987	123
65°	106	342	1236	1390	1410	106
75°	78	210	678	745	748	82
85°	28	64	168	185	188	30
90°	14	41	110	55	55	14
95°	139	546	1815	936	637	155
105°	499	756	3062	4650	4338	529
115°	886	1076	2453	4893	5585	876
125°	1233	1383	2231	3770	4448	1095
135°	1470	1618	2162	3044	3451	1137
145°	1705	1814	2134	2597	2800	1068
155°	1927	1980	2134	2343	2411	885
165°	2079	2106	2134	2218	2246	587
175°	2162	2162	2149	2176	2176	205
180°	2162	2162	2162	2162	2162	

TEST NUMBER: P938005

CATALOG NUMBER: SQ4-FB-125U-075D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	871.4	871.4	871.4	871.4	871.4	871.4	871.4	871.4	871.4	871.4	871.4
2.5°	871.4	871.4	877.0	879.8	885.4	888.2	893.8	899.4	916.3	919.1	924.7
5°	849.0	860.2	896.6	910.6	949.9	1003.1	1025.5	1062.1	1137.7	1160.1	1174.1
7.5°	815.4	840.6	930.3	952.7	1050.8	1190.9	1249.8	1328.2	1448.7	1507.6	1555.2
10°	762.1	815.4	975.1	1028.3	1188.1	1401.1	1510.4	1619.6	1801.8	1883.0	1913.9
12.5°	703.3	790.2	1022.7	1095.7	1325.4	1636.5	1768.2	1888.6	2096.0	2205.3	2222.1
15°	636.1	753.7	1067.7	1174.1	1471.1	1832.6	1978.3	2126.8	2320.1	2398.6	2418.2
17.5°	577.2	725.7	1109.7	1221.8	1583.2	2009.1	2157.6	2280.9	2437.8	2491.1	2505.1
20°	504.4	680.9	1137.7	1283.4	1700.9	2138.0	2280.9	2376.2	2482.7	2516.3	2521.9
22.5°	451.1	633.3	1154.5	1305.8	1779.4	2216.5	2337.0	2412.6	2485.5	2496.7	2499.5
25°	406.3	580.0	1151.7	1331.0	1846.6	2264.1	2356.6	2412.6	2454.6	2460.2	2460.2
27.5°	364.3	521.2	1140.5	1336.6	1897.0	2275.3	2348.2	2387.4	2407.0	2418.2	2418.2
30°	327.8	465.1	1112.5	1325.4	1919.5	2264.1	2323.0	2342.6	2362.2	2379.0	2387.4
32.5°	299.8	411.9	1070.5	1303.0	1922.3	2236.1	2278.1	2289.3	2317.3	2356.6	2370.6
35°	274.6	358.7	1022.7	1272.2	1905.5	2191.3	2219.3	2230.5	2286.5	2345.4	2365.0
37.5°	249.4	319.4	961.1	1219.0	1880.2	2138.0	2157.6	2177.2	2264.1	2334.2	2356.6
40°	224.2	285.8	888.2	1160.1	1841.0	2073.6	2090.4	2121.2	2236.1	2317.3	2339.8
42.5°	204.5	257.8	809.8	1098.5	1790.6	2000.7	2025.9	2070.8	2202.5	2289.3	2314.5
45°	187.7	229.8	725.7	1014.3	1726.1	1925.1	1961.5	2023.1	2163.2	2247.3	2269.7
47.5°	170.9	210.2	638.9	927.5	1656.1	1849.4	1897.0	1967.1	2110.0	2191.3	2210.9
50°	156.9	190.5	552.0	835.0	1580.4	1768.2	1824.2	1897.0	2042.8	2118.4	2143.6
52.5°	145.7	173.7	470.7	742.5	1493.6	1684.1	1748.5	1824.2	1961.5	2034.3	2051.2
55°	134.5	159.7	400.7	644.5	1403.9	1594.4	1664.5	1737.3	1871.8	1933.5	1944.7
57.5°	128.9	148.5	341.8	552.0	1308.6	1493.6	1572.0	1639.3	1765.4	1813.0	1824.2
60°	120.5	140.1	297.0	473.5	1205.0	1398.3	1465.5	1532.8	1639.3	1678.5	1686.9
62.5°	112.1	134.5	263.4	397.9	1098.5	1286.2	1353.5	1415.1	1504.8	1532.8	1544.0
65°	106.5	128.9	238.2	341.8	989.1	1168.5	1235.8	1289.0	1361.9	1389.9	1395.5
67.5°	100.9	123.3	218.6	294.2	879.8	1050.8	1101.3	1151.7	1207.8	1235.8	1238.6
70°	92.5	117.7	201.7	260.6	767.7	916.3	958.3	1011.5	1056.4	1070.5	1078.9
72.5°	86.9	109.3	190.5	235.4	652.9	787.4	826.6	857.4	896.6	910.6	910.6
75°	78.5	98.1	179.3	210.2	535.2	644.5	678.1	708.9	739.7	745.3	736.9
77.5°	70.0	86.9	154.1	176.5	417.5	510.0	538.0	554.8	580.0	585.6	588.4
80°	58.8	75.7	120.5	137.3	302.6	375.5	395.1	409.1	431.5	431.5	437.1
82.5°	44.8	58.8	86.9	98.1	204.5	257.8	274.6	283.0	297.0	297.0	297.0
85°	28.0	36.4	56.0	64.4	123.3	156.9	168.1	170.9	182.1	184.9	184.9
87.5°	14.0	19.6	36.4	39.2	64.4	81.3	81.3	86.9	86.9	84.1	81.3
90°	14.5	26.1	37.7	40.6	63.8	94.7	110.2	98.0	73.5	55.1	55.1
92.5°	58.0	156.6	255.4	280.0	393.7	545.2	620.9	544.1	390.7	275.6	264.7
95°	139.3	319.8	500.3	545.5	968.6	1532.8	1814.9	1619.5	1228.8	935.8	902.5
97.5°	240.8	400.0	559.4	599.2	1304.7	2245.4	2715.8	2592.3	2345.4	2160.2	2096.9
100°	319.1	463.6	608.0	644.2	1427.1	2471.0	2992.9	3002.0	3020.0	3033.5	2958.3
102.5°	385.9	520.7	655.4	689.1	1483.2	2541.9	3071.3	3228.6	3543.2	3779.2	3714.8
105°	499.0	613.2	727.3	755.9	1524.8	2549.9	3062.5	3415.2	4120.6	4649.6	4615.0
107.5°	615.1	721.5	827.9	854.5	1532.5	2436.5	2888.5	3380.4	4364.3	5102.3	5110.7
110°	693.5	789.5	885.6	909.6	1520.8	2335.8	2743.3	3293.4	4393.3	5218.4	5254.5

TEST NUMBER: P938005

CATALOG NUMBER: SQ4-FB-125U-075D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	770.4	861.9	953.4	976.3	1521.3	2248.0	2611.4	3174.3	4300.0	5144.4	5199.9
115°	886.4	970.8	1055.3	1076.4	1535.4	2147.3	2453.2	2995.5	4080.0	4893.4	4970.3
117.5°	1001.1	1077.7	1154.5	1173.7	1563.9	2084.2	2344.4	2833.8	3812.6	4546.6	4631.9
120°	1067.7	1139.9	1212.2	1230.3	1587.1	2063.0	2300.9	2748.1	3642.4	4313.1	4396.0
122.5°	1133.0	1205.9	1278.7	1297.0	1620.5	2051.9	2267.6	2670.2	3475.5	4079.5	4161.3
125°	1233.2	1299.6	1366.0	1382.6	1665.5	2042.7	2231.2	2573.3	3257.4	3770.5	3845.7
127.5°	1314.4	1381.5	1448.5	1465.3	1710.4	2037.3	2200.8	2494.4	3081.8	3522.4	3585.9
130°	1357.9	1430.1	1502.3	1520.4	1743.3	2040.6	2189.2	2450.6	2973.6	3365.8	3424.4
132.5°	1402.9	1475.1	1547.4	1565.4	1769.9	2042.7	2179.0	2413.1	2881.2	3232.3	3284.9
135°	1469.6	1535.4	1601.2	1617.6	1799.0	2040.8	2161.6	2357.7	2749.7	3043.7	3089.0
137.5°	1537.8	1602.9	1668.0	1684.3	1842.4	2053.3	2158.8	2324.4	2655.8	2904.4	2941.4
140°	1594.3	1654.3	1714.3	1729.3	1869.0	2055.4	2148.6	2291.7	2577.9	2792.7	2827.3
142.5°	1637.9	1693.3	1748.8	1762.6	1891.3	2062.8	2148.6	2274.3	2525.8	2714.4	2744.2
145°	1704.6	1753.0	1801.4	1813.5	1920.3	2062.8	2134.1	2236.9	2442.6	2596.8	2619.4
147.5°	1771.3	1818.4	1865.5	1877.2	1962.9	2077.0	2134.1	2215.0	2376.8	2498.2	2516.8
150°	1814.9	1857.4	1900.0	1910.7	1985.1	2084.4	2134.1	2202.5	2339.1	2441.6	2456.7
152.5°	1859.9	1892.1	1924.4	1932.4	1999.7	2089.3	2134.1	2192.5	2309.1	2396.6	2408.1
155°	1926.6	1950.5	1974.3	1980.3	2031.5	2099.9	2134.1	2180.5	2273.4	2342.9	2350.5
157.5°	1976.0	1999.1	2022.4	2028.2	2063.5	2110.6	2134.1	2170.1	2242.3	2296.5	2301.8
160°	2009.3	2027.3	2045.5	2049.9	2078.0	2115.4	2134.1	2165.0	2226.9	2273.4	2276.4
162.5°	2042.7	2056.2	2069.7	2073.1	2093.5	2120.6	2134.1	2160.2	2212.5	2251.6	2254.5
165°	2078.9	2091.1	2103.4	2106.5	2115.7	2127.9	2134.1	2152.8	2190.1	2218.2	2221.2
167.5°	2112.3	2118.1	2123.9	2125.3	2133.1	2143.4	2148.6	2160.8	2185.3	2203.7	2205.0
170°	2134.1	2139.9	2145.7	2147.1	2147.5	2148.2	2148.6	2160.8	2185.3	2203.7	2203.7
172.5°	2145.7	2147.0	2148.3	2148.6	2148.6	2148.6	2148.6	2158.3	2177.6	2192.1	2191.0
175°	2161.6	2161.6	2161.6	2161.6	2157.3	2151.5	2148.6	2154.7	2167.0	2176.1	2176.1
177.5°	2161.6	2161.6	2161.6	2161.6	2158.3	2153.7	2151.5	2156.3	2165.9	2173.2	2171.9
180°	2161.6	2161.6	2161.6	2161.6	2161.6	2161.6	2161.6	2161.6	2161.6	2161.6	2161.6

TEST NUMBER: P938005

CATALOG NUMBER: SQ4-FB-125U-075D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	871.4	871.4
2.5°	930.3	924.7
5°	1196.5	1202.2
7.5°	1611.2	1608.4
10°	2003.5	2028.7
12.5°	2289.3	2294.9
15°	2463.1	2474.3
17.5°	2530.3	2533.1
20°	2533.1	2527.5
22.5°	2502.3	2496.7
25°	2465.9	2463.1
27.5°	2432.2	2435.0
30°	2418.2	2426.6
32.5°	2418.2	2432.2
35°	2423.8	2437.8
37.5°	2421.0	2437.8
40°	2409.8	2429.4
42.5°	2379.0	2393.0
45°	2331.4	2348.2
47.5°	2269.7	2280.9
50°	2191.3	2202.5
52.5°	2093.2	2096.0
55°	1975.5	1986.7
57.5°	1849.4	1852.2
60°	1709.3	1717.7
62.5°	1560.8	1560.8
65°	1403.9	1409.5
67.5°	1241.4	1255.4
70°	1076.1	1078.9
72.5°	913.5	913.5
75°	745.3	748.1
77.5°	585.6	585.6
80°	434.3	437.1
82.5°	299.8	305.4
85°	187.7	187.7
87.5°	86.9	78.5
90°	55.1	55.1
92.5°	220.8	177.0
95°	769.7	636.9
97.5°	1844.2	1591.4
100°	2657.1	2356.0
102.5°	3456.8	3199.0
105°	4476.4	4337.8
107.5°	5144.2	5177.7
110°	5398.9	5543.3



TEST NUMBER: P938005

CATALOG NUMBER: SQ4-FB-125U-075D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	5421.6	5643.4
115°	5277.8	5585.4
117.5°	4973.0	5314.1
120°	4727.3	5058.7
122.5°	4488.2	4815.1
125°	4146.9	4448.0
127.5°	3840.0	4094.0
130°	3659.1	3893.8
132.5°	3495.0	3705.2
135°	3270.1	3451.3
137.5°	3089.8	3238.1
140°	2966.0	3104.6
142.5°	2863.5	2982.7
145°	2709.6	2799.9
147.5°	2591.7	2666.5
150°	2517.4	2578.0
152.5°	2453.9	2499.7
155°	2380.9	2411.1
157.5°	2323.1	2344.4
160°	2288.7	2300.9
162.5°	2266.1	2277.7
165°	2233.5	2245.8
167.5°	2210.1	2215.3
170°	2203.7	2203.7
172.5°	2186.4	2181.9
175°	2176.1	2176.1
177.5°	2166.8	2161.6
180°	2161.6	2161.6

(END OF REPORT)