

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938401

Luminaire Tested: SQ4-FB-150U-075D-B40-1D-UNV-W2A-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938401
REPORT IS A COMBINATION OF REPORTS P933622 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-075D-B40-1D-UNV-W2A-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 24163.4 lumens
Efficiency: N/A
Efficacy: 126.6 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 190.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938401

CATALOG NUMBER: SQ4-FB-150U-075D-B40-1D-UNV-W2A-W-12

Luminous Intensity Polar Plot



TEST NUMBER: P938401

CATALOG NUMBER: SQ4-FB-150U-075D-B40-1D-UNV-W2A-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	88	84	81	83	79	76	73	62	60	58	46	45	43	32	31	30
2	84	77	71	66	75	69	64	59	54	50	47	40	38	36	27	26	25
3	76	67	60	54	68	60	54	49	47	43	39	35	32	30	24	22	21
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	21	19	17
5	64	52	44	38	57	47	40	35	37	32	28	28	24	21	19	17	15
6	58	47	39	33	52	42	35	30	33	28	24	25	21	18	17	15	13
7	54	42	34	28	48	38	31	26	30	25	21	22	19	16	15	13	11
8	50	38	30	25	44	34	27	23	27	22	18	20	17	14	14	12	10
9	46	34	27	22	41	31	24	20	24	20	16	18	15	12	13	10	9
10	43	31	24	19	38	28	22	18	22	18	14	17	13	11	12	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2756	2756	2756
5°	2693	3186	3705
10°	2444	4646	6142
15°	2078	6071	7416
20°	1692	7037	7558
25°	1412	7366	7404
30°	1191	7414	7390
35°	1054	7293	7581
40°	919	7135	7779
45°	833	7020	7810
50°	764	6917	7680
55°	733	6765	7340
60°	751	6471	6802
65°	783	6023	6064
70°	835	5255	5123
75°	930	4289	3998
80°	1024	2978	2693
85°	927	1583	1379

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 7810 cd/sqm

TEST NUMBER: P938401

CATALOG NUMBER: SQ4-FB-150U-075D-B40-1D-UNV-W2A-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.3	0.5
10°-20°	510.8	2.1
20°-30°	893.5	3.7
30°-40°	1150.3	4.8
40°-50°	1284.8	5.3
50°-60°	1230.5	5.1
60°-70°	975.2	4.0
70°-80°	573.4	2.4
80°-90°	169.5	0.7
90°-100°	1297.8	5.4
100°-110°	3412.1	14.1
110°-120°	3538.0	14.6
120°-130°	2837.9	11.7
130°-140°	2226.7	9.2
140°-150°	1709.1	7.1
150°-160°	1230.8	5.1
160°-170°	753.1	3.1
170°-180°	254.4	1.1
0°-30°	1519.6	6.3
0°-40°	2669.9	11.0
0°-60°	5185.2	21.5
0°-90°	6903.3	28.6
90°-120°	8247.9	34.1
90°-150°	15021.7	62.2
90°-180°	17260.0	71.4
0°-180°	24163.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	868	931	1049	1186	1229	80
15°	650	1200	2023	2452	2530	181
25°	415	1361	2410	2516	2518	191
35°	281	1301	2269	2398	2493	175
45°	192	1037	2006	2298	2401	148
55°	138	659	1702	1977	2031	125
65°	109	350	1264	1421	1441	108
75°	80	215	693	762	765	84
85°	29	66	172	189	192	30
90°	18	50	136	68	68	17
95°	172	672	2236	1153	784	190
105°	615	931	3772	5727	5343	652
115°	1092	1326	3022	6027	6880	1078
125°	1519	1703	2748	4644	5479	1348
135°	1810	1992	2662	3749	4251	1401
145°	2100	2234	2628	3199	3449	1315
155°	2373	2439	2628	2886	2970	1090
165°	2561	2595	2628	2732	2766	723
175°	2662	2662	2646	2680	2680	253
180°	2662	2662	2662	2662	2662	

TEST NUMBER: P938401

CATALOG NUMBER: SQ4-FB-150U-075D-B40-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	891.0	891.0	891.0	891.0	891.0	891.0	891.0	891.0	891.0	891.0	891.0
2.5°	891.0	891.0	896.7	899.6	905.3	908.2	913.9	919.7	936.9	939.7	945.4
5°	868.1	879.6	916.8	931.1	971.2	1025.7	1048.6	1085.9	1163.3	1186.2	1200.5
7.5°	833.7	859.5	951.2	974.1	1074.4	1217.7	1277.9	1358.1	1481.3	1541.5	1590.2
10°	779.3	833.7	997.0	1051.5	1214.9	1432.6	1544.3	1656.1	1842.3	1925.4	1956.9
12.5°	719.1	807.9	1045.7	1120.3	1355.2	1673.3	1807.9	1931.1	2143.1	2254.9	2272.0
15°	650.4	770.7	1091.7	1200.5	1504.2	1873.8	2022.8	2174.6	2372.3	2452.5	2472.6
17.5°	590.2	742.0	1134.6	1249.2	1618.8	2054.3	2206.1	2332.2	2492.6	2547.1	2561.4
20°	515.7	696.2	1163.3	1312.3	1739.2	2186.1	2332.2	2429.6	2538.5	2572.9	2578.6
22.5°	461.3	647.5	1180.5	1335.2	1819.4	2266.3	2389.5	2466.9	2541.4	2552.8	2555.7
25°	415.4	593.1	1177.6	1361.0	1888.1	2315.0	2409.6	2466.9	2509.8	2515.6	2515.6
27.5°	372.4	532.9	1166.2	1366.7	1939.7	2326.5	2401.0	2441.1	2461.1	2472.6	2472.6
30°	335.2	475.6	1137.5	1355.2	1962.6	2315.0	2375.2	2395.2	2415.3	2432.5	2441.1
32.5°	306.6	421.2	1094.5	1332.3	1965.5	2286.4	2329.3	2340.8	2369.5	2409.6	2423.9
35°	280.8	366.7	1045.7	1300.8	1948.3	2240.5	2269.2	2280.6	2337.9	2398.1	2418.2
37.5°	255.0	326.6	982.7	1246.4	1922.5	2186.1	2206.1	2226.2	2315.0	2386.6	2409.6
40°	229.2	292.2	908.2	1186.2	1882.4	2120.2	2137.4	2168.9	2286.4	2369.5	2392.4
42.5°	209.1	263.6	828.0	1123.2	1830.8	2045.7	2071.5	2117.3	2252.0	2340.8	2366.6
45°	192.0	234.9	742.0	1037.1	1764.9	1968.4	2005.6	2068.6	2211.9	2297.8	2320.7
47.5°	174.8	214.9	653.2	948.3	1693.3	1891.0	1939.7	2011.3	2157.4	2240.5	2260.6
50°	160.4	194.8	564.4	853.8	1616.0	1807.9	1865.2	1939.7	2088.7	2166.0	2191.8
52.5°	149.0	177.6	481.3	759.2	1527.1	1722.0	1787.9	1865.2	2005.6	2080.1	2097.3
55°	137.5	163.3	409.7	658.9	1435.5	1630.3	1701.9	1776.4	1913.9	1976.9	1988.4
57.5°	131.8	151.8	349.5	564.4	1338.1	1527.1	1607.4	1676.1	1805.0	1853.8	1865.2
60°	123.2	143.2	303.7	484.2	1232.0	1429.7	1498.5	1567.3	1676.1	1716.2	1724.8
62.5°	114.6	137.5	269.3	406.8	1123.2	1315.1	1383.9	1446.9	1538.6	1567.3	1578.7
65°	108.9	131.8	243.5	349.5	1011.3	1194.8	1263.6	1318.0	1392.5	1421.1	1426.9
67.5°	103.1	126.1	223.5	300.8	899.6	1074.4	1126.0	1177.6	1234.9	1263.6	1266.4
70°	94.5	120.3	206.3	266.4	785.0	936.9	979.8	1034.3	1080.1	1094.5	1103.1
72.5°	88.8	111.7	194.8	240.7	667.5	805.1	845.2	876.7	916.8	931.1	931.1
75°	80.2	100.3	183.4	214.9	547.2	658.9	693.3	724.8	756.4	762.1	753.5
77.5°	71.6	88.8	157.6	180.5	426.9	521.4	550.1	567.3	593.1	598.8	601.6
80°	60.2	77.4	123.2	140.4	309.4	383.9	404.0	418.3	441.2	441.2	446.9
82.5°	45.8	60.2	88.8	100.3	209.1	263.6	280.8	289.4	303.7	303.7	303.7
85°	28.6	37.2	57.3	65.9	126.1	160.4	171.9	174.8	186.2	189.1	189.1
87.5°	14.3	20.1	37.2	40.1	65.9	83.1	83.1	88.8	88.8	86.0	83.1
90°	17.9	32.2	46.5	50.0	78.6	116.7	135.8	120.7	90.5	67.9	67.9
92.5°	71.4	192.9	314.5	344.9	484.9	671.5	764.8	670.2	481.2	339.5	326.0
95°	171.5	393.8	616.3	671.8	1193.1	1888.0	2235.5	1994.8	1513.6	1152.6	1111.7
97.5°	296.6	492.8	688.9	738.0	1607.1	2765.8	3345.1	3193.0	2888.9	2660.7	2582.9
100°	393.1	571.0	748.9	793.4	1757.8	3043.5	3686.4	3697.5	3719.7	3736.4	3643.7
102.5°	475.3	641.3	807.3	848.8	1826.8	3130.9	3782.9	3976.7	4364.3	4655.0	4575.5
105°	614.7	755.3	895.9	931.0	1878.1	3140.8	3772.2	4206.6	5075.4	5727.0	5684.4
107.5°	757.7	888.7	1019.7	1052.5	1887.6	3001.0	3557.8	4163.7	5375.6	6284.6	6294.9
110°	854.2	972.5	1090.8	1120.4	1873.3	2877.1	3379.1	4056.6	5411.4	6427.5	6472.0

TEST NUMBER: P938401

CATALOG NUMBER: SQ4-FB-150U-075D-B40-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	948.9	1061.7	1174.5	1202.6	1873.9	2768.9	3216.4	3909.8	5296.4	6336.4	6404.7
115°	1091.9	1195.9	1299.9	1325.9	1891.2	2644.9	3021.7	3689.6	5025.4	6027.3	6122.0
117.5°	1233.0	1327.4	1422.0	1445.6	1926.2	2567.1	2887.6	3490.4	4696.0	5600.2	5705.3
120°	1315.1	1404.1	1493.0	1515.3	1954.9	2541.0	2834.1	3384.8	4486.3	5312.5	5414.6
122.5°	1395.5	1485.3	1575.1	1597.5	1996.0	2527.3	2793.0	3288.9	4280.9	5024.8	5125.5
125°	1518.9	1600.7	1682.5	1703.0	2051.4	2516.0	2748.3	3169.6	4012.2	4644.2	4736.9
127.5°	1618.9	1701.5	1784.1	1804.8	2106.7	2509.5	2710.8	3072.5	3796.0	4338.7	4416.9
130°	1672.6	1761.5	1850.4	1872.7	2147.2	2513.4	2696.4	3018.5	3662.6	4145.7	4217.9
132.5°	1728.0	1816.9	1905.8	1928.0	2180.0	2515.9	2683.9	2972.2	3548.9	3981.3	4046.0
135°	1810.1	1891.1	1972.2	1992.4	2215.8	2513.7	2662.5	2904.0	3386.8	3748.9	3804.7
137.5°	1894.1	1974.4	2054.6	2074.6	2269.4	2529.0	2658.9	2863.0	3271.3	3577.4	3623.1
140°	1963.9	2037.7	2111.6	2130.0	2302.1	2531.6	2646.4	2822.7	3175.4	3439.8	3482.5
142.5°	2017.4	2085.7	2154.0	2171.1	2329.5	2540.8	2646.4	2801.3	3111.0	3343.4	3380.1
145°	2099.7	2159.3	2218.8	2233.6	2365.2	2540.8	2628.5	2755.2	3008.5	3198.6	3226.4
147.5°	2181.8	2239.8	2297.7	2312.2	2417.7	2558.3	2628.5	2728.2	2927.6	3077.1	3100.1
150°	2235.5	2287.9	2340.3	2353.4	2445.1	2567.4	2628.5	2712.8	2881.1	3007.4	3026.0
152.5°	2290.9	2330.6	2370.2	2380.1	2462.9	2573.3	2628.5	2700.5	2844.2	2952.0	2966.1
155°	2373.1	2402.5	2431.8	2439.2	2502.3	2586.4	2628.5	2685.7	2800.2	2885.9	2895.3
157.5°	2433.8	2462.4	2490.9	2498.1	2541.5	2599.5	2628.5	2673.0	2762.0	2828.7	2835.3
160°	2474.9	2497.1	2519.4	2524.9	2559.5	2605.5	2628.5	2666.6	2742.9	2800.1	2803.9
162.5°	2515.9	2532.7	2549.3	2553.5	2578.5	2611.8	2628.5	2660.7	2725.1	2773.3	2776.9
165°	2560.6	2575.7	2590.8	2594.6	2605.9	2621.0	2628.5	2651.6	2697.6	2732.2	2736.0
167.5°	2601.8	2609.0	2616.0	2617.8	2627.4	2640.1	2646.4	2661.5	2691.7	2714.3	2715.9
170°	2628.5	2635.7	2642.9	2644.7	2645.3	2646.0	2646.4	2661.5	2691.7	2714.3	2714.3
172.5°	2642.9	2644.4	2646.0	2646.4	2646.4	2646.4	2646.4	2658.3	2682.2	2700.1	2698.6
175°	2662.5	2662.5	2662.5	2662.5	2657.2	2650.0	2646.4	2653.9	2669.0	2680.4	2680.4
177.5°	2662.5	2662.5	2662.5	2662.5	2658.3	2652.8	2650.0	2656.0	2667.9	2676.8	2675.1
180°	2662.5	2662.5	2662.5	2662.5	2662.5	2662.5	2662.5	2662.5	2662.5	2662.5	2662.5

TEST NUMBER: P938401

CATALOG NUMBER: SQ4-FB-150U-075D-B40-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	891.0	891.0
2.5°	951.2	945.4
5°	1223.5	1229.2
7.5°	1647.5	1644.6
10°	2048.6	2074.4
12.5°	2340.8	2346.5
15°	2518.4	2529.9
17.5°	2587.2	2590.1
20°	2590.1	2584.3
22.5°	2558.5	2552.8
25°	2521.3	2518.4
27.5°	2486.9	2489.8
30°	2472.6	2481.2
32.5°	2472.6	2486.9
35°	2478.3	2492.6
37.5°	2475.5	2492.6
40°	2464.0	2484.1
42.5°	2432.5	2446.8
45°	2383.8	2401.0
47.5°	2320.7	2332.2
50°	2240.5	2252.0
52.5°	2140.3	2143.1
55°	2019.9	2031.4
57.5°	1891.0	1893.9
60°	1747.7	1756.3
62.5°	1595.9	1595.9
65°	1435.5	1441.2
67.5°	1269.3	1283.6
70°	1100.3	1103.1
72.5°	934.0	934.0
75°	762.1	765.0
77.5°	598.8	598.8
80°	444.1	446.9
82.5°	306.6	312.3
85°	192.0	192.0
87.5°	88.8	80.2
90°	67.9	67.9
92.5°	272.0	218.0
95°	948.0	784.4
97.5°	2271.6	1960.2
100°	3272.9	2902.0
102.5°	4257.9	3940.1
105°	5513.7	5342.9
107.5°	6336.2	6377.5
110°	6650.0	6827.9

TEST NUMBER: P938401

CATALOG NUMBER: SQ4-FB-150U-075D-B40-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	6677.9	6951.2
115°	6500.8	6879.6
117.5°	6125.4	6545.5
120°	5822.7	6231.0
122.5°	5528.2	5930.8
125°	5107.8	5478.7
127.5°	4729.8	5042.7
130°	4507.0	4796.1
132.5°	4304.9	4563.8
135°	4027.9	4251.1
137.5°	3805.8	3988.4
140°	3653.3	3824.0
142.5°	3527.0	3673.9
145°	3337.6	3448.8
147.5°	3192.3	3284.3
150°	3100.7	3175.4
152.5°	3022.5	3078.8
155°	2932.5	2969.9
157.5°	2861.5	2887.6
160°	2819.0	2834.1
162.5°	2791.2	2805.5
165°	2751.1	2766.2
167.5°	2722.2	2728.6
170°	2714.3	2714.3
172.5°	2693.1	2687.6
175°	2680.4	2680.4
177.5°	2668.8	2662.5
180°	2662.5	2662.5

(END OF REPORT)