

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938307

Luminaire Tested: SQ4-FB-150U-050D-B50-1D-UNV-W2A-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938307
REPORT IS A COMBINATION OF REPORTS P933637 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-050D-B50-1D-UNV-W2A-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10705.5 lumens
Efficiency: N/A
Efficacy: 128.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 83.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938307

CATALOG NUMBER: SQ4-FB-150U-050D-B50-1D-UNV-W2A-W-6

Luminous Intensity Polar Plot



TEST NUMBER: P938307

CATALOG NUMBER: SQ4-FB-150U-050D-B50-1D-UNV-W2A-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21		
1	91	87	83	80	80	77	74	71	58	56	54	41	40	39	26	25	24	17		
2	83	75	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14		
3	75	66	59	53	66	59	53	48	45	40	37	32	29	27	20	18	17	12		
4	69	58	50	45	60	52	45	40	39	35	31	28	25	23	17	16	14	10		
5	63	51	44	38	55	46	39	34	35	30	27	25	22	19	15	14	12	8		
6	57	46	38	32	51	41	34	29	31	26	23	22	19	17	14	12	11	7		
7	53	41	33	28	47	37	30	25	28	23	20	20	17	14	12	11	9	6		
8	49	37	30	24	43	33	27	22	25	21	17	18	15	13	11	9	8	5		
9	45	34	26	21	40	30	24	19	23	18	15	16	13	11	10	9	7	5		
10	42	31	24	19	37	27	21	17	21	17	14	15	12	10	10	8	6	4		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1808	1808	1808
5°	1765	2088	2429
10°	1600	3044	4027
15°	1359	3975	4864
20°	1107	4606	4957
25°	923	4819	4856
30°	778	4848	4847
35°	688	4766	4972
40°	599	4660	5101
45°	542	4582	5122
50°	496	4512	5037
55°	475	4410	4814
60°	486	4214	4461
65°	505	3917	3976
70°	536	3414	3359
75°	592	2780	2622
80°	641	1925	1766
85°	560	1021	905

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5122 cd/sqm

TEST NUMBER: P938307

CATALOG NUMBER: SQ4-FB-150U-050D-B50-1D-UNV-W2A-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.8	0.4
10°-20°	167.5	1.6
20°-30°	293.0	2.7
30°-40°	377.2	3.5
40°-50°	421.3	3.9
50°-60°	403.5	3.8
60°-70°	319.8	3.0
70°-80°	188.0	1.8
80°-90°	57.2	0.5
90°-100°	634.7	5.9
100°-110°	1668.5	15.6
110°-120°	1730.1	16.2
120°-130°	1387.7	13.0
130°-140°	1088.9	10.2
140°-150°	835.8	7.8
150°-160°	601.9	5.6
160°-170°	368.3	3.4
170°-180°	124.4	1.2
0°-30°	498.3	4.7
0°-40°	875.5	8.2
0°-60°	1700.2	15.9
0°-90°	2265.2	21.2
90°-120°	4033.3	37.7
90°-150°	7345.7	68.6
90°-180°	8440.0	78.8
0°-180°	10705.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	292	292	292	292	292	
5°	285	305	344	389	403	26
15°	213	394	663	804	830	59
25°	136	446	790	825	826	63
35°	92	427	744	786	817	57
45°	63	340	658	754	787	49
55°	45	216	558	648	666	41
65°	36	115	414	466	472	35
75°	26	70	227	250	251	28
85°	9	22	56	62	63	10
90°	9	24	66	33	33	8
95°	84	329	1093	564	384	93
105°	301	455	1845	2801	2613	319
115°	534	648	1478	2947	3364	527
125°	743	833	1344	2271	2679	659
135°	885	974	1302	1833	2079	685
145°	1027	1092	1285	1564	1686	643
155°	1160	1193	1285	1411	1452	533
165°	1252	1269	1285	1336	1353	353
175°	1302	1302	1294	1311	1311	124
180°	1302	1302	1302	1302	1302	

TEST NUMBER: P938307

CATALOG NUMBER: SQ4-FB-150U-050D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	292.2	292.2	292.2	292.2	292.2	292.2	292.2	292.2	292.2	292.2	292.2
2.5°	292.2	292.2	294.0	295.0	296.9	297.9	299.7	301.6	307.2	308.1	310.0
5°	284.7	288.4	300.7	305.3	318.5	336.3	343.8	356.0	381.4	388.9	393.7
7.5°	273.4	281.9	311.9	319.4	352.3	399.3	419.0	445.3	485.7	505.5	521.5
10°	255.5	273.4	326.9	344.8	398.4	469.7	506.4	543.0	604.1	631.3	641.7
12.5°	235.8	265.0	342.9	367.3	444.4	548.6	592.8	633.3	702.7	739.4	745.0
15°	213.2	252.7	357.9	393.7	493.2	614.4	663.2	713.1	777.9	804.2	810.8
17.5°	193.5	243.3	372.0	409.7	530.8	673.6	723.4	764.8	817.3	835.2	839.9
20°	169.1	228.3	381.4	430.3	570.3	716.8	764.8	796.7	832.4	843.7	845.6
22.5°	151.2	212.3	387.0	437.8	596.5	743.1	783.5	808.8	833.3	837.1	838.0
25°	136.3	194.5	386.1	446.3	619.1	759.1	790.1	808.8	822.9	824.8	824.8
27.5°	122.2	174.8	382.4	448.1	636.1	762.9	787.3	800.4	807.0	810.8	810.8
30°	109.9	156.0	372.9	444.4	643.5	759.1	778.9	785.4	791.9	797.6	800.4
32.5°	100.5	138.1	358.8	436.8	644.5	749.7	763.8	767.6	776.9	790.1	794.8
35°	92.1	120.3	342.9	426.6	638.9	734.7	744.0	747.9	766.6	786.3	792.9
37.5°	83.6	107.1	322.2	408.7	630.4	716.8	723.4	730.0	759.1	782.6	790.1
40°	75.2	95.8	297.9	388.9	617.3	695.2	700.9	711.1	749.7	776.9	784.5
42.5°	68.6	86.4	271.5	368.3	600.3	670.8	679.2	694.2	738.4	767.6	776.0
45°	63.0	77.1	243.3	340.1	578.7	645.4	657.6	678.3	725.3	753.5	760.9
47.5°	57.3	70.4	214.2	310.9	555.3	620.1	636.1	659.5	707.4	734.7	741.2
50°	52.6	63.9	185.1	279.9	529.9	592.8	611.6	636.1	684.9	710.2	718.7
52.5°	48.8	58.3	157.8	249.0	500.7	564.6	586.3	611.6	657.6	682.1	687.7
55°	45.1	53.5	134.3	216.0	470.6	534.5	558.1	582.4	627.6	648.2	652.0
57.5°	43.2	49.8	114.6	185.1	438.7	500.7	527.1	549.6	591.9	607.8	611.6
60°	40.4	47.0	99.6	158.8	404.0	468.8	491.4	513.9	549.6	562.7	565.5
62.5°	37.5	45.1	88.4	133.4	368.3	431.2	453.7	474.5	504.5	513.9	517.6
65°	35.7	43.2	79.9	114.6	331.7	391.7	414.3	432.2	456.5	466.0	467.8
67.5°	33.8	41.4	73.3	98.6	295.0	352.3	369.2	386.1	404.9	414.3	415.3
70°	31.0	39.4	67.6	87.3	257.4	307.2	321.3	339.1	354.2	358.8	361.7
72.5°	29.1	36.6	63.9	78.9	218.9	263.9	277.1	287.5	300.7	305.3	305.3
75°	26.3	32.9	60.1	70.4	179.4	216.0	227.3	237.7	248.0	249.9	247.0
77.5°	23.4	29.1	51.7	59.2	140.0	171.0	180.4	186.1	194.5	196.3	197.3
80°	19.7	25.4	40.4	46.0	101.4	125.9	132.4	137.2	144.7	144.7	146.5
82.5°	15.0	19.7	29.1	32.9	68.6	86.4	92.1	94.9	99.6	99.6	99.6
85°	9.4	12.2	18.8	21.6	41.4	52.6	56.4	57.3	61.1	62.0	62.0
87.5°	4.7	6.5	12.2	13.2	21.6	27.3	27.3	29.1	29.1	28.2	27.3
90°	8.8	15.8	22.7	24.5	38.5	57.1	66.4	59.0	44.3	33.3	33.3
92.5°	34.9	94.3	153.8	168.7	237.1	328.4	374.0	327.7	235.4	166.1	159.4
95°	83.9	192.6	301.4	328.6	583.5	923.3	1093.2	975.5	740.1	563.6	543.6
97.5°	145.1	241.0	336.9	360.9	785.9	1352.5	1635.8	1561.5	1412.7	1301.2	1263.0
100°	192.2	279.3	366.2	388.0	859.6	1488.3	1802.7	1808.1	1819.1	1827.2	1781.9
102.5°	232.5	313.6	394.8	415.1	893.4	1531.0	1849.9	1944.6	2134.1	2276.3	2237.4
105°	300.6	369.3	438.0	455.2	918.4	1535.9	1844.6	2057.0	2481.9	2800.6	2779.7
107.5°	370.5	434.6	498.7	514.6	923.0	1467.5	1739.8	2036.1	2628.7	3073.2	3078.3
110°	417.7	475.6	533.4	547.9	916.1	1406.9	1652.3	1983.6	2646.2	3143.1	3164.9

TEST NUMBER: P938307

CATALOG NUMBER: SQ4-FB-150U-050D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	464.0	519.1	574.2	588.0	916.3	1354.0	1572.9	1911.9	2590.0	3098.5	3132.0
115°	533.9	584.8	635.7	648.4	924.8	1293.3	1477.6	1804.2	2457.4	2947.3	2993.7
117.5°	602.9	649.1	695.4	706.9	942.0	1255.4	1412.1	1706.9	2296.3	2738.5	2789.9
120°	643.2	686.7	730.2	741.0	955.9	1242.6	1385.9	1655.2	2193.9	2597.8	2647.7
122.5°	682.5	726.4	770.3	781.2	976.0	1235.9	1365.8	1608.3	2093.4	2457.2	2506.4
125°	742.7	782.7	822.8	832.8	1003.1	1230.4	1343.9	1550.0	1962.0	2271.0	2316.3
127.5°	791.7	832.0	872.4	882.5	1030.2	1227.1	1325.5	1502.4	1856.2	2121.6	2159.9
130°	817.9	861.4	905.0	915.8	1050.1	1229.1	1318.6	1476.1	1791.0	2027.2	2062.6
132.5°	845.0	888.5	932.0	942.9	1066.1	1230.4	1312.5	1453.4	1735.4	1946.8	1978.5
135°	885.2	924.8	964.4	974.3	1083.5	1229.1	1302.0	1420.1	1656.2	1833.3	1860.5
137.5°	926.2	965.5	1004.7	1014.5	1109.8	1236.7	1300.2	1400.1	1599.7	1749.4	1771.7
140°	960.3	996.5	1032.5	1041.6	1125.8	1238.0	1294.2	1380.4	1552.8	1682.1	1703.0
142.5°	986.5	1019.9	1053.4	1061.7	1139.2	1242.5	1294.2	1369.9	1521.3	1634.9	1652.8
145°	1026.7	1055.9	1085.0	1092.3	1156.7	1242.5	1285.4	1347.3	1471.2	1564.2	1577.7
147.5°	1066.9	1095.3	1123.6	1130.7	1182.3	1251.0	1285.4	1334.1	1431.5	1504.7	1516.0
150°	1093.2	1118.7	1144.3	1150.8	1195.6	1255.5	1285.4	1326.6	1408.8	1470.6	1479.7
152.5°	1120.2	1139.7	1159.1	1164.0	1204.4	1258.4	1285.4	1320.5	1390.8	1443.5	1450.4
155°	1160.4	1174.8	1189.2	1192.7	1223.6	1264.8	1285.4	1313.3	1369.2	1411.2	1415.8
157.5°	1190.1	1204.1	1218.1	1221.6	1242.9	1271.2	1285.4	1307.1	1350.7	1383.3	1386.4
160°	1210.3	1221.1	1231.9	1234.7	1251.6	1274.1	1285.4	1304.1	1341.3	1369.2	1371.1
162.5°	1230.4	1238.5	1246.6	1248.7	1260.9	1277.2	1285.4	1301.1	1332.5	1356.2	1357.9
165°	1252.2	1259.6	1266.9	1268.7	1274.3	1281.6	1285.4	1296.7	1319.2	1336.1	1338.0
167.5°	1272.3	1275.8	1279.3	1280.1	1284.8	1291.1	1294.2	1301.5	1316.3	1327.3	1328.1
170°	1285.4	1288.8	1292.4	1293.2	1293.5	1294.0	1294.2	1301.5	1316.3	1327.3	1327.3
172.5°	1292.4	1293.1	1294.0	1294.2	1294.2	1294.2	1294.2	1299.9	1311.6	1320.3	1319.6
175°	1302.0	1302.0	1302.0	1302.0	1299.4	1295.9	1294.2	1297.8	1305.2	1310.7	1310.7
177.5°	1302.0	1302.0	1302.0	1302.0	1299.9	1297.2	1295.8	1298.7	1304.6	1309.0	1308.3
180°	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0

TEST NUMBER: P938307

CATALOG NUMBER: SQ4-FB-150U-050D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	292.2	292.2
2.5°	311.9	310.0
5°	401.2	403.0
7.5°	540.2	539.3
10°	671.7	680.1
12.5°	767.6	769.4
15°	825.8	829.6
17.5°	848.4	849.3
20°	849.3	847.4
22.5°	838.9	837.1
25°	826.8	825.8
27.5°	815.5	816.4
30°	810.8	813.6
32.5°	810.8	815.5
35°	812.7	817.3
37.5°	811.7	817.3
40°	807.9	814.5
42.5°	797.6	802.3
45°	781.7	787.3
47.5°	760.9	764.8
50°	734.7	738.4
52.5°	701.8	702.7
55°	662.3	666.1
57.5°	620.1	621.0
60°	573.1	575.9
62.5°	523.3	523.3
65°	470.6	472.5
67.5°	416.2	420.9
70°	360.8	361.7
72.5°	306.3	306.3
75°	249.9	250.9
77.5°	196.3	196.3
80°	145.6	146.5
82.5°	100.5	102.4
85°	63.0	63.0
87.5°	29.1	26.3
90°	33.3	33.3
92.5°	133.0	106.6
95°	463.5	383.6
97.5°	1110.8	958.6
100°	1600.5	1419.1
102.5°	2082.1	1926.7
105°	2696.2	2612.7
107.5°	3098.5	3118.6
110°	3251.8	3338.9

TEST NUMBER: P938307

CATALOG NUMBER: SQ4-FB-150U-050D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3265.5	3399.1
115°	3178.9	3364.2
117.5°	2995.3	3200.8
120°	2847.4	3047.0
122.5°	2703.3	2900.2
125°	2497.7	2679.1
127.5°	2312.9	2465.9
130°	2204.0	2345.3
132.5°	2105.0	2231.7
135°	1969.7	2078.8
137.5°	1861.1	1950.4
140°	1786.5	1870.0
142.5°	1724.7	1796.5
145°	1632.1	1686.4
147.5°	1561.0	1606.1
150°	1516.3	1552.8
152.5°	1478.0	1505.6
155°	1434.0	1452.3
157.5°	1399.3	1412.1
160°	1378.5	1385.9
162.5°	1364.9	1371.9
165°	1345.2	1352.6
167.5°	1331.2	1334.3
170°	1327.3	1327.3
172.5°	1316.9	1314.2
175°	1310.7	1310.7
177.5°	1305.1	1302.0
180°	1302.0	1302.0

(END OF REPORT)