

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938602

Luminaire Tested: SQ4-FB-150U-125D-B40-1D-UNV-W2A-W-4

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938602
REPORT IS A COMBINATION OF REPORTS P933632 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-125D-B40-1D-UNV-W2A-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9644.6 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 83.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938602

CATALOG NUMBER: SQ4-FB-150U-125D-B40-1D-UNV-W2A-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P938602

CATALOG NUMBER: SQ4-FB-150U-125D-B40-1D-UNV-W2A-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	95	91	87	83	86	83	79	76	68	65	63	54	52	51	41	40	39
2	86	79	72	67	78	72	66	62	59	55	51	47	44	42	36	34	32
3	78	69	61	55	71	63	56	51	51	47	43	41	37	35	31	29	27
4	71	60	52	46	65	55	48	43	45	40	36	36	32	29	27	25	23
5	65	53	45	39	59	49	42	36	40	35	30	32	28	25	24	22	19
6	60	48	39	34	54	44	36	31	36	30	26	29	25	21	22	19	17
7	55	43	35	29	50	39	32	27	32	27	23	26	22	19	20	17	15
8	51	39	31	25	46	35	28	24	29	24	20	23	19	16	18	15	13
9	47	35	27	22	43	32	25	21	27	21	18	21	17	15	17	14	11
10	44	32	25	20	40	29	23	18	24	19	16	20	16	13	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4663	4663	4663
5°	4551	5385	6268
10°	4123	7845	10392
15°	3500	10242	12548
20°	2847	11860	12788
25°	2372	12403	12529
30°	1997	12471	12506
35°	1762	12254	12828
40°	1534	11975	13162
45°	1387	11767	13214
50°	1269	11578	12995
55°	1211	11306	12419
60°	1236	10796	11510
65°	1280	10024	10260
70°	1353	8726	8668
75°	1486	7096	6765
80°	1587	4905	4558
85°	1333	2586	2333

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 13214 cd/sqm

TEST NUMBER: P938602

CATALOG NUMBER: SQ4-FB-150U-125D-B40-1D-UNV-W2A-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.0	0.7
10°-20°	288.1	3.0
20°-30°	504.0	5.2
30°-40°	648.8	6.7
40°-50°	724.6	7.5
50°-60°	694.0	7.2
60°-70°	550.0	5.7
70°-80°	323.4	3.4
80°-90°	93.2	1.0
90°-100°	432.6	4.5
100°-110°	1137.4	11.8
110°-120°	1179.3	12.2
120°-130°	946.0	9.8
130°-140°	742.2	7.7
140°-150°	569.7	5.9
150°-160°	410.3	4.3
160°-170°	251.0	2.6
170°-180°	84.8	0.9
0°-30°	857.1	8.9
0°-40°	1505.8	15.6
0°-60°	2924.5	30.3
0°-90°	3891.2	40.3
90°-120°	2749.3	28.5
90°-150°	5007.2	51.9
90°-180°	5753.0	59.7
0°-180°	9644.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	502	502	502	502	502	
5°	490	525	591	669	693	45
15°	367	677	1141	1383	1427	102
25°	234	768	1359	1419	1420	108
35°	158	734	1280	1353	1406	99
45°	108	585	1131	1296	1354	84
55°	78	372	960	1115	1146	71
65°	61	197	713	802	813	61
75°	45	121	391	430	432	47
85°	16	37	97	107	108	17
90°	6	17	45	23	23	6
95°	57	224	745	384	262	63
105°	205	310	1257	1909	1781	217
115°	364	442	1007	2009	2293	359
125°	506	568	916	1548	1826	449
135°	603	664	888	1250	1417	467
145°	700	744	876	1066	1150	438
155°	791	813	876	962	990	363
165°	854	865	876	911	922	241
175°	888	888	882	894	894	84
180°	888	888	888	888	888	

TEST NUMBER: P938602

CATALOG NUMBER: SQ4-FB-150U-125D-B40-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	502.5	502.5	502.5	502.5	502.5	502.5	502.5	502.5	502.5	502.5	502.5
2.5°	502.5	502.5	505.8	507.4	510.6	512.3	515.5	518.8	528.4	530.0	533.3
5°	489.6	496.1	517.1	525.2	547.8	578.5	591.4	612.4	656.1	669.0	677.1
7.5°	470.2	484.8	536.5	549.4	605.9	686.7	720.7	766.0	835.4	869.3	896.8
10°	439.5	470.2	562.3	593.1	685.1	807.9	871.0	934.0	1039.0	1085.9	1103.7
12.5°	405.6	455.7	589.8	631.8	764.4	943.7	1019.7	1089.2	1208.7	1271.8	1281.4
15°	366.8	434.7	615.7	677.1	848.3	1056.8	1140.8	1226.5	1338.1	1383.2	1394.6
17.5°	332.9	418.6	639.9	704.6	913.0	1158.6	1244.3	1315.4	1405.9	1436.6	1444.6
20°	290.9	392.7	656.1	740.1	980.9	1233.0	1315.4	1370.3	1431.7	1451.1	1454.4
22.5°	260.1	365.2	665.7	753.0	1026.1	1278.2	1347.7	1391.3	1433.4	1439.9	1441.4
25°	234.4	334.5	664.2	767.5	1064.9	1305.7	1359.1	1391.3	1415.6	1418.8	1418.8
27.5°	210.1	300.5	657.7	770.8	1094.0	1312.2	1354.2	1376.8	1388.1	1394.6	1394.6
30°	189.1	268.3	641.6	764.4	1106.9	1305.7	1339.6	1350.9	1362.2	1372.0	1376.8
32.5°	173.0	237.5	617.3	751.4	1108.6	1289.5	1313.8	1320.2	1336.4	1359.1	1367.1
35°	158.3	206.9	589.8	733.6	1098.8	1263.7	1279.8	1286.3	1318.6	1352.6	1363.8
37.5°	143.8	184.2	554.3	703.0	1084.3	1233.0	1244.3	1255.6	1305.7	1346.1	1359.1
40°	129.3	164.8	512.3	669.0	1061.7	1195.8	1205.5	1223.3	1289.5	1336.4	1349.3
42.5°	117.9	148.7	467.0	633.5	1032.5	1153.8	1168.3	1194.2	1270.1	1320.2	1334.8
45°	108.3	132.6	418.6	584.9	995.4	1110.2	1131.2	1166.7	1247.5	1296.0	1308.9
47.5°	98.6	121.2	368.4	534.9	955.0	1066.5	1094.0	1134.4	1216.8	1263.7	1275.0
50°	90.5	109.9	318.3	481.5	911.4	1019.7	1052.0	1094.0	1178.0	1221.6	1236.2
52.5°	84.0	100.2	271.5	428.2	861.3	971.1	1008.4	1052.0	1131.2	1173.2	1182.9
55°	77.5	92.1	231.1	371.7	809.6	919.5	959.9	1001.9	1079.4	1115.0	1121.5
57.5°	74.3	85.7	197.1	318.3	754.6	861.3	906.6	945.4	1018.0	1045.5	1052.0
60°	69.5	80.8	171.3	273.1	694.9	806.4	845.2	883.9	945.4	968.0	972.8
62.5°	64.7	77.5	151.9	229.5	633.5	741.7	780.5	816.0	867.8	883.9	890.3
65°	61.4	74.3	137.3	197.1	570.4	673.8	712.6	743.4	785.4	801.5	804.8
67.5°	58.2	71.1	126.1	169.7	507.4	605.9	635.1	664.2	696.5	712.6	714.2
70°	53.3	67.9	116.3	150.3	442.7	528.4	552.7	583.3	609.2	617.3	622.2
72.5°	50.1	63.0	109.9	135.7	376.6	454.1	476.7	494.5	517.1	525.2	525.2
75°	45.3	56.5	103.4	121.2	308.7	371.7	391.1	408.8	426.6	429.8	425.0
77.5°	40.4	50.1	88.9	101.8	240.8	294.1	310.3	319.9	334.5	337.7	339.3
80°	33.9	43.6	69.5	79.2	174.5	216.5	227.9	235.9	248.9	248.9	252.1
82.5°	25.9	33.9	50.1	56.5	117.9	148.7	158.3	163.2	171.3	171.3	171.3
85°	16.1	21.0	32.3	37.1	71.1	90.5	96.9	98.6	105.0	106.7	106.7
87.5°	8.1	11.3	21.0	22.6	37.1	46.9	46.9	50.1	50.1	48.5	46.9
90°	5.9	10.7	15.5	16.7	26.3	39.0	45.3	40.2	30.2	22.6	22.6
92.5°	23.8	64.3	104.9	115.0	161.6	223.8	254.9	223.4	160.4	113.2	108.7
95°	57.2	131.3	205.4	223.9	397.7	629.3	745.2	665.0	504.5	384.2	370.5
97.5°	98.8	164.3	229.7	246.0	535.7	922.0	1115.1	1064.3	962.9	886.9	860.9
100°	131.0	190.3	249.6	264.4	585.9	1014.5	1228.8	1232.5	1240.0	1245.5	1214.6
102.5°	158.4	213.8	269.1	283.0	609.0	1043.6	1261.0	1325.5	1454.8	1551.7	1525.2
105°	204.9	251.8	298.6	310.4	626.0	1046.9	1257.4	1402.1	1691.8	1909.0	1894.8
107.5°	252.6	296.2	340.0	350.9	629.2	1000.4	1185.9	1387.9	1791.9	2094.9	2098.3
110°	284.7	324.1	363.7	373.5	624.5	959.0	1126.3	1352.2	1803.8	2142.5	2157.3

TEST NUMBER: P938602

CATALOG NUMBER: SQ4-FB-150U-125D-B40-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	316.3	353.9	391.6	400.9	624.7	923.0	1072.2	1303.3	1765.5	2112.2	2134.9
115°	364.0	398.6	433.3	442.0	630.4	881.7	1007.2	1229.8	1675.2	2009.1	2040.7
117.5°	411.0	442.5	474.1	481.9	642.1	855.8	962.5	1163.5	1565.3	1866.7	1901.8
120°	438.3	468.0	497.7	505.1	651.6	847.0	944.7	1128.2	1495.4	1770.9	1804.9
122.5°	465.2	495.1	525.1	532.5	665.3	842.5	931.0	1096.3	1427.0	1675.0	1708.5
125°	506.3	533.6	560.9	567.7	683.8	838.7	916.1	1056.5	1337.4	1548.1	1579.0
127.5°	539.7	567.2	594.7	601.6	702.2	836.5	903.6	1024.2	1265.4	1446.3	1472.3
130°	557.5	587.1	616.7	624.2	715.8	837.8	898.8	1006.2	1220.9	1381.9	1406.0
132.5°	576.0	605.7	635.3	642.7	726.7	838.7	894.6	990.7	1183.0	1327.1	1348.7
135°	603.4	630.4	657.3	664.1	738.6	837.8	887.5	968.0	1128.9	1249.6	1268.2
137.5°	631.4	658.1	684.8	691.5	756.5	843.1	886.3	954.3	1090.4	1192.5	1207.7
140°	654.7	679.3	703.9	710.0	767.4	843.9	882.1	940.9	1058.4	1146.6	1160.8
142.5°	672.5	695.2	718.0	723.7	776.5	846.9	882.1	933.8	1037.0	1114.5	1126.7
145°	699.9	719.8	739.6	744.5	788.4	847.0	876.2	918.4	1002.8	1066.2	1075.4
147.5°	727.2	746.6	765.9	770.8	805.9	852.8	876.2	909.4	975.8	1025.7	1033.3
150°	745.2	762.7	780.0	784.4	815.0	855.8	876.2	904.3	960.3	1002.5	1008.7
152.5°	763.6	776.9	790.1	793.4	821.0	857.8	876.2	900.2	948.1	984.0	988.7
155°	791.0	800.9	810.6	813.1	834.1	862.2	876.2	895.3	933.4	962.0	965.1
157.5°	811.3	820.8	830.3	832.7	847.2	866.6	876.2	891.0	920.6	942.9	945.1
160°	824.9	832.4	839.8	841.6	853.2	868.6	876.2	888.9	914.3	933.3	934.6
162.5°	838.7	844.2	849.8	851.2	859.5	870.7	876.2	886.9	908.4	924.4	925.6
165°	853.6	858.5	863.6	864.8	868.7	873.7	876.2	883.9	899.2	910.7	911.9
167.5°	867.2	869.6	872.0	872.6	875.7	880.0	882.1	887.2	897.2	904.8	905.3
170°	876.2	878.6	881.0	881.6	881.8	882.0	882.1	887.2	897.2	904.8	904.8
172.5°	881.0	881.5	882.0	882.1	882.1	882.1	882.1	886.1	894.1	900.0	899.5
175°	887.5	887.5	887.5	887.5	885.7	883.3	882.1	884.6	889.7	893.5	893.5
177.5°	887.5	887.5	887.5	887.5	886.1	884.3	883.4	885.4	889.3	892.3	891.7
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5

TEST NUMBER: P938602

CATALOG NUMBER: SQ4-FB-150U-125D-B40-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	502.5	502.5
2.5°	536.5	533.3
5°	690.0	693.2
7.5°	929.2	927.6
10°	1155.4	1170.0
12.5°	1320.2	1323.4
15°	1420.5	1426.9
17.5°	1459.2	1460.9
20°	1460.9	1457.6
22.5°	1443.0	1439.9
25°	1422.0	1420.5
27.5°	1402.6	1404.2
30°	1394.6	1399.5
32.5°	1394.6	1402.6
35°	1397.8	1405.9
37.5°	1396.2	1405.9
40°	1389.7	1401.0
42.5°	1372.0	1380.0
45°	1344.4	1354.2
47.5°	1308.9	1315.4
50°	1263.7	1270.1
52.5°	1207.1	1208.7
55°	1139.2	1145.7
57.5°	1066.5	1068.2
60°	985.8	990.6
62.5°	900.1	900.1
65°	809.6	812.8
67.5°	715.9	724.0
70°	620.6	622.2
72.5°	526.8	526.8
75°	429.8	431.5
77.5°	337.7	337.7
80°	250.5	252.1
82.5°	173.0	176.1
85°	108.3	108.3
87.5°	50.1	45.3
90°	22.6	22.6
92.5°	90.6	72.7
95°	316.0	261.5
97.5°	757.2	653.4
100°	1091.0	967.3
102.5°	1419.3	1313.4
105°	1837.9	1781.0
107.5°	2112.1	2125.8
110°	2216.7	2276.0

TEST NUMBER: P938602

CATALOG NUMBER: SQ4-FB-150U-125D-B40-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2226.0	2317.0
115°	2167.0	2293.2
117.5°	2041.8	2181.8
120°	1940.9	2077.0
122.5°	1842.8	1976.9
125°	1702.6	1826.2
127.5°	1576.6	1680.9
130°	1502.3	1598.7
132.5°	1434.9	1521.2
135°	1342.6	1417.0
137.5°	1268.6	1329.5
140°	1217.7	1274.6
142.5°	1175.7	1224.6
145°	1112.6	1149.6
147.5°	1064.1	1094.8
150°	1033.6	1058.4
152.5°	1007.5	1026.2
155°	977.5	990.0
157.5°	953.8	962.5
160°	939.6	944.7
162.5°	930.4	935.1
165°	917.0	922.1
167.5°	907.4	909.5
170°	904.8	904.8
172.5°	897.7	895.9
175°	893.5	893.5
177.5°	889.6	887.5
180°	887.5	887.5

(END OF REPORT)