

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936305

Luminaire Tested: SQ4-FB-025U-050D-B50-1D-UNV-W2A-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936305
REPORT IS A COMBINATION OF REPORTS P933429 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-050D-B50-1D-UNV-W2A-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7233.8 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 66
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936305

CATALOG NUMBER: SQ4-FB-025U-050D-B50-1D-UNV-W2A-W-12

Luminous Intensity Polar Plot



TEST NUMBER: P936305

CATALOG NUMBER: SQ4-FB-025U-050D-B50-1D-UNV-W2A-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68
1	100	95	91	87	93	89	86	82	78	75	73	68	66	64	59	57	56
2	90	82	76	70	84	77	71	66	68	63	59	59	55	52	51	48	46
3	82	72	64	57	76	67	60	55	59	53	49	51	47	43	44	41	38
4	75	63	54	48	69	59	52	46	52	46	41	45	40	37	39	35	32
5	68	56	47	41	63	52	45	39	46	40	35	40	35	31	35	31	28
6	63	50	41	35	58	47	39	33	41	35	30	36	31	27	31	27	24
7	58	45	36	30	54	42	34	29	37	31	26	33	27	23	28	24	21
8	53	40	32	26	50	38	31	25	34	27	23	30	24	21	26	22	18
9	50	37	29	23	46	35	27	22	31	25	20	27	22	18	24	19	16
10	46	34	26	21	43	32	25	20	28	22	18	25	20	16	22	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1808	1808	1808
5°	1767	2090	2430
10°	1603	3047	4029
15°	1363	3982	4864
20°	1110	4616	4958
25°	926	4831	4857
30°	782	4863	4848
35°	691	4784	4973
40°	603	4680	5103
45°	546	4605	5123
50°	502	4537	5038
55°	481	4437	4814
60°	493	4244	4462
65°	514	3950	3977
70°	548	3448	3360
75°	610	2813	2622
80°	672	1954	1767
85°	609	1038	904

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5123 cd/sqm

TEST NUMBER: P936305

CATALOG NUMBER: SQ4-FB-025U-050D-B50-1D-UNV-W2A-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.6	1.0
10°-20°	335.1	4.6
20°-30°	586.1	8.1
30°-40°	754.5	10.4
40°-50°	842.7	11.6
50°-60°	807.2	11.2
60°-70°	639.7	8.8
70°-80°	376.1	5.2
80°-90°	106.1	1.5
90°-100°	203.8	2.8
100°-110°	535.9	7.4
110°-120°	555.7	7.7
120°-130°	445.7	6.2
130°-140°	349.7	4.8
140°-150°	268.4	3.7
150°-160°	193.3	2.7
160°-170°	118.3	1.6
170°-180°	40.0	0.6
0°-30°	996.8	13.8
0°-40°	1751.3	24.2
0°-60°	3401.2	47.0
0°-90°	4523.1	62.5
90°-120°	1295.4	17.9
90°-150°	2359.2	32.6
90°-180°	2711.0	37.5
0°-180°	7233.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	584	584	584	584	584	
5°	570	611	688	778	806	53
15°	427	788	1327	1609	1659	119
25°	272	893	1580	1650	1652	126
35°	184	853	1488	1573	1635	115
45°	126	680	1316	1507	1575	97
55°	90	432	1116	1297	1332	82
65°	72	229	829	932	945	71
75°	53	141	455	500	502	55
85°	19	43	113	124	126	20
90°	3	8	21	11	11	4
95°	27	106	351	181	123	30
105°	97	146	592	899	839	102
115°	172	208	475	947	1080	169
125°	238	268	432	729	860	212
135°	284	313	418	589	668	220
145°	330	351	413	502	542	207
155°	373	383	413	453	466	171
165°	402	408	413	429	434	114
175°	418	418	416	421	421	40
180°	418	418	418	418	418	

TEST NUMBER: P936305

CATALOG NUMBER: SQ4-FB-025U-050D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	584.5	584.5	584.5	584.5	584.5	584.5	584.5	584.5	584.5	584.5	584.5
2.5°	584.5	584.5	588.2	590.1	593.8	595.7	599.5	603.3	614.6	616.4	620.2
5°	569.5	576.9	601.4	610.7	637.1	672.8	687.8	712.3	763.0	778.0	787.5
7.5°	546.9	563.8	623.9	638.9	704.8	798.8	838.2	890.8	971.6	1011.1	1043.0
10°	511.2	546.9	654.0	689.8	796.8	939.7	1012.9	1086.2	1208.4	1263.0	1283.6
12.5°	471.7	530.0	685.9	734.8	888.9	1097.5	1185.9	1266.7	1405.8	1479.1	1490.3
15°	426.7	505.6	716.0	787.5	986.7	1229.1	1326.8	1426.4	1556.1	1608.7	1621.9
17.5°	387.1	486.7	744.2	819.4	1061.9	1347.5	1447.0	1529.8	1635.1	1670.7	1680.2
20°	338.3	456.7	763.0	860.8	1140.8	1434.0	1529.8	1593.7	1665.1	1687.6	1691.4
22.5°	302.6	424.7	774.3	875.8	1193.4	1486.6	1567.3	1618.2	1667.0	1674.5	1676.3
25°	272.5	389.0	772.4	892.7	1238.5	1518.5	1580.5	1618.2	1646.3	1650.1	1650.1
27.5°	244.3	349.6	764.9	896.5	1272.3	1526.1	1574.9	1601.2	1614.3	1621.9	1621.9
30°	219.9	312.0	746.1	888.9	1287.3	1518.5	1558.0	1571.2	1584.3	1595.6	1601.2
32.5°	201.1	276.3	717.9	873.9	1289.2	1499.7	1527.9	1535.4	1554.2	1580.5	1589.9
35°	184.2	240.6	685.9	853.2	1278.0	1469.6	1488.4	1496.0	1533.5	1573.0	1586.1
37.5°	167.3	214.3	644.6	817.5	1261.0	1434.0	1447.0	1460.2	1518.5	1565.5	1580.5
40°	150.4	191.7	595.7	778.0	1234.7	1390.7	1402.0	1422.7	1499.7	1554.2	1569.2
42.5°	137.2	172.9	543.1	736.7	1200.9	1341.9	1358.8	1388.9	1477.1	1535.4	1552.3
45°	125.9	154.1	486.7	680.3	1157.7	1291.1	1315.5	1356.9	1450.9	1507.2	1522.2
47.5°	114.6	140.9	428.5	622.0	1110.7	1240.4	1272.3	1319.3	1415.1	1469.6	1482.8
50°	105.3	127.8	370.2	560.0	1059.9	1185.9	1223.4	1272.3	1370.1	1420.8	1437.7
52.5°	97.7	116.6	315.7	498.0	1001.7	1129.5	1172.7	1223.4	1315.5	1364.4	1375.7
55°	90.2	107.1	268.7	432.3	941.6	1069.3	1116.3	1165.2	1255.4	1296.8	1304.2
57.5°	86.5	99.6	229.3	370.2	877.7	1001.7	1054.3	1099.4	1183.9	1216.0	1223.4
60°	80.8	94.0	199.2	317.7	808.1	937.8	982.9	1028.0	1099.4	1125.8	1131.4
62.5°	75.2	90.2	176.6	266.8	736.7	862.6	907.8	949.0	1009.2	1028.0	1035.5
65°	71.5	86.5	159.7	229.3	663.4	783.7	828.8	864.5	913.4	932.1	935.9
67.5°	67.6	82.7	146.5	197.4	590.1	704.8	738.6	772.4	810.0	828.8	830.7
70°	62.0	78.9	135.3	174.8	514.9	614.6	642.8	678.5	708.5	717.9	723.6
72.5°	58.3	73.3	127.8	157.8	437.9	528.1	554.4	575.1	601.4	610.7	610.7
75°	52.6	65.8	120.3	140.9	358.9	432.3	454.8	475.5	496.1	499.9	494.3
77.5°	47.0	58.3	103.4	118.4	280.0	342.0	360.8	372.1	389.0	392.7	394.6
80°	39.5	50.7	80.8	92.1	203.0	251.8	265.0	274.4	289.4	289.4	293.2
82.5°	30.1	39.5	58.3	65.8	137.2	172.9	184.2	189.8	199.2	199.2	199.2
85°	18.8	24.5	37.5	43.2	82.7	105.3	112.7	114.6	122.2	124.0	124.0
87.5°	9.4	13.2	24.5	26.3	43.2	54.5	54.5	58.3	58.3	56.4	54.5
90°	2.8	5.0	7.3	7.8	12.3	18.3	21.3	19.0	14.2	10.6	10.6
92.5°	11.2	30.3	49.4	54.2	76.1	105.4	120.1	105.3	75.6	53.3	51.2
95°	26.9	61.8	96.8	105.5	187.4	296.5	351.1	313.3	237.7	181.0	174.6
97.5°	46.6	77.4	108.3	115.9	252.4	434.4	525.4	501.5	453.7	417.9	405.6
100°	61.7	89.7	117.6	124.6	276.1	478.0	579.0	580.8	584.2	586.8	572.3
102.5°	74.6	100.7	126.7	133.3	286.9	491.8	594.1	624.6	685.4	731.0	718.5
105°	96.6	118.6	140.7	146.2	295.0	493.2	592.4	660.6	797.1	899.4	892.7
107.5°	119.0	139.5	160.2	165.3	296.5	471.3	558.7	653.9	844.2	987.1	988.6
110°	134.1	152.7	171.3	176.0	294.2	451.9	530.7	637.1	849.8	1009.5	1016.5

TEST NUMBER: P936305

CATALOG NUMBER: SQ4-FB-025U-050D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	149.1	166.7	184.5	188.9	294.3	434.9	505.2	614.1	831.8	995.2	1005.9
115°	171.5	187.8	204.2	208.3	297.0	415.3	474.6	579.5	789.2	946.6	961.5
117.5°	193.6	208.5	223.3	227.1	302.5	403.2	453.6	548.3	737.6	879.5	896.1
120°	206.5	220.5	234.5	238.0	307.0	399.0	445.1	531.5	704.6	834.3	850.4
122.5°	219.2	233.3	247.3	250.9	313.5	396.9	438.6	516.5	672.3	789.1	804.9
125°	238.5	251.4	264.3	267.5	322.2	395.2	431.6	497.7	630.1	729.4	743.9
127.5°	254.2	267.2	280.2	283.5	330.9	394.1	425.7	482.5	596.2	681.4	693.7
130°	262.6	276.7	290.7	294.1	337.3	394.7	423.5	474.1	575.3	651.1	662.5
132.5°	271.4	285.3	299.3	302.8	342.4	395.2	421.5	466.8	557.4	625.3	635.5
135°	284.3	297.0	309.7	312.9	348.0	394.8	418.2	456.1	531.9	588.8	597.6
137.5°	297.5	310.1	322.6	325.8	356.4	397.2	417.6	449.6	513.7	561.8	569.0
140°	308.4	320.0	331.7	334.6	361.6	397.6	415.6	443.3	498.7	540.2	547.0
142.5°	316.8	327.6	338.3	341.0	365.8	399.0	415.6	439.9	488.6	525.1	530.9
145°	329.8	339.1	348.5	350.8	371.5	399.0	412.8	432.7	472.5	502.3	506.7
147.5°	342.7	351.7	360.9	363.1	379.7	401.8	412.8	428.5	459.8	483.3	486.9
150°	351.1	359.3	367.5	369.6	384.0	403.2	412.8	426.1	452.5	472.3	475.2
152.5°	359.8	366.0	372.2	373.8	386.8	404.1	412.8	424.1	446.7	463.6	465.9
155°	372.7	377.2	381.9	383.0	392.9	406.2	412.8	421.8	439.8	453.3	454.8
157.5°	382.2	386.7	391.3	392.4	399.2	408.3	412.8	419.8	433.7	444.2	445.2
160°	388.7	392.2	395.7	396.6	402.0	409.2	412.8	418.8	430.8	439.7	440.3
162.5°	395.2	397.8	400.4	401.1	405.0	410.2	412.8	417.9	428.0	435.5	436.1
165°	402.2	404.5	406.9	407.5	409.3	411.6	412.8	416.5	423.7	429.1	429.6
167.5°	408.6	409.7	410.9	411.1	412.6	414.6	415.6	418.0	422.7	426.3	426.6
170°	412.8	413.9	415.1	415.3	415.4	415.5	415.6	418.0	422.7	426.3	426.3
172.5°	415.1	415.3	415.5	415.6	415.6	415.6	415.6	417.5	421.2	424.0	423.8
175°	418.2	418.2	418.2	418.2	417.3	416.2	415.6	416.8	419.2	421.0	421.0
177.5°	418.2	418.2	418.2	418.2	417.5	416.7	416.2	417.1	419.0	420.4	420.1
180°	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2

TEST NUMBER: P936305

CATALOG NUMBER: SQ4-FB-025U-050D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	584.5	584.5
2.5°	623.9	620.2
5°	802.5	806.2
7.5°	1080.6	1078.8
10°	1343.7	1360.7
12.5°	1535.4	1539.1
15°	1652.0	1659.4
17.5°	1697.1	1698.9
20°	1698.9	1695.2
22.5°	1678.2	1674.5
25°	1653.8	1652.0
27.5°	1631.2	1633.2
30°	1621.9	1627.5
32.5°	1621.9	1631.2
35°	1625.6	1635.1
37.5°	1623.8	1635.1
40°	1616.2	1629.4
42.5°	1595.6	1605.0
45°	1563.6	1574.9
47.5°	1522.2	1529.8
50°	1469.6	1477.1
52.5°	1403.9	1405.8
55°	1325.0	1332.4
57.5°	1240.4	1242.2
60°	1146.4	1152.0
62.5°	1046.8	1046.8
65°	941.6	945.3
67.5°	832.6	841.9
70°	721.7	723.6
72.5°	612.7	612.7
75°	499.9	501.7
77.5°	392.7	392.7
80°	291.3	293.2
82.5°	201.1	204.8
85°	125.9	125.9
87.5°	58.3	52.6
90°	10.6	10.6
92.5°	42.8	34.3
95°	148.9	123.2
97.5°	356.8	307.8
100°	514.1	455.8
102.5°	668.7	618.8
105°	865.9	839.1
107.5°	995.2	1001.6
110°	1044.4	1072.3

TEST NUMBER: P936305

CATALOG NUMBER: SQ4-FB-025U-050D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1048.8	1091.7
115°	1021.0	1080.5
117.5°	962.0	1028.0
120°	914.5	978.6
122.5°	868.2	931.5
125°	802.1	860.4
127.5°	742.8	791.9
130°	707.9	753.3
132.5°	676.1	716.8
135°	632.6	667.6
137.5°	597.7	626.4
140°	573.8	600.6
142.5°	554.0	577.0
145°	524.2	541.6
147.5°	501.4	515.8
150°	487.0	498.7
152.5°	474.7	483.5
155°	460.6	466.4
157.5°	449.4	453.6
160°	442.7	445.1
162.5°	438.3	440.6
165°	432.1	434.4
167.5°	427.5	428.5
170°	426.3	426.3
172.5°	422.9	422.1
175°	421.0	421.0
177.5°	419.2	418.2
180°	418.2	418.2

(END OF REPORT)