

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938607

Luminaire Tested: SQ4-FB-150U-125D-B50-1D-UNV-W2A-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938607
REPORT IS A COMBINATION OF REPORTS P933640 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-125D-B50-1D-UNV-W2A-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14149.2 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 124.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938607

CATALOG NUMBER: SQ4-FB-150U-125D-B50-1D-UNV-W2A-W-6

Luminous Intensity Polar Plot



TEST NUMBER: P938607

CATALOG NUMBER: SQ4-FB-150U-125D-B50-1D-UNV-W2A-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	95	91	87	83	86	83	79	76	68	65	63	54	52	51	41	40	39
2	86	79	72	67	78	72	66	62	59	55	51	47	44	42	36	34	32
3	78	69	61	55	71	63	56	51	51	47	43	41	37	35	31	29	27
4	71	60	52	46	65	55	48	43	45	40	36	36	32	29	27	25	23
5	65	53	45	39	59	49	42	36	40	35	30	32	28	25	24	22	19
6	60	48	39	34	54	44	36	31	36	30	26	29	25	21	22	19	17
7	55	43	35	29	50	39	32	27	32	27	23	26	22	19	20	17	15
8	51	39	31	25	46	35	28	24	29	24	20	23	19	16	18	15	13
9	47	35	27	22	43	32	25	21	27	21	18	21	17	15	17	14	11
10	44	32	25	20	40	29	23	18	24	19	16	20	16	13	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4561	4561	4561
5°	4454	5270	6131
10°	4039	7681	10164
15°	3432	10033	12274
20°	2792	11623	12508
25°	2329	12160	12254
30°	1963	12234	12231
35°	1735	12027	12547
40°	1511	11760	12874
45°	1367	11563	12924
50°	1252	11385	12710
55°	1199	11127	12147
60°	1225	10634	11257
65°	1273	9885	10035
70°	1354	8615	8478
75°	1494	7019	6616
80°	1621	4862	4458
85°	1413	2574	2282

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 12924 cd/sqm

TEST NUMBER: P938607

CATALOG NUMBER: SQ4-FB-150U-125D-B50-1D-UNV-W2A-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.4	0.7
10°-20°	422.7	3.0
20°-30°	739.4	5.2
30°-40°	951.8	6.7
40°-50°	1063.1	7.5
50°-60°	1018.2	7.2
60°-70°	807.0	5.7
70°-80°	474.5	3.4
80°-90°	136.8	1.0
90°-100°	634.7	4.5
100°-110°	1668.5	11.8
110°-120°	1730.1	12.2
120°-130°	1387.7	9.8
130°-140°	1088.9	7.7
140°-150°	835.8	5.9
150°-160°	601.9	4.3
160°-170°	368.3	2.6
170°-180°	124.4	0.9
0°-30°	1257.5	8.9
0°-40°	2209.3	15.6
0°-60°	4290.6	30.3
0°-90°	5708.9	40.3
90°-120°	4033.3	28.5
90°-150°	7345.7	51.9
90°-180°	8440.0	59.7
0°-180°	14149.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	737	737	737	737	737	
5°	718	771	868	982	1017	66
15°	538	993	1674	2029	2094	150
25°	344	1126	1994	2082	2084	158
35°	232	1076	1878	1984	2063	145
45°	159	858	1660	1901	1987	123
55°	114	545	1408	1636	1681	104
65°	90	289	1046	1176	1192	89
75°	66	178	574	631	633	70
85°	24	54	142	156	159	25
90°	9	24	66	33	33	9
95°	84	329	1093	564	384	93
105°	301	455	1845	2801	2613	319
115°	534	648	1478	2947	3364	527
125°	743	833	1344	2271	2679	659
135°	885	974	1302	1833	2079	685
145°	1027	1092	1285	1564	1686	643
155°	1160	1193	1285	1411	1452	533
165°	1252	1269	1285	1336	1353	353
175°	1302	1302	1294	1311	1311	124
180°	1302	1302	1302	1302	1302	

TEST NUMBER: P938607

CATALOG NUMBER: SQ4-FB-150U-125D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	737.3	737.3	737.3	737.3	737.3	737.3	737.3	737.3	737.3	737.3	737.3
2.5°	737.3	737.3	742.1	744.4	749.2	751.6	756.3	761.0	775.2	777.6	782.4
5°	718.3	727.9	758.7	770.6	803.7	848.7	867.7	898.5	962.6	981.5	993.4
7.5°	689.9	711.2	787.1	806.0	889.1	1007.6	1057.4	1123.8	1225.7	1275.5	1315.8
10°	644.8	689.9	825.0	870.1	1005.3	1185.4	1277.9	1370.4	1524.5	1593.2	1619.3
12.5°	595.1	668.6	865.4	927.0	1121.4	1384.6	1496.0	1597.9	1773.4	1865.9	1880.0
15°	538.2	637.7	903.3	993.4	1244.6	1550.5	1673.8	1799.4	1963.1	2029.4	2046.0
17.5°	488.4	614.0	938.9	1033.7	1339.5	1699.9	1825.5	1929.8	2062.6	2107.7	2119.5
20°	426.7	576.1	962.6	1085.9	1439.1	1809.0	1929.8	2010.4	2100.6	2129.0	2133.7
22.5°	381.7	535.8	976.8	1104.8	1505.5	1875.3	1977.3	2041.3	2102.9	2112.4	2114.8
25°	343.8	490.7	974.4	1126.1	1562.4	1915.6	1993.9	2041.3	2076.8	2081.6	2081.6
27.5°	308.2	440.9	964.9	1130.9	1605.1	1925.1	1986.7	2020.0	2036.5	2046.0	2046.0
30°	277.4	393.6	941.2	1121.4	1624.0	1915.6	1965.4	1982.0	1998.6	2012.9	2020.0
32.5°	253.7	348.5	905.6	1102.4	1626.4	1891.9	1927.5	1936.9	1960.7	1993.9	2005.7
35°	232.4	303.5	865.4	1076.3	1612.2	1854.0	1877.7	1887.1	1934.6	1984.4	2001.0
37.5°	211.0	270.3	813.2	1031.3	1590.8	1809.0	1825.5	1842.1	1915.6	1974.8	1993.9
40°	189.7	241.8	751.6	981.5	1557.6	1754.4	1768.6	1794.7	1891.9	1960.7	1979.6
42.5°	173.1	218.1	685.2	929.3	1514.9	1692.8	1714.1	1752.0	1863.4	1936.9	1958.3
45°	158.9	194.4	614.0	858.3	1460.4	1628.7	1659.5	1711.7	1830.3	1901.4	1920.4
47.5°	144.6	177.8	540.5	784.7	1401.2	1564.7	1605.1	1664.3	1785.2	1854.0	1870.6
50°	132.7	161.2	467.1	706.5	1337.1	1496.0	1543.4	1605.1	1728.4	1792.3	1813.6
52.5°	123.3	147.0	398.3	628.3	1263.6	1424.8	1479.4	1543.4	1659.5	1721.2	1735.5
55°	113.8	135.1	339.0	545.3	1187.8	1349.0	1408.3	1469.9	1583.7	1635.9	1645.3
57.5°	109.1	125.6	289.3	467.1	1107.2	1263.6	1330.0	1386.9	1493.7	1533.9	1543.4
60°	101.9	118.5	251.3	400.7	1019.5	1183.0	1240.0	1296.9	1386.9	1420.1	1427.2
62.5°	94.8	113.8	222.9	336.6	929.3	1088.2	1145.1	1197.3	1273.1	1296.9	1306.3
65°	90.1	109.1	201.6	289.3	836.9	988.6	1045.5	1090.5	1152.2	1175.9	1180.7
67.5°	85.4	104.3	184.9	248.9	744.4	889.1	931.8	974.4	1021.8	1045.5	1047.9
70°	78.3	99.6	170.7	220.5	649.6	775.2	810.8	855.8	893.8	905.6	912.8
72.5°	73.5	92.5	161.2	199.1	552.4	666.2	699.4	725.4	758.7	770.6	770.6
75°	66.4	82.9	151.8	177.8	452.8	545.3	573.8	599.8	625.9	630.6	623.5
77.5°	59.3	73.5	130.4	149.3	353.2	431.5	455.2	469.4	490.7	495.5	497.9
80°	49.8	64.0	101.9	116.2	256.0	317.7	334.3	346.1	365.1	365.1	369.9
82.5°	37.9	49.8	73.5	82.9	173.1	218.1	232.4	239.5	251.3	251.3	251.3
85°	23.7	30.8	47.4	54.5	104.3	132.7	142.2	144.6	154.1	156.4	156.4
87.5°	11.9	16.6	30.8	33.2	54.5	68.7	68.7	73.5	73.5	71.2	68.7
90°	8.8	15.8	22.7	24.5	38.5	57.1	66.4	59.0	44.3	33.3	33.3
92.5°	34.9	94.3	153.8	168.7	237.1	328.4	374.0	327.7	235.4	166.1	159.4
95°	83.9	192.6	301.4	328.6	583.5	923.3	1093.2	975.5	740.1	563.6	543.6
97.5°	145.1	241.0	336.9	360.9	785.9	1352.5	1635.8	1561.5	1412.7	1301.2	1263.0
100°	192.2	279.3	366.2	388.0	859.6	1488.3	1802.7	1808.1	1819.1	1827.2	1781.9
102.5°	232.5	313.6	394.8	415.1	893.4	1531.0	1849.9	1944.6	2134.1	2276.3	2237.4
105°	300.6	369.3	438.0	455.2	918.4	1535.9	1844.6	2057.0	2481.9	2800.6	2779.7
107.5°	370.5	434.6	498.7	514.6	923.0	1467.5	1739.8	2036.1	2628.7	3073.2	3078.3
110°	417.7	475.6	533.4	547.9	916.1	1406.9	1652.3	1983.6	2646.2	3143.1	3164.9

TEST NUMBER: P938607

CATALOG NUMBER: SQ4-FB-150U-125D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	464.0	519.1	574.2	588.0	916.3	1354.0	1572.9	1911.9	2590.0	3098.5	3132.0
115°	533.9	584.8	635.7	648.4	924.8	1293.3	1477.6	1804.2	2457.4	2947.3	2993.7
117.5°	602.9	649.1	695.4	706.9	942.0	1255.4	1412.1	1706.9	2296.3	2738.5	2789.9
120°	643.2	686.7	730.2	741.0	955.9	1242.6	1385.9	1655.2	2193.9	2597.8	2647.7
122.5°	682.5	726.4	770.3	781.2	976.0	1235.9	1365.8	1608.3	2093.4	2457.2	2506.4
125°	742.7	782.7	822.8	832.8	1003.1	1230.4	1343.9	1550.0	1962.0	2271.0	2316.3
127.5°	791.7	832.0	872.4	882.5	1030.2	1227.1	1325.5	1502.4	1856.2	2121.6	2159.9
130°	817.9	861.4	905.0	915.8	1050.1	1229.1	1318.6	1476.1	1791.0	2027.2	2062.6
132.5°	845.0	888.5	932.0	942.9	1066.1	1230.4	1312.5	1453.4	1735.4	1946.8	1978.5
135°	885.2	924.8	964.4	974.3	1083.5	1229.1	1302.0	1420.1	1656.2	1833.3	1860.5
137.5°	926.2	965.5	1004.7	1014.5	1109.8	1236.7	1300.2	1400.1	1599.7	1749.4	1771.7
140°	960.3	996.5	1032.5	1041.6	1125.8	1238.0	1294.2	1380.4	1552.8	1682.1	1703.0
142.5°	986.5	1019.9	1053.4	1061.7	1139.2	1242.5	1294.2	1369.9	1521.3	1634.9	1652.8
145°	1026.7	1055.9	1085.0	1092.3	1156.7	1242.5	1285.4	1347.3	1471.2	1564.2	1577.7
147.5°	1066.9	1095.3	1123.6	1130.7	1182.3	1251.0	1285.4	1334.1	1431.5	1504.7	1516.0
150°	1093.2	1118.7	1144.3	1150.8	1195.6	1255.5	1285.4	1326.6	1408.8	1470.6	1479.7
152.5°	1120.2	1139.7	1159.1	1164.0	1204.4	1258.4	1285.4	1320.5	1390.8	1443.5	1450.4
155°	1160.4	1174.8	1189.2	1192.7	1223.6	1264.8	1285.4	1313.3	1369.2	1411.2	1415.8
157.5°	1190.1	1204.1	1218.1	1221.6	1242.9	1271.2	1285.4	1307.1	1350.7	1383.3	1386.4
160°	1210.3	1221.1	1231.9	1234.7	1251.6	1274.1	1285.4	1304.1	1341.3	1369.2	1371.1
162.5°	1230.4	1238.5	1246.6	1248.7	1260.9	1277.2	1285.4	1301.1	1332.5	1356.2	1357.9
165°	1252.2	1259.6	1266.9	1268.7	1274.3	1281.6	1285.4	1296.7	1319.2	1336.1	1338.0
167.5°	1272.3	1275.8	1279.3	1280.1	1284.8	1291.1	1294.2	1301.5	1316.3	1327.3	1328.1
170°	1285.4	1288.8	1292.4	1293.2	1293.5	1294.0	1294.2	1301.5	1316.3	1327.3	1327.3
172.5°	1292.4	1293.1	1294.0	1294.2	1294.2	1294.2	1294.2	1299.9	1311.6	1320.3	1319.6
175°	1302.0	1302.0	1302.0	1302.0	1299.4	1295.9	1294.2	1297.8	1305.2	1310.7	1310.7
177.5°	1302.0	1302.0	1302.0	1302.0	1299.9	1297.2	1295.8	1298.7	1304.6	1309.0	1308.3
180°	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0

TEST NUMBER: P938607

CATALOG NUMBER: SQ4-FB-150U-125D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	737.3	737.3
2.5°	787.1	782.4
5°	1012.4	1017.1
7.5°	1363.3	1360.8
10°	1695.1	1716.5
12.5°	1936.9	1941.7
15°	2083.9	2093.5
17.5°	2140.8	2143.2
20°	2143.2	2138.5
22.5°	2117.1	2112.4
25°	2086.3	2083.9
27.5°	2057.9	2060.2
30°	2046.0	2053.1
32.5°	2046.0	2057.9
35°	2050.8	2062.6
37.5°	2048.4	2062.6
40°	2038.9	2055.5
42.5°	2012.9	2024.7
45°	1972.5	1986.7
47.5°	1920.4	1929.8
50°	1854.0	1863.4
52.5°	1771.0	1773.4
55°	1671.4	1680.9
57.5°	1564.7	1567.1
60°	1446.2	1453.3
62.5°	1320.6	1320.6
65°	1187.8	1192.5
67.5°	1050.3	1062.1
70°	910.4	912.8
72.5°	772.9	772.9
75°	630.6	633.0
77.5°	495.5	495.5
80°	367.4	369.9
82.5°	253.7	258.4
85°	158.9	158.9
87.5°	73.5	66.4
90°	33.3	33.3
92.5°	133.0	106.6
95°	463.5	383.6
97.5°	1110.8	958.6
100°	1600.5	1419.1
102.5°	2082.1	1926.7
105°	2696.2	2612.7
107.5°	3098.5	3118.6
110°	3251.8	3338.9

TEST NUMBER: P938607

CATALOG NUMBER: SQ4-FB-150U-125D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3265.5	3399.1
115°	3178.9	3364.2
117.5°	2995.3	3200.8
120°	2847.4	3047.0
122.5°	2703.3	2900.2
125°	2497.7	2679.1
127.5°	2312.9	2465.9
130°	2204.0	2345.3
132.5°	2105.0	2231.7
135°	1969.7	2078.8
137.5°	1861.1	1950.4
140°	1786.5	1870.0
142.5°	1724.7	1796.5
145°	1632.1	1686.4
147.5°	1561.0	1606.1
150°	1516.3	1552.8
152.5°	1478.0	1505.6
155°	1434.0	1452.3
157.5°	1399.3	1412.1
160°	1378.5	1385.9
162.5°	1364.9	1371.9
165°	1345.2	1352.6
167.5°	1331.2	1334.3
170°	1327.3	1327.3
172.5°	1316.9	1314.2
175°	1310.7	1310.7
177.5°	1305.1	1302.0
180°	1302.0	1302.0

(END OF REPORT)