

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P621898

Luminaire Tested: VLT-FB-150U-075D-930-UNV-STD-W-4

Issue Date: 9/2/2020

**Test Information**

Test Method: LM-79-2019  
Report Number: P621898  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2203-563-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 9/2/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: VLT-FB-150U-075D-930-UNV-STD-W-4  
Description: CORELITE VAULT SUSPENDED LED LUMINAIRE  
LIGHT SHAPING LENS - BATWING  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7306.8 lumens  
Efficiency: N/A  
Efficacy: 104.1 lumens/watt  
Spacing Criteria (0/90/45): 1.05 / 1.83 / 1.75  
Luminous Opening: Rectangular (W 0.38' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 70.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P621898  
CATALOG NUMBER: VLT-FB-150U-075D-930-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P621898

CATALOG NUMBER: VLT-FB-150U-075D-930-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	48	46	35	34	33	27
2	86	79	73	68	77	71	66	62	57	53	51	43	41	39	31	30	29	23
3	78	70	63	57	70	63	57	52	50	46	43	39	36	34	28	26	25	20
4	72	62	54	49	64	56	49	45	45	40	37	35	31	29	25	23	22	17
5	66	55	47	42	59	50	43	38	40	35	32	31	28	25	23	21	19	15
6	61	49	42	36	54	45	38	33	36	31	28	28	25	22	21	18	17	14
7	56	44	37	31	50	40	34	29	33	28	24	25	22	20	19	17	15	12
8	52	40	33	28	47	37	30	26	30	25	21	23	20	17	17	15	13	11
9	48	37	29	25	43	33	27	23	27	22	19	21	18	16	16	14	12	10
10	45	33	26	22	40	30	24	20	25	20	17	20	16	14	15	12	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4532	4532	4532
5°	4493	4817	5159
10°	4405	5696	7033
15°	4272	6942	8563
20°	4068	7998	8998
25°	3852	8649	9086
30°	3605	8849	9040
35°	3362	8849	8680
40°	3162	8573	8405
45°	3009	8310	4025
50°	2923	7867	3467
55°	2842	5267	2746
60°	2763	3205	1989
65°	2703	2442	2070
70°	2667	2127	2127
75°	2598	2207	2135
80°	2281	2227	2120
85°	1688	2322	2009

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 8310 cd/sqm



TEST NUMBER: P621898

CATALOG NUMBER: VLT-FB-150U-075D-930-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.1	0.9
10°-20°	251.1	3.4
20°-30°	425.3	5.8
30°-40°	515.9	7.1
40°-50°	454.1	6.2
50°-60°	281.0	3.8
60°-70°	152.4	2.1
70°-80°	86.8	1.2
80°-90°	30.5	0.4
90°-100°	115.4	1.6
100°-110°	822.3	11.3
110°-120°	1116.3	15.3
120°-130°	908.6	12.4
130°-140°	730.8	10.0
140°-150°	576.1	7.9
150°-160°	421.3	5.8
160°-170°	261.7	3.6
170°-180°	89.2	1.2
0°-30°	744.5	10.2
0°-40°	1260.4	17.2
0°-60°	1995.5	27.3
0°-90°	2265.1	31.0
90°-120°	2054.0	28.1
90°-150°	4269.5	58.4
90°-180°	5042.0	69.0
0°-180°	7306.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	632	632	632	632	632	
5°	624	644	669	697	716	59
15°	575	663	934	1105	1153	161
25°	486	666	1092	1125	1148	223
35°	384	617	1010	996	991	241
45°	296	507	819	694	397	230
55°	227	354	421	243	220	203
65°	159	199	144	123	122	158
75°	94	82	80	78	77	98
85°	20	28	28	26	24	25
90°	0	6	12	18	18	3
95°	47	88	47	53	65	53
105°	183	281	1068	1365	903	193
115°	325	394	921	1914	2237	322
125°	466	530	868	1517	1794	414
135°	578	642	874	1250	1434	445
145°	685	742	880	1089	1204	430
155°	803	832	897	987	1033	369
165°	891	903	921	945	962	250
175°	939	944	939	932	927	89
180°	939	939	939	939	939	



TEST NUMBER: P621898

CATALOG NUMBER: VLT-FB-150U-075D-930-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	631.5	631.5	631.5	631.5	631.5
2.5°	629.4	636.5	639.7	645.9	648.9
5°	623.8	643.9	668.7	697.4	716.2
7.5°	613.8	649.7	728.3	818.7	857.4
10°	604.5	653.5	781.7	912.5	965.2
12.5°	594.3	657.3	844.3	1002.9	1056.6
15°	575.0	662.9	934.4	1104.9	1152.6
17.5°	550.1	666.3	1012.4	1158.9	1189.6
20°	532.7	666.9	1047.4	1165.7	1178.3
22.5°	516.2	667.6	1072.0	1149.2	1159.8
25°	486.5	665.9	1092.3	1124.9	1147.5
27.5°	456.7	658.5	1082.3	1108.6	1124.9
30°	435.1	651.0	1067.9	1089.7	1091.0
32.5°	414.6	638.5	1046.3	1052.7	1050.9
35°	383.8	617.2	1010.1	995.9	990.9
37.5°	355.0	589.0	957.3	934.4	933.1
40°	337.6	568.5	915.2	893.4	897.2
42.5°	321.1	545.0	877.2	851.7	781.2
45°	296.5	507.3	818.9	694.0	396.6
47.5°	275.2	464.4	752.9	371.8	341.4
50°	261.8	435.0	704.7	326.9	310.6
52.5°	248.5	407.6	642.0	294.0	272.6
55°	227.2	353.9	421.0	243.3	219.5
57.5°	206.9	297.5	257.2	189.1	163.3
60°	192.5	264.1	223.3	152.4	138.6
62.5°	179.2	236.7	190.5	135.2	132.5
65°	159.2	199.3	143.8	123.2	121.9
67.5°	140.4	163.8	109.6	110.9	109.6
70°	127.1	138.4	101.4	102.7	101.4
72.5°	114.7	114.0	93.2	92.4	91.1
75°	93.7	82.4	79.6	78.3	77.0
77.5°	71.6	60.8	64.2	62.9	61.6
80°	55.2	51.4	53.9	52.6	51.3
82.5°	40.8	42.1	43.6	41.3	40.0
85°	20.5	28.1	28.2	25.6	24.4
87.5°	6.2	13.3	13.7	12.8	11.8
90°	0.0	5.8	11.8	17.7	17.7
92.5°	14.2	19.9	26.0	36.7	41.3
95°	47.2	87.6	47.2	53.4	64.9
97.5°	83.8	168.1	347.1	102.4	88.5
100°	112.2	210.3	696.5	205.0	135.8
102.5°	140.5	243.2	942.1	541.0	296.3
105°	183.0	281.1	1068.4	1364.9	903.1
107.5°	225.5	299.4	1020.0	1986.4	1860.6
110°	253.8	323.1	991.7	2087.3	2243.1



TEST NUMBER: P621898

CATALOG NUMBER: VLT-FB-150U-075D-930-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	282.2	351.4	963.3	2028.3	2290.3
115°	324.7	393.9	920.8	1914.0	2237.2
117.5°	368.3	436.4	910.2	1790.2	2122.7
120°	401.4	464.9	891.3	1696.1	2042.4
122.5°	425.0	493.1	867.7	1615.2	1933.8
125°	466.3	529.8	867.7	1517.4	1794.5
127.5°	500.6	565.2	868.9	1404.0	1677.6
130°	519.5	588.7	873.6	1328.1	1587.9
132.5°	543.1	612.3	873.6	1294.0	1507.6
135°	578.5	642.0	873.6	1249.7	1434.4
137.5°	608.0	676.1	873.6	1200.7	1358.8
140°	631.6	695.1	873.6	1172.0	1316.3
142.5°	655.2	714.1	878.3	1138.8	1273.8
145°	684.7	742.4	879.5	1088.8	1204.2
147.5°	720.1	770.9	886.6	1052.7	1141.6
150°	743.8	789.9	891.3	1028.8	1103.8
152.5°	767.4	808.9	891.3	1009.6	1070.8
155°	802.8	831.6	897.2	986.8	1033.0
157.5°	831.1	858.8	904.3	972.4	1005.8
160°	850.0	873.1	909.0	962.8	991.7
162.5°	864.2	887.3	913.8	957.9	977.5
165°	891.3	902.9	920.8	944.9	962.2
167.5°	906.7	917.1	926.7	938.8	949.2
170°	920.8	926.6	926.7	938.7	944.5
172.5°	925.6	936.0	931.5	934.0	939.7
175°	938.6	944.3	938.6	932.5	926.7
177.5°	938.6	943.2	938.6	938.5	933.8
180°	938.6	938.6	938.6	938.6	938.6

(END OF REPORT)