

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427753

Luminaire Tested: SQ2W-F-K-100U-075D-L830-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427753
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-20)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-F-K-100U-075D-L830-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7738.4 lumens
Efficiency: N/A
Efficacy: 129.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427753

CATALOG NUMBER: SQ2W-F-K-100U-075D-L830-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427753

CATALOG NUMBER: SQ2W-F-K-100U-075D-L830-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44				44
1	96	92	88	84	88	84	81	78	70	67	65	56	55	53	44	43	42				36	
2	87	80	74	69	80	73	68	64	61	57	54	49	47	44	39	37	35				30	
3	80	70	63	57	73	64	58	53	53	49	45	43	40	37	34	32	30				25	
4	73	62	54	48	66	57	50	45	47	42	38	39	35	32	30	28	25				22	
5	67	55	47	41	61	51	44	38	42	37	33	35	31	27	27	24	22				19	
6	61	49	41	35	56	45	38	33	38	33	28	31	27	24	25	22	19				16	
7	57	44	36	31	52	41	34	29	34	29	25	28	24	21	22	19	17				14	
8	53	40	33	27	48	37	30	25	31	26	22	26	22	19	21	18	15				13	
9	49	37	29	24	45	34	27	23	29	23	20	24	20	17	19	16	14				12	
10	46	34	26	22	42	31	25	20	26	21	18	22	18	15	18	15	13				10	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19279	19279	19279	19279
5°	19163	19381	19163	19381
10°	19095	19315	19095	19315
15°	18990	19229	18990	19229
20°	18871	19058	18871	19058
25°	18666	18832	18666	18832
30°	18468	18593	18468	18593
35°	18232	18348	18232	18348
40°	18025	18079	18025	18079
45°	17762	17762	17762	17762
50°	17404	17447	17404	17447
55°	16996	17019	16996	17019
60°	16536	16536	16536	16536
65°	16000	15935	16000	15935
70°	15243	15087	15243	15087
75°	14217	13899	14217	13899
80°	12664	12041	12664	12041
85°	10133	8577	10133	8577

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 17881 cd/sqm



TEST NUMBER: P1427753

CATALOG NUMBER: SQ2W-F-K-100U-075D-L830-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.0	1.5
10°-20°	322.8	4.2
20°-30°	486.0	6.3
30°-40°	581.1	7.5
40°-50°	600.1	7.8
50°-60°	541.2	7.0
60°-70°	414.6	5.4
70°-80°	239.6	3.1
80°-90°	68.4	0.9
90°-100°	119.2	1.5
100°-110°	347.5	4.5
110°-120°	567.1	7.3
120°-130°	719.6	9.3
130°-140°	770.0	9.9
140°-150°	719.0	9.3
150°-160°	591.6	7.6
160°-170°	396.8	5.1
170°-180°	140.9	1.8
0°-30°	921.8	11.9
0°-40°	1502.9	19.4
0°-60°	2644.2	34.2
0°-90°	3366.9	43.5
90°-120°	1033.7	13.4
90°-150°	3242.2	41.9
90°-180°	4371.0	56.5
0°-180°	7738.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1194	1194	1194	1194	1194	
5°	1182	1196	1182	1196	1182	112
15°	1136	1150	1136	1150	1136	320
25°	1048	1057	1048	1057	1048	483
35°	925	931	925	931	925	579
45°	778	778	778	778	778	599
55°	604	605	604	605	604	539
65°	419	417	419	417	419	414
75°	228	223	228	223	228	241
85°	55	46	55	46	55	64
90°	4	33	4	65	4	6
95°	47	35	47	204	47	57
105°	221	354	221	487	221	235
115°	423	587	423	723	423	417
125°	626	930	626	886	626	560
135°	851	1217	851	982	851	658
145°	1087	1403	1087	1003	1087	680
155°	1292	1524	1292	1040	1292	594
165°	1428	1589	1428	1198	1428	402
175°	1493	1556	1493	1405	1493	142
180°	1497	1497	1497	1497	1497	



TEST NUMBER: P1427753

CATALOG NUMBER: SQ2W-F-K-100U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1194.1	1194.1	1194.1	1194.1	1194.1	1194.1	1194.1	1194.1	1194.1	1194.1	1194.1
2.5°	1188.1	1193.8	1199.4	1197.0	1192.0	1190.0	1191.2	1192.3	1192.9	1193.5	1192.9
5°	1182.4	1189.8	1197.3	1194.7	1188.7	1186.1	1186.8	1188.3	1192.1	1195.8	1192.1
7.5°	1172.8	1180.2	1187.7	1185.3	1179.6	1177.2	1178.1	1179.8	1183.7	1187.6	1183.7
10°	1164.7	1172.2	1179.6	1177.0	1171.0	1168.8	1170.3	1172.2	1175.2	1178.1	1175.2
12.5°	1154.6	1162.1	1169.6	1167.4	1162.0	1159.8	1160.7	1162.2	1165.4	1168.7	1165.4
15°	1136.1	1143.6	1151.1	1149.0	1143.8	1141.7	1142.8	1144.4	1147.4	1150.4	1147.4
17.5°	1113.7	1120.8	1127.8	1125.9	1121.0	1119.2	1120.5	1122.1	1124.7	1127.4	1124.7
20°	1098.3	1105.0	1111.7	1109.8	1104.9	1102.6	1103.0	1104.0	1106.6	1109.2	1106.6
22.5°	1079.4	1086.1	1092.9	1091.1	1086.6	1083.9	1083.1	1083.3	1086.5	1089.7	1086.5
25°	1047.8	1054.5	1061.3	1059.9	1055.7	1053.1	1052.0	1051.8	1054.4	1057.1	1054.4
27.5°	1014.8	1020.4	1026.1	1024.9	1021.4	1019.3	1018.6	1018.5	1020.4	1022.2	1020.4
30°	990.6	996.2	1001.8	1000.4	996.7	994.4	993.7	993.6	995.5	997.3	995.5
32.5°	965.1	970.4	975.7	973.7	969.4	967.2	967.0	967.4	969.6	971.8	969.6
35°	925.0	929.5	934.0	932.0	927.9	926.1	926.4	927.2	929.0	930.9	929.0
37.5°	884.8	888.3	891.7	889.7	885.9	884.0	883.9	884.2	885.8	887.4	885.8
40°	855.2	859.0	862.7	860.6	856.4	854.2	853.8	854.0	855.9	857.8	855.9
42.5°	825.0	827.8	830.6	828.7	825.2	823.6	823.8	824.2	825.2	826.1	825.2
45°	777.9	780.5	783.1	781.2	777.9	776.2	776.2	776.4	777.1	777.9	777.1
47.5°	728.6	730.6	732.6	731.2	728.5	727.0	726.6	726.5	727.7	728.9	727.7
50°	692.9	695.5	698.2	696.9	694.2	692.6	691.8	691.6	693.1	694.6	693.1
52.5°	657.9	660.9	663.8	662.5	659.9	658.1	657.0	656.6	657.8	659.0	657.8
55°	603.8	607.2	610.5	609.7	607.4	605.6	604.1	603.1	603.9	604.6	603.9
57.5°	548.5	551.7	555.0	554.4	552.5	550.6	548.8	547.7	548.8	549.8	548.8
60°	512.1	515.1	518.1	517.2	514.9	513.1	511.6	510.6	511.4	512.1	511.4
62.5°	475.1	478.1	481.1	479.9	477.4	475.4	473.9	473.0	473.7	474.5	473.7
65°	418.8	421.4	424.0	423.0	420.7	418.9	417.4	416.4	416.7	417.1	416.7
67.5°	361.9	364.2	366.4	365.4	363.2	361.0	358.9	357.4	358.0	358.6	358.0
70°	322.9	325.2	327.4	326.6	324.7	322.8	321.0	319.6	319.6	319.6	319.6
72.5°	285.2	287.2	289.1	288.0	285.8	284.0	282.4	281.2	281.2	281.2	281.2
75°	227.9	229.0	230.1	229.6	228.5	227.0	225.1	223.6	223.2	222.8	223.2
77.5°	172.6	172.6	172.6	171.5	170.1	168.7	167.2	166.1	165.6	165.2	165.6
80°	136.2	136.2	136.2	135.4	134.3	133.1	132.0	131.0	130.3	129.5	130.3
82.5°	102.6	102.0	101.4	100.4	99.3	97.9	96.1	95.0	95.8	96.5	95.8
85°	54.7	53.9	53.2	52.1	51.0	49.7	48.2	47.0	46.6	46.3	46.6
87.5°	17.7	18.3	19.3	19.6	19.7	18.9	17.7	17.0	17.0	16.7	17.0
90°	4.5	10.6	18.1	24.2	28.7	30.2	30.2	31.8	33.3	33.3	33.3
92.5°	16.6	26.3	26.6	26.6	32.4	35.1	37.5	37.8	39.3	39.3	39.3
95°	46.9	51.4	77.1	75.6	51.4	40.8	34.8	34.8	34.8	34.8	34.8
97.5°	89.5	96.2	100.4	134.6	142.2	137.3	111.9	94.1	84.1	79.5	84.1
100°	127.0	130.1	139.1	140.6	178.4	214.7	196.6	173.9	166.4	161.8	166.4
102.5°	164.5	166.4	180.3	186.6	195.4	216.0	278.9	271.9	266.8	265.9	266.8
105°	220.8	222.3	248.0	260.1	266.2	266.2	264.7	294.9	343.3	353.9	343.3
107.5°	281.0	287.9	318.2	350.5	357.5	359.3	351.5	346.9	345.1	346.3	345.1
110°	322.1	332.7	369.0	409.8	420.4	423.4	420.4	415.9	412.9	412.9	412.9



TEST NUMBER: P1427753

CATALOG NUMBER: SQ2W-F-K-100U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	362.0	377.5	418.6	465.5	483.3	492.4	485.7	482.4	479.4	481.8	479.4
115°	423.4	446.1	500.6	549.0	585.3	589.8	588.3	588.3	586.8	586.8	586.8
117.5°	480.3	516.6	577.7	634.0	676.0	688.1	694.1	692.3	690.5	693.5	690.5
120°	520.2	562.6	632.1	695.7	736.5	754.6	760.7	757.7	760.7	757.7	760.7
122.5°	562.6	614.6	682.9	748.9	797.0	817.5	824.8	825.4	826.0	824.2	826.0
125°	626.1	689.6	769.8	837.8	887.7	911.9	918.0	919.5	922.5	930.1	922.5
127.5°	690.2	762.2	850.2	915.8	967.0	996.3	1005.7	1009.0	1015.3	1018.7	1015.3
130°	735.0	816.6	905.9	967.9	1017.8	1049.5	1066.2	1070.7	1078.3	1076.7	1078.3
132.5°	782.2	867.4	957.9	1022.3	1068.6	1102.8	1117.0	1130.0	1132.7	1134.8	1132.7
135°	851.4	943.7	1034.4	1097.9	1141.8	1175.0	1193.2	1205.3	1212.9	1217.4	1212.9
137.5°	924.3	1021.7	1108.8	1165.4	1209.5	1238.3	1258.8	1271.5	1279.4	1283.0	1279.4
140°	973.9	1067.7	1152.4	1211.3	1250.7	1279.4	1297.5	1312.7	1321.7	1321.7	1321.7
142.5°	1021.1	1113.6	1195.9	1254.9	1289.4	1315.7	1335.0	1346.5	1356.8	1356.8	1356.8
145°	1087.3	1179.6	1255.2	1314.2	1342.9	1367.1	1388.3	1397.4	1403.4	1403.4	1403.4
147.5°	1156.6	1238.3	1307.2	1363.8	1388.0	1416.4	1433.0	1440.3	1447.9	1444.5	1447.9
150°	1197.7	1273.3	1339.9	1392.8	1417.0	1444.2	1460.9	1466.9	1474.5	1469.9	1474.5
152.5°	1237.7	1309.6	1370.1	1419.4	1440.0	1467.2	1486.3	1492.3	1497.5	1494.1	1497.5
155°	1291.5	1355.0	1411.0	1456.3	1474.5	1500.2	1518.3	1525.9	1531.9	1524.4	1531.9
157.5°	1339.6	1394.3	1443.0	1484.8	1504.1	1526.2	1543.1	1552.5	1558.6	1555.2	1558.6
160°	1368.6	1418.5	1462.4	1501.7	1519.8	1539.5	1557.7	1568.2	1574.3	1569.8	1574.3
162.5°	1392.8	1437.9	1479.3	1515.0	1530.7	1548.0	1569.8	1579.1	1585.2	1579.4	1585.2
165°	1427.6	1463.9	1500.2	1530.4	1544.0	1557.7	1580.3	1590.9	1595.5	1589.4	1595.5
167.5°	1453.9	1481.7	1511.1	1537.1	1547.1	1560.4	1583.1	1591.8	1597.6	1590.0	1597.6
170°	1468.4	1492.6	1518.3	1539.5	1547.1	1559.2	1581.9	1589.4	1593.9	1586.4	1593.9
172.5°	1480.5	1498.7	1519.5	1538.3	1542.2	1551.9	1573.4	1580.9	1584.3	1577.9	1584.3
175°	1492.6	1503.2	1518.3	1530.4	1528.9	1535.0	1553.1	1559.2	1565.2	1556.1	1565.2
177.5°	1498.4	1503.2	1508.1	1515.3	1510.5	1510.5	1523.8	1527.4	1528.6	1523.8	1528.6
180°	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2



TEST NUMBER: P1427753

CATALOG NUMBER: SQ2W-F-K-100U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1194.1	1194.1	1194.1	1194.1	1194.1	1194.1	1194.1	1194.1	1194.1	1194.1	1194.1
2.5°	1192.3	1191.2	1190.0	1192.0	1197.0	1199.4	1193.8	1188.1	1193.8	1199.4	1197.0
5°	1188.3	1186.8	1186.1	1188.7	1194.7	1197.3	1189.8	1182.4	1189.8	1197.3	1194.7
7.5°	1179.8	1178.1	1177.2	1179.6	1185.3	1187.7	1180.2	1172.8	1180.2	1187.7	1185.3
10°	1172.2	1170.3	1168.8	1171.0	1177.0	1179.6	1172.2	1164.7	1172.2	1179.6	1177.0
12.5°	1162.2	1160.7	1159.8	1162.0	1167.4	1169.6	1162.1	1154.6	1162.1	1169.6	1167.4
15°	1144.4	1142.8	1141.7	1143.8	1149.0	1151.1	1143.6	1136.1	1143.6	1151.1	1149.0
17.5°	1122.1	1120.5	1119.2	1121.0	1125.9	1127.8	1120.8	1113.7	1120.8	1127.8	1125.9
20°	1104.0	1103.0	1102.6	1104.9	1109.8	1111.7	1105.0	1098.3	1105.0	1111.7	1109.8
22.5°	1083.3	1083.1	1083.9	1086.6	1091.1	1092.9	1086.1	1079.4	1086.1	1092.9	1091.1
25°	1051.8	1052.0	1053.1	1055.7	1059.9	1061.3	1054.5	1047.8	1054.5	1061.3	1059.9
27.5°	1018.5	1018.6	1019.3	1021.4	1024.9	1026.1	1020.4	1014.8	1020.4	1026.1	1024.9
30°	993.6	993.7	994.4	996.7	1000.4	1001.8	996.2	990.6	996.2	1001.8	1000.4
32.5°	967.4	967.0	967.2	969.4	973.7	975.7	970.4	965.1	970.4	975.7	973.7
35°	927.2	926.4	926.1	927.9	932.0	934.0	929.5	925.0	929.5	934.0	932.0
37.5°	884.2	883.9	884.0	885.9	889.7	891.7	888.3	884.8	888.3	891.7	889.7
40°	854.0	853.8	854.2	856.4	860.6	862.7	859.0	855.2	859.0	862.7	860.6
42.5°	824.2	823.8	823.6	825.2	828.7	830.6	827.8	825.0	827.8	830.6	828.7
45°	776.4	776.2	776.2	777.9	781.2	783.1	780.5	777.9	780.5	783.1	781.2
47.5°	726.5	726.6	727.0	728.5	731.2	732.6	730.6	728.6	730.6	732.6	731.2
50°	691.6	691.8	692.6	694.2	696.9	698.2	695.5	692.9	695.5	698.2	696.9
52.5°	656.6	657.0	658.1	659.9	662.5	663.8	660.9	657.9	660.9	663.8	662.5
55°	603.1	604.1	605.6	607.4	609.7	610.5	607.2	603.8	607.2	610.5	609.7
57.5°	547.7	548.8	550.6	552.5	554.4	555.0	551.7	548.5	551.7	555.0	554.4
60°	510.6	511.6	513.1	514.9	517.2	518.1	515.1	512.1	515.1	518.1	517.2
62.5°	473.0	473.9	475.4	477.4	479.9	481.1	478.1	475.1	478.1	481.1	479.9
65°	416.4	417.4	418.9	420.7	423.0	424.0	421.4	418.8	421.4	424.0	423.0
67.5°	357.4	358.9	361.0	363.2	365.4	366.4	364.2	361.9	364.2	366.4	365.4
70°	319.6	321.0	322.8	324.7	326.6	327.4	325.2	322.9	325.2	327.4	326.6
72.5°	281.2	282.4	284.0	285.8	288.0	289.1	287.2	285.2	287.2	289.1	288.0
75°	223.6	225.1	227.0	228.5	229.6	230.1	229.0	227.9	229.0	230.1	229.6
77.5°	166.1	167.2	168.7	170.1	171.5	172.6	172.6	172.6	172.6	172.6	171.5
80°	131.0	132.0	133.1	134.3	135.4	136.2	136.2	136.2	136.2	136.2	135.4
82.5°	95.0	96.1	97.9	99.3	100.4	101.4	102.0	102.6	102.0	101.4	100.4
85°	47.0	48.2	49.7	51.0	52.1	53.2	53.9	54.7	53.9	53.2	52.1
87.5°	17.0	17.7	18.9	19.7	19.6	19.3	18.3	17.7	18.3	18.9	20.2
90°	31.8	30.2	30.2	28.7	24.2	18.1	10.6	4.5	10.6	16.6	27.2
92.5°	37.8	37.5	35.1	32.4	26.6	26.6	26.3	16.6	28.7	40.8	58.7
95°	34.8	34.8	40.8	51.4	75.6	77.1	51.4	46.9	66.5	93.8	118.0
97.5°	94.1	111.9	137.3	142.2	134.6	100.4	96.2	89.5	121.9	148.8	187.8
100°	173.9	196.6	214.7	178.4	140.6	139.1	130.1	127.0	161.8	187.5	225.3
102.5°	271.9	278.9	216.0	195.4	186.6	180.3	166.4	164.5	199.3	234.7	266.5
105°	294.9	264.7	266.2	266.2	260.1	248.0	222.3	220.8	260.1	300.9	340.3
107.5°	346.9	351.5	359.3	357.5	350.5	318.2	287.9	281.0	316.4	365.4	408.6
110°	415.9	420.4	423.4	420.4	409.8	369.0	332.7	322.1	353.9	405.3	452.2



TEST NUMBER: P1427753

CATALOG NUMBER: SQ2W-F-K-100U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	482.4	485.7	492.4	483.3	465.5	418.6	377.5	362.0	393.8	446.4	494.5
115°	588.3	588.3	589.8	585.3	549.0	500.6	446.1	423.4	450.7	499.1	552.0
117.5°	692.3	694.1	688.1	676.0	634.0	577.7	516.6	480.3	501.8	552.9	607.3
120°	757.7	760.7	754.6	736.5	695.7	632.1	562.6	520.2	536.9	586.8	641.2
122.5°	825.4	824.8	817.5	797.0	748.9	682.9	614.6	562.6	569.5	615.8	669.0
125°	919.5	918.0	911.9	887.7	837.8	769.8	689.6	626.1	617.0	656.3	710.8
127.5°	1009.0	1005.7	996.3	967.0	915.8	850.2	762.2	690.2	669.9	694.7	744.6
130°	1070.7	1066.2	1049.5	1017.8	967.9	905.9	816.6	735.0	706.2	721.4	765.2
132.5°	1130.0	1117.0	1102.8	1068.6	1022.3	957.9	867.4	782.2	742.5	749.2	783.4
135°	1205.3	1193.2	1175.0	1141.8	1097.9	1034.4	943.7	851.4	797.0	790.9	810.6
137.5°	1271.5	1258.8	1238.3	1209.5	1165.4	1108.8	1021.7	924.3	855.7	835.4	842.9
140°	1312.7	1297.5	1279.4	1250.7	1211.3	1152.4	1067.7	973.9	896.8	868.1	863.5
142.5°	1346.5	1335.0	1315.7	1289.4	1254.9	1195.9	1113.6	1021.1	939.1	901.9	891.3
145°	1397.4	1388.3	1367.1	1342.9	1314.2	1255.2	1179.6	1087.3	1005.7	957.3	934.6
147.5°	1440.3	1433.0	1416.4	1388.0	1363.8	1307.2	1238.3	1156.6	1072.8	1012.9	983.6
150°	1466.9	1460.9	1444.2	1417.0	1392.8	1339.9	1273.3	1197.7	1117.6	1054.1	1016.3
152.5°	1492.3	1486.3	1467.2	1440.0	1419.4	1370.1	1309.6	1237.7	1156.3	1092.8	1053.8
155°	1525.9	1518.3	1500.2	1474.5	1456.3	1411.0	1355.0	1291.5	1221.9	1155.4	1111.5
157.5°	1552.5	1543.1	1526.2	1504.1	1484.8	1443.0	1394.3	1339.6	1278.8	1215.3	1170.5
160°	1568.2	1557.7	1539.5	1519.8	1501.7	1462.4	1418.5	1368.6	1312.7	1255.2	1206.8
162.5°	1579.1	1569.8	1548.0	1530.7	1515.0	1479.3	1437.9	1392.8	1342.9	1292.7	1247.9
165°	1590.9	1580.3	1557.7	1544.0	1530.4	1500.2	1463.9	1427.6	1385.3	1344.4	1308.1
167.5°	1591.8	1583.1	1560.4	1547.1	1537.1	1511.1	1481.7	1453.9	1420.9	1388.9	1358.6
170°	1589.4	1581.9	1559.2	1547.1	1539.5	1518.3	1492.6	1468.4	1442.7	1415.5	1391.3
172.5°	1580.9	1573.4	1551.9	1542.2	1538.3	1519.5	1498.7	1480.5	1458.4	1438.5	1419.1
175°	1559.2	1553.1	1535.0	1528.9	1530.4	1518.3	1503.2	1492.6	1479.0	1466.9	1456.3
177.5°	1527.4	1523.8	1510.5	1510.5	1515.3	1508.1	1503.2	1498.4	1492.3	1488.7	1485.1
180°	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2



TEST NUMBER: P1427753

CATALOG NUMBER: SQ2W-F-K-100U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1194.1	1194.1	1194.1	1194.1	1194.1	1194.1	1194.1	1194.1	1194.1	1194.1	1194.1
2.5°	1192.0	1190.0	1191.2	1192.3	1192.9	1193.5	1192.9	1192.3	1191.2	1190.0	1192.0
5°	1188.7	1186.1	1186.8	1188.3	1192.1	1195.8	1192.1	1188.3	1186.8	1186.1	1188.7
7.5°	1179.6	1177.2	1178.1	1179.8	1183.7	1187.6	1183.7	1179.8	1178.1	1177.2	1179.6
10°	1171.0	1168.8	1170.3	1172.2	1175.2	1178.1	1175.2	1172.2	1170.3	1168.8	1171.0
12.5°	1162.0	1159.8	1160.7	1162.2	1165.4	1168.7	1165.4	1162.2	1160.7	1159.8	1162.0
15°	1143.8	1141.7	1142.8	1144.4	1147.4	1150.4	1147.4	1144.4	1142.8	1141.7	1143.8
17.5°	1121.0	1119.2	1120.5	1122.1	1124.7	1127.4	1124.7	1122.1	1120.5	1119.2	1121.0
20°	1104.9	1102.6	1103.0	1104.0	1106.6	1109.2	1106.6	1104.0	1103.0	1102.6	1104.9
22.5°	1086.6	1083.9	1083.1	1083.3	1086.5	1089.7	1086.5	1083.3	1083.1	1083.9	1086.6
25°	1055.7	1053.1	1052.0	1051.8	1054.4	1057.1	1054.4	1051.8	1052.0	1053.1	1055.7
27.5°	1021.4	1019.3	1018.6	1018.5	1020.4	1022.2	1020.4	1018.5	1018.6	1019.3	1021.4
30°	996.7	994.4	993.7	993.6	995.5	997.3	995.5	993.6	993.7	994.4	996.7
32.5°	969.4	967.2	967.0	967.4	969.6	971.8	969.6	967.4	967.0	967.2	969.4
35°	927.9	926.1	926.4	927.2	929.0	930.9	929.0	927.2	926.4	926.1	927.9
37.5°	885.9	884.0	883.9	884.2	885.8	887.4	885.8	884.2	883.9	884.0	885.9
40°	856.4	854.2	853.8	854.0	855.9	857.8	855.9	854.0	853.8	854.2	856.4
42.5°	825.2	823.6	823.8	824.2	825.2	826.1	825.2	824.2	823.8	823.6	825.2
45°	777.9	776.2	776.2	776.4	777.1	777.9	777.1	776.4	776.2	776.2	777.9
47.5°	728.5	727.0	726.6	726.5	727.7	728.9	727.7	726.5	726.6	727.0	728.5
50°	694.2	692.6	691.8	691.6	693.1	694.6	693.1	691.6	691.8	692.6	694.2
52.5°	659.9	658.1	657.0	656.6	657.8	659.0	657.8	656.6	657.0	658.1	659.9
55°	607.4	605.6	604.1	603.1	603.9	604.6	603.9	603.1	604.1	605.6	607.4
57.5°	552.5	550.6	548.8	547.7	548.8	549.8	548.8	547.7	548.8	550.6	552.5
60°	514.9	513.1	511.6	510.6	511.4	512.1	511.4	510.6	511.6	513.1	514.9
62.5°	477.4	475.4	473.9	473.0	473.7	474.5	473.7	473.0	473.9	475.4	477.4
65°	420.7	418.9	417.4	416.4	416.7	417.1	416.7	416.4	417.4	418.9	420.7
67.5°	363.2	361.0	358.9	357.4	358.0	358.6	358.0	357.4	358.9	361.0	363.2
70°	324.7	322.8	321.0	319.6	319.6	319.6	319.6	319.6	321.0	322.8	324.7
72.5°	285.8	284.0	282.4	281.2	281.2	281.2	281.2	281.2	282.4	284.0	285.8
75°	228.5	227.0	225.1	223.6	223.2	222.8	223.2	223.6	225.1	227.0	228.5
77.5°	170.1	168.7	167.2	166.1	165.6	165.2	165.6	166.1	167.2	168.7	170.1
80°	134.3	133.1	132.0	131.0	130.3	129.5	130.3	131.0	132.0	133.1	134.3
82.5°	99.3	97.9	96.1	95.0	95.8	96.5	95.8	95.0	96.1	97.9	99.3
85°	51.0	49.7	48.2	47.0	46.6	46.3	46.6	47.0	48.2	49.7	51.0
87.5°	20.9	21.9	22.9	23.1	24.0	23.1	24.0	23.1	22.9	21.9	20.9
90°	34.8	45.4	56.0	62.0	68.1	65.0	68.1	62.0	56.0	45.4	34.8
92.5°	69.9	87.7	100.7	111.6	116.4	115.8	116.4	111.6	100.7	87.7	69.9
95°	140.6	161.8	183.0	198.1	207.2	204.2	207.2	198.1	183.0	161.8	140.6
97.5°	216.9	245.3	268.9	283.1	292.2	298.2	292.2	283.1	268.9	245.3	216.9
100°	267.7	294.9	322.1	338.8	353.9	359.9	353.9	338.8	322.1	294.9	267.7
102.5°	308.8	344.5	374.1	392.0	404.7	410.7	404.7	392.0	374.1	344.5	308.8
105°	376.6	414.4	446.1	468.8	482.4	487.0	482.4	468.8	446.1	414.4	376.6
107.5°	444.3	483.3	512.7	537.8	554.4	564.1	554.4	537.8	512.7	483.3	444.3
110°	497.5	529.3	561.1	583.7	600.4	606.4	600.4	583.7	561.1	529.3	497.5



TEST NUMBER: P1427753

CATALOG NUMBER: SQ2W-F-K-100U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	542.3	577.7	609.5	632.1	651.2	659.7	651.2	632.1	609.5	577.7	542.3
115°	604.9	651.8	680.5	701.7	715.3	722.9	715.3	701.7	680.5	651.8	604.9
117.5°	656.9	705.9	737.4	753.7	760.1	765.5	760.1	753.7	737.4	705.9	656.9
120°	689.6	735.0	771.3	792.4	800.0	803.0	800.0	792.4	771.3	735.0	689.6
122.5°	719.8	762.8	797.9	823.9	836.3	839.3	836.3	823.9	797.9	762.8	719.8
125°	762.2	803.0	839.3	865.0	878.6	886.2	878.6	865.0	839.3	803.0	762.2
127.5°	799.1	843.3	876.5	899.8	913.1	919.2	913.1	899.8	876.5	843.3	799.1
130°	819.7	865.0	898.3	924.0	936.1	942.2	936.1	924.0	898.3	865.0	819.7
132.5°	835.4	883.2	917.7	940.9	954.3	960.3	954.3	940.9	917.7	883.2	835.4
135°	854.4	904.3	940.6	963.3	975.4	981.5	975.4	963.3	940.6	904.3	854.4
137.5°	871.1	916.4	954.3	978.1	989.0	993.0	989.0	978.1	954.3	916.4	871.1
140°	883.2	922.5	960.3	983.0	995.1	996.6	995.1	983.0	960.3	922.5	883.2
142.5°	898.9	929.8	962.7	985.4	997.5	1000.2	997.5	985.4	962.7	929.8	898.9
145°	927.0	945.2	967.9	989.0	999.6	1002.6	999.6	989.0	967.9	945.2	927.0
147.5°	962.4	968.2	980.0	993.9	1004.2	1006.3	1004.2	993.9	980.0	968.2	962.4
150°	989.0	987.5	992.1	1001.1	1010.2	1008.7	1010.2	1001.1	992.1	987.5	989.0
152.5°	1019.3	1010.5	1010.2	1014.4	1018.7	1018.4	1018.7	1014.4	1010.2	1010.5	1019.3
155°	1070.7	1054.1	1045.0	1042.0	1042.0	1040.5	1042.0	1042.0	1045.0	1054.1	1070.7
157.5°	1127.3	1104.0	1090.4	1083.1	1081.0	1077.7	1081.0	1083.1	1090.4	1104.0	1127.3
160°	1166.0	1140.3	1126.7	1114.6	1110.0	1105.5	1110.0	1114.6	1126.7	1140.3	1166.0
162.5°	1202.3	1177.8	1162.9	1152.1	1147.5	1140.6	1147.5	1152.1	1162.9	1177.8	1202.3
165°	1261.2	1235.5	1218.9	1209.8	1203.8	1197.7	1203.8	1209.8	1218.9	1235.5	1261.2
167.5°	1320.2	1292.1	1281.2	1270.9	1265.2	1254.3	1265.2	1270.9	1281.2	1292.1	1320.2
170°	1356.5	1330.8	1324.8	1315.7	1305.1	1293.0	1305.1	1315.7	1324.8	1330.8	1356.5
172.5°	1388.0	1370.7	1364.7	1355.6	1352.3	1342.6	1352.3	1355.6	1364.7	1370.7	1388.0
175°	1433.6	1420.0	1420.0	1418.5	1414.0	1404.9	1414.0	1418.5	1420.0	1420.0	1433.6
177.5°	1471.8	1464.5	1469.3	1469.3	1468.1	1459.7	1468.1	1469.3	1469.3	1464.5	1471.8
180°	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2



TEST NUMBER: P1427753

CATALOG NUMBER: SQ2W-F-K-100U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1194.1	1194.1	1194.1	1194.1
2.5°	1197.0	1199.4	1193.8	1188.1
5°	1194.7	1197.3	1189.8	1182.4
7.5°	1185.3	1187.7	1180.2	1172.8
10°	1177.0	1179.6	1172.2	1164.7
12.5°	1167.4	1169.6	1162.1	1154.6
15°	1149.0	1151.1	1143.6	1136.1
17.5°	1125.9	1127.8	1120.8	1113.7
20°	1109.8	1111.7	1105.0	1098.3
22.5°	1091.1	1092.9	1086.1	1079.4
25°	1059.9	1061.3	1054.5	1047.8
27.5°	1024.9	1026.1	1020.4	1014.8
30°	1000.4	1001.8	996.2	990.6
32.5°	973.7	975.7	970.4	965.1
35°	932.0	934.0	929.5	925.0
37.5°	889.7	891.7	888.3	884.8
40°	860.6	862.7	859.0	855.2
42.5°	828.7	830.6	827.8	825.0
45°	781.2	783.1	780.5	777.9
47.5°	731.2	732.6	730.6	728.6
50°	696.9	698.2	695.5	692.9
52.5°	662.5	663.8	660.9	657.9
55°	609.7	610.5	607.2	603.8
57.5°	554.4	555.0	551.7	548.5
60°	517.2	518.1	515.1	512.1
62.5°	479.9	481.1	478.1	475.1
65°	423.0	424.0	421.4	418.8
67.5°	365.4	366.4	364.2	361.9
70°	326.6	327.4	325.2	322.9
72.5°	288.0	289.1	287.2	285.2
75°	229.6	230.1	229.0	227.9
77.5°	171.5	172.6	172.6	172.6
80°	135.4	136.2	136.2	136.2
82.5°	100.4	101.4	102.0	102.6
85°	52.1	53.2	53.9	54.7
87.5°	20.2	18.9	18.3	17.7
90°	27.2	16.6	10.6	4.5
92.5°	58.7	40.8	28.7	16.6
95°	118.0	93.8	66.5	46.9
97.5°	187.8	148.8	121.9	89.5
100°	225.3	187.5	161.8	127.0
102.5°	266.5	234.7	199.3	164.5
105°	340.3	300.9	260.1	220.8
107.5°	408.6	365.4	316.4	281.0
110°	452.2	405.3	353.9	322.1



TEST NUMBER: P1427753

CATALOG NUMBER: SQ2W-F-K-100U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	494.5	446.4	393.8	362.0
115°	552.0	499.1	450.7	423.4
117.5°	607.3	552.9	501.8	480.3
120°	641.2	586.8	536.9	520.2
122.5°	669.0	615.8	569.5	562.6
125°	710.8	656.3	617.0	626.1
127.5°	744.6	694.7	669.9	690.2
130°	765.2	721.4	706.2	735.0
132.5°	783.4	749.2	742.5	782.2
135°	810.6	790.9	797.0	851.4
137.5°	842.9	835.4	855.7	924.3
140°	863.5	868.1	896.8	973.9
142.5°	891.3	901.9	939.1	1021.1
145°	934.6	957.3	1005.7	1087.3
147.5°	983.6	1012.9	1072.8	1156.6
150°	1016.3	1054.1	1117.6	1197.7
152.5°	1053.8	1092.8	1156.3	1237.7
155°	1111.5	1155.4	1221.9	1291.5
157.5°	1170.5	1215.3	1278.8	1339.6
160°	1206.8	1255.2	1312.7	1368.6
162.5°	1247.9	1292.7	1342.9	1392.8
165°	1308.1	1344.4	1385.3	1427.6
167.5°	1358.6	1388.9	1420.9	1453.9
170°	1391.3	1415.5	1442.7	1468.4
172.5°	1419.1	1438.5	1458.4	1480.5
175°	1456.3	1466.9	1479.0	1492.6
177.5°	1485.1	1488.7	1492.3	1498.4
180°	1497.2	1497.2	1497.2	1497.2



TEST NUMBER: P1427753

CATALOG NUMBER: SQ2W-F-K-100U-075D-L830-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.51	18.33	18.52	19.35	20.71	17.43	18.24	18.44	19.26	20.62
	3H	19.30	20.03	20.32	21.06	22.44	19.20	19.93	20.22	20.96	22.34
	4H	19.99	20.69	21.02	21.72	23.11	19.88	20.57	20.91	21.60	22.99
	6H	20.43	21.07	21.47	22.10	23.50	20.29	20.93	21.33	21.96	23.36
	8H	20.59	21.19	21.63	22.25	23.64	20.43	21.04	21.48	22.09	23.49
	12H	20.67	21.25	21.72	22.29	23.71	20.49	21.07	21.54	22.12	23.54
4H	2H	18.09	18.78	19.12	19.81	21.20	18.02	18.71	19.06	19.75	21.13
	3H	20.10	20.68	21.15	21.74	23.14	20.01	20.59	21.06	21.65	23.05
	4H	20.92	21.45	21.97	22.50	23.92	20.81	21.34	21.86	22.39	23.81
	6H	21.47	21.92	22.53	23.00	24.42	21.33	21.78	22.39	22.86	24.27
	8H	21.68	22.11	22.74	23.17	24.61	21.52	21.95	22.58	23.01	24.45
	12H	21.79	22.18	22.87	23.26	24.70	21.61	21.99	22.69	23.07	24.51
8H	4H	21.16	21.58	22.22	22.65	24.08	21.06	21.49	22.12	22.55	23.99
	6H	21.84	22.20	22.93	23.31	24.74	21.71	22.07	22.80	23.18	24.61
	8H	22.15	22.46	23.24	23.55	25.00	21.99	22.30	23.09	23.39	24.85
	12H	22.33	22.60	23.43	23.69	25.18	22.14	22.41	23.24	23.50	24.99
12H	4H	21.15	21.54	22.23	22.62	24.06	21.06	21.44	22.14	22.52	23.96
	6H	21.89	22.20	22.99	23.30	24.75	21.77	22.08	22.86	23.17	24.62
	8H	22.23	22.50	23.32	23.59	25.08	22.07	22.35	23.17	23.43	24.92