

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937507

Luminaire Tested: SQ4-FB-100U-050D-B50-1D-UNV-W2A-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937507
REPORT IS A COMBINATION OF REPORTS P933573 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-050D-B50-1D-UNV-W2A-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7892.3 lumens
Efficiency: N/A
Efficacy: 127.7 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 61.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937507

CATALOG NUMBER: SQ4-FB-100U-050D-B50-1D-UNV-W2A-W-6

Luminous Intensity Polar Plot



TEST NUMBER: P937507

CATALOG NUMBER: SQ4-FB-100U-050D-B50-1D-UNV-W2A-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37
1	93	88	84	81	83	79	76	73	62	60	58	46	45	44	32	31	30
2	84	77	71	66	75	69	64	59	54	50	47	40	38	36	28	26	25
3	76	67	60	54	68	60	54	49	47	43	39	35	32	30	24	22	21
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	21	19	18
5	64	52	44	38	57	47	40	35	37	32	28	28	24	21	19	17	15
6	58	47	39	33	52	42	35	30	33	28	24	25	21	18	17	15	13
7	54	42	34	28	48	38	31	26	30	25	21	22	19	16	15	13	11
8	50	38	30	25	44	34	27	23	27	22	18	20	17	14	14	12	10
9	46	34	27	22	41	31	24	20	24	20	16	18	15	12	13	11	9
10	43	31	24	19	38	28	22	18	22	18	14	17	14	11	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1808	1808	1808
5°	1765	2088	2429
10°	1600	3044	4027
15°	1359	3975	4864
20°	1107	4606	4957
25°	923	4819	4856
30°	778	4848	4847
35°	688	4766	4972
40°	599	4660	5101
45°	542	4582	5122
50°	496	4512	5037
55°	475	4410	4814
60°	486	4214	4461
65°	505	3917	3976
70°	536	3414	3359
75°	592	2780	2622
80°	641	1925	1766
85°	560	1021	905

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5122 cd/sqm

TEST NUMBER: P937507

CATALOG NUMBER: SQ4-FB-100U-050D-B50-1D-UNV-W2A-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.8	0.5
10°-20°	167.5	2.1
20°-30°	293.0	3.7
30°-40°	377.2	4.8
40°-50°	421.3	5.3
50°-60°	403.5	5.1
60°-70°	319.8	4.1
70°-80°	188.0	2.4
80°-90°	55.6	0.7
90°-100°	423.2	5.4
100°-110°	1112.7	14.1
110°-120°	1153.8	14.6
120°-130°	925.5	11.7
130°-140°	726.2	9.2
140°-150°	557.4	7.1
150°-160°	401.4	5.1
160°-170°	245.6	3.1
170°-180°	83.0	1.1
0°-30°	498.3	6.3
0°-40°	875.5	11.1
0°-60°	1700.2	21.5
0°-90°	2263.6	28.7
90°-120°	2689.7	34.1
90°-150°	4898.7	62.1
90°-180°	5629.0	71.3
0°-180°	7892.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	292	292	292	292	292	
5°	285	305	344	389	403	26
15°	213	394	663	804	830	59
25°	136	446	790	825	826	63
35°	92	427	744	786	817	57
45°	63	340	658	754	787	49
55°	45	216	558	648	666	41
65°	36	115	414	466	472	35
75°	26	70	227	250	251	28
85°	9	22	56	62	63	10
90°	6	16	44	22	22	5
95°	56	219	729	376	256	62
105°	200	304	1230	1868	1742	212
115°	356	432	985	1966	2244	352
125°	495	555	896	1515	1787	440
135°	590	650	868	1223	1386	457
145°	685	728	857	1043	1125	429
155°	774	795	857	941	968	356
165°	835	846	857	891	902	236
175°	868	868	863	874	874	82
180°	868	868	868	868	868	

TEST NUMBER: P937507

CATALOG NUMBER: SQ4-FB-100U-050D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	292.2	292.2	292.2	292.2	292.2	292.2	292.2	292.2	292.2	292.2	292.2
2.5°	292.2	292.2	294.0	295.0	296.9	297.9	299.7	301.6	307.2	308.1	310.0
5°	284.7	288.4	300.7	305.3	318.5	336.3	343.8	356.0	381.4	388.9	393.7
7.5°	273.4	281.9	311.9	319.4	352.3	399.3	419.0	445.3	485.7	505.5	521.5
10°	255.5	273.4	326.9	344.8	398.4	469.7	506.4	543.0	604.1	631.3	641.7
12.5°	235.8	265.0	342.9	367.3	444.4	548.6	592.8	633.3	702.7	739.4	745.0
15°	213.2	252.7	357.9	393.7	493.2	614.4	663.2	713.1	777.9	804.2	810.8
17.5°	193.5	243.3	372.0	409.7	530.8	673.6	723.4	764.8	817.3	835.2	839.9
20°	169.1	228.3	381.4	430.3	570.3	716.8	764.8	796.7	832.4	843.7	845.6
22.5°	151.2	212.3	387.0	437.8	596.5	743.1	783.5	808.8	833.3	837.1	838.0
25°	136.3	194.5	386.1	446.3	619.1	759.1	790.1	808.8	822.9	824.8	824.8
27.5°	122.2	174.8	382.4	448.1	636.1	762.9	787.3	800.4	807.0	810.8	810.8
30°	109.9	156.0	372.9	444.4	643.5	759.1	778.9	785.4	791.9	797.6	800.4
32.5°	100.5	138.1	358.8	436.8	644.5	749.7	763.8	767.6	776.9	790.1	794.8
35°	92.1	120.3	342.9	426.6	638.9	734.7	744.0	747.9	766.6	786.3	792.9
37.5°	83.6	107.1	322.2	408.7	630.4	716.8	723.4	730.0	759.1	782.6	790.1
40°	75.2	95.8	297.9	388.9	617.3	695.2	700.9	711.1	749.7	776.9	784.5
42.5°	68.6	86.4	271.5	368.3	600.3	670.8	679.2	694.2	738.4	767.6	776.0
45°	63.0	77.1	243.3	340.1	578.7	645.4	657.6	678.3	725.3	753.5	760.9
47.5°	57.3	70.4	214.2	310.9	555.3	620.1	636.1	659.5	707.4	734.7	741.2
50°	52.6	63.9	185.1	279.9	529.9	592.8	611.6	636.1	684.9	710.2	718.7
52.5°	48.8	58.3	157.8	249.0	500.7	564.6	586.3	611.6	657.6	682.1	687.7
55°	45.1	53.5	134.3	216.0	470.6	534.5	558.1	582.4	627.6	648.2	652.0
57.5°	43.2	49.8	114.6	185.1	438.7	500.7	527.1	549.6	591.9	607.8	611.6
60°	40.4	47.0	99.6	158.8	404.0	468.8	491.4	513.9	549.6	562.7	565.5
62.5°	37.5	45.1	88.4	133.4	368.3	431.2	453.7	474.5	504.5	513.9	517.6
65°	35.7	43.2	79.9	114.6	331.7	391.7	414.3	432.2	456.5	466.0	467.8
67.5°	33.8	41.4	73.3	98.6	295.0	352.3	369.2	386.1	404.9	414.3	415.3
70°	31.0	39.4	67.6	87.3	257.4	307.2	321.3	339.1	354.2	358.8	361.7
72.5°	29.1	36.6	63.9	78.9	218.9	263.9	277.1	287.5	300.7	305.3	305.3
75°	26.3	32.9	60.1	70.4	179.4	216.0	227.3	237.7	248.0	249.9	247.0
77.5°	23.4	29.1	51.7	59.2	140.0	171.0	180.4	186.1	194.5	196.3	197.3
80°	19.7	25.4	40.4	46.0	101.4	125.9	132.4	137.2	144.7	144.7	146.5
82.5°	15.0	19.7	29.1	32.9	68.6	86.4	92.1	94.9	99.6	99.6	99.6
85°	9.4	12.2	18.8	21.6	41.4	52.6	56.4	57.3	61.1	62.0	62.0
87.5°	4.7	6.5	12.2	13.2	21.6	27.3	27.3	29.1	29.1	28.2	27.3
90°	5.8	10.5	15.1	16.3	25.7	38.1	44.3	39.3	29.5	22.1	22.1
92.5°	23.4	63.0	102.6	112.5	158.1	218.9	249.4	218.6	156.9	110.7	106.3
95°	55.9	128.4	201.0	219.1	389.1	615.7	729.0	650.5	493.5	375.8	362.5
97.5°	96.8	160.7	224.7	240.7	524.1	902.0	1090.9	1041.3	942.1	867.7	842.3
100°	128.2	186.2	244.2	258.7	573.2	992.5	1202.2	1205.8	1213.1	1218.5	1188.2
102.5°	155.0	209.2	263.3	276.8	595.8	1021.0	1233.6	1296.9	1423.2	1518.0	1492.2
105°	200.4	246.3	292.2	303.6	612.5	1024.3	1230.2	1371.9	1655.1	1867.6	1853.7
107.5°	247.0	289.8	332.6	343.2	615.6	978.6	1160.2	1357.8	1753.0	2049.5	2052.8
110°	278.5	317.1	355.8	365.4	610.9	938.3	1101.9	1322.8	1764.7	2096.1	2110.6

TEST NUMBER: P937507

CATALOG NUMBER: SQ4-FB-100U-050D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	309.4	346.2	383.0	392.2	611.1	903.0	1048.9	1275.0	1727.2	2066.4	2088.6
115°	356.0	389.9	423.8	432.3	616.7	862.5	985.4	1203.2	1638.9	1965.6	1996.5
117.5°	402.1	432.9	463.7	471.4	628.1	837.1	941.7	1138.3	1531.4	1826.3	1860.5
120°	428.9	457.9	486.9	494.2	637.5	828.6	924.2	1103.8	1463.0	1732.5	1765.7
122.5°	455.1	484.4	513.7	521.0	650.9	824.2	910.8	1072.6	1396.0	1638.6	1671.5
125°	495.3	522.0	548.7	555.4	669.0	820.5	896.3	1033.7	1308.4	1514.6	1544.8
127.5°	528.0	554.9	581.9	588.6	687.1	818.4	884.0	1002.0	1237.9	1414.9	1440.4
130°	545.5	574.5	603.5	610.7	700.3	819.7	879.4	984.3	1194.4	1352.0	1375.5
132.5°	563.5	592.5	621.5	628.8	711.0	820.5	875.3	969.3	1157.3	1298.4	1319.5
135°	590.3	616.7	643.2	649.8	722.6	819.7	868.2	947.0	1104.5	1222.6	1240.8
137.5°	617.7	643.8	670.1	676.6	740.1	824.8	867.1	933.7	1066.8	1166.7	1181.5
140°	640.4	664.5	688.6	694.6	750.7	825.6	863.0	920.6	1035.5	1121.7	1135.7
142.5°	657.9	680.2	702.5	708.1	759.7	828.6	863.0	913.5	1014.5	1090.3	1102.2
145°	684.7	704.1	723.6	728.4	771.4	828.6	857.2	898.5	981.2	1043.1	1052.2
147.5°	711.5	730.4	749.3	754.0	788.4	834.2	857.2	889.7	954.7	1003.5	1011.0
150°	729.0	746.1	763.2	767.5	797.4	837.2	857.2	884.7	939.5	980.7	986.8
152.5°	747.1	760.1	773.0	776.2	803.2	839.2	857.2	880.7	927.6	962.7	967.3
155°	773.9	783.4	793.0	795.4	816.0	843.5	857.2	875.9	913.2	941.1	944.2
157.5°	793.7	803.1	812.3	814.6	828.8	847.8	857.2	871.7	900.7	922.5	924.7
160°	807.1	814.4	821.6	823.4	834.7	849.8	857.2	869.6	894.5	913.2	914.4
162.5°	820.5	825.9	831.4	832.8	840.9	851.8	857.2	867.7	888.7	904.4	905.5
165°	835.1	839.9	844.9	846.1	849.8	854.8	857.2	864.7	879.7	891.0	892.3
167.5°	848.4	850.8	853.1	853.7	856.8	861.0	863.0	868.0	877.8	885.2	885.7
170°	857.2	859.6	861.9	862.5	862.6	862.9	863.0	868.0	877.8	885.2	885.2
172.5°	861.9	862.4	862.9	863.0	863.0	863.0	863.0	866.9	874.7	880.5	880.0
175°	868.2	868.2	868.2	868.2	866.5	864.1	863.0	865.4	870.4	874.1	874.1
177.5°	868.2	868.2	868.2	868.2	866.9	865.2	864.2	866.2	870.0	872.9	872.4
180°	868.2	868.2	868.2	868.2	868.2	868.2	868.2	868.2	868.2	868.2	868.2

TEST NUMBER: P937507

CATALOG NUMBER: SQ4-FB-100U-050D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	292.2	292.2
2.5°	311.9	310.0
5°	401.2	403.0
7.5°	540.2	539.3
10°	671.7	680.1
12.5°	767.6	769.4
15°	825.8	829.6
17.5°	848.4	849.3
20°	849.3	847.4
22.5°	838.9	837.1
25°	826.8	825.8
27.5°	815.5	816.4
30°	810.8	813.6
32.5°	810.8	815.5
35°	812.7	817.3
37.5°	811.7	817.3
40°	807.9	814.5
42.5°	797.6	802.3
45°	781.7	787.3
47.5°	760.9	764.8
50°	734.7	738.4
52.5°	701.8	702.7
55°	662.3	666.1
57.5°	620.1	621.0
60°	573.1	575.9
62.5°	523.3	523.3
65°	470.6	472.5
67.5°	416.2	420.9
70°	360.8	361.7
72.5°	306.3	306.3
75°	249.9	250.9
77.5°	196.3	196.3
80°	145.6	146.5
82.5°	100.5	102.4
85°	63.0	63.0
87.5°	29.1	26.3
90°	22.1	22.1
92.5°	88.6	71.1
95°	309.2	255.8
97.5°	740.8	639.2
100°	1067.3	946.3
102.5°	1388.5	1284.9
105°	1798.0	1742.4
107.5°	2066.4	2079.8
110°	2168.7	2226.7



TEST NUMBER: P937507

CATALOG NUMBER: SQ4-FB-100U-050D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2177.7	2266.8
115°	2120.0	2243.6
117.5°	1997.5	2134.6
120°	1898.9	2032.0
122.5°	1802.8	1934.1
125°	1665.7	1786.6
127.5°	1542.5	1644.5
130°	1469.8	1564.1
132.5°	1403.9	1488.3
135°	1313.6	1386.3
137.5°	1241.1	1300.7
140°	1191.4	1247.1
142.5°	1150.2	1198.1
145°	1088.5	1124.7
147.5°	1041.0	1071.1
150°	1011.1	1035.5
152.5°	985.7	1004.0
155°	956.3	968.5
157.5°	933.2	941.7
160°	919.3	924.2
162.5°	910.2	914.9
165°	897.2	902.1
167.5°	887.8	889.8
170°	885.2	885.2
172.5°	878.2	876.5
175°	874.1	874.1
177.5°	870.3	868.2
180°	868.2	868.2

(END OF REPORT)