

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937606

Luminaire Tested: SQ4-FB-100U-075D-B50-1D-UNV-W2A-W-4

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937606
REPORT IS A COMBINATION OF REPORTS P933566 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-075D-B50-1D-UNV-W2A-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6001.8 lumens
Efficiency: N/A
Efficacy: 122.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 49.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937606

CATALOG NUMBER: SQ4-FB-100U-075D-B50-1D-UNV-W2A-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P937606

CATALOG NUMBER: SQ4-FB-100U-075D-B50-1D-UNV-W2A-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45
1	95	90	86	83	86	82	78	75	66	64	62	52	50	49	39	38	37
2	86	78	72	67	77	71	66	61	58	54	50	45	42	40	34	32	30
3	78	68	61	55	70	62	56	50	50	46	42	39	36	33	29	27	25
4	71	60	52	46	64	55	48	42	44	39	35	35	31	28	26	23	21
5	65	53	45	39	58	48	41	36	39	34	30	31	27	24	23	20	18
6	60	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16
7	55	42	34	29	49	39	32	27	32	26	22	25	21	18	19	16	14
8	51	38	31	25	46	35	28	23	29	23	20	23	19	16	17	14	12
9	47	35	27	22	42	32	25	21	26	21	17	21	17	14	16	13	11
10	44	32	24	20	40	29	23	18	24	19	15	19	15	12	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2696	2696	2696
5°	2630	3113	3623
10°	2383	4534	6006
15°	2023	5920	7252
20°	1645	6855	7392
25°	1370	7168	7241
30°	1154	7208	7227
35°	1019	7082	7415
40°	886	6922	7608
45°	801	6801	7638
50°	733	6692	7511
55°	700	6535	7178
60°	715	6240	6652
65°	740	5794	5930
70°	782	5043	5010
75°	859	4101	3910
80°	917	2834	2634
85°	770	1495	1349

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 7638 cd/sqm

TEST NUMBER: P937606

CATALOG NUMBER: SQ4-FB-100U-075D-B50-1D-UNV-W2A-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.6	0.6
10°-20°	166.5	2.8
20°-30°	291.3	4.9
30°-40°	375.0	6.2
40°-50°	418.8	7.0
50°-60°	401.1	6.7
60°-70°	317.9	5.3
70°-80°	186.9	3.1
80°-90°	54.1	0.9
90°-100°	282.1	4.7
100°-110°	741.8	12.4
110°-120°	769.2	12.8
120°-130°	617.0	10.3
130°-140°	484.1	8.1
140°-150°	371.6	6.2
150°-160°	267.6	4.5
160°-170°	163.7	2.7
170°-180°	55.3	0.9
0°-30°	495.4	8.3
0°-40°	870.4	14.5
0°-60°	1690.3	28.2
0°-90°	2249.3	37.5
90°-120°	1793.2	29.9
90°-150°	3265.8	54.4
90°-180°	3752.0	62.5
0°-180°	6001.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	290	290	290	290	290	
5°	283	304	342	387	401	26
15°	212	391	659	800	825	59
25°	135	444	786	820	821	62
35°	92	424	740	782	813	57
45°	63	338	654	749	783	48
55°	45	215	555	644	662	41
65°	36	114	412	463	470	35
75°	26	70	226	248	249	27
85°	9	22	56	62	63	10
90°	4	11	30	15	15	4
95°	37	146	486	251	170	41
105°	134	202	820	1245	1162	142
115°	237	288	657	1310	1496	234
125°	330	370	598	1010	1191	293
135°	394	433	579	815	924	304
145°	456	486	572	695	750	286
155°	516	530	572	627	646	237
165°	557	564	572	594	601	157
175°	579	579	575	583	583	55
180°	579	579	579	579	579	

TEST NUMBER: P937606

CATALOG NUMBER: SQ4-FB-100U-075D-B50-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	290.5	290.5	290.5	290.5	290.5	290.5	290.5	290.5	290.5	290.5	290.5
2.5°	290.5	290.5	292.3	293.3	295.1	296.1	297.9	299.8	305.4	306.4	308.2
5°	283.0	286.7	298.9	303.6	316.6	334.4	341.8	354.0	379.2	386.7	391.3
7.5°	271.8	280.2	310.1	317.6	350.2	397.0	416.6	442.7	482.9	502.5	518.4
10°	254.0	271.8	325.0	342.8	396.0	467.0	503.4	539.9	600.6	627.6	637.9
12.5°	234.4	263.4	340.9	365.2	441.8	545.5	589.4	629.5	698.6	735.1	740.7
15°	212.0	251.2	355.9	391.3	490.4	610.8	659.4	708.9	773.4	799.5	806.0
17.5°	192.4	241.9	369.9	407.2	527.7	669.7	719.2	760.3	812.6	830.3	835.0
20°	168.1	227.0	379.2	427.8	566.9	712.6	760.3	792.0	827.5	838.7	840.6
22.5°	150.4	211.1	384.8	435.2	593.1	738.8	779.0	804.2	828.5	832.2	833.1
25°	135.4	193.3	383.9	443.6	615.5	754.7	785.5	804.2	818.2	820.1	820.1
27.5°	121.4	173.7	380.1	445.5	632.3	758.4	782.7	795.8	802.3	806.0	806.0
30°	109.3	155.0	370.8	441.8	639.8	754.7	774.3	780.8	787.4	793.0	795.8
32.5°	99.9	137.3	356.8	434.3	640.7	745.3	759.3	763.1	772.4	785.5	790.2
35°	91.5	119.6	340.9	424.0	635.1	730.4	739.7	743.5	762.1	781.8	788.3
37.5°	83.1	106.5	320.4	406.3	626.7	712.6	719.2	725.7	754.7	778.0	785.5
40°	74.7	95.3	296.1	386.7	613.6	691.2	696.8	707.0	745.3	772.4	779.9
42.5°	68.2	85.9	269.9	366.1	596.8	666.9	675.3	690.2	734.1	763.1	771.5
45°	62.6	76.6	241.9	338.1	575.3	641.7	653.8	674.3	721.0	749.1	756.5
47.5°	57.0	70.0	213.0	309.2	552.0	616.4	632.3	655.7	703.3	730.4	736.9
50°	52.3	63.5	184.0	278.3	526.8	589.4	608.0	632.3	680.9	706.1	714.5
52.5°	48.6	57.9	156.9	247.5	497.8	561.3	582.8	608.0	653.8	678.1	683.7
55°	44.8	53.2	133.6	214.8	467.9	531.4	554.8	579.1	623.9	644.5	648.2
57.5°	43.0	49.5	113.9	184.0	436.2	497.8	524.0	546.4	588.4	604.3	608.0
60°	40.2	46.7	99.0	157.8	401.6	466.1	488.5	510.9	546.4	559.5	562.3
62.5°	37.4	44.8	87.8	132.6	366.1	428.7	451.1	471.7	501.6	510.9	514.6
65°	35.5	43.0	79.4	113.9	329.7	389.5	411.9	429.6	453.9	463.3	465.1
67.5°	33.6	41.1	72.9	98.1	293.3	350.2	367.1	383.9	402.6	411.9	412.8
70°	30.8	39.2	67.2	86.9	255.9	305.4	319.4	337.2	352.1	356.8	359.6
72.5°	29.0	36.4	63.5	78.5	217.6	262.5	275.5	285.8	298.9	303.6	303.6
75°	26.2	32.7	59.8	70.0	178.4	214.8	226.0	236.3	246.6	248.4	245.6
77.5°	23.4	29.0	51.4	58.8	139.2	170.0	179.3	184.9	193.3	195.2	196.1
80°	19.6	25.2	40.2	45.8	100.9	125.2	131.7	136.4	143.8	143.8	145.7
82.5°	14.9	19.6	29.0	32.7	68.2	85.9	91.5	94.3	99.0	99.0	99.0
85°	9.3	12.1	18.7	21.5	41.1	52.3	56.0	57.0	60.7	61.6	61.6
87.5°	4.7	6.5	12.1	13.1	21.5	27.1	27.1	29.0	29.0	28.0	27.1
90°	3.9	7.0	10.1	10.8	17.1	25.4	29.5	26.2	19.7	14.8	14.8
92.5°	15.5	41.9	68.4	75.0	105.4	146.0	166.3	145.7	104.6	73.8	70.9
95°	37.3	85.6	134.0	146.1	259.4	410.4	486.0	433.7	329.0	250.6	241.7
97.5°	64.4	107.1	149.8	160.5	349.4	601.3	727.2	694.1	628.0	578.4	561.5
100°	85.5	124.1	162.8	172.5	382.2	661.7	801.5	803.9	808.7	812.3	792.1
102.5°	103.3	139.4	175.5	184.6	397.2	680.7	822.5	864.6	948.9	1012.0	994.7
105°	133.7	164.2	194.7	202.4	408.3	682.8	820.1	914.6	1103.4	1245.1	1235.9
107.5°	164.8	193.2	221.7	228.8	410.4	652.4	773.4	905.2	1168.7	1366.3	1368.6
110°	185.7	211.5	237.1	243.6	407.2	625.5	734.6	881.9	1176.5	1397.4	1407.1

TEST NUMBER: P937606

CATALOG NUMBER: SQ4-FB-100U-075D-B50-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	206.3	230.8	255.3	261.4	407.4	602.0	699.3	850.0	1151.4	1377.6	1392.4
115°	237.3	259.9	282.5	288.2	411.1	575.1	657.0	802.2	1092.6	1310.4	1331.0
117.5°	268.1	288.6	309.2	314.3	418.8	558.2	627.8	758.9	1021.0	1217.6	1240.4
120°	285.9	305.2	324.6	329.4	425.0	552.5	616.2	735.9	975.4	1155.0	1177.2
122.5°	303.5	323.0	342.5	347.4	433.9	549.5	607.2	715.0	930.6	1092.4	1114.3
125°	330.3	348.0	365.8	370.2	446.0	547.0	597.5	689.1	872.3	1009.7	1029.8
127.5°	351.9	369.9	387.9	392.4	458.0	545.5	589.4	668.0	825.3	943.2	960.2
130°	363.6	382.9	402.3	407.1	466.8	546.5	586.3	656.3	796.3	901.3	917.0
132.5°	375.7	395.0	414.3	419.2	473.9	547.0	583.5	646.1	771.5	865.5	879.6
135°	393.6	411.1	428.8	433.2	481.8	546.5	578.9	631.4	736.3	815.0	827.2
137.5°	411.8	429.3	446.6	451.0	493.3	549.8	578.1	622.4	711.1	777.7	787.6
140°	426.9	443.0	459.1	463.1	500.5	550.4	575.3	613.6	690.3	747.9	757.1
142.5°	438.6	453.5	468.3	472.0	506.5	552.4	575.3	609.0	676.3	726.8	734.9
145°	456.4	469.4	482.3	485.6	514.3	552.5	571.5	599.1	654.1	695.4	701.4
147.5°	474.4	487.0	499.5	502.7	525.7	556.2	571.5	593.2	636.5	669.0	674.1
150°	486.0	497.4	508.7	511.6	531.6	558.3	571.5	589.8	626.3	653.8	657.8
152.5°	498.0	506.6	515.3	517.4	535.5	559.5	571.5	587.1	618.3	641.8	644.8
155°	515.9	522.3	528.7	530.3	544.1	562.4	571.5	583.9	608.8	627.4	629.4
157.5°	529.1	535.4	541.5	543.1	552.6	565.2	571.5	581.1	600.5	614.9	616.3
160°	538.1	542.9	547.7	548.9	556.5	566.5	571.5	579.8	596.4	608.8	609.6
162.5°	547.0	550.6	554.2	555.2	560.6	567.9	571.5	578.5	592.4	602.9	603.6
165°	556.7	559.9	563.2	564.0	566.6	569.8	571.5	576.6	586.6	594.0	594.9
167.5°	565.6	567.2	568.8	569.2	571.2	573.9	575.3	578.6	585.2	590.1	590.5
170°	571.5	573.0	574.6	575.0	575.1	575.3	575.3	578.6	585.2	590.1	590.1
172.5°	574.6	575.0	575.3	575.3	575.3	575.3	575.3	578.0	583.1	587.0	586.7
175°	578.9	578.9	578.9	578.9	577.7	576.1	575.3	577.0	580.3	582.7	582.7
177.5°	578.9	578.9	578.9	578.9	578.0	576.7	576.1	577.4	580.0	582.0	581.6
180°	578.9	578.9	578.9	578.9	578.9	578.9	578.9	578.9	578.9	578.9	578.9

TEST NUMBER: P937606

CATALOG NUMBER: SQ4-FB-100U-075D-B50-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	290.5	290.5
2.5°	310.1	308.2
5°	398.8	400.7
7.5°	537.1	536.1
10°	667.8	676.2
12.5°	763.1	764.9
15°	821.0	824.7
17.5°	843.4	844.3
20°	844.3	842.5
22.5°	834.1	832.2
25°	821.9	821.0
27.5°	810.7	811.6
30°	806.0	808.8
32.5°	806.0	810.7
35°	807.9	812.6
37.5°	807.0	812.6
40°	803.2	809.8
42.5°	793.0	797.6
45°	777.1	782.7
47.5°	756.5	760.3
50°	730.4	734.1
52.5°	697.7	698.6
55°	658.5	662.2
57.5°	616.4	617.4
60°	569.7	572.5
62.5°	520.2	520.2
65°	467.9	469.8
67.5°	413.8	418.4
70°	358.7	359.6
72.5°	304.5	304.5
75°	248.4	249.4
77.5°	195.2	195.2
80°	144.8	145.7
82.5°	99.9	101.8
85°	62.6	62.6
87.5°	29.0	26.2
90°	14.8	14.8
92.5°	59.1	47.4
95°	206.1	170.5
97.5°	493.8	426.2
100°	711.5	630.9
102.5°	925.7	856.7
105°	1198.7	1161.6
107.5°	1377.6	1386.5
110°	1445.7	1484.4

TEST NUMBER: P937606

CATALOG NUMBER: SQ4-FB-100U-075D-B50-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1451.8	1511.2
115°	1413.3	1495.7
117.5°	1331.7	1423.0
120°	1265.9	1354.7
122.5°	1201.9	1289.4
125°	1110.4	1191.1
127.5°	1028.3	1096.3
130°	979.9	1042.7
132.5°	935.9	992.2
135°	875.6	924.2
137.5°	827.4	867.1
140°	794.3	831.4
142.5°	766.8	798.8
145°	725.6	749.8
147.5°	694.1	714.0
150°	674.1	690.3
152.5°	657.1	669.4
155°	637.5	645.7
157.5°	622.1	627.8
160°	612.9	616.2
162.5°	606.8	609.9
165°	598.1	601.4
167.5°	591.8	593.2
170°	590.1	590.1
172.5°	585.5	584.3
175°	582.7	582.7
177.5°	580.3	578.9
180°	578.9	578.9

(END OF REPORT)