

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435895

Luminaire Tested: SQ2W-FB-0U-100D-L830-UNV-STD-W-WM-4

Issue Date: 3/24/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1435895  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/24/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-FB-0U-100D-L830-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT N/A - DIRECT ONLY  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4505.0 lumens  
Efficiency: N/A  
Efficacy: 119.8 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1435895

CATALOG NUMBER: SQ2W-FB-0U-100D-L830-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1435895

CATALOG NUMBER: SQ2W-FB-0U-100D-L830-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84				84
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69				69
3	89	78	70	63	87	77	69	63	74	67	61	71	65	60	68	63	59	57				57
4	81	69	60	53	79	67	59	52	65	58	52	63	56	51	60	55	50	48				48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41				41
6	68	54	45	39	66	53	45	38	52	44	38	50	43	38	48	42	37	35				35
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	31				31
8	58	44	36	30	57	44	35	29	42	35	29	41	34	29	40	34	29	27				27
9	54	40	32	26	53	40	32	26	39	31	26	38	31	26	37	30	26	24				24
10	51	37	29	23	49	37	29	23	36	28	23	35	28	23	34	28	23	21				21

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7364	7364	7364	7364
5°	7180	13044	7180	13044
10°	6723	25382	6723	25382
15°	6084	29215	6084	29215
20°	5388	30596	5388	30596
25°	4765	31097	4765	31097
30°	4212	31481	4212	31481
35°	3761	33844	3761	33844
40°	3421	35959	3421	35959
45°	3156	37654	3156	37654
50°	2974	38338	2974	38338
55°	2902	38643	2902	38643
60°	2974	38452	2974	38452
65°	3098	37367	3098	37367
70°	3210	28262	3210	28262
75°	3556	15595	3556	15595
80°	3673	14477	3673	14477
85°	3649	6095	3649	6095

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 52.5°  
 Luminance: 38993 cd/sqm



TEST NUMBER: P1435895

CATALOG NUMBER: SQ2W-FB-0U-100D-L830-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.4	1.7
10°-20°	348.7	7.7
20°-30°	613.6	13.6
30°-40°	794.3	17.6
40°-50°	876.0	19.4
50°-60°	817.6	18.1
60°-70°	631.6	14.0
70°-80°	291.2	6.5
80°-90°	55.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1038.7	23.1
0°-40°	1833.0	40.7
0°-60°	3526.6	78.3
0°-90°	4505.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4505.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	456	456	456	456	456	
5°	443	805	443	805	443	41
15°	364	1748	364	1748	364	101
25°	268	1746	268	1746	268	123
35°	191	1717	191	1717	191	120
45°	138	1649	138	1649	138	107
55°	103	1373	103	1373	103	93
65°	81	978	81	978	81	80
75°	57	250	57	250	57	59
85°	20	33	20	33	20	21
90°	0	0	0	0	0	



TEST NUMBER: P1435895

CATALOG NUMBER: SQ2W-FB-OU-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	456.1	456.1	456.1	456.1	456.1	456.1	456.1	456.1	456.1	456.1	456.1
2.5°	452.6	461.2	469.8	478.9	488.3	498.4	509.4	518.7	523.4	528.1	523.4
5°	443.0	472.2	501.5	543.9	590.6	643.8	703.2	754.1	779.5	804.8	779.5
7.5°	425.9	485.3	544.8	670.8	818.9	972.7	1132.1	1264.4	1315.1	1365.8	1315.1
10°	410.1	492.9	575.8	789.5	1046.8	1244.6	1383.0	1493.6	1520.9	1548.2	1520.9
12.5°	392.5	505.0	617.5	881.3	1195.5	1401.2	1498.2	1578.1	1606.1	1634.2	1606.1
15°	364.0	524.8	685.7	983.9	1328.0	1539.5	1618.4	1685.4	1716.6	1747.8	1716.6
17.5°	334.6	548.7	762.7	1066.9	1401.2	1607.5	1685.7	1748.5	1765.5	1782.4	1765.5
20°	313.6	565.1	816.5	1121.3	1443.9	1638.9	1706.1	1759.2	1770.0	1780.7	1770.0
22.5°	294.3	575.4	856.5	1161.7	1474.9	1657.0	1707.9	1748.9	1760.4	1771.9	1760.4
25°	267.5	584.3	901.1	1205.4	1505.6	1671.8	1703.9	1730.0	1737.8	1745.6	1737.8
27.5°	241.7	576.4	911.1	1211.5	1500.6	1655.7	1676.7	1694.4	1702.0	1709.6	1702.0
30°	225.9	566.0	906.2	1203.9	1487.6	1637.2	1652.8	1667.1	1677.9	1688.6	1677.9
32.5°	211.8	553.6	895.3	1189.3	1467.5	1614.0	1628.8	1645.7	1668.9	1692.1	1668.9
35°	190.8	527.0	863.3	1154.2	1430.1	1579.7	1603.0	1631.3	1674.2	1717.1	1674.2
37.5°	172.8	493.1	813.3	1101.3	1378.5	1541.5	1590.5	1637.5	1678.8	1720.2	1678.8
40°	162.3	469.3	776.3	1062.1	1340.9	1512.9	1578.2	1635.9	1671.0	1706.1	1671.0
42.5°	151.8	442.4	733.0	1016.5	1297.6	1476.2	1552.5	1618.4	1653.5	1688.6	1653.5
45°	138.2	399.4	660.6	941.5	1229.0	1417.6	1507.3	1582.8	1616.0	1649.1	1616.0
47.5°	125.4	352.3	579.2	861.4	1162.0	1359.8	1455.0	1532.3	1556.5	1580.7	1556.5
50°	118.4	321.1	523.9	807.0	1116.9	1318.7	1412.3	1487.3	1506.8	1526.3	1506.8
52.5°	111.4	290.7	470.1	753.8	1072.3	1275.6	1363.7	1434.3	1452.2	1470.2	1452.2
55°	103.1	249.3	395.5	676.2	1001.7	1203.0	1280.0	1341.6	1357.2	1372.8	1357.2
57.5°	95.6	213.5	331.5	603.4	926.5	1121.0	1186.7	1239.1	1251.8	1264.5	1251.8
60°	92.1	194.4	296.8	557.7	871.6	1058.2	1117.7	1165.4	1178.1	1190.8	1178.1
62.5°	86.8	175.9	265.0	512.1	811.9	989.2	1044.0	1088.0	1099.9	1111.8	1099.9
65°	81.1	153.3	225.4	448.1	721.0	880.3	926.2	962.5	970.3	978.1	970.3
67.5°	73.2	134.5	195.7	389.5	627.5	760.7	789.2	806.9	792.2	777.6	792.2
70°	68.0	124.5	181.0	353.8	565.3	675.9	685.7	682.5	640.6	598.7	640.6
72.5°	64.5	114.8	165.1	314.6	497.3	577.9	556.4	520.5	441.2	361.8	441.2
75°	57.0	98.0	138.9	251.5	387.9	409.4	315.8	246.1	248.0	250.0	248.0
77.5°	46.5	77.1	107.7	176.9	259.0	275.2	225.7	189.0	190.8	192.5	190.8
80°	39.5	63.8	88.2	115.5	143.8	156.9	155.0	153.8	154.7	155.7	154.7
82.5°	32.5	50.6	68.7	85.1	100.9	109.7	111.7	112.8	111.5	110.1	111.5
85°	19.7	30.5	41.2	47.5	52.4	50.9	43.1	36.8	34.8	32.9	34.8
87.5°	7.0	10.9	14.8	13.5	10.3	8.8	8.8	8.8	8.8	8.8	8.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1435895

CATALOG NUMBER: SQ2W-FB-OU-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	456.1	456.1	456.1	456.1	456.1	456.1	456.1	456.1	456.1	456.1	456.1
2.5°	518.7	509.4	498.4	488.3	478.9	469.8	461.2	452.6	461.2	469.8	478.9
5°	754.1	703.2	643.8	590.6	543.9	501.5	472.2	443.0	472.2	501.5	543.9
7.5°	1264.4	1132.1	972.7	818.9	670.8	544.8	485.3	425.9	485.3	544.8	670.8
10°	1493.6	1383.0	1244.6	1046.8	789.5	575.8	492.9	410.1	492.9	575.8	789.5
12.5°	1578.1	1498.2	1401.2	1195.5	881.3	617.5	505.0	392.5	505.0	617.5	881.3
15°	1685.4	1618.4	1539.5	1328.0	983.9	685.7	524.8	364.0	524.8	685.7	983.9
17.5°	1748.5	1685.7	1607.5	1401.2	1066.9	762.7	548.7	334.6	548.7	762.7	1066.9
20°	1759.2	1706.1	1638.9	1443.9	1121.3	816.5	565.1	313.6	565.1	816.5	1121.3
22.5°	1748.9	1707.9	1657.0	1474.9	1161.7	856.5	575.4	294.3	575.4	856.5	1161.7
25°	1730.0	1703.9	1671.8	1505.6	1205.4	901.1	584.3	267.5	584.3	901.1	1205.4
27.5°	1694.4	1676.7	1655.7	1500.6	1211.5	911.1	576.4	241.7	576.4	911.1	1211.5
30°	1667.1	1652.8	1637.2	1487.6	1203.9	906.2	566.0	225.9	566.0	906.2	1203.9
32.5°	1645.7	1628.8	1614.0	1467.5	1189.3	895.3	553.6	211.8	553.6	895.3	1189.3
35°	1631.3	1603.0	1579.7	1430.1	1154.2	863.3	527.0	190.8	527.0	863.3	1154.2
37.5°	1637.5	1590.5	1541.5	1378.5	1101.3	813.3	493.1	172.8	493.1	813.3	1101.3
40°	1635.9	1578.2	1512.9	1340.9	1062.1	776.3	469.3	162.3	469.3	776.3	1062.1
42.5°	1618.4	1552.5	1476.2	1297.6	1016.5	733.0	442.4	151.8	442.4	733.0	1016.5
45°	1582.8	1507.3	1417.6	1229.0	941.5	660.6	399.4	138.2	399.4	660.6	941.5
47.5°	1532.3	1455.0	1359.8	1162.0	861.4	579.2	352.3	125.4	352.3	579.2	861.4
50°	1487.3	1412.3	1318.7	1116.9	807.0	523.9	321.1	118.4	321.1	523.9	807.0
52.5°	1434.3	1363.7	1275.6	1072.3	753.8	470.1	290.7	111.4	290.7	470.1	753.8
55°	1341.6	1280.0	1203.0	1001.7	676.2	395.5	249.3	103.1	249.3	395.5	676.2
57.5°	1239.1	1186.7	1121.0	926.5	603.4	331.5	213.5	95.6	213.5	331.5	603.4
60°	1165.4	1117.7	1058.2	871.6	557.7	296.8	194.4	92.1	194.4	296.8	557.7
62.5°	1088.0	1044.0	989.2	811.9	512.1	265.0	175.9	86.8	175.9	265.0	512.1
65°	962.5	926.2	880.3	721.0	448.1	225.4	153.3	81.1	153.3	225.4	448.1
67.5°	806.9	789.2	760.7	627.5	389.5	195.7	134.5	73.2	134.5	195.7	389.5
70°	682.5	685.7	675.9	565.3	353.8	181.0	124.5	68.0	124.5	181.0	353.8
72.5°	520.5	556.4	577.9	497.3	314.6	165.1	114.8	64.5	114.8	165.1	314.6
75°	246.1	315.8	409.4	387.9	251.5	138.9	98.0	57.0	98.0	138.9	251.5
77.5°	189.0	225.7	275.2	259.0	176.9	107.7	77.1	46.5	77.1	107.7	176.9
80°	153.8	155.0	156.9	143.8	115.5	88.2	63.8	39.5	63.8	88.2	115.5
82.5°	112.8	111.7	109.7	100.9	85.1	68.7	50.6	32.5	50.6	68.7	85.1
85°	36.8	43.1	50.9	52.4	47.5	41.2	30.5	19.7	30.5	41.2	47.5
87.5°	8.8	8.8	8.8	10.3	13.5	14.8	10.9	7.0	10.9	14.8	13.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1435895

CATALOG NUMBER: SQ2W-FB-OU-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	456.1	456.1	456.1	456.1	456.1	456.1	456.1	456.1	456.1	456.1	456.1
2.5°	488.3	498.4	509.4	518.7	523.4	528.1	523.4	518.7	509.4	498.4	488.3
5°	590.6	643.8	703.2	754.1	779.5	804.8	779.5	754.1	703.2	643.8	590.6
7.5°	818.9	972.7	1132.1	1264.4	1315.1	1365.8	1315.1	1264.4	1132.1	972.7	818.9
10°	1046.8	1244.6	1383.0	1493.6	1520.9	1548.2	1520.9	1493.6	1383.0	1244.6	1046.8
12.5°	1195.5	1401.2	1498.2	1578.1	1606.1	1634.2	1606.1	1578.1	1498.2	1401.2	1195.5
15°	1328.0	1539.5	1618.4	1685.4	1716.6	1747.8	1716.6	1685.4	1618.4	1539.5	1328.0
17.5°	1401.2	1607.5	1685.7	1748.5	1765.5	1782.4	1765.5	1748.5	1685.7	1607.5	1401.2
20°	1443.9	1638.9	1706.1	1759.2	1770.0	1780.7	1770.0	1759.2	1706.1	1638.9	1443.9
22.5°	1474.9	1657.0	1707.9	1748.9	1760.4	1771.9	1760.4	1748.9	1707.9	1657.0	1474.9
25°	1505.6	1671.8	1703.9	1730.0	1737.8	1745.6	1737.8	1730.0	1703.9	1671.8	1505.6
27.5°	1500.6	1655.7	1676.7	1694.4	1702.0	1709.6	1702.0	1694.4	1676.7	1655.7	1500.6
30°	1487.6	1637.2	1652.8	1667.1	1677.9	1688.6	1677.9	1667.1	1652.8	1637.2	1487.6
32.5°	1467.5	1614.0	1628.8	1645.7	1668.9	1692.1	1668.9	1645.7	1628.8	1614.0	1467.5
35°	1430.1	1579.7	1603.0	1631.3	1674.2	1717.1	1674.2	1631.3	1603.0	1579.7	1430.1
37.5°	1378.5	1541.5	1590.5	1637.5	1678.8	1720.2	1678.8	1637.5	1590.5	1541.5	1378.5
40°	1340.9	1512.9	1578.2	1635.9	1671.0	1706.1	1671.0	1635.9	1578.2	1512.9	1340.9
42.5°	1297.6	1476.2	1552.5	1618.4	1653.5	1688.6	1653.5	1618.4	1552.5	1476.2	1297.6
45°	1229.0	1417.6	1507.3	1582.8	1616.0	1649.1	1616.0	1582.8	1507.3	1417.6	1229.0
47.5°	1162.0	1359.8	1455.0	1532.3	1556.5	1580.7	1556.5	1532.3	1455.0	1359.8	1162.0
50°	1116.9	1318.7	1412.3	1487.3	1506.8	1526.3	1506.8	1487.3	1412.3	1318.7	1116.9
52.5°	1072.3	1275.6	1363.7	1434.3	1452.2	1470.2	1452.2	1434.3	1363.7	1275.6	1072.3
55°	1001.7	1203.0	1280.0	1341.6	1357.2	1372.8	1357.2	1341.6	1280.0	1203.0	1001.7
57.5°	926.5	1121.0	1186.7	1239.1	1251.8	1264.5	1251.8	1239.1	1186.7	1121.0	926.5
60°	871.6	1058.2	1117.7	1165.4	1178.1	1190.8	1178.1	1165.4	1117.7	1058.2	871.6
62.5°	811.9	989.2	1044.0	1088.0	1099.9	1111.8	1099.9	1088.0	1044.0	989.2	811.9
65°	721.0	880.3	926.2	962.5	970.3	978.1	970.3	962.5	926.2	880.3	721.0
67.5°	627.5	760.7	789.2	806.9	792.2	777.6	792.2	806.9	789.2	760.7	627.5
70°	565.3	675.9	685.7	682.5	640.6	598.7	640.6	682.5	685.7	675.9	565.3
72.5°	497.3	577.9	556.4	520.5	441.2	361.8	441.2	520.5	556.4	577.9	497.3
75°	387.9	409.4	315.8	246.1	248.0	250.0	248.0	246.1	315.8	409.4	387.9
77.5°	259.0	275.2	225.7	189.0	190.8	192.5	190.8	189.0	225.7	275.2	259.0
80°	143.8	156.9	155.0	153.8	154.7	155.7	154.7	153.8	155.0	156.9	143.8
82.5°	100.9	109.7	111.7	112.8	111.5	110.1	111.5	112.8	111.7	109.7	100.9
85°	52.4	50.9	43.1	36.8	34.8	32.9	34.8	36.8	43.1	50.9	52.4
87.5°	10.3	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	10.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1435895

CATALOG NUMBER: SQ2W-FB-0U-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	456.1	456.1	456.1	456.1
2.5°	478.9	469.8	461.2	452.6
5°	543.9	501.5	472.2	443.0
7.5°	670.8	544.8	485.3	425.9
10°	789.5	575.8	492.9	410.1
12.5°	881.3	617.5	505.0	392.5
15°	983.9	685.7	524.8	364.0
17.5°	1066.9	762.7	548.7	334.6
20°	1121.3	816.5	565.1	313.6
22.5°	1161.7	856.5	575.4	294.3
25°	1205.4	901.1	584.3	267.5
27.5°	1211.5	911.1	576.4	241.7
30°	1203.9	906.2	566.0	225.9
32.5°	1189.3	895.3	553.6	211.8
35°	1154.2	863.3	527.0	190.8
37.5°	1101.3	813.3	493.1	172.8
40°	1062.1	776.3	469.3	162.3
42.5°	1016.5	733.0	442.4	151.8
45°	941.5	660.6	399.4	138.2
47.5°	861.4	579.2	352.3	125.4
50°	807.0	523.9	321.1	118.4
52.5°	753.8	470.1	290.7	111.4
55°	676.2	395.5	249.3	103.1
57.5°	603.4	331.5	213.5	95.6
60°	557.7	296.8	194.4	92.1
62.5°	512.1	265.0	175.9	86.8
65°	448.1	225.4	153.3	81.1
67.5°	389.5	195.7	134.5	73.2
70°	353.8	181.0	124.5	68.0
72.5°	314.6	165.1	114.8	64.5
75°	251.5	138.9	98.0	57.0
77.5°	176.9	107.7	77.1	46.5
80°	115.5	88.2	63.8	39.5
82.5°	85.1	68.7	50.6	32.5
85°	47.5	41.2	30.5	19.7
87.5°	13.5	14.8	10.9	7.0
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P1435895  
 CATALOG NUMBER: SQ2W-FB-0U-100D-L830-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.88	18.56	17.24	18.87	19.19	26.47	28.16	26.84	28.47	28.78
	3H	17.87	19.40	18.25	19.72	20.08	28.14	29.66	28.51	29.99	30.35
	4H	18.31	19.74	18.71	20.09	20.46	28.35	29.79	28.75	30.13	30.51
	6H	18.60	19.93	19.01	20.30	20.69	28.47	29.80	28.88	30.16	30.55
	8H	18.72	19.99	19.14	20.38	20.78	28.51	29.78	28.93	30.17	30.57
	12H	18.80	20.01	19.23	20.40	20.82	28.51	29.73	28.94	30.11	30.54
4H	2H	21.69	23.13	22.09	23.47	23.85	26.93	28.37	27.33	28.72	29.09
	3H	22.89	24.10	23.30	24.49	24.89	28.90	30.10	29.30	30.49	30.89
	4H	23.21	24.30	23.64	24.71	25.14	29.15	30.24	29.58	30.65	31.09
	6H	23.40	24.34	23.85	24.78	25.24	29.33	30.28	29.79	30.72	31.17
	8H	23.46	24.34	23.92	24.78	25.25	29.40	30.28	29.86	30.73	31.19
	12H	23.50	24.29	23.98	24.77	25.24	29.42	30.22	29.90	30.69	31.16
8H	4H	24.47	25.36	24.93	25.80	26.26	29.31	30.20	29.77	30.64	31.10
	6H	24.77	25.50	25.26	25.99	26.46	29.55	30.28	30.04	30.77	31.24
	8H	24.88	25.54	25.39	26.04	26.53	29.65	30.31	30.16	30.81	31.30
	12H	24.96	25.54	25.47	26.03	26.59	29.69	30.27	30.20	30.76	31.32
12H	4H	24.54	25.33	25.02	25.81	26.28	29.31	30.10	29.79	30.57	31.04
	6H	24.89	25.54	25.40	26.05	26.54	29.54	30.20	30.05	30.70	31.19
	8H	25.07	25.64	25.57	26.13	26.69	29.68	30.26	30.19	30.75	31.31