

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937707

Luminaire Tested: SQ4-FB-100U-100D-B50-1D-UNV-W2A-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937707
REPORT IS A COMBINATION OF REPORTS P933575 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-100D-B50-1D-UNV-W2A-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10085.3 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 87
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937707

CATALOG NUMBER: SQ4-FB-100U-100D-B50-1D-UNV-W2A-W-6

Luminous Intensity Polar Plot



TEST NUMBER: P937707

CATALOG NUMBER: SQ4-FB-100U-100D-B50-1D-UNV-W2A-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	91	87	84	88	84	80	77	69	67	65	56	55	53	44	43	42
2	87	79	73	68	79	73	67	63	60	56	53	49	46	43	38	36	34
3	79	69	62	56	72	63	57	52	53	48	44	43	39	36	33	31	29
4	72	61	53	46	65	56	49	43	46	41	37	38	34	30	29	27	24
5	66	54	46	39	60	49	42	37	41	36	31	33	29	26	26	23	21
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	20	18
7	56	43	35	29	51	40	32	27	33	27	23	27	23	19	21	18	16
8	51	39	31	26	47	36	29	24	30	24	20	25	20	17	19	16	14
9	48	35	28	23	44	33	26	21	27	22	18	22	18	15	18	15	12
10	44	32	25	20	41	30	23	19	25	20	16	21	16	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3561	3561	3561
5°	3478	4114	4787
10°	3153	5997	7935
15°	2679	7833	9582
20°	2180	9075	9766
25°	1818	9494	9567
30°	1532	9552	9549
35°	1354	9390	9796
40°	1179	9181	10051
45°	1067	9028	10090
50°	979	8889	9924
55°	935	8687	9484
60°	957	8302	8789
65°	994	7718	7834
70°	1057	6727	6618
75°	1166	5479	5165
80°	1266	3796	3481
85°	1103	2011	1781

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 10090 cd/sqm

TEST NUMBER: P937707

CATALOG NUMBER: SQ4-FB-100U-100D-B50-1D-UNV-W2A-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.5	0.7
10°-20°	330.0	3.3
20°-30°	577.3	5.7
30°-40°	743.1	7.4
40°-50°	830.0	8.2
50°-60°	795.0	7.9
60°-70°	630.0	6.2
70°-80°	370.5	3.7
80°-90°	106.2	1.1
90°-100°	423.2	4.2
100°-110°	1112.7	11.0
110°-120°	1153.8	11.4
120°-130°	925.5	9.2
130°-140°	726.2	7.2
140°-150°	557.4	5.5
150°-160°	401.4	4.0
160°-170°	245.6	2.4
170°-180°	83.0	0.8
0°-30°	981.8	9.7
0°-40°	1724.9	17.1
0°-60°	3349.9	33.2
0°-90°	4456.6	44.2
90°-120°	2689.7	26.7
90°-150°	4898.7	48.6
90°-180°	5629.0	55.8
0°-180°	10085.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	576	576	576	576	576	
5°	561	602	677	766	794	52
15°	420	776	1307	1584	1634	117
25°	268	879	1557	1625	1627	124
35°	181	840	1466	1549	1610	113
45°	124	670	1296	1484	1551	96
55°	89	426	1100	1277	1312	81
65°	70	226	816	918	931	70
75°	52	139	448	492	494	54
85°	18	43	111	122	124	20
90°	6	16	44	22	22	6
95°	56	219	729	376	256	62
105°	200	304	1230	1868	1742	212
115°	356	432	985	1966	2244	352
125°	495	555	896	1515	1787	440
135°	590	650	868	1223	1386	457
145°	685	728	857	1043	1125	429
155°	774	795	857	941	968	356
165°	835	846	857	891	902	236
175°	868	868	863	874	874	82
180°	868	868	868	868	868	

TEST NUMBER: P937707

CATALOG NUMBER: SQ4-FB-100U-100D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	575.6	575.6	575.6	575.6	575.6	575.6	575.6	575.6	575.6	575.6	575.6
2.5°	575.6	575.6	579.4	581.2	584.9	586.7	590.5	594.2	605.2	607.1	610.8
5°	560.9	568.2	592.3	601.6	627.5	662.7	677.4	701.5	751.5	766.3	775.6
7.5°	538.6	555.3	614.6	629.3	694.1	786.7	825.6	877.4	957.0	995.8	1027.3
10°	503.4	538.6	644.2	679.3	784.8	925.5	997.7	1069.9	1190.2	1243.9	1264.3
12.5°	464.6	522.0	675.7	723.8	875.5	1081.0	1168.0	1247.5	1384.6	1456.8	1467.9
15°	420.2	497.9	705.3	775.6	971.7	1210.6	1306.9	1404.9	1532.6	1584.4	1597.4
17.5°	381.4	479.4	733.0	807.1	1045.8	1327.2	1425.3	1506.7	1610.4	1645.5	1654.8
20°	333.2	449.8	751.5	847.8	1123.6	1412.3	1506.7	1569.7	1640.0	1662.2	1665.9
22.5°	298.0	418.3	762.6	862.5	1175.3	1464.1	1543.7	1593.7	1641.9	1649.3	1651.1
25°	268.4	383.1	760.7	879.3	1219.8	1495.6	1556.7	1593.7	1621.5	1625.2	1625.2
27.5°	240.6	344.3	753.4	882.9	1253.1	1503.0	1551.1	1577.1	1590.0	1597.4	1597.4
30°	216.6	307.3	734.9	875.5	1267.9	1495.6	1534.5	1547.5	1560.4	1571.5	1577.1
32.5°	198.1	272.1	707.0	860.7	1269.8	1477.1	1504.9	1512.2	1530.7	1556.7	1565.9
35°	181.4	237.0	675.7	840.3	1258.7	1447.5	1466.0	1473.4	1510.4	1549.3	1562.2
37.5°	164.8	211.0	634.9	805.2	1242.0	1412.3	1425.3	1438.3	1495.6	1541.8	1556.7
40°	148.0	188.8	586.7	766.3	1216.1	1369.7	1380.8	1401.2	1477.1	1530.7	1545.6
42.5°	135.1	170.3	534.9	725.6	1182.8	1321.6	1338.2	1367.8	1454.9	1512.2	1529.0
45°	124.0	151.8	479.4	670.1	1140.2	1271.6	1295.7	1336.5	1428.9	1484.5	1499.4
47.5°	112.9	138.8	422.1	612.7	1093.9	1221.7	1253.1	1299.4	1393.8	1447.5	1460.4
50°	103.7	125.9	364.6	551.6	1043.9	1168.0	1205.0	1253.1	1349.3	1399.3	1416.0
52.5°	96.3	114.8	310.9	490.5	986.6	1112.5	1155.0	1205.0	1295.7	1343.8	1355.0
55°	88.8	105.5	264.7	425.7	927.4	1053.2	1099.5	1147.6	1236.4	1277.2	1284.6
57.5°	85.2	98.1	225.8	364.6	864.4	986.6	1038.4	1082.9	1166.1	1197.6	1205.0
60°	79.6	92.6	196.2	312.8	796.0	923.6	968.1	1012.5	1082.9	1108.8	1114.3
62.5°	74.1	88.8	174.0	262.8	725.6	849.6	894.0	934.7	994.0	1012.5	1019.9
65°	70.3	85.2	157.4	225.8	653.4	771.9	816.3	851.4	899.6	918.1	921.8
67.5°	66.6	81.4	144.4	194.4	581.2	694.1	727.4	760.7	797.8	816.3	818.2
70°	61.1	77.7	133.3	172.1	507.2	605.2	633.1	668.2	697.8	707.0	712.6
72.5°	57.3	72.2	125.9	155.5	431.3	520.1	546.0	566.4	592.3	601.6	601.6
75°	51.8	64.8	118.4	138.8	353.5	425.7	447.9	468.3	488.7	492.4	486.8
77.5°	46.2	57.3	101.8	116.7	275.8	336.9	355.4	366.5	383.1	386.9	388.7
80°	38.9	50.0	79.6	90.7	199.9	248.1	261.0	270.2	285.1	285.1	288.8
82.5°	29.6	38.9	57.3	64.8	135.1	170.3	181.4	187.0	196.2	196.2	196.2
85°	18.5	24.1	37.0	42.6	81.4	103.7	111.1	112.9	120.3	122.2	122.2
87.5°	9.2	13.0	24.1	25.9	42.6	53.7	53.7	57.3	57.3	55.6	53.7
90°	5.8	10.5	15.1	16.3	25.7	38.1	44.3	39.3	29.5	22.1	22.1
92.5°	23.4	63.0	102.6	112.5	158.1	218.9	249.4	218.6	156.9	110.7	106.3
95°	55.9	128.4	201.0	219.1	389.1	615.7	729.0	650.5	493.5	375.8	362.5
97.5°	96.8	160.7	224.7	240.7	524.1	902.0	1090.9	1041.3	942.1	867.7	842.3
100°	128.2	186.2	244.2	258.7	573.2	992.5	1202.2	1205.8	1213.1	1218.5	1188.2
102.5°	155.0	209.2	263.3	276.8	595.8	1021.0	1233.6	1296.9	1423.2	1518.0	1492.2
105°	200.4	246.3	292.2	303.6	612.5	1024.3	1230.2	1371.9	1655.1	1867.6	1853.7
107.5°	247.0	289.8	332.6	343.2	615.6	978.6	1160.2	1357.8	1753.0	2049.5	2052.8
110°	278.5	317.1	355.8	365.4	610.9	938.3	1101.9	1322.8	1764.7	2096.1	2110.6



TEST NUMBER: P937707

CATALOG NUMBER: SQ4-FB-100U-100D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	309.4	346.2	383.0	392.2	611.1	903.0	1048.9	1275.0	1727.2	2066.4	2088.6
115°	356.0	389.9	423.8	432.3	616.7	862.5	985.4	1203.2	1638.9	1965.6	1996.5
117.5°	402.1	432.9	463.7	471.4	628.1	837.1	941.7	1138.3	1531.4	1826.3	1860.5
120°	428.9	457.9	486.9	494.2	637.5	828.6	924.2	1103.8	1463.0	1732.5	1765.7
122.5°	455.1	484.4	513.7	521.0	650.9	824.2	910.8	1072.6	1396.0	1638.6	1671.5
125°	495.3	522.0	548.7	555.4	669.0	820.5	896.3	1033.7	1308.4	1514.6	1544.8
127.5°	528.0	554.9	581.9	588.6	687.1	818.4	884.0	1002.0	1237.9	1414.9	1440.4
130°	545.5	574.5	603.5	610.7	700.3	819.7	879.4	984.3	1194.4	1352.0	1375.5
132.5°	563.5	592.5	621.5	628.8	711.0	820.5	875.3	969.3	1157.3	1298.4	1319.5
135°	590.3	616.7	643.2	649.8	722.6	819.7	868.2	947.0	1104.5	1222.6	1240.8
137.5°	617.7	643.8	670.1	676.6	740.1	824.8	867.1	933.7	1066.8	1166.7	1181.5
140°	640.4	664.5	688.6	694.6	750.7	825.6	863.0	920.6	1035.5	1121.7	1135.7
142.5°	657.9	680.2	702.5	708.1	759.7	828.6	863.0	913.5	1014.5	1090.3	1102.2
145°	684.7	704.1	723.6	728.4	771.4	828.6	857.2	898.5	981.2	1043.1	1052.2
147.5°	711.5	730.4	749.3	754.0	788.4	834.2	857.2	889.7	954.7	1003.5	1011.0
150°	729.0	746.1	763.2	767.5	797.4	837.2	857.2	884.7	939.5	980.7	986.8
152.5°	747.1	760.1	773.0	776.2	803.2	839.2	857.2	880.7	927.6	962.7	967.3
155°	773.9	783.4	793.0	795.4	816.0	843.5	857.2	875.9	913.2	941.1	944.2
157.5°	793.7	803.1	812.3	814.6	828.8	847.8	857.2	871.7	900.7	922.5	924.7
160°	807.1	814.4	821.6	823.4	834.7	849.8	857.2	869.6	894.5	913.2	914.4
162.5°	820.5	825.9	831.4	832.8	840.9	851.8	857.2	867.7	888.7	904.4	905.5
165°	835.1	839.9	844.9	846.1	849.8	854.8	857.2	864.7	879.7	891.0	892.3
167.5°	848.4	850.8	853.1	853.7	856.8	861.0	863.0	868.0	877.8	885.2	885.7
170°	857.2	859.6	861.9	862.5	862.6	862.9	863.0	868.0	877.8	885.2	885.2
172.5°	861.9	862.4	862.9	863.0	863.0	863.0	863.0	866.9	874.7	880.5	880.0
175°	868.2	868.2	868.2	868.2	866.5	864.1	863.0	865.4	870.4	874.1	874.1
177.5°	868.2	868.2	868.2	868.2	866.9	865.2	864.2	866.2	870.0	872.9	872.4
180°	868.2	868.2	868.2	868.2	868.2	868.2	868.2	868.2	868.2	868.2	868.2

TEST NUMBER: P937707

CATALOG NUMBER: SQ4-FB-100U-100D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	575.6	575.6
2.5°	614.6	610.8
5°	790.4	794.1
7.5°	1064.3	1062.5
10°	1323.5	1340.1
12.5°	1512.2	1516.0
15°	1627.0	1634.4
17.5°	1671.5	1673.3
20°	1673.3	1669.6
22.5°	1652.9	1649.3
25°	1628.9	1627.0
27.5°	1606.7	1608.5
30°	1597.4	1602.9
32.5°	1597.4	1606.7
35°	1601.2	1610.4
37.5°	1599.3	1610.4
40°	1591.8	1604.8
42.5°	1571.5	1580.8
45°	1540.1	1551.1
47.5°	1499.4	1506.7
50°	1447.5	1454.9
52.5°	1382.7	1384.6
55°	1305.0	1312.4
57.5°	1221.7	1223.5
60°	1129.1	1134.6
62.5°	1031.0	1031.0
65°	927.4	931.0
67.5°	820.0	829.2
70°	710.8	712.6
72.5°	603.5	603.5
75°	492.4	494.2
77.5°	386.9	386.9
80°	286.9	288.8
82.5°	198.1	201.7
85°	124.0	124.0
87.5°	57.3	51.8
90°	22.1	22.1
92.5°	88.6	71.1
95°	309.2	255.8
97.5°	740.8	639.2
100°	1067.3	946.3
102.5°	1388.5	1284.9
105°	1798.0	1742.4
107.5°	2066.4	2079.8
110°	2168.7	2226.7

TEST NUMBER: P937707

CATALOG NUMBER: SQ4-FB-100U-100D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2177.7	2266.8
115°	2120.0	2243.6
117.5°	1997.5	2134.6
120°	1898.9	2032.0
122.5°	1802.8	1934.1
125°	1665.7	1786.6
127.5°	1542.5	1644.5
130°	1469.8	1564.1
132.5°	1403.9	1488.3
135°	1313.6	1386.3
137.5°	1241.1	1300.7
140°	1191.4	1247.1
142.5°	1150.2	1198.1
145°	1088.5	1124.7
147.5°	1041.0	1071.1
150°	1011.1	1035.5
152.5°	985.7	1004.0
155°	956.3	968.5
157.5°	933.2	941.7
160°	919.3	924.2
162.5°	910.2	914.9
165°	897.2	902.1
167.5°	887.8	889.8
170°	885.2	885.2
172.5°	878.2	876.5
175°	874.1	874.1
177.5°	870.3	868.2
180°	868.2	868.2

(END OF REPORT)