

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435973

Luminaire Tested: SQ2W-FB-K-075U-125D-L830-UNV-STD-W-WM-4

Issue Date: 3/24/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1435973  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/24/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-FB-K-075U-125D-L830-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8878.9 lumens  
Efficiency: N/A  
Efficacy: 122.0 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 72.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1435973

CATALOG NUMBER: SQ2W-FB-K-075U-125D-L830-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1435973

CATALOG NUMBER: SQ2W-FB-K-075U-125D-L830-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	96	92	88	94	90	87	83	79	77	74	69	67	65	60	59	57	53
2	91	83	77	71	85	78	73	68	69	64	61	60	57	54	52	50	47	43
3	83	73	65	59	77	68	61	56	60	55	50	53	48	45	46	42	40	36
4	75	64	56	49	70	60	53	47	53	47	42	47	42	38	40	37	34	30
5	69	57	48	42	64	53	46	40	47	41	36	41	36	32	36	32	29	26
6	63	51	42	36	59	48	40	34	42	36	31	37	32	28	32	28	25	22
7	58	45	37	31	54	43	35	30	38	32	27	33	28	24	29	25	22	19
8	54	41	33	27	50	39	31	26	34	28	24	30	25	22	27	22	19	17
9	50	37	29	24	47	35	28	23	31	25	21	28	23	19	24	20	17	15
10	47	34	26	21	44	32	25	21	29	23	19	26	21	17	22	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9171	9171	9171	9171
5°	8940	16241	8940	16241
10°	8371	31606	8371	31606
15°	7577	36377	7577	36377
20°	6709	38095	6709	38095
25°	5934	38720	5934	38720
30°	5242	39197	5242	39197
35°	4683	42140	4683	42140
40°	4260	44775	4260	44775
45°	3927	46886	3927	46886
50°	3705	47737	3705	47737
55°	3612	48115	3612	48115
60°	3704	47878	3704	47878
65°	3859	46524	3859	46524
70°	3994	35188	3994	35188
75°	4429	19419	4429	19419
80°	4575	18029	4575	18029
85°	4557	7595	4557	7595

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 52.5°  
 Luminance: 48551 cd/sqm



TEST NUMBER: P1435973

CATALOG NUMBER: SQ2W-FB-K-075U-125D-L830-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.2	1.1
10°-20°	434.2	4.9
20°-30°	764.0	8.6
30°-40°	989.0	11.1
40°-50°	1090.7	12.3
50°-60°	1018.0	11.5
60°-70°	786.5	8.9
70°-80°	362.5	4.1
80°-90°	73.9	0.8
90°-100°	89.0	1.0
100°-110°	259.5	2.9
110°-120°	423.5	4.8
120°-130°	537.4	6.1
130°-140°	575.1	6.5
140°-150°	537.0	6.0
150°-160°	441.9	5.0
160°-170°	296.3	3.3
170°-180°	105.2	1.2
0°-30°	1293.4	14.6
0°-40°	2282.4	25.7
0°-60°	4391.1	49.5
0°-90°	5614.1	63.2
90°-120°	772.0	8.7
90°-150°	2421.5	27.3
90°-180°	3265.0	36.8
0°-180°	8878.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	568	568	568	568	568	
5°	552	1002	552	1002	552	51
15°	453	2176	453	2176	453	126
25°	333	2174	333	2174	333	153
35°	238	2138	238	2138	238	149
45°	172	2053	172	2053	172	133
55°	128	1709	128	1709	128	116
65°	101	1218	101	1218	101	99
75°	71	311	71	311	71	73
85°	25	41	25	41	25	26
90°	3	25	3	49	3	4
95°	35	26	35	152	35	42
105°	165	264	165	364	165	175
115°	316	438	316	540	316	312
125°	468	695	468	662	468	418
135°	636	909	636	733	636	491
145°	812	1048	812	749	812	508
155°	965	1138	965	777	965	443
165°	1066	1187	1066	894	1066	300
175°	1115	1162	1115	1049	1115	106
180°	1118	1118	1118	1118	1118	



TEST NUMBER: P1435973

CATALOG NUMBER: SQ2W-FB-K-075U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	568.0	568.0	568.0	568.0	568.0	568.0	568.0	568.0	568.0	568.0	568.0
2.5°	563.6	574.3	584.9	596.4	608.0	620.6	634.2	645.9	651.7	657.5	651.7
5°	551.6	588.0	624.4	677.2	735.4	801.6	875.6	939.0	970.6	1002.1	970.6
7.5°	530.3	604.3	678.3	835.2	1019.7	1211.2	1409.7	1574.4	1637.5	1700.6	1637.5
10°	510.6	613.8	716.9	983.0	1303.4	1549.7	1722.1	1859.8	1893.8	1927.8	1893.8
12.5°	488.8	628.8	768.9	1097.3	1488.6	1744.6	1865.5	1964.9	1999.9	2034.8	1999.9
15°	453.3	653.5	853.8	1225.1	1653.5	1916.9	2015.2	2098.6	2137.4	2176.3	2137.4
17.5°	416.7	683.2	949.7	1328.5	1744.8	2001.6	2098.9	2177.2	2198.3	2219.4	2198.3
20°	390.5	703.6	1016.7	1396.2	1797.9	2040.6	2124.4	2190.5	2203.9	2217.2	2203.9
22.5°	366.4	716.4	1066.4	1446.5	1836.5	2063.2	2126.6	2177.7	2192.0	2206.3	2192.0
25°	333.1	727.5	1122.0	1500.9	1874.7	2081.6	2121.6	2154.1	2163.8	2173.5	2163.8
27.5°	300.9	717.7	1134.4	1508.5	1868.5	2061.6	2087.8	2109.8	2119.3	2128.7	2119.3
30°	281.2	704.8	1128.3	1499.1	1852.2	2038.5	2057.9	2075.8	2089.2	2102.5	2089.2
32.5°	263.8	689.3	1114.7	1480.9	1827.2	2009.6	2028.1	2049.1	2078.0	2106.9	2078.0
35°	237.6	656.2	1074.9	1437.2	1780.6	1966.9	1996.0	2031.2	2084.6	2138.0	2084.6
37.5°	215.2	614.0	1012.7	1371.3	1716.4	1919.5	1980.4	2038.9	2090.4	2141.9	2090.4
40°	202.1	584.3	966.6	1322.5	1669.6	1883.8	1965.1	2037.0	2080.7	2124.4	2080.7
42.5°	189.0	550.8	912.7	1265.7	1615.7	1838.2	1933.1	2015.2	2058.8	2102.5	2058.8
45°	172.0	497.3	822.5	1172.3	1530.3	1765.2	1876.8	1970.9	2012.1	2053.4	2012.1
47.5°	156.2	438.7	721.2	1072.6	1446.8	1693.2	1811.6	1908.0	1938.1	1968.2	1938.1
50°	147.5	399.9	652.3	1004.8	1390.8	1642.0	1758.5	1851.9	1876.2	1900.5	1876.2
52.5°	138.7	362.0	585.3	938.6	1335.2	1588.3	1698.0	1785.9	1808.2	1830.6	1808.2
55°	128.3	310.4	492.4	841.9	1247.3	1497.9	1593.7	1670.5	1689.9	1709.3	1689.9
57.5°	119.1	265.9	412.7	751.3	1153.7	1395.8	1477.6	1542.9	1558.7	1574.4	1558.7
60°	114.7	242.1	369.5	694.5	1085.2	1317.6	1391.7	1451.1	1466.9	1482.7	1466.9
62.5°	108.1	219.1	330.0	637.7	1011.0	1231.7	1299.9	1354.8	1369.6	1384.4	1369.6
65°	101.0	190.8	280.6	557.9	897.7	1096.2	1153.2	1198.4	1208.1	1217.8	1208.1
67.5°	91.2	167.4	243.6	484.9	781.3	947.2	982.6	1004.7	986.5	968.3	986.5
70°	84.6	155.0	225.4	440.5	703.9	841.6	853.8	849.8	797.6	745.4	797.6
72.5°	80.3	142.9	205.5	391.7	619.2	719.5	692.8	648.1	549.3	450.5	549.3
75°	71.0	122.0	172.9	313.1	483.0	509.7	393.2	306.4	308.9	311.3	308.9
77.5°	57.9	96.0	134.1	220.3	322.4	342.7	281.1	235.4	237.6	239.7	237.6
80°	49.2	79.5	109.8	143.8	179.0	195.4	193.0	191.4	192.7	193.9	192.7
82.5°	40.4	63.0	85.6	105.9	125.6	136.6	139.1	140.5	138.8	137.1	138.8
85°	24.6	37.9	51.3	59.2	65.2	63.4	53.7	45.8	43.4	41.0	43.4
87.5°	9.4	15.2	21.2	20.4	17.2	15.4	15.4	15.7	15.9	15.9	15.9
90°	3.4	7.9	13.6	18.1	21.5	22.6	22.6	23.7	24.8	24.8	24.8
92.5°	12.4	19.7	19.9	19.9	24.2	26.2	28.0	28.2	29.4	29.4	29.4
95°	35.0	38.4	57.6	56.5	38.4	30.5	26.0	26.0	26.0	26.0	26.0
97.5°	66.9	71.8	75.0	100.5	106.2	102.6	83.6	70.3	62.8	59.4	62.8
100°	94.9	97.1	103.9	105.0	133.3	160.4	146.8	129.9	124.2	120.9	124.2
102.5°	122.9	124.2	134.6	139.4	145.9	161.3	208.3	203.1	199.2	198.6	199.2
105°	164.9	166.0	185.2	194.3	198.8	198.8	197.7	220.2	256.4	264.3	256.4
107.5°	209.9	215.1	237.6	261.8	267.0	268.4	262.5	259.1	257.7	258.7	257.7
110°	240.6	248.5	275.6	306.1	314.0	316.3	314.0	310.6	308.3	308.3	308.3

TEST NUMBER: P1435973

CATALOG NUMBER: SQ2W-FB-K-075U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	270.4	281.9	312.6	347.7	361.0	367.8	362.8	360.3	358.0	359.9	358.0
115°	316.3	333.2	373.9	410.0	437.1	440.5	439.4	439.4	438.2	438.2	438.2
117.5°	358.7	385.8	431.5	473.5	504.9	513.9	518.4	517.1	515.7	518.0	515.7
120°	388.5	420.2	472.1	519.6	550.1	563.6	568.1	565.9	568.1	565.9	568.1
122.5°	420.2	459.0	510.1	559.3	595.2	610.6	616.0	616.5	616.9	615.6	616.9
125°	467.6	515.0	574.9	625.7	663.0	681.1	685.6	686.7	689.0	694.6	689.0
127.5°	515.5	569.3	635.0	684.0	722.2	744.1	751.1	753.6	758.3	760.8	758.3
130°	548.9	609.9	676.6	722.9	760.1	783.9	796.3	799.7	805.3	804.2	805.3
132.5°	584.2	647.9	715.4	763.5	798.1	823.6	834.2	843.9	846.0	847.6	846.0
135°	635.9	704.8	772.6	820.0	852.8	877.6	891.2	900.2	905.8	909.2	905.8
137.5°	690.3	763.1	828.1	870.4	903.4	924.8	940.2	949.7	955.5	958.2	955.5
140°	727.4	797.4	860.7	904.7	934.1	955.5	969.1	980.4	987.2	987.2	987.2
142.5°	762.6	831.7	893.2	937.2	963.0	982.6	997.1	1005.7	1013.4	1013.4	1013.4
145°	812.1	881.0	937.5	981.5	1003.0	1021.0	1036.9	1043.6	1048.2	1048.2	1048.2
147.5°	863.8	924.8	976.3	1018.6	1036.6	1057.9	1070.3	1075.7	1081.4	1078.9	1081.4
150°	894.5	951.0	1000.7	1040.2	1058.3	1078.7	1091.1	1095.6	1101.2	1097.9	1101.2
152.5°	924.4	978.1	1023.3	1060.1	1075.5	1095.8	1110.1	1114.6	1118.4	1115.9	1118.4
155°	964.6	1012.0	1053.8	1087.7	1101.2	1120.4	1134.0	1139.6	1144.2	1138.5	1144.2
157.5°	1000.5	1041.4	1077.7	1108.9	1123.4	1139.9	1152.5	1159.5	1164.0	1161.6	1164.0
160°	1022.2	1059.4	1092.2	1121.6	1135.1	1149.8	1163.4	1171.3	1175.8	1172.4	1175.8
162.5°	1040.2	1073.9	1104.9	1131.5	1143.3	1156.1	1172.4	1179.4	1183.9	1179.6	1183.9
165°	1066.2	1093.3	1120.4	1143.0	1153.2	1163.4	1180.3	1188.2	1191.6	1187.1	1191.6
167.5°	1085.9	1106.7	1128.6	1148.0	1155.5	1165.4	1182.3	1188.9	1193.2	1187.5	1193.2
170°	1096.7	1114.8	1134.0	1149.8	1155.5	1164.5	1181.4	1187.1	1190.5	1184.8	1190.5
172.5°	1105.8	1119.3	1134.9	1148.9	1151.8	1159.1	1175.1	1180.8	1183.2	1178.5	1183.2
175°	1114.8	1122.7	1134.0	1143.0	1141.9	1146.4	1160.0	1164.5	1169.0	1162.2	1169.0
177.5°	1119.1	1122.7	1126.3	1131.7	1128.1	1128.1	1138.1	1140.8	1141.7	1138.1	1141.7
180°	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2



TEST NUMBER: P1435973

CATALOG NUMBER: SQ2W-FB-K-075U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	568.0	568.0	568.0	568.0	568.0	568.0	568.0	568.0	568.0	568.0	568.0
2.5°	645.9	634.2	620.6	608.0	596.4	584.9	574.3	563.6	574.3	584.9	596.4
5°	939.0	875.6	801.6	735.4	677.2	624.4	588.0	551.6	588.0	624.4	677.2
7.5°	1574.4	1409.7	1211.2	1019.7	835.2	678.3	604.3	530.3	604.3	678.3	835.2
10°	1859.8	1722.1	1549.7	1303.4	983.0	716.9	613.8	510.6	613.8	716.9	983.0
12.5°	1964.9	1865.5	1744.6	1488.6	1097.3	768.9	628.8	488.8	628.8	768.9	1097.3
15°	2098.6	2015.2	1916.9	1653.5	1225.1	853.8	653.5	453.3	653.5	853.8	1225.1
17.5°	2177.2	2098.9	2001.6	1744.8	1328.5	949.7	683.2	416.7	683.2	949.7	1328.5
20°	2190.5	2124.4	2040.6	1797.9	1396.2	1016.7	703.6	390.5	703.6	1016.7	1396.2
22.5°	2177.7	2126.6	2063.2	1836.5	1446.5	1066.4	716.4	366.4	716.4	1066.4	1446.5
25°	2154.1	2121.6	2081.6	1874.7	1500.9	1122.0	727.5	333.1	727.5	1122.0	1500.9
27.5°	2109.8	2087.8	2061.6	1868.5	1508.5	1134.4	717.7	300.9	717.7	1134.4	1508.5
30°	2075.8	2057.9	2038.5	1852.2	1499.1	1128.3	704.8	281.2	704.8	1128.3	1499.1
32.5°	2049.1	2028.1	2009.6	1827.2	1480.9	1114.7	689.3	263.8	689.3	1114.7	1480.9
35°	2031.2	1996.0	1966.9	1780.6	1437.2	1074.9	656.2	237.6	656.2	1074.9	1437.2
37.5°	2038.9	1980.4	1919.5	1716.4	1371.3	1012.7	614.0	215.2	614.0	1012.7	1371.3
40°	2037.0	1965.1	1883.8	1669.6	1322.5	966.6	584.3	202.1	584.3	966.6	1322.5
42.5°	2015.2	1933.1	1838.2	1615.7	1265.7	912.7	550.8	189.0	550.8	912.7	1265.7
45°	1970.9	1876.8	1765.2	1530.3	1172.3	822.5	497.3	172.0	497.3	822.5	1172.3
47.5°	1908.0	1811.6	1693.2	1446.8	1072.6	721.2	438.7	156.2	438.7	721.2	1072.6
50°	1851.9	1758.5	1642.0	1390.8	1004.8	652.3	399.9	147.5	399.9	652.3	1004.8
52.5°	1785.9	1698.0	1588.3	1335.2	938.6	585.3	362.0	138.7	362.0	585.3	938.6
55°	1670.5	1593.7	1497.9	1247.3	841.9	492.4	310.4	128.3	310.4	492.4	841.9
57.5°	1542.9	1477.6	1395.8	1153.7	751.3	412.7	265.9	119.1	265.9	412.7	751.3
60°	1451.1	1391.7	1317.6	1085.2	694.5	369.5	242.1	114.7	242.1	369.5	694.5
62.5°	1354.8	1299.9	1231.7	1011.0	637.7	330.0	219.1	108.1	219.1	330.0	637.7
65°	1198.4	1153.2	1096.2	897.7	557.9	280.6	190.8	101.0	190.8	280.6	557.9
67.5°	1004.7	982.6	947.2	781.3	484.9	243.6	167.4	91.2	167.4	243.6	484.9
70°	849.8	853.8	841.6	703.9	440.5	225.4	155.0	84.6	155.0	225.4	440.5
72.5°	648.1	692.8	719.5	619.2	391.7	205.5	142.9	80.3	142.9	205.5	391.7
75°	306.4	393.2	509.7	483.0	313.1	172.9	122.0	71.0	122.0	172.9	313.1
77.5°	235.4	281.1	342.7	322.4	220.3	134.1	96.0	57.9	96.0	134.1	220.3
80°	191.4	193.0	195.4	179.0	143.8	109.8	79.5	49.2	79.5	109.8	143.8
82.5°	140.5	139.1	136.6	125.6	105.9	85.6	63.0	40.4	63.0	85.6	105.9
85°	45.8	53.7	63.4	65.2	59.2	51.3	37.9	24.6	37.9	51.3	59.2
87.5°	15.7	15.4	15.4	17.2	20.4	21.2	15.2	9.4	15.2	20.9	20.8
90°	23.7	22.6	22.6	21.5	18.1	13.6	7.9	3.4	7.9	12.4	20.3
92.5°	28.2	28.0	26.2	24.2	19.9	19.9	19.7	12.4	21.5	30.5	43.8
95°	26.0	26.0	30.5	38.4	56.5	57.6	38.4	35.0	49.7	70.0	88.1
97.5°	70.3	83.6	102.6	106.2	100.5	75.0	71.8	66.9	91.0	111.1	140.3
100°	129.9	146.8	160.4	133.3	105.0	103.9	97.1	94.9	120.9	140.1	168.3
102.5°	203.1	208.3	161.3	145.9	139.4	134.6	124.2	122.9	148.9	175.3	199.0
105°	220.2	197.7	198.8	198.8	194.3	185.2	166.0	164.9	194.3	224.8	254.1
107.5°	259.1	262.5	268.4	267.0	261.8	237.6	215.1	209.9	236.3	272.9	305.2
110°	310.6	314.0	316.3	314.0	306.1	275.6	248.5	240.6	264.3	302.7	337.7



TEST NUMBER: P1435973

CATALOG NUMBER: SQ2W-FB-K-075U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	360.3	362.8	367.8	361.0	347.7	312.6	281.9	270.4	294.1	333.4	369.3
115°	439.4	439.4	440.5	437.1	410.0	373.9	333.2	316.3	336.6	372.7	412.3
117.5°	517.1	518.4	513.9	504.9	473.5	431.5	385.8	358.7	374.8	412.9	453.6
120°	565.9	568.1	563.6	550.1	519.6	472.1	420.2	388.5	401.0	438.2	478.9
122.5°	616.5	616.0	610.6	595.2	559.3	510.1	459.0	420.2	425.4	459.9	499.7
125°	686.7	685.6	681.1	663.0	625.7	574.9	515.0	467.6	460.8	490.2	530.9
127.5°	753.6	751.1	744.1	722.2	684.0	635.0	569.3	515.5	500.4	518.9	556.2
130°	799.7	796.3	783.9	760.1	722.9	676.6	609.9	548.9	527.5	538.8	571.5
132.5°	843.9	834.2	823.6	798.1	763.5	715.4	647.9	584.2	554.6	559.5	585.1
135°	900.2	891.2	877.6	852.8	820.0	772.6	704.8	635.9	595.2	590.7	605.4
137.5°	949.7	940.2	924.8	903.4	870.4	828.1	763.1	690.3	639.1	623.9	629.6
140°	980.4	969.1	955.5	934.1	904.7	860.7	797.4	727.4	669.8	648.3	644.9
142.5°	1005.7	997.1	982.6	963.0	937.2	893.2	831.7	762.6	701.4	673.6	665.7
145°	1043.6	1036.9	1021.0	1003.0	981.5	937.5	881.0	812.1	751.1	715.0	698.0
147.5°	1075.7	1070.3	1057.9	1036.6	1018.6	976.3	924.8	863.8	801.3	756.5	734.6
150°	1095.6	1091.1	1078.7	1058.3	1040.2	1000.7	951.0	894.5	834.7	787.2	759.0
152.5°	1114.6	1110.1	1095.8	1075.5	1060.1	1023.3	978.1	924.4	863.6	816.2	787.0
155°	1139.6	1134.0	1120.4	1101.2	1087.7	1053.8	1012.0	964.6	912.6	862.9	830.2
157.5°	1159.5	1152.5	1139.9	1123.4	1108.9	1077.7	1041.4	1000.5	955.1	907.6	874.2
160°	1171.3	1163.4	1149.8	1135.1	1121.6	1092.2	1059.4	1022.2	980.4	937.5	901.3
162.5°	1179.4	1172.4	1156.1	1143.3	1131.5	1104.9	1073.9	1040.2	1003.0	965.5	932.0
165°	1188.2	1180.3	1163.4	1153.2	1143.0	1120.4	1093.3	1066.2	1034.6	1004.1	977.0
167.5°	1188.9	1182.3	1165.4	1155.5	1148.0	1128.6	1106.7	1085.9	1061.3	1037.3	1014.7
170°	1187.1	1181.4	1164.5	1155.5	1149.8	1134.0	1114.8	1096.7	1077.5	1057.2	1039.1
172.5°	1180.8	1175.1	1159.1	1151.8	1148.9	1134.9	1119.3	1105.8	1089.3	1074.4	1059.9
175°	1164.5	1160.0	1146.4	1141.9	1143.0	1134.0	1122.7	1114.8	1104.6	1095.6	1087.7
177.5°	1140.8	1138.1	1128.1	1128.1	1131.7	1126.3	1122.7	1119.1	1114.6	1111.9	1109.1
180°	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2

TEST NUMBER: P1435973

CATALOG NUMBER: SQ2W-FB-K-075U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	568.0	568.0	568.0	568.0	568.0	568.0	568.0	568.0	568.0	568.0	568.0
2.5°	608.0	620.6	634.2	645.9	651.7	657.5	651.7	645.9	634.2	620.6	608.0
5°	735.4	801.6	875.6	939.0	970.6	1002.1	970.6	939.0	875.6	801.6	735.4
7.5°	1019.7	1211.2	1409.7	1574.4	1637.5	1700.6	1637.5	1574.4	1409.7	1211.2	1019.7
10°	1303.4	1549.7	1722.1	1859.8	1893.8	1927.8	1893.8	1859.8	1722.1	1549.7	1303.4
12.5°	1488.6	1744.6	1865.5	1964.9	1999.9	2034.8	1999.9	1964.9	1865.5	1744.6	1488.6
15°	1653.5	1916.9	2015.2	2098.6	2137.4	2176.3	2137.4	2098.6	2015.2	1916.9	1653.5
17.5°	1744.8	2001.6	2098.9	2177.2	2198.3	2219.4	2198.3	2177.2	2098.9	2001.6	1744.8
20°	1797.9	2040.6	2124.4	2190.5	2203.9	2217.2	2203.9	2190.5	2124.4	2040.6	1797.9
22.5°	1836.5	2063.2	2126.6	2177.7	2192.0	2206.3	2192.0	2177.7	2126.6	2063.2	1836.5
25°	1874.7	2081.6	2121.6	2154.1	2163.8	2173.5	2163.8	2154.1	2121.6	2081.6	1874.7
27.5°	1868.5	2061.6	2087.8	2109.8	2119.3	2128.7	2119.3	2109.8	2087.8	2061.6	1868.5
30°	1852.2	2038.5	2057.9	2075.8	2089.2	2102.5	2089.2	2075.8	2057.9	2038.5	1852.2
32.5°	1827.2	2009.6	2028.1	2049.1	2078.0	2106.9	2078.0	2049.1	2028.1	2009.6	1827.2
35°	1780.6	1966.9	1996.0	2031.2	2084.6	2138.0	2084.6	2031.2	1996.0	1966.9	1780.6
37.5°	1716.4	1919.5	1980.4	2038.9	2090.4	2141.9	2090.4	2038.9	1980.4	1919.5	1716.4
40°	1669.6	1883.8	1965.1	2037.0	2080.7	2124.4	2080.7	2037.0	1965.1	1883.8	1669.6
42.5°	1615.7	1838.2	1933.1	2015.2	2058.8	2102.5	2058.8	2015.2	1933.1	1838.2	1615.7
45°	1530.3	1765.2	1876.8	1970.9	2012.1	2053.4	2012.1	1970.9	1876.8	1765.2	1530.3
47.5°	1446.8	1693.2	1811.6	1908.0	1938.1	1968.2	1938.1	1908.0	1811.6	1693.2	1446.8
50°	1390.8	1642.0	1758.5	1851.9	1876.2	1900.5	1876.2	1851.9	1758.5	1642.0	1390.8
52.5°	1335.2	1588.3	1698.0	1785.9	1808.2	1830.6	1808.2	1785.9	1698.0	1588.3	1335.2
55°	1247.3	1497.9	1593.7	1670.5	1689.9	1709.3	1689.9	1670.5	1593.7	1497.9	1247.3
57.5°	1153.7	1395.8	1477.6	1542.9	1558.7	1574.4	1558.7	1542.9	1477.6	1395.8	1153.7
60°	1085.2	1317.6	1391.7	1451.1	1466.9	1482.7	1466.9	1451.1	1391.7	1317.6	1085.2
62.5°	1011.0	1231.7	1299.9	1354.8	1369.6	1384.4	1369.6	1354.8	1299.9	1231.7	1011.0
65°	897.7	1096.2	1153.2	1198.4	1208.1	1217.8	1208.1	1198.4	1153.2	1096.2	897.7
67.5°	781.3	947.2	982.6	1004.7	986.5	968.3	986.5	1004.7	982.6	947.2	781.3
70°	703.9	841.6	853.8	849.8	797.6	745.4	797.6	849.8	853.8	841.6	703.9
72.5°	619.2	719.5	692.8	648.1	549.3	450.5	549.3	648.1	692.8	719.5	619.2
75°	483.0	509.7	393.2	306.4	308.9	311.3	308.9	306.4	393.2	509.7	483.0
77.5°	322.4	342.7	281.1	235.4	237.6	239.7	237.6	235.4	281.1	342.7	322.4
80°	179.0	195.4	193.0	191.4	192.7	193.9	192.7	191.4	193.0	195.4	179.0
82.5°	125.6	136.6	139.1	140.5	138.8	137.1	138.8	140.5	139.1	136.6	125.6
85°	65.2	63.4	53.7	45.8	43.4	41.0	43.4	45.8	53.7	63.4	65.2
87.5°	18.1	17.7	19.3	20.2	21.1	20.6	21.1	20.2	19.3	17.7	18.1
90°	26.0	33.9	41.8	46.3	50.8	48.6	50.8	46.3	41.8	33.9	26.0
92.5°	52.2	65.5	75.2	83.4	87.0	86.5	87.0	83.4	75.2	65.5	52.2
95°	105.0	120.9	136.7	148.0	154.7	152.5	154.7	148.0	136.7	120.9	105.0
97.5°	162.0	183.2	200.8	211.4	218.2	222.7	218.2	211.4	200.8	183.2	162.0
100°	199.9	220.2	240.6	253.0	264.3	268.8	264.3	253.0	240.6	220.2	199.9
102.5°	230.6	257.3	279.4	292.8	302.2	306.8	302.2	292.8	279.4	257.3	230.6
105°	281.2	309.5	333.2	350.1	360.3	363.7	360.3	350.1	333.2	309.5	281.2
107.5°	331.8	361.0	382.9	401.6	414.1	421.3	414.1	401.6	382.9	361.0	331.8
110°	371.6	395.3	419.0	436.0	448.4	452.9	448.4	436.0	419.0	395.3	371.6



TEST NUMBER: P1435973

CATALOG NUMBER: SQ2W-FB-K-075U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	405.0	431.5	455.2	472.1	486.4	492.7	486.4	472.1	455.2	431.5	405.0
115°	451.8	486.8	508.3	524.1	534.2	539.9	534.2	524.1	508.3	486.8	451.8
117.5°	490.6	527.2	550.7	562.9	567.7	571.7	567.7	562.9	550.7	527.2	490.6
120°	515.0	548.9	576.0	591.8	597.5	599.8	597.5	591.8	576.0	548.9	515.0
122.5°	537.6	569.7	595.9	615.3	624.6	626.9	624.6	615.3	595.9	569.7	537.6
125°	569.3	599.8	626.9	646.1	656.2	661.9	656.2	646.1	626.9	599.8	569.3
127.5°	596.8	629.8	654.6	672.0	682.0	686.5	682.0	672.0	654.6	629.8	596.8
130°	612.2	646.1	670.9	690.1	699.1	703.7	699.1	690.1	670.9	646.1	612.2
132.5°	623.9	659.6	685.4	702.8	712.7	717.2	712.7	702.8	685.4	659.6	623.9
135°	638.2	675.4	702.5	719.5	728.5	733.0	728.5	719.5	702.5	675.4	638.2
137.5°	650.6	684.5	712.7	730.5	738.7	741.6	738.7	730.5	712.7	684.5	650.6
140°	659.6	689.0	717.2	734.2	743.2	744.3	743.2	734.2	717.2	689.0	659.6
142.5°	671.4	694.4	719.0	736.0	745.0	747.0	745.0	736.0	719.0	694.4	671.4
145°	692.4	705.9	722.9	738.7	746.6	748.8	746.6	738.7	722.9	705.9	692.4
147.5°	718.8	723.1	731.9	742.3	750.0	751.6	750.0	742.3	731.9	723.1	718.8
150°	738.7	737.5	740.9	747.7	754.5	753.4	754.5	747.7	740.9	737.5	738.7
152.5°	761.3	754.7	754.5	757.7	760.8	760.6	760.8	757.7	754.5	754.7	761.3
155°	799.7	787.2	780.5	778.2	778.2	777.1	778.2	778.2	780.5	787.2	799.7
157.5°	841.9	824.5	814.4	808.9	807.4	804.9	807.4	808.9	814.4	824.5	841.9
160°	870.8	851.6	841.5	832.4	829.0	825.6	829.0	832.4	841.5	851.6	870.8
162.5°	897.9	879.6	868.6	860.4	857.0	851.9	857.0	860.4	868.6	879.6	897.9
165°	942.0	922.8	910.4	903.6	899.1	894.5	899.1	903.6	910.4	922.8	942.0
167.5°	986.0	965.0	956.9	949.2	944.9	936.8	944.9	949.2	956.9	965.0	986.0
170°	1013.1	993.9	989.4	982.6	974.7	965.7	974.7	982.6	989.4	993.9	1013.1
172.5°	1036.6	1023.8	1019.2	1012.5	1010.0	1002.7	1010.0	1012.5	1019.2	1023.8	1036.6
175°	1070.7	1060.6	1060.6	1059.4	1056.1	1049.3	1056.1	1059.4	1060.6	1060.6	1070.7
177.5°	1099.2	1093.8	1097.4	1097.4	1096.5	1090.2	1096.5	1097.4	1097.4	1093.8	1099.2
180°	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2



TEST NUMBER: P1435973

CATALOG NUMBER: SQ2W-FB-K-075U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	568.0	568.0	568.0	568.0
2.5°	596.4	584.9	574.3	563.6
5°	677.2	624.4	588.0	551.6
7.5°	835.2	678.3	604.3	530.3
10°	983.0	716.9	613.8	510.6
12.5°	1097.3	768.9	628.8	488.8
15°	1225.1	853.8	653.5	453.3
17.5°	1328.5	949.7	683.2	416.7
20°	1396.2	1016.7	703.6	390.5
22.5°	1446.5	1066.4	716.4	366.4
25°	1500.9	1122.0	727.5	333.1
27.5°	1508.5	1134.4	717.7	300.9
30°	1499.1	1128.3	704.8	281.2
32.5°	1480.9	1114.7	689.3	263.8
35°	1437.2	1074.9	656.2	237.6
37.5°	1371.3	1012.7	614.0	215.2
40°	1322.5	966.6	584.3	202.1
42.5°	1265.7	912.7	550.8	189.0
45°	1172.3	822.5	497.3	172.0
47.5°	1072.6	721.2	438.7	156.2
50°	1004.8	652.3	399.9	147.5
52.5°	938.6	585.3	362.0	138.7
55°	841.9	492.4	310.4	128.3
57.5°	751.3	412.7	265.9	119.1
60°	694.5	369.5	242.1	114.7
62.5°	637.7	330.0	219.1	108.1
65°	557.9	280.6	190.8	101.0
67.5°	484.9	243.6	167.4	91.2
70°	440.5	225.4	155.0	84.6
72.5°	391.7	205.5	142.9	80.3
75°	313.1	172.9	122.0	71.0
77.5°	220.3	134.1	96.0	57.9
80°	143.8	109.8	79.5	49.2
82.5°	105.9	85.6	63.0	40.4
85°	59.2	51.3	37.9	24.6
87.5°	20.8	20.9	15.2	9.4
90°	20.3	12.4	7.9	3.4
92.5°	43.8	30.5	21.5	12.4
95°	88.1	70.0	49.7	35.0
97.5°	140.3	111.1	91.0	66.9
100°	168.3	140.1	120.9	94.9
102.5°	199.0	175.3	148.9	122.9
105°	254.1	224.8	194.3	164.9
107.5°	305.2	272.9	236.3	209.9
110°	337.7	302.7	264.3	240.6



TEST NUMBER: P1435973

CATALOG NUMBER: SQ2W-FB-K-075U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	369.3	333.4	294.1	270.4
115°	412.3	372.7	336.6	316.3
117.5°	453.6	412.9	374.8	358.7
120°	478.9	438.2	401.0	388.5
122.5°	499.7	459.9	425.4	420.2
125°	530.9	490.2	460.8	467.6
127.5°	556.2	518.9	500.4	515.5
130°	571.5	538.8	527.5	548.9
132.5°	585.1	559.5	554.6	584.2
135°	605.4	590.7	595.2	635.9
137.5°	629.6	623.9	639.1	690.3
140°	644.9	648.3	669.8	727.4
142.5°	665.7	673.6	701.4	762.6
145°	698.0	715.0	751.1	812.1
147.5°	734.6	756.5	801.3	863.8
150°	759.0	787.2	834.7	894.5
152.5°	787.0	816.2	863.6	924.4
155°	830.2	862.9	912.6	964.6
157.5°	874.2	907.6	955.1	1000.5
160°	901.3	937.5	980.4	1022.2
162.5°	932.0	965.5	1003.0	1040.2
165°	977.0	1004.1	1034.6	1066.2
167.5°	1014.7	1037.3	1061.3	1085.9
170°	1039.1	1057.2	1077.5	1096.7
172.5°	1059.9	1074.4	1089.3	1105.8
175°	1087.7	1095.6	1104.6	1114.8
177.5°	1109.1	1111.9	1114.6	1119.1
180°	1118.2	1118.2	1118.2	1118.2



TEST NUMBER: P1435973  
 CATALOG NUMBER: SQ2W-FB-K-075U-125D-L830-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.00	16.03	15.83	16.89	17.95	24.60	25.63	25.42	26.48	27.55
	3H	15.95	16.88	16.79	17.74	18.84	26.22	27.14	27.06	28.01	29.10
	4H	16.36	17.23	17.22	18.10	19.21	26.40	27.28	27.26	28.15	29.25
	6H	16.62	17.43	17.49	18.31	19.43	26.49	27.29	27.36	28.17	29.29
	8H	16.72	17.49	17.60	18.39	19.50	26.51	27.28	27.39	28.18	29.29
	12H	16.77	17.51	17.66	18.40	19.54	26.49	27.22	27.38	28.12	29.26
4H	2H	19.74	20.62	20.60	21.49	22.59	24.98	25.86	25.85	26.73	27.83
	3H	20.89	21.62	21.76	22.52	23.64	26.89	27.62	27.76	28.52	29.64
	4H	21.18	21.84	22.06	22.74	23.89	27.12	27.78	28.00	28.68	29.83
	6H	21.32	21.89	22.22	22.82	23.97	27.26	27.83	28.16	28.76	29.91
	8H	21.36	21.90	22.27	22.82	23.98	27.31	27.84	28.21	28.76	29.93
	12H	21.38	21.86	22.30	22.80	23.96	27.30	27.78	28.22	28.72	29.89
8H	4H	22.38	22.92	23.29	23.84	25.00	27.22	27.76	28.13	28.68	29.84
	6H	22.65	23.09	23.58	24.05	25.21	27.43	27.87	28.36	28.83	29.99
	8H	22.75	23.14	23.69	24.09	25.27	27.52	27.91	28.46	28.86	30.04
	12H	22.80	23.14	23.75	24.09	25.32	27.53	27.88	28.48	28.82	30.05
12H	4H	22.42	22.90	23.34	23.84	25.00	27.18	27.67	28.11	28.60	29.77
	6H	22.76	23.15	23.70	24.10	25.28	27.41	27.81	28.36	28.76	29.94
	8H	22.90	23.25	23.85	24.19	25.42	27.52	27.87	28.47	28.81	30.04