

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427831

Luminaire Tested: SQ2W-PH1-0U-100D-L830-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427831
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-10)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PH1-0U-100D-L830-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE HEX LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT N/A - DIRECT ONLY
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5096.1 lumens
Efficiency: N/A
Efficacy: 135.5 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427831

CATALOG NUMBER: SQ2W-PH1-0U-100D-L830-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427831

CATALOG NUMBER: SQ2W-PH1-OU-100D-L830-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72
3	91	81	73	67	89	80	72	67	77	71	65	74	69	64	72	67	63	61
4	84	72	64	57	82	71	63	57	69	62	56	66	60	55	64	59	55	53
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46
6	72	59	50	44	70	58	49	43	56	48	43	54	48	43	53	47	42	40
7	66	53	45	39	65	52	44	38	51	43	38	49	43	38	48	42	38	36
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	37212	37212	37212	37212
5°	37426	34014	37426	34014
10°	36563	30919	36563	30919
15°	36728	30315	36728	30315
20°	35418	30558	35418	30558
25°	34769	29847	34769	29847
30°	34015	30090	34015	30090
35°	33757	35271	33757	35271
40°	33788	27962	33788	27962
45°	33798	24085	33798	24085
50°	33324	22584	33324	22584
55°	32900	21666	32900	21666
60°	32575	20324	32575	20324
65°	32003	17677	32003	17677
70°	30226	12628	30226	12628
75°	26949	9576	26949	9576
80°	22017	8972	22017	8972
85°	13820	6095	13820	6095

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 33798 cd/sqm



TEST NUMBER: P1427831

CATALOG NUMBER: SQ2W-PH1-0U-100D-L830-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.8	4.0
10°-20°	533.4	10.5
20°-30°	782.1	15.3
30°-40°	947.0	18.6
40°-50°	931.2	18.3
50°-60°	810.0	15.9
60°-70°	563.4	11.1
70°-80°	267.2	5.2
80°-90°	58.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1518.3	29.8
0°-40°	2465.4	48.4
0°-60°	4206.6	82.5
0°-90°	5096.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5096.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2305	2305	2305	2305	2305	
5°	2309	2099	2309	2099	2309	217
15°	2197	1814	2197	1814	2197	613
25°	1952	1675	1952	1675	1952	898
35°	1713	1790	1713	1790	1713	1073
45°	1480	1055	1480	1055	1480	1138
55°	1169	770	1169	770	1169	1044
65°	838	463	838	463	838	823
75°	432	154	432	154	432	458
85°	75	33	75	33	75	102
90°	0	0	0	0	0	



TEST NUMBER: P1427831

CATALOG NUMBER: SQ2W-PH1-OU-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2304.8	2304.8	2304.8	2304.8	2304.8	2304.8	2304.8	2304.8	2304.8	2304.8	2304.8
2.5°	2299.5	2310.4	2321.4	2306.0	2281.8	2265.0	2255.7	2248.3	2246.7	2245.1	2246.7
5°	2309.2	2308.2	2307.2	2261.7	2201.2	2155.9	2125.7	2102.6	2100.6	2098.7	2100.6
7.5°	2267.1	2236.9	2206.6	2145.4	2073.9	2021.5	1988.1	1962.7	1961.2	1959.6	1961.2
10°	2230.2	2184.4	2138.6	2069.4	1992.4	1938.8	1908.6	1885.9	1885.9	1885.9	1885.9
12.5°	2221.5	2149.1	2076.8	2001.0	1924.0	1874.3	1851.9	1836.2	1840.9	1845.6	1840.9
15°	2197.3	2088.2	1979.0	1902.0	1835.7	1799.7	1793.8	1792.1	1802.9	1813.6	1802.9
17.5°	2117.5	2000.0	1882.4	1814.7	1763.7	1744.4	1756.8	1769.3	1781.8	1794.3	1781.8
20°	2061.4	1945.4	1829.4	1766.8	1722.0	1711.2	1734.6	1755.1	1766.8	1778.5	1766.8
22.5°	2014.0	1896.5	1778.9	1723.5	1688.8	1684.3	1710.1	1730.9	1737.2	1743.4	1737.2
25°	1951.7	1819.2	1686.6	1646.2	1636.4	1642.8	1665.2	1681.3	1678.3	1675.4	1678.3
27.5°	1877.2	1738.8	1600.4	1574.4	1585.9	1598.5	1612.1	1622.8	1624.5	1626.3	1624.5
30°	1824.5	1686.1	1547.7	1527.0	1545.5	1561.6	1575.3	1588.7	1601.3	1614.0	1601.3
32.5°	1773.7	1630.6	1487.5	1472.6	1500.5	1530.6	1563.0	1594.5	1623.6	1652.6	1623.6
35°	1712.7	1563.6	1414.5	1402.8	1436.9	1480.7	1534.3	1598.4	1693.9	1789.5	1693.9
37.5°	1648.7	1488.8	1329.0	1323.7	1369.9	1416.1	1462.3	1504.5	1534.9	1565.3	1534.9
40°	1603.1	1435.4	1267.8	1267.5	1323.1	1380.6	1440.0	1467.1	1396.9	1326.7	1396.9
42.5°	1553.9	1386.3	1218.6	1213.7	1263.0	1326.4	1403.8	1432.2	1313.7	1195.2	1313.7
45°	1480.2	1305.8	1131.3	1125.0	1174.7	1209.8	1230.2	1224.4	1139.6	1054.8	1139.6
47.5°	1393.4	1227.1	1060.9	1059.5	1113.1	1117.0	1071.2	1028.5	995.4	962.3	995.4
50°	1326.7	1169.8	1012.9	1019.7	1081.1	1075.3	1002.2	942.0	920.6	899.1	920.6
52.5°	1261.8	1112.7	963.6	981.7	1055.6	1043.9	946.6	870.1	855.6	841.2	855.6
55°	1168.8	1025.6	882.3	923.2	1025.6	1010.0	876.5	775.6	772.7	769.7	772.7
57.5°	1070.2	934.7	799.2	827.6	910.7	894.3	778.5	692.9	698.0	703.1	698.0
60°	1008.8	877.2	745.6	749.3	798.0	782.4	702.5	641.1	635.2	629.4	635.2
62.5°	943.8	818.5	693.2	675.0	692.5	674.2	620.0	577.9	572.1	566.2	572.1
65°	837.7	723.7	609.6	575.3	567.5	541.2	496.3	462.7	462.7	462.7	462.7
67.5°	721.0	621.6	522.2	483.8	465.6	439.5	405.4	374.0	350.6	327.2	350.6
70°	640.3	552.6	464.9	424.7	400.3	369.1	331.1	298.7	283.1	267.5	283.1
72.5°	554.4	479.1	403.9	362.7	332.9	302.5	271.5	243.8	225.8	207.9	225.8
75°	432.0	371.6	311.2	271.2	238.1	207.4	179.1	157.4	155.5	153.5	155.5
77.5°	312.3	268.2	224.2	191.8	163.4	142.0	127.8	117.2	117.3	117.5	117.3
80°	236.8	203.7	170.6	140.3	111.1	96.0	95.0	94.5	95.5	96.5	95.5
82.5°	166.7	142.1	117.5	98.2	80.7	72.6	74.0	75.0	75.2	75.4	75.2
85°	74.6	62.9	51.2	46.8	44.8	41.9	38.0	34.8	33.9	32.9	33.9
87.5°	15.8	15.0	14.2	12.3	9.9	8.8	8.8	8.8	8.8	8.8	8.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1427831

CATALOG NUMBER: SQ2W-PH1-OU-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2304.8	2304.8	2304.8	2304.8	2304.8	2304.8	2304.8	2304.8	2304.8	2304.8	2304.8
2.5°	2248.3	2255.7	2265.0	2281.8	2306.0	2321.4	2310.4	2299.5	2310.4	2321.4	2306.0
5°	2102.6	2125.7	2155.9	2201.2	2261.7	2307.2	2308.2	2309.2	2308.2	2307.2	2261.7
7.5°	1962.7	1988.1	2021.5	2073.9	2145.4	2206.6	2236.9	2267.1	2236.9	2206.6	2145.4
10°	1885.9	1908.6	1938.8	1992.4	2069.4	2138.6	2184.4	2230.2	2184.4	2138.6	2069.4
12.5°	1836.2	1851.9	1874.3	1924.0	2001.0	2076.8	2149.1	2221.5	2149.1	2076.8	2001.0
15°	1792.1	1793.8	1799.7	1835.7	1902.0	1979.0	2088.2	2197.3	2088.2	1979.0	1902.0
17.5°	1769.3	1756.8	1744.4	1763.7	1814.7	1882.4	2000.0	2117.5	2000.0	1882.4	1814.7
20°	1755.1	1734.6	1711.2	1722.0	1766.8	1829.4	1945.4	2061.4	1945.4	1829.4	1766.8
22.5°	1730.9	1710.1	1684.3	1688.8	1723.5	1778.9	1896.5	2014.0	1896.5	1778.9	1723.5
25°	1681.3	1665.2	1642.8	1636.4	1646.2	1686.6	1819.2	1951.7	1819.2	1686.6	1646.2
27.5°	1622.8	1612.1	1598.5	1585.9	1574.4	1600.4	1738.8	1877.2	1738.8	1600.4	1574.4
30°	1588.7	1575.3	1561.6	1545.5	1527.0	1547.7	1686.1	1824.5	1686.1	1547.7	1527.0
32.5°	1594.5	1563.0	1530.6	1500.5	1472.6	1487.5	1630.6	1773.7	1630.6	1487.5	1472.6
35°	1598.4	1534.3	1480.7	1436.9	1402.8	1414.5	1563.6	1712.7	1563.6	1414.5	1402.8
37.5°	1504.5	1462.3	1416.1	1369.9	1323.7	1329.0	1488.8	1648.7	1488.8	1329.0	1323.7
40°	1467.1	1440.0	1380.6	1323.1	1267.5	1267.8	1435.4	1603.1	1435.4	1267.8	1267.5
42.5°	1432.2	1403.8	1326.4	1263.0	1213.7	1218.6	1386.3	1553.9	1386.3	1218.6	1213.7
45°	1224.4	1230.2	1209.8	1174.7	1125.0	1131.3	1305.8	1480.2	1305.8	1131.3	1125.0
47.5°	1028.5	1071.2	1117.0	1113.1	1059.5	1060.9	1227.1	1393.4	1227.1	1060.9	1059.5
50°	942.0	1002.2	1075.3	1081.1	1019.7	1012.9	1169.8	1326.7	1169.8	1012.9	1019.7
52.5°	870.1	946.6	1043.9	1055.6	981.7	963.6	1112.7	1261.8	1112.7	963.6	981.7
55°	775.6	876.5	1010.0	1025.6	923.2	882.3	1025.6	1168.8	1025.6	882.3	923.2
57.5°	692.9	778.5	894.3	910.7	827.6	799.2	934.7	1070.2	934.7	799.2	827.6
60°	641.1	702.5	782.4	798.0	749.3	745.6	877.2	1008.8	877.2	745.6	749.3
62.5°	577.9	620.0	674.2	692.5	675.0	693.2	818.5	943.8	818.5	693.2	675.0
65°	462.7	496.3	541.2	567.5	575.3	609.6	723.7	837.7	723.7	609.6	575.3
67.5°	374.0	405.4	439.5	465.6	483.8	522.2	621.6	721.0	621.6	522.2	483.8
70°	298.7	331.1	369.1	400.3	424.7	464.9	552.6	640.3	552.6	464.9	424.7
72.5°	243.8	271.5	302.5	332.9	362.7	403.9	479.1	554.4	479.1	403.9	362.7
75°	157.4	179.1	207.4	238.1	271.2	311.2	371.6	432.0	371.6	311.2	271.2
77.5°	117.2	127.8	142.0	163.4	191.8	224.2	268.2	312.3	268.2	224.2	191.8
80°	94.5	95.0	96.0	111.1	140.3	170.6	203.7	236.8	203.7	170.6	140.3
82.5°	75.0	74.0	72.6	80.7	98.2	117.5	142.1	166.7	142.1	117.5	98.2
85°	34.8	38.0	41.9	44.8	46.8	51.2	62.9	74.6	62.9	51.2	46.8
87.5°	8.8	8.8	8.8	9.9	12.3	14.2	15.0	15.8	15.0	14.2	12.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1427831

CATALOG NUMBER: SQ2W-PH1-0U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2304.8	2304.8	2304.8	2304.8	2304.8	2304.8	2304.8	2304.8	2304.8	2304.8	2304.8
2.5°	2281.8	2265.0	2255.7	2248.3	2246.7	2245.1	2246.7	2248.3	2255.7	2265.0	2281.8
5°	2201.2	2155.9	2125.7	2102.6	2100.6	2098.7	2100.6	2102.6	2125.7	2155.9	2201.2
7.5°	2073.9	2021.5	1988.1	1962.7	1961.2	1959.6	1961.2	1962.7	1988.1	2021.5	2073.9
10°	1992.4	1938.8	1908.6	1885.9	1885.9	1885.9	1885.9	1885.9	1908.6	1938.8	1992.4
12.5°	1924.0	1874.3	1851.9	1836.2	1840.9	1845.6	1840.9	1836.2	1851.9	1874.3	1924.0
15°	1835.7	1799.7	1793.8	1792.1	1802.9	1813.6	1802.9	1792.1	1793.8	1799.7	1835.7
17.5°	1763.7	1744.4	1756.8	1769.3	1781.8	1794.3	1781.8	1769.3	1756.8	1744.4	1763.7
20°	1722.0	1711.2	1734.6	1755.1	1766.8	1778.5	1766.8	1755.1	1734.6	1711.2	1722.0
22.5°	1688.8	1684.3	1710.1	1730.9	1737.2	1743.4	1737.2	1730.9	1710.1	1684.3	1688.8
25°	1636.4	1642.8	1665.2	1681.3	1678.3	1675.4	1678.3	1681.3	1665.2	1642.8	1636.4
27.5°	1585.9	1598.5	1612.1	1622.8	1624.5	1626.3	1624.5	1622.8	1612.1	1598.5	1585.9
30°	1545.5	1561.6	1575.3	1588.7	1601.3	1614.0	1601.3	1588.7	1575.3	1561.6	1545.5
32.5°	1500.5	1530.6	1563.0	1594.5	1623.6	1652.6	1623.6	1594.5	1563.0	1530.6	1500.5
35°	1436.9	1480.7	1534.3	1598.4	1693.9	1789.5	1693.9	1598.4	1534.3	1480.7	1436.9
37.5°	1369.9	1416.1	1462.3	1504.5	1534.9	1565.3	1534.9	1504.5	1462.3	1416.1	1369.9
40°	1323.1	1380.6	1440.0	1467.1	1396.9	1326.7	1396.9	1467.1	1440.0	1380.6	1323.1
42.5°	1263.0	1326.4	1403.8	1432.2	1313.7	1195.2	1313.7	1432.2	1403.8	1326.4	1263.0
45°	1174.7	1209.8	1230.2	1224.4	1139.6	1054.8	1139.6	1224.4	1230.2	1209.8	1174.7
47.5°	1113.1	1117.0	1071.2	1028.5	995.4	962.3	995.4	1028.5	1071.2	1117.0	1113.1
50°	1081.1	1075.3	1002.2	942.0	920.6	899.1	920.6	942.0	1002.2	1075.3	1081.1
52.5°	1055.6	1043.9	946.6	870.1	855.6	841.2	855.6	870.1	946.6	1043.9	1055.6
55°	1025.6	1010.0	876.5	775.6	772.7	769.7	772.7	775.6	876.5	1010.0	1025.6
57.5°	910.7	894.3	778.5	692.9	698.0	703.1	698.0	692.9	778.5	894.3	910.7
60°	798.0	782.4	702.5	641.1	635.2	629.4	635.2	641.1	702.5	782.4	798.0
62.5°	692.5	674.2	620.0	577.9	572.1	566.2	572.1	577.9	620.0	674.2	692.5
65°	567.5	541.2	496.3	462.7	462.7	462.7	462.7	462.7	496.3	541.2	567.5
67.5°	465.6	439.5	405.4	374.0	350.6	327.2	350.6	374.0	405.4	439.5	465.6
70°	400.3	369.1	331.1	298.7	283.1	267.5	283.1	298.7	331.1	369.1	400.3
72.5°	332.9	302.5	271.5	243.8	225.8	207.9	225.8	243.8	271.5	302.5	332.9
75°	238.1	207.4	179.1	157.4	155.5	153.5	155.5	157.4	179.1	207.4	238.1
77.5°	163.4	142.0	127.8	117.2	117.3	117.5	117.3	117.2	127.8	142.0	163.4
80°	111.1	96.0	95.0	94.5	95.5	96.5	95.5	94.5	95.0	96.0	111.1
82.5°	80.7	72.6	74.0	75.0	75.2	75.4	75.2	75.0	74.0	72.6	80.7
85°	44.8	41.9	38.0	34.8	33.9	32.9	33.9	34.8	38.0	41.9	44.8
87.5°	9.9	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	9.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1427831

CATALOG NUMBER: SQ2W-PH1-0U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2304.8	2304.8	2304.8	2304.8
2.5°	2306.0	2321.4	2310.4	2299.5
5°	2261.7	2307.2	2308.2	2309.2
7.5°	2145.4	2206.6	2236.9	2267.1
10°	2069.4	2138.6	2184.4	2230.2
12.5°	2001.0	2076.8	2149.1	2221.5
15°	1902.0	1979.0	2088.2	2197.3
17.5°	1814.7	1882.4	2000.0	2117.5
20°	1766.8	1829.4	1945.4	2061.4
22.5°	1723.5	1778.9	1896.5	2014.0
25°	1646.2	1686.6	1819.2	1951.7
27.5°	1574.4	1600.4	1738.8	1877.2
30°	1527.0	1547.7	1686.1	1824.5
32.5°	1472.6	1487.5	1630.6	1773.7
35°	1402.8	1414.5	1563.6	1712.7
37.5°	1323.7	1329.0	1488.8	1648.7
40°	1267.5	1267.8	1435.4	1603.1
42.5°	1213.7	1218.6	1386.3	1553.9
45°	1125.0	1131.3	1305.8	1480.2
47.5°	1059.5	1060.9	1227.1	1393.4
50°	1019.7	1012.9	1169.8	1326.7
52.5°	981.7	963.6	1112.7	1261.8
55°	923.2	882.3	1025.6	1168.8
57.5°	827.6	799.2	934.7	1070.2
60°	749.3	745.6	877.2	1008.8
62.5°	675.0	693.2	818.5	943.8
65°	575.3	609.6	723.7	837.7
67.5°	483.8	522.2	621.6	721.0
70°	424.7	464.9	552.6	640.3
72.5°	362.7	403.9	479.1	554.4
75°	271.2	311.2	371.6	432.0
77.5°	191.8	224.2	268.2	312.3
80°	140.3	170.6	203.7	236.8
82.5°	98.2	117.5	142.1	166.7
85°	46.8	51.2	62.9	74.6
87.5°	12.3	14.2	15.0	15.8
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P1427831
 CATALOG NUMBER: SQ2W-PH1-0U-100D-L830-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	23.29	24.88	23.65	25.19	25.51	22.11	23.70	22.48	24.02	24.33
	3H	25.51	26.94	25.89	27.27	27.63	23.22	24.65	23.59	24.98	25.34
	4H	26.36	27.70	26.76	28.05	28.43	23.49	24.84	23.89	25.19	25.56
	6H	26.86	28.11	27.27	28.47	28.86	23.67	24.91	24.08	25.28	25.67
	8H	27.03	28.22	27.46	28.61	29.01	23.75	24.94	24.17	25.32	25.72
	12H	27.12	28.25	27.55	28.63	29.06	23.78	24.92	24.21	25.30	25.73
4H	2H	23.81	25.15	24.20	25.50	25.88	22.88	24.23	23.28	24.58	24.95
	3H	26.12	27.24	26.53	27.64	28.04	24.18	25.30	24.59	25.70	26.10
	4H	27.02	28.03	27.46	28.45	28.88	24.50	25.51	24.93	25.92	26.36
	6H	27.62	28.50	28.08	28.94	29.40	24.74	25.61	25.19	26.06	26.51
	8H	27.84	28.66	28.30	29.11	29.57	24.84	25.66	25.30	26.11	26.57
	12H	27.96	28.70	28.44	29.17	29.64	24.90	25.63	25.38	26.11	26.58
8H	4H	27.10	27.92	27.56	28.37	28.83	24.78	25.60	25.25	26.05	26.51
	6H	27.76	28.44	28.26	28.93	29.41	25.08	25.76	25.58	26.25	26.72
	8H	28.03	28.64	28.54	29.15	29.63	25.23	25.84	25.74	26.35	26.84
	12H	28.19	28.73	28.70	29.22	29.79	25.33	25.87	25.84	26.36	26.92
12H	4H	27.09	27.82	27.57	28.30	28.77	24.81	25.55	25.29	26.02	26.50
	6H	27.74	28.35	28.25	28.86	29.35	25.12	25.73	25.63	26.24	26.72
	8H	28.05	28.59	28.56	29.08	29.64	25.32	25.85	25.82	26.34	26.91