

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428047

Luminaire Tested: SQ2W-PP3-K-050U-100D-L830-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428047
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-7)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PP3-K-050U-100D-L830-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE PRISM LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7376.7 lumens
Efficiency: N/A
Efficacy: 140.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.41 / 1.4
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 52.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428047

CATALOG NUMBER: SQ2W-PP3-K-050U-100D-L830-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428047

CATALOG NUMBER: SQ2W-PP3-K-050U-100D-L830-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	75	75	75	71	
1	103	99	95	92	98	94	91	88	85	82	80	76	74	72	68	66	65	65	65	65	61	
2	95	87	81	76	89	83	78	73	75	71	67	67	64	61	61	58	56	56	56	56	52	
3	87	77	70	64	82	74	67	62	67	62	57	60	56	53	54	51	48	48	48	48	45	
4	80	69	61	55	75	66	59	53	60	54	49	54	49	46	49	45	42	42	42	42	39	
5	73	62	54	48	69	59	52	46	54	48	43	49	44	40	44	40	37	37	37	37	34	
6	68	56	48	42	64	53	46	40	49	42	38	44	39	35	40	36	33	33	33	33	30	
7	63	50	42	37	59	48	41	36	44	38	34	40	35	31	37	33	29	29	29	29	27	
8	58	46	38	33	55	44	37	32	40	34	30	37	32	28	34	30	26	26	26	26	24	
9	55	42	35	29	52	40	33	29	37	31	27	34	29	25	31	27	24	24	24	24	22	
10	51	39	31	27	48	37	30	26	34	28	24	32	27	23	29	25	22	22	22	22	20	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	33494	33494	33494	33494
5°	33231	33836	33231	33836
10°	33401	34083	33401	34083
15°	33320	34162	33320	34162
20°	33082	34853	33082	34853
25°	32895	36684	32895	36684
30°	32708	37449	32708	37449
35°	32244	37518	32244	37518
40°	31383	34665	31383	34665
45°	30444	26388	30444	26388
50°	29250	21978	29250	21978
55°	27223	15803	27223	15803
60°	23440	11331	23440	11331
65°	19770	11144	19770	11144
70°	16461	10664	16461	10664
75°	13955	9987	13955	9987
80°	11827	8972	11827	8972
85°	9337	4872	9337	4872

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 33305 cd/sqm



TEST NUMBER: P1428047

CATALOG NUMBER: SQ2W-PP3-K-050U-100D-L830-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.5	2.7
10°-20°	571.7	7.8
20°-30°	895.7	12.1
30°-40°	1104.9	15.0
40°-50°	1040.2	14.1
50°-60°	736.5	10.0
60°-70°	419.7	5.7
70°-80°	207.7	2.8
80°-90°	53.8	0.7
90°-100°	58.6	0.8
100°-110°	170.8	2.3
110°-120°	278.8	3.8
120°-130°	353.7	4.8
130°-140°	378.5	5.1
140°-150°	353.4	4.8
150°-160°	290.8	3.9
160°-170°	195.1	2.6
170°-180°	69.3	0.9
0°-30°	1664.9	22.6
0°-40°	2769.8	37.5
0°-60°	4546.5	61.6
0°-90°	5227.7	70.9
90°-120°	508.2	6.9
90°-150°	1593.8	21.6
90°-180°	2149.0	29.1
0°-180°	7376.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2074	2074	2074	2074	2074	
5°	2050	2088	2050	2088	2050	195
15°	1993	2044	1993	2044	1993	562
25°	1846	2059	1846	2059	1846	850
35°	1636	1904	1636	1904	1636	1020
45°	1333	1156	1333	1156	1333	1026
55°	967	561	967	561	967	853
65°	518	292	518	292	518	520
75°	224	160	224	160	224	242
85°	50	26	50	26	50	59
90°	2	16	2	32	2	4
95°	23	17	23	100	23	28
105°	108	174	108	239	108	115
115°	208	288	208	355	208	205
125°	308	457	308	436	308	275
135°	418	598	418	482	418	323
145°	534	690	534	493	534	334
155°	635	749	635	512	635	292
165°	702	781	702	589	702	198
175°	734	765	734	691	734	70
180°	736	736	736	736	736	



TEST NUMBER: P1428047

CATALOG NUMBER: SQ2W-PP3-K-050U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2074.5	2074.5	2074.5	2074.5	2074.5	2074.5	2074.5	2074.5	2074.5	2074.5	2074.5
2.5°	2058.7	2072.0	2085.3	2082.1	2073.6	2070.1	2071.6	2073.2	2074.7	2076.3	2074.7
5°	2050.4	2067.0	2083.6	2081.1	2072.3	2068.9	2070.9	2074.0	2080.9	2087.7	2080.9
7.5°	2042.5	2059.5	2076.4	2074.2	2065.7	2063.0	2066.3	2070.9	2079.3	2087.7	2079.3
10°	2037.3	2051.9	2066.5	2064.3	2056.5	2055.0	2059.9	2065.3	2072.1	2078.9	2072.1
12.5°	2021.5	2035.3	2049.1	2047.3	2040.3	2040.0	2046.5	2052.8	2058.8	2064.9	2058.8
15°	1993.4	2006.1	2018.7	2019.0	2015.1	2017.5	2026.3	2034.1	2039.0	2043.8	2039.0
17.5°	1955.2	1970.6	1986.0	1989.6	1989.2	1995.2	2007.7	2018.3	2023.4	2028.5	2023.4
20°	1925.4	1943.9	1962.5	1968.5	1970.5	1979.3	1994.9	2009.0	2018.7	2028.5	2018.7
22.5°	1893.8	1915.5	1937.1	1945.2	1948.7	1962.1	1985.5	2007.2	2024.0	2040.8	2024.0
25°	1846.5	1867.9	1889.4	1904.9	1918.6	1942.5	1976.6	2008.5	2033.8	2059.2	2033.8
27.5°	1791.2	1812.5	1833.7	1860.5	1889.2	1922.7	1961.1	1994.9	2015.0	2035.1	2015.0
30°	1754.4	1774.8	1795.3	1826.0	1860.1	1897.1	1937.1	1971.7	1990.2	2008.7	1990.2
32.5°	1708.8	1730.0	1751.2	1783.9	1820.3	1860.1	1903.2	1939.7	1956.7	1973.7	1956.7
35°	1635.9	1656.4	1676.9	1714.9	1758.7	1803.1	1847.9	1884.0	1893.7	1903.5	1893.7
37.5°	1552.2	1575.4	1598.6	1641.2	1690.3	1727.5	1752.6	1771.6	1772.2	1772.8	1772.2
40°	1489.0	1519.2	1549.4	1592.1	1638.9	1664.7	1669.6	1670.1	1657.4	1644.7	1657.4
42.5°	1427.6	1466.4	1505.2	1539.5	1572.2	1578.9	1559.6	1531.1	1474.7	1418.4	1474.7
45°	1333.3	1379.1	1424.9	1445.9	1458.6	1415.7	1317.2	1233.7	1194.7	1155.7	1194.7
47.5°	1232.9	1278.1	1323.3	1317.5	1294.7	1229.8	1122.8	1035.8	1008.9	982.0	1008.9
50°	1164.5	1207.3	1250.2	1219.3	1163.7	1090.6	1000.0	925.7	900.3	875.0	900.3
52.5°	1087.3	1125.5	1163.7	1116.9	1041.9	964.9	886.0	817.1	778.5	739.9	778.5
55°	967.1	993.4	1019.7	968.6	891.6	806.8	714.2	635.5	598.4	561.4	598.4
57.5°	822.4	840.9	859.4	819.1	759.3	675.0	566.2	474.3	432.7	391.2	432.7
60°	725.9	740.5	755.1	718.6	665.0	584.5	477.3	391.8	371.3	350.9	371.3
62.5°	638.1	651.2	664.3	626.2	571.0	499.2	410.7	342.5	335.3	328.1	335.3
65°	517.5	530.2	542.9	502.9	445.4	389.4	334.8	293.6	292.6	291.7	292.6
67.5°	411.8	425.7	439.5	401.9	347.1	305.7	277.6	256.3	255.1	253.9	255.1
70°	348.7	363.3	377.9	342.8	291.2	257.6	242.0	229.8	227.8	225.9	227.8
72.5°	296.0	309.9	323.7	293.1	247.7	219.9	209.8	201.9	200.7	199.6	200.7
75°	223.7	234.4	245.1	223.0	189.8	170.8	165.9	162.0	161.1	160.1	161.1
77.5°	162.3	169.1	175.9	161.4	139.8	127.7	125.1	123.0	122.0	121.1	122.0
80°	127.2	130.1	133.0	122.8	108.2	100.4	99.4	98.4	97.5	96.5	97.5
82.5°	95.6	94.6	93.7	87.7	80.1	75.8	74.9	73.7	71.9	70.2	71.9
85°	50.4	48.5	46.5	44.6	42.6	39.7	35.8	32.2	29.2	26.3	29.2
87.5°	16.2	16.8	17.6	15.2	11.8	9.6	8.8	8.4	8.5	8.5	8.5
90°	2.2	5.2	8.9	11.9	14.1	14.9	14.9	15.6	16.4	16.4	16.4
92.5°	8.2	12.9	13.1	13.1	15.9	17.2	18.4	18.6	19.3	19.3	19.3
95°	23.0	25.3	37.9	37.2	25.3	20.1	17.1	17.1	17.1	17.1	17.1
97.5°	44.0	47.3	49.4	66.2	69.9	67.5	55.0	46.2	41.3	39.1	41.3
100°	62.4	63.9	68.4	69.1	87.7	105.6	96.6	85.5	81.8	79.5	81.8
102.5°	80.9	81.8	88.6	91.7	96.1	106.2	137.1	133.7	131.1	130.7	131.1
105°	108.5	109.3	121.9	127.9	130.8	130.8	130.1	145.0	168.8	174.0	168.8
107.5°	138.1	141.5	156.4	172.3	175.7	176.6	172.8	170.5	169.6	170.2	169.6
110°	158.3	163.6	181.4	201.5	206.7	208.2	206.7	204.4	203.0	203.0	203.0



TEST NUMBER: P1428047

CATALOG NUMBER: SQ2W-PP3-K-050U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	178.0	185.6	205.8	228.8	237.6	242.1	238.8	237.2	235.7	236.9	235.7
115°	208.2	219.3	246.1	269.9	287.7	289.9	289.2	289.2	288.4	288.4	288.4
117.5°	236.1	254.0	284.0	311.6	332.3	338.3	341.2	340.3	339.4	340.9	339.4
120°	255.7	276.6	310.8	342.0	362.0	371.0	373.9	372.5	373.9	372.5	373.9
122.5°	276.6	302.1	335.7	368.1	391.8	401.9	405.5	405.8	406.1	405.2	406.1
125°	307.8	339.0	378.4	411.9	436.4	448.3	451.3	452.0	453.5	457.2	453.5
127.5°	339.3	374.7	418.0	450.2	475.3	489.8	494.4	496.0	499.1	500.8	499.1
130°	361.3	401.4	445.3	475.8	500.3	515.9	524.1	526.3	530.1	529.3	530.1
132.5°	384.5	426.4	470.9	502.6	525.3	542.1	549.1	555.5	556.8	557.9	556.8
135°	418.5	463.9	508.5	539.7	561.3	577.6	586.6	592.5	596.2	598.5	596.2
137.5°	454.4	502.3	545.1	572.9	594.6	608.7	618.8	625.1	628.9	630.7	628.9
140°	478.8	524.9	566.5	595.5	614.8	628.9	637.9	645.3	649.8	649.8	649.8
142.5°	502.0	547.5	587.9	616.9	633.8	646.8	656.3	661.9	667.0	667.0	667.0
145°	534.5	579.9	617.0	646.0	660.2	672.1	682.5	686.9	689.9	689.9	689.9
147.5°	568.6	608.7	642.6	670.4	682.3	696.3	704.5	708.0	711.8	710.1	711.8
150°	588.8	626.0	658.7	684.7	696.6	710.0	718.1	721.1	724.8	722.6	724.8
152.5°	608.4	643.8	673.5	697.8	707.9	721.3	730.6	733.6	736.1	734.5	736.1
155°	634.9	666.1	693.6	715.9	724.8	737.5	746.4	750.1	753.1	749.4	753.1
157.5°	658.5	685.4	709.4	729.9	739.4	750.3	758.6	763.2	766.2	764.5	766.2
160°	672.8	697.3	718.9	738.2	747.1	756.8	765.7	770.9	773.9	771.7	773.9
162.5°	684.7	706.8	727.2	744.8	752.5	761.0	771.7	776.3	779.3	776.4	779.3
165°	701.8	719.6	737.5	752.3	759.0	765.7	776.9	782.1	784.3	781.3	784.3
167.5°	714.7	728.4	742.8	755.6	760.5	767.1	778.2	782.5	785.4	781.6	785.4
170°	721.9	733.8	746.4	756.8	760.5	766.5	777.6	781.3	783.6	779.9	783.6
172.5°	727.8	736.7	747.0	756.2	758.1	762.9	773.5	777.2	778.8	775.7	778.8
175°	733.8	739.0	746.4	752.3	751.6	754.6	763.5	766.5	769.4	765.0	769.4
177.5°	736.6	739.0	741.3	744.9	742.5	742.5	749.1	750.9	751.5	749.1	751.5
180°	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0



TEST NUMBER: P1428047

CATALOG NUMBER: SQ2W-PP3-K-050U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2074.5	2074.5	2074.5	2074.5	2074.5	2074.5	2074.5	2074.5	2074.5	2074.5	2074.5
2.5°	2073.2	2071.6	2070.1	2073.6	2082.1	2085.3	2072.0	2058.7	2072.0	2085.3	2082.1
5°	2074.0	2070.9	2068.9	2072.3	2081.1	2083.6	2067.0	2050.4	2067.0	2083.6	2081.1
7.5°	2070.9	2066.3	2063.0	2065.7	2074.2	2076.4	2059.5	2042.5	2059.5	2076.4	2074.2
10°	2065.3	2059.9	2055.0	2056.5	2064.3	2066.5	2051.9	2037.3	2051.9	2066.5	2064.3
12.5°	2052.8	2046.5	2040.0	2040.3	2047.3	2049.1	2035.3	2021.5	2035.3	2049.1	2047.3
15°	2034.1	2026.3	2017.5	2015.1	2019.0	2018.7	2006.1	1993.4	2006.1	2018.7	2019.0
17.5°	2018.3	2007.7	1995.2	1989.2	1989.6	1986.0	1970.6	1955.2	1970.6	1986.0	1989.6
20°	2009.0	1994.9	1979.3	1970.5	1968.5	1962.5	1943.9	1925.4	1943.9	1962.5	1968.5
22.5°	2007.2	1985.5	1962.1	1948.7	1945.2	1937.1	1915.5	1893.8	1915.5	1937.1	1945.2
25°	2008.5	1976.6	1942.5	1918.6	1904.9	1889.4	1867.9	1846.5	1867.9	1889.4	1904.9
27.5°	1994.9	1961.1	1922.7	1889.2	1860.5	1833.7	1812.5	1791.2	1812.5	1833.7	1860.5
30°	1971.7	1937.1	1897.1	1860.1	1826.0	1795.3	1774.8	1754.4	1774.8	1795.3	1826.0
32.5°	1939.7	1903.2	1860.1	1820.3	1783.9	1751.2	1730.0	1708.8	1730.0	1751.2	1783.9
35°	1884.0	1847.9	1803.1	1758.7	1714.9	1676.9	1656.4	1635.9	1656.4	1676.9	1714.9
37.5°	1771.6	1752.6	1727.5	1690.3	1641.2	1598.6	1575.4	1552.2	1575.4	1598.6	1641.2
40°	1670.1	1669.6	1664.7	1638.9	1592.1	1549.4	1519.2	1489.0	1519.2	1549.4	1592.1
42.5°	1531.1	1559.6	1578.9	1572.2	1539.5	1505.2	1466.4	1427.6	1466.4	1505.2	1539.5
45°	1233.7	1317.2	1415.7	1458.6	1445.9	1424.9	1379.1	1333.3	1379.1	1424.9	1445.9
47.5°	1035.8	1122.8	1229.8	1294.7	1317.5	1323.3	1278.1	1232.9	1278.1	1323.3	1317.5
50°	925.7	1000.0	1090.6	1163.7	1219.3	1250.2	1207.3	1164.5	1207.3	1250.2	1219.3
52.5°	817.1	886.0	964.9	1041.9	1116.9	1163.7	1125.5	1087.3	1125.5	1163.7	1116.9
55°	635.5	714.2	806.8	891.6	968.6	1019.7	993.4	967.1	993.4	1019.7	968.6
57.5°	474.3	566.2	675.0	759.3	819.1	859.4	840.9	822.4	840.9	859.4	819.1
60°	391.8	477.3	584.5	665.0	718.6	755.1	740.5	725.9	740.5	755.1	718.6
62.5°	342.5	410.7	499.2	571.0	626.2	664.3	651.2	638.1	651.2	664.3	626.2
65°	293.6	334.8	389.4	445.4	502.9	542.9	530.2	517.5	530.2	542.9	502.9
67.5°	256.3	277.6	305.7	347.1	401.9	439.5	425.7	411.8	425.7	439.5	401.9
70°	229.8	242.0	257.6	291.2	342.8	377.9	363.3	348.7	363.3	377.9	342.8
72.5°	201.9	209.8	219.9	247.7	293.1	323.7	309.9	296.0	309.9	323.7	293.1
75°	162.0	165.9	170.8	189.8	223.0	245.1	234.4	223.7	234.4	245.1	223.0
77.5°	123.0	125.1	127.7	139.8	161.4	175.9	169.1	162.3	169.1	175.9	161.4
80°	98.4	99.4	100.4	108.2	122.8	133.0	130.1	127.2	130.1	133.0	122.8
82.5°	73.7	74.9	75.8	80.1	87.7	93.7	94.6	95.6	94.6	93.7	87.7
85°	32.2	35.8	39.7	42.6	44.6	46.5	48.5	50.4	48.5	46.5	44.6
87.5°	8.4	8.8	9.6	11.8	15.2	17.6	16.8	16.2	16.8	17.4	15.5
90°	15.6	14.9	14.9	14.1	11.9	8.9	5.2	2.2	5.2	8.2	13.4
92.5°	18.6	18.4	17.2	15.9	13.1	13.1	12.9	8.2	14.1	20.1	28.8
95°	17.1	17.1	20.1	25.3	37.2	37.9	25.3	23.0	32.7	46.1	58.0
97.5°	46.2	55.0	67.5	69.9	66.2	49.4	47.3	44.0	59.9	73.2	92.3
100°	85.5	96.6	105.6	87.7	69.1	68.4	63.9	62.4	79.5	92.2	110.8
102.5°	133.7	137.1	106.2	96.1	91.7	88.6	81.8	80.9	98.0	115.4	131.0
105°	145.0	130.1	130.8	130.8	127.9	121.9	109.3	108.5	127.9	147.9	167.3
107.5°	170.5	172.8	176.6	175.7	172.3	156.4	141.5	138.1	155.5	179.6	200.9
110°	204.4	206.7	208.2	206.7	201.5	181.4	163.6	158.3	174.0	199.2	222.3



TEST NUMBER: P1428047

CATALOG NUMBER: SQ2W-PP3-K-050U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	237.2	238.8	242.1	237.6	228.8	205.8	185.6	178.0	193.6	219.5	243.1
115°	289.2	289.2	289.9	287.7	269.9	246.1	219.3	208.2	221.5	245.3	271.4
117.5°	340.3	341.2	338.3	332.3	311.6	284.0	254.0	236.1	246.7	271.8	298.6
120°	372.5	373.9	371.0	362.0	342.0	310.8	276.6	255.7	263.9	288.4	315.2
122.5°	405.8	405.5	401.9	391.8	368.1	335.7	302.1	276.6	280.0	302.7	328.9
125°	452.0	451.3	448.3	436.4	411.9	378.4	339.0	307.8	303.3	322.6	349.4
127.5°	496.0	494.4	489.8	475.3	450.2	418.0	374.7	339.3	329.3	341.5	366.1
130°	526.3	524.1	515.9	500.3	475.8	445.3	401.4	361.3	347.2	354.6	376.2
132.5°	555.5	549.1	542.1	525.3	502.6	470.9	426.4	384.5	365.0	368.3	385.1
135°	592.5	586.6	577.6	561.3	539.7	508.5	463.9	418.5	391.8	388.8	398.5
137.5°	625.1	618.8	608.7	594.6	572.9	545.1	502.3	454.4	420.6	410.7	414.4
140°	645.3	637.9	628.9	614.8	595.5	566.5	524.9	478.8	440.9	426.7	424.5
142.5°	661.9	656.3	646.8	633.8	616.9	587.9	547.5	502.0	461.7	443.4	438.2
145°	686.9	682.5	672.1	660.2	646.0	617.0	579.9	534.5	494.4	470.6	459.4
147.5°	708.0	704.5	696.3	682.3	670.4	642.6	608.7	568.6	527.4	497.9	483.5
150°	721.1	718.1	710.0	696.6	684.7	658.7	626.0	588.8	549.4	518.2	499.6
152.5°	733.6	730.6	721.3	707.9	697.8	673.5	643.8	608.4	568.4	537.2	518.0
155°	750.1	746.4	737.5	724.8	715.9	693.6	666.1	634.9	600.7	568.0	546.4
157.5°	763.2	758.6	750.3	739.4	729.9	709.4	685.4	658.5	628.6	597.4	575.4
160°	770.9	765.7	756.8	747.1	738.2	718.9	697.3	672.8	645.3	617.0	593.3
162.5°	776.3	771.7	761.0	752.5	744.8	727.2	706.8	684.7	660.2	635.5	613.5
165°	782.1	776.9	765.7	759.0	752.3	737.5	719.6	701.8	681.0	660.9	643.1
167.5°	782.5	778.2	767.1	760.5	755.6	742.8	728.4	714.7	698.5	682.8	667.9
170°	781.3	777.6	766.5	760.5	756.8	746.4	733.8	721.9	709.2	695.8	684.0
172.5°	777.2	773.5	762.9	758.1	756.2	747.0	736.7	727.8	717.0	707.1	697.6
175°	766.5	763.5	754.6	751.6	752.3	746.4	739.0	733.8	727.1	721.1	715.9
177.5°	750.9	749.1	742.5	742.5	744.9	741.3	739.0	736.6	733.6	731.8	730.0
180°	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0



TEST NUMBER: P1428047

CATALOG NUMBER: SQ2W-PP3-K-050U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2074.5	2074.5	2074.5	2074.5	2074.5	2074.5	2074.5	2074.5	2074.5	2074.5	2074.5
2.5°	2073.6	2070.1	2071.6	2073.2	2074.7	2076.3	2074.7	2073.2	2071.6	2070.1	2073.6
5°	2072.3	2068.9	2070.9	2074.0	2080.9	2087.7	2080.9	2074.0	2070.9	2068.9	2072.3
7.5°	2065.7	2063.0	2066.3	2070.9	2079.3	2087.7	2079.3	2070.9	2066.3	2063.0	2065.7
10°	2056.5	2055.0	2059.9	2065.3	2072.1	2078.9	2072.1	2065.3	2059.9	2055.0	2056.5
12.5°	2040.3	2040.0	2046.5	2052.8	2058.8	2064.9	2058.8	2052.8	2046.5	2040.0	2040.3
15°	2015.1	2017.5	2026.3	2034.1	2039.0	2043.8	2039.0	2034.1	2026.3	2017.5	2015.1
17.5°	1989.2	1995.2	2007.7	2018.3	2023.4	2028.5	2023.4	2018.3	2007.7	1995.2	1989.2
20°	1970.5	1979.3	1994.9	2009.0	2018.7	2028.5	2018.7	2009.0	1994.9	1979.3	1970.5
22.5°	1948.7	1962.1	1985.5	2007.2	2024.0	2040.8	2024.0	2007.2	1985.5	1962.1	1948.7
25°	1918.6	1942.5	1976.6	2008.5	2033.8	2059.2	2033.8	2008.5	1976.6	1942.5	1918.6
27.5°	1889.2	1922.7	1961.1	1994.9	2015.0	2035.1	2015.0	1994.9	1961.1	1922.7	1889.2
30°	1860.1	1897.1	1937.1	1971.7	1990.2	2008.7	1990.2	1971.7	1937.1	1897.1	1860.1
32.5°	1820.3	1860.1	1903.2	1939.7	1956.7	1973.7	1956.7	1939.7	1903.2	1860.1	1820.3
35°	1758.7	1803.1	1847.9	1884.0	1893.7	1903.5	1893.7	1884.0	1847.9	1803.1	1758.7
37.5°	1690.3	1727.5	1752.6	1771.6	1772.2	1772.8	1772.2	1771.6	1752.6	1727.5	1690.3
40°	1638.9	1664.7	1669.6	1670.1	1657.4	1644.7	1657.4	1670.1	1669.6	1664.7	1638.9
42.5°	1572.2	1578.9	1559.6	1531.1	1474.7	1418.4	1474.7	1531.1	1559.6	1578.9	1572.2
45°	1458.6	1415.7	1317.2	1233.7	1194.7	1155.7	1194.7	1233.7	1317.2	1415.7	1458.6
47.5°	1294.7	1229.8	1122.8	1035.8	1008.9	982.0	1008.9	1035.8	1122.8	1229.8	1294.7
50°	1163.7	1090.6	1000.0	925.7	900.3	875.0	900.3	925.7	1000.0	1090.6	1163.7
52.5°	1041.9	964.9	886.0	817.1	778.5	739.9	778.5	817.1	886.0	964.9	1041.9
55°	891.6	806.8	714.2	635.5	598.4	561.4	598.4	635.5	714.2	806.8	891.6
57.5°	759.3	675.0	566.2	474.3	432.7	391.2	432.7	474.3	566.2	675.0	759.3
60°	665.0	584.5	477.3	391.8	371.3	350.9	371.3	391.8	477.3	584.5	665.0
62.5°	571.0	499.2	410.7	342.5	335.3	328.1	335.3	342.5	410.7	499.2	571.0
65°	445.4	389.4	334.8	293.6	292.6	291.7	292.6	293.6	334.8	389.4	445.4
67.5°	347.1	305.7	277.6	256.3	255.1	253.9	255.1	256.3	277.6	305.7	347.1
70°	291.2	257.6	242.0	229.8	227.8	225.9	227.8	229.8	242.0	257.6	291.2
72.5°	247.7	219.9	209.8	201.9	200.7	199.6	200.7	201.9	209.8	219.9	247.7
75°	189.8	170.8	165.9	162.0	161.1	160.1	161.1	162.0	165.9	170.8	189.8
77.5°	139.8	127.7	125.1	123.0	122.0	121.1	122.0	123.0	125.1	127.7	139.8
80°	108.2	100.4	99.4	98.4	97.5	96.5	97.5	98.4	99.4	100.4	108.2
82.5°	80.1	75.8	74.9	73.7	71.9	70.2	71.9	73.7	74.9	75.8	80.1
85°	42.6	39.7	35.8	32.2	29.2	26.3	29.2	32.2	35.8	39.7	42.6
87.5°	12.4	11.1	11.3	11.4	12.0	11.7	12.0	11.4	11.3	11.1	12.4
90°	17.1	22.3	27.5	30.5	33.5	32.0	33.5	30.5	27.5	22.3	17.1
92.5°	34.3	43.1	49.5	54.9	57.2	56.9	57.2	49.5	43.1	34.3	34.3
95°	69.1	79.5	90.0	97.4	101.8	100.4	101.8	97.4	90.0	79.5	69.1
97.5°	106.6	120.6	132.2	139.2	143.6	146.6	143.6	139.2	132.2	120.6	106.6
100°	131.6	145.0	158.3	166.5	174.0	176.9	174.0	166.5	158.3	145.0	131.6
102.5°	151.8	169.4	183.9	192.7	198.9	201.9	198.9	192.7	183.9	169.4	151.8
105°	185.1	203.7	219.3	230.5	237.2	239.4	237.2	230.5	219.3	203.7	185.1
107.5°	218.4	237.6	252.0	264.4	272.5	277.3	272.5	264.4	252.0	237.6	218.4
110°	244.6	260.2	275.8	287.0	295.1	298.1	295.1	287.0	275.8	260.2	244.6



TEST NUMBER: P1428047

CATALOG NUMBER: SQ2W-PP3-K-050U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	266.6	284.0	299.6	310.8	320.1	324.3	320.1	310.8	299.6	284.0	266.6
115°	297.4	320.4	334.5	344.9	351.6	355.4	351.6	344.9	334.5	320.4	297.4
117.5°	322.9	347.0	362.5	370.5	373.6	376.3	373.6	370.5	362.5	347.0	322.9
120°	339.0	361.3	379.1	389.6	393.3	394.8	393.3	389.6	379.1	361.3	339.0
122.5°	353.9	375.0	392.2	405.0	411.1	412.6	411.1	405.0	392.2	375.0	353.9
125°	374.7	394.8	412.6	425.2	431.9	435.6	431.9	425.2	412.6	394.8	374.7
127.5°	392.8	414.5	430.9	442.3	448.9	451.9	448.9	442.3	430.9	414.5	392.8
130°	402.9	425.2	441.6	454.2	460.2	463.2	460.2	454.2	441.6	425.2	402.9
132.5°	410.7	434.2	451.1	462.6	469.1	472.1	469.1	462.6	451.1	434.2	410.7
135°	420.0	444.6	462.4	473.6	479.5	482.5	479.5	473.6	462.4	444.6	420.0
137.5°	428.2	450.5	469.1	480.8	486.2	488.1	486.2	480.8	469.1	450.5	428.2
140°	434.2	453.5	472.1	483.2	489.2	489.9	489.2	483.2	472.1	453.5	434.2
142.5°	441.9	457.1	473.3	484.4	490.4	491.7	490.4	484.4	473.3	457.1	441.9
145°	455.7	464.6	475.8	486.2	491.4	492.9	491.4	486.2	475.8	464.6	455.7
147.5°	473.1	475.9	481.7	488.6	493.6	494.7	493.6	488.6	481.7	475.9	473.1
150°	486.2	485.5	487.7	492.1	496.6	495.9	496.6	492.1	487.7	485.5	486.2
152.5°	501.1	496.8	496.6	498.7	500.8	500.6	500.8	498.7	496.6	496.8	501.1
155°	526.3	518.2	513.7	512.2	512.2	511.5	512.2	512.2	513.7	518.2	526.3
157.5°	554.1	542.7	536.0	532.4	531.4	529.8	531.4	532.4	536.0	542.7	554.1
160°	573.2	560.5	553.9	547.9	545.7	543.4	545.7	547.9	553.9	560.5	573.2
162.5°	591.0	579.0	571.7	566.3	564.1	560.7	564.1	566.3	571.7	579.0	591.0
165°	620.0	607.4	599.2	594.7	591.8	588.8	591.8	594.7	599.2	607.4	620.0
167.5°	649.0	635.2	629.8	624.8	621.9	616.6	621.9	624.8	629.8	635.2	649.0
170°	666.9	654.2	651.2	646.8	641.6	635.6	641.6	646.8	651.2	654.2	666.9
172.5°	682.3	673.8	670.9	666.4	664.8	660.0	664.8	666.4	670.9	673.8	682.3
175°	704.8	698.1	698.1	697.3	695.1	690.6	695.1	697.3	698.1	698.1	704.8
177.5°	723.5	719.9	722.3	722.3	721.7	717.6	721.7	722.3	722.3	719.9	723.5
180°	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0



TEST NUMBER: P1428047

CATALOG NUMBER: SQ2W-PP3-K-050U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2074.5	2074.5	2074.5	2074.5
2.5°	2082.1	2085.3	2072.0	2058.7
5°	2081.1	2083.6	2067.0	2050.4
7.5°	2074.2	2076.4	2059.5	2042.5
10°	2064.3	2066.5	2051.9	2037.3
12.5°	2047.3	2049.1	2035.3	2021.5
15°	2019.0	2018.7	2006.1	1993.4
17.5°	1989.6	1986.0	1970.6	1955.2
20°	1968.5	1962.5	1943.9	1925.4
22.5°	1945.2	1937.1	1915.5	1893.8
25°	1904.9	1889.4	1867.9	1846.5
27.5°	1860.5	1833.7	1812.5	1791.2
30°	1826.0	1795.3	1774.8	1754.4
32.5°	1783.9	1751.2	1730.0	1708.8
35°	1714.9	1676.9	1656.4	1635.9
37.5°	1641.2	1598.6	1575.4	1552.2
40°	1592.1	1549.4	1519.2	1489.0
42.5°	1539.5	1505.2	1466.4	1427.6
45°	1445.9	1424.9	1379.1	1333.3
47.5°	1317.5	1323.3	1278.1	1232.9
50°	1219.3	1250.2	1207.3	1164.5
52.5°	1116.9	1163.7	1125.5	1087.3
55°	968.6	1019.7	993.4	967.1
57.5°	819.1	859.4	840.9	822.4
60°	718.6	755.1	740.5	725.9
62.5°	626.2	664.3	651.2	638.1
65°	502.9	542.9	530.2	517.5
67.5°	401.9	439.5	425.7	411.8
70°	342.8	377.9	363.3	348.7
72.5°	293.1	323.7	309.9	296.0
75°	223.0	245.1	234.4	223.7
77.5°	161.4	175.9	169.1	162.3
80°	122.8	133.0	130.1	127.2
82.5°	87.7	93.7	94.6	95.6
85°	44.6	46.5	48.5	50.4
87.5°	15.5	17.4	16.8	16.2
90°	13.4	8.2	5.2	2.2
92.5°	28.8	20.1	14.1	8.2
95°	58.0	46.1	32.7	23.0
97.5°	92.3	73.2	59.9	44.0
100°	110.8	92.2	79.5	62.4
102.5°	131.0	115.4	98.0	80.9
105°	167.3	147.9	127.9	108.5
107.5°	200.9	179.6	155.5	138.1
110°	222.3	199.2	174.0	158.3



TEST NUMBER: P1428047

CATALOG NUMBER: SQ2W-PP3-K-050U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	243.1	219.5	193.6	178.0
115°	271.4	245.3	221.5	208.2
117.5°	298.6	271.8	246.7	236.1
120°	315.2	288.4	263.9	255.7
122.5°	328.9	302.7	280.0	276.6
125°	349.4	322.6	303.3	307.8
127.5°	366.1	341.5	329.3	339.3
130°	376.2	354.6	347.2	361.3
132.5°	385.1	368.3	365.0	384.5
135°	398.5	388.8	391.8	418.5
137.5°	414.4	410.7	420.6	454.4
140°	424.5	426.7	440.9	478.8
142.5°	438.2	443.4	461.7	502.0
145°	459.4	470.6	494.4	534.5
147.5°	483.5	497.9	527.4	568.6
150°	499.6	518.2	549.4	588.8
152.5°	518.0	537.2	568.4	608.4
155°	546.4	568.0	600.7	634.9
157.5°	575.4	597.4	628.6	658.5
160°	593.3	617.0	645.3	672.8
162.5°	613.5	635.5	660.2	684.7
165°	643.1	660.9	681.0	701.8
167.5°	667.9	682.8	698.5	714.7
170°	684.0	695.8	709.2	721.9
172.5°	697.6	707.1	717.0	727.8
175°	715.9	721.1	727.1	733.8
177.5°	730.0	731.8	733.6	736.6
180°	736.0	736.0	736.0	736.0



TEST NUMBER: P1428047
 CATALOG NUMBER: SQ2W-PP3-K-050U-100D-L830-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.41	22.45	22.18	23.23	24.17	17.18	18.22	17.95	19.00	19.94
	3H	22.49	23.41	23.26	24.20	25.17	18.51	19.43	19.29	20.22	21.20
	4H	22.87	23.74	23.66	24.53	25.52	19.07	19.95	19.87	20.74	21.73
	6H	23.07	23.87	23.87	24.68	25.67	19.45	20.25	20.25	21.05	22.05
	8H	23.14	23.90	23.95	24.72	25.72	19.58	20.34	20.40	21.17	22.17
	12H	23.16	23.89	23.98	24.71	25.73	19.62	20.35	20.44	21.17	22.19
4H	2H	21.56	22.43	22.35	23.22	24.21	18.12	18.99	18.91	19.79	20.77
	3H	22.87	23.59	23.68	24.42	25.42	19.56	20.28	20.37	21.11	22.11
	4H	23.38	24.03	24.20	24.87	25.89	20.18	20.84	21.01	21.67	22.70
	6H	23.71	24.27	24.55	25.12	26.16	20.64	21.20	21.48	22.06	23.09
	8H	23.82	24.34	24.66	25.19	26.24	20.81	21.34	21.66	22.19	23.23
	12H	23.87	24.34	24.73	25.21	26.26	20.87	21.34	21.73	22.21	23.26
8H	4H	23.41	23.94	24.26	24.79	25.83	20.51	21.03	21.35	21.88	22.93
	6H	23.83	24.27	24.70	25.16	26.20	21.07	21.51	21.94	22.40	23.45
	8H	24.01	24.40	24.89	25.29	26.35	21.32	21.71	22.20	22.59	23.66
	12H	24.12	24.46	25.00	25.34	26.45	21.43	21.77	22.31	22.65	23.76
12H	4H	23.38	23.85	24.24	24.72	25.77	20.53	21.00	21.39	21.87	22.92
	6H	23.82	24.21	24.71	25.10	26.16	21.14	21.52	22.02	22.41	23.47
	8H	24.03	24.37	24.91	25.25	26.36	21.42	21.76	22.30	22.64	23.76