

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428065

Luminaire Tested: SQ2W-PP3-K-075U-075D-L830-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428065
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-7)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PP3-K-075U-075D-L830-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE PRISM LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7155.4 lumens
Efficiency: N/A
Efficacy: 142.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.41 / 1.4
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 50.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428065

CATALOG NUMBER: SQ2W-PP3-K-075U-075D-L830-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428065

CATALOG NUMBER: SQ2W-PP3-K-075U-075D-L830-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20														
RC	80					70					50					30					10					0									
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																																			
0	108	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54	54	54	42	42	42	30	30	30	18	18	18	6				
1	99	95	92	88	88	92	89	85	83	76	74	72	65	63	62	54	53	52	47	47	47	36	36	36	24	24	24	12	12	12	0				
2	91	84	78	73	73	84	78	73	69	67	64	60	57	55	52	48	46	45	40	40	40	30	30	30	20	20	20	10	10	10	0				
3	83	74	67	61	61	77	69	63	58	60	55	51	51	48	45	43	41	38	35	35	35	25	25	25	15	15	15	5	5	5	0				
4	76	66	58	52	52	71	62	55	49	53	48	44	46	42	39	39	36	34	30	30	30	20	20	20	10	10	10	5	5	5	0				
5	70	59	51	45	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26	26	26	15	15	15	5	5	5	0	0	0	0				
6	65	53	45	39	39	60	50	42	37	43	38	33	37	33	30	32	29	26	23	23	23	10	10	10	5	5	5	0	0	0	0				
7	60	48	40	35	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21	21	21	5	5	5	0	0	0	0	0	0	0				
8	56	43	36	31	31	52	41	34	29	36	30	26	31	27	24	27	23	21	19	19	19	0	0	0	0	0	0	0	0	0	0				
9	52	40	32	27	27	48	37	31	26	33	27	24	29	24	21	25	21	19	17	17	17	0	0	0	0	0	0	0	0	0	0				
10	48	36	29	25	25	45	34	28	23	30	25	21	27	22	19	23	20	17	15	15	15	0	0	0	0	0	0	0	0	0	0				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	24913	24913	24913	24913
5°	24716	25167	24716	25167
10°	24841	25349	24841	25349
15°	24782	25409	24782	25409
20°	24606	25922	24606	25922
25°	24465	27283	24465	27283
30°	24326	27853	24326	27853
35°	23983	27904	23983	27904
40°	23342	25783	23342	25783
45°	22644	19627	22644	19627
50°	21755	16347	21755	16347
55°	20248	11752	20248	11752
60°	17434	8428	17434	8428
65°	14705	8286	14705	8286
70°	12241	7931	12241	7931
75°	10380	7430	10380	7430
80°	8796	6676	8796	6676
85°	6947	3631	6947	3631

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 24770 cd/sqm



TEST NUMBER: P1428065

CATALOG NUMBER: SQ2W-PP3-K-075U-075D-L830-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.9	2.1
10°-20°	425.2	5.9
20°-30°	666.2	9.3
30°-40°	821.8	11.5
40°-50°	773.6	10.8
50°-60°	547.8	7.7
60°-70°	312.1	4.4
70°-80°	154.5	2.2
80°-90°	42.4	0.6
90°-100°	89.0	1.2
100°-110°	259.5	3.6
110°-120°	423.5	5.9
120°-130°	537.4	7.5
130°-140°	575.1	8.0
140°-150°	537.0	7.5
150°-160°	441.9	6.2
160°-170°	296.3	4.1
170°-180°	105.2	1.5
0°-30°	1238.3	17.3
0°-40°	2060.0	28.8
0°-60°	3381.5	47.3
0°-90°	3890.5	54.4
90°-120°	772.0	10.8
90°-150°	2421.5	33.8
90°-180°	3265.0	45.6
0°-180°	7155.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1543	1543	1543	1543	1543	
5°	1525	1553	1525	1553	1525	145
15°	1483	1520	1483	1520	1483	418
25°	1373	1532	1373	1532	1373	633
35°	1217	1416	1217	1416	1217	759
45°	992	860	992	860	992	763
55°	719	418	719	418	719	635
65°	385	217	385	217	385	387
75°	166	119	166	119	166	180
85°	38	20	38	20	38	44
90°	3	25	3	49	3	4
95°	35	26	35	152	35	42
105°	165	264	165	364	165	175
115°	316	438	316	540	316	312
125°	468	695	468	662	468	418
135°	636	909	636	733	636	491
145°	812	1048	812	749	812	508
155°	965	1138	965	777	965	443
165°	1066	1187	1066	894	1066	300
175°	1115	1162	1115	1049	1115	106
180°	1118	1118	1118	1118	1118	



TEST NUMBER: P1428065

CATALOG NUMBER: SQ2W-PP3-K-075U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1543.0	1543.0	1543.0	1543.0	1543.0	1543.0	1543.0	1543.0	1543.0	1543.0	1543.0
2.5°	1531.2	1541.1	1550.9	1548.6	1542.2	1539.6	1540.8	1542.0	1543.1	1544.3	1543.1
5°	1525.0	1537.3	1549.7	1547.9	1541.3	1538.8	1540.2	1542.6	1547.7	1552.8	1547.7
7.5°	1519.2	1531.8	1544.4	1542.7	1536.4	1534.4	1536.9	1540.3	1546.5	1552.8	1546.5
10°	1515.2	1526.1	1537.0	1535.4	1529.6	1528.5	1532.1	1536.1	1541.2	1546.2	1541.2
12.5°	1503.5	1513.8	1524.1	1522.7	1517.5	1517.3	1522.1	1526.8	1531.3	1535.8	1531.3
15°	1482.6	1492.0	1501.5	1501.6	1498.7	1500.6	1507.1	1512.9	1516.5	1520.1	1516.5
17.5°	1454.2	1465.7	1477.1	1479.8	1479.5	1484.0	1493.3	1501.2	1504.9	1508.7	1504.9
20°	1432.1	1445.8	1459.6	1464.1	1465.6	1472.1	1483.7	1494.2	1501.5	1508.7	1501.5
22.5°	1408.6	1424.7	1440.8	1446.7	1449.3	1459.3	1476.7	1492.9	1505.4	1517.8	1505.4
25°	1373.3	1389.3	1405.2	1416.8	1427.0	1444.7	1470.1	1493.9	1512.7	1531.5	1512.7
27.5°	1332.2	1348.0	1363.8	1383.8	1405.1	1430.0	1458.6	1483.7	1498.7	1513.6	1498.7
30°	1304.8	1320.1	1335.3	1358.1	1383.5	1411.0	1440.8	1466.5	1480.3	1494.0	1480.3
32.5°	1270.9	1286.7	1302.5	1326.8	1353.9	1383.5	1415.5	1442.7	1455.3	1467.9	1455.3
35°	1216.8	1232.0	1247.2	1275.5	1308.1	1341.1	1374.4	1401.2	1408.5	1415.7	1408.5
37.5°	1154.5	1171.7	1189.0	1220.7	1257.2	1284.8	1303.5	1317.7	1318.1	1318.5	1318.1
40°	1107.5	1129.9	1152.4	1184.1	1218.9	1238.1	1241.8	1242.1	1232.7	1223.3	1232.7
42.5°	1061.8	1090.7	1119.5	1145.0	1169.3	1174.4	1160.0	1138.8	1096.9	1055.0	1096.9
45°	991.7	1025.7	1059.8	1075.4	1084.8	1052.9	979.7	917.6	888.6	859.6	888.6
47.5°	917.0	950.6	984.2	979.9	963.0	914.7	835.1	770.4	750.4	730.4	750.4
50°	866.1	898.0	929.9	906.9	865.5	811.2	743.8	688.5	669.6	650.8	669.6
52.5°	808.7	837.1	865.5	830.7	774.9	717.7	658.9	607.7	579.0	550.3	579.0
55°	719.3	738.9	758.4	720.4	663.1	600.0	531.2	472.6	445.1	417.5	445.1
57.5°	611.6	625.4	639.2	609.2	564.7	502.0	421.1	352.7	321.9	291.0	321.9
60°	539.9	550.7	561.6	534.4	494.6	434.8	355.0	291.4	276.2	261.0	276.2
62.5°	474.6	484.3	494.1	465.7	424.7	371.3	305.4	254.7	249.4	244.0	249.4
65°	384.9	394.3	403.8	374.1	331.3	289.6	249.0	218.4	217.7	216.9	217.7
67.5°	306.3	316.6	326.9	298.9	258.2	227.4	206.5	190.6	189.7	188.9	189.7
70°	259.3	270.2	281.1	255.0	216.6	191.6	180.0	170.9	169.4	168.0	169.4
72.5°	220.2	230.5	240.8	218.0	184.2	163.6	156.0	150.2	149.3	148.4	149.3
75°	166.4	174.3	182.3	165.8	141.2	127.0	123.4	120.5	119.8	119.1	119.8
77.5°	120.7	125.8	130.8	120.0	104.0	95.0	93.1	91.5	90.8	90.0	90.8
80°	94.6	96.8	98.9	91.3	80.5	74.7	73.9	73.2	72.5	71.8	72.5
82.5°	71.1	70.4	69.7	65.2	59.6	56.4	55.7	54.8	53.5	52.2	53.5
85°	37.5	36.1	34.6	33.2	31.7	29.5	26.6	23.9	21.7	19.6	21.7
87.5°	12.4	13.3	14.5	13.2	11.0	9.4	8.9	8.7	8.9	8.9	8.9
90°	3.4	7.9	13.6	18.1	21.5	22.6	22.6	23.7	24.8	24.8	24.8
92.5°	12.4	19.7	19.9	19.9	24.2	26.2	28.0	28.2	29.4	29.4	29.4
95°	35.0	38.4	57.6	56.5	38.4	30.5	26.0	26.0	26.0	26.0	26.0
97.5°	66.9	71.8	75.0	100.5	106.2	102.6	83.6	70.3	62.8	59.4	62.8
100°	94.9	97.1	103.9	105.0	133.3	160.4	146.8	129.9	124.2	120.9	124.2
102.5°	122.9	124.2	134.6	139.4	145.9	161.3	208.3	203.1	199.2	198.6	199.2
105°	164.9	166.0	185.2	194.3	198.8	198.8	197.7	220.2	256.4	264.3	256.4
107.5°	209.9	215.1	237.6	261.8	267.0	268.4	262.5	259.1	257.7	258.7	257.7
110°	240.6	248.5	275.6	306.1	314.0	316.3	314.0	310.6	308.3	308.3	308.3



TEST NUMBER: P1428065

CATALOG NUMBER: SQ2W-PP3-K-075U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	270.4	281.9	312.6	347.7	361.0	367.8	362.8	360.3	358.0	359.9	358.0
115°	316.3	333.2	373.9	410.0	437.1	440.5	439.4	439.4	438.2	438.2	438.2
117.5°	358.7	385.8	431.5	473.5	504.9	513.9	518.4	517.1	515.7	518.0	515.7
120°	388.5	420.2	472.1	519.6	550.1	563.6	568.1	565.9	568.1	565.9	568.1
122.5°	420.2	459.0	510.1	559.3	595.2	610.6	616.0	616.5	616.9	615.6	616.9
125°	467.6	515.0	574.9	625.7	663.0	681.1	685.6	686.7	689.0	694.6	689.0
127.5°	515.5	569.3	635.0	684.0	722.2	744.1	751.1	753.6	758.3	760.8	758.3
130°	548.9	609.9	676.6	722.9	760.1	783.9	796.3	799.7	805.3	804.2	805.3
132.5°	584.2	647.9	715.4	763.5	798.1	823.6	834.2	843.9	846.0	847.6	846.0
135°	635.9	704.8	772.6	820.0	852.8	877.6	891.2	900.2	905.8	909.2	905.8
137.5°	690.3	763.1	828.1	870.4	903.4	924.8	940.2	949.7	955.5	958.2	955.5
140°	727.4	797.4	860.7	904.7	934.1	955.5	969.1	980.4	987.2	987.2	987.2
142.5°	762.6	831.7	893.2	937.2	963.0	982.6	997.1	1005.7	1013.4	1013.4	1013.4
145°	812.1	881.0	937.5	981.5	1003.0	1021.0	1036.9	1043.6	1048.2	1048.2	1048.2
147.5°	863.8	924.8	976.3	1018.6	1036.6	1057.9	1070.3	1075.7	1081.4	1078.9	1081.4
150°	894.5	951.0	1000.7	1040.2	1058.3	1078.7	1091.1	1095.6	1101.2	1097.9	1101.2
152.5°	924.4	978.1	1023.3	1060.1	1075.5	1095.8	1110.1	1114.6	1118.4	1115.9	1118.4
155°	964.6	1012.0	1053.8	1087.7	1101.2	1120.4	1134.0	1139.6	1144.2	1138.5	1144.2
157.5°	1000.5	1041.4	1077.7	1108.9	1123.4	1139.9	1152.5	1159.5	1164.0	1161.6	1164.0
160°	1022.2	1059.4	1092.2	1121.6	1135.1	1149.8	1163.4	1171.3	1175.8	1172.4	1175.8
162.5°	1040.2	1073.9	1104.9	1131.5	1143.3	1156.1	1172.4	1179.4	1183.9	1179.6	1183.9
165°	1066.2	1093.3	1120.4	1143.0	1153.2	1163.4	1180.3	1188.2	1191.6	1187.1	1191.6
167.5°	1085.9	1106.7	1128.6	1148.0	1155.5	1165.4	1182.3	1188.9	1193.2	1187.5	1193.2
170°	1096.7	1114.8	1134.0	1149.8	1155.5	1164.5	1181.4	1187.1	1190.5	1184.8	1190.5
172.5°	1105.8	1119.3	1134.9	1148.9	1151.8	1159.1	1175.1	1180.8	1183.2	1178.5	1183.2
175°	1114.8	1122.7	1134.0	1143.0	1141.9	1146.4	1160.0	1164.5	1169.0	1162.2	1169.0
177.5°	1119.1	1122.7	1126.3	1131.7	1128.1	1128.1	1138.1	1140.8	1141.7	1138.1	1141.7
180°	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2



TEST NUMBER: P1428065

CATALOG NUMBER: SQ2W-PP3-K-075U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1543.0	1543.0	1543.0	1543.0	1543.0	1543.0	1543.0	1543.0	1543.0	1543.0	1543.0
2.5°	1542.0	1540.8	1539.6	1542.2	1548.6	1550.9	1541.1	1531.2	1541.1	1550.9	1548.6
5°	1542.6	1540.2	1538.8	1541.3	1547.9	1549.7	1537.3	1525.0	1537.3	1549.7	1547.9
7.5°	1540.3	1536.9	1534.4	1536.4	1542.7	1544.4	1531.8	1519.2	1531.8	1544.4	1542.7
10°	1536.1	1532.1	1528.5	1529.6	1535.4	1537.0	1526.1	1515.2	1526.1	1537.0	1535.4
12.5°	1526.8	1522.1	1517.3	1517.5	1522.7	1524.1	1513.8	1503.5	1513.8	1524.1	1522.7
15°	1512.9	1507.1	1500.6	1498.7	1501.6	1501.5	1492.0	1482.6	1492.0	1501.5	1501.6
17.5°	1501.2	1493.3	1484.0	1479.5	1479.8	1477.1	1465.7	1454.2	1465.7	1477.1	1479.8
20°	1494.2	1483.7	1472.1	1465.6	1464.1	1459.6	1445.8	1432.1	1445.8	1459.6	1464.1
22.5°	1492.9	1476.7	1459.3	1449.3	1446.7	1440.8	1424.7	1408.6	1424.7	1440.8	1446.7
25°	1493.9	1470.1	1444.7	1427.0	1416.8	1405.2	1389.3	1373.3	1389.3	1405.2	1416.8
27.5°	1483.7	1458.6	1430.0	1405.1	1383.8	1363.8	1348.0	1332.2	1348.0	1363.8	1383.8
30°	1466.5	1440.8	1411.0	1383.5	1358.1	1335.3	1320.1	1304.8	1320.1	1335.3	1358.1
32.5°	1442.7	1415.5	1383.5	1353.9	1326.8	1302.5	1286.7	1270.9	1286.7	1302.5	1326.8
35°	1401.2	1374.4	1341.1	1308.1	1275.5	1247.2	1232.0	1216.8	1232.0	1247.2	1275.5
37.5°	1317.7	1303.5	1284.8	1257.2	1220.7	1189.0	1171.7	1154.5	1171.7	1189.0	1220.7
40°	1242.1	1241.8	1238.1	1218.9	1184.1	1152.4	1129.9	1107.5	1129.9	1152.4	1184.1
42.5°	1138.8	1160.0	1174.4	1169.3	1145.0	1119.5	1090.7	1061.8	1090.7	1119.5	1145.0
45°	917.6	979.7	1052.9	1084.8	1075.4	1059.8	1025.7	991.7	1025.7	1059.8	1075.4
47.5°	770.4	835.1	914.7	963.0	979.9	984.2	950.6	917.0	950.6	984.2	979.9
50°	688.5	743.8	811.2	865.5	906.9	929.9	898.0	866.1	898.0	929.9	906.9
52.5°	607.7	658.9	717.7	774.9	830.7	865.5	837.1	808.7	837.1	865.5	830.7
55°	472.6	531.2	600.0	663.1	720.4	758.4	738.9	719.3	738.9	758.4	720.4
57.5°	352.7	421.1	502.0	564.7	609.2	639.2	625.4	611.6	625.4	639.2	609.2
60°	291.4	355.0	434.8	494.6	534.4	561.6	550.7	539.9	550.7	561.6	534.4
62.5°	254.7	305.4	371.3	424.7	465.7	494.1	484.3	474.6	484.3	494.1	465.7
65°	218.4	249.0	289.6	331.3	374.1	403.8	394.3	384.9	394.3	403.8	374.1
67.5°	190.6	206.5	227.4	258.2	298.9	326.9	316.6	306.3	316.6	326.9	298.9
70°	170.9	180.0	191.6	216.6	255.0	281.1	270.2	259.3	270.2	281.1	255.0
72.5°	150.2	156.0	163.6	184.2	218.0	240.8	230.5	220.2	230.5	240.8	218.0
75°	120.5	123.4	127.0	141.2	165.8	182.3	174.3	166.4	174.3	182.3	165.8
77.5°	91.5	93.1	95.0	104.0	120.0	130.8	125.8	120.7	125.8	130.8	120.0
80°	73.2	73.9	74.7	80.5	91.3	98.9	96.8	94.6	96.8	98.9	91.3
82.5°	54.8	55.7	56.4	59.6	65.2	69.7	70.4	71.1	70.4	69.7	65.2
85°	23.9	26.6	29.5	31.7	33.2	34.6	36.1	37.5	36.1	34.6	33.2
87.5°	8.7	8.9	9.4	11.0	13.2	14.5	13.3	12.4	13.3	14.2	13.6
90°	23.7	22.6	22.6	21.5	18.1	13.6	7.9	3.4	7.9	12.4	20.3
92.5°	28.2	28.0	26.2	24.2	19.9	19.9	19.7	12.4	21.5	30.5	43.8
95°	26.0	26.0	30.5	38.4	56.5	57.6	38.4	35.0	49.7	70.0	88.1
97.5°	70.3	83.6	102.6	106.2	100.5	75.0	71.8	66.9	91.0	111.1	140.3
100°	129.9	146.8	160.4	133.3	105.0	103.9	97.1	94.9	120.9	140.1	168.3
102.5°	203.1	208.3	161.3	145.9	139.4	134.6	124.2	122.9	148.9	175.3	199.0
105°	220.2	197.7	198.8	198.8	194.3	185.2	166.0	164.9	194.3	224.8	254.1
107.5°	259.1	262.5	268.4	267.0	261.8	237.6	215.1	209.9	236.3	272.9	305.2
110°	310.6	314.0	316.3	314.0	306.1	275.6	248.5	240.6	264.3	302.7	337.7



TEST NUMBER: P1428065

CATALOG NUMBER: SQ2W-PP3-K-075U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	360.3	362.8	367.8	361.0	347.7	312.6	281.9	270.4	294.1	333.4	369.3
115°	439.4	439.4	440.5	437.1	410.0	373.9	333.2	316.3	336.6	372.7	412.3
117.5°	517.1	518.4	513.9	504.9	473.5	431.5	385.8	358.7	374.8	412.9	453.6
120°	565.9	568.1	563.6	550.1	519.6	472.1	420.2	388.5	401.0	438.2	478.9
122.5°	616.5	616.0	610.6	595.2	559.3	510.1	459.0	420.2	425.4	459.9	499.7
125°	686.7	685.6	681.1	663.0	625.7	574.9	515.0	467.6	460.8	490.2	530.9
127.5°	753.6	751.1	744.1	722.2	684.0	635.0	569.3	515.5	500.4	518.9	556.2
130°	799.7	796.3	783.9	760.1	722.9	676.6	609.9	548.9	527.5	538.8	571.5
132.5°	843.9	834.2	823.6	798.1	763.5	715.4	647.9	584.2	554.6	559.5	585.1
135°	900.2	891.2	877.6	852.8	820.0	772.6	704.8	635.9	595.2	590.7	605.4
137.5°	949.7	940.2	924.8	903.4	870.4	828.1	763.1	690.3	639.1	623.9	629.6
140°	980.4	969.1	955.5	934.1	904.7	860.7	797.4	727.4	669.8	648.3	644.9
142.5°	1005.7	997.1	982.6	963.0	937.2	893.2	831.7	762.6	701.4	673.6	665.7
145°	1043.6	1036.9	1021.0	1003.0	981.5	937.5	881.0	812.1	751.1	715.0	698.0
147.5°	1075.7	1070.3	1057.9	1036.6	1018.6	976.3	924.8	863.8	801.3	756.5	734.6
150°	1095.6	1091.1	1078.7	1058.3	1040.2	1000.7	951.0	894.5	834.7	787.2	759.0
152.5°	1114.6	1110.1	1095.8	1075.5	1060.1	1023.3	978.1	924.4	863.6	816.2	787.0
155°	1139.6	1134.0	1120.4	1101.2	1087.7	1053.8	1012.0	964.6	912.6	862.9	830.2
157.5°	1159.5	1152.5	1139.9	1123.4	1108.9	1077.7	1041.4	1000.5	955.1	907.6	874.2
160°	1171.3	1163.4	1149.8	1135.1	1121.6	1092.2	1059.4	1022.2	980.4	937.5	901.3
162.5°	1179.4	1172.4	1156.1	1143.3	1131.5	1104.9	1073.9	1040.2	1003.0	965.5	932.0
165°	1188.2	1180.3	1163.4	1153.2	1143.0	1120.4	1093.3	1066.2	1034.6	1004.1	977.0
167.5°	1188.9	1182.3	1165.4	1155.5	1148.0	1128.6	1106.7	1085.9	1061.3	1037.3	1014.7
170°	1187.1	1181.4	1164.5	1155.5	1149.8	1134.0	1114.8	1096.7	1077.5	1057.2	1039.1
172.5°	1180.8	1175.1	1159.1	1151.8	1148.9	1134.9	1119.3	1105.8	1089.3	1074.4	1059.9
175°	1164.5	1160.0	1146.4	1141.9	1143.0	1134.0	1122.7	1114.8	1104.6	1095.6	1087.7
177.5°	1140.8	1138.1	1128.1	1128.1	1131.7	1126.3	1122.7	1119.1	1114.6	1111.9	1109.1
180°	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2



TEST NUMBER: P1428065

CATALOG NUMBER: SQ2W-PP3-K-075U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1543.0	1543.0	1543.0	1543.0	1543.0	1543.0	1543.0	1543.0	1543.0	1543.0	1543.0
2.5°	1542.2	1539.6	1540.8	1542.0	1543.1	1544.3	1543.1	1542.0	1540.8	1539.6	1542.2
5°	1541.3	1538.8	1540.2	1542.6	1547.7	1552.8	1547.7	1542.6	1540.2	1538.8	1541.3
7.5°	1536.4	1534.4	1536.9	1540.3	1546.5	1552.8	1546.5	1540.3	1536.9	1534.4	1536.4
10°	1529.6	1528.5	1532.1	1536.1	1541.2	1546.2	1541.2	1536.1	1532.1	1528.5	1529.6
12.5°	1517.5	1517.3	1522.1	1526.8	1531.3	1535.8	1531.3	1526.8	1522.1	1517.3	1517.5
15°	1498.7	1500.6	1507.1	1512.9	1516.5	1520.1	1516.5	1512.9	1507.1	1500.6	1498.7
17.5°	1479.5	1484.0	1493.3	1501.2	1504.9	1508.7	1504.9	1501.2	1493.3	1484.0	1479.5
20°	1465.6	1472.1	1483.7	1494.2	1501.5	1508.7	1501.5	1494.2	1483.7	1472.1	1465.6
22.5°	1449.3	1459.3	1476.7	1492.9	1505.4	1517.8	1505.4	1492.9	1476.7	1459.3	1449.3
25°	1427.0	1444.7	1470.1	1493.9	1512.7	1531.5	1512.7	1493.9	1470.1	1444.7	1427.0
27.5°	1405.1	1430.0	1458.6	1483.7	1498.7	1513.6	1498.7	1483.7	1458.6	1430.0	1405.1
30°	1383.5	1411.0	1440.8	1466.5	1480.3	1494.0	1480.3	1466.5	1440.8	1411.0	1383.5
32.5°	1353.9	1383.5	1415.5	1442.7	1455.3	1467.9	1455.3	1442.7	1415.5	1383.5	1353.9
35°	1308.1	1341.1	1374.4	1401.2	1408.5	1415.7	1408.5	1401.2	1374.4	1341.1	1308.1
37.5°	1257.2	1284.8	1303.5	1317.7	1318.1	1318.5	1318.1	1317.7	1303.5	1284.8	1257.2
40°	1218.9	1238.1	1241.8	1242.1	1232.7	1223.3	1232.7	1242.1	1241.8	1238.1	1218.9
42.5°	1169.3	1174.4	1160.0	1138.8	1096.9	1055.0	1096.9	1138.8	1160.0	1174.4	1169.3
45°	1084.8	1052.9	979.7	917.6	888.6	859.6	888.6	917.6	979.7	1052.9	1084.8
47.5°	963.0	914.7	835.1	770.4	750.4	730.4	750.4	770.4	835.1	914.7	963.0
50°	865.5	811.2	743.8	688.5	669.6	650.8	669.6	688.5	743.8	811.2	865.5
52.5°	774.9	717.7	658.9	607.7	579.0	550.3	579.0	607.7	658.9	717.7	774.9
55°	663.1	600.0	531.2	472.6	445.1	417.5	445.1	472.6	531.2	600.0	663.1
57.5°	564.7	502.0	421.1	352.7	321.9	291.0	321.9	352.7	421.1	502.0	564.7
60°	494.6	434.8	355.0	291.4	276.2	261.0	276.2	291.4	355.0	434.8	494.6
62.5°	424.7	371.3	305.4	254.7	249.4	244.0	249.4	254.7	305.4	371.3	424.7
65°	331.3	289.6	249.0	218.4	217.7	216.9	217.7	218.4	249.0	289.6	331.3
67.5°	258.2	227.4	206.5	190.6	189.7	188.9	189.7	190.6	206.5	227.4	258.2
70°	216.6	191.6	180.0	170.9	169.4	168.0	169.4	170.9	180.0	191.6	216.6
72.5°	184.2	163.6	156.0	150.2	149.3	148.4	149.3	150.2	156.0	163.6	184.2
75°	141.2	127.0	123.4	120.5	119.8	119.1	119.8	120.5	123.4	127.0	141.2
77.5°	104.0	95.0	93.1	91.5	90.8	90.0	90.8	91.5	93.1	95.0	104.0
80°	80.5	74.7	73.9	73.2	72.5	71.8	72.5	73.2	73.9	74.7	80.5
82.5°	59.6	56.4	55.7	54.8	53.5	52.2	53.5	54.8	55.7	56.4	59.6
85°	31.7	29.5	26.6	23.9	21.7	19.6	21.7	23.9	26.6	29.5	31.7
87.5°	11.9	11.7	12.7	13.2	14.1	13.6	14.1	13.2	12.7	11.7	11.9
90°	26.0	33.9	41.8	46.3	50.8	48.6	50.8	46.3	41.8	33.9	26.0
92.5°	52.2	65.5	75.2	83.4	87.0	86.5	87.0	83.4	75.2	65.5	52.2
95°	105.0	120.9	136.7	148.0	154.7	152.5	154.7	148.0	136.7	120.9	105.0
97.5°	162.0	183.2	200.8	211.4	218.2	222.7	218.2	211.4	200.8	183.2	162.0
100°	199.9	220.2	240.6	253.0	264.3	268.8	264.3	253.0	240.6	220.2	199.9
102.5°	230.6	257.3	279.4	292.8	302.2	306.8	302.2	292.8	279.4	257.3	230.6
105°	281.2	309.5	333.2	350.1	360.3	363.7	360.3	350.1	333.2	309.5	281.2
107.5°	331.8	361.0	382.9	401.6	414.1	421.3	414.1	401.6	382.9	361.0	331.8
110°	371.6	395.3	419.0	436.0	448.4	452.9	448.4	436.0	419.0	395.3	371.6



TEST NUMBER: P1428065

CATALOG NUMBER: SQ2W-PP3-K-075U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	405.0	431.5	455.2	472.1	486.4	492.7	486.4	472.1	455.2	431.5	405.0
115°	451.8	486.8	508.3	524.1	534.2	539.9	534.2	524.1	508.3	486.8	451.8
117.5°	490.6	527.2	550.7	562.9	567.7	571.7	567.7	562.9	550.7	527.2	490.6
120°	515.0	548.9	576.0	591.8	597.5	599.8	597.5	591.8	576.0	548.9	515.0
122.5°	537.6	569.7	595.9	615.3	624.6	626.9	624.6	615.3	595.9	569.7	537.6
125°	569.3	599.8	626.9	646.1	656.2	661.9	656.2	646.1	626.9	599.8	569.3
127.5°	596.8	629.8	654.6	672.0	682.0	686.5	682.0	672.0	654.6	629.8	596.8
130°	612.2	646.1	670.9	690.1	699.1	703.7	699.1	690.1	670.9	646.1	612.2
132.5°	623.9	659.6	685.4	702.8	712.7	717.2	712.7	702.8	685.4	659.6	623.9
135°	638.2	675.4	702.5	719.5	728.5	733.0	728.5	719.5	702.5	675.4	638.2
137.5°	650.6	684.5	712.7	730.5	738.7	741.6	738.7	730.5	712.7	684.5	650.6
140°	659.6	689.0	717.2	734.2	743.2	744.3	743.2	734.2	717.2	689.0	659.6
142.5°	671.4	694.4	719.0	736.0	745.0	747.0	745.0	736.0	719.0	694.4	671.4
145°	692.4	705.9	722.9	738.7	746.6	748.8	746.6	738.7	722.9	705.9	692.4
147.5°	718.8	723.1	731.9	742.3	750.0	751.6	750.0	742.3	731.9	723.1	718.8
150°	738.7	737.5	740.9	747.7	754.5	753.4	754.5	747.7	740.9	737.5	738.7
152.5°	761.3	754.7	754.5	757.7	760.8	760.6	760.8	757.7	754.5	754.7	761.3
155°	799.7	787.2	780.5	778.2	778.2	777.1	778.2	778.2	780.5	787.2	799.7
157.5°	841.9	824.5	814.4	808.9	807.4	804.9	807.4	808.9	814.4	824.5	841.9
160°	870.8	851.6	841.5	832.4	829.0	825.6	829.0	832.4	841.5	851.6	870.8
162.5°	897.9	879.6	868.6	860.4	857.0	851.9	857.0	860.4	868.6	879.6	897.9
165°	942.0	922.8	910.4	903.6	899.1	894.5	899.1	903.6	910.4	922.8	942.0
167.5°	986.0	965.0	956.9	949.2	944.9	936.8	944.9	949.2	956.9	965.0	986.0
170°	1013.1	993.9	989.4	982.6	974.7	965.7	974.7	982.6	989.4	993.9	1013.1
172.5°	1036.6	1023.8	1019.2	1012.5	1010.0	1002.7	1010.0	1012.5	1019.2	1023.8	1036.6
175°	1070.7	1060.6	1060.6	1059.4	1056.1	1049.3	1056.1	1059.4	1060.6	1060.6	1070.7
177.5°	1099.2	1093.8	1097.4	1097.4	1096.5	1090.2	1096.5	1097.4	1097.4	1093.8	1099.2
180°	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2



TEST NUMBER: P1428065

CATALOG NUMBER: SQ2W-PP3-K-075U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1543.0	1543.0	1543.0	1543.0
2.5°	1548.6	1550.9	1541.1	1531.2
5°	1547.9	1549.7	1537.3	1525.0
7.5°	1542.7	1544.4	1531.8	1519.2
10°	1535.4	1537.0	1526.1	1515.2
12.5°	1522.7	1524.1	1513.8	1503.5
15°	1501.6	1501.5	1492.0	1482.6
17.5°	1479.8	1477.1	1465.7	1454.2
20°	1464.1	1459.6	1445.8	1432.1
22.5°	1446.7	1440.8	1424.7	1408.6
25°	1416.8	1405.2	1389.3	1373.3
27.5°	1383.8	1363.8	1348.0	1332.2
30°	1358.1	1335.3	1320.1	1304.8
32.5°	1326.8	1302.5	1286.7	1270.9
35°	1275.5	1247.2	1232.0	1216.8
37.5°	1220.7	1189.0	1171.7	1154.5
40°	1184.1	1152.4	1129.9	1107.5
42.5°	1145.0	1119.5	1090.7	1061.8
45°	1075.4	1059.8	1025.7	991.7
47.5°	979.9	984.2	950.6	917.0
50°	906.9	929.9	898.0	866.1
52.5°	830.7	865.5	837.1	808.7
55°	720.4	758.4	738.9	719.3
57.5°	609.2	639.2	625.4	611.6
60°	534.4	561.6	550.7	539.9
62.5°	465.7	494.1	484.3	474.6
65°	374.1	403.8	394.3	384.9
67.5°	298.9	326.9	316.6	306.3
70°	255.0	281.1	270.2	259.3
72.5°	218.0	240.8	230.5	220.2
75°	165.8	182.3	174.3	166.4
77.5°	120.0	130.8	125.8	120.7
80°	91.3	98.9	96.8	94.6
82.5°	65.2	69.7	70.4	71.1
85°	33.2	34.6	36.1	37.5
87.5°	13.6	14.2	13.3	12.4
90°	20.3	12.4	7.9	3.4
92.5°	43.8	30.5	21.5	12.4
95°	88.1	70.0	49.7	35.0
97.5°	140.3	111.1	91.0	66.9
100°	168.3	140.1	120.9	94.9
102.5°	199.0	175.3	148.9	122.9
105°	254.1	224.8	194.3	164.9
107.5°	305.2	272.9	236.3	209.9
110°	337.7	302.7	264.3	240.6



TEST NUMBER: P1428065

CATALOG NUMBER: SQ2W-PP3-K-075U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	369.3	333.4	294.1	270.4
115°	412.3	372.7	336.6	316.3
117.5°	453.6	412.9	374.8	358.7
120°	478.9	438.2	401.0	388.5
122.5°	499.7	459.9	425.4	420.2
125°	530.9	490.2	460.8	467.6
127.5°	556.2	518.9	500.4	515.5
130°	571.5	538.8	527.5	548.9
132.5°	585.1	559.5	554.6	584.2
135°	605.4	590.7	595.2	635.9
137.5°	629.6	623.9	639.1	690.3
140°	644.9	648.3	669.8	727.4
142.5°	665.7	673.6	701.4	762.6
145°	698.0	715.0	751.1	812.1
147.5°	734.6	756.5	801.3	863.8
150°	759.0	787.2	834.7	894.5
152.5°	787.0	816.2	863.6	924.4
155°	830.2	862.9	912.6	964.6
157.5°	874.2	907.6	955.1	1000.5
160°	901.3	937.5	980.4	1022.2
162.5°	932.0	965.5	1003.0	1040.2
165°	977.0	1004.1	1034.6	1066.2
167.5°	1014.7	1037.3	1061.3	1085.9
170°	1039.1	1057.2	1077.5	1096.7
172.5°	1059.9	1074.4	1089.3	1105.8
175°	1087.7	1095.6	1104.6	1114.8
177.5°	1109.1	1111.9	1114.6	1119.1
180°	1118.2	1118.2	1118.2	1118.2



TEST NUMBER: P1428065
 CATALOG NUMBER: SQ2W-PP3-K-075U-075D-L830-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.02	19.89	19.95	20.83	22.04	14.79	15.66	15.72	16.60	17.81
	3H	20.08	20.86	21.02	21.81	23.04	16.10	16.88	17.04	17.83	19.06
	4H	20.45	21.19	21.41	22.14	23.38	16.66	17.39	17.61	18.35	19.59
	6H	20.65	21.32	21.61	22.28	23.54	17.03	17.70	17.99	18.66	19.91
	8H	20.71	21.35	21.68	22.33	23.58	17.16	17.80	18.13	18.77	20.02
	12H	20.73	21.34	21.71	22.31	23.59	17.19	17.80	18.17	18.77	20.05
4H	2H	19.14	19.88	20.10	20.83	22.07	15.70	16.44	16.66	17.39	18.63
	3H	20.44	21.04	21.41	22.03	23.28	17.13	17.73	18.10	18.72	19.97
	4H	20.95	21.50	21.92	22.48	23.76	17.75	18.30	18.73	19.28	20.56
	6H	21.26	21.74	22.25	22.74	24.02	18.20	18.67	19.19	19.67	20.95
	8H	21.37	21.82	22.36	22.81	24.10	18.37	18.81	19.36	19.80	21.10
	12H	21.42	21.82	22.43	22.83	24.13	18.42	18.82	19.43	19.83	21.13
8H	4H	20.97	21.41	21.96	22.40	23.70	18.06	18.50	19.05	19.50	20.79
	6H	21.38	21.75	22.39	22.78	24.07	18.62	18.99	19.63	20.02	21.31
	8H	21.56	21.88	22.58	22.91	24.22	18.87	19.19	19.89	20.21	21.52
	12H	21.66	21.94	22.68	22.96	24.31	18.97	19.25	19.99	20.27	21.63
12H	4H	20.93	21.33	21.93	22.34	23.63	18.07	18.47	19.08	19.48	20.78
	6H	21.37	21.69	22.39	22.72	24.03	18.68	19.01	19.71	20.03	21.34
	8H	21.57	21.85	22.59	22.87	24.23	18.96	19.25	19.99	20.26	21.62