

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428149

Luminaire Tested: SQ2W-PP3-K-150U-125D-L830-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428149
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-7)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PP3-K-150U-125D-L830-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE PRISM LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13088.9 lumens
Efficiency: N/A
Efficacy: 125.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.41 / 1.4
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 104.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428149

CATALOG NUMBER: SQ2W-PP3-K-150U-125D-L830-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428149

CATALOG NUMBER: SQ2W-PP3-K-150U-125D-L830-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	94	90	87	91	87	84	81	74	71	69	62	60	59	50	49	48	43				
2	90	83	77	72	83	77	72	67	65	61	58	55	52	50	45	43	41	37				
3	82	73	66	60	76	68	62	57	58	53	49	49	45	42	40	38	36	32				
4	75	65	57	51	69	60	54	48	52	47	42	44	40	37	36	33	31	28				
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	24				
6	64	52	44	39	59	49	42	36	42	36	32	36	31	28	30	27	24	21				
7	59	47	39	34	55	44	37	32	38	32	28	32	28	25	27	24	22	19				
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	17				
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	23	20	17	15				
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	41706	41706	41706	41706
5°	41379	42131	41379	42131
10°	41588	42439	41588	42439
15°	41489	42538	41489	42538
20°	41191	43398	41191	43398
25°	40958	45677	40958	45677
30°	40726	46631	40726	46631
35°	40149	46715	40149	46715
40°	39078	43163	39078	43163
45°	37908	32857	37908	32857
50°	36419	27366	36419	27366
55°	33897	19676	33897	19676
60°	29185	14108	29185	14108
65°	24618	13876	24618	13876
70°	20497	13274	20497	13274
75°	17373	12433	17373	12433
80°	14728	11167	14728	11167
85°	11634	6076	11634	6076

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 41467 cd/sqm



TEST NUMBER: P1428149

CATALOG NUMBER: SQ2W-PP3-K-150U-125D-L830-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	246.0	1.9
10°-20°	711.9	5.4
20°-30°	1115.2	8.5
30°-40°	1375.7	10.5
40°-50°	1295.2	9.9
50°-60°	917.1	7.0
60°-70°	522.6	4.0
70°-80°	258.7	2.0
80°-90°	72.5	0.6
90°-100°	179.2	1.4
100°-110°	522.6	4.0
110°-120°	852.8	6.5
120°-130°	1082.1	8.3
130°-140°	1157.9	8.8
140°-150°	1081.2	8.3
150°-160°	889.7	6.8
160°-170°	596.7	4.6
170°-180°	211.9	1.6
0°-30°	2073.1	15.8
0°-40°	3448.8	26.3
0°-60°	5661.0	43.3
0°-90°	6514.8	49.8
90°-120°	1554.5	11.9
90°-150°	4875.8	37.3
90°-180°	6574.0	50.2
0°-180°	13088.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2583	2583	2583	2583	2583	
5°	2553	2600	2553	2600	2553	243
15°	2482	2545	2482	2545	2482	699
25°	2299	2564	2299	2564	2299	1059
35°	2037	2370	2037	2370	2037	1270
45°	1660	1439	1660	1439	1660	1278
55°	1204	699	1204	699	1204	1062
65°	644	363	644	363	644	647
75°	278	199	278	199	278	302
85°	63	33	63	33	63	74
90°	7	50	7	98	7	8
95°	70	52	70	307	70	85
105°	332	532	332	732	332	353
115°	637	882	637	1087	637	628
125°	942	1399	942	1333	942	842
135°	1280	1831	1280	1476	1280	989
145°	1635	2110	1635	1508	1635	1023
155°	1942	2292	1942	1565	1942	893
165°	2147	2390	2147	1801	2147	604
175°	2245	2340	2245	2113	2245	213
180°	2252	2252	2252	2252	2252	



TEST NUMBER: P1428149

CATALOG NUMBER: SQ2W-PP3-K-150U-125D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2583.1	2583.1	2583.1	2583.1	2583.1	2583.1	2583.1	2583.1	2583.1	2583.1	2583.1
2.5°	2563.5	2580.0	2596.5	2592.6	2581.9	2577.5	2579.5	2581.4	2583.4	2585.3	2583.4
5°	2553.1	2573.7	2594.3	2591.3	2580.4	2576.1	2578.6	2582.5	2591.0	2599.5	2591.0
7.5°	2543.2	2564.4	2585.5	2582.8	2572.1	2568.8	2572.9	2578.6	2589.1	2599.5	2589.1
10°	2536.7	2554.9	2573.1	2570.4	2560.7	2558.8	2564.9	2571.6	2580.1	2588.6	2580.1
12.5°	2517.0	2534.3	2551.5	2549.3	2540.5	2540.2	2548.2	2556.1	2563.6	2571.1	2563.6
15°	2482.1	2497.9	2513.6	2513.9	2509.1	2512.1	2523.0	2532.8	2538.8	2544.9	2538.8
17.5°	2434.6	2453.7	2472.9	2477.4	2476.9	2484.4	2499.9	2513.2	2519.5	2525.8	2519.5
20°	2397.4	2420.5	2443.6	2451.1	2453.6	2464.5	2483.9	2501.5	2513.6	2525.8	2513.6
22.5°	2358.1	2385.1	2412.0	2422.0	2426.4	2443.1	2472.3	2499.3	2520.2	2541.1	2520.2
25°	2299.1	2325.8	2352.5	2372.0	2388.9	2418.7	2461.1	2500.9	2532.4	2564.0	2532.4
27.5°	2230.3	2256.8	2283.2	2316.6	2352.3	2394.0	2441.9	2484.0	2509.0	2534.0	2509.0
30°	2184.5	2209.9	2235.4	2273.7	2316.1	2362.2	2412.0	2455.1	2478.1	2501.2	2478.1
32.5°	2127.7	2154.1	2180.6	2221.2	2266.6	2316.1	2369.8	2415.3	2436.4	2457.5	2436.4
35°	2037.0	2062.5	2088.0	2135.3	2189.9	2245.1	2301.0	2345.9	2358.0	2370.1	2358.0
37.5°	1932.7	1961.6	1990.5	2043.6	2104.7	2151.0	2182.3	2205.9	2206.7	2207.4	2206.7
40°	1854.1	1891.7	1929.3	1982.4	2040.6	2072.8	2078.9	2079.5	2063.7	2047.9	2063.7
42.5°	1777.6	1825.9	1874.2	1916.9	1957.6	1966.0	1942.0	1906.4	1836.3	1766.1	1836.3
45°	1660.2	1717.2	1774.3	1800.4	1816.1	1762.7	1640.2	1536.1	1487.6	1439.0	1487.6
47.5°	1535.1	1591.4	1647.7	1640.5	1612.1	1531.3	1398.0	1289.7	1256.2	1222.7	1256.2
50°	1449.9	1503.3	1556.7	1518.2	1449.0	1358.0	1245.1	1152.6	1121.0	1089.5	1121.0
52.5°	1353.8	1401.4	1449.0	1390.8	1297.3	1201.4	1103.1	1017.4	969.4	921.3	969.4
55°	1204.2	1236.9	1269.7	1206.0	1110.1	1004.5	889.3	791.3	745.1	699.0	745.1
57.5°	1024.0	1047.0	1070.1	1020.0	945.4	840.5	705.0	590.5	538.8	487.1	538.8
60°	903.8	922.0	940.2	894.7	828.0	727.8	594.4	487.9	462.4	436.9	462.4
62.5°	794.6	810.9	827.1	779.7	711.0	621.5	511.3	426.5	417.5	408.5	417.5
65°	644.4	660.2	676.0	626.2	554.6	484.8	416.9	365.6	364.4	363.2	364.4
67.5°	512.8	530.0	547.3	500.4	432.2	380.6	345.7	319.1	317.7	316.2	317.7
70°	434.2	452.4	470.6	426.9	362.6	320.7	301.3	286.1	283.7	281.2	283.7
72.5°	368.6	385.9	403.1	365.0	308.4	273.8	261.2	251.4	249.9	248.5	249.9
75°	278.5	291.9	305.2	277.6	236.3	212.7	206.6	201.8	200.5	199.3	200.5
77.5°	202.1	210.6	219.1	201.0	174.0	159.0	155.8	153.2	151.9	150.7	151.9
80°	158.4	162.0	165.7	152.9	134.7	125.0	123.8	122.6	121.4	120.1	121.4
82.5°	119.1	117.8	116.6	109.2	99.8	94.4	93.2	91.7	89.6	87.4	89.6
85°	62.8	60.4	57.9	55.5	53.1	49.5	44.6	40.0	36.4	32.8	36.4
87.5°	21.0	22.8	25.1	23.3	19.8	17.3	16.4	16.1	16.6	16.6	16.6
90°	6.8	15.9	27.3	36.4	43.2	45.5	45.5	47.8	50.0	50.0	50.0
92.5°	25.0	39.6	40.0	40.0	48.7	52.8	56.4	56.9	59.1	59.1	59.1
95°	70.5	77.3	116.0	113.7	77.3	61.4	52.3	52.3	52.3	52.3	52.3
97.5°	134.6	144.6	151.0	202.4	213.8	206.5	168.3	141.5	126.4	119.6	126.4
100°	191.0	195.6	209.2	211.5	268.4	322.9	295.7	261.5	250.2	243.3	250.2
102.5°	247.4	250.2	271.1	280.6	293.8	324.8	419.4	408.9	401.2	399.8	401.2
105°	332.0	334.3	373.0	391.2	400.3	400.3	398.0	443.5	516.3	532.2	516.3
107.5°	422.6	433.0	478.5	527.2	537.6	540.4	528.5	521.7	519.0	520.8	519.0
110°	484.4	500.3	554.9	616.3	632.2	636.8	632.2	625.4	620.9	620.9	620.9

TEST NUMBER: P1428149

CATALOG NUMBER: SQ2W-PP3-K-150U-125D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	544.5	567.7	629.5	700.0	726.9	740.5	730.5	725.5	720.9	724.6	720.9
115°	636.8	670.9	752.8	825.6	880.1	887.0	884.7	884.7	882.4	882.4	882.4
117.5°	722.3	776.9	868.8	953.4	1016.6	1034.8	1043.9	1041.2	1038.4	1043.0	1038.4
120°	782.3	846.0	950.6	1046.2	1107.6	1134.9	1144.0	1139.4	1144.0	1139.4	1144.0
122.5°	846.0	924.3	1027.1	1126.2	1198.5	1229.5	1240.4	1241.3	1242.2	1239.5	1242.2
125°	941.5	1037.1	1157.6	1259.9	1335.0	1371.4	1380.5	1382.8	1387.3	1398.7	1387.3
127.5°	1038.0	1146.2	1278.6	1377.3	1454.2	1498.3	1512.4	1517.4	1526.9	1531.9	1526.9
130°	1105.3	1228.1	1362.3	1455.5	1530.6	1578.3	1603.4	1610.2	1621.6	1619.3	1621.6
132.5°	1176.3	1304.5	1440.5	1537.4	1607.0	1658.4	1679.8	1699.3	1703.4	1706.6	1703.4
135°	1280.4	1419.1	1555.6	1651.1	1717.1	1767.1	1794.4	1812.6	1824.0	1830.8	1824.0
137.5°	1390.0	1536.5	1667.5	1752.6	1819.0	1862.2	1893.1	1912.2	1924.0	1929.5	1924.0
140°	1464.6	1605.6	1733.0	1821.7	1880.8	1924.0	1951.3	1974.1	1987.7	1987.7	1987.7
142.5°	1535.6	1674.8	1798.5	1887.2	1939.0	1978.6	2007.7	2025.0	2040.5	2040.5	2040.5
145°	1635.2	1773.9	1887.6	1976.3	2019.6	2055.9	2087.8	2101.4	2110.5	2110.5	2110.5
147.5°	1739.4	1862.2	1965.9	2050.9	2087.3	2130.1	2155.1	2166.0	2177.4	2172.4	2177.4
150°	1801.2	1914.9	2015.0	2094.6	2131.0	2171.9	2196.9	2206.0	2217.4	2210.6	2217.4
152.5°	1861.3	1969.5	2060.5	2134.6	2165.6	2206.5	2235.2	2244.2	2252.0	2247.0	2252.0
155°	1942.2	2037.7	2121.9	2190.1	2217.4	2256.1	2283.4	2294.7	2303.8	2292.5	2303.8
157.5°	2014.5	2096.9	2170.1	2232.9	2262.0	2295.2	2320.7	2334.8	2343.9	2338.9	2343.9
160°	2058.2	2133.3	2199.2	2258.3	2285.6	2315.2	2342.5	2358.4	2367.5	2360.7	2367.5
162.5°	2094.6	2162.4	2224.7	2278.4	2302.0	2327.9	2360.7	2374.8	2383.9	2375.2	2383.9
165°	2146.9	2201.5	2256.1	2301.6	2322.0	2342.5	2376.6	2392.5	2399.4	2390.3	2399.4
167.5°	2186.5	2228.3	2272.5	2311.6	2326.6	2346.6	2380.7	2393.9	2402.5	2391.2	2402.5
170°	2208.3	2244.7	2283.4	2315.2	2326.6	2344.8	2378.9	2390.3	2397.1	2385.7	2397.1
172.5°	2226.5	2253.8	2285.2	2313.4	2319.3	2333.9	2366.2	2377.5	2382.5	2373.0	2382.5
175°	2244.7	2260.6	2283.4	2301.6	2299.3	2308.4	2335.7	2344.8	2353.9	2340.2	2353.9
177.5°	2253.3	2260.6	2267.9	2278.8	2271.5	2271.5	2291.6	2297.0	2298.8	2291.6	2298.8
180°	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5



TEST NUMBER: P1428149

CATALOG NUMBER: SQ2W-PP3-K-150U-125D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2583.1	2583.1	2583.1	2583.1	2583.1	2583.1	2583.1	2583.1	2583.1	2583.1	2583.1
2.5°	2581.4	2579.5	2577.5	2581.9	2592.6	2596.5	2580.0	2563.5	2580.0	2596.5	2592.6
5°	2582.5	2578.6	2576.1	2580.4	2591.3	2594.3	2573.7	2553.1	2573.7	2594.3	2591.3
7.5°	2578.6	2572.9	2568.8	2572.1	2582.8	2585.5	2564.4	2543.2	2564.4	2585.5	2582.8
10°	2571.6	2564.9	2558.8	2560.7	2570.4	2573.1	2554.9	2536.7	2554.9	2573.1	2570.4
12.5°	2556.1	2548.2	2540.2	2540.5	2549.3	2551.5	2534.3	2517.0	2534.3	2551.5	2549.3
15°	2532.8	2523.0	2512.1	2509.1	2513.9	2513.6	2497.9	2482.1	2497.9	2513.6	2513.9
17.5°	2513.2	2499.9	2484.4	2476.9	2477.4	2472.9	2453.7	2434.6	2453.7	2472.9	2477.4
20°	2501.5	2483.9	2464.5	2453.6	2451.1	2443.6	2420.5	2397.4	2420.5	2443.6	2451.1
22.5°	2499.3	2472.3	2443.1	2426.4	2422.0	2412.0	2385.1	2358.1	2385.1	2412.0	2422.0
25°	2500.9	2461.1	2418.7	2388.9	2372.0	2352.5	2325.8	2299.1	2325.8	2352.5	2372.0
27.5°	2484.0	2441.9	2394.0	2352.3	2316.6	2283.2	2256.8	2230.3	2256.8	2283.2	2316.6
30°	2455.1	2412.0	2362.2	2316.1	2273.7	2235.4	2209.9	2184.5	2209.9	2235.4	2273.7
32.5°	2415.3	2369.8	2316.1	2266.6	2221.2	2180.6	2154.1	2127.7	2154.1	2180.6	2221.2
35°	2345.9	2301.0	2245.1	2189.9	2135.3	2088.0	2062.5	2037.0	2062.5	2088.0	2135.3
37.5°	2205.9	2182.3	2151.0	2104.7	2043.6	1990.5	1961.6	1932.7	1961.6	1990.5	2043.6
40°	2079.5	2078.9	2072.8	2040.6	1982.4	1929.3	1891.7	1854.1	1891.7	1929.3	1982.4
42.5°	1906.4	1942.0	1966.0	1957.6	1916.9	1874.2	1825.9	1777.6	1825.9	1874.2	1916.9
45°	1536.1	1640.2	1762.7	1816.1	1800.4	1774.3	1717.2	1660.2	1717.2	1774.3	1800.4
47.5°	1289.7	1398.0	1531.3	1612.1	1640.5	1647.7	1591.4	1535.1	1591.4	1647.7	1640.5
50°	1152.6	1245.1	1358.0	1449.0	1518.2	1556.7	1503.3	1449.9	1503.3	1556.7	1518.2
52.5°	1017.4	1103.1	1201.4	1297.3	1390.8	1449.0	1401.4	1353.8	1401.4	1449.0	1390.8
55°	791.3	889.3	1004.5	1110.1	1206.0	1269.7	1236.9	1204.2	1236.9	1269.7	1206.0
57.5°	590.5	705.0	840.5	945.4	1020.0	1070.1	1047.0	1024.0	1047.0	1070.1	1020.0
60°	487.9	594.4	727.8	828.0	894.7	940.2	922.0	903.8	922.0	940.2	894.7
62.5°	426.5	511.3	621.5	711.0	779.7	827.1	810.9	794.6	810.9	827.1	779.7
65°	365.6	416.9	484.8	554.6	626.2	676.0	660.2	644.4	660.2	676.0	626.2
67.5°	319.1	345.7	380.6	432.2	500.4	547.3	530.0	512.8	530.0	547.3	500.4
70°	286.1	301.3	320.7	362.6	426.9	470.6	452.4	434.2	452.4	470.6	426.9
72.5°	251.4	261.2	273.8	308.4	365.0	403.1	385.9	368.6	385.9	403.1	365.0
75°	201.8	206.6	212.7	236.3	277.6	305.2	291.9	278.5	291.9	305.2	277.6
77.5°	153.2	155.8	159.0	174.0	201.0	219.1	210.6	202.1	210.6	219.1	201.0
80°	122.6	123.8	125.0	134.7	152.9	165.7	162.0	158.4	162.0	165.7	152.9
82.5°	91.7	93.2	94.4	99.8	109.2	116.6	117.8	119.1	117.8	116.6	109.2
85°	40.0	44.6	49.5	53.1	55.5	57.9	60.4	62.8	60.4	57.9	55.5
87.5°	16.1	16.4	17.3	19.8	23.3	25.1	22.8	21.0	22.8	24.7	24.2
90°	47.8	45.5	45.5	43.2	36.4	27.3	15.9	6.8	15.9	25.0	40.9
92.5°	56.9	56.4	52.8	48.7	40.0	40.0	39.6	25.0	43.2	61.4	88.2
95°	52.3	52.3	61.4	77.3	113.7	116.0	77.3	70.5	100.1	141.0	177.4
97.5°	141.5	168.3	206.5	213.8	202.4	151.0	144.6	134.6	183.3	223.8	282.5
100°	261.5	295.7	322.9	268.4	211.5	209.2	195.6	191.0	243.3	282.0	338.9
102.5°	408.9	419.4	324.8	293.8	280.6	271.1	250.2	247.4	299.7	353.0	400.7
105°	443.5	398.0	400.3	400.3	391.2	373.0	334.3	332.0	391.2	452.6	511.7
107.5°	521.7	528.5	540.4	537.6	527.2	478.5	433.0	422.6	475.8	549.5	614.5
110°	625.4	632.2	636.8	632.2	616.3	554.9	500.3	484.4	532.2	609.5	680.0



TEST NUMBER: P1428149

CATALOG NUMBER: SQ2W-PP3-K-150U-125D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	725.5	730.5	740.5	726.9	700.0	629.5	567.7	544.5	592.2	671.4	743.7
115°	884.7	884.7	887.0	880.1	825.6	752.8	670.9	636.8	677.7	750.5	830.1
117.5°	1041.2	1043.9	1034.8	1016.6	953.4	868.8	776.9	722.3	754.6	831.5	913.3
120°	1139.4	1144.0	1134.9	1107.6	1046.2	950.6	846.0	782.3	807.4	882.4	964.3
122.5°	1241.3	1240.4	1229.5	1198.5	1126.2	1027.1	924.3	846.0	856.5	926.1	1006.1
125°	1382.8	1380.5	1371.4	1335.0	1259.9	1157.6	1037.1	941.5	927.9	987.0	1068.9
127.5°	1517.4	1512.4	1498.3	1454.2	1377.3	1278.6	1146.2	1038.0	1007.5	1044.8	1119.9
130°	1610.2	1603.4	1578.3	1530.6	1455.5	1362.3	1228.1	1105.3	1062.1	1084.8	1150.8
132.5°	1699.3	1679.8	1658.4	1607.0	1537.4	1440.5	1304.5	1176.3	1116.7	1126.7	1178.1
135°	1812.6	1794.4	1767.1	1717.1	1651.1	1555.6	1419.1	1280.4	1198.5	1189.4	1219.0
137.5°	1912.2	1893.1	1862.2	1819.0	1752.6	1667.5	1536.5	1390.0	1286.8	1256.3	1267.7
140°	1974.1	1951.3	1924.0	1880.8	1821.7	1733.0	1605.6	1464.6	1348.6	1305.4	1298.6
142.5°	2025.0	2007.7	1978.6	1939.0	1887.2	1798.5	1674.8	1535.6	1412.3	1356.4	1340.5
145°	2101.4	2087.8	2055.9	2019.6	1976.3	1887.6	1773.9	1635.2	1512.4	1439.6	1405.5
147.5°	2166.0	2155.1	2130.1	2087.3	2050.9	1965.9	1862.2	1739.4	1613.4	1523.3	1479.2
150°	2206.0	2196.9	2171.9	2131.0	2094.6	2015.0	1914.9	1801.2	1680.7	1585.2	1528.3
152.5°	2244.2	2235.2	2206.5	2165.6	2134.6	2060.5	1969.5	1861.3	1738.9	1643.4	1584.7
155°	2294.7	2283.4	2256.1	2217.4	2190.1	2121.9	2037.7	1942.2	1837.6	1737.5	1671.6
157.5°	2334.8	2320.7	2295.2	2262.0	2232.9	2170.1	2096.9	2014.5	1923.1	1827.6	1760.3
160°	2358.4	2342.5	2315.2	2285.6	2258.3	2199.2	2133.3	2058.2	1974.1	1887.6	1814.9
162.5°	2374.8	2360.7	2327.9	2302.0	2278.4	2224.7	2162.4	2094.6	2019.6	1944.0	1876.7
165°	2392.5	2376.6	2342.5	2322.0	2301.6	2256.1	2201.5	2146.9	2083.2	2021.8	1967.2
167.5°	2393.9	2380.7	2346.6	2326.6	2311.6	2272.5	2228.3	2186.5	2136.9	2088.7	2043.2
170°	2390.3	2378.9	2344.8	2326.6	2315.2	2283.4	2244.7	2208.3	2169.7	2128.7	2092.3
172.5°	2377.5	2366.2	2333.9	2319.3	2313.4	2285.2	2253.8	2226.5	2193.3	2163.3	2134.2
175°	2344.8	2335.7	2308.4	2299.3	2301.6	2283.4	2260.6	2244.7	2224.2	2206.0	2190.1
177.5°	2297.0	2291.6	2271.5	2271.5	2278.8	2267.9	2260.6	2253.3	2244.2	2238.8	2233.3
180°	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5



TEST NUMBER: P1428149

CATALOG NUMBER: SQ2W-PP3-K-150U-125D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2583.1	2583.1	2583.1	2583.1	2583.1	2583.1	2583.1	2583.1	2583.1	2583.1	2583.1
2.5°	2581.9	2577.5	2579.5	2581.4	2583.4	2585.3	2583.4	2581.4	2579.5	2577.5	2581.9
5°	2580.4	2576.1	2578.6	2582.5	2591.0	2599.5	2591.0	2582.5	2578.6	2576.1	2580.4
7.5°	2572.1	2568.8	2572.9	2578.6	2589.1	2599.5	2589.1	2578.6	2572.9	2568.8	2572.1
10°	2560.7	2558.8	2564.9	2571.6	2580.1	2588.6	2580.1	2571.6	2564.9	2558.8	2560.7
12.5°	2540.5	2540.2	2548.2	2556.1	2563.6	2571.1	2563.6	2556.1	2548.2	2540.2	2540.5
15°	2509.1	2512.1	2523.0	2532.8	2538.8	2544.9	2538.8	2532.8	2523.0	2512.1	2509.1
17.5°	2476.9	2484.4	2499.9	2513.2	2519.5	2525.8	2519.5	2513.2	2499.9	2484.4	2476.9
20°	2453.6	2464.5	2483.9	2501.5	2513.6	2525.8	2513.6	2501.5	2483.9	2464.5	2453.6
22.5°	2426.4	2443.1	2472.3	2499.3	2520.2	2541.1	2520.2	2499.3	2472.3	2443.1	2426.4
25°	2388.9	2418.7	2461.1	2500.9	2532.4	2564.0	2532.4	2500.9	2461.1	2418.7	2388.9
27.5°	2352.3	2394.0	2441.9	2484.0	2509.0	2534.0	2509.0	2484.0	2441.9	2394.0	2352.3
30°	2316.1	2362.2	2412.0	2455.1	2478.1	2501.2	2478.1	2455.1	2412.0	2362.2	2316.1
32.5°	2266.6	2316.1	2369.8	2415.3	2436.4	2457.5	2436.4	2415.3	2369.8	2316.1	2266.6
35°	2189.9	2245.1	2301.0	2345.9	2358.0	2370.1	2358.0	2345.9	2301.0	2245.1	2189.9
37.5°	2104.7	2151.0	2182.3	2205.9	2206.7	2207.4	2206.7	2205.9	2182.3	2151.0	2104.7
40°	2040.6	2072.8	2078.9	2079.5	2063.7	2047.9	2063.7	2079.5	2078.9	2072.8	2040.6
42.5°	1957.6	1966.0	1942.0	1906.4	1836.3	1766.1	1836.3	1906.4	1942.0	1966.0	1957.6
45°	1816.1	1762.7	1640.2	1536.1	1487.6	1439.0	1487.6	1536.1	1640.2	1762.7	1816.1
47.5°	1612.1	1531.3	1398.0	1289.7	1256.2	1222.7	1256.2	1289.7	1398.0	1531.3	1612.1
50°	1449.0	1358.0	1245.1	1152.6	1121.0	1089.5	1121.0	1152.6	1245.1	1358.0	1449.0
52.5°	1297.3	1201.4	1103.1	1017.4	969.4	921.3	969.4	1017.4	1103.1	1201.4	1297.3
55°	1110.1	1004.5	889.3	791.3	745.1	699.0	745.1	791.3	889.3	1004.5	1110.1
57.5°	945.4	840.5	705.0	590.5	538.8	487.1	538.8	590.5	705.0	840.5	945.4
60°	828.0	727.8	594.4	487.9	462.4	436.9	462.4	487.9	594.4	727.8	828.0
62.5°	711.0	621.5	511.3	426.5	417.5	408.5	417.5	426.5	511.3	621.5	711.0
65°	554.6	484.8	416.9	365.6	364.4	363.2	364.4	365.6	416.9	484.8	554.6
67.5°	432.2	380.6	345.7	319.1	317.7	316.2	317.7	319.1	345.7	380.6	432.2
70°	362.6	320.7	301.3	286.1	283.7	281.2	283.7	286.1	301.3	320.7	362.6
72.5°	308.4	273.8	261.2	251.4	249.9	248.5	249.9	251.4	261.2	273.8	308.4
75°	236.3	212.7	206.6	201.8	200.5	199.3	200.5	201.8	206.6	212.7	236.3
77.5°	174.0	159.0	155.8	153.2	151.9	150.7	151.9	153.2	155.8	159.0	174.0
80°	134.7	125.0	123.8	122.6	121.4	120.1	121.4	122.6	123.8	125.0	134.7
82.5°	99.8	94.4	93.2	91.7	89.6	87.4	89.6	91.7	93.2	94.4	99.8
85°	53.1	49.5	44.6	40.0	36.4	32.8	36.4	40.0	44.6	49.5	53.1
87.5°	21.6	21.9	24.1	25.2	27.0	26.1	27.0	25.2	24.1	21.9	21.6
90°	52.3	68.2	84.1	93.2	102.3	97.8	102.3	93.2	84.1	68.2	52.3
92.5°	105.1	131.9	151.5	167.8	175.1	174.2	175.1	167.8	151.5	131.9	105.1
95°	211.5	243.3	275.2	297.9	311.6	307.0	311.6	297.9	275.2	243.3	211.5
97.5°	326.1	368.9	404.4	425.7	439.4	448.5	439.4	425.7	404.4	368.9	326.1
100°	402.5	443.5	484.4	509.4	532.2	541.3	532.2	509.4	484.4	443.5	402.5
102.5°	464.4	518.1	562.7	589.5	608.6	617.7	608.6	589.5	562.7	518.1	464.4
105°	566.3	623.1	670.9	705.0	725.5	732.3	725.5	705.0	670.9	623.1	566.3
107.5°	668.2	726.9	771.0	808.7	833.7	848.3	833.7	808.7	771.0	726.9	668.2
110°	748.2	796.0	843.8	877.9	902.9	912.0	902.9	877.9	843.8	796.0	748.2



TEST NUMBER: P1428149

CATALOG NUMBER: SQ2W-PP3-K-150U-125D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	815.6	868.8	916.5	950.6	979.3	992.0	979.3	950.6	916.5	868.8	815.6
115°	909.7	980.2	1023.4	1055.3	1075.7	1087.1	1075.7	1055.3	1023.4	980.2	909.7
117.5°	987.9	1061.6	1108.9	1133.5	1143.0	1151.2	1143.0	1133.5	1108.9	1061.6	987.9
120°	1037.1	1105.3	1159.9	1191.7	1203.1	1207.6	1203.1	1191.7	1159.9	1105.3	1037.1
122.5°	1082.6	1147.1	1199.9	1239.0	1257.7	1262.2	1257.7	1239.0	1199.9	1147.1	1082.6
125°	1146.2	1207.6	1262.2	1300.9	1321.4	1332.7	1321.4	1300.9	1262.2	1207.6	1146.2
127.5°	1201.7	1268.1	1318.2	1353.2	1373.2	1382.3	1373.2	1353.2	1318.2	1268.1	1201.7
130°	1232.7	1300.9	1350.9	1389.6	1407.8	1416.9	1407.8	1389.6	1350.9	1300.9	1232.7
132.5°	1256.3	1328.2	1380.0	1415.1	1435.1	1444.2	1435.1	1415.1	1380.0	1328.2	1256.3
135°	1285.0	1360.0	1414.6	1448.7	1466.9	1476.0	1466.9	1448.7	1414.6	1360.0	1285.0
137.5°	1310.0	1378.2	1435.1	1471.0	1487.4	1493.3	1487.4	1471.0	1435.1	1378.2	1310.0
140°	1328.2	1387.3	1444.2	1478.3	1496.5	1498.7	1496.5	1478.3	1444.2	1387.3	1328.2
142.5°	1351.8	1398.2	1447.8	1481.9	1500.1	1504.2	1500.1	1481.9	1447.8	1398.2	1351.8
145°	1394.1	1421.4	1455.5	1487.4	1503.3	1507.8	1503.3	1487.4	1455.5	1421.4	1394.1
147.5°	1447.3	1456.0	1473.7	1494.6	1510.1	1513.3	1510.1	1494.6	1473.7	1456.0	1447.3
150°	1487.4	1485.1	1491.9	1505.6	1519.2	1516.9	1519.2	1505.6	1491.9	1485.1	1487.4
152.5°	1532.9	1519.7	1519.2	1525.6	1531.9	1531.5	1531.9	1525.6	1519.2	1519.7	1532.9
155°	1610.2	1585.2	1571.5	1567.0	1567.0	1564.7	1567.0	1567.0	1571.5	1585.2	1610.2
157.5°	1695.2	1660.2	1639.7	1628.8	1625.6	1620.6	1625.6	1628.8	1639.7	1660.2	1695.2
160°	1753.5	1714.8	1694.3	1676.1	1669.3	1662.5	1669.3	1676.1	1694.3	1714.8	1753.5
162.5°	1808.0	1771.2	1748.9	1732.5	1725.7	1715.3	1725.7	1732.5	1748.9	1771.2	1808.0
165°	1896.7	1858.1	1833.1	1819.4	1810.3	1801.2	1810.3	1819.4	1833.1	1858.1	1896.7
167.5°	1985.4	1943.1	1926.8	1911.3	1902.7	1886.3	1902.7	1911.3	1926.8	1943.1	1985.4
170°	2040.0	2001.4	1992.3	1978.6	1962.7	1944.5	1962.7	1978.6	1992.3	2001.4	2040.0
172.5°	2087.3	2061.4	2052.3	2038.7	2033.7	2019.1	2033.7	2038.7	2052.3	2061.4	2087.3
175°	2156.0	2135.5	2135.5	2133.3	2126.4	2112.8	2126.4	2133.3	2135.5	2135.5	2156.0
177.5°	2213.3	2202.4	2209.7	2209.7	2207.9	2195.1	2207.9	2209.7	2209.7	2202.4	2213.3
180°	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5



TEST NUMBER: P1428149

CATALOG NUMBER: SQ2W-PP3-K-150U-125D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2583.1	2583.1	2583.1	2583.1
2.5°	2592.6	2596.5	2580.0	2563.5
5°	2591.3	2594.3	2573.7	2553.1
7.5°	2582.8	2585.5	2564.4	2543.2
10°	2570.4	2573.1	2554.9	2536.7
12.5°	2549.3	2551.5	2534.3	2517.0
15°	2513.9	2513.6	2497.9	2482.1
17.5°	2477.4	2472.9	2453.7	2434.6
20°	2451.1	2443.6	2420.5	2397.4
22.5°	2422.0	2412.0	2385.1	2358.1
25°	2372.0	2352.5	2325.8	2299.1
27.5°	2316.6	2283.2	2256.8	2230.3
30°	2273.7	2235.4	2209.9	2184.5
32.5°	2221.2	2180.6	2154.1	2127.7
35°	2135.3	2088.0	2062.5	2037.0
37.5°	2043.6	1990.5	1961.6	1932.7
40°	1982.4	1929.3	1891.7	1854.1
42.5°	1916.9	1874.2	1825.9	1777.6
45°	1800.4	1774.3	1717.2	1660.2
47.5°	1640.5	1647.7	1591.4	1535.1
50°	1518.2	1556.7	1503.3	1449.9
52.5°	1390.8	1449.0	1401.4	1353.8
55°	1206.0	1269.7	1236.9	1204.2
57.5°	1020.0	1070.1	1047.0	1024.0
60°	894.7	940.2	922.0	903.8
62.5°	779.7	827.1	810.9	794.6
65°	626.2	676.0	660.2	644.4
67.5°	500.4	547.3	530.0	512.8
70°	426.9	470.6	452.4	434.2
72.5°	365.0	403.1	385.9	368.6
75°	277.6	305.2	291.9	278.5
77.5°	201.0	219.1	210.6	202.1
80°	152.9	165.7	162.0	158.4
82.5°	109.2	116.6	117.8	119.1
85°	55.5	57.9	60.4	62.8
87.5°	24.2	24.7	22.8	21.0
90°	40.9	25.0	15.9	6.8
92.5°	88.2	61.4	43.2	25.0
95°	177.4	141.0	100.1	70.5
97.5°	282.5	223.8	183.3	134.6
100°	338.9	282.0	243.3	191.0
102.5°	400.7	353.0	299.7	247.4
105°	511.7	452.6	391.2	332.0
107.5°	614.5	549.5	475.8	422.6
110°	680.0	609.5	532.2	484.4



TEST NUMBER: P1428149

CATALOG NUMBER: SQ2W-PP3-K-150U-125D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	743.7	671.4	592.2	544.5
115°	830.1	750.5	677.7	636.8
117.5°	913.3	831.5	754.6	722.3
120°	964.3	882.4	807.4	782.3
122.5°	1006.1	926.1	856.5	846.0
125°	1068.9	987.0	927.9	941.5
127.5°	1119.9	1044.8	1007.5	1038.0
130°	1150.8	1084.8	1062.1	1105.3
132.5°	1178.1	1126.7	1116.7	1176.3
135°	1219.0	1189.4	1198.5	1280.4
137.5°	1267.7	1256.3	1286.8	1390.0
140°	1298.6	1305.4	1348.6	1464.6
142.5°	1340.5	1356.4	1412.3	1535.6
145°	1405.5	1439.6	1512.4	1635.2
147.5°	1479.2	1523.3	1613.4	1739.4
150°	1528.3	1585.2	1680.7	1801.2
152.5°	1584.7	1643.4	1738.9	1861.3
155°	1671.6	1737.5	1837.6	1942.2
157.5°	1760.3	1827.6	1923.1	2014.5
160°	1814.9	1887.6	1974.1	2058.2
162.5°	1876.7	1944.0	2019.6	2094.6
165°	1967.2	2021.8	2083.2	2146.9
167.5°	2043.2	2088.7	2136.9	2186.5
170°	2092.3	2128.7	2169.7	2208.3
172.5°	2134.2	2163.3	2193.3	2226.5
175°	2190.1	2206.0	2224.2	2244.7
177.5°	2233.3	2238.8	2244.2	2253.3
180°	2251.5	2251.5	2251.5	2251.5



TEST NUMBER: P1428149
 CATALOG NUMBER: SQ2W-PP3-K-150U-125D-L830-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.39	21.22	21.36	22.20	23.47	16.16	16.99	17.13	17.97	19.24
	3H	21.45	22.19	22.43	23.18	24.48	17.47	18.21	18.45	19.20	20.50
	4H	21.82	22.52	22.81	23.51	24.81	18.03	18.73	19.02	19.71	21.02
	6H	22.01	22.65	23.01	23.65	24.97	18.39	19.03	19.39	20.03	21.35
	8H	22.07	22.68	23.08	23.69	25.01	18.52	19.13	19.52	20.14	21.46
	12H	22.09	22.67	23.10	23.68	25.02	18.55	19.13	19.56	20.14	21.48
4H	2H	20.51	21.21	21.51	22.20	23.50	17.07	17.77	18.07	18.76	20.06
	3H	21.80	22.38	22.80	23.40	24.72	18.49	19.07	19.50	20.09	21.41
	4H	22.31	22.83	23.32	23.85	25.19	19.11	19.64	20.12	20.65	21.99
	6H	22.62	23.07	23.64	24.11	25.45	19.55	20.01	20.58	21.04	22.38
	8H	22.73	23.15	23.75	24.18	25.54	19.72	20.15	20.75	21.17	22.53
	12H	22.77	23.15	23.82	24.20	25.56	19.77	20.15	20.81	21.20	22.56
8H	4H	22.32	22.75	23.35	23.77	25.13	19.42	19.84	20.44	20.87	22.22
	6H	22.73	23.08	23.78	24.15	25.51	19.97	20.32	21.02	21.39	22.75
	8H	22.91	23.22	23.97	24.28	25.65	20.22	20.53	21.28	21.59	22.96
	12H	23.01	23.28	24.07	24.33	25.75	20.32	20.59	21.38	21.64	23.06
12H	4H	22.28	22.66	23.32	23.71	25.07	19.43	19.81	20.47	20.85	22.21
	6H	22.73	23.04	23.78	24.09	25.46	20.04	20.35	21.10	21.40	22.78
	8H	22.92	23.19	23.98	24.24	25.66	20.31	20.59	21.37	21.63	23.05