

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428173

Luminaire Tested: SQ2W-PR1-0U-125D-L830-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1428173  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-PR1-0U-125D-L830-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - PERCEIVE RIPPLE LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT N/A - DIRECT ONLY  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6444.4 lumens  
Efficiency: N/A  
Efficacy: 131.0 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 49.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1428173

CATALOG NUMBER: SQ2W-PR1-0U-125D-L830-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1428173

CATALOG NUMBER: SQ2W-PR1-0U-125D-L830-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	101	97	100	97	94	96	94	92	92	90	89				87	
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	80	77				75	
3	93	84	77	71	91	82	76	70	80	74	69	77	72	68	74	70	67				65	
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58				56	
5	80	68	60	53	78	67	59	53	65	58	53	63	57	52	61	56	52				50	
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46				44	
7	69	56	48	42	67	55	47	42	54	47	42	52	46	41	51	45	41				39	
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37				35	
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34				32	
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31				29	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	43249	43249	43249	43249
5°	43192	43990	43192	43990
10°	43647	45438	43647	45438
15°	43633	44226	43633	44226
20°	42929	45038	42929	45038
25°	42807	46893	42807	46893
30°	42762	47343	42762	47343
35°	42357	44078	42357	44078
40°	41380	38789	41380	38789
45°	39154	30674	39154	30674
50°	35597	23799	35597	23799
55°	31282	18525	31282	18525
60°	27070	15254	27070	15254
65°	23365	13352	23365	13352
70°	21012	11858	21012	11858
75°	19251	10904	19251	10904
80°	16755	10665	16755	10665
85°	12134	5057	12134	5057

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 20°  
 Vertical Angle: 45°  
 Luminance: 42036 cd/sqm



TEST NUMBER: P1428173

CATALOG NUMBER: SQ2W-PR1-0U-125D-L830-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	258.7	4.0
10°-20°	748.9	11.6
20°-30°	1157.6	18.0
30°-40°	1392.1	21.6
40°-50°	1250.1	19.4
50°-60°	837.6	13.0
60°-70°	487.3	7.6
70°-80°	250.3	3.9
80°-90°	61.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2165.2	33.6
0°-40°	3557.3	55.2
0°-60°	5645.1	87.6
0°-90°	6444.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6444.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2679	2679	2679	2679	2679	
5°	2665	2714	2665	2714	2665	254
15°	2610	2646	2610	2646	2610	733
25°	2403	2632	2403	2632	2403	1108
35°	2149	2236	2149	2236	2149	1340
45°	1715	1343	1715	1343	1715	1312
55°	1111	658	1111	658	1111	999
65°	612	350	612	350	612	619
75°	309	175	309	175	309	327
85°	66	27	66	27	66	84
90°	0	0	0	0	0	



TEST NUMBER: P1428173

CATALOG NUMBER: SQ2W-PR1-0U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2678.7	2678.7	2678.7	2678.7	2678.7	2678.7	2678.7	2678.7	2678.7	2678.7	2678.7
2.5°	2667.8	2682.3	2696.9	2690.3	2676.7	2670.4	2671.4	2672.9	2675.8	2678.7	2675.8
5°	2665.0	2685.7	2706.3	2701.4	2688.1	2682.6	2685.1	2689.9	2702.0	2714.2	2702.0
7.5°	2664.5	2693.9	2723.2	2725.5	2718.7	2718.8	2725.8	2735.1	2751.1	2767.2	2751.1
10°	2662.3	2697.5	2732.7	2737.8	2733.0	2731.2	2732.4	2737.5	2754.5	2771.5	2754.5
12.5°	2649.2	2690.2	2731.2	2726.9	2707.5	2697.0	2695.3	2696.3	2705.5	2714.7	2705.5
15°	2610.4	2659.0	2707.5	2687.8	2645.3	2625.9	2629.5	2633.8	2639.9	2645.9	2639.9
17.5°	2542.2	2592.9	2643.6	2625.9	2585.4	2571.6	2584.8	2597.6	2609.5	2621.3	2609.5
20°	2498.5	2548.2	2598.0	2585.8	2553.1	2545.2	2562.2	2580.1	2600.7	2621.3	2600.7
22.5°	2459.1	2508.9	2558.7	2550.9	2524.0	2522.4	2546.2	2571.1	2599.5	2627.9	2599.5
25°	2402.9	2446.6	2490.3	2491.2	2477.8	2491.2	2531.2	2569.2	2600.7	2632.3	2600.7
27.5°	2343.9	2369.6	2395.4	2412.4	2426.4	2460.5	2514.7	2560.8	2582.9	2605.0	2582.9
30°	2293.7	2310.7	2327.7	2359.2	2395.6	2437.5	2484.8	2522.4	2530.9	2539.4	2530.9
32.5°	2239.1	2249.3	2259.5	2303.9	2359.7	2400.1	2425.1	2441.1	2430.2	2419.3	2430.2
35°	2149.0	2157.5	2165.9	2222.7	2295.5	2322.2	2302.8	2282.5	2259.4	2236.3	2259.4
37.5°	2041.9	2059.4	2076.9	2123.1	2178.9	2178.4	2121.7	2072.4	2046.0	2019.5	2046.0
40°	1963.3	1992.4	2021.5	2052.5	2084.0	2057.3	1972.4	1901.1	1870.7	1840.4	1870.7
42.5°	1867.2	1913.8	1960.4	1967.3	1961.0	1903.7	1795.4	1705.0	1667.8	1630.7	1667.8
45°	1714.8	1777.9	1841.0	1804.9	1735.7	1642.3	1524.6	1426.0	1384.7	1343.4	1384.7
47.5°	1535.1	1599.9	1664.7	1596.7	1484.3	1375.5	1270.4	1182.0	1143.4	1104.8	1143.4
50°	1417.2	1469.3	1521.5	1444.5	1324.3	1215.1	1116.8	1032.5	990.0	947.5	990.0
52.5°	1297.0	1334.6	1372.3	1295.9	1181.6	1075.3	977.0	893.6	855.0	816.4	855.0
55°	1111.3	1130.8	1150.2	1079.5	978.8	881.7	788.2	711.5	684.8	658.1	684.8
57.5°	941.0	953.3	965.7	898.7	805.3	718.9	639.5	575.1	555.4	535.7	555.4
60°	838.3	846.8	855.3	787.3	693.9	616.2	554.3	503.9	488.2	472.4	488.2
62.5°	744.4	750.9	757.5	691.9	602.4	532.9	483.7	443.7	431.9	420.0	431.9
65°	611.6	617.7	623.8	568.0	491.5	434.5	396.8	366.5	358.0	349.5	358.0
67.5°	506.2	509.4	512.6	466.6	404.2	358.2	328.6	304.4	296.4	288.3	296.4
70°	445.1	446.3	447.5	406.9	352.2	311.6	284.9	263.3	257.3	251.2	257.3
72.5°	390.5	388.8	387.1	350.8	303.0	268.1	246.3	228.9	224.8	220.6	224.8
75°	308.6	304.9	301.3	271.2	232.4	205.7	191.1	179.6	177.2	174.8	177.2
77.5°	230.5	226.6	222.7	197.7	165.7	147.2	142.4	138.7	138.7	138.7	138.7
80°	180.2	175.4	170.5	151.1	126.8	114.7	114.7	114.7	114.7	114.7	114.7
82.5°	134.3	127.5	120.8	108.9	95.3	88.5	88.5	88.2	87.3	86.3	87.3
85°	65.5	59.5	53.4	51.9	51.9	48.2	41.0	34.6	30.9	27.3	30.9
87.5°	17.5	17.5	17.5	13.8	9.0	6.6	6.6	6.6	6.6	6.6	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428173

CATALOG NUMBER: SQ2W-PR1-0U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2678.7	2678.7	2678.7	2678.7	2678.7	2678.7	2678.7	2678.7	2678.7	2678.7	2678.7
2.5°	2672.9	2671.4	2670.4	2676.7	2690.3	2696.9	2682.3	2667.8	2682.3	2696.9	2690.3
5°	2689.9	2685.1	2682.6	2688.1	2701.4	2706.3	2685.7	2665.0	2685.7	2706.3	2701.4
7.5°	2735.1	2725.8	2718.8	2718.7	2725.5	2723.2	2693.9	2664.5	2693.9	2723.2	2725.5
10°	2737.5	2732.4	2731.2	2733.0	2737.8	2732.7	2697.5	2662.3	2697.5	2732.7	2737.8
12.5°	2696.3	2695.3	2697.0	2707.5	2726.9	2731.2	2690.2	2649.2	2690.2	2731.2	2726.9
15°	2633.8	2629.5	2625.9	2645.3	2687.8	2707.5	2659.0	2610.4	2659.0	2707.5	2687.8
17.5°	2597.6	2584.8	2571.6	2585.4	2625.9	2643.6	2592.9	2542.2	2592.9	2643.6	2625.9
20°	2580.1	2562.2	2545.2	2553.1	2585.8	2598.0	2548.2	2498.5	2548.2	2598.0	2585.8
22.5°	2571.1	2546.2	2522.4	2524.0	2550.9	2558.7	2508.9	2459.1	2508.9	2558.7	2550.9
25°	2569.2	2531.2	2491.2	2477.8	2491.2	2490.3	2446.6	2402.9	2446.6	2490.3	2491.2
27.5°	2560.8	2514.7	2460.5	2426.4	2412.4	2395.4	2369.6	2343.9	2369.6	2395.4	2412.4
30°	2522.4	2484.8	2437.5	2395.6	2359.2	2327.7	2310.7	2293.7	2310.7	2327.7	2359.2
32.5°	2441.1	2425.1	2400.1	2359.7	2303.9	2259.5	2249.3	2239.1	2249.3	2259.5	2303.9
35°	2282.5	2302.8	2322.2	2295.5	2222.7	2165.9	2157.5	2149.0	2157.5	2165.9	2222.7
37.5°	2072.4	2121.7	2178.4	2178.9	2123.1	2076.9	2059.4	2041.9	2059.4	2076.9	2123.1
40°	1901.1	1972.4	2057.3	2084.0	2052.5	2021.5	1992.4	1963.3	1992.4	2021.5	2052.5
42.5°	1705.0	1795.4	1903.7	1961.0	1967.3	1960.4	1913.8	1867.2	1913.8	1960.4	1967.3
45°	1426.0	1524.6	1642.3	1735.7	1804.9	1841.0	1777.9	1714.8	1777.9	1841.0	1804.9
47.5°	1182.0	1270.4	1375.5	1484.3	1596.7	1664.7	1599.9	1535.1	1599.9	1664.7	1596.7
50°	1032.5	1116.8	1215.1	1324.3	1444.5	1521.5	1469.3	1417.2	1469.3	1521.5	1444.5
52.5°	893.6	977.0	1075.3	1181.6	1295.9	1372.3	1334.6	1297.0	1334.6	1372.3	1295.9
55°	711.5	788.2	881.7	978.8	1079.5	1150.2	1130.8	1111.3	1130.8	1150.2	1079.5
57.5°	575.1	639.5	718.9	805.3	898.7	965.7	953.3	941.0	953.3	965.7	898.7
60°	503.9	554.3	616.2	693.9	787.3	855.3	846.8	838.3	846.8	855.3	787.3
62.5°	443.7	483.7	532.9	602.4	691.9	757.5	750.9	744.4	750.9	757.5	691.9
65°	366.5	396.8	434.5	491.5	568.0	623.8	617.7	611.6	617.7	623.8	568.0
67.5°	304.4	328.6	358.2	404.2	466.6	512.6	509.4	506.2	509.4	512.6	466.6
70°	263.3	284.9	311.6	352.2	406.9	447.5	446.3	445.1	446.3	447.5	406.9
72.5°	228.9	246.3	268.1	303.0	350.8	387.1	388.8	390.5	388.8	387.1	350.8
75°	179.6	191.1	205.7	232.4	271.2	301.3	304.9	308.6	304.9	301.3	271.2
77.5°	138.7	142.4	147.2	165.7	197.7	222.7	226.6	230.5	226.6	222.7	197.7
80°	114.7	114.7	114.7	126.8	151.1	170.5	175.4	180.2	175.4	170.5	151.1
82.5°	88.2	88.5	88.5	95.3	108.9	120.8	127.5	134.3	127.5	120.8	108.9
85°	34.6	41.0	48.2	51.9	51.9	53.4	59.5	65.5	59.5	53.4	51.9
87.5°	6.6	6.6	6.6	9.0	13.8	17.5	17.5	17.5	17.5	17.5	13.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428173

CATALOG NUMBER: SQ2W-PR1-0U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2678.7	2678.7	2678.7	2678.7	2678.7	2678.7	2678.7	2678.7	2678.7	2678.7	2678.7
2.5°	2676.7	2670.4	2671.4	2672.9	2675.8	2678.7	2675.8	2672.9	2671.4	2670.4	2676.7
5°	2688.1	2682.6	2685.1	2689.9	2702.0	2714.2	2702.0	2689.9	2685.1	2682.6	2688.1
7.5°	2718.7	2718.8	2725.8	2735.1	2751.1	2767.2	2751.1	2735.1	2725.8	2718.8	2718.7
10°	2733.0	2731.2	2732.4	2737.5	2754.5	2771.5	2754.5	2737.5	2732.4	2731.2	2733.0
12.5°	2707.5	2697.0	2695.3	2696.3	2705.5	2714.7	2705.5	2696.3	2695.3	2697.0	2707.5
15°	2645.3	2625.9	2629.5	2633.8	2639.9	2645.9	2639.9	2633.8	2629.5	2625.9	2645.3
17.5°	2585.4	2571.6	2584.8	2597.6	2609.5	2621.3	2609.5	2597.6	2584.8	2571.6	2585.4
20°	2553.1	2545.2	2562.2	2580.1	2600.7	2621.3	2600.7	2580.1	2562.2	2545.2	2553.1
22.5°	2524.0	2522.4	2546.2	2571.1	2599.5	2627.9	2599.5	2571.1	2546.2	2522.4	2524.0
25°	2477.8	2491.2	2531.2	2569.2	2600.7	2632.3	2600.7	2569.2	2531.2	2491.2	2477.8
27.5°	2426.4	2460.5	2514.7	2560.8	2582.9	2605.0	2582.9	2560.8	2514.7	2460.5	2426.4
30°	2395.6	2437.5	2484.8	2522.4	2530.9	2539.4	2530.9	2522.4	2484.8	2437.5	2395.6
32.5°	2359.7	2400.1	2425.1	2441.1	2430.2	2419.3	2430.2	2441.1	2425.1	2400.1	2359.7
35°	2295.5	2322.2	2302.8	2282.5	2259.4	2236.3	2259.4	2282.5	2302.8	2322.2	2295.5
37.5°	2178.9	2178.4	2121.7	2072.4	2046.0	2019.5	2046.0	2072.4	2121.7	2178.4	2178.9
40°	2084.0	2057.3	1972.4	1901.1	1870.7	1840.4	1870.7	1901.1	1972.4	2057.3	2084.0
42.5°	1961.0	1903.7	1795.4	1705.0	1667.8	1630.7	1667.8	1705.0	1795.4	1903.7	1961.0
45°	1735.7	1642.3	1524.6	1426.0	1384.7	1343.4	1384.7	1426.0	1524.6	1642.3	1735.7
47.5°	1484.3	1375.5	1270.4	1182.0	1143.4	1104.8	1143.4	1182.0	1270.4	1375.5	1484.3
50°	1324.3	1215.1	1116.8	1032.5	990.0	947.5	990.0	1032.5	1116.8	1215.1	1324.3
52.5°	1181.6	1075.3	977.0	893.6	855.0	816.4	855.0	893.6	977.0	1075.3	1181.6
55°	978.8	881.7	788.2	711.5	684.8	658.1	684.8	711.5	788.2	881.7	978.8
57.5°	805.3	718.9	639.5	575.1	555.4	535.7	555.4	575.1	639.5	718.9	805.3
60°	693.9	616.2	554.3	503.9	488.2	472.4	488.2	503.9	554.3	616.2	693.9
62.5°	602.4	532.9	483.7	443.7	431.9	420.0	431.9	443.7	483.7	532.9	602.4
65°	491.5	434.5	396.8	366.5	358.0	349.5	358.0	366.5	396.8	434.5	491.5
67.5°	404.2	358.2	328.6	304.4	296.4	288.3	296.4	304.4	328.6	358.2	404.2
70°	352.2	311.6	284.9	263.3	257.3	251.2	257.3	263.3	284.9	311.6	352.2
72.5°	303.0	268.1	246.3	228.9	224.8	220.6	224.8	228.9	246.3	268.1	303.0
75°	232.4	205.7	191.1	179.6	177.2	174.8	177.2	179.6	191.1	205.7	232.4
77.5°	165.7	147.2	142.4	138.7	138.7	138.7	138.7	138.7	142.4	147.2	165.7
80°	126.8	114.7	114.7	114.7	114.7	114.7	114.7	114.7	114.7	114.7	126.8
82.5°	95.3	88.5	88.5	88.2	87.3	86.3	87.3	88.2	88.5	88.5	95.3
85°	51.9	48.2	41.0	34.6	30.9	27.3	30.9	41.0	48.2	48.2	51.9
87.5°	9.0	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	9.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428173

CATALOG NUMBER: SQ2W-PR1-0U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	2678.7	2678.7	2678.7	2678.7
2.5°	2690.3	2696.9	2682.3	2667.8
5°	2701.4	2706.3	2685.7	2665.0
7.5°	2725.5	2723.2	2693.9	2664.5
10°	2737.8	2732.7	2697.5	2662.3
12.5°	2726.9	2731.2	2690.2	2649.2
15°	2687.8	2707.5	2659.0	2610.4
17.5°	2625.9	2643.6	2592.9	2542.2
20°	2585.8	2598.0	2548.2	2498.5
22.5°	2550.9	2558.7	2508.9	2459.1
25°	2491.2	2490.3	2446.6	2402.9
27.5°	2412.4	2395.4	2369.6	2343.9
30°	2359.2	2327.7	2310.7	2293.7
32.5°	2303.9	2259.5	2249.3	2239.1
35°	2222.7	2165.9	2157.5	2149.0
37.5°	2123.1	2076.9	2059.4	2041.9
40°	2052.5	2021.5	1992.4	1963.3
42.5°	1967.3	1960.4	1913.8	1867.2
45°	1804.9	1841.0	1777.9	1714.8
47.5°	1596.7	1664.7	1599.9	1535.1
50°	1444.5	1521.5	1469.3	1417.2
52.5°	1295.9	1372.3	1334.6	1297.0
55°	1079.5	1150.2	1130.8	1111.3
57.5°	898.7	965.7	953.3	941.0
60°	787.3	855.3	846.8	838.3
62.5°	691.9	757.5	750.9	744.4
65°	568.0	623.8	617.7	611.6
67.5°	466.6	512.6	509.4	506.2
70°	406.9	447.5	446.3	445.1
72.5°	350.8	387.1	388.8	390.5
75°	271.2	301.3	304.9	308.6
77.5°	197.7	222.7	226.6	230.5
80°	151.1	170.5	175.4	180.2
82.5°	108.9	120.8	127.5	134.3
85°	51.9	53.4	59.5	65.5
87.5°	13.8	17.5	17.5	17.5
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P1428173  
 CATALOG NUMBER: SQ2W-PR1-0U-125D-L830-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	23.69	25.18	24.05	25.49	25.81	20.06	21.55	20.42	21.86	22.18
	3H	24.94	26.28	25.32	26.60	26.97	21.26	22.60	21.64	22.93	23.29
	4H	25.45	26.71	25.85	27.05	27.43	21.76	23.01	22.16	23.36	23.74
	6H	25.78	26.94	26.19	27.30	27.70	22.13	23.28	22.54	23.65	24.04
	8H	25.90	27.00	26.33	27.39	27.79	22.28	23.38	22.71	23.77	24.17
	12H	25.96	27.01	26.39	27.39	27.82	22.33	23.38	22.76	23.77	24.20
4H	2H	23.86	25.12	24.26	25.47	25.84	20.84	22.09	21.24	22.44	22.82
	3H	25.38	26.41	25.79	26.82	27.22	22.25	23.29	22.66	23.69	24.09
	4H	26.03	26.96	26.47	27.38	27.82	22.82	23.75	23.25	24.17	24.61
	6H	26.50	27.30	26.95	27.75	28.21	23.29	24.09	23.74	24.54	25.00
	8H	26.67	27.42	27.13	27.86	28.33	23.48	24.23	23.94	24.68	25.15
	12H	26.76	27.43	27.24	27.91	28.38	23.55	24.23	24.04	24.71	25.18
8H	4H	26.10	26.85	26.56	27.30	27.77	23.19	23.94	23.66	24.39	24.86
	6H	26.65	27.27	27.15	27.77	28.24	23.75	24.37	24.25	24.87	25.34
	8H	26.89	27.45	27.40	27.96	28.45	24.01	24.57	24.53	25.08	25.57
	12H	27.03	27.53	27.54	28.02	28.59	24.13	24.63	24.64	25.12	25.69
12H	4H	26.09	26.76	26.57	27.24	27.71	23.24	23.91	23.72	24.39	24.86
	6H	26.64	27.20	27.16	27.71	28.20	23.82	24.38	24.34	24.89	25.38
	8H	26.92	27.41	27.43	27.91	28.47	24.14	24.63	24.65	25.13	25.69