

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938407

Luminaire Tested: SQ4-FB-150U-075D-B50-1D-UNV-W2A-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938407
REPORT IS A COMBINATION OF REPORTS P933638 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-075D-B50-1D-UNV-W2A-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11816.0 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 95.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938407

CATALOG NUMBER: SQ4-FB-150U-075D-B50-1D-UNV-W2A-W-6

Luminous Intensity Polar Plot



TEST NUMBER: P938407

CATALOG NUMBER: SQ4-FB-150U-075D-B50-1D-UNV-W2A-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	88	84	81	83	79	76	73	62	60	58	46	45	43	32	31	30
2	84	77	71	66	75	69	64	59	54	50	47	40	38	36	27	26	25
3	76	67	60	54	68	60	54	49	47	43	39	35	32	30	24	22	21
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	21	19	17
5	64	52	44	38	57	47	40	35	37	32	28	28	24	21	19	17	15
6	58	47	39	33	52	42	35	30	33	28	24	25	21	18	17	15	13
7	54	42	34	28	48	38	31	26	30	25	21	22	19	16	15	13	11
8	50	38	30	25	44	34	27	23	27	22	18	20	17	14	14	12	10
9	46	34	27	22	41	31	24	20	24	20	16	18	15	12	13	10	9
10	43	31	24	19	38	28	22	18	22	18	14	17	13	11	12	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2695	2695	2695
5°	2632	3115	3623
10°	2387	4539	6006
15°	2028	5929	7253
20°	1650	6869	7392
25°	1376	7186	7242
30°	1160	7230	7228
35°	1025	7108	7415
40°	893	6949	7609
45°	808	6833	7638
50°	741	6728	7512
55°	708	6575	7178
60°	724	6283	6652
65°	752	5841	5930
70°	799	5090	5010
75°	882	4147	3910
80°	957	2872	2635
85°	835	1522	1349

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 7638 cd/sqm

TEST NUMBER: P938407

CATALOG NUMBER: SQ4-FB-150U-075D-B50-1D-UNV-W2A-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.4	0.5
10°-20°	249.8	2.1
20°-30°	437.0	3.7
30°-40°	562.5	4.8
40°-50°	628.3	5.3
50°-60°	601.7	5.1
60°-70°	476.9	4.0
70°-80°	280.4	2.4
80°-90°	82.9	0.7
90°-100°	634.7	5.4
100°-110°	1668.5	14.1
110°-120°	1730.1	14.6
120°-130°	1387.7	11.7
130°-140°	1088.9	9.2
140°-150°	835.8	7.1
150°-160°	601.9	5.1
160°-170°	368.3	3.1
170°-180°	124.4	1.1
0°-30°	743.1	6.3
0°-40°	1305.6	11.0
0°-60°	2535.6	21.5
0°-90°	3375.7	28.6
90°-120°	4033.3	34.1
90°-150°	7345.7	62.2
90°-180°	8440.0	71.4
0°-180°	11816.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	436	436	436	436	436	
5°	424	455	513	580	601	39
15°	318	587	989	1199	1237	89
25°	203	666	1178	1230	1232	94
35°	137	636	1110	1173	1219	86
45°	94	507	981	1124	1174	73
55°	67	322	832	967	993	61
65°	53	171	618	695	705	53
75°	39	105	339	373	374	41
85°	14	32	84	92	94	15
90°	9	24	66	33	33	8
95°	84	329	1093	564	384	93
105°	301	455	1845	2801	2613	319
115°	534	648	1478	2947	3364	527
125°	743	833	1344	2271	2679	659
135°	885	974	1302	1833	2079	685
145°	1027	1092	1285	1564	1686	643
155°	1160	1193	1285	1411	1452	533
165°	1252	1269	1285	1336	1353	353
175°	1302	1302	1294	1311	1311	124
180°	1302	1302	1302	1302	1302	

TEST NUMBER: P938407

CATALOG NUMBER: SQ4-FB-150U-075D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	435.7	435.7	435.7	435.7	435.7	435.7	435.7	435.7	435.7	435.7	435.7
2.5°	435.7	435.7	438.5	439.9	442.7	444.1	446.9	449.7	458.1	459.5	462.3
5°	424.5	430.1	448.3	455.3	474.9	501.6	512.8	531.0	568.8	580.0	587.0
7.5°	407.7	420.3	465.1	476.3	525.4	595.4	624.8	664.1	724.3	753.7	777.6
10°	381.1	407.7	487.5	514.2	594.0	700.5	755.1	809.8	900.8	941.5	956.9
12.5°	351.7	395.1	511.4	547.8	662.7	818.2	884.0	944.3	1047.9	1102.7	1111.1
15°	318.0	376.9	533.8	587.0	735.5	916.3	989.1	1063.5	1160.1	1199.3	1209.2
17.5°	288.6	362.9	554.8	610.8	791.6	1004.5	1078.9	1140.5	1219.0	1245.6	1252.6
20°	252.2	340.4	568.8	641.7	850.4	1069.1	1140.5	1188.1	1241.4	1258.2	1261.0
22.5°	225.6	316.6	577.2	652.9	889.6	1108.3	1168.5	1206.4	1242.8	1248.4	1249.8
25°	203.1	290.0	575.8	665.5	923.3	1132.1	1178.3	1206.4	1227.4	1230.2	1230.2
27.5°	182.1	260.6	570.2	668.3	948.5	1137.7	1174.1	1193.7	1203.6	1209.2	1209.2
30°	163.9	232.6	556.2	662.7	959.7	1132.1	1161.5	1171.3	1181.1	1189.5	1193.7
32.5°	149.9	205.9	535.2	651.5	961.1	1118.1	1139.1	1144.7	1158.7	1178.3	1185.3
35°	137.3	179.3	511.4	636.1	952.7	1095.7	1109.7	1115.3	1143.3	1172.7	1182.5
37.5°	124.7	159.7	480.5	609.4	940.1	1069.1	1078.9	1088.7	1132.1	1167.1	1178.3
40°	112.1	142.9	444.1	580.0	920.5	1036.7	1045.1	1060.6	1118.1	1158.7	1169.9
42.5°	102.3	128.9	404.9	549.2	895.2	1000.3	1012.9	1035.3	1101.3	1144.7	1157.3
45°	93.9	114.9	362.9	507.2	863.0	962.5	980.7	1011.5	1081.7	1123.7	1134.9
47.5°	85.5	105.1	319.4	463.7	828.0	924.7	948.5	983.5	1055.0	1095.7	1105.5
50°	78.5	95.3	276.0	417.5	790.2	884.0	912.1	948.5	1021.3	1059.2	1071.9
52.5°	72.9	86.9	235.4	371.3	746.7	842.0	874.2	912.1	980.7	1017.1	1025.5
55°	67.2	79.9	200.3	322.2	701.9	797.2	832.2	868.6	935.9	966.7	972.3
57.5°	64.4	74.3	170.9	276.0	654.3	746.7	786.0	819.6	882.6	906.4	912.1
60°	60.2	70.0	148.5	236.8	602.4	699.1	732.7	766.3	819.6	839.2	843.4
62.5°	56.0	67.2	131.7	198.9	549.2	643.1	676.7	707.5	752.3	766.3	772.0
65°	53.2	64.4	119.1	170.9	494.6	584.2	617.8	644.5	680.9	694.9	697.7
67.5°	50.4	61.6	109.3	147.1	439.9	525.4	550.6	575.8	603.8	617.8	619.2
70°	46.2	58.8	100.9	130.3	383.9	458.1	479.1	505.8	528.2	535.2	539.4
72.5°	43.4	54.6	95.3	117.7	326.4	393.7	413.3	428.7	448.3	455.3	455.3
75°	39.2	49.0	89.7	105.1	267.6	322.2	339.0	354.5	369.9	372.7	368.5
77.5°	35.0	43.4	77.1	88.3	208.7	255.0	269.0	277.4	290.0	292.8	294.2
80°	29.4	37.8	60.2	68.6	151.3	187.7	197.5	204.5	215.8	215.8	218.6
82.5°	22.4	29.4	43.4	49.0	102.3	128.9	137.3	141.5	148.5	148.5	148.5
85°	14.0	18.2	28.0	32.2	61.6	78.5	84.1	85.5	91.1	92.5	92.5
87.5°	7.0	9.8	18.2	19.6	32.2	40.6	40.6	43.4	43.4	42.0	40.6
90°	8.8	15.8	22.7	24.5	38.5	57.1	66.4	59.0	44.3	33.3	33.3
92.5°	34.9	94.3	153.8	168.7	237.1	328.4	374.0	327.7	235.4	166.1	159.4
95°	83.9	192.6	301.4	328.6	583.5	923.3	1093.2	975.5	740.1	563.6	543.6
97.5°	145.1	241.0	336.9	360.9	785.9	1352.5	1635.8	1561.5	1412.7	1301.2	1263.0
100°	192.2	279.3	366.2	388.0	859.6	1488.3	1802.7	1808.1	1819.1	1827.2	1781.9
102.5°	232.5	313.6	394.8	415.1	893.4	1531.0	1849.9	1944.6	2134.1	2276.3	2237.4
105°	300.6	369.3	438.0	455.2	918.4	1535.9	1844.6	2057.0	2481.9	2800.6	2779.7
107.5°	370.5	434.6	498.7	514.6	923.0	1467.5	1739.8	2036.1	2628.7	3073.2	3078.3
110°	417.7	475.6	533.4	547.9	916.1	1406.9	1652.3	1983.6	2646.2	3143.1	3164.9

TEST NUMBER: P938407

CATALOG NUMBER: SQ4-FB-150U-075D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	464.0	519.1	574.2	588.0	916.3	1354.0	1572.9	1911.9	2590.0	3098.5	3132.0
115°	533.9	584.8	635.7	648.4	924.8	1293.3	1477.6	1804.2	2457.4	2947.3	2993.7
117.5°	602.9	649.1	695.4	706.9	942.0	1255.4	1412.1	1706.9	2296.3	2738.5	2789.9
120°	643.2	686.7	730.2	741.0	955.9	1242.6	1385.9	1655.2	2193.9	2597.8	2647.7
122.5°	682.5	726.4	770.3	781.2	976.0	1235.9	1365.8	1608.3	2093.4	2457.2	2506.4
125°	742.7	782.7	822.8	832.8	1003.1	1230.4	1343.9	1550.0	1962.0	2271.0	2316.3
127.5°	791.7	832.0	872.4	882.5	1030.2	1227.1	1325.5	1502.4	1856.2	2121.6	2159.9
130°	817.9	861.4	905.0	915.8	1050.1	1229.1	1318.6	1476.1	1791.0	2027.2	2062.6
132.5°	845.0	888.5	932.0	942.9	1066.1	1230.4	1312.5	1453.4	1735.4	1946.8	1978.5
135°	885.2	924.8	964.4	974.3	1083.5	1229.1	1302.0	1420.1	1656.2	1833.3	1860.5
137.5°	926.2	965.5	1004.7	1014.5	1109.8	1236.7	1300.2	1400.1	1599.7	1749.4	1771.7
140°	960.3	996.5	1032.5	1041.6	1125.8	1238.0	1294.2	1380.4	1552.8	1682.1	1703.0
142.5°	986.5	1019.9	1053.4	1061.7	1139.2	1242.5	1294.2	1369.9	1521.3	1634.9	1652.8
145°	1026.7	1055.9	1085.0	1092.3	1156.7	1242.5	1285.4	1347.3	1471.2	1564.2	1577.7
147.5°	1066.9	1095.3	1123.6	1130.7	1182.3	1251.0	1285.4	1334.1	1431.5	1504.7	1516.0
150°	1093.2	1118.7	1144.3	1150.8	1195.6	1255.5	1285.4	1326.6	1408.8	1470.6	1479.7
152.5°	1120.2	1139.7	1159.1	1164.0	1204.4	1258.4	1285.4	1320.5	1390.8	1443.5	1450.4
155°	1160.4	1174.8	1189.2	1192.7	1223.6	1264.8	1285.4	1313.3	1369.2	1411.2	1415.8
157.5°	1190.1	1204.1	1218.1	1221.6	1242.9	1271.2	1285.4	1307.1	1350.7	1383.3	1386.4
160°	1210.3	1221.1	1231.9	1234.7	1251.6	1274.1	1285.4	1304.1	1341.3	1369.2	1371.1
162.5°	1230.4	1238.5	1246.6	1248.7	1260.9	1277.2	1285.4	1301.1	1332.5	1356.2	1357.9
165°	1252.2	1259.6	1266.9	1268.7	1274.3	1281.6	1285.4	1296.7	1319.2	1336.1	1338.0
167.5°	1272.3	1275.8	1279.3	1280.1	1284.8	1291.1	1294.2	1301.5	1316.3	1327.3	1328.1
170°	1285.4	1288.8	1292.4	1293.2	1293.5	1294.0	1294.2	1301.5	1316.3	1327.3	1327.3
172.5°	1292.4	1293.1	1294.0	1294.2	1294.2	1294.2	1294.2	1299.9	1311.6	1320.3	1319.6
175°	1302.0	1302.0	1302.0	1302.0	1299.4	1295.9	1294.2	1297.8	1305.2	1310.7	1310.7
177.5°	1302.0	1302.0	1302.0	1302.0	1299.9	1297.2	1295.8	1298.7	1304.6	1309.0	1308.3
180°	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0

TEST NUMBER: P938407

CATALOG NUMBER: SQ4-FB-150U-075D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	435.7	435.7
2.5°	465.1	462.3
5°	598.2	601.0
7.5°	805.6	804.2
10°	1001.7	1014.3
12.5°	1144.7	1147.5
15°	1231.6	1237.2
17.5°	1265.2	1266.6
20°	1266.6	1263.8
22.5°	1251.2	1248.4
25°	1233.0	1231.6
27.5°	1216.2	1217.6
30°	1209.2	1213.4
32.5°	1209.2	1216.2
35°	1212.0	1219.0
37.5°	1210.6	1219.0
40°	1205.0	1214.8
42.5°	1189.5	1196.5
45°	1165.7	1174.1
47.5°	1134.9	1140.5
50°	1095.7	1101.3
52.5°	1046.5	1047.9
55°	987.7	993.3
57.5°	924.7	926.1
60°	854.6	858.8
62.5°	780.4	780.4
65°	701.9	704.7
67.5°	620.6	627.6
70°	538.0	539.4
72.5°	456.7	456.7
75°	372.7	374.1
77.5°	292.8	292.8
80°	217.2	218.6
82.5°	149.9	152.7
85°	93.9	93.9
87.5°	43.4	39.2
90°	33.3	33.3
92.5°	133.0	106.6
95°	463.5	383.6
97.5°	1110.8	958.6
100°	1600.5	1419.1
102.5°	2082.1	1926.7
105°	2696.2	2612.7
107.5°	3098.5	3118.6
110°	3251.8	3338.9

TEST NUMBER: P938407

CATALOG NUMBER: SQ4-FB-150U-075D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3265.5	3399.1
115°	3178.9	3364.2
117.5°	2995.3	3200.8
120°	2847.4	3047.0
122.5°	2703.3	2900.2
125°	2497.7	2679.1
127.5°	2312.9	2465.9
130°	2204.0	2345.3
132.5°	2105.0	2231.7
135°	1969.7	2078.8
137.5°	1861.1	1950.4
140°	1786.5	1870.0
142.5°	1724.7	1796.5
145°	1632.1	1686.4
147.5°	1561.0	1606.1
150°	1516.3	1552.8
152.5°	1478.0	1505.6
155°	1434.0	1452.3
157.5°	1399.3	1412.1
160°	1378.5	1385.9
162.5°	1364.9	1371.9
165°	1345.2	1352.6
167.5°	1331.2	1334.3
170°	1327.3	1327.3
172.5°	1316.9	1314.2
175°	1310.7	1310.7
177.5°	1305.1	1302.0
180°	1302.0	1302.0

(END OF REPORT)