

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938408

Luminaire Tested: SQ4-FB-150U-075D-B50-1D-UNV-W2A-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938408
REPORT IS A COMBINATION OF REPORTS P933646 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-075D-B50-1D-UNV-W2A-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15754.7 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 127.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938408

CATALOG NUMBER: SQ4-FB-150U-075D-B50-1D-UNV-W2A-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P938408

CATALOG NUMBER: SQ4-FB-150U-075D-B50-1D-UNV-W2A-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	88	84	81	83	79	76	73	62	60	58	46	45	43	32	31	30
2	84	77	71	66	75	69	64	59	54	50	47	40	38	36	27	26	25
3	76	67	60	54	68	60	54	49	47	43	39	35	32	30	24	22	21
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	21	19	17
5	64	52	44	38	57	47	40	35	37	32	28	28	24	21	19	17	15
6	58	47	39	33	52	42	35	30	33	28	24	25	21	18	17	15	13
7	54	42	34	28	48	38	31	26	30	25	21	22	19	16	15	13	11
8	50	38	30	25	44	34	27	23	27	22	18	20	17	14	14	12	10
9	46	34	27	22	41	31	24	20	24	20	16	18	15	12	13	10	9
10	43	31	24	19	38	28	22	18	22	18	14	17	13	11	12	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2695	2695	2695
5°	2633	3115	3623
10°	2388	4541	6007
15°	2030	5933	7253
20°	1652	6875	7392
25°	1379	7195	7242
30°	1163	7241	7228
35°	1028	7120	7415
40°	895	6964	7608
45°	811	6850	7638
50°	744	6747	7511
55°	713	6596	7179
60°	729	6306	6653
65°	759	5866	5930
70°	808	5116	5010
75°	896	4171	3910
80°	978	2893	2634
85°	871	1535	1349

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 7638 cd/sqm

TEST NUMBER: P938408

CATALOG NUMBER: SQ4-FB-150U-075D-B50-1D-UNV-W2A-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.1	0.5
10°-20°	333.1	2.1
20°-30°	582.6	3.7
30°-40°	750.0	4.8
40°-50°	837.7	5.3
50°-60°	802.3	5.1
60°-70°	635.8	4.0
70°-80°	373.9	2.4
80°-90°	110.5	0.7
90°-100°	846.2	5.4
100°-110°	2224.7	14.1
110°-120°	2306.8	14.6
120°-130°	1850.3	11.7
130°-140°	1451.9	9.2
140°-150°	1114.3	7.1
150°-160°	802.5	5.1
160°-170°	491.0	3.1
170°-180°	165.9	1.1
0°-30°	990.8	6.3
0°-40°	1740.8	11.0
0°-60°	3380.8	21.5
0°-90°	4501.0	28.6
90°-120°	5377.7	34.1
90°-150°	9794.2	62.2
90°-180°	11254.0	71.4
0°-180°	15754.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	581	581	581	581	581	
5°	566	607	684	773	801	52
15°	424	783	1319	1599	1650	118
25°	271	887	1571	1640	1642	125
35°	183	848	1480	1564	1625	114
45°	125	676	1308	1498	1566	97
55°	90	430	1110	1289	1324	82
65°	71	228	824	926	940	70
75°	52	140	452	497	499	55
85°	19	43	112	123	125	20
90°	12	33	88	44	44	11
95°	112	438	1458	752	512	124
105°	401	607	2460	3734	3484	425
115°	712	864	1970	3930	4486	703
125°	990	1110	1792	3028	3572	879
135°	1180	1299	1736	2444	2772	913
145°	1369	1456	1714	2086	2249	858
155°	1547	1590	1714	1882	1936	711
165°	1670	1692	1714	1781	1804	471
175°	1736	1736	1726	1748	1748	165
180°	1736	1736	1736	1736	1736	

TEST NUMBER: P938408

CATALOG NUMBER: SQ4-FB-150U-075D-B50-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	580.9	580.9	580.9	580.9	580.9	580.9	580.9	580.9	580.9	580.9	580.9
2.5°	580.9	580.9	584.7	586.6	590.3	592.2	595.9	599.6	610.8	612.7	616.4
5°	566.0	573.5	597.8	607.1	633.3	668.7	683.7	708.0	758.4	773.4	782.7
7.5°	543.6	560.4	620.2	635.1	700.5	793.9	833.1	885.4	965.8	1005.0	1036.7
10°	508.1	543.6	650.1	685.6	792.0	934.0	1006.9	1079.8	1201.2	1255.4	1275.9
12.5°	468.9	526.8	681.8	730.4	883.6	1091.0	1178.8	1259.1	1397.4	1470.2	1481.4
15°	424.0	502.5	711.7	782.7	980.7	1221.8	1318.9	1417.9	1546.8	1599.1	1612.2
17.5°	384.8	483.8	739.7	814.4	1055.4	1339.4	1438.5	1520.6	1625.3	1660.7	1670.1
20°	336.2	453.9	758.4	855.5	1134.0	1425.4	1520.6	1584.2	1655.1	1677.6	1681.3
22.5°	300.7	422.2	769.6	870.5	1186.3	1477.7	1558.0	1608.4	1657.0	1664.5	1666.3
25°	270.9	386.7	767.7	887.3	1231.1	1509.4	1571.1	1608.4	1636.5	1640.2	1640.2
27.5°	242.8	347.4	760.3	891.0	1264.7	1516.9	1565.5	1591.6	1604.7	1612.2	1612.2
30°	218.6	310.1	741.6	883.6	1279.7	1509.4	1548.7	1561.7	1574.8	1586.0	1591.6
32.5°	199.9	274.6	713.6	868.6	1281.5	1490.8	1518.8	1526.2	1544.9	1571.1	1580.4
35°	183.1	239.1	681.8	848.1	1270.3	1460.9	1479.5	1487.0	1524.4	1563.6	1576.7
37.5°	166.3	213.0	640.7	812.6	1253.5	1425.4	1438.5	1451.5	1509.4	1556.1	1571.1
40°	149.4	190.5	592.2	773.4	1227.4	1382.4	1393.6	1414.2	1490.8	1544.9	1559.9
42.5°	136.4	171.9	539.9	732.3	1193.7	1333.8	1350.7	1380.5	1468.3	1526.2	1543.1
45°	125.2	153.2	483.8	676.2	1150.8	1283.4	1307.7	1348.8	1442.2	1498.2	1513.2
47.5°	113.9	140.1	425.9	618.3	1104.1	1233.0	1264.7	1311.4	1406.7	1460.9	1473.9
50°	104.6	127.0	368.0	556.7	1053.6	1178.8	1216.2	1264.7	1361.9	1412.3	1429.1
52.5°	97.1	115.8	313.8	495.0	995.6	1122.8	1165.7	1216.2	1307.7	1356.3	1367.5
55°	89.7	106.5	267.1	429.6	935.9	1063.0	1109.7	1158.3	1247.9	1289.0	1296.5
57.5°	85.9	99.0	227.9	368.0	872.4	995.6	1047.9	1092.9	1176.9	1208.7	1216.2
60°	80.3	93.4	198.0	315.7	803.2	932.1	977.0	1021.8	1092.9	1119.0	1124.6
62.5°	74.7	89.7	175.6	265.3	732.3	857.4	902.2	943.3	1003.1	1021.8	1029.3
65°	71.0	85.9	158.8	227.9	659.4	779.0	823.8	859.3	907.8	926.5	930.3
67.5°	67.2	82.2	145.7	196.1	586.6	700.5	734.1	767.7	805.1	823.8	825.7
70°	61.6	78.5	134.5	173.7	511.8	610.8	638.9	674.3	704.2	713.6	719.2
72.5°	57.9	72.9	127.0	156.9	435.2	524.9	551.1	571.6	597.8	607.1	607.1
75°	52.3	65.4	119.6	140.1	356.8	429.6	452.1	472.6	493.2	496.9	491.3
77.5°	46.7	57.9	102.7	117.7	278.3	340.0	358.7	369.9	386.7	390.4	392.3
80°	39.2	50.4	80.3	91.5	201.7	250.3	263.4	272.7	287.7	287.7	291.4
82.5°	29.9	39.2	57.9	65.4	136.4	171.9	183.1	188.7	198.0	198.0	198.0
85°	18.7	24.3	37.4	43.0	82.2	104.6	112.1	113.9	121.4	123.3	123.3
87.5°	9.3	13.1	24.3	26.2	43.0	54.2	54.2	57.9	57.9	56.0	54.2
90°	11.7	21.0	30.3	32.6	51.3	76.1	88.5	78.7	59.0	44.3	44.3
92.5°	46.6	125.8	205.1	224.9	316.2	437.9	498.7	437.0	313.8	221.4	212.6
95°	111.9	256.8	401.8	438.0	777.8	1230.9	1457.5	1300.6	986.9	751.5	724.8
97.5°	193.4	321.3	449.3	481.2	1047.9	1803.4	2181.1	2081.9	1883.6	1734.8	1684.1
100°	256.3	372.3	488.3	517.3	1146.1	1984.4	2403.6	2410.8	2425.3	2436.2	2375.7
102.5°	309.9	418.2	526.3	553.4	1191.1	2041.4	2466.5	2592.9	2845.5	3035.0	2983.3
105°	400.8	492.4	584.1	607.0	1224.5	2047.8	2459.5	2742.8	3309.3	3734.1	3706.3
107.5°	494.0	579.5	664.8	686.2	1230.7	1956.7	2319.7	2714.8	3505.0	4097.6	4104.4
110°	556.9	634.1	711.2	730.5	1221.4	1875.9	2203.2	2644.9	3528.3	4190.9	4219.8

TEST NUMBER: P938408

CATALOG NUMBER: SQ4-FB-150U-075D-B50-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	618.7	692.2	765.7	784.1	1221.8	1805.3	2097.1	2549.2	3453.3	4131.4	4175.9
115°	711.9	779.7	847.5	864.5	1233.1	1724.4	1970.2	2405.6	3276.6	3929.8	3991.5
117.5°	803.9	865.5	927.2	942.6	1255.9	1673.8	1882.8	2275.8	3061.8	3651.4	3719.8
120°	857.5	915.5	973.5	988.0	1274.6	1656.7	1847.8	2206.9	2925.2	3463.8	3530.3
122.5°	909.9	968.5	1026.9	1041.6	1301.4	1647.9	1821.0	2144.4	2791.2	3276.2	3341.9
125°	990.3	1043.7	1097.0	1110.3	1337.5	1640.4	1791.9	2066.6	2615.9	3028.0	3088.5
127.5°	1055.6	1109.4	1163.3	1176.7	1373.6	1636.2	1767.4	2003.2	2475.0	2828.8	2879.8
130°	1090.5	1148.5	1206.5	1221.0	1400.1	1638.7	1758.1	1968.0	2388.1	2703.0	2750.2
132.5°	1126.7	1184.7	1242.7	1257.2	1421.5	1640.5	1749.9	1937.9	2313.8	2595.8	2638.0
135°	1180.2	1233.1	1285.9	1299.1	1444.7	1638.9	1735.9	1893.4	2208.3	2444.4	2480.7
137.5°	1235.0	1287.3	1339.5	1352.6	1479.6	1649.0	1733.7	1866.8	2132.9	2332.5	2362.3
140°	1280.4	1328.6	1376.7	1388.8	1501.0	1650.7	1725.5	1840.4	2070.4	2242.8	2270.6
142.5°	1315.4	1359.9	1404.5	1415.6	1518.9	1656.6	1725.5	1826.4	2028.4	2179.9	2203.8
145°	1369.0	1407.8	1446.7	1456.4	1542.2	1656.6	1713.8	1796.4	1961.6	2085.5	2103.6
147.5°	1422.6	1460.4	1498.2	1507.7	1576.4	1668.0	1713.8	1778.8	1908.7	2006.2	2021.3
150°	1457.5	1491.7	1525.9	1534.4	1594.2	1673.9	1713.8	1768.7	1878.5	1960.8	1973.0
152.5°	1493.7	1519.5	1545.5	1551.9	1605.9	1677.8	1713.8	1760.7	1854.4	1924.7	1933.8
155°	1547.3	1566.4	1585.6	1590.3	1631.5	1686.3	1713.8	1751.1	1825.7	1881.6	1887.7
157.5°	1586.9	1605.5	1624.1	1628.8	1657.1	1694.9	1713.8	1742.8	1800.8	1844.4	1848.7
160°	1613.7	1628.1	1642.6	1646.3	1668.8	1698.8	1713.8	1738.6	1788.4	1825.7	1828.1
162.5°	1640.5	1651.3	1662.2	1664.9	1681.2	1703.0	1713.8	1734.8	1776.7	1808.2	1810.6
165°	1669.5	1679.3	1689.2	1691.7	1699.0	1708.8	1713.8	1728.8	1758.9	1781.4	1783.8
167.5°	1696.3	1701.0	1705.7	1706.9	1713.0	1721.4	1725.5	1735.3	1755.0	1769.7	1770.8
170°	1713.8	1718.5	1723.1	1724.4	1724.7	1725.2	1725.5	1735.3	1755.0	1769.7	1769.7
172.5°	1723.1	1724.2	1725.2	1725.5	1725.5	1725.5	1725.5	1733.2	1748.7	1760.4	1759.5
175°	1735.9	1735.9	1735.9	1735.9	1732.5	1727.8	1725.5	1730.4	1740.2	1747.6	1747.6
177.5°	1735.9	1735.9	1735.9	1735.9	1733.2	1729.6	1727.8	1731.7	1739.5	1745.3	1744.2
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9

TEST NUMBER: P938408

CATALOG NUMBER: SQ4-FB-150U-075D-B50-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	580.9	580.9
2.5°	620.2	616.4
5°	797.6	801.4
7.5°	1074.2	1072.3
10°	1335.7	1352.5
12.5°	1526.2	1530.0
15°	1642.1	1649.5
17.5°	1686.9	1688.8
20°	1688.8	1685.0
22.5°	1668.2	1664.5
25°	1643.9	1642.1
27.5°	1621.5	1623.4
30°	1612.2	1617.8
32.5°	1612.2	1621.5
35°	1615.9	1625.3
37.5°	1614.0	1625.3
40°	1606.6	1619.6
42.5°	1586.0	1595.4
45°	1554.3	1565.5
47.5°	1513.2	1520.6
50°	1460.9	1468.3
52.5°	1395.5	1397.4
55°	1317.0	1324.5
57.5°	1233.0	1234.8
60°	1139.6	1145.2
62.5°	1040.5	1040.5
65°	935.9	939.6
67.5°	827.5	836.9
70°	717.3	719.2
72.5°	609.0	609.0
75°	496.9	498.8
77.5°	390.4	390.4
80°	289.5	291.4
82.5°	199.9	203.6
85°	125.2	125.2
87.5°	57.9	52.3
90°	44.3	44.3
92.5°	177.4	142.2
95°	618.1	511.5
97.5°	1481.0	1278.1
100°	2133.9	1892.1
102.5°	2776.1	2569.1
105°	3595.0	3483.6
107.5°	4131.3	4158.2
110°	4335.8	4451.8

TEST NUMBER: P938408

CATALOG NUMBER: SQ4-FB-150U-075D-B50-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	4354.0	4532.1
115°	4238.6	4485.5
117.5°	3993.8	4267.7
120°	3796.5	4062.6
122.5°	3604.4	3866.9
125°	3330.4	3572.2
127.5°	3083.9	3287.9
130°	2938.6	3127.1
132.5°	2806.8	2975.6
135°	2626.2	2771.7
137.5°	2481.4	2600.4
140°	2382.0	2493.3
142.5°	2299.6	2395.4
145°	2176.1	2248.6
147.5°	2081.3	2141.4
150°	2021.7	2070.4
152.5°	1970.6	2007.4
155°	1912.1	1936.4
157.5°	1865.7	1882.8
160°	1838.0	1847.8
162.5°	1819.8	1829.1
165°	1793.7	1803.6
167.5°	1775.0	1779.1
170°	1769.7	1769.7
172.5°	1755.9	1752.3
175°	1747.6	1747.6
177.5°	1740.0	1735.9
180°	1735.9	1735.9

(END OF REPORT)