

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428377

Luminaire Tested: SQ2W-PW1-K-050U-075D-L830-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1428377  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-PW1-K-050U-075D-L830-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - PERCEIVE WAVES LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5952.2 lumens  
Efficiency: N/A  
Efficacy: 143.1 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 41.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1428377

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L830-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1428377

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L830-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64
1	102	98	94	90	95	92	89	86	81	79	76	71	69	68	62	61	60	55
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	56	53	51	47
3	85	76	69	63	80	72	66	61	64	59	55	57	53	50	50	47	45	41
4	79	68	60	54	74	64	57	52	57	52	48	51	47	43	45	42	39	36
5	72	61	53	47	68	58	51	45	52	46	42	46	42	38	41	37	34	32
6	67	55	47	41	63	52	45	40	47	41	37	42	37	34	37	34	31	28
7	62	50	42	37	58	48	40	35	43	37	33	38	34	30	34	30	27	25
8	58	46	38	33	54	43	36	32	39	33	29	35	31	27	32	28	25	23
9	54	42	34	29	51	40	33	28	36	30	26	33	28	24	29	25	23	21
10	51	39	31	27	48	37	30	26	33	28	24	30	26	22	27	23	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	27651	27651	27651	27651
5°	27466	27941	27466	27941
10°	27515	28184	27515	28184
15°	27508	28354	27508	28354
20°	27520	27800	27520	27800
25°	27370	25831	27370	25831
30°	27186	23353	27186	23353
35°	26971	21090	26971	21090
40°	26436	18632	26436	18632
45°	25400	16276	25400	16276
50°	23639	13930	23639	13930
55°	21624	11293	21624	11293
60°	19381	9742	19381	9742
65°	16947	8661	16947	8661
70°	13860	7855	13860	7855
75°	10786	7224	10786	7224
80°	8033	6369	8033	6369
85°	5446	3631	5446	3631

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25400 cd/sqm



TEST NUMBER: P1428377

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L830-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	163.1	2.7
10°-20°	472.5	7.9
20°-30°	695.4	11.7
30°-40°	760.3	12.8
40°-50°	682.0	11.5
50°-60°	508.8	8.5
60°-70°	321.5	5.4
70°-80°	159.3	2.7
80°-90°	40.3	0.7
90°-100°	58.6	1.0
100°-110°	170.8	2.9
110°-120°	278.8	4.7
120°-130°	353.7	5.9
130°-140°	378.5	6.4
140°-150°	353.4	5.9
150°-160°	290.8	4.9
160°-170°	195.1	3.3
170°-180°	69.3	1.2
0°-30°	1330.9	22.4
0°-40°	2091.2	35.1
0°-60°	3282.0	55.1
0°-90°	3803.2	63.9
90°-120°	508.2	8.5
90°-150°	1593.8	26.8
90°-180°	2149.0	36.1
0°-180°	5952.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1713	1713	1713	1713	1713	
5°	1695	1724	1695	1724	1695	161
15°	1646	1696	1646	1696	1646	465
25°	1536	1450	1536	1450	1536	708
35°	1368	1070	1368	1070	1368	853
45°	1112	713	1112	713	1112	853
55°	768	401	768	401	768	686
65°	444	227	444	227	444	440
75°	173	116	173	116	173	190
85°	29	20	29	20	29	37
90°	2	16	2	32	2	3
95°	23	17	23	100	23	28
105°	108	174	108	239	108	115
115°	208	288	208	355	208	205
125°	308	457	308	436	308	275
135°	418	598	418	482	418	323
145°	534	690	534	493	534	334
155°	635	749	635	512	635	292
165°	702	781	702	589	702	198
175°	734	765	734	691	734	70
180°	736	736	736	736	736	



TEST NUMBER: P1428377

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1712.6	1712.6	1712.6	1712.6	1712.6	1712.6	1712.6	1712.6	1712.6	1712.6	1712.6
2.5°	1700.9	1710.7	1720.6	1718.3	1711.9	1709.0	1709.6	1710.4	1712.2	1713.9	1712.2
5°	1694.7	1707.0	1719.3	1717.5	1711.0	1708.1	1708.8	1711.0	1717.5	1724.0	1717.5
7.5°	1686.2	1698.6	1711.1	1710.5	1705.6	1704.4	1706.8	1710.3	1716.7	1723.0	1716.7
10°	1678.3	1691.4	1704.4	1704.4	1700.1	1699.7	1703.4	1707.5	1713.3	1719.1	1713.3
12.5°	1667.9	1681.5	1695.2	1696.2	1693.0	1693.5	1697.7	1702.3	1708.1	1713.9	1708.1
15°	1645.7	1660.2	1674.7	1677.8	1677.1	1679.3	1684.3	1689.0	1692.7	1696.3	1692.7
17.5°	1620.0	1634.5	1649.0	1651.8	1650.8	1650.9	1652.3	1653.7	1655.4	1657.1	1655.4
20°	1601.7	1616.2	1630.7	1632.7	1630.5	1626.9	1621.8	1618.0	1618.0	1618.0	1618.0
22.5°	1575.6	1591.3	1606.9	1607.0	1601.9	1592.5	1578.7	1567.3	1562.6	1558.0	1562.6
25°	1536.4	1551.7	1566.9	1559.8	1545.3	1523.9	1495.7	1471.7	1460.9	1450.0	1460.9
27.5°	1490.8	1503.1	1515.4	1497.0	1468.3	1433.8	1393.7	1359.8	1344.7	1329.6	1344.7
30°	1458.2	1467.6	1477.0	1447.8	1405.8	1362.6	1318.4	1281.6	1267.1	1252.6	1267.1
32.5°	1424.2	1427.9	1431.5	1393.0	1340.5	1291.3	1245.4	1207.0	1191.3	1175.7	1191.3
35°	1368.4	1361.9	1355.4	1304.3	1238.3	1182.1	1135.8	1097.5	1083.7	1070.0	1083.7
37.5°	1302.6	1283.1	1263.7	1206.1	1135.8	1076.3	1027.8	987.5	972.3	957.1	972.3
40°	1254.3	1226.7	1199.2	1137.4	1064.2	1003.3	954.7	914.5	899.3	884.0	899.3
42.5°	1200.8	1166.3	1131.8	1068.2	995.0	934.1	885.6	845.2	829.4	813.6	829.4
45°	1112.4	1071.8	1031.2	965.0	890.4	829.5	782.4	743.2	728.0	712.8	728.0
47.5°	1012.9	972.6	932.3	866.3	791.8	731.7	686.0	648.5	635.5	622.4	635.5
50°	941.1	902.0	862.8	799.8	728.7	670.4	624.7	586.5	570.5	554.6	570.5
52.5°	868.0	833.0	797.9	737.1	667.8	609.8	562.9	522.4	500.6	478.9	500.6
55°	768.2	734.9	701.5	644.3	579.0	520.3	468.1	425.9	413.6	401.2	413.6
57.5°	665.5	636.6	607.8	556.3	497.3	444.1	396.7	358.6	348.4	338.3	348.4
60°	600.2	574.9	549.5	500.2	442.9	394.4	354.5	322.0	311.9	301.7	311.9
62.5°	537.6	515.1	492.6	445.4	389.9	346.2	314.5	288.6	280.1	271.7	280.1
65°	443.6	427.0	410.3	371.3	324.9	288.7	262.6	241.2	234.0	226.7	234.0
67.5°	352.3	343.0	333.7	304.6	268.8	239.4	216.5	198.1	193.3	188.5	193.3
70°	293.6	290.7	287.8	263.7	232.5	207.5	188.7	173.6	170.0	166.4	170.0
72.5°	242.7	243.9	245.0	225.0	197.9	176.9	162.1	150.4	148.0	145.5	148.0
75°	172.9	178.7	184.5	171.3	151.7	136.8	126.7	118.7	117.3	115.8	117.3
77.5°	117.8	126.5	135.2	126.6	112.2	101.3	93.7	87.8	86.6	85.5	86.6
80°	86.4	95.1	103.8	97.9	87.0	78.7	72.9	68.5	68.5	68.5	68.5
82.5°	60.3	67.3	74.3	70.0	62.1	56.6	53.7	51.5	51.5	51.5	51.5
85°	29.4	33.0	36.6	35.3	32.4	28.8	24.5	21.0	20.3	19.6	20.3
87.5°	8.3	10.6	13.1	11.9	9.5	7.9	7.3	7.0	7.2	7.2	7.2
90°	2.2	5.2	8.9	11.9	14.1	14.9	14.9	15.6	16.4	16.4	16.4
92.5°	8.2	12.9	13.1	13.1	15.9	17.2	18.4	18.6	19.3	19.3	19.3
95°	23.0	25.3	37.9	37.2	25.3	20.1	17.1	17.1	17.1	17.1	17.1
97.5°	44.0	47.3	49.4	66.2	69.9	67.5	55.0	46.2	41.3	39.1	41.3
100°	62.4	63.9	68.4	69.1	87.7	105.6	96.6	85.5	81.8	79.5	81.8
102.5°	80.9	81.8	88.6	91.7	96.1	106.2	137.1	133.7	131.1	130.7	131.1
105°	108.5	109.3	121.9	127.9	130.8	130.8	130.1	145.0	168.8	174.0	168.8
107.5°	138.1	141.5	156.4	172.3	175.7	176.6	172.8	170.5	169.6	170.2	169.6
110°	158.3	163.6	181.4	201.5	206.7	208.2	206.7	204.4	203.0	203.0	203.0



TEST NUMBER: P1428377

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	178.0	185.6	205.8	228.8	237.6	242.1	238.8	237.2	235.7	236.9	235.7
115°	208.2	219.3	246.1	269.9	287.7	289.9	289.2	289.2	288.4	288.4	288.4
117.5°	236.1	254.0	284.0	311.6	332.3	338.3	341.2	340.3	339.4	340.9	339.4
120°	255.7	276.6	310.8	342.0	362.0	371.0	373.9	372.5	373.9	372.5	373.9
122.5°	276.6	302.1	335.7	368.1	391.8	401.9	405.5	405.8	406.1	405.2	406.1
125°	307.8	339.0	378.4	411.9	436.4	448.3	451.3	452.0	453.5	457.2	453.5
127.5°	339.3	374.7	418.0	450.2	475.3	489.8	494.4	496.0	499.1	500.8	499.1
130°	361.3	401.4	445.3	475.8	500.3	515.9	524.1	526.3	530.1	529.3	530.1
132.5°	384.5	426.4	470.9	502.6	525.3	542.1	549.1	555.5	556.8	557.9	556.8
135°	418.5	463.9	508.5	539.7	561.3	577.6	586.6	592.5	596.2	598.5	596.2
137.5°	454.4	502.3	545.1	572.9	594.6	608.7	618.8	625.1	628.9	630.7	628.9
140°	478.8	524.9	566.5	595.5	614.8	628.9	637.9	645.3	649.8	649.8	649.8
142.5°	502.0	547.5	587.9	616.9	633.8	646.8	656.3	661.9	667.0	667.0	667.0
145°	534.5	579.9	617.0	646.0	660.2	672.1	682.5	686.9	689.9	689.9	689.9
147.5°	568.6	608.7	642.6	670.4	682.3	696.3	704.5	708.0	711.8	710.1	711.8
150°	588.8	626.0	658.7	684.7	696.6	710.0	718.1	721.1	724.8	722.6	724.8
152.5°	608.4	643.8	673.5	697.8	707.9	721.3	730.6	733.6	736.1	734.5	736.1
155°	634.9	666.1	693.6	715.9	724.8	737.5	746.4	750.1	753.1	749.4	753.1
157.5°	658.5	685.4	709.4	729.9	739.4	750.3	758.6	763.2	766.2	764.5	766.2
160°	672.8	697.3	718.9	738.2	747.1	756.8	765.7	770.9	773.9	771.7	773.9
162.5°	684.7	706.8	727.2	744.8	752.5	761.0	771.7	776.3	779.3	776.4	779.3
165°	701.8	719.6	737.5	752.3	759.0	765.7	776.9	782.1	784.3	781.3	784.3
167.5°	714.7	728.4	742.8	755.6	760.5	767.1	778.2	782.5	785.4	781.6	785.4
170°	721.9	733.8	746.4	756.8	760.5	766.5	777.6	781.3	783.6	779.9	783.6
172.5°	727.8	736.7	747.0	756.2	758.1	762.9	773.5	777.2	778.8	775.7	778.8
175°	733.8	739.0	746.4	752.3	751.6	754.6	763.5	766.5	769.4	765.0	769.4
177.5°	736.6	739.0	741.3	744.9	742.5	742.5	749.1	750.9	751.5	749.1	751.5
180°	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0



TEST NUMBER: P1428377

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1712.6	1712.6	1712.6	1712.6	1712.6	1712.6	1712.6	1712.6	1712.6	1712.6	1712.6
2.5°	1710.4	1709.6	1709.0	1711.9	1718.3	1720.6	1710.7	1700.9	1710.7	1720.6	1718.3
5°	1711.0	1708.8	1708.1	1711.0	1717.5	1719.3	1707.0	1694.7	1707.0	1719.3	1717.5
7.5°	1710.3	1706.8	1704.4	1705.6	1710.5	1711.1	1698.6	1686.2	1698.6	1711.1	1710.5
10°	1707.5	1703.4	1699.7	1700.1	1704.4	1704.4	1691.4	1678.3	1691.4	1704.4	1704.4
12.5°	1702.3	1697.7	1693.5	1693.0	1696.2	1695.2	1681.5	1667.9	1681.5	1695.2	1696.2
15°	1689.0	1684.3	1679.3	1677.1	1677.8	1674.7	1660.2	1645.7	1660.2	1674.7	1677.8
17.5°	1653.7	1652.3	1650.9	1650.8	1651.8	1649.0	1634.5	1620.0	1634.5	1649.0	1651.8
20°	1618.0	1621.8	1626.9	1630.5	1632.7	1630.7	1616.2	1601.7	1616.2	1630.7	1632.7
22.5°	1567.3	1578.7	1592.5	1601.9	1607.0	1606.9	1591.3	1575.6	1591.3	1606.9	1607.0
25°	1471.7	1495.7	1523.9	1545.3	1559.8	1566.9	1551.7	1536.4	1551.7	1566.9	1559.8
27.5°	1359.8	1393.7	1433.8	1468.3	1497.0	1515.4	1503.1	1490.8	1503.1	1515.4	1497.0
30°	1281.6	1318.4	1362.6	1405.8	1447.8	1477.0	1467.6	1458.2	1467.6	1477.0	1447.8
32.5°	1207.0	1245.4	1291.3	1340.5	1393.0	1431.5	1427.9	1424.2	1427.9	1431.5	1393.0
35°	1097.5	1135.8	1182.1	1238.3	1304.3	1355.4	1361.9	1368.4	1361.9	1355.4	1304.3
37.5°	987.5	1027.8	1076.3	1135.8	1206.1	1263.7	1283.1	1302.6	1283.1	1263.7	1206.1
40°	914.5	954.7	1003.3	1064.2	1137.4	1199.2	1226.7	1254.3	1226.7	1199.2	1137.4
42.5°	845.2	885.6	934.1	995.0	1068.2	1131.8	1166.3	1200.8	1166.3	1131.8	1068.2
45°	743.2	782.4	829.5	890.4	965.0	1031.2	1071.8	1112.4	1071.8	1031.2	965.0
47.5°	648.5	686.0	731.7	791.8	866.3	932.3	972.6	1012.9	972.6	932.3	866.3
50°	586.5	624.7	670.4	728.7	799.8	862.8	902.0	941.1	902.0	862.8	799.8
52.5°	522.4	562.9	609.8	667.8	737.1	797.9	833.0	868.0	833.0	797.9	737.1
55°	425.9	468.1	520.3	579.0	644.3	701.5	734.9	768.2	734.9	701.5	644.3
57.5°	358.6	396.7	444.1	497.3	556.3	607.8	636.6	665.5	636.6	607.8	556.3
60°	322.0	354.5	394.4	442.9	500.2	549.5	574.9	600.2	574.9	549.5	500.2
62.5°	288.6	314.5	346.2	389.9	445.4	492.6	515.1	537.6	515.1	492.6	445.4
65°	241.2	262.6	288.7	324.9	371.3	410.3	427.0	443.6	427.0	410.3	371.3
67.5°	198.1	216.5	239.4	268.8	304.6	333.7	343.0	352.3	343.0	333.7	304.6
70°	173.6	188.7	207.5	232.5	263.7	287.8	290.7	293.6	290.7	287.8	263.7
72.5°	150.4	162.1	176.9	197.9	225.0	245.0	243.9	242.7	243.9	245.0	225.0
75°	118.7	126.7	136.8	151.7	171.3	184.5	178.7	172.9	178.7	184.5	171.3
77.5°	87.8	93.7	101.3	112.2	126.6	135.2	126.5	117.8	126.5	135.2	126.6
80°	68.5	72.9	78.7	87.0	97.9	103.8	95.1	86.4	95.1	103.8	97.9
82.5°	51.5	53.7	56.6	62.1	70.0	74.3	67.3	60.3	67.3	74.3	70.0
85°	21.0	24.5	28.8	32.4	35.3	36.6	33.0	29.4	33.0	36.6	35.3
87.5°	7.0	7.3	7.9	9.5	11.9	13.1	10.6	8.3	10.6	12.9	12.2
90°	15.6	14.9	14.9	14.1	11.9	8.9	5.2	2.2	5.2	8.2	13.4
92.5°	18.6	18.4	17.2	15.9	13.1	13.1	12.9	8.2	14.1	20.1	28.8
95°	17.1	17.1	20.1	25.3	37.2	37.9	25.3	23.0	32.7	46.1	58.0
97.5°	46.2	55.0	67.5	69.9	66.2	49.4	47.3	44.0	59.9	73.2	92.3
100°	85.5	96.6	105.6	87.7	69.1	68.4	63.9	62.4	79.5	92.2	110.8
102.5°	133.7	137.1	106.2	96.1	91.7	88.6	81.8	80.9	98.0	115.4	131.0
105°	145.0	130.1	130.8	130.8	127.9	121.9	109.3	108.5	127.9	147.9	167.3
107.5°	170.5	172.8	176.6	175.7	172.3	156.4	141.5	138.1	155.5	179.6	200.9
110°	204.4	206.7	208.2	206.7	201.5	181.4	163.6	158.3	174.0	199.2	222.3



TEST NUMBER: P1428377

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	237.2	238.8	242.1	237.6	228.8	205.8	185.6	178.0	193.6	219.5	243.1
115°	289.2	289.2	289.9	287.7	269.9	246.1	219.3	208.2	221.5	245.3	271.4
117.5°	340.3	341.2	338.3	332.3	311.6	284.0	254.0	236.1	246.7	271.8	298.6
120°	372.5	373.9	371.0	362.0	342.0	310.8	276.6	255.7	263.9	288.4	315.2
122.5°	405.8	405.5	401.9	391.8	368.1	335.7	302.1	276.6	280.0	302.7	328.9
125°	452.0	451.3	448.3	436.4	411.9	378.4	339.0	307.8	303.3	322.6	349.4
127.5°	496.0	494.4	489.8	475.3	450.2	418.0	374.7	339.3	329.3	341.5	366.1
130°	526.3	524.1	515.9	500.3	475.8	445.3	401.4	361.3	347.2	354.6	376.2
132.5°	555.5	549.1	542.1	525.3	502.6	470.9	426.4	384.5	365.0	368.3	385.1
135°	592.5	586.6	577.6	561.3	539.7	508.5	463.9	418.5	391.8	388.8	398.5
137.5°	625.1	618.8	608.7	594.6	572.9	545.1	502.3	454.4	420.6	410.7	414.4
140°	645.3	637.9	628.9	614.8	595.5	566.5	524.9	478.8	440.9	426.7	424.5
142.5°	661.9	656.3	646.8	633.8	616.9	587.9	547.5	502.0	461.7	443.4	438.2
145°	686.9	682.5	672.1	660.2	646.0	617.0	579.9	534.5	494.4	470.6	459.4
147.5°	708.0	704.5	696.3	682.3	670.4	642.6	608.7	568.6	527.4	497.9	483.5
150°	721.1	718.1	710.0	696.6	684.7	658.7	626.0	588.8	549.4	518.2	499.6
152.5°	733.6	730.6	721.3	707.9	697.8	673.5	643.8	608.4	568.4	537.2	518.0
155°	750.1	746.4	737.5	724.8	715.9	693.6	666.1	634.9	600.7	568.0	546.4
157.5°	763.2	758.6	750.3	739.4	729.9	709.4	685.4	658.5	628.6	597.4	575.4
160°	770.9	765.7	756.8	747.1	738.2	718.9	697.3	672.8	645.3	617.0	593.3
162.5°	776.3	771.7	761.0	752.5	744.8	727.2	706.8	684.7	660.2	635.5	613.5
165°	782.1	776.9	765.7	759.0	752.3	737.5	719.6	701.8	681.0	660.9	643.1
167.5°	782.5	778.2	767.1	760.5	755.6	742.8	728.4	714.7	698.5	682.8	667.9
170°	781.3	777.6	766.5	760.5	756.8	746.4	733.8	721.9	709.2	695.8	684.0
172.5°	777.2	773.5	762.9	758.1	756.2	747.0	736.7	727.8	717.0	707.1	697.6
175°	766.5	763.5	754.6	751.6	752.3	746.4	739.0	733.8	727.1	721.1	715.9
177.5°	750.9	749.1	742.5	742.5	744.9	741.3	739.0	736.6	733.6	731.8	730.0
180°	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0



TEST NUMBER: P1428377

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1712.6	1712.6	1712.6	1712.6	1712.6	1712.6	1712.6	1712.6	1712.6	1712.6	1712.6
2.5°	1711.9	1709.0	1709.6	1710.4	1712.2	1713.9	1712.2	1710.4	1709.6	1709.0	1711.9
5°	1711.0	1708.1	1708.8	1711.0	1717.5	1724.0	1717.5	1711.0	1708.8	1708.1	1711.0
7.5°	1705.6	1704.4	1706.8	1710.3	1716.7	1723.0	1716.7	1710.3	1706.8	1704.4	1705.6
10°	1700.1	1699.7	1703.4	1707.5	1713.3	1719.1	1713.3	1707.5	1703.4	1699.7	1700.1
12.5°	1693.0	1693.5	1697.7	1702.3	1708.1	1713.9	1708.1	1702.3	1697.7	1693.5	1693.0
15°	1677.1	1679.3	1684.3	1689.0	1692.7	1696.3	1692.7	1689.0	1684.3	1679.3	1677.1
17.5°	1650.8	1650.9	1652.3	1653.7	1655.4	1657.1	1655.4	1653.7	1652.3	1650.9	1650.8
20°	1630.5	1626.9	1621.8	1618.0	1618.0	1618.0	1618.0	1618.0	1621.8	1626.9	1630.5
22.5°	1601.9	1592.5	1578.7	1567.3	1562.6	1558.0	1562.6	1567.3	1578.7	1592.5	1601.9
25°	1545.3	1523.9	1495.7	1471.7	1460.9	1450.0	1460.9	1471.7	1495.7	1523.9	1545.3
27.5°	1468.3	1433.8	1393.7	1359.8	1344.7	1329.6	1344.7	1359.8	1393.7	1433.8	1468.3
30°	1405.8	1362.6	1318.4	1281.6	1267.1	1252.6	1267.1	1281.6	1318.4	1362.6	1405.8
32.5°	1340.5	1291.3	1245.4	1207.0	1191.3	1175.7	1191.3	1207.0	1245.4	1291.3	1340.5
35°	1238.3	1182.1	1135.8	1097.5	1083.7	1070.0	1083.7	1097.5	1135.8	1182.1	1238.3
37.5°	1135.8	1076.3	1027.8	987.5	972.3	957.1	972.3	987.5	1027.8	1076.3	1135.8
40°	1064.2	1003.3	954.7	914.5	899.3	884.0	899.3	914.5	954.7	1003.3	1064.2
42.5°	995.0	934.1	885.6	845.2	829.4	813.6	829.4	845.2	885.6	934.1	995.0
45°	890.4	829.5	782.4	743.2	728.0	712.8	728.0	743.2	782.4	829.5	890.4
47.5°	791.8	731.7	686.0	648.5	635.5	622.4	635.5	648.5	686.0	731.7	791.8
50°	728.7	670.4	624.7	586.5	570.5	554.6	570.5	586.5	624.7	670.4	728.7
52.5°	667.8	609.8	562.9	522.4	500.6	478.9	500.6	522.4	562.9	609.8	667.8
55°	579.0	520.3	468.1	425.9	413.6	401.2	413.6	425.9	468.1	520.3	579.0
57.5°	497.3	444.1	396.7	358.6	348.4	338.3	348.4	358.6	396.7	444.1	497.3
60°	442.9	394.4	354.5	322.0	311.9	301.7	311.9	322.0	354.5	394.4	442.9
62.5°	389.9	346.2	314.5	288.6	280.1	271.7	280.1	288.6	314.5	346.2	389.9
65°	324.9	288.7	262.6	241.2	234.0	226.7	234.0	241.2	262.6	288.7	324.9
67.5°	268.8	239.4	216.5	198.1	193.3	188.5	193.3	198.1	216.5	239.4	268.8
70°	232.5	207.5	188.7	173.6	170.0	166.4	170.0	173.6	188.7	207.5	232.5
72.5°	197.9	176.9	162.1	150.4	148.0	145.5	148.0	150.4	162.1	176.9	197.9
75°	151.7	136.8	126.7	118.7	117.3	115.8	117.3	118.7	126.7	136.8	151.7
77.5°	112.2	101.3	93.7	87.8	86.6	85.5	86.6	87.8	93.7	101.3	112.2
80°	87.0	78.7	72.9	68.5	68.5	68.5	68.5	68.5	72.9	78.7	87.0
82.5°	62.1	56.6	53.7	51.5	51.5	51.5	51.5	51.5	53.7	56.6	62.1
85°	32.4	28.8	24.5	21.0	20.3	19.6	20.3	21.0	24.5	28.8	32.4
87.5°	10.1	9.4	9.9	10.0	10.6	10.3	10.6	10.0	9.9	9.4	10.1
90°	17.1	22.3	27.5	30.5	33.5	32.0	33.5	30.5	27.5	22.3	17.1
92.5°	34.3	43.1	49.5	54.9	57.2	56.9	57.2	54.9	49.5	43.1	34.3
95°	69.1	79.5	90.0	97.4	101.8	100.4	101.8	97.4	90.0	79.5	69.1
97.5°	106.6	120.6	132.2	139.2	143.6	146.6	143.6	139.2	132.2	120.6	106.6
100°	131.6	145.0	158.3	166.5	174.0	176.9	174.0	166.5	158.3	145.0	131.6
102.5°	151.8	169.4	183.9	192.7	198.9	201.9	198.9	192.7	183.9	169.4	151.8
105°	185.1	203.7	219.3	230.5	237.2	239.4	237.2	230.5	219.3	203.7	185.1
107.5°	218.4	237.6	252.0	264.4	272.5	277.3	272.5	264.4	252.0	237.6	218.4
110°	244.6	260.2	275.8	287.0	295.1	298.1	295.1	287.0	275.8	260.2	244.6



TEST NUMBER: P1428377

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	266.6	284.0	299.6	310.8	320.1	324.3	320.1	310.8	299.6	284.0	266.6
115°	297.4	320.4	334.5	344.9	351.6	355.4	351.6	344.9	334.5	320.4	297.4
117.5°	322.9	347.0	362.5	370.5	373.6	376.3	373.6	370.5	362.5	347.0	322.9
120°	339.0	361.3	379.1	389.6	393.3	394.8	393.3	389.6	379.1	361.3	339.0
122.5°	353.9	375.0	392.2	405.0	411.1	412.6	411.1	405.0	392.2	375.0	353.9
125°	374.7	394.8	412.6	425.2	431.9	435.6	431.9	425.2	412.6	394.8	374.7
127.5°	392.8	414.5	430.9	442.3	448.9	451.9	448.9	442.3	430.9	414.5	392.8
130°	402.9	425.2	441.6	454.2	460.2	463.2	460.2	454.2	441.6	425.2	402.9
132.5°	410.7	434.2	451.1	462.6	469.1	472.1	469.1	462.6	451.1	434.2	410.7
135°	420.0	444.6	462.4	473.6	479.5	482.5	479.5	473.6	462.4	444.6	420.0
137.5°	428.2	450.5	469.1	480.8	486.2	488.1	486.2	480.8	469.1	450.5	428.2
140°	434.2	453.5	472.1	483.2	489.2	489.9	489.2	483.2	472.1	453.5	434.2
142.5°	441.9	457.1	473.3	484.4	490.4	491.7	490.4	484.4	473.3	457.1	441.9
145°	455.7	464.6	475.8	486.2	491.4	492.9	491.4	486.2	475.8	464.6	455.7
147.5°	473.1	475.9	481.7	488.6	493.6	494.7	493.6	488.6	481.7	475.9	473.1
150°	486.2	485.5	487.7	492.1	496.6	495.9	496.6	492.1	487.7	485.5	486.2
152.5°	501.1	496.8	496.6	498.7	500.8	500.6	500.8	498.7	496.6	496.8	501.1
155°	526.3	518.2	513.7	512.2	512.2	511.5	512.2	512.2	513.7	518.2	526.3
157.5°	554.1	542.7	536.0	532.4	531.4	529.8	531.4	532.4	536.0	542.7	554.1
160°	573.2	560.5	553.9	547.9	545.7	543.4	545.7	547.9	553.9	560.5	573.2
162.5°	591.0	579.0	571.7	566.3	564.1	560.7	564.1	566.3	571.7	579.0	591.0
165°	620.0	607.4	599.2	594.7	591.8	588.8	591.8	594.7	599.2	607.4	620.0
167.5°	649.0	635.2	629.8	624.8	621.9	616.6	621.9	624.8	629.8	635.2	649.0
170°	666.9	654.2	651.2	646.8	641.6	635.6	641.6	646.8	651.2	654.2	666.9
172.5°	682.3	673.8	670.9	666.4	664.8	660.0	664.8	666.4	670.9	673.8	682.3
175°	704.8	698.1	698.1	697.3	695.1	690.6	695.1	697.3	698.1	698.1	704.8
177.5°	723.5	719.9	722.3	722.3	721.7	717.6	721.7	722.3	722.3	719.9	723.5
180°	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0



TEST NUMBER: P1428377

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	1712.6	1712.6	1712.6	1712.6
2.5°	1718.3	1720.6	1710.7	1700.9
5°	1717.5	1719.3	1707.0	1694.7
7.5°	1710.5	1711.1	1698.6	1686.2
10°	1704.4	1704.4	1691.4	1678.3
12.5°	1696.2	1695.2	1681.5	1667.9
15°	1677.8	1674.7	1660.2	1645.7
17.5°	1651.8	1649.0	1634.5	1620.0
20°	1632.7	1630.7	1616.2	1601.7
22.5°	1607.0	1606.9	1591.3	1575.6
25°	1559.8	1566.9	1551.7	1536.4
27.5°	1497.0	1515.4	1503.1	1490.8
30°	1447.8	1477.0	1467.6	1458.2
32.5°	1393.0	1431.5	1427.9	1424.2
35°	1304.3	1355.4	1361.9	1368.4
37.5°	1206.1	1263.7	1283.1	1302.6
40°	1137.4	1199.2	1226.7	1254.3
42.5°	1068.2	1131.8	1166.3	1200.8
45°	965.0	1031.2	1071.8	1112.4
47.5°	866.3	932.3	972.6	1012.9
50°	799.8	862.8	902.0	941.1
52.5°	737.1	797.9	833.0	868.0
55°	644.3	701.5	734.9	768.2
57.5°	556.3	607.8	636.6	665.5
60°	500.2	549.5	574.9	600.2
62.5°	445.4	492.6	515.1	537.6
65°	371.3	410.3	427.0	443.6
67.5°	304.6	333.7	343.0	352.3
70°	263.7	287.8	290.7	293.6
72.5°	225.0	245.0	243.9	242.7
75°	171.3	184.5	178.7	172.9
77.5°	126.6	135.2	126.5	117.8
80°	97.9	103.8	95.1	86.4
82.5°	70.0	74.3	67.3	60.3
85°	35.3	36.6	33.0	29.4
87.5°	12.2	12.9	10.6	8.3
90°	13.4	8.2	5.2	2.2
92.5°	28.8	20.1	14.1	8.2
95°	58.0	46.1	32.7	23.0
97.5°	92.3	73.2	59.9	44.0
100°	110.8	92.2	79.5	62.4
102.5°	131.0	115.4	98.0	80.9
105°	167.3	147.9	127.9	108.5
107.5°	200.9	179.6	155.5	138.1
110°	222.3	199.2	174.0	158.3

TEST NUMBER: P1428377

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	243.1	219.5	193.6	178.0
115°	271.4	245.3	221.5	208.2
117.5°	298.6	271.8	246.7	236.1
120°	315.2	288.4	263.9	255.7
122.5°	328.9	302.7	280.0	276.6
125°	349.4	322.6	303.3	307.8
127.5°	366.1	341.5	329.3	339.3
130°	376.2	354.6	347.2	361.3
132.5°	385.1	368.3	365.0	384.5
135°	398.5	388.8	391.8	418.5
137.5°	414.4	410.7	420.6	454.4
140°	424.5	426.7	440.9	478.8
142.5°	438.2	443.4	461.7	502.0
145°	459.4	470.6	494.4	534.5
147.5°	483.5	497.9	527.4	568.6
150°	499.6	518.2	549.4	588.8
152.5°	518.0	537.2	568.4	608.4
155°	546.4	568.0	600.7	634.9
157.5°	575.4	597.4	628.6	658.5
160°	593.3	617.0	645.3	672.8
162.5°	613.5	635.5	660.2	684.7
165°	643.1	660.9	681.0	701.8
167.5°	667.9	682.8	698.5	714.7
170°	684.0	695.8	709.2	721.9
172.5°	697.6	707.1	717.0	727.8
175°	715.9	721.1	727.1	733.8
177.5°	730.0	731.8	733.6	736.6
180°	736.0	736.0	736.0	736.0



TEST NUMBER: P1428377

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L830-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.66	20.61	20.50	21.46	22.52	15.91	16.86	16.74	17.71	18.77
	3H	20.97	21.82	21.82	22.68	23.77	17.18	18.03	18.03	18.89	19.98
	4H	21.38	22.18	22.25	23.05	24.15	17.69	18.49	18.56	19.36	20.46
	6H	21.57	22.30	22.44	23.18	24.29	18.01	18.74	18.89	19.62	20.73
	8H	21.61	22.31	22.50	23.20	24.32	18.12	18.82	19.01	19.72	20.83
	12H	21.61	22.28	22.51	23.17	24.30	18.16	18.82	19.05	19.71	20.85
4H	2H	19.80	20.60	20.67	21.47	22.57	16.73	17.53	17.60	18.40	19.50
	3H	21.35	22.01	22.23	22.91	24.03	18.18	18.85	19.06	19.75	20.86
	4H	21.90	22.50	22.79	23.40	24.54	18.77	19.37	19.66	20.27	21.41
	6H	22.22	22.73	23.12	23.66	24.80	19.15	19.67	20.06	20.59	21.74
	8H	22.31	22.79	23.22	23.71	24.86	19.31	19.79	20.22	20.71	21.86
	12H	22.33	22.77	23.26	23.70	24.87	19.35	19.79	20.28	20.72	21.88
8H	4H	21.94	22.43	22.85	23.34	24.50	19.11	19.60	20.03	20.52	21.67
	6H	22.37	22.77	23.31	23.73	24.88	19.61	20.01	20.55	20.97	22.12
	8H	22.54	22.89	23.49	23.84	25.02	19.83	20.18	20.78	21.13	22.31
	12H	22.62	22.93	23.57	23.87	25.10	19.92	20.23	20.87	21.17	22.39
12H	4H	21.91	22.34	22.84	23.28	24.44	19.14	19.57	20.07	20.51	21.67
	6H	22.36	22.72	23.31	23.67	24.84	19.69	20.04	20.63	20.99	22.16
	8H	22.56	22.87	23.51	23.81	25.03	19.93	20.25	20.88	21.19	22.41