

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428431

Luminaire Tested: SQ2W-PW1-K-100U-100D-L830-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428431
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PW1-K-100U-100D-L830-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE WAVES LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9487.0 lumens
Efficiency: N/A
Efficacy: 134.2 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 70.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428431

CATALOG NUMBER: SQ2W-PW1-K-100U-100D-L830-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428431

CATALOG NUMBER: SQ2W-PW1-K-100U-100D-L830-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	74	72	64	63	61	54	53	52	47
2	91	84	78	73	84	78	73	69	67	63	60	57	55	52	48	46	44	40
3	83	74	67	62	77	69	63	58	60	55	51	51	48	45	43	41	39	35
4	77	66	58	53	71	62	55	50	54	48	44	46	42	39	39	36	34	30
5	70	59	51	45	65	55	48	43	48	43	39	42	37	34	35	32	30	27
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26	24
7	60	48	41	35	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	44	36	31	52	41	35	30	36	31	27	32	27	24	27	24	21	19
9	52	40	33	28	49	38	31	27	33	28	24	29	25	22	25	22	19	17
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	23	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	37177	37177	37177	37177
5°	36928	37568	36928	37568
10°	36996	37895	36996	37895
15°	36986	38122	36986	38122
20°	37001	37377	37001	37377
25°	36801	34730	36801	34730
30°	36550	31399	36550	31399
35°	36265	28355	36265	28355
40°	35543	25052	35543	25052
45°	34149	21881	34149	21881
50°	31782	18728	31782	18728
55°	29075	15186	29075	15186
60°	26059	13100	26059	13100
65°	22788	11644	22788	11644
70°	18632	10560	18632	10560
75°	14504	9713	14504	9713
80°	10804	8563	10804	8563
85°	7317	4872	7317	4872

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 34149 cd/sqm



TEST NUMBER: P1428431

CATALOG NUMBER: SQ2W-PW1-K-100U-100D-L830-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.3	2.3
10°-20°	635.3	6.7
20°-30°	934.9	9.9
30°-40°	1022.2	10.8
40°-50°	917.0	9.7
50°-60°	684.0	7.2
60°-70°	432.3	4.6
70°-80°	214.2	2.3
80°-90°	56.3	0.6
90°-100°	119.2	1.3
100°-110°	347.5	3.7
110°-120°	567.1	6.0
120°-130°	719.6	7.6
130°-140°	770.0	8.1
140°-150°	719.0	7.6
150°-160°	591.6	6.2
160°-170°	396.8	4.2
170°-180°	140.9	1.5
0°-30°	1789.5	18.9
0°-40°	2811.7	29.6
0°-60°	4412.7	46.5
0°-90°	5115.6	53.9
90°-120°	1033.7	10.9
90°-150°	3242.2	34.2
90°-180°	4371.0	46.1
0°-180°	9487.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2303	2303	2303	2303	2303	
5°	2278	2318	2278	2318	2278	217
15°	2213	2281	2213	2281	2213	625
25°	2066	1950	2066	1950	2066	951
35°	1840	1439	1840	1439	1840	1147
45°	1496	958	1496	958	1496	1147
55°	1033	540	1033	540	1033	922
65°	596	305	596	305	596	591
75°	232	156	232	156	232	256
85°	40	26	40	26	40	50
90°	4	33	4	65	4	5
95°	47	35	47	204	47	57
105°	221	354	221	487	221	235
115°	423	587	423	723	423	417
125°	626	930	626	886	626	560
135°	851	1217	851	982	851	658
145°	1087	1403	1087	1003	1087	680
155°	1292	1524	1292	1040	1292	594
165°	1428	1589	1428	1198	1428	402
175°	1493	1556	1493	1405	1493	142
180°	1497	1497	1497	1497	1497	



TEST NUMBER: P1428431

CATALOG NUMBER: SQ2W-PW1-K-100U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6
2.5°	2286.8	2300.1	2313.3	2310.2	2301.6	2297.7	2298.5	2299.7	2302.0	2304.4	2302.0
5°	2278.5	2295.1	2311.6	2309.2	2300.4	2296.5	2297.5	2300.4	2309.2	2318.0	2309.2
7.5°	2267.1	2283.8	2300.6	2299.8	2293.2	2291.5	2294.9	2299.5	2308.1	2316.6	2308.1
10°	2256.6	2274.1	2291.6	2291.6	2285.8	2285.3	2290.2	2295.8	2303.6	2311.4	2303.6
12.5°	2242.5	2260.8	2279.2	2280.5	2276.2	2276.9	2282.6	2288.8	2296.6	2304.4	2296.6
15°	2212.7	2232.2	2251.7	2255.8	2254.9	2257.8	2264.6	2270.9	2275.8	2280.7	2275.8
17.5°	2178.1	2197.5	2217.0	2220.9	2219.5	2219.7	2221.5	2223.4	2225.7	2228.1	2225.7
20°	2153.5	2173.0	2192.5	2195.2	2192.2	2187.4	2180.5	2175.4	2175.4	2175.4	2175.4
22.5°	2118.4	2139.5	2160.5	2160.7	2153.8	2141.2	2122.6	2107.2	2101.0	2094.7	2101.0
25°	2065.8	2086.2	2106.7	2097.2	2077.7	2049.0	2010.9	1978.8	1964.2	1949.5	1964.2
27.5°	2004.4	2020.9	2037.5	2012.7	1974.1	1927.8	1873.8	1828.2	1808.0	1787.7	1808.0
30°	1960.5	1973.2	1985.8	1946.6	1890.1	1832.1	1772.6	1723.2	1703.7	1684.2	1703.7
32.5°	1914.9	1919.8	1924.6	1872.9	1802.4	1736.2	1674.4	1622.8	1601.7	1580.7	1601.7
35°	1839.9	1831.1	1822.4	1753.6	1664.9	1589.4	1527.0	1475.6	1457.1	1438.6	1457.1
37.5°	1751.3	1725.2	1699.1	1621.6	1527.1	1447.2	1381.9	1327.8	1307.3	1286.8	1307.3
40°	1686.4	1649.4	1612.3	1529.2	1430.8	1348.9	1283.6	1229.5	1209.1	1188.6	1209.1
42.5°	1614.5	1568.1	1521.7	1436.2	1337.8	1255.9	1190.6	1136.3	1115.1	1093.8	1115.1
45°	1495.6	1441.0	1386.4	1297.5	1197.1	1115.2	1051.9	999.3	978.8	958.3	978.8
47.5°	1361.8	1307.6	1253.4	1164.8	1064.6	983.8	922.4	871.9	854.4	836.8	854.4
50°	1265.3	1212.7	1160.1	1075.3	979.8	901.3	839.9	788.5	767.0	745.6	767.0
52.5°	1167.1	1119.9	1072.7	991.1	897.9	819.8	756.9	702.3	673.1	643.9	673.1
55°	1032.9	988.1	943.2	866.2	778.5	699.6	629.4	572.6	556.0	539.5	556.0
57.5°	894.7	855.9	817.1	747.9	668.6	597.1	533.3	482.1	468.5	454.8	468.5
60°	807.0	772.9	738.8	672.5	595.5	530.2	476.6	433.0	419.3	405.7	419.3
62.5°	722.8	692.6	662.4	598.8	524.2	465.5	422.8	388.0	376.7	365.3	376.7
65°	596.5	574.1	551.7	499.3	436.9	388.2	353.1	324.3	314.6	304.8	314.6
67.5°	473.7	461.2	448.7	409.5	361.4	321.9	291.1	266.4	259.9	253.5	259.9
70°	394.7	390.8	386.9	354.5	312.6	279.0	253.7	233.4	228.6	223.7	228.6
72.5°	326.3	327.9	329.4	302.5	266.0	237.9	218.0	202.2	198.9	195.6	198.9
75°	232.5	240.3	248.0	230.3	203.9	184.0	170.3	159.6	157.6	155.7	157.6
77.5°	158.3	170.0	181.7	170.2	150.9	136.2	126.0	118.0	116.5	114.9	116.5
80°	116.2	127.9	139.6	131.6	117.0	105.7	98.0	92.1	92.1	92.1	92.1
82.5°	81.1	90.5	99.9	94.2	83.4	76.1	72.2	69.3	69.3	69.3	69.3
85°	39.5	44.3	49.2	47.5	43.6	38.7	32.9	28.3	27.3	26.3	27.3
87.5°	11.4	15.0	18.8	17.7	14.7	12.7	11.9	11.6	11.9	11.9	11.9
90°	4.5	10.6	18.1	24.2	28.7	30.2	30.2	31.8	33.3	33.3	33.3
92.5°	16.6	26.3	26.6	26.6	32.4	35.1	37.5	37.8	39.3	39.3	39.3
95°	46.9	51.4	77.1	75.6	51.4	40.8	34.8	34.8	34.8	34.8	34.8
97.5°	89.5	96.2	100.4	134.6	142.2	137.3	111.9	94.1	84.1	79.5	84.1
100°	127.0	130.1	139.1	140.6	178.4	214.7	196.6	173.9	166.4	161.8	166.4
102.5°	164.5	166.4	180.3	186.6	195.4	216.0	278.9	271.9	266.8	265.9	266.8
105°	220.8	222.3	248.0	260.1	266.2	266.2	264.7	294.9	343.3	353.9	343.3
107.5°	281.0	287.9	318.2	350.5	357.5	359.3	351.5	346.9	345.1	346.3	345.1
110°	322.1	332.7	369.0	409.8	420.4	423.4	420.4	415.9	412.9	412.9	412.9

TEST NUMBER: P1428431

CATALOG NUMBER: SQ2W-PW1-K-100U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	362.0	377.5	418.6	465.5	483.3	492.4	485.7	482.4	479.4	481.8	479.4
115°	423.4	446.1	500.6	549.0	585.3	589.8	588.3	588.3	586.8	586.8	586.8
117.5°	480.3	516.6	577.7	634.0	676.0	688.1	694.1	692.3	690.5	693.5	690.5
120°	520.2	562.6	632.1	695.7	736.5	754.6	760.7	757.7	760.7	757.7	760.7
122.5°	562.6	614.6	682.9	748.9	797.0	817.5	824.8	825.4	826.0	824.2	826.0
125°	626.1	689.6	769.8	837.8	887.7	911.9	918.0	919.5	922.5	930.1	922.5
127.5°	690.2	762.2	850.2	915.8	967.0	996.3	1005.7	1009.0	1015.3	1018.7	1015.3
130°	735.0	816.6	905.9	967.9	1017.8	1049.5	1066.2	1070.7	1078.3	1076.7	1078.3
132.5°	782.2	867.4	957.9	1022.3	1068.6	1102.8	1117.0	1130.0	1132.7	1134.8	1132.7
135°	851.4	943.7	1034.4	1097.9	1141.8	1175.0	1193.2	1205.3	1212.9	1217.4	1212.9
137.5°	924.3	1021.7	1108.8	1165.4	1209.5	1238.3	1258.8	1271.5	1279.4	1283.0	1279.4
140°	973.9	1067.7	1152.4	1211.3	1250.7	1279.4	1297.5	1312.7	1321.7	1321.7	1321.7
142.5°	1021.1	1113.6	1195.9	1254.9	1289.4	1315.7	1335.0	1346.5	1356.8	1356.8	1356.8
145°	1087.3	1179.6	1255.2	1314.2	1342.9	1367.1	1388.3	1397.4	1403.4	1403.4	1403.4
147.5°	1156.6	1238.3	1307.2	1363.8	1388.0	1416.4	1433.0	1440.3	1447.9	1444.5	1447.9
150°	1197.7	1273.3	1339.9	1392.8	1417.0	1444.2	1460.9	1466.9	1474.5	1469.9	1474.5
152.5°	1237.7	1309.6	1370.1	1419.4	1440.0	1467.2	1486.3	1492.3	1497.5	1494.1	1497.5
155°	1291.5	1355.0	1411.0	1456.3	1474.5	1500.2	1518.3	1525.9	1531.9	1524.4	1531.9
157.5°	1339.6	1394.3	1443.0	1484.8	1504.1	1526.2	1543.1	1552.5	1558.6	1555.2	1558.6
160°	1368.6	1418.5	1462.4	1501.7	1519.8	1539.5	1557.7	1568.2	1574.3	1569.8	1574.3
162.5°	1392.8	1437.9	1479.3	1515.0	1530.7	1548.0	1569.8	1579.1	1585.2	1579.4	1585.2
165°	1427.6	1463.9	1500.2	1530.4	1544.0	1557.7	1580.3	1590.9	1595.5	1589.4	1595.5
167.5°	1453.9	1481.7	1511.1	1537.1	1547.1	1560.4	1583.1	1591.8	1597.6	1590.0	1597.6
170°	1468.4	1492.6	1518.3	1539.5	1547.1	1559.2	1581.9	1589.4	1593.9	1586.4	1593.9
172.5°	1480.5	1498.7	1519.5	1538.3	1542.2	1551.9	1573.4	1580.9	1584.3	1577.9	1584.3
175°	1492.6	1503.2	1518.3	1530.4	1528.9	1535.0	1553.1	1559.2	1565.2	1556.1	1565.2
177.5°	1498.4	1503.2	1508.1	1515.3	1510.5	1510.5	1523.8	1527.4	1528.6	1523.8	1528.6
180°	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2



TEST NUMBER: P1428431

CATALOG NUMBER: SQ2W-PW1-K-100U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6
2.5°	2299.7	2298.5	2297.7	2301.6	2310.2	2313.3	2300.1	2286.8	2300.1	2313.3	2310.2
5°	2300.4	2297.5	2296.5	2300.4	2309.2	2311.6	2295.1	2278.5	2295.1	2311.6	2309.2
7.5°	2299.5	2294.9	2291.5	2293.2	2299.8	2300.6	2283.8	2267.1	2283.8	2300.6	2299.8
10°	2295.8	2290.2	2285.3	2285.8	2291.6	2291.6	2274.1	2256.6	2274.1	2291.6	2291.6
12.5°	2288.8	2282.6	2276.9	2276.2	2280.5	2279.2	2260.8	2242.5	2260.8	2279.2	2280.5
15°	2270.9	2264.6	2257.8	2254.9	2255.8	2251.7	2232.2	2212.7	2232.2	2251.7	2255.8
17.5°	2223.4	2221.5	2219.7	2219.5	2220.9	2217.0	2197.5	2178.1	2197.5	2217.0	2220.9
20°	2175.4	2180.5	2187.4	2192.2	2195.2	2192.5	2173.0	2153.5	2173.0	2192.5	2195.2
22.5°	2107.2	2122.6	2141.2	2153.8	2160.7	2160.5	2139.5	2118.4	2139.5	2160.5	2160.7
25°	1978.8	2010.9	2049.0	2077.7	2097.2	2106.7	2086.2	2065.8	2086.2	2106.7	2097.2
27.5°	1828.2	1873.8	1927.8	1974.1	2012.7	2037.5	2020.9	2004.4	2020.9	2037.5	2012.7
30°	1723.2	1772.6	1832.1	1890.1	1946.6	1985.8	1973.2	1960.5	1973.2	1985.8	1946.6
32.5°	1622.8	1674.4	1736.2	1802.4	1872.9	1924.6	1919.8	1914.9	1919.8	1924.6	1872.9
35°	1475.6	1527.0	1589.4	1664.9	1753.6	1822.4	1831.1	1839.9	1831.1	1822.4	1753.6
37.5°	1327.8	1381.9	1447.2	1527.1	1621.6	1699.1	1725.2	1751.3	1725.2	1699.1	1621.6
40°	1229.5	1283.6	1348.9	1430.8	1529.2	1612.3	1649.4	1686.4	1649.4	1612.3	1529.2
42.5°	1136.3	1190.6	1255.9	1337.8	1436.2	1521.7	1568.1	1614.5	1568.1	1521.7	1436.2
45°	999.3	1051.9	1115.2	1197.1	1297.5	1386.4	1441.0	1495.6	1441.0	1386.4	1297.5
47.5°	871.9	922.4	983.8	1064.6	1164.8	1253.4	1307.6	1361.8	1307.6	1253.4	1164.8
50°	788.5	839.9	901.3	979.8	1075.3	1160.1	1212.7	1265.3	1212.7	1160.1	1075.3
52.5°	702.3	756.9	819.8	897.9	991.1	1072.7	1119.9	1167.1	1119.9	1072.7	991.1
55°	572.6	629.4	699.6	778.5	866.2	943.2	988.1	1032.9	988.1	943.2	866.2
57.5°	482.1	533.3	597.1	668.6	747.9	817.1	855.9	894.7	855.9	817.1	747.9
60°	433.0	476.6	530.2	595.5	672.5	738.8	772.9	807.0	772.9	738.8	672.5
62.5°	388.0	422.8	465.5	524.2	598.8	662.4	692.6	722.8	692.6	662.4	598.8
65°	324.3	353.1	388.2	436.9	499.3	551.7	574.1	596.5	574.1	551.7	499.3
67.5°	266.4	291.1	321.9	361.4	409.5	448.7	461.2	473.7	461.2	448.7	409.5
70°	233.4	253.7	279.0	312.6	354.5	386.9	390.8	394.7	390.8	386.9	354.5
72.5°	202.2	218.0	237.9	266.0	302.5	329.4	327.9	326.3	327.9	329.4	302.5
75°	159.6	170.3	184.0	203.9	230.3	248.0	240.3	232.5	240.3	248.0	230.3
77.5°	118.0	126.0	136.2	150.9	170.2	181.7	170.0	158.3	170.0	181.7	170.2
80°	92.1	98.0	105.7	117.0	131.6	139.6	127.9	116.2	127.9	139.6	131.6
82.5°	69.3	72.2	76.1	83.4	94.2	99.9	90.5	81.1	90.5	99.9	94.2
85°	28.3	32.9	38.7	43.6	47.5	49.2	44.3	39.5	44.3	49.2	47.5
87.5°	11.6	11.9	12.7	14.7	17.7	18.8	15.0	11.4	15.0	18.5	18.3
90°	31.8	30.2	30.2	28.7	24.2	18.1	10.6	4.5	10.6	16.6	27.2
92.5°	37.8	37.5	35.1	32.4	26.6	26.6	26.3	16.6	28.7	40.8	58.7
95°	34.8	34.8	40.8	51.4	75.6	77.1	51.4	46.9	66.5	93.8	118.0
97.5°	94.1	111.9	137.3	142.2	134.6	100.4	96.2	89.5	121.9	148.8	187.8
100°	173.9	196.6	214.7	178.4	140.6	139.1	130.1	127.0	161.8	187.5	225.3
102.5°	271.9	278.9	216.0	195.4	186.6	180.3	166.4	164.5	199.3	234.7	266.5
105°	294.9	264.7	266.2	266.2	260.1	248.0	222.3	220.8	260.1	300.9	340.3
107.5°	346.9	351.5	359.3	357.5	350.5	318.2	287.9	281.0	316.4	365.4	408.6
110°	415.9	420.4	423.4	420.4	409.8	369.0	332.7	322.1	353.9	405.3	452.2



TEST NUMBER: P1428431

CATALOG NUMBER: SQ2W-PW1-K-100U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	482.4	485.7	492.4	483.3	465.5	418.6	377.5	362.0	393.8	446.4	494.5
115°	588.3	588.3	589.8	585.3	549.0	500.6	446.1	423.4	450.7	499.1	552.0
117.5°	692.3	694.1	688.1	676.0	634.0	577.7	516.6	480.3	501.8	552.9	607.3
120°	757.7	760.7	754.6	736.5	695.7	632.1	562.6	520.2	536.9	586.8	641.2
122.5°	825.4	824.8	817.5	797.0	748.9	682.9	614.6	562.6	569.5	615.8	669.0
125°	919.5	918.0	911.9	887.7	837.8	769.8	689.6	626.1	617.0	656.3	710.8
127.5°	1009.0	1005.7	996.3	967.0	915.8	850.2	762.2	690.2	669.9	694.7	744.6
130°	1070.7	1066.2	1049.5	1017.8	967.9	905.9	816.6	735.0	706.2	721.4	765.2
132.5°	1130.0	1117.0	1102.8	1068.6	1022.3	957.9	867.4	782.2	742.5	749.2	783.4
135°	1205.3	1193.2	1175.0	1141.8	1097.9	1034.4	943.7	851.4	797.0	790.9	810.6
137.5°	1271.5	1258.8	1238.3	1209.5	1165.4	1108.8	1021.7	924.3	855.7	835.4	842.9
140°	1312.7	1297.5	1279.4	1250.7	1211.3	1152.4	1067.7	973.9	896.8	868.1	863.5
142.5°	1346.5	1335.0	1315.7	1289.4	1254.9	1195.9	1113.6	1021.1	939.1	901.9	891.3
145°	1397.4	1388.3	1367.1	1342.9	1314.2	1255.2	1179.6	1087.3	1005.7	957.3	934.6
147.5°	1440.3	1433.0	1416.4	1388.0	1363.8	1307.2	1238.3	1156.6	1072.8	1012.9	983.6
150°	1466.9	1460.9	1444.2	1417.0	1392.8	1339.9	1273.3	1197.7	1117.6	1054.1	1016.3
152.5°	1492.3	1486.3	1467.2	1440.0	1419.4	1370.1	1309.6	1237.7	1156.3	1092.8	1053.8
155°	1525.9	1518.3	1500.2	1474.5	1456.3	1411.0	1355.0	1291.5	1221.9	1155.4	1111.5
157.5°	1552.5	1543.1	1526.2	1504.1	1484.8	1443.0	1394.3	1339.6	1278.8	1215.3	1170.5
160°	1568.2	1557.7	1539.5	1519.8	1501.7	1462.4	1418.5	1368.6	1312.7	1255.2	1206.8
162.5°	1579.1	1569.8	1548.0	1530.7	1515.0	1479.3	1437.9	1392.8	1342.9	1292.7	1247.9
165°	1590.9	1580.3	1557.7	1544.0	1530.4	1500.2	1463.9	1427.6	1385.3	1344.4	1308.1
167.5°	1591.8	1583.1	1560.4	1547.1	1537.1	1511.1	1481.7	1453.9	1420.9	1388.9	1358.6
170°	1589.4	1581.9	1559.2	1547.1	1539.5	1518.3	1492.6	1468.4	1442.7	1415.5	1391.3
172.5°	1580.9	1573.4	1551.9	1542.2	1538.3	1519.5	1498.7	1480.5	1458.4	1438.5	1419.1
175°	1559.2	1553.1	1535.0	1528.9	1530.4	1518.3	1503.2	1492.6	1479.0	1466.9	1456.3
177.5°	1527.4	1523.8	1510.5	1510.5	1515.3	1508.1	1503.2	1498.4	1492.3	1488.7	1485.1
180°	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2



TEST NUMBER: P1428431

CATALOG NUMBER: SQ2W-PW1-K-100U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6
2.5°	2301.6	2297.7	2298.5	2299.7	2302.0	2304.4	2302.0	2299.7	2298.5	2297.7	2301.6
5°	2300.4	2296.5	2297.5	2300.4	2309.2	2318.0	2309.2	2300.4	2297.5	2296.5	2300.4
7.5°	2293.2	2291.5	2294.9	2299.5	2308.1	2316.6	2308.1	2299.5	2294.9	2291.5	2293.2
10°	2285.8	2285.3	2290.2	2295.8	2303.6	2311.4	2303.6	2295.8	2290.2	2285.3	2285.8
12.5°	2276.2	2276.9	2282.6	2288.8	2296.6	2304.4	2296.6	2288.8	2282.6	2276.9	2276.2
15°	2254.9	2257.8	2264.6	2270.9	2275.8	2280.7	2275.8	2270.9	2264.6	2257.8	2254.9
17.5°	2219.5	2219.7	2221.5	2223.4	2225.7	2228.1	2225.7	2223.4	2221.5	2219.7	2219.5
20°	2192.2	2187.4	2180.5	2175.4	2175.4	2175.4	2175.4	2175.4	2180.5	2187.4	2192.2
22.5°	2153.8	2141.2	2122.6	2107.2	2101.0	2094.7	2101.0	2107.2	2122.6	2141.2	2153.8
25°	2077.7	2049.0	2010.9	1978.8	1964.2	1949.5	1964.2	1978.8	2010.9	2049.0	2077.7
27.5°	1974.1	1927.8	1873.8	1828.2	1808.0	1787.7	1808.0	1828.2	1873.8	1927.8	1974.1
30°	1890.1	1832.1	1772.6	1723.2	1703.7	1684.2	1703.7	1723.2	1772.6	1832.1	1890.1
32.5°	1802.4	1736.2	1674.4	1622.8	1601.7	1580.7	1601.7	1622.8	1674.4	1736.2	1802.4
35°	1664.9	1589.4	1527.0	1475.6	1457.1	1438.6	1457.1	1475.6	1527.0	1589.4	1664.9
37.5°	1527.1	1447.2	1381.9	1327.8	1307.3	1286.8	1307.3	1327.8	1381.9	1447.2	1527.1
40°	1430.8	1348.9	1283.6	1229.5	1209.1	1188.6	1209.1	1229.5	1283.6	1348.9	1430.8
42.5°	1337.8	1255.9	1190.6	1136.3	1115.1	1093.8	1115.1	1136.3	1190.6	1255.9	1337.8
45°	1197.1	1115.2	1051.9	999.3	978.8	958.3	978.8	999.3	1051.9	1115.2	1197.1
47.5°	1064.6	983.8	922.4	871.9	854.4	836.8	854.4	871.9	922.4	983.8	1064.6
50°	979.8	901.3	839.9	788.5	767.0	745.6	767.0	788.5	839.9	901.3	979.8
52.5°	897.9	819.8	756.9	702.3	673.1	643.9	673.1	702.3	756.9	819.8	897.9
55°	778.5	699.6	629.4	572.6	556.0	539.5	556.0	572.6	629.4	699.6	778.5
57.5°	668.6	597.1	533.3	482.1	468.5	454.8	468.5	482.1	533.3	597.1	668.6
60°	595.5	530.2	476.6	433.0	419.3	405.7	419.3	433.0	476.6	530.2	595.5
62.5°	524.2	465.5	422.8	388.0	376.7	365.3	376.7	388.0	422.8	465.5	524.2
65°	436.9	388.2	353.1	324.3	314.6	304.8	314.6	324.3	353.1	388.2	436.9
67.5°	361.4	321.9	291.1	266.4	259.9	253.5	259.9	266.4	291.1	321.9	361.4
70°	312.6	279.0	253.7	233.4	228.6	223.7	228.6	233.4	253.7	279.0	312.6
72.5°	266.0	237.9	218.0	202.2	198.9	195.6	198.9	202.2	218.0	237.9	266.0
75°	203.9	184.0	170.3	159.6	157.6	155.7	157.6	159.6	170.3	184.0	203.9
77.5°	150.9	136.2	126.0	118.0	116.5	114.9	116.5	118.0	126.0	136.2	150.9
80°	117.0	105.7	98.0	92.1	92.1	92.1	92.1	92.1	98.0	105.7	117.0
82.5°	83.4	76.1	72.2	69.3	69.3	69.3	69.3	69.3	72.2	76.1	83.4
85°	43.6	38.7	32.9	28.3	27.3	26.3	27.3	28.3	32.9	38.7	43.6
87.5°	15.9	15.7	17.0	17.7	18.9	18.3	18.9	17.7	17.0	15.7	15.9
90°	34.8	45.4	56.0	62.0	68.1	65.0	68.1	62.0	56.0	45.4	34.8
92.5°	69.9	87.7	100.7	111.6	116.4	115.8	116.4	111.6	100.7	87.7	69.9
95°	140.6	161.8	183.0	198.1	207.2	204.2	207.2	198.1	183.0	161.8	140.6
97.5°	216.9	245.3	268.9	283.1	292.2	298.2	292.2	283.1	268.9	245.3	216.9
100°	267.7	294.9	322.1	338.8	353.9	359.9	353.9	338.8	322.1	294.9	267.7
102.5°	308.8	344.5	374.1	392.0	404.7	410.7	404.7	392.0	374.1	344.5	308.8
105°	376.6	414.4	446.1	468.8	482.4	487.0	482.4	468.8	446.1	414.4	376.6
107.5°	444.3	483.3	512.7	537.8	554.4	564.1	554.4	537.8	512.7	483.3	444.3
110°	497.5	529.3	561.1	583.7	600.4	606.4	600.4	583.7	561.1	529.3	497.5



TEST NUMBER: P1428431

CATALOG NUMBER: SQ2W-PW1-K-100U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	542.3	577.7	609.5	632.1	651.2	659.7	651.2	632.1	609.5	577.7	542.3
115°	604.9	651.8	680.5	701.7	715.3	722.9	715.3	701.7	680.5	651.8	604.9
117.5°	656.9	705.9	737.4	753.7	760.1	765.5	760.1	753.7	737.4	705.9	656.9
120°	689.6	735.0	771.3	792.4	800.0	803.0	800.0	792.4	771.3	735.0	689.6
122.5°	719.8	762.8	797.9	823.9	836.3	839.3	836.3	823.9	797.9	762.8	719.8
125°	762.2	803.0	839.3	865.0	878.6	886.2	878.6	865.0	839.3	803.0	762.2
127.5°	799.1	843.3	876.5	899.8	913.1	919.2	913.1	899.8	876.5	843.3	799.1
130°	819.7	865.0	898.3	924.0	936.1	942.2	936.1	924.0	898.3	865.0	819.7
132.5°	835.4	883.2	917.7	940.9	954.3	960.3	954.3	940.9	917.7	883.2	835.4
135°	854.4	904.3	940.6	963.3	975.4	981.5	975.4	963.3	940.6	904.3	854.4
137.5°	871.1	916.4	954.3	978.1	989.0	993.0	989.0	978.1	954.3	916.4	871.1
140°	883.2	922.5	960.3	983.0	995.1	996.6	995.1	983.0	960.3	922.5	883.2
142.5°	898.9	929.8	962.7	985.4	997.5	1000.2	997.5	985.4	962.7	929.8	898.9
145°	927.0	945.2	967.9	989.0	999.6	1002.6	999.6	989.0	967.9	945.2	927.0
147.5°	962.4	968.2	980.0	993.9	1004.2	1006.3	1004.2	993.9	980.0	968.2	962.4
150°	989.0	987.5	992.1	1001.1	1010.2	1008.7	1010.2	1001.1	992.1	987.5	989.0
152.5°	1019.3	1010.5	1010.2	1014.4	1018.7	1018.4	1018.7	1014.4	1010.2	1010.5	1019.3
155°	1070.7	1054.1	1045.0	1042.0	1042.0	1040.5	1042.0	1042.0	1045.0	1054.1	1070.7
157.5°	1127.3	1104.0	1090.4	1083.1	1081.0	1077.7	1081.0	1083.1	1090.4	1104.0	1127.3
160°	1166.0	1140.3	1126.7	1114.6	1110.0	1105.5	1110.0	1114.6	1126.7	1140.3	1166.0
162.5°	1202.3	1177.8	1162.9	1152.1	1147.5	1140.6	1147.5	1152.1	1162.9	1177.8	1202.3
165°	1261.2	1235.5	1218.9	1209.8	1203.8	1197.7	1203.8	1209.8	1218.9	1235.5	1261.2
167.5°	1320.2	1292.1	1281.2	1270.9	1265.2	1254.3	1265.2	1270.9	1281.2	1292.1	1320.2
170°	1356.5	1330.8	1324.8	1315.7	1305.1	1293.0	1305.1	1315.7	1324.8	1330.8	1356.5
172.5°	1388.0	1370.7	1364.7	1355.6	1352.3	1342.6	1352.3	1355.6	1364.7	1370.7	1388.0
175°	1433.6	1420.0	1420.0	1418.5	1414.0	1404.9	1414.0	1418.5	1420.0	1420.0	1433.6
177.5°	1471.8	1464.5	1469.3	1469.3	1468.1	1459.7	1468.1	1469.3	1469.3	1464.5	1471.8
180°	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2



TEST NUMBER: P1428431

CATALOG NUMBER: SQ2W-PW1-K-100U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2302.6	2302.6	2302.6	2302.6
2.5°	2310.2	2313.3	2300.1	2286.8
5°	2309.2	2311.6	2295.1	2278.5
7.5°	2299.8	2300.6	2283.8	2267.1
10°	2291.6	2291.6	2274.1	2256.6
12.5°	2280.5	2279.2	2260.8	2242.5
15°	2255.8	2251.7	2232.2	2212.7
17.5°	2220.9	2217.0	2197.5	2178.1
20°	2195.2	2192.5	2173.0	2153.5
22.5°	2160.7	2160.5	2139.5	2118.4
25°	2097.2	2106.7	2086.2	2065.8
27.5°	2012.7	2037.5	2020.9	2004.4
30°	1946.6	1985.8	1973.2	1960.5
32.5°	1872.9	1924.6	1919.8	1914.9
35°	1753.6	1822.4	1831.1	1839.9
37.5°	1621.6	1699.1	1725.2	1751.3
40°	1529.2	1612.3	1649.4	1686.4
42.5°	1436.2	1521.7	1568.1	1614.5
45°	1297.5	1386.4	1441.0	1495.6
47.5°	1164.8	1253.4	1307.6	1361.8
50°	1075.3	1160.1	1212.7	1265.3
52.5°	991.1	1072.7	1119.9	1167.1
55°	866.2	943.2	988.1	1032.9
57.5°	747.9	817.1	855.9	894.7
60°	672.5	738.8	772.9	807.0
62.5°	598.8	662.4	692.6	722.8
65°	499.3	551.7	574.1	596.5
67.5°	409.5	448.7	461.2	473.7
70°	354.5	386.9	390.8	394.7
72.5°	302.5	329.4	327.9	326.3
75°	230.3	248.0	240.3	232.5
77.5°	170.2	181.7	170.0	158.3
80°	131.6	139.6	127.9	116.2
82.5°	94.2	99.9	90.5	81.1
85°	47.5	49.2	44.3	39.5
87.5°	18.3	18.5	15.0	11.4
90°	27.2	16.6	10.6	4.5
92.5°	58.7	40.8	28.7	16.6
95°	118.0	93.8	66.5	46.9
97.5°	187.8	148.8	121.9	89.5
100°	225.3	187.5	161.8	127.0
102.5°	266.5	234.7	199.3	164.5
105°	340.3	300.9	260.1	220.8
107.5°	408.6	365.4	316.4	281.0
110°	452.2	405.3	353.9	322.1

TEST NUMBER: P1428431

CATALOG NUMBER: SQ2W-PW1-K-100U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	494.5	446.4	393.8	362.0
115°	552.0	499.1	450.7	423.4
117.5°	607.3	552.9	501.8	480.3
120°	641.2	586.8	536.9	520.2
122.5°	669.0	615.8	569.5	562.6
125°	710.8	656.3	617.0	626.1
127.5°	744.6	694.7	669.9	690.2
130°	765.2	721.4	706.2	735.0
132.5°	783.4	749.2	742.5	782.2
135°	810.6	790.9	797.0	851.4
137.5°	842.9	835.4	855.7	924.3
140°	863.5	868.1	896.8	973.9
142.5°	891.3	901.9	939.1	1021.1
145°	934.6	957.3	1005.7	1087.3
147.5°	983.6	1012.9	1072.8	1156.6
150°	1016.3	1054.1	1117.6	1197.7
152.5°	1053.8	1092.8	1156.3	1237.7
155°	1111.5	1155.4	1221.9	1291.5
157.5°	1170.5	1215.3	1278.8	1339.6
160°	1206.8	1255.2	1312.7	1368.6
162.5°	1247.9	1292.7	1342.9	1392.8
165°	1308.1	1344.4	1385.3	1427.6
167.5°	1358.6	1388.9	1420.9	1453.9
170°	1391.3	1415.5	1442.7	1468.4
172.5°	1419.1	1438.5	1458.4	1480.5
175°	1456.3	1466.9	1479.0	1492.6
177.5°	1485.1	1488.7	1492.3	1498.4
180°	1497.2	1497.2	1497.2	1497.2

TEST NUMBER: P1428431

CATALOG NUMBER: SQ2W-PW1-K-100U-100D-L830-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.84	20.69	20.77	21.64	22.85	16.08	16.94	17.02	17.88	19.10
	3H	21.14	21.90	22.08	22.85	24.10	17.35	18.12	18.30	19.07	20.31
	4H	21.55	22.27	22.50	23.22	24.48	17.86	18.58	18.82	19.54	20.79
	6H	21.73	22.39	22.69	23.35	24.62	18.17	18.83	19.14	19.79	21.06
	8H	21.77	22.40	22.74	23.38	24.64	18.28	18.91	19.26	19.89	21.15
	12H	21.77	22.37	22.75	23.34	24.63	18.31	18.91	19.29	19.89	21.17
4H	2H	19.97	20.69	20.93	21.65	22.90	16.89	17.62	17.86	18.57	19.82
	3H	21.51	22.11	22.48	23.09	24.36	18.34	18.94	19.31	19.93	21.19
	4H	22.05	22.60	23.03	23.58	24.87	18.92	19.47	19.90	20.45	21.73
	6H	22.36	22.83	23.36	23.84	25.12	19.30	19.77	20.30	20.78	22.06
	8H	22.45	22.89	23.45	23.89	25.19	19.45	19.89	20.45	20.89	22.19
	12H	22.48	22.87	23.49	23.88	25.19	19.49	19.89	20.51	20.90	22.21
8H	4H	22.09	22.53	23.09	23.53	24.83	19.26	19.70	20.26	20.70	22.00
	6H	22.51	22.87	23.53	23.91	25.21	19.75	20.12	20.77	21.16	22.45
	8H	22.68	23.00	23.71	24.03	25.35	19.97	20.29	21.00	21.32	22.64
	12H	22.76	23.04	23.79	24.06	25.42	20.06	20.34	21.09	21.36	22.72
12H	4H	22.05	22.44	23.06	23.46	24.76	19.28	19.67	20.29	20.69	21.99
	6H	22.51	22.83	23.53	23.85	25.17	19.83	20.15	20.86	21.17	22.49
	8H	22.70	22.98	23.73	24.00	25.36	20.07	20.35	21.10	21.37	22.74