

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P621559

Luminaire Tested: VLT-F-150U-075D-830-UNV-STD-W-4

Issue Date: 9/2/2020

Test Information

Test Method: LM-79-2019
Report Number: P621559
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2203-563-1)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: VLT-F-150U-075D-830-UNV-STD-W-4
Description: CORELITE VAULT SUSPENDED LED LUMINAIRE
FROSTED LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8978.4 lumens
Efficiency: N/A
Efficacy: 127.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.23
Luminous Opening: Rectangular (W 0.38' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 70.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P621559

CATALOG NUMBER: VLT-F-150U-075D-830-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P621559

CATALOG NUMBER: VLT-F-150U-075D-830-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	95	91	87	84	85	82	79	76	66	64	62	51	49	48	37	36	35
2	86	80	74	69	78	72	67	63	58	55	52	45	43	41	33	32	31
3	79	70	63	58	71	64	58	53	52	47	44	40	37	35	30	28	27
4	73	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23
5	67	56	48	42	60	51	44	39	41	37	33	33	29	27	24	22	21
6	61	50	42	37	55	46	39	34	37	32	29	30	26	23	22	20	18
7	57	45	38	32	51	41	35	30	34	29	25	27	23	21	20	18	16
8	53	41	34	29	48	38	31	27	31	26	23	25	21	19	19	17	15
9	49	37	30	26	44	34	28	24	28	24	20	23	19	17	17	15	13
10	46	34	27	23	41	32	25	21	26	21	18	21	18	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10564	10564	10564
5°	10451	10528	10616
10°	10395	10439	10494
15°	10282	10293	10293
20°	10116	10069	9976
25°	9923	9754	9585
30°	9691	9414	9036
35°	9433	9006	7927
40°	9161	8434	6382
45°	8875	7470	4631
50°	8574	6248	3208
55°	8277	4757	2397
60°	7967	3295	1811
65°	7619	2350	1859
70°	7117	1979	1916
75°	6579	2024	1941
80°	5719	2136	2013
85°	4635	2379	2001

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8875 cd/sqm



TEST NUMBER: P621559

CATALOG NUMBER: VLT-F-150U-075D-830-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.7	1.5
10°-20°	390.1	4.3
20°-30°	567.5	6.3
30°-40°	627.8	7.0
40°-50°	539.0	6.0
50°-60°	373.2	4.2
60°-70°	222.4	2.5
70°-80°	109.6	1.2
80°-90°	36.3	0.4
90°-100°	136.7	1.5
100°-110°	974.3	10.9
110°-120°	1322.8	14.7
120°-130°	1076.6	12.0
130°-140°	865.9	9.6
140°-150°	682.6	7.6
150°-160°	499.1	5.6
160°-170°	310.0	3.5
170°-180°	105.7	1.2
0°-30°	1096.3	12.2
0°-40°	1724.1	19.2
0°-60°	2636.2	29.4
0°-90°	3004.5	33.5
90°-120°	2433.8	27.1
90°-150°	5059.0	56.3
90°-180°	5974.0	66.5
0°-180°	8978.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1472	1472	1472	1472	1472	
5°	1451	1473	1462	1460	1474	138
15°	1384	1402	1386	1378	1386	390
25°	1253	1262	1232	1211	1211	577
35°	1077	1074	1028	945	905	673
45°	874	860	736	532	456	675
55°	662	633	380	218	192	591
65°	449	361	138	111	110	444
75°	237	103	73	71	70	250
85°	56	28	29	26	24	65
90°	0	7	14	21	21	5
95°	56	104	56	63	77	63
105°	217	333	1266	1617	1070	229
115°	385	467	1091	2268	2651	382
125°	553	628	1028	1798	2126	491
135°	685	761	1035	1481	1700	527
145°	811	880	1042	1290	1427	510
155°	951	985	1063	1169	1224	437
165°	1056	1070	1091	1120	1140	297
175°	1112	1119	1112	1105	1098	105
180°	1112	1112	1112	1112	1112	

TEST NUMBER: P621559

CATALOG NUMBER: VLT-F-150U-075D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1472.2	1472.2	1472.2	1472.2	1472.2
2.5°	1460.0	1476.7	1468.5	1468.7	1474.6
5°	1450.9	1473.2	1461.5	1460.3	1473.7
7.5°	1437.5	1458.0	1446.0	1444.5	1456.1
10°	1426.6	1445.9	1432.6	1429.8	1440.2
12.5°	1410.7	1430.1	1415.6	1410.4	1420.8
15°	1384.0	1401.8	1385.5	1378.1	1385.5
17.5°	1350.2	1365.1	1346.6	1334.8	1339.3
20°	1324.7	1339.5	1318.6	1302.0	1306.4
22.5°	1296.7	1309.2	1285.7	1266.6	1269.9
25°	1253.2	1262.1	1231.9	1210.6	1210.6
27.5°	1204.8	1210.2	1175.0	1152.7	1146.4
30°	1169.5	1172.5	1136.1	1109.8	1090.5
32.5°	1133.0	1134.8	1093.5	1051.1	1021.1
35°	1076.8	1073.8	1028.1	945.1	904.9
37.5°	1016.8	1010.3	956.3	829.9	770.2
40°	977.9	969.0	900.3	748.3	681.3
42.5°	937.8	925.3	838.3	664.1	590.1
45°	874.5	859.6	736.1	532.1	456.3
47.5°	811.8	792.2	631.5	412.2	347.1
50°	768.0	747.2	559.7	339.5	287.4
52.5°	724.2	703.4	486.7	285.0	243.6
55°	661.6	633.3	380.2	218.4	191.6
57.5°	597.7	557.2	283.2	170.2	149.3
60°	555.1	501.6	229.6	141.1	126.2
62.5°	513.7	445.9	188.3	123.1	120.1
65°	448.7	360.9	138.4	111.0	109.5
67.5°	386.6	275.4	102.8	100.0	98.6
70°	339.2	217.2	94.3	92.7	91.3
72.5°	296.6	166.3	85.8	84.2	82.7
75°	237.3	103.4	73.0	71.4	70.0
77.5°	177.3	65.2	60.2	58.7	57.2
80°	138.4	53.6	51.7	50.2	48.7
82.5°	104.3	43.4	42.0	40.4	38.9
85°	56.3	28.0	28.9	25.8	24.3
87.5°	19.5	14.9	16.2	15.1	13.9
90°	0.0	6.8	14.0	21.0	21.0
92.5°	16.8	23.6	30.8	43.5	49.0
95°	56.0	103.8	56.0	63.3	76.9
97.5°	99.3	199.2	411.3	121.3	104.9
100°	132.9	249.2	825.3	242.9	160.9
102.5°	166.5	288.2	1116.3	641.1	351.1
105°	216.8	333.1	1266.0	1617.2	1070.1
107.5°	267.2	354.7	1208.6	2353.7	2204.6
110°	300.8	382.8	1175.0	2473.2	2657.8



TEST NUMBER: P621559

CATALOG NUMBER: VLT-F-150U-075D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	334.3	416.4	1141.5	2403.3	2713.8
115°	384.7	466.8	1091.1	2267.9	2650.8
117.5°	436.4	517.1	1078.5	2121.2	2515.2
120°	475.6	550.8	1056.1	2009.7	2420.0
122.5°	503.6	584.3	1028.2	1913.8	2291.3
125°	552.6	627.8	1028.2	1798.0	2126.3
127.5°	593.1	669.7	1029.6	1663.6	1987.8
130°	615.5	697.6	1035.2	1573.7	1881.5
132.5°	643.5	725.5	1035.2	1533.3	1786.3
135°	685.4	760.7	1035.2	1480.8	1699.6
137.5°	720.4	801.1	1035.2	1422.7	1610.1
140°	748.4	823.6	1035.2	1388.8	1559.7
142.5°	776.4	846.1	1040.8	1349.3	1509.4
145°	811.3	879.7	1042.2	1290.1	1426.8
147.5°	853.3	913.5	1050.5	1247.4	1352.7
150°	881.3	936.0	1056.1	1219.0	1307.9
152.5°	909.3	958.5	1056.1	1196.3	1268.8
155°	951.2	985.4	1063.1	1169.3	1224.0
157.5°	984.8	1017.6	1071.5	1152.2	1191.8
160°	1007.2	1034.5	1077.1	1140.8	1175.0
162.5°	1024.0	1051.3	1082.7	1135.0	1158.3
165°	1056.1	1069.8	1091.1	1119.6	1140.1
167.5°	1074.3	1086.6	1098.1	1112.4	1124.7
170°	1091.1	1098.0	1098.1	1112.3	1119.1
172.5°	1096.7	1109.0	1103.7	1106.7	1113.5
175°	1112.1	1118.9	1112.1	1104.9	1098.1
177.5°	1112.1	1117.6	1112.1	1112.0	1106.5
180°	1112.1	1112.1	1112.1	1112.1	1112.1



TEST NUMBER: P621559

CATALOG NUMBER: VLT-F-150U-075D-830-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.03	14.73	15.12	15.81	17.31	6.26	6.96	7.36	8.05	9.54
	3H	15.51	16.13	16.61	17.23	18.74	7.60	8.23	8.71	9.32	10.83
	4H	16.01	16.61	17.13	17.71	19.22	8.25	8.84	9.36	9.94	11.46
	6H	16.40	16.95	17.53	18.05	19.58	8.83	9.38	9.95	10.48	12.00
	8H	16.53	17.05	17.66	18.17	19.69	9.05	9.57	10.18	10.69	12.21
	12H	16.61	17.10	17.74	18.21	19.75	9.21	9.70	10.34	10.81	12.36
4H	2H	13.84	14.43	14.96	15.53	17.04	6.86	7.45	7.98	8.55	10.06
	3H	15.46	15.95	16.59	17.08	18.60	8.40	8.89	9.52	10.01	11.54
	4H	16.04	16.50	17.17	17.61	19.16	9.18	9.64	10.32	10.75	12.30
	6H	16.53	16.92	17.67	18.05	19.59	9.92	10.30	11.05	11.44	12.98
	8H	16.71	17.07	17.85	18.20	19.76	10.21	10.57	11.34	11.70	13.25
	12H	16.84	17.16	17.99	18.30	19.86	10.42	10.74	11.57	11.88	13.44
8H	4H	15.95	16.31	17.09	17.44	19.00	9.63	9.99	10.76	11.12	12.67
	6H	16.48	16.78	17.64	17.95	19.50	10.51	10.80	11.66	11.97	13.53
	8H	16.71	16.97	17.88	18.12	19.70	10.90	11.16	12.06	12.31	13.88
	12H	16.90	17.13	18.06	18.27	19.88	11.22	11.44	12.38	12.59	14.20
12H	4H	15.89	16.22	17.05	17.36	18.92	9.67	10.00	10.82	11.14	12.70
	6H	16.45	16.71	17.62	17.86	19.44	10.62	10.88	11.78	12.03	13.60
	8H	16.69	16.92	17.85	18.06	19.67	11.06	11.29	12.22	12.43	14.04

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

8 of 8