

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427501

Luminaire Tested: SQ2W-BBM-K-025U-100D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2024
Report Number: P1427501
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-BBM-K-025U-100D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - BLACK DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4772.1 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.17 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 45.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427501

CATALOG NUMBER: SQ2W-BBM-K-025U-100D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427501

CATALOG NUMBER: SQ2W-BBM-K-025U-100D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	92	92	92	84	84	84	80
1	108	104	102	99	103	100	98	96	93	91	89	86	84	83	79	78	77	74
2	101	95	91	87	97	92	88	84	85	82	79	79	77	75	74	72	70	68
3	94	87	81	77	91	84	79	75	79	74	71	74	70	67	69	66	64	61
4	88	80	73	68	85	77	71	67	72	68	64	68	64	61	64	61	58	56
5	83	73	66	61	79	71	65	60	67	62	58	63	59	55	59	56	53	51
6	77	67	60	55	74	65	59	54	62	56	52	58	54	50	55	52	49	47
7	73	62	55	50	70	60	54	49	57	52	48	54	50	46	51	48	45	43
8	68	57	50	46	66	56	49	45	53	48	44	50	46	42	48	44	41	39
9	64	53	46	42	62	52	46	41	49	44	40	47	42	39	45	41	38	36
10	60	49	43	38	58	48	42	38	46	41	37	44	39	36	42	38	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	41476	41476	41476	41476
5°	41800	41863	41800	41863
10°	42326	42262	42326	42262
15°	43088	42229	43088	42229
20°	43143	41466	43143	41466
25°	42078	40429	42078	40429
30°	39554	37710	39554	37710
35°	35106	33789	35106	33789
40°	28791	27248	28791	27248
45°	17166	16109	17166	16109
50°	5358	5069	5358	5069
55°	2027	2027	2027	2027
60°	126	42	126	42
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 20096 cd/sqm



TEST NUMBER: P1427501

CATALOG NUMBER: SQ2W-BBM-K-025U-100D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.6	5.1
10°-20°	719.5	15.1
20°-30°	1058.5	22.2
30°-40°	1081.9	22.7
40°-50°	623.2	13.1
50°-60°	107.3	2.2
60°-70°	3.9	0.1
70°-80°	0.0	0.0
80°-90°	1.7	0.0
90°-100°	25.4	0.5
100°-110°	74.0	1.6
110°-120°	120.8	2.5
120°-130°	153.3	3.2
130°-140°	164.0	3.4
140°-150°	153.1	3.2
150°-160°	126.0	2.6
160°-170°	84.5	1.8
170°-180°	30.0	0.6
0°-30°	2023.6	42.4
0°-40°	3105.5	65.1
0°-60°	3835.9	80.4
0°-90°	3841.5	80.5
90°-120°	220.2	4.6
90°-150°	690.5	14.5
90°-180°	931.0	19.5
0°-180°	4772.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2569	2569	2569	2569	2569	
5°	2579	2583	2579	2583	2579	246
15°	2578	2526	2578	2526	2578	726
25°	2362	2269	2362	2269	2362	1078
35°	1781	1714	1781	1714	1781	1100
45°	752	706	752	706	752	582
55°	72	72	72	72	72	76
65°	0	0	0	0	0	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	7	1	14	1	1
95°	10	7	10	44	10	12
105°	47	75	47	104	47	50
115°	90	125	90	154	90	89
125°	133	198	133	189	133	119
135°	181	259	181	209	181	140
145°	232	299	232	214	232	145
155°	275	325	275	222	275	126
165°	304	338	304	255	304	86
175°	318	331	318	299	318	30
180°	319	319	319	319	319	



TEST NUMBER: P1427501

CATALOG NUMBER: SQ2W-BBM-K-025U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2568.9	2568.9	2568.9	2568.9	2568.9	2568.9	2568.9	2568.9	2568.9	2568.9	2568.9
2.5°	2580.2	2577.0	2573.8	2566.1	2557.0	2557.7	2568.2	2575.5	2573.2	2570.9	2573.2
5°	2579.1	2576.3	2573.4	2565.4	2555.7	2558.6	2574.0	2585.3	2584.1	2583.0	2584.1
7.5°	2577.6	2575.7	2573.7	2568.1	2561.2	2564.1	2576.8	2585.6	2582.8	2579.9	2582.8
10°	2581.7	2581.1	2580.6	2571.9	2560.4	2561.3	2574.4	2583.6	2580.7	2577.8	2580.7
12.5°	2583.8	2587.3	2590.8	2578.4	2560.5	2556.8	2567.2	2573.7	2568.6	2563.5	2568.6
15°	2577.8	2587.6	2597.3	2579.6	2552.7	2540.2	2541.9	2541.3	2533.9	2526.4	2533.9
17.5°	2549.1	2562.8	2576.5	2553.1	2517.3	2496.3	2490.0	2482.7	2472.2	2461.7	2472.2
20°	2511.0	2527.0	2543.0	2517.5	2478.0	2452.9	2442.1	2431.6	2422.5	2413.4	2422.5
22.5°	2457.6	2472.2	2486.8	2462.3	2424.7	2399.1	2385.5	2373.5	2366.2	2358.9	2366.2
25°	2362.0	2371.7	2381.4	2356.4	2319.8	2296.4	2286.1	2277.4	2273.4	2269.4	2273.4
27.5°	2226.5	2229.3	2232.0	2212.1	2184.7	2164.6	2151.8	2140.9	2135.8	2130.6	2135.8
30°	2121.6	2121.6	2121.6	2106.2	2085.7	2068.5	2054.8	2042.1	2032.4	2022.7	2032.4
32.5°	1999.3	1997.9	1996.6	1985.3	1970.6	1955.8	1940.7	1927.0	1917.3	1907.6	1917.3
35°	1781.1	1787.4	1793.7	1785.8	1773.3	1759.5	1744.7	1731.4	1722.8	1714.3	1722.8
37.5°	1544.9	1547.3	1549.7	1543.2	1533.7	1521.0	1505.0	1491.2	1484.0	1476.8	1484.0
40°	1366.0	1366.6	1367.2	1359.2	1348.3	1337.2	1325.8	1314.5	1303.6	1292.8	1303.6
42.5°	1157.3	1168.9	1180.4	1175.5	1165.1	1150.8	1132.5	1117.7	1113.2	1108.8	1113.2
45°	751.8	802.6	853.4	872.1	880.1	873.8	853.3	823.2	764.3	705.5	764.3
47.5°	377.8	441.1	504.4	548.2	585.6	574.9	516.3	456.8	394.6	332.3	394.6
50°	213.3	251.0	288.7	347.4	413.1	402.2	314.8	244.0	222.9	201.8	222.9
52.5°	142.4	159.1	175.7	223.0	280.5	276.7	211.7	159.9	148.0	136.0	148.0
55°	72.0	76.5	81.1	101.9	128.2	127.7	100.2	78.8	75.4	72.0	75.4
57.5°	24.4	30.6	36.8	46.0	56.3	56.6	46.9	38.2	32.6	27.0	32.6
60°	3.9	9.6	15.3	22.7	30.7	29.8	20.1	11.6	6.4	1.3	6.4
62.5°	0.8	2.4	4.0	10.0	17.6	17.4	9.5	3.2	1.7	0.3	1.7
65°	0.0	0.0	0.0	0.4	1.0	1.0	0.4	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.2	0.5	0.8	1.0	1.2	1.3	1.3	1.4	1.4	1.4	1.4
90°	1.0	2.3	3.9	5.2	6.1	6.4	6.4	6.8	7.1	7.1	7.1
92.5°	3.5	5.6	5.7	5.7	6.9	7.5	8.0	8.1	8.4	8.4	8.4
95°	10.0	11.0	16.4	16.1	11.0	8.7	7.4	7.4	7.4	7.4	7.4
97.5°	19.1	20.5	21.4	28.7	30.3	29.2	23.8	20.0	17.9	16.9	17.9
100°	27.1	27.7	29.6	30.0	38.0	45.7	41.9	37.0	35.4	34.5	35.4
102.5°	35.0	35.4	38.4	39.7	41.6	46.0	59.4	57.9	56.8	56.6	56.8
105°	47.0	47.3	52.8	55.4	56.7	56.7	56.4	62.8	73.1	75.4	73.1
107.5°	59.8	61.3	67.8	74.7	76.1	76.5	74.9	73.9	73.5	73.8	73.5
110°	68.6	70.9	78.6	87.3	89.5	90.2	89.5	88.6	87.9	87.9	87.9



TEST NUMBER: P1427501

CATALOG NUMBER: SQ2W-BBM-K-025U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	77.1	80.4	89.2	99.1	102.9	104.9	103.5	102.7	102.1	102.6	102.1
115°	90.2	95.0	106.6	116.9	124.6	125.6	125.3	125.3	125.0	125.0	125.0
117.5°	102.3	110.0	123.0	135.0	144.0	146.5	147.8	147.5	147.1	147.7	147.1
120°	110.8	119.8	134.6	148.2	156.9	160.7	162.0	161.4	162.0	161.4	162.0
122.5°	119.8	130.9	145.5	159.5	169.7	174.1	175.7	175.8	175.9	175.5	175.9
125°	133.3	146.9	163.9	178.4	189.1	194.2	195.5	195.8	196.5	198.1	196.5
127.5°	147.0	162.3	181.1	195.1	205.9	212.2	214.2	214.9	216.2	217.0	216.2
130°	156.5	173.9	192.9	206.1	216.8	223.5	227.1	228.0	229.6	229.3	229.6
132.5°	166.6	184.7	204.0	217.7	227.6	234.9	237.9	240.7	241.2	241.7	241.2
135°	181.3	201.0	220.3	233.8	243.2	250.3	254.1	256.7	258.3	259.3	258.3
137.5°	196.9	217.6	236.2	248.2	257.6	263.7	268.1	270.8	272.5	273.3	272.5
140°	207.4	227.4	245.4	258.0	266.4	272.5	276.3	279.6	281.5	281.5	281.5
142.5°	217.5	237.2	254.7	267.3	274.6	280.2	284.3	286.8	289.0	289.0	289.0
145°	231.6	251.2	267.3	279.9	286.0	291.2	295.7	297.6	298.9	298.9	298.9
147.5°	246.3	263.7	278.4	290.5	295.6	301.7	305.2	306.8	308.4	307.7	308.4
150°	255.1	271.2	285.4	296.6	301.8	307.6	311.1	312.4	314.0	313.1	314.0
152.5°	263.6	278.9	291.8	302.3	306.7	312.5	316.5	317.8	318.9	318.2	318.9
155°	275.1	288.6	300.5	310.2	314.0	319.5	323.4	325.0	326.3	324.7	326.3
157.5°	285.3	297.0	307.3	316.2	320.3	325.0	328.7	330.7	331.9	331.2	331.9
160°	291.5	302.1	311.5	319.8	323.7	327.9	331.7	334.0	335.3	334.3	335.3
162.5°	296.6	306.2	315.1	322.7	326.0	329.7	334.3	336.3	337.6	336.4	337.6
165°	304.0	311.8	319.5	326.0	328.8	331.7	336.6	338.8	339.8	338.5	339.8
167.5°	309.7	315.6	321.8	327.4	329.5	332.3	337.2	339.0	340.3	338.6	340.3
170°	312.7	317.9	323.4	327.9	329.5	332.1	336.9	338.5	339.5	337.9	339.5
172.5°	315.3	319.2	323.6	327.6	328.5	330.5	335.1	336.7	337.4	336.1	337.4
175°	317.9	320.2	323.4	326.0	325.6	326.9	330.8	332.1	333.4	331.4	333.4
177.5°	319.1	320.2	321.2	322.7	321.7	321.7	324.5	325.3	325.6	324.5	325.6
180°	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9



TEST NUMBER: P1427501

CATALOG NUMBER: SQ2W-BBM-K-025U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2568.9	2568.9	2568.9	2568.9	2568.9	2568.9	2568.9	2568.9	2568.9	2568.9	2568.9
2.5°	2575.5	2568.2	2557.7	2557.0	2566.1	2573.8	2577.0	2580.2	2577.0	2573.8	2566.1
5°	2585.3	2574.0	2558.6	2555.7	2565.4	2573.4	2576.3	2579.1	2576.3	2573.4	2565.4
7.5°	2585.6	2576.8	2564.1	2561.2	2568.1	2573.7	2575.7	2577.6	2575.7	2573.7	2568.1
10°	2583.6	2574.4	2561.3	2560.4	2571.9	2580.6	2581.1	2581.7	2581.1	2580.6	2571.9
12.5°	2573.7	2567.2	2556.8	2560.5	2578.4	2590.8	2587.3	2583.8	2587.3	2590.8	2578.4
15°	2541.3	2541.9	2540.2	2552.7	2579.6	2597.3	2587.6	2577.8	2587.6	2597.3	2579.6
17.5°	2482.7	2490.0	2496.3	2517.3	2553.1	2576.5	2562.8	2549.1	2562.8	2576.5	2553.1
20°	2431.6	2442.1	2452.9	2478.0	2517.5	2543.0	2527.0	2511.0	2527.0	2543.0	2517.5
22.5°	2373.5	2385.5	2399.1	2424.7	2462.3	2486.8	2472.2	2457.6	2472.2	2486.8	2462.3
25°	2277.4	2286.1	2296.4	2319.8	2356.4	2381.4	2371.7	2362.0	2371.7	2381.4	2356.4
27.5°	2140.9	2151.8	2164.6	2184.7	2212.1	2232.0	2229.3	2226.5	2229.3	2232.0	2212.1
30°	2042.1	2054.8	2068.5	2085.7	2106.2	2121.6	2121.6	2121.6	2121.6	2121.6	2106.2
32.5°	1927.0	1940.7	1955.8	1970.6	1985.3	1996.6	1997.9	1999.3	1997.9	1996.6	1985.3
35°	1731.4	1744.7	1759.5	1773.3	1785.8	1793.7	1787.4	1781.1	1787.4	1793.7	1785.8
37.5°	1491.2	1505.0	1521.0	1533.7	1543.2	1549.7	1547.3	1544.9	1547.3	1549.7	1543.2
40°	1314.5	1325.8	1337.2	1348.3	1359.2	1367.2	1366.6	1366.0	1366.6	1367.2	1359.2
42.5°	1117.7	1132.5	1150.8	1165.1	1175.5	1180.4	1168.9	1157.3	1168.9	1180.4	1175.5
45°	823.2	853.3	873.8	880.1	872.1	853.4	802.6	751.8	802.6	853.4	872.1
47.5°	456.8	516.3	574.9	585.6	548.2	504.4	441.1	377.8	441.1	504.4	548.2
50°	244.0	314.8	402.2	413.1	347.4	288.7	251.0	213.3	251.0	288.7	347.4
52.5°	159.9	211.7	276.7	280.5	223.0	175.7	159.1	142.4	159.1	175.7	223.0
55°	78.8	100.2	127.7	128.2	101.9	81.1	76.5	72.0	76.5	81.1	101.9
57.5°	38.2	46.9	56.6	56.3	46.0	36.8	30.6	24.4	30.6	36.8	46.0
60°	11.6	20.1	29.8	30.7	22.7	15.3	9.6	3.9	9.6	15.3	22.7
62.5°	3.2	9.5	17.4	17.6	10.0	4.0	2.4	0.8	2.4	4.0	10.0
65°	0.0	0.4	1.0	1.0	0.4	0.0	0.0	0.0	0.0	0.0	0.4
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	1.4	1.3	1.3	1.2	1.0	0.8	0.5	0.2	0.5	0.7	1.2
90°	6.8	6.4	6.4	6.1	5.2	3.9	2.3	1.0	2.3	3.5	5.8
92.5°	8.1	8.0	7.5	6.9	5.7	5.7	5.6	3.5	6.1	8.7	12.5
95°	7.4	7.4	8.7	11.0	16.1	16.4	11.0	10.0	14.2	20.0	25.1
97.5°	20.0	23.8	29.2	30.3	28.7	21.4	20.5	19.1	26.0	31.7	40.0
100°	37.0	41.9	45.7	38.0	30.0	29.6	27.7	27.1	34.5	39.9	48.0
102.5°	57.9	59.4	46.0	41.6	39.7	38.4	35.4	35.0	42.5	50.0	56.8
105°	62.8	56.4	56.7	56.7	55.4	52.8	47.3	47.0	55.4	64.1	72.5
107.5°	73.9	74.9	76.5	76.1	74.7	67.8	61.3	59.8	67.4	77.8	87.0
110°	88.6	89.5	90.2	89.5	87.3	78.6	70.9	68.6	75.4	86.3	96.3



TEST NUMBER: P1427501

CATALOG NUMBER: SQ2W-BBM-K-025U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	102.7	103.5	104.9	102.9	99.1	89.2	80.4	77.1	83.9	95.1	105.3
115°	125.3	125.3	125.6	124.6	116.9	106.6	95.0	90.2	96.0	106.3	117.6
117.5°	147.5	147.8	146.5	144.0	135.0	123.0	110.0	102.3	106.9	117.8	129.3
120°	161.4	162.0	160.7	156.9	148.2	134.6	119.8	110.8	114.3	125.0	136.6
122.5°	175.8	175.7	174.1	169.7	159.5	145.5	130.9	119.8	121.3	131.2	142.5
125°	195.8	195.5	194.2	189.1	178.4	163.9	146.9	133.3	131.4	139.8	151.4
127.5°	214.9	214.2	212.2	205.9	195.1	181.1	162.3	147.0	142.7	148.0	158.6
130°	228.0	227.1	223.5	216.8	206.1	192.9	173.9	156.5	150.4	153.6	163.0
132.5°	240.7	237.9	234.9	227.6	217.7	204.0	184.7	166.6	158.1	159.6	166.8
135°	256.7	254.1	250.3	243.2	233.8	220.3	201.0	181.3	169.7	168.5	172.6
137.5°	270.8	268.1	263.7	257.6	248.2	236.2	217.6	196.9	182.2	177.9	179.5
140°	279.6	276.3	272.5	266.4	258.0	245.4	227.4	207.4	191.0	184.9	183.9
142.5°	286.8	284.3	280.2	274.6	267.3	254.7	237.2	217.5	200.0	192.1	189.8
145°	297.6	295.7	291.2	286.0	279.9	267.3	251.2	231.6	214.2	203.9	199.0
147.5°	306.8	305.2	301.7	295.6	290.5	278.4	263.7	246.3	228.5	215.7	209.5
150°	312.4	311.1	307.6	301.8	296.6	285.4	271.2	255.1	238.0	224.5	216.4
152.5°	317.8	316.5	312.5	306.7	302.3	291.8	278.9	263.6	246.3	232.7	224.4
155°	325.0	323.4	319.5	314.0	310.2	300.5	288.6	275.1	260.2	246.1	236.7
157.5°	330.7	328.7	325.0	320.3	316.2	307.3	297.0	285.3	272.4	258.8	249.3
160°	334.0	331.7	327.9	323.7	319.8	311.5	302.1	291.5	279.6	267.3	257.0
162.5°	336.3	334.3	329.7	326.0	322.7	315.1	306.2	296.6	286.0	275.3	265.8
165°	338.8	336.6	331.7	328.8	326.0	319.5	311.8	304.0	295.0	286.3	278.6
167.5°	339.0	337.2	332.3	329.5	327.4	321.8	315.6	309.7	302.6	295.8	289.4
170°	338.5	336.9	332.1	329.5	327.9	323.4	317.9	312.7	307.3	301.5	296.3
172.5°	336.7	335.1	330.5	328.5	327.6	323.6	319.2	315.3	310.6	306.4	302.2
175°	332.1	330.8	326.9	325.6	326.0	323.4	320.2	317.9	315.0	312.4	310.2
177.5°	325.3	324.5	321.7	321.7	322.7	321.2	320.2	319.1	317.8	317.1	316.3
180°	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9



TEST NUMBER: P1427501

CATALOG NUMBER: SQ2W-BBM-K-025U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2568.9	2568.9	2568.9	2568.9	2568.9	2568.9	2568.9	2568.9	2568.9	2568.9	2568.9
2.5°	2557.0	2557.7	2568.2	2575.5	2573.2	2570.9	2573.2	2575.5	2568.2	2557.7	2557.0
5°	2555.7	2558.6	2574.0	2585.3	2584.1	2583.0	2584.1	2585.3	2574.0	2558.6	2555.7
7.5°	2561.2	2564.1	2576.8	2585.6	2582.8	2579.9	2582.8	2585.6	2576.8	2564.1	2561.2
10°	2560.4	2561.3	2574.4	2583.6	2580.7	2577.8	2580.7	2583.6	2574.4	2561.3	2560.4
12.5°	2560.5	2556.8	2567.2	2573.7	2568.6	2563.5	2568.6	2573.7	2567.2	2556.8	2560.5
15°	2552.7	2540.2	2541.9	2541.3	2533.9	2526.4	2533.9	2541.3	2541.9	2540.2	2552.7
17.5°	2517.3	2496.3	2490.0	2482.7	2472.2	2461.7	2472.2	2482.7	2490.0	2496.3	2517.3
20°	2478.0	2452.9	2442.1	2431.6	2422.5	2413.4	2422.5	2431.6	2442.1	2452.9	2478.0
22.5°	2424.7	2399.1	2385.5	2373.5	2366.2	2358.9	2366.2	2373.5	2385.5	2399.1	2424.7
25°	2319.8	2296.4	2286.1	2277.4	2273.4	2269.4	2273.4	2277.4	2286.1	2296.4	2319.8
27.5°	2184.7	2164.6	2151.8	2140.9	2135.8	2130.6	2135.8	2140.9	2151.8	2164.6	2184.7
30°	2085.7	2068.5	2054.8	2042.1	2032.4	2022.7	2032.4	2042.1	2054.8	2068.5	2085.7
32.5°	1970.6	1955.8	1940.7	1927.0	1917.3	1907.6	1917.3	1927.0	1940.7	1955.8	1970.6
35°	1773.3	1759.5	1744.7	1731.4	1722.8	1714.3	1722.8	1731.4	1744.7	1759.5	1773.3
37.5°	1533.7	1521.0	1505.0	1491.2	1484.0	1476.8	1484.0	1491.2	1505.0	1521.0	1533.7
40°	1348.3	1337.2	1325.8	1314.5	1303.6	1292.8	1303.6	1314.5	1325.8	1337.2	1348.3
42.5°	1165.1	1150.8	1132.5	1117.7	1113.2	1108.8	1113.2	1117.7	1132.5	1150.8	1165.1
45°	880.1	873.8	853.3	823.2	764.3	705.5	764.3	823.2	853.3	873.8	880.1
47.5°	585.6	574.9	516.3	456.8	394.6	332.3	394.6	456.8	516.3	574.9	585.6
50°	413.1	402.2	314.8	244.0	222.9	201.8	222.9	244.0	314.8	402.2	413.1
52.5°	280.5	276.7	211.7	159.9	148.0	136.0	148.0	159.9	211.7	276.7	280.5
55°	128.2	127.7	100.2	78.8	75.4	72.0	75.4	78.8	100.2	127.7	128.2
57.5°	56.3	56.6	46.9	38.2	32.6	27.0	32.6	38.2	46.9	56.6	56.3
60°	30.7	29.8	20.1	11.6	6.4	1.3	6.4	11.6	20.1	29.8	30.7
62.5°	17.6	17.4	9.5	3.2	1.7	0.3	1.7	3.2	9.5	17.4	17.6
65°	1.0	1.0	0.4	0.0	0.0	0.0	0.0	0.4	1.0	1.0	1.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	1.5	1.9	2.4	2.6	2.9	2.8	2.9	2.6	2.4	1.9	1.5
90°	7.4	9.7	11.9	13.2	14.5	13.8	14.5	13.2	11.9	9.7	7.4
92.5°	14.9	18.7	21.5	23.8	24.8	24.7	24.8	23.8	21.5	18.7	14.9
95°	30.0	34.5	39.0	42.2	44.1	43.5	44.1	42.2	39.0	34.5	30.0
97.5°	46.2	52.2	57.3	60.3	62.2	63.5	62.2	60.3	57.3	52.2	46.2
100°	57.0	62.8	68.6	72.1	75.4	76.7	75.4	72.1	68.6	62.8	57.0
102.5°	65.8	73.4	79.7	83.5	86.2	87.5	86.2	83.5	79.7	73.4	65.8
105°	80.2	88.3	95.0	99.8	102.7	103.7	102.7	99.8	95.0	88.3	80.2
107.5°	94.6	102.9	109.2	114.5	118.1	120.1	118.1	114.5	109.2	102.9	94.6
110°	106.0	112.7	119.5	124.3	127.9	129.2	127.9	124.3	119.5	112.7	106.0



TEST NUMBER: P1427501

CATALOG NUMBER: SQ2W-BBM-K-025U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	115.5	123.0	129.8	134.6	138.7	140.5	138.7	134.6	129.8	123.0	115.5
115°	128.8	138.8	144.9	149.4	152.3	154.0	152.3	149.4	144.9	138.8	128.8
117.5°	139.9	150.3	157.0	160.5	161.9	163.0	161.9	160.5	157.0	150.3	139.9
120°	146.9	156.5	164.3	168.8	170.4	171.0	170.4	168.8	164.3	156.5	146.9
122.5°	153.3	162.5	169.9	175.5	178.1	178.8	178.1	175.5	169.9	162.5	153.3
125°	162.3	171.0	178.8	184.2	187.1	188.7	187.1	184.2	178.8	171.0	162.3
127.5°	170.2	179.6	186.7	191.6	194.5	195.8	194.5	191.6	186.7	179.6	170.2
130°	174.6	184.2	191.3	196.8	199.4	200.7	199.4	196.8	191.3	184.2	174.6
132.5°	177.9	188.1	195.4	200.4	203.2	204.5	203.2	200.4	195.4	188.1	177.9
135°	182.0	192.6	200.3	205.2	207.7	209.0	207.7	205.2	200.3	192.6	182.0
137.5°	185.5	195.2	203.2	208.3	210.6	211.5	210.6	208.3	203.2	195.2	185.5
140°	188.1	196.5	204.5	209.4	211.9	212.3	211.9	209.4	204.5	196.5	188.1
142.5°	191.4	198.0	205.0	209.9	212.4	213.0	212.4	209.9	205.0	198.0	191.4
145°	197.4	201.3	206.1	210.6	212.9	213.5	212.9	210.6	206.1	201.3	197.4
147.5°	205.0	206.2	208.7	211.7	213.9	214.3	213.9	211.7	208.7	206.2	205.0
150°	210.6	210.3	211.3	213.2	215.2	214.8	215.2	213.2	211.3	210.3	210.6
152.5°	217.1	215.2	215.2	216.1	217.0	216.9	217.0	216.1	215.2	215.2	217.1
155°	228.0	224.5	222.6	221.9	221.9	221.6	221.9	221.9	222.6	224.5	228.0
157.5°	240.1	235.1	232.2	230.7	230.2	229.5	230.2	230.7	232.2	235.1	240.1
160°	248.3	242.9	240.0	237.4	236.4	235.4	236.4	237.4	240.0	242.9	248.3
162.5°	256.1	250.8	247.7	245.4	244.4	242.9	244.4	245.4	247.7	250.8	256.1
165°	268.6	263.1	259.6	257.7	256.4	255.1	256.4	257.7	259.6	263.1	268.6
167.5°	281.2	275.2	272.9	270.7	269.5	267.1	269.5	270.7	272.9	275.2	281.2
170°	288.9	283.4	282.1	280.2	278.0	275.4	278.0	280.2	282.1	283.4	288.9
172.5°	295.6	291.9	290.6	288.7	288.0	285.9	288.0	288.7	290.6	291.9	295.6
175°	305.3	302.4	302.4	302.1	301.1	299.2	301.1	302.1	302.4	302.4	305.3
177.5°	313.5	311.9	312.9	312.9	312.7	310.9	312.7	312.9	312.9	311.9	313.5
180°	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9



TEST NUMBER: P1427501

CATALOG NUMBER: SQ2W-BBM-K-025U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2568.9	2568.9	2568.9	2568.9
2.5°	2566.1	2573.8	2577.0	2580.2
5°	2565.4	2573.4	2576.3	2579.1
7.5°	2568.1	2573.7	2575.7	2577.6
10°	2571.9	2580.6	2581.1	2581.7
12.5°	2578.4	2590.8	2587.3	2583.8
15°	2579.6	2597.3	2587.6	2577.8
17.5°	2553.1	2576.5	2562.8	2549.1
20°	2517.5	2543.0	2527.0	2511.0
22.5°	2462.3	2486.8	2472.2	2457.6
25°	2356.4	2381.4	2371.7	2362.0
27.5°	2212.1	2232.0	2229.3	2226.5
30°	2106.2	2121.6	2121.6	2121.6
32.5°	1985.3	1996.6	1997.9	1999.3
35°	1785.8	1793.7	1787.4	1781.1
37.5°	1543.2	1549.7	1547.3	1544.9
40°	1359.2	1367.2	1366.6	1366.0
42.5°	1175.5	1180.4	1168.9	1157.3
45°	872.1	853.4	802.6	751.8
47.5°	548.2	504.4	441.1	377.8
50°	347.4	288.7	251.0	213.3
52.5°	223.0	175.7	159.1	142.4
55°	101.9	81.1	76.5	72.0
57.5°	46.0	36.8	30.6	24.4
60°	22.7	15.3	9.6	3.9
62.5°	10.0	4.0	2.4	0.8
65°	0.4	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	1.2	0.7	0.5	0.2
90°	5.8	3.5	2.3	1.0
92.5°	12.5	8.7	6.1	3.5
95°	25.1	20.0	14.2	10.0
97.5°	40.0	31.7	26.0	19.1
100°	48.0	39.9	34.5	27.1
102.5°	56.8	50.0	42.5	35.0
105°	72.5	64.1	55.4	47.0
107.5°	87.0	77.8	67.4	59.8
110°	96.3	86.3	75.4	68.6



TEST NUMBER: P1427501

CATALOG NUMBER: SQ2W-BBM-K-025U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	105.3	95.1	83.9	77.1
115°	117.6	106.3	96.0	90.2
117.5°	129.3	117.8	106.9	102.3
120°	136.6	125.0	114.3	110.8
122.5°	142.5	131.2	121.3	119.8
125°	151.4	139.8	131.4	133.3
127.5°	158.6	148.0	142.7	147.0
130°	163.0	153.6	150.4	156.5
132.5°	166.8	159.6	158.1	166.6
135°	172.6	168.5	169.7	181.3
137.5°	179.5	177.9	182.2	196.9
140°	183.9	184.9	191.0	207.4
142.5°	189.8	192.1	200.0	217.5
145°	199.0	203.9	214.2	231.6
147.5°	209.5	215.7	228.5	246.3
150°	216.4	224.5	238.0	255.1
152.5°	224.4	232.7	246.3	263.6
155°	236.7	246.1	260.2	275.1
157.5°	249.3	258.8	272.4	285.3
160°	257.0	267.3	279.6	291.5
162.5°	265.8	275.3	286.0	296.6
165°	278.6	286.3	295.0	304.0
167.5°	289.4	295.8	302.6	309.7
170°	296.3	301.5	307.3	312.7
172.5°	302.2	306.4	310.6	315.3
175°	310.2	312.4	315.0	317.9
177.5°	316.3	317.1	317.8	319.1
180°	318.9	318.9	318.9	318.9



TEST NUMBER: P1427501
 CATALOG NUMBER: SQ2W-BBM-K-025U-100D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	1.22	2.12	1.90	2.78	3.55	1.44	2.34	2.12	3.01	3.77
	3H	1.04	1.83	1.73	2.51	3.31	1.26	2.05	1.95	2.73	3.53
	4H	0.94	1.68	1.65	2.37	3.19	1.16	1.90	1.87	2.59	3.41
	6H	0.83	1.51	1.56	2.21	3.04	1.06	1.73	1.78	2.43	3.26
	8H	0.78	1.42	1.51	2.13	2.97	1.00	1.64	1.73	2.35	3.19
	12H	0.72	1.33	1.46	2.04	2.89	0.94	1.55	1.68	2.26	3.12
4H	2H	0.95	1.69	1.66	2.37	3.20	1.17	1.91	1.88	2.60	3.42
	3H	0.76	1.36	1.48	2.09	2.92	0.98	1.58	1.70	2.31	3.14
	4H	0.65	1.19	1.39	1.92	2.78	0.87	1.41	1.61	2.14	3.01
	6H	0.54	1.00	1.30	1.76	2.64	0.76	1.22	1.52	1.98	2.86
	8H	0.48	0.91	1.24	1.65	2.54	0.70	1.13	1.46	1.88	2.76
	12H	0.41	0.79	1.19	1.56	2.45	0.63	1.01	1.41	1.78	2.67
8H	4H	0.48	0.91	1.24	1.65	2.54	0.70	1.13	1.46	1.88	2.76
	6H	0.36	0.70	1.14	1.50	2.39	0.58	0.93	1.36	1.72	2.61
	8H	0.29	0.60	1.09	1.40	2.30	0.51	0.82	1.31	1.62	2.52
	12H	0.23	0.50	1.02	1.28	2.25	0.45	0.72	1.25	1.50	2.47
12H	4H	0.41	0.79	1.19	1.56	2.45	0.63	1.01	1.41	1.78	2.67
	6H	0.29	0.60	1.09	1.40	2.30	0.51	0.82	1.31	1.62	2.52
	8H	0.23	0.50	1.02	1.28	2.25	0.45	0.72	1.25	1.50	2.47