

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427522

Luminaire Tested: SQ2W-BBM-K-075U-075D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1427522  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-BBM-K-075U-075D-L930-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - BLACK DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5655.1 lumens  
Efficiency: N/A  
Efficacy: 110.5 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.17 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 51.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1427522

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L930-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1427522

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L930-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				
1	100	96	93	90	92	89	87	84	76	75	73	64	63	62	53	53	52	47				
2	93	87	82	77	86	81	76	73	70	66	64	59	57	55	50	48	47	43				
3	86	78	72	67	80	73	68	63	63	59	56	54	52	49	46	44	43	39				
4	80	71	64	59	74	66	60	56	58	53	50	50	47	44	43	40	39	35				
5	74	64	57	52	69	60	54	50	53	48	45	46	43	40	40	37	35	32				
6	69	59	51	46	64	55	49	44	49	44	40	42	39	36	37	34	32	29				
7	64	54	46	42	60	50	44	40	45	40	36	39	36	33	34	31	29	27				
8	60	49	42	37	56	46	40	36	41	36	33	36	33	30	32	29	27	25				
9	56	45	39	34	53	43	37	33	38	33	30	34	30	27	30	27	25	23				
10	53	42	35	31	49	40	34	30	35	31	27	32	28	25	28	25	23	21				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	31041	31041	31041	31041
5°	31285	31332	31285	31332
10°	31678	31632	31678	31632
15°	32250	31607	32250	31607
20°	32291	31035	32291	31035
25°	31493	30258	31493	30258
30°	29604	28224	29604	28224
35°	26276	25288	26276	25288
40°	21549	20394	21549	20394
45°	12848	12056	12848	12056
50°	4011	3793	4011	3793
55°	1517	1517	1517	1517
60°	94	32	94	32
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 15040 cd/sqm



TEST NUMBER: P1427522

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L930-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.8	3.3
10°-20°	538.5	9.5
20°-30°	792.2	14.0
30°-40°	809.7	14.3
40°-50°	466.4	8.2
50°-60°	80.3	1.4
60°-70°	2.9	0.1
70°-80°	0.0	0.0
80°-90°	5.0	0.1
90°-100°	75.7	1.3
100°-110°	220.8	3.9
110°-120°	360.3	6.4
120°-130°	457.2	8.1
130°-140°	489.2	8.7
140°-150°	456.8	8.1
150°-160°	375.9	6.6
160°-170°	252.1	4.5
170°-180°	89.5	1.6
0°-30°	1514.5	26.8
0°-40°	2324.3	41.1
0°-60°	2871.0	50.8
0°-90°	2878.9	50.9
90°-120°	656.7	11.6
90°-150°	2059.9	36.4
90°-180°	2777.0	49.1
0°-180°	5655.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1923	1923	1923	1923	1923	
5°	1930	1933	1930	1933	1930	184
15°	1929	1891	1929	1891	1929	543
25°	1768	1698	1768	1698	1768	807
35°	1333	1283	1333	1283	1333	823
45°	563	528	563	528	563	435
55°	54	54	54	54	54	57
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	3	21	3	41	3	2
95°	30	22	30	130	30	36
105°	140	225	140	309	140	149
115°	269	373	269	459	269	265
125°	398	591	398	563	398	356
135°	541	773	541	624	541	418
145°	691	892	691	637	691	432
155°	820	968	820	661	820	377
165°	907	1010	907	761	907	255
175°	948	989	948	893	948	90
180°	951	951	951	951	951	



TEST NUMBER: P1427522

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6
2.5°	1931.1	1928.7	1926.3	1920.6	1913.7	1914.3	1922.1	1927.6	1925.9	1924.2	1925.9
5°	1930.3	1928.2	1926.1	1920.1	1912.8	1914.9	1926.5	1934.9	1934.1	1933.2	1934.1
7.5°	1929.2	1927.7	1926.3	1922.1	1916.9	1919.1	1928.6	1935.2	1933.0	1930.9	1933.0
10°	1932.2	1931.8	1931.4	1924.9	1916.3	1917.0	1926.8	1933.6	1931.5	1929.4	1931.5
12.5°	1933.8	1936.4	1939.1	1929.7	1916.4	1913.6	1921.4	1926.3	1922.4	1918.6	1922.4
15°	1929.4	1936.6	1943.9	1930.6	1910.6	1901.2	1902.4	1902.0	1896.4	1890.9	1896.4
17.5°	1907.8	1918.1	1928.3	1910.8	1884.1	1868.3	1863.6	1858.1	1850.3	1842.4	1850.3
20°	1879.4	1891.3	1903.3	1884.2	1854.7	1835.9	1827.7	1819.9	1813.1	1806.3	1813.1
22.5°	1839.3	1850.3	1861.2	1842.9	1814.7	1795.6	1785.4	1776.4	1770.9	1765.5	1770.9
25°	1767.8	1775.0	1782.3	1763.6	1736.3	1718.7	1711.0	1704.5	1701.5	1698.5	1701.5
27.5°	1666.4	1668.5	1670.5	1655.6	1635.1	1620.1	1610.5	1602.4	1598.5	1594.7	1598.5
30°	1587.9	1587.9	1587.9	1576.4	1561.0	1548.2	1537.9	1528.4	1521.1	1513.9	1521.1
32.5°	1496.4	1495.3	1494.3	1485.8	1474.9	1463.8	1452.5	1442.2	1435.0	1427.7	1435.0
35°	1333.1	1337.8	1342.5	1336.6	1327.2	1316.9	1305.8	1295.9	1289.4	1283.0	1289.4
37.5°	1156.3	1158.1	1159.9	1155.0	1147.9	1138.4	1126.4	1116.1	1110.7	1105.3	1110.7
40°	1022.4	1022.8	1023.2	1017.3	1009.1	1000.8	992.3	983.8	975.7	967.6	975.7
42.5°	866.2	874.8	883.5	879.8	872.0	861.3	847.6	836.5	833.2	829.8	833.2
45°	562.7	600.7	638.7	652.7	658.7	654.0	638.6	616.1	572.1	528.0	572.1
47.5°	282.8	330.1	377.5	410.3	438.3	430.3	386.4	341.9	295.3	248.7	295.3
50°	159.7	187.9	216.1	260.0	309.2	301.0	235.6	182.6	166.8	151.0	166.8
52.5°	106.6	119.0	131.5	166.9	209.9	207.1	158.4	119.7	110.7	101.8	110.7
55°	53.9	57.3	60.7	76.3	96.0	95.5	75.0	59.0	56.4	53.9	56.4
57.5°	18.3	22.9	27.5	34.4	42.1	42.3	35.1	28.6	24.4	20.2	24.4
60°	2.9	7.2	11.4	17.0	23.0	22.3	15.1	8.7	4.8	1.0	4.8
62.5°	0.6	1.8	3.0	7.5	13.1	13.0	7.1	2.4	1.3	0.2	1.3
65°	0.0	0.0	0.0	0.3	0.7	0.7	0.3	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.6	1.3	2.3	3.1	3.7	3.8	3.8	4.0	4.2	4.2	4.2
90°	2.9	6.7	11.5	15.4	18.3	19.2	19.2	20.2	21.1	21.1	21.1
92.5°	10.6	16.7	16.9	16.9	20.6	22.3	23.8	24.0	25.0	25.0	25.0
95°	29.8	32.7	49.0	48.0	32.7	25.9	22.1	22.1	22.1	22.1	22.1
97.5°	56.9	61.1	63.8	85.5	90.3	87.2	71.1	59.8	53.4	50.5	53.4
100°	80.7	82.6	88.4	89.4	113.4	136.4	124.9	110.5	105.7	102.8	105.7
102.5°	104.5	105.7	114.5	118.6	124.1	137.2	177.2	172.8	169.5	168.9	169.5
105°	140.3	141.2	157.6	165.3	169.1	169.1	168.1	187.4	218.1	224.8	218.1
107.5°	178.5	182.9	202.2	222.7	227.1	228.3	223.3	220.4	219.3	220.0	219.3
110°	204.7	211.4	234.4	260.4	267.1	269.0	267.1	264.2	262.3	262.3	262.3



TEST NUMBER: P1427522

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	230.0	239.8	266.0	295.7	307.1	312.8	308.6	306.5	304.6	306.1	304.6
115°	269.0	283.4	318.0	348.8	371.8	374.7	373.8	373.8	372.8	372.8	372.8
117.5°	305.2	328.2	367.0	402.8	429.5	437.2	441.0	439.9	438.7	440.6	438.7
120°	330.5	357.4	401.6	442.0	467.9	479.4	483.3	481.4	483.3	481.4	483.3
122.5°	357.4	390.5	433.9	475.8	506.3	519.4	524.0	524.4	524.8	523.6	524.8
125°	397.8	438.1	489.1	532.3	564.0	579.4	583.2	584.2	586.1	590.9	586.1
127.5°	438.5	484.2	540.2	581.9	614.3	633.0	638.9	641.0	645.1	647.2	645.1
130°	467.0	518.8	575.5	614.9	646.6	666.8	677.4	680.3	685.1	684.1	685.1
132.5°	496.9	551.1	608.6	649.5	678.9	700.6	709.7	717.9	719.6	721.0	719.6
135°	540.9	599.5	657.2	697.5	725.4	746.5	758.1	765.8	770.6	773.4	770.6
137.5°	587.2	649.1	704.5	740.4	768.5	786.7	799.8	807.8	812.8	815.1	812.8
140°	618.8	678.3	732.1	769.6	794.6	812.8	824.4	834.0	839.7	839.7	839.7
142.5°	648.7	707.5	759.8	797.3	819.2	835.9	848.2	855.5	862.0	862.0	862.0
145°	690.8	749.4	797.5	834.9	853.2	868.6	882.0	887.8	891.6	891.6	891.6
147.5°	734.8	786.7	830.5	866.5	881.8	899.9	910.5	915.1	919.9	917.8	919.9
150°	761.0	809.0	851.3	884.9	900.3	917.6	928.1	932.0	936.8	933.9	936.8
152.5°	786.3	832.1	870.5	901.8	914.9	932.2	944.3	948.1	951.4	949.3	951.4
155°	820.5	860.9	896.4	925.3	936.8	953.1	964.6	969.5	973.3	968.5	973.3
157.5°	851.1	885.9	916.8	943.3	955.6	969.6	980.4	986.4	990.2	988.1	990.2
160°	869.5	901.2	929.1	954.1	965.6	978.1	989.6	996.4	1000.2	997.3	1000.2
162.5°	884.9	913.5	939.9	962.5	972.5	983.5	997.3	1003.3	1007.1	1003.5	1007.1
165°	907.0	930.1	953.1	972.3	981.0	989.6	1004.0	1010.8	1013.7	1009.8	1013.7
167.5°	923.7	941.4	960.0	976.6	982.9	991.4	1005.8	1011.3	1015.0	1010.2	1015.0
170°	932.9	948.3	964.6	978.1	982.9	990.6	1005.0	1009.8	1012.7	1007.9	1012.7
172.5°	940.6	952.2	965.4	977.3	979.8	986.0	999.6	1004.4	1006.5	1002.5	1006.5
175°	948.3	955.0	964.6	972.3	971.4	975.2	986.7	990.6	994.4	988.7	994.4
177.5°	952.0	955.0	958.1	962.7	959.7	959.7	968.1	970.4	971.2	968.1	971.2
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1427522

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6
2.5°	1927.6	1922.1	1914.3	1913.7	1920.6	1926.3	1928.7	1931.1	1928.7	1926.3	1920.6
5°	1934.9	1926.5	1914.9	1912.8	1920.1	1926.1	1928.2	1930.3	1928.2	1926.1	1920.1
7.5°	1935.2	1928.6	1919.1	1916.9	1922.1	1926.3	1927.7	1929.2	1927.7	1926.3	1922.1
10°	1933.6	1926.8	1917.0	1916.3	1924.9	1931.4	1931.8	1932.2	1931.8	1931.4	1924.9
12.5°	1926.3	1921.4	1913.6	1916.4	1929.7	1939.1	1936.4	1933.8	1936.4	1939.1	1929.7
15°	1902.0	1902.4	1901.2	1910.6	1930.6	1943.9	1936.6	1929.4	1936.6	1943.9	1930.6
17.5°	1858.1	1863.6	1868.3	1884.1	1910.8	1928.3	1918.1	1907.8	1918.1	1928.3	1910.8
20°	1819.9	1827.7	1835.9	1854.7	1884.2	1903.3	1891.3	1879.4	1891.3	1903.3	1884.2
22.5°	1776.4	1785.4	1795.6	1814.7	1842.9	1861.2	1850.3	1839.3	1850.3	1861.2	1842.9
25°	1704.5	1711.0	1718.7	1736.3	1763.6	1782.3	1775.0	1767.8	1775.0	1782.3	1763.6
27.5°	1602.4	1610.5	1620.1	1635.1	1655.6	1670.5	1668.5	1666.4	1668.5	1670.5	1655.6
30°	1528.4	1537.9	1548.2	1561.0	1576.4	1587.9	1587.9	1587.9	1587.9	1587.9	1576.4
32.5°	1442.2	1452.5	1463.8	1474.9	1485.8	1494.3	1495.3	1496.4	1495.3	1494.3	1485.8
35°	1295.9	1305.8	1316.9	1327.2	1336.6	1342.5	1337.8	1333.1	1337.8	1342.5	1336.6
37.5°	1116.1	1126.4	1138.4	1147.9	1155.0	1159.9	1158.1	1156.3	1158.1	1159.9	1155.0
40°	983.8	992.3	1000.8	1009.1	1017.3	1023.2	1022.8	1022.4	1022.8	1023.2	1017.3
42.5°	836.5	847.6	861.3	872.0	879.8	883.5	874.8	866.2	874.8	883.5	879.8
45°	616.1	638.6	654.0	658.7	652.7	638.7	600.7	562.7	600.7	638.7	652.7
47.5°	341.9	386.4	430.3	438.3	410.3	377.5	330.1	282.8	330.1	377.5	410.3
50°	182.6	235.6	301.0	309.2	260.0	216.1	187.9	159.7	187.9	216.1	260.0
52.5°	119.7	158.4	207.1	209.9	166.9	131.5	119.0	106.6	119.0	131.5	166.9
55°	59.0	75.0	95.5	96.0	76.3	60.7	57.3	53.9	57.3	60.7	76.3
57.5°	28.6	35.1	42.3	42.1	34.4	27.5	22.9	18.3	22.9	27.5	34.4
60°	8.7	15.1	22.3	23.0	17.0	11.4	7.2	2.9	7.2	11.4	17.0
62.5°	2.4	7.1	13.0	13.1	7.5	3.0	1.8	0.6	1.8	3.0	7.5
65°	0.0	0.3	0.7	0.7	0.3	0.0	0.0	0.0	0.0	0.0	0.3
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	4.0	3.8	3.8	3.7	3.1	2.3	1.3	0.6	1.3	2.1	3.5
90°	20.2	19.2	19.2	18.3	15.4	11.5	6.7	2.9	6.7	10.6	17.3
92.5°	24.0	23.8	22.3	20.6	16.9	16.9	16.7	10.6	18.3	25.9	37.3
95°	22.1	22.1	25.9	32.7	48.0	49.0	32.7	29.8	42.3	59.6	74.9
97.5°	59.8	71.1	87.2	90.3	85.5	63.8	61.1	56.9	77.4	94.5	119.3
100°	110.5	124.9	136.4	113.4	89.4	88.4	82.6	80.7	102.8	119.1	143.2
102.5°	172.8	177.2	137.2	124.1	118.6	114.5	105.7	104.5	126.6	149.1	169.3
105°	187.4	168.1	169.1	169.1	165.3	157.6	141.2	140.3	165.3	191.2	216.2
107.5°	220.4	223.3	228.3	227.1	222.7	202.2	182.9	178.5	201.0	232.1	259.6
110°	264.2	267.1	269.0	267.1	260.4	234.4	211.4	204.7	224.8	257.5	287.3



TEST NUMBER: P1427522

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	306.5	308.6	312.8	307.1	295.7	266.0	239.8	230.0	250.2	283.6	314.2
115°	373.8	373.8	374.7	371.8	348.8	318.0	283.4	269.0	286.3	317.1	350.7
117.5°	439.9	441.0	437.2	429.5	402.8	367.0	328.2	305.2	318.8	351.3	385.9
120°	481.4	483.3	479.4	467.9	442.0	401.6	357.4	330.5	341.1	372.8	407.4
122.5°	524.4	524.0	519.4	506.3	475.8	433.9	390.5	357.4	361.8	391.2	425.1
125°	584.2	583.2	579.4	564.0	532.3	489.1	438.1	397.8	392.0	417.0	451.6
127.5°	641.0	638.9	633.0	614.3	581.9	540.2	484.2	438.5	425.6	441.4	473.1
130°	680.3	677.4	666.8	646.6	614.9	575.5	518.8	467.0	448.7	458.3	486.2
132.5°	717.9	709.7	700.6	678.9	649.5	608.6	551.1	496.9	471.8	476.0	497.7
135°	765.8	758.1	746.5	725.4	697.5	657.2	599.5	540.9	506.3	502.5	515.0
137.5°	807.8	799.8	786.7	768.5	740.4	704.5	649.1	587.2	543.6	530.7	535.6
140°	834.0	824.4	812.8	794.6	769.6	732.1	678.3	618.8	569.8	551.5	548.6
142.5°	855.5	848.2	835.9	819.2	797.3	759.8	707.5	648.7	596.7	573.0	566.3
145°	887.8	882.0	868.6	853.2	834.9	797.5	749.4	690.8	638.9	608.2	593.8
147.5°	915.1	910.5	899.9	881.8	866.5	830.5	786.7	734.8	681.6	643.5	624.9
150°	932.0	928.1	917.6	900.3	884.9	851.3	809.0	761.0	710.0	669.7	645.7
152.5°	948.1	944.3	932.2	914.9	901.8	870.5	832.1	786.3	734.6	694.3	669.5
155°	969.5	964.6	953.1	936.8	925.3	896.4	860.9	820.5	776.3	734.1	706.2
157.5°	986.4	980.4	969.6	955.6	943.3	916.8	885.9	851.1	812.5	772.1	743.7
160°	996.4	989.6	978.1	965.6	954.1	929.1	901.2	869.5	834.0	797.5	766.7
162.5°	1003.3	997.3	983.5	972.5	962.5	939.9	913.5	884.9	853.2	821.3	792.9
165°	1010.8	1004.0	989.6	981.0	972.3	953.1	930.1	907.0	880.1	854.2	831.1
167.5°	1011.3	1005.8	991.4	982.9	976.6	960.0	941.4	923.7	902.8	882.4	863.2
170°	1009.8	1005.0	990.6	982.9	978.1	964.6	948.3	932.9	916.6	899.3	883.9
172.5°	1004.4	999.6	986.0	979.8	977.3	965.4	952.2	940.6	926.6	913.9	901.6
175°	990.6	986.7	975.2	971.4	972.3	964.6	955.0	948.3	939.7	932.0	925.3
177.5°	970.4	968.1	959.7	959.7	962.7	958.1	955.0	952.0	948.1	945.8	943.5
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1427522

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6
2.5°	1913.7	1914.3	1922.1	1927.6	1925.9	1924.2	1925.9	1927.6	1922.1	1914.3	1913.7
5°	1912.8	1914.9	1926.5	1934.9	1934.1	1933.2	1934.1	1934.9	1926.5	1914.9	1912.8
7.5°	1916.9	1919.1	1928.6	1935.2	1933.0	1930.9	1933.0	1935.2	1928.6	1919.1	1916.9
10°	1916.3	1917.0	1926.8	1933.6	1931.5	1929.4	1931.5	1933.6	1926.8	1917.0	1916.3
12.5°	1916.4	1913.6	1921.4	1926.3	1922.4	1918.6	1922.4	1926.3	1921.4	1913.6	1916.4
15°	1910.6	1901.2	1902.4	1902.0	1896.4	1890.9	1896.4	1902.0	1902.4	1901.2	1910.6
17.5°	1884.1	1868.3	1863.6	1858.1	1850.3	1842.4	1850.3	1858.1	1863.6	1868.3	1884.1
20°	1854.7	1835.9	1827.7	1819.9	1813.1	1806.3	1813.1	1819.9	1827.7	1835.9	1854.7
22.5°	1814.7	1795.6	1785.4	1776.4	1770.9	1765.5	1770.9	1776.4	1785.4	1795.6	1814.7
25°	1736.3	1718.7	1711.0	1704.5	1701.5	1698.5	1701.5	1704.5	1711.0	1718.7	1736.3
27.5°	1635.1	1620.1	1610.5	1602.4	1598.5	1594.7	1598.5	1602.4	1610.5	1620.1	1635.1
30°	1561.0	1548.2	1537.9	1528.4	1521.1	1513.9	1521.1	1528.4	1537.9	1548.2	1561.0
32.5°	1474.9	1463.8	1452.5	1442.2	1435.0	1427.7	1435.0	1442.2	1452.5	1463.8	1474.9
35°	1327.2	1316.9	1305.8	1295.9	1289.4	1283.0	1289.4	1295.9	1305.8	1316.9	1327.2
37.5°	1147.9	1138.4	1126.4	1116.1	1110.7	1105.3	1110.7	1116.1	1126.4	1138.4	1147.9
40°	1009.1	1000.8	992.3	983.8	975.7	967.6	975.7	983.8	992.3	1000.8	1009.1
42.5°	872.0	861.3	847.6	836.5	833.2	829.8	833.2	836.5	847.6	861.3	872.0
45°	658.7	654.0	638.6	616.1	572.1	528.0	572.1	616.1	638.6	654.0	658.7
47.5°	438.3	430.3	386.4	341.9	295.3	248.7	295.3	341.9	386.4	430.3	438.3
50°	309.2	301.0	235.6	182.6	166.8	151.0	166.8	182.6	235.6	301.0	309.2
52.5°	209.9	207.1	158.4	119.7	110.7	101.8	110.7	119.7	158.4	207.1	209.9
55°	96.0	95.5	75.0	59.0	56.4	53.9	56.4	75.0	95.5	96.0	
57.5°	42.1	42.3	35.1	28.6	24.4	20.2	24.4	35.1	42.3	42.1	
60°	23.0	22.3	15.1	8.7	4.8	1.0	4.8	15.1	22.3	23.0	
62.5°	13.1	13.0	7.1	2.4	1.3	0.2	1.3	7.1	13.0	13.1	
65°	0.7	0.7	0.3	0.0	0.0	0.0	0.0	0.3	0.7	0.7	
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
87.5°	4.4	5.8	7.1	7.9	8.6	8.3	8.6	7.9	7.1	5.8	4.4
90°	22.1	28.8	35.5	39.4	43.2	41.3	43.2	39.4	35.5	28.8	22.1
92.5°	44.4	55.7	64.0	70.9	74.0	73.6	74.0	70.9	64.0	55.7	44.4
95°	89.4	102.8	116.3	125.9	131.6	129.7	131.6	125.9	116.3	102.8	89.4
97.5°	137.8	155.8	170.8	179.9	185.6	189.5	185.6	179.9	170.8	155.8	137.8
100°	170.1	187.4	204.7	215.2	224.8	228.7	224.8	215.2	204.7	187.4	170.1
102.5°	196.2	218.9	237.7	249.0	257.1	261.0	257.1	249.0	237.7	218.9	196.2
105°	239.2	263.3	283.4	297.8	306.5	309.4	306.5	297.8	283.4	263.3	239.2
107.5°	282.3	307.1	325.7	341.7	352.2	358.4	352.2	341.7	325.7	307.1	282.3
110°	316.1	336.3	356.5	370.9	381.4	385.3	381.4	370.9	356.5	336.3	316.1



TEST NUMBER: P1427522

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	344.5	367.0	387.2	401.6	413.7	419.1	413.7	401.6	387.2	367.0	344.5
115°	384.3	414.1	432.4	445.8	454.5	459.3	454.5	445.8	432.4	414.1	384.3
117.5°	417.4	448.5	468.5	478.9	482.9	486.4	482.9	478.9	468.5	448.5	417.4
120°	438.1	467.0	490.0	503.5	508.3	510.2	508.3	503.5	490.0	467.0	438.1
122.5°	457.3	484.6	506.9	523.4	531.3	533.2	531.3	523.4	506.9	484.6	457.3
125°	484.2	510.2	533.2	549.6	558.2	563.0	558.2	549.6	533.2	510.2	484.2
127.5°	507.7	535.7	556.9	571.7	580.1	584.0	580.1	571.7	556.9	535.7	507.7
130°	520.8	549.6	570.7	587.1	594.7	598.6	594.7	587.1	570.7	549.6	520.8
132.5°	530.7	561.1	583.0	597.8	606.3	610.1	606.3	597.8	583.0	561.1	530.7
135°	542.9	574.6	597.6	612.0	619.7	623.6	619.7	612.0	597.6	574.6	542.9
137.5°	553.4	582.2	606.3	621.4	628.4	630.9	628.4	621.4	606.3	582.2	553.4
140°	561.1	586.1	610.1	624.5	632.2	633.2	632.2	624.5	610.1	586.1	561.1
142.5°	571.1	590.7	611.6	626.1	633.7	635.5	633.7	626.1	611.6	590.7	571.1
145°	589.0	600.5	614.9	628.4	635.1	637.0	635.1	628.4	614.9	600.5	589.0
147.5°	611.5	615.1	622.6	631.4	638.0	639.3	638.0	631.4	622.6	615.1	611.5
150°	628.4	627.4	630.3	636.1	641.8	640.9	641.8	636.1	630.3	627.4	628.4
152.5°	647.6	642.0	641.8	644.5	647.2	647.0	647.2	644.5	641.8	642.0	647.6
155°	680.3	669.7	663.9	662.0	662.0	661.0	662.0	662.0	663.9	669.7	680.3
157.5°	716.2	701.4	692.7	688.1	686.8	684.7	686.8	688.1	692.7	701.4	716.2
160°	740.8	724.4	715.8	708.1	705.2	702.3	705.2	708.1	715.8	724.4	740.8
162.5°	763.8	748.3	738.9	731.9	729.1	724.6	729.1	731.9	738.9	748.3	763.8
165°	801.3	785.0	774.4	768.6	764.8	761.0	764.8	768.6	774.4	785.0	801.3
167.5°	838.8	820.9	814.0	807.5	803.8	796.9	803.8	807.5	814.0	820.9	838.8
170°	861.8	845.5	841.7	835.9	829.2	821.5	829.2	835.9	841.7	845.5	861.8
172.5°	881.8	870.9	867.0	861.3	859.2	853.0	859.2	861.3	867.0	870.9	881.8
175°	910.8	902.2	902.2	901.2	898.4	892.6	898.4	901.2	902.2	902.2	910.8
177.5°	935.1	930.4	933.5	933.5	932.8	927.4	932.8	933.5	933.5	930.4	935.1
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1427522

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	1922.6	1922.6	1922.6	1922.6
2.5°	1920.6	1926.3	1928.7	1931.1
5°	1920.1	1926.1	1928.2	1930.3
7.5°	1922.1	1926.3	1927.7	1929.2
10°	1924.9	1931.4	1931.8	1932.2
12.5°	1929.7	1939.1	1936.4	1933.8
15°	1930.6	1943.9	1936.6	1929.4
17.5°	1910.8	1928.3	1918.1	1907.8
20°	1884.2	1903.3	1891.3	1879.4
22.5°	1842.9	1861.2	1850.3	1839.3
25°	1763.6	1782.3	1775.0	1767.8
27.5°	1655.6	1670.5	1668.5	1666.4
30°	1576.4	1587.9	1587.9	1587.9
32.5°	1485.8	1494.3	1495.3	1496.4
35°	1336.6	1342.5	1337.8	1333.1
37.5°	1155.0	1159.9	1158.1	1156.3
40°	1017.3	1023.2	1022.8	1022.4
42.5°	879.8	883.5	874.8	866.2
45°	652.7	638.7	600.7	562.7
47.5°	410.3	377.5	330.1	282.8
50°	260.0	216.1	187.9	159.7
52.5°	166.9	131.5	119.0	106.6
55°	76.3	60.7	57.3	53.9
57.5°	34.4	27.5	22.9	18.3
60°	17.0	11.4	7.2	2.9
62.5°	7.5	3.0	1.8	0.6
65°	0.3	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	3.5	2.1	1.3	0.6
90°	17.3	10.6	6.7	2.9
92.5°	37.3	25.9	18.3	10.6
95°	74.9	59.6	42.3	29.8
97.5°	119.3	94.5	77.4	56.9
100°	143.2	119.1	102.8	80.7
102.5°	169.3	149.1	126.6	104.5
105°	216.2	191.2	165.3	140.3
107.5°	259.6	232.1	201.0	178.5
110°	287.3	257.5	224.8	204.7

TEST NUMBER: P1427522

CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	314.2	283.6	250.2	230.0
115°	350.7	317.1	286.3	269.0
117.5°	385.9	351.3	318.8	305.2
120°	407.4	372.8	341.1	330.5
122.5°	425.1	391.2	361.8	357.4
125°	451.6	417.0	392.0	397.8
127.5°	473.1	441.4	425.6	438.5
130°	486.2	458.3	448.7	467.0
132.5°	497.7	476.0	471.8	496.9
135°	515.0	502.5	506.3	540.9
137.5°	535.6	530.7	543.6	587.2
140°	548.6	551.5	569.8	618.8
142.5°	566.3	573.0	596.7	648.7
145°	593.8	608.2	638.9	690.8
147.5°	624.9	643.5	681.6	734.8
150°	645.7	669.7	710.0	761.0
152.5°	669.5	694.3	734.6	786.3
155°	706.2	734.1	776.3	820.5
157.5°	743.7	772.1	812.5	851.1
160°	766.7	797.5	834.0	869.5
162.5°	792.9	821.3	853.2	884.9
165°	831.1	854.2	880.1	907.0
167.5°	863.2	882.4	902.8	923.7
170°	883.9	899.3	916.6	932.9
172.5°	901.6	913.9	926.6	940.6
175°	925.3	932.0	939.7	948.3
177.5°	943.5	945.8	948.1	952.0
180°	951.2	951.2	951.2	951.2



TEST NUMBER: P1427522  
 CATALOG NUMBER: SQ2W-BBM-K-075U-075D-L930-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.58	0.00	0.00	0.00	0.00	0.82
	3H	0.00	0.00	0.00	0.00	0.34	0.00	0.00	0.00	0.00	0.58
	4H	0.00	0.00	0.00	0.00	0.21	0.00	0.00	0.00	0.00	0.44
	6H	0.00	0.00	0.00	0.00	0.07	0.00	0.00	0.00	0.00	0.30
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.22
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.15
4H	2H	0.00	0.00	0.00	0.00	0.22	0.00	0.00	0.00	0.00	0.45
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.19
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.05
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00