

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427552

Luminaire Tested: SQ2W-BBM-K-125U-125D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2024
Report Number: P1427552
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-BBM-K-125U-125D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - BLACK DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9527.1 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.17 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 93.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427552

CATALOG NUMBER: SQ2W-BBM-K-125U-125D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427552

CATALOG NUMBER: SQ2W-BBM-K-125U-125D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	100	96	93	90	92	89	87	84	76	74	73	64	63	62	53	52	52	46
2	93	87	82	77	86	81	76	73	69	66	64	59	57	55	49	48	47	42
3	86	78	72	67	80	73	68	63	63	59	56	54	51	49	46	44	42	39
4	80	71	64	59	74	66	60	56	58	53	50	50	47	44	42	40	38	35
5	74	64	57	52	69	60	54	49	53	48	44	46	42	40	39	37	35	32
6	69	58	51	46	64	55	49	44	48	44	40	42	39	36	36	34	32	29
7	64	53	46	41	60	50	44	40	44	40	36	39	35	33	34	31	29	27
8	60	49	42	37	56	46	40	36	41	36	33	36	32	30	32	29	27	25
9	56	45	38	34	52	43	37	33	38	33	30	34	30	27	29	27	25	23
10	53	42	35	31	49	40	34	30	35	31	27	31	28	25	28	25	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	51908	51908	51908	51908
5°	52315	52393	52315	52393
10°	52973	52894	52973	52894
15°	53928	52853	53928	52853
20°	53997	51896	53997	51896
25°	52662	50599	52662	50599
30°	49503	47195	49503	47195
35°	43936	42288	43936	42288
40°	36032	34102	36032	34102
45°	21484	20162	21484	20162
50°	6707	6342	6707	6342
55°	2536	2536	2536	2536
60°	155	52	155	52
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 25151 cd/sqm



TEST NUMBER: P1427552

CATALOG NUMBER: SQ2W-BBM-K-125U-125D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	307.4	3.2
10°-20°	900.5	9.5
20°-30°	1324.8	13.9
30°-40°	1354.0	14.2
40°-50°	780.0	8.2
50°-60°	134.2	1.4
60°-70°	4.8	0.1
70°-80°	0.0	0.0
80°-90°	8.6	0.1
90°-100°	128.5	1.3
100°-110°	374.8	3.9
110°-120°	611.6	6.4
120°-130°	776.1	8.1
130°-140°	830.4	8.7
140°-150°	775.4	8.1
150°-160°	638.1	6.7
160°-170°	427.9	4.5
170°-180°	151.9	1.6
0°-30°	2532.6	26.6
0°-40°	3886.6	40.8
0°-60°	4800.9	50.4
0°-90°	4814.3	50.5
90°-120°	1114.9	11.7
90°-150°	3496.8	36.7
90°-180°	4715.0	49.5
0°-180°	9527.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	3215	3215	3215	3215	3215	
5°	3228	3233	3228	3233	3228	308
15°	3226	3162	3226	3162	3226	908
25°	2956	2840	2956	2840	2956	1349
35°	2229	2146	2229	2146	2229	1377
45°	941	883	941	883	941	728
55°	90	90	90	90	90	95
65°	0	0	0	0	0	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	5	36	5	70	5	4
95°	51	38	51	220	51	61
105°	238	382	238	525	238	253
115°	457	633	457	780	457	450
125°	675	1003	675	956	675	604
135°	918	1313	918	1058	918	710
145°	1173	1514	1173	1081	1173	734
155°	1393	1644	1393	1122	1393	640
165°	1540	1714	1540	1292	1540	433
175°	1610	1678	1610	1515	1610	153
180°	1615	1615	1615	1615	1615	



TEST NUMBER: P1427552

CATALOG NUMBER: SQ2W-BBM-K-125U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0
2.5°	3229.2	3225.2	3221.2	3211.6	3200.2	3201.0	3214.2	3223.3	3220.5	3217.6	3220.5
5°	3227.9	3224.3	3220.8	3210.7	3198.6	3202.2	3221.5	3235.6	3234.2	3232.7	3234.2
7.5°	3226.0	3223.5	3221.1	3214.1	3205.5	3209.1	3225.0	3236.0	3232.4	3228.9	3232.4
10°	3231.1	3230.4	3229.7	3218.8	3204.5	3205.6	3222.0	3233.4	3229.9	3226.3	3229.9
12.5°	3233.7	3238.1	3242.6	3226.9	3204.6	3200.0	3213.0	3221.1	3214.7	3208.3	3214.7
15°	3226.3	3238.4	3250.6	3228.4	3194.8	3179.1	3181.3	3180.5	3171.3	3162.0	3171.3
17.5°	3190.3	3207.4	3224.6	3195.3	3150.6	3124.3	3116.4	3107.2	3094.1	3080.9	3094.1
20°	3142.7	3162.7	3182.7	3150.7	3101.4	3069.9	3056.3	3043.3	3031.9	3020.4	3031.9
22.5°	3075.8	3094.1	3112.4	3081.7	3034.6	3002.6	2985.6	2970.5	2961.4	2952.2	2961.4
25°	2956.1	2968.2	2980.4	2949.1	2903.4	2874.1	2861.2	2850.3	2845.3	2840.3	2845.3
27.5°	2786.6	2790.0	2793.4	2768.6	2734.3	2709.1	2693.1	2679.5	2673.0	2666.6	2673.0
30°	2655.3	2655.3	2655.3	2636.0	2610.3	2588.9	2571.7	2555.8	2543.7	2531.5	2543.7
32.5°	2502.2	2500.5	2498.8	2484.6	2466.3	2447.8	2428.9	2411.7	2399.5	2387.4	2399.5
35°	2229.1	2237.0	2244.9	2235.0	2219.3	2202.2	2183.6	2166.9	2156.2	2145.5	2156.2
37.5°	1933.5	1936.5	1939.5	1931.4	1919.5	1903.6	1883.6	1866.3	1857.3	1848.3	1857.3
40°	1709.6	1710.4	1711.1	1701.1	1687.5	1673.5	1659.3	1645.1	1631.6	1618.0	1631.6
42.5°	1448.5	1462.9	1477.3	1471.2	1458.2	1440.2	1417.4	1398.8	1393.2	1387.7	1393.2
45°	940.9	1004.5	1068.1	1091.5	1101.5	1093.7	1067.9	1030.2	956.6	883.0	956.6
47.5°	472.8	552.0	631.2	686.1	732.9	719.6	646.2	571.7	493.8	415.9	493.8
50°	267.0	314.2	361.3	434.8	517.0	503.4	394.0	305.4	279.0	252.5	279.0
52.5°	178.2	199.1	219.9	279.1	351.0	346.3	264.9	200.2	185.2	170.2	185.2
55°	90.1	95.8	101.5	127.6	160.5	159.8	125.4	98.6	94.4	90.1	94.4
57.5°	30.6	38.3	46.0	57.6	70.4	70.8	58.7	47.8	40.8	33.8	40.8
60°	4.8	12.0	19.1	28.4	38.4	37.3	25.2	14.5	8.0	1.6	8.0
62.5°	1.0	3.0	5.0	12.5	22.0	21.8	11.9	4.0	2.2	0.3	2.2
65°	0.0	0.0	0.0	0.5	1.3	1.3	0.5	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	1.0	2.3	3.9	5.2	6.2	6.5	6.5	6.9	7.2	7.2	7.2
90°	4.9	11.4	19.6	26.1	31.0	32.6	32.6	34.3	35.9	35.9	35.9
92.5°	17.9	28.4	28.7	28.7	34.9	37.8	40.4	40.8	42.4	42.4	42.4
95°	50.6	55.5	83.2	81.6	55.5	44.0	37.5	37.5	37.5	37.5	37.5
97.5°	96.6	103.7	108.3	145.2	153.3	148.1	120.7	101.5	90.7	85.8	90.7
100°	137.0	140.3	150.1	151.7	192.5	231.6	212.0	187.6	179.4	174.5	179.4
102.5°	177.5	179.4	194.4	201.3	210.7	232.9	300.8	293.3	287.7	286.7	287.7
105°	238.1	239.8	267.5	280.5	287.1	287.1	285.4	318.1	370.2	381.7	370.2
107.5°	303.0	310.5	343.2	378.1	385.6	387.5	379.1	374.2	372.2	373.5	372.2
110°	347.4	358.8	398.0	442.0	453.4	456.7	453.4	448.5	445.3	445.3	445.3



TEST NUMBER: P1427552

CATALOG NUMBER: SQ2W-BBM-K-125U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	390.5	407.1	451.5	502.0	521.3	531.1	523.9	520.3	517.0	519.6	517.0
115°	456.7	481.2	539.9	592.1	631.2	636.1	634.5	634.5	632.8	632.8	632.8
117.5°	518.0	557.2	623.1	683.7	729.1	742.1	748.6	746.7	744.7	748.0	744.7
120°	561.1	606.7	681.8	750.3	794.3	813.9	820.4	817.1	820.4	817.1	820.4
122.5°	606.7	662.9	736.6	807.7	859.6	881.7	889.6	890.2	890.9	888.9	890.9
125°	675.2	743.8	830.2	903.6	957.4	983.5	990.0	991.7	994.9	1003.1	994.9
127.5°	744.4	822.0	917.0	987.8	1042.9	1074.5	1084.6	1088.2	1095.1	1098.7	1095.1
130°	792.7	880.8	977.0	1043.9	1097.7	1131.9	1149.9	1154.8	1162.9	1161.3	1162.9
132.5°	843.6	935.6	1033.1	1102.6	1152.5	1189.3	1204.7	1218.7	1221.6	1223.9	1221.6
135°	918.3	1017.8	1115.6	1184.1	1231.4	1267.3	1286.9	1299.9	1308.1	1313.0	1308.1
137.5°	996.9	1101.9	1195.9	1256.9	1304.5	1335.5	1357.7	1371.4	1379.9	1383.8	1379.9
140°	1050.4	1151.5	1242.8	1306.5	1348.9	1379.9	1399.4	1415.7	1425.5	1425.5	1425.5
142.5°	1101.3	1201.1	1289.8	1353.4	1390.6	1419.0	1439.9	1452.3	1463.4	1463.4	1463.4
145°	1172.7	1272.2	1353.8	1417.4	1448.4	1474.5	1497.3	1507.1	1513.6	1513.6	1513.6
147.5°	1247.4	1335.5	1409.9	1470.9	1497.0	1527.6	1545.6	1553.4	1561.6	1558.0	1561.6
150°	1291.8	1373.3	1445.1	1502.2	1528.3	1557.6	1575.6	1582.1	1590.3	1585.4	1590.3
152.5°	1334.8	1412.5	1477.7	1530.9	1553.1	1582.4	1603.0	1609.5	1615.0	1611.5	1615.0
155°	1392.9	1461.4	1521.8	1570.7	1590.3	1618.0	1637.6	1645.7	1652.2	1644.1	1652.2
157.5°	1444.8	1503.8	1556.3	1601.3	1622.2	1646.0	1664.3	1674.4	1680.9	1677.4	1680.9
160°	1476.1	1529.9	1577.2	1619.6	1639.2	1660.4	1680.0	1691.4	1697.9	1693.0	1697.9
162.5°	1502.2	1550.8	1595.5	1634.0	1650.9	1669.5	1693.0	1703.1	1709.6	1703.5	1709.6
165°	1539.7	1578.8	1618.0	1650.6	1665.3	1680.0	1704.4	1715.8	1720.7	1714.2	1720.7
167.5°	1568.1	1598.1	1629.7	1657.8	1668.5	1682.9	1707.4	1716.8	1723.0	1714.9	1723.0
170°	1583.7	1609.8	1637.6	1660.4	1668.5	1681.6	1706.1	1714.2	1719.1	1711.0	1719.1
172.5°	1596.8	1616.4	1638.9	1659.1	1663.3	1673.8	1696.9	1705.1	1708.7	1701.8	1708.7
175°	1609.8	1621.2	1637.6	1650.6	1649.0	1655.5	1675.1	1681.6	1688.1	1678.3	1688.1
177.5°	1616.0	1621.2	1626.5	1634.3	1629.1	1629.1	1643.4	1647.3	1648.6	1643.4	1648.6
180°	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7



TEST NUMBER: P1427552

CATALOG NUMBER: SQ2W-BBM-K-125U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0
2.5°	3223.3	3214.2	3201.0	3200.2	3211.6	3221.2	3225.2	3229.2	3225.2	3221.2	3211.6
5°	3235.6	3221.5	3202.2	3198.6	3210.7	3220.8	3224.3	3227.9	3224.3	3220.8	3210.7
7.5°	3236.0	3225.0	3209.1	3205.5	3214.1	3221.1	3223.5	3226.0	3223.5	3221.1	3214.1
10°	3233.4	3222.0	3205.6	3204.5	3218.8	3229.7	3230.4	3231.1	3230.4	3229.7	3218.8
12.5°	3221.1	3213.0	3200.0	3204.6	3226.9	3242.6	3238.1	3233.7	3238.1	3242.6	3226.9
15°	3180.5	3181.3	3179.1	3194.8	3228.4	3250.6	3238.4	3226.3	3238.4	3250.6	3228.4
17.5°	3107.2	3116.4	3124.3	3150.6	3195.3	3224.6	3207.4	3190.3	3207.4	3224.6	3195.3
20°	3043.3	3056.3	3069.9	3101.4	3150.7	3182.7	3162.7	3142.7	3162.7	3182.7	3150.7
22.5°	2970.5	2985.6	3002.6	3034.6	3081.7	3112.4	3094.1	3075.8	3094.1	3112.4	3081.7
25°	2850.3	2861.2	2874.1	2903.4	2949.1	2980.4	2968.2	2956.1	2968.2	2980.4	2949.1
27.5°	2679.5	2693.1	2709.1	2734.3	2768.6	2793.4	2790.0	2786.6	2790.0	2793.4	2768.6
30°	2555.8	2571.7	2588.9	2610.3	2636.0	2655.3	2655.3	2655.3	2655.3	2655.3	2636.0
32.5°	2411.7	2428.9	2447.8	2466.3	2484.6	2498.8	2500.5	2502.2	2500.5	2498.8	2484.6
35°	2166.9	2183.6	2202.2	2219.3	2235.0	2244.9	2237.0	2229.1	2237.0	2244.9	2235.0
37.5°	1866.3	1883.6	1903.6	1919.5	1931.4	1939.5	1936.5	1933.5	1936.5	1939.5	1931.4
40°	1645.1	1659.3	1673.5	1687.5	1701.1	1711.1	1710.4	1709.6	1710.4	1711.1	1701.1
42.5°	1398.8	1417.4	1440.2	1458.2	1471.2	1477.3	1462.9	1448.5	1462.9	1477.3	1471.2
45°	1030.2	1067.9	1093.7	1101.5	1091.5	1068.1	1004.5	940.9	1004.5	1068.1	1091.5
47.5°	571.7	646.2	719.6	732.9	686.1	631.2	552.0	472.8	552.0	631.2	686.1
50°	305.4	394.0	503.4	517.0	434.8	361.3	314.2	267.0	314.2	361.3	434.8
52.5°	200.2	264.9	346.3	351.0	279.1	219.9	199.1	178.2	199.1	219.9	279.1
55°	98.6	125.4	159.8	160.5	127.6	101.5	95.8	90.1	95.8	101.5	127.6
57.5°	47.8	58.7	70.8	70.4	57.6	46.0	38.3	30.6	38.3	46.0	57.6
60°	14.5	25.2	37.3	38.4	28.4	19.1	12.0	4.8	12.0	19.1	28.4
62.5°	4.0	11.9	21.8	22.0	12.5	5.0	3.0	1.0	3.0	5.0	12.5
65°	0.0	0.5	1.3	1.3	0.5	0.0	0.0	0.0	0.0	0.0	0.5
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	6.9	6.5	6.5	6.2	5.2	3.9	2.3	1.0	2.3	3.6	5.9
90°	34.3	32.6	32.6	31.0	26.1	19.6	11.4	4.9	11.4	17.9	29.4
92.5°	40.8	40.4	37.8	34.9	28.7	28.7	28.4	17.9	31.0	44.0	63.3
95°	37.5	37.5	44.0	55.5	81.6	83.2	55.5	50.6	71.8	101.1	127.2
97.5°	101.5	120.7	148.1	153.3	145.2	108.3	103.7	96.6	131.5	160.5	202.6
100°	187.6	212.0	231.6	192.5	151.7	150.1	140.3	137.0	174.5	202.2	243.0
102.5°	293.3	300.8	232.9	210.7	201.3	194.4	179.4	177.5	215.0	253.1	287.4
105°	318.1	285.4	287.1	287.1	280.5	267.5	239.8	238.1	280.5	324.6	367.0
107.5°	374.2	379.1	387.5	385.6	378.1	343.2	310.5	303.0	341.2	394.1	440.7
110°	448.5	453.4	456.7	453.4	442.0	398.0	358.8	347.4	381.7	437.1	487.7



TEST NUMBER: P1427552

CATALOG NUMBER: SQ2W-BBM-K-125U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	520.3	523.9	531.1	521.3	502.0	451.5	407.1	390.5	424.7	481.5	533.3
115°	634.5	634.5	636.1	631.2	592.1	539.9	481.2	456.7	486.0	538.2	595.3
117.5°	746.7	748.6	742.1	729.1	683.7	623.1	557.2	518.0	541.2	596.3	655.0
120°	817.1	820.4	813.9	794.3	750.3	681.8	606.7	561.1	579.0	632.8	691.6
122.5°	890.2	889.6	881.7	859.6	807.7	736.6	662.9	606.7	614.2	664.2	721.6
125°	991.7	990.0	983.5	957.4	903.6	830.2	743.8	675.2	665.5	707.9	766.6
127.5°	1088.2	1084.6	1074.5	1042.9	987.8	917.0	822.0	744.4	722.5	749.3	803.1
130°	1154.8	1149.9	1131.9	1097.7	1043.9	977.0	880.8	792.7	761.7	778.0	825.3
132.5°	1218.7	1204.7	1189.3	1152.5	1102.6	1033.1	935.6	843.6	800.8	808.0	844.9
135°	1299.9	1286.9	1267.3	1231.4	1184.1	1115.6	1017.8	918.3	859.6	853.0	874.2
137.5°	1371.4	1357.7	1335.5	1304.5	1256.9	1195.9	1101.9	996.9	922.8	901.0	909.1
140°	1415.7	1399.4	1379.9	1348.9	1306.5	1242.8	1151.5	1050.4	967.2	936.2	931.3
142.5°	1452.3	1439.9	1419.0	1390.6	1353.4	1289.8	1201.1	1101.3	1012.9	972.7	961.3
145°	1507.1	1497.3	1474.5	1448.4	1417.4	1353.8	1272.2	1172.7	1084.6	1032.4	1008.0
147.5°	1553.4	1545.6	1527.6	1497.0	1470.9	1409.9	1335.5	1247.4	1157.1	1092.5	1060.8
150°	1582.1	1575.6	1557.6	1528.3	1502.2	1445.1	1373.3	1291.8	1205.3	1136.8	1096.1
152.5°	1609.5	1603.0	1582.4	1553.1	1530.9	1477.7	1412.5	1334.8	1247.1	1178.6	1136.5
155°	1645.7	1637.6	1618.0	1590.3	1570.7	1521.8	1461.4	1392.9	1317.9	1246.1	1198.8
157.5°	1674.4	1664.3	1646.0	1622.2	1601.3	1556.3	1503.8	1444.8	1379.2	1310.7	1262.4
160°	1691.4	1680.0	1660.4	1639.2	1619.6	1577.2	1529.9	1476.1	1415.7	1353.8	1301.6
162.5°	1703.1	1693.0	1669.5	1650.9	1634.0	1595.5	1550.8	1502.2	1448.4	1394.2	1345.9
165°	1715.8	1704.4	1680.0	1665.3	1650.6	1618.0	1578.8	1539.7	1494.0	1450.0	1410.8
167.5°	1716.8	1707.4	1682.9	1668.5	1657.8	1629.7	1598.1	1568.1	1532.5	1497.9	1465.3
170°	1714.2	1706.1	1681.6	1668.5	1660.4	1637.6	1609.8	1583.7	1556.0	1526.6	1500.6
172.5°	1705.1	1696.9	1673.8	1663.3	1659.1	1638.9	1616.4	1596.8	1573.0	1551.4	1530.6
175°	1681.6	1675.1	1655.5	1649.0	1650.6	1637.6	1621.2	1609.8	1595.2	1582.1	1570.7
177.5°	1647.3	1643.4	1629.1	1629.1	1634.3	1626.5	1621.2	1616.0	1609.5	1605.6	1601.7
180°	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7



TEST NUMBER: P1427552

CATALOG NUMBER: SQ2W-BBM-K-125U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0
2.5°	3200.2	3201.0	3214.2	3223.3	3220.5	3217.6	3220.5	3223.3	3214.2	3201.0	3200.2
5°	3198.6	3202.2	3221.5	3235.6	3234.2	3232.7	3234.2	3235.6	3221.5	3202.2	3198.6
7.5°	3205.5	3209.1	3225.0	3236.0	3232.4	3228.9	3232.4	3236.0	3225.0	3209.1	3205.5
10°	3204.5	3205.6	3222.0	3233.4	3229.9	3226.3	3229.9	3233.4	3222.0	3205.6	3204.5
12.5°	3204.6	3200.0	3213.0	3221.1	3214.7	3208.3	3214.7	3221.1	3213.0	3200.0	3204.6
15°	3194.8	3179.1	3181.3	3180.5	3171.3	3162.0	3171.3	3180.5	3181.3	3179.1	3194.8
17.5°	3150.6	3124.3	3116.4	3107.2	3094.1	3080.9	3094.1	3107.2	3116.4	3124.3	3150.6
20°	3101.4	3069.9	3056.3	3043.3	3031.9	3020.4	3031.9	3043.3	3056.3	3069.9	3101.4
22.5°	3034.6	3002.6	2985.6	2970.5	2961.4	2952.2	2961.4	2970.5	2985.6	3002.6	3034.6
25°	2903.4	2874.1	2861.2	2850.3	2845.3	2840.3	2845.3	2850.3	2861.2	2874.1	2903.4
27.5°	2734.3	2709.1	2693.1	2679.5	2673.0	2666.6	2673.0	2679.5	2693.1	2709.1	2734.3
30°	2610.3	2588.9	2571.7	2555.8	2543.7	2531.5	2543.7	2555.8	2571.7	2588.9	2610.3
32.5°	2466.3	2447.8	2428.9	2411.7	2399.5	2387.4	2399.5	2411.7	2428.9	2447.8	2466.3
35°	2219.3	2202.2	2183.6	2166.9	2156.2	2145.5	2156.2	2166.9	2183.6	2202.2	2219.3
37.5°	1919.5	1903.6	1883.6	1866.3	1857.3	1848.3	1857.3	1866.3	1883.6	1903.6	1919.5
40°	1687.5	1673.5	1659.3	1645.1	1631.6	1618.0	1631.6	1645.1	1659.3	1673.5	1687.5
42.5°	1458.2	1440.2	1417.4	1398.8	1393.2	1387.7	1393.2	1398.8	1417.4	1440.2	1458.2
45°	1101.5	1093.7	1067.9	1030.2	956.6	883.0	956.6	1030.2	1067.9	1093.7	1101.5
47.5°	732.9	719.6	646.2	571.7	493.8	415.9	493.8	571.7	646.2	719.6	732.9
50°	517.0	503.4	394.0	305.4	279.0	252.5	279.0	305.4	394.0	503.4	517.0
52.5°	351.0	346.3	264.9	200.2	185.2	170.2	185.2	200.2	264.9	346.3	351.0
55°	160.5	159.8	125.4	98.6	94.4	90.1	94.4	98.6	125.4	159.8	160.5
57.5°	70.4	70.8	58.7	47.8	40.8	33.8	40.8	47.8	58.7	70.8	70.4
60°	38.4	37.3	25.2	14.5	8.0	1.6	8.0	14.5	25.2	37.3	38.4
62.5°	22.0	21.8	11.9	4.0	2.2	0.3	2.2	4.0	11.9	21.8	22.0
65°	1.3	1.3	0.5	0.0	0.0	0.0	0.0	0.5	1.3	1.3	1.3
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	7.5	9.8	12.1	13.4	14.7	14.0	14.7	13.4	12.1	9.8	7.5
90°	37.5	48.9	60.3	66.9	73.4	70.1	73.4	66.9	60.3	48.9	37.5
92.5°	75.4	94.6	108.6	120.4	125.6	124.9	125.6	120.4	108.6	94.6	75.4
95°	151.7	174.5	197.4	213.7	223.5	220.2	223.5	213.7	197.4	174.5	151.7
97.5°	233.9	264.6	290.0	305.3	315.1	321.6	315.1	305.3	290.0	264.6	233.9
100°	288.7	318.1	347.4	365.4	381.7	388.2	381.7	365.4	347.4	318.1	288.7
102.5°	333.1	371.5	403.5	422.8	436.5	443.0	436.5	422.8	403.5	371.5	333.1
105°	406.1	446.9	481.2	505.6	520.3	525.2	520.3	505.6	481.2	446.9	406.1
107.5°	479.2	521.3	552.9	580.0	597.9	608.4	597.9	580.0	552.9	521.3	479.2
110°	536.6	570.9	605.1	629.6	647.5	654.0	647.5	629.6	605.1	570.9	536.6



TEST NUMBER: P1427552

CATALOG NUMBER: SQ2W-BBM-K-125U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	584.9	623.1	657.3	681.8	702.3	711.5	702.3	681.8	657.3	623.1	584.9
115°	652.4	703.0	734.0	756.8	771.5	779.6	771.5	756.8	734.0	703.0	652.4
117.5°	708.5	761.4	795.3	812.9	819.8	825.6	819.8	812.9	795.3	761.4	708.5
120°	743.8	792.7	831.8	854.7	862.8	866.1	862.8	854.7	831.8	792.7	743.8
122.5°	776.4	822.7	860.5	888.6	902.0	905.2	902.0	888.6	860.5	822.7	776.4
125°	822.0	866.1	905.2	933.0	947.6	955.8	947.6	933.0	905.2	866.1	822.0
127.5°	861.8	909.5	945.3	970.5	984.8	991.3	984.8	970.5	945.3	909.5	861.8
130°	884.0	933.0	968.8	996.6	1009.6	1016.1	1009.6	996.6	968.8	933.0	884.0
132.5°	901.0	952.5	989.7	1014.8	1029.2	1035.7	1029.2	1014.8	989.7	952.5	901.0
135°	921.5	975.4	1014.5	1039.0	1052.0	1058.5	1052.0	1039.0	1014.5	975.4	921.5
137.5°	939.5	988.4	1029.2	1055.0	1066.7	1070.9	1066.7	1055.0	1029.2	988.4	939.5
140°	952.5	994.9	1035.7	1060.2	1073.2	1074.9	1073.2	1060.2	1035.7	994.9	952.5
142.5°	969.5	1002.8	1038.3	1062.8	1075.8	1078.8	1075.8	1062.8	1038.3	1002.8	969.5
145°	999.8	1019.4	1043.9	1066.7	1078.1	1081.4	1078.1	1066.7	1043.9	1019.4	999.8
147.5°	1038.0	1044.2	1056.9	1071.9	1083.0	1085.3	1083.0	1071.9	1056.9	1044.2	1038.0
150°	1066.7	1065.1	1070.0	1079.7	1089.5	1087.9	1089.5	1079.7	1070.0	1065.1	1066.7
152.5°	1099.3	1089.9	1089.5	1094.1	1098.7	1098.3	1098.7	1094.1	1089.5	1089.9	1099.3
155°	1154.8	1136.8	1127.0	1123.8	1123.8	1122.2	1123.8	1123.8	1127.0	1136.8	1154.8
157.5°	1215.8	1190.7	1176.0	1168.1	1165.9	1162.3	1165.9	1168.1	1176.0	1190.7	1215.8
160°	1257.5	1229.8	1215.1	1202.1	1197.2	1192.3	1197.2	1202.1	1215.1	1229.8	1257.5
162.5°	1296.7	1270.2	1254.3	1242.5	1237.6	1230.1	1237.6	1242.5	1254.3	1270.2	1296.7
165°	1360.3	1332.6	1314.6	1304.8	1298.3	1291.8	1298.3	1304.8	1314.6	1332.6	1360.3
167.5°	1423.9	1393.6	1381.8	1370.7	1364.5	1352.8	1364.5	1370.7	1381.8	1393.6	1423.9
170°	1463.0	1435.3	1428.8	1419.0	1407.6	1394.5	1407.6	1419.0	1428.8	1435.3	1463.0
172.5°	1497.0	1478.4	1471.8	1462.1	1458.5	1448.0	1458.5	1462.1	1471.8	1478.4	1497.0
175°	1546.2	1531.5	1531.5	1529.9	1525.0	1515.2	1525.0	1529.9	1531.5	1531.5	1546.2
177.5°	1587.3	1579.5	1584.7	1584.7	1583.4	1574.3	1583.4	1584.7	1584.7	1579.5	1587.3
180°	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7



TEST NUMBER: P1427552

CATALOG NUMBER: SQ2W-BBM-K-125U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	3215.0	3215.0	3215.0	3215.0
2.5°	3211.6	3221.2	3225.2	3229.2
5°	3210.7	3220.8	3224.3	3227.9
7.5°	3214.1	3221.1	3223.5	3226.0
10°	3218.8	3229.7	3230.4	3231.1
12.5°	3226.9	3242.6	3238.1	3233.7
15°	3228.4	3250.6	3238.4	3226.3
17.5°	3195.3	3224.6	3207.4	3190.3
20°	3150.7	3182.7	3162.7	3142.7
22.5°	3081.7	3112.4	3094.1	3075.8
25°	2949.1	2980.4	2968.2	2956.1
27.5°	2768.6	2793.4	2790.0	2786.6
30°	2636.0	2655.3	2655.3	2655.3
32.5°	2484.6	2498.8	2500.5	2502.2
35°	2235.0	2244.9	2237.0	2229.1
37.5°	1931.4	1939.5	1936.5	1933.5
40°	1701.1	1711.1	1710.4	1709.6
42.5°	1471.2	1477.3	1462.9	1448.5
45°	1091.5	1068.1	1004.5	940.9
47.5°	686.1	631.2	552.0	472.8
50°	434.8	361.3	314.2	267.0
52.5°	279.1	219.9	199.1	178.2
55°	127.6	101.5	95.8	90.1
57.5°	57.6	46.0	38.3	30.6
60°	28.4	19.1	12.0	4.8
62.5°	12.5	5.0	3.0	1.0
65°	0.5	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	5.9	3.6	2.3	1.0
90°	29.4	17.9	11.4	4.9
92.5°	63.3	44.0	31.0	17.9
95°	127.2	101.1	71.8	50.6
97.5°	202.6	160.5	131.5	96.6
100°	243.0	202.2	174.5	137.0
102.5°	287.4	253.1	215.0	177.5
105°	367.0	324.6	280.5	238.1
107.5°	440.7	394.1	341.2	303.0
110°	487.7	437.1	381.7	347.4



TEST NUMBER: P1427552

CATALOG NUMBER: SQ2W-BBM-K-125U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	533.3	481.5	424.7	390.5
115°	595.3	538.2	486.0	456.7
117.5°	655.0	596.3	541.2	518.0
120°	691.6	632.8	579.0	561.1
122.5°	721.6	664.2	614.2	606.7
125°	766.6	707.9	665.5	675.2
127.5°	803.1	749.3	722.5	744.4
130°	825.3	778.0	761.7	792.7
132.5°	844.9	808.0	800.8	843.6
135°	874.2	853.0	859.6	918.3
137.5°	909.1	901.0	922.8	996.9
140°	931.3	936.2	967.2	1050.4
142.5°	961.3	972.7	1012.9	1101.3
145°	1008.0	1032.4	1084.6	1172.7
147.5°	1060.8	1092.5	1157.1	1247.4
150°	1096.1	1136.8	1205.3	1291.8
152.5°	1136.5	1178.6	1247.1	1334.8
155°	1198.8	1246.1	1317.9	1392.9
157.5°	1262.4	1310.7	1379.2	1444.8
160°	1301.6	1353.8	1415.7	1476.1
162.5°	1345.9	1394.2	1448.4	1502.2
165°	1410.8	1450.0	1494.0	1539.7
167.5°	1465.3	1497.9	1532.5	1568.1
170°	1500.6	1526.6	1556.0	1583.7
172.5°	1530.6	1551.4	1573.0	1596.8
175°	1570.7	1582.1	1595.2	1609.8
177.5°	1601.7	1605.6	1609.5	1616.0
180°	1614.7	1614.7	1614.7	1614.7



TEST NUMBER: P1427552
 CATALOG NUMBER: SQ2W-BBM-K-125U-125D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.09	0.37	1.06	2.34	0.00	0.32	0.60	1.29	2.57
	3H	0.00	0.00	0.19	0.80	2.10	0.00	0.04	0.42	1.03	2.33
	4H	0.00	0.00	0.09	0.66	1.97	0.00	0.00	0.32	0.89	2.20
	6H	0.00	0.00	0.00	0.51	1.82	0.00	0.00	0.22	0.73	2.05
	8H	0.00	0.00	0.00	0.43	1.75	0.00	0.00	0.17	0.66	1.97
	12H	0.00	0.00	0.00	0.34	1.67	0.00	0.00	0.11	0.57	1.90
4H	2H	0.00	0.00	0.11	0.67	1.98	0.00	0.00	0.34	0.90	2.21
	3H	0.00	0.00	0.00	0.39	1.71	0.00	0.00	0.14	0.62	1.94
	4H	0.00	0.00	0.00	0.23	1.57	0.00	0.00	0.03	0.46	1.80
	6H	0.00	0.00	0.00	0.08	1.42	0.00	0.00	0.00	0.30	1.65
	8H	0.00	0.00	0.00	0.00	1.33	0.00	0.00	0.00	0.21	1.56
	12H	0.00	0.00	0.00	0.00	1.24	0.00	0.00	0.00	0.11	1.47
8H	4H	0.00	0.00	0.00	0.00	1.33	0.00	0.00	0.00	0.21	1.56
	6H	0.00	0.00	0.00	0.00	1.19	0.00	0.00	0.00	0.07	1.42
	8H	0.00	0.00	0.00	0.00	1.10	0.00	0.00	0.00	0.00	1.33
	12H	0.00	0.00	0.00	0.00	1.04	0.00	0.00	0.00	0.00	1.27
12H	4H	0.00	0.00	0.00	0.00	1.24	0.00	0.00	0.00	0.11	1.47
	6H	0.00	0.00	0.00	0.00	1.10	0.00	0.00	0.00	0.00	1.33
	8H	0.00	0.00	0.00	0.00	1.04	0.00	0.00	0.00	0.00	1.27