

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427558

Luminaire Tested: SQ2W-BBM-K-150U-075D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1427558  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-BBM-K-150U-075D-L930-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - BLACK DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8474.1 lumens  
Efficiency: N/A  
Efficacy: 102.5 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.17 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 82.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1427558

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L930-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1427558

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L930-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				
1	96	92	88	86	86	83	80	78	67	65	64	52	51	50	39	38	37	31				
2	88	82	77	72	80	74	70	66	60	57	55	48	46	44	36	35	34	28				
3	81	73	67	62	74	67	61	57	55	51	48	43	41	39	33	32	30	26				
4	75	66	59	54	68	60	54	50	49	45	42	40	37	35	30	29	28	24				
5	69	59	52	47	63	54	48	44	45	41	37	36	33	31	28	26	25	22				
6	64	54	46	41	58	49	43	39	41	37	33	33	30	28	26	24	23	20				
7	60	49	42	37	54	45	39	34	38	33	30	31	28	25	24	22	21	18				
8	56	45	38	33	51	41	35	31	35	30	27	28	25	23	23	20	19	17				
9	52	41	34	29	47	38	32	28	32	27	24	26	23	21	21	19	17	15				
10	49	38	31	27	44	35	29	25	29	25	22	24	21	19	20	18	16	14				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	31041	31041	31041	31041
5°	31285	31332	31285	31332
10°	31678	31632	31678	31632
15°	32250	31607	32250	31607
20°	32291	31035	32291	31035
25°	31493	30258	31493	30258
30°	29604	28224	29604	28224
35°	26276	25288	26276	25288
40°	21549	20394	21549	20394
45°	12848	12056	12848	12056
50°	4011	3793	4011	3793
55°	1517	1517	1517	1517
60°	94	32	94	32
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 15040 cd/sqm



TEST NUMBER: P1427558

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L930-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.8	2.2
10°-20°	538.5	6.4
20°-30°	792.2	9.3
30°-40°	809.7	9.6
40°-50°	466.4	5.5
50°-60°	80.3	0.9
60°-70°	2.9	0.0
70°-80°	0.0	0.0
80°-90°	10.2	0.1
90°-100°	152.4	1.8
100°-110°	444.5	5.2
110°-120°	725.4	8.6
120°-130°	920.5	10.9
130°-140°	985.0	11.6
140°-150°	919.8	10.9
150°-160°	756.8	8.9
160°-170°	507.6	6.0
170°-180°	180.2	2.1
0°-30°	1514.5	17.9
0°-40°	2324.3	27.4
0°-60°	2871.0	33.9
0°-90°	2884.0	34.0
90°-120°	1322.4	15.6
90°-150°	4147.7	48.9
90°-180°	5592.0	66.0
0°-180°	8474.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1923	1923	1923	1923	1923	
5°	1930	1933	1930	1933	1930	184
15°	1929	1891	1929	1891	1929	543
25°	1768	1698	1768	1698	1768	807
35°	1333	1283	1333	1283	1333	823
45°	563	528	563	528	563	435
55°	54	54	54	54	54	57
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	6	43	6	83	6	5
95°	60	44	60	261	60	72
105°	282	453	282	623	282	300
115°	542	751	542	925	542	534
125°	801	1190	801	1134	801	717
135°	1089	1557	1089	1256	1089	842
145°	1391	1795	1391	1283	1391	870
155°	1652	1950	1652	1331	1652	759
165°	1826	2033	1826	1532	1826	514
175°	1910	1991	1910	1797	1910	181
180°	1915	1915	1915	1915	1915	



TEST NUMBER: P1427558

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6
2.5°	1931.1	1928.7	1926.3	1920.6	1913.7	1914.3	1922.1	1927.6	1925.9	1924.2	1925.9
5°	1930.3	1928.2	1926.1	1920.1	1912.8	1914.9	1926.5	1934.9	1934.1	1933.2	1934.1
7.5°	1929.2	1927.7	1926.3	1922.1	1916.9	1919.1	1928.6	1935.2	1933.0	1930.9	1933.0
10°	1932.2	1931.8	1931.4	1924.9	1916.3	1917.0	1926.8	1933.6	1931.5	1929.4	1931.5
12.5°	1933.8	1936.4	1939.1	1929.7	1916.4	1913.6	1921.4	1926.3	1922.4	1918.6	1922.4
15°	1929.4	1936.6	1943.9	1930.6	1910.6	1901.2	1902.4	1902.0	1896.4	1890.9	1896.4
17.5°	1907.8	1918.1	1928.3	1910.8	1884.1	1868.3	1863.6	1858.1	1850.3	1842.4	1850.3
20°	1879.4	1891.3	1903.3	1884.2	1854.7	1835.9	1827.7	1819.9	1813.1	1806.3	1813.1
22.5°	1839.3	1850.3	1861.2	1842.9	1814.7	1795.6	1785.4	1776.4	1770.9	1765.5	1770.9
25°	1767.8	1775.0	1782.3	1763.6	1736.3	1718.7	1711.0	1704.5	1701.5	1698.5	1701.5
27.5°	1666.4	1668.5	1670.5	1655.6	1635.1	1620.1	1610.5	1602.4	1598.5	1594.7	1598.5
30°	1587.9	1587.9	1587.9	1576.4	1561.0	1548.2	1537.9	1528.4	1521.1	1513.9	1521.1
32.5°	1496.4	1495.3	1494.3	1485.8	1474.9	1463.8	1452.5	1442.2	1435.0	1427.7	1435.0
35°	1333.1	1337.8	1342.5	1336.6	1327.2	1316.9	1305.8	1295.9	1289.4	1283.0	1289.4
37.5°	1156.3	1158.1	1159.9	1155.0	1147.9	1138.4	1126.4	1116.1	1110.7	1105.3	1110.7
40°	1022.4	1022.8	1023.2	1017.3	1009.1	1000.8	992.3	983.8	975.7	967.6	975.7
42.5°	866.2	874.8	883.5	879.8	872.0	861.3	847.6	836.5	833.2	829.8	833.2
45°	562.7	600.7	638.7	652.7	658.7	654.0	638.6	616.1	572.1	528.0	572.1
47.5°	282.8	330.1	377.5	410.3	438.3	430.3	386.4	341.9	295.3	248.7	295.3
50°	159.7	187.9	216.1	260.0	309.2	301.0	235.6	182.6	166.8	151.0	166.8
52.5°	106.6	119.0	131.5	166.9	209.9	207.1	158.4	119.7	110.7	101.8	110.7
55°	53.9	57.3	60.7	76.3	96.0	95.5	75.0	59.0	56.4	53.9	56.4
57.5°	18.3	22.9	27.5	34.4	42.1	42.3	35.1	28.6	24.4	20.2	24.4
60°	2.9	7.2	11.4	17.0	23.0	22.3	15.1	8.7	4.8	1.0	4.8
62.5°	0.6	1.8	3.0	7.5	13.1	13.0	7.1	2.4	1.3	0.2	1.3
65°	0.0	0.0	0.0	0.3	0.7	0.7	0.3	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	1.2	2.7	4.6	6.2	7.4	7.7	7.7	8.1	8.5	8.5	8.5
90°	5.8	13.5	23.2	31.0	36.8	38.7	38.7	40.6	42.6	42.6	42.6
92.5°	21.3	33.7	34.0	34.0	41.4	44.9	48.0	48.4	50.3	50.3	50.3
95°	60.0	65.8	98.7	96.7	65.8	52.2	44.5	44.5	44.5	44.5	44.5
97.5°	114.5	123.0	128.5	172.2	181.9	175.7	143.2	120.3	107.6	101.8	107.6
100°	162.5	166.4	178.0	179.9	228.3	274.7	251.5	222.5	212.8	207.0	212.8
102.5°	210.5	212.8	230.6	238.7	250.0	276.3	356.7	347.8	341.3	340.1	341.3
105°	282.5	284.4	317.3	332.8	340.5	340.5	338.6	377.3	439.2	452.7	439.2
107.5°	359.5	368.4	407.0	448.4	457.3	459.7	449.6	443.8	441.5	443.0	441.5
110°	412.1	425.6	472.1	524.3	537.8	541.7	537.8	532.0	528.2	528.2	528.2



TEST NUMBER: P1427558

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	463.2	482.9	535.5	595.5	618.3	629.9	621.4	617.2	613.3	616.4	613.3
115°	541.7	570.7	640.4	702.3	748.7	754.5	752.6	752.6	750.6	750.6	750.6
117.5°	614.4	660.9	739.0	811.0	864.8	880.3	888.0	885.7	883.4	887.2	883.4
120°	665.5	719.7	808.7	889.9	942.2	965.4	973.1	969.3	973.1	969.3	973.1
122.5°	719.7	786.2	873.7	958.0	1019.6	1045.9	1055.2	1055.9	1056.7	1054.4	1056.7
125°	800.9	882.2	984.7	1071.8	1135.6	1166.6	1174.3	1176.3	1180.1	1189.8	1180.1
127.5°	883.0	975.1	1087.7	1171.6	1237.0	1274.5	1286.5	1290.8	1298.9	1303.2	1298.9
130°	940.2	1044.7	1158.8	1238.2	1302.0	1342.6	1363.9	1369.7	1379.4	1377.5	1379.4
132.5°	1000.6	1109.7	1225.4	1307.8	1367.0	1410.7	1428.9	1445.6	1449.0	1451.8	1449.0
135°	1089.2	1207.2	1323.3	1404.5	1460.7	1503.2	1526.4	1541.9	1551.6	1557.4	1551.6
137.5°	1182.5	1307.0	1418.5	1490.8	1547.3	1584.1	1610.4	1626.6	1636.7	1641.3	1636.7
140°	1245.9	1365.9	1474.2	1549.6	1599.9	1636.7	1659.9	1679.3	1690.9	1690.9	1690.9
142.5°	1306.3	1424.7	1529.9	1605.4	1649.5	1683.1	1707.9	1722.6	1735.8	1735.8	1735.8
145°	1391.0	1509.0	1605.8	1681.2	1718.0	1748.9	1776.0	1787.6	1795.3	1795.3	1795.3
147.5°	1479.6	1584.1	1672.3	1744.7	1775.6	1812.0	1833.3	1842.6	1852.2	1848.0	1852.2
150°	1532.2	1629.0	1714.1	1781.8	1812.8	1847.6	1868.9	1876.6	1886.3	1880.5	1886.3
152.5°	1583.3	1675.4	1752.8	1815.9	1842.2	1877.0	1901.4	1909.1	1915.7	1911.4	1915.7
155°	1652.2	1733.4	1805.0	1863.1	1886.3	1919.2	1942.4	1952.1	1959.8	1950.1	1959.8
157.5°	1713.7	1783.7	1846.0	1899.4	1924.2	1952.4	1974.1	1986.1	1993.8	1989.6	1993.8
160°	1750.8	1814.7	1870.8	1921.1	1944.3	1969.5	1992.7	2006.2	2014.0	2008.2	2014.0
162.5°	1781.8	1839.5	1892.5	1938.1	1958.2	1980.3	2008.2	2020.2	2027.9	2020.5	2027.9
165°	1826.3	1872.7	1919.2	1957.9	1975.3	1992.7	2021.7	2035.2	2041.0	2033.3	2041.0
167.5°	1860.0	1895.6	1933.1	1966.4	1979.1	1996.2	2025.2	2036.4	2043.8	2034.1	2043.8
170°	1878.5	1909.5	1942.4	1969.5	1979.1	1994.6	2023.6	2033.3	2039.1	2029.4	2039.1
172.5°	1894.0	1917.2	1943.9	1967.9	1972.9	1985.3	2012.8	2022.5	2026.7	2018.6	2026.7
175°	1909.5	1923.0	1942.4	1957.9	1955.9	1963.7	1986.9	1994.6	2002.4	1990.7	2002.4
177.5°	1916.8	1923.0	1929.2	1938.5	1932.3	1932.3	1949.3	1954.0	1955.5	1949.3	1955.5
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1427558

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6
2.5°	1927.6	1922.1	1914.3	1913.7	1920.6	1926.3	1928.7	1931.1	1928.7	1926.3	1920.6
5°	1934.9	1926.5	1914.9	1912.8	1920.1	1926.1	1928.2	1930.3	1928.2	1926.1	1920.1
7.5°	1935.2	1928.6	1919.1	1916.9	1922.1	1926.3	1927.7	1929.2	1927.7	1926.3	1922.1
10°	1933.6	1926.8	1917.0	1916.3	1924.9	1931.4	1931.8	1932.2	1931.8	1931.4	1924.9
12.5°	1926.3	1921.4	1913.6	1916.4	1929.7	1939.1	1936.4	1933.8	1936.4	1939.1	1929.7
15°	1902.0	1902.4	1901.2	1910.6	1930.6	1943.9	1936.6	1929.4	1936.6	1943.9	1930.6
17.5°	1858.1	1863.6	1868.3	1884.1	1910.8	1928.3	1918.1	1907.8	1918.1	1928.3	1910.8
20°	1819.9	1827.7	1835.9	1854.7	1884.2	1903.3	1891.3	1879.4	1891.3	1903.3	1884.2
22.5°	1776.4	1785.4	1795.6	1814.7	1842.9	1861.2	1850.3	1839.3	1850.3	1861.2	1842.9
25°	1704.5	1711.0	1718.7	1736.3	1763.6	1782.3	1775.0	1767.8	1775.0	1782.3	1763.6
27.5°	1602.4	1610.5	1620.1	1635.1	1655.6	1670.5	1668.5	1666.4	1668.5	1670.5	1655.6
30°	1528.4	1537.9	1548.2	1561.0	1576.4	1587.9	1587.9	1587.9	1587.9	1587.9	1576.4
32.5°	1442.2	1452.5	1463.8	1474.9	1485.8	1494.3	1495.3	1496.4	1495.3	1494.3	1485.8
35°	1295.9	1305.8	1316.9	1327.2	1336.6	1342.5	1337.8	1333.1	1337.8	1342.5	1336.6
37.5°	1116.1	1126.4	1138.4	1147.9	1155.0	1159.9	1158.1	1156.3	1158.1	1159.9	1155.0
40°	983.8	992.3	1000.8	1009.1	1017.3	1023.2	1022.8	1022.4	1022.8	1023.2	1017.3
42.5°	836.5	847.6	861.3	872.0	879.8	883.5	874.8	866.2	874.8	883.5	879.8
45°	616.1	638.6	654.0	658.7	652.7	638.7	600.7	562.7	600.7	638.7	652.7
47.5°	341.9	386.4	430.3	438.3	410.3	377.5	330.1	282.8	330.1	377.5	410.3
50°	182.6	235.6	301.0	309.2	260.0	216.1	187.9	159.7	187.9	216.1	260.0
52.5°	119.7	158.4	207.1	209.9	166.9	131.5	119.0	106.6	119.0	131.5	166.9
55°	59.0	75.0	95.5	96.0	76.3	60.7	57.3	53.9	57.3	60.7	76.3
57.5°	28.6	35.1	42.3	42.1	34.4	27.5	22.9	18.3	22.9	27.5	34.4
60°	8.7	15.1	22.3	23.0	17.0	11.4	7.2	2.9	7.2	11.4	17.0
62.5°	2.4	7.1	13.0	13.1	7.5	3.0	1.8	0.6	1.8	3.0	7.5
65°	0.0	0.3	0.7	0.7	0.3	0.0	0.0	0.0	0.0	0.0	0.3
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	8.1	7.7	7.7	7.4	6.2	4.6	2.7	1.2	2.7	4.3	7.0
90°	40.6	38.7	38.7	36.8	31.0	23.2	13.5	5.8	13.5	21.3	34.8
92.5°	48.4	48.0	44.9	41.4	34.0	34.0	33.7	21.3	36.8	52.2	75.1
95°	44.5	44.5	52.2	65.8	96.7	98.7	65.8	60.0	85.1	119.9	150.9
97.5°	120.3	143.2	175.7	181.9	172.2	128.5	123.0	114.5	155.9	190.4	240.3
100°	222.5	251.5	274.7	228.3	179.9	178.0	166.4	162.5	207.0	239.9	288.3
102.5°	347.8	356.7	276.3	250.0	238.7	230.6	212.8	210.5	255.0	300.3	340.9
105°	377.3	338.6	340.5	340.5	332.8	317.3	284.4	282.5	332.8	385.0	435.3
107.5°	443.8	449.6	459.7	457.3	448.4	407.0	368.4	359.5	404.7	467.4	522.7
110°	532.0	537.8	541.7	537.8	524.3	472.1	425.6	412.1	452.7	518.5	578.5



TEST NUMBER: P1427558

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	617.2	621.4	629.9	618.3	595.5	535.5	482.9	463.2	503.8	571.1	632.6
115°	752.6	752.6	754.5	748.7	702.3	640.4	570.7	541.7	576.5	638.4	706.1
117.5°	885.7	888.0	880.3	864.8	811.0	739.0	660.9	614.4	641.9	707.3	777.0
120°	969.3	973.1	965.4	942.2	889.9	808.7	719.7	665.5	686.8	750.6	820.3
122.5°	1055.9	1055.2	1045.9	1019.6	958.0	873.7	786.2	719.7	728.6	787.8	855.9
125°	1176.3	1174.3	1166.6	1135.6	1071.8	984.7	882.2	800.9	789.3	839.6	909.3
127.5°	1290.8	1286.5	1274.5	1237.0	1171.6	1087.7	975.1	883.0	857.0	888.8	952.6
130°	1369.7	1363.9	1342.6	1302.0	1238.2	1158.8	1044.7	940.2	903.5	922.8	978.9
132.5°	1445.6	1428.9	1410.7	1367.0	1307.8	1225.4	1109.7	1000.6	949.9	958.4	1002.1
135°	1541.9	1526.4	1503.2	1460.7	1404.5	1323.3	1207.2	1089.2	1019.6	1011.8	1037.0
137.5°	1626.6	1610.4	1584.1	1547.3	1490.8	1418.5	1307.0	1182.5	1094.6	1068.7	1078.4
140°	1679.3	1659.9	1636.7	1599.9	1549.6	1474.2	1365.9	1245.9	1147.2	1110.5	1104.7
142.5°	1722.6	1707.9	1683.1	1649.5	1605.4	1529.9	1424.7	1306.3	1201.4	1153.8	1140.3
145°	1787.6	1776.0	1748.9	1718.0	1681.2	1605.8	1509.0	1391.0	1286.5	1224.6	1195.6
147.5°	1842.6	1833.3	1812.0	1775.6	1744.7	1672.3	1584.1	1479.6	1372.4	1295.8	1258.3
150°	1876.6	1868.9	1847.6	1812.8	1781.8	1714.1	1629.0	1532.2	1429.7	1348.4	1300.1
152.5°	1909.1	1901.4	1877.0	1842.2	1815.9	1752.8	1675.4	1583.3	1479.2	1398.0	1348.1
155°	1952.1	1942.4	1919.2	1886.3	1863.1	1805.0	1733.4	1652.2	1563.2	1478.1	1422.0
157.5°	1986.1	1974.1	1952.4	1924.2	1899.4	1846.0	1783.7	1713.7	1635.9	1554.7	1497.4
160°	2006.2	1992.7	1969.5	1944.3	1921.1	1870.8	1814.7	1750.8	1679.3	1605.8	1543.8
162.5°	2020.2	2008.2	1980.3	1958.2	1938.1	1892.5	1839.5	1781.8	1718.0	1653.7	1596.5
165°	2035.2	2021.7	1992.7	1975.3	1957.9	1919.2	1872.7	1826.3	1772.1	1719.9	1673.5
167.5°	2036.4	2025.2	1996.2	1979.1	1966.4	1933.1	1895.6	1860.0	1817.8	1776.8	1738.1
170°	2033.3	2023.6	1994.6	1979.1	1969.5	1942.4	1909.5	1878.5	1845.6	1810.8	1779.9
172.5°	2022.5	2012.8	1985.3	1972.9	1967.9	1943.9	1917.2	1894.0	1865.8	1840.2	1815.5
175°	1994.6	1986.9	1963.7	1955.9	1957.9	1942.4	1923.0	1909.5	1892.1	1876.6	1863.1
177.5°	1954.0	1949.3	1932.3	1932.3	1938.5	1929.2	1923.0	1916.8	1909.1	1904.5	1899.8
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1427558

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6
2.5°	1913.7	1914.3	1922.1	1927.6	1925.9	1924.2	1925.9	1927.6	1922.1	1914.3	1913.7
5°	1912.8	1914.9	1926.5	1934.9	1934.1	1933.2	1934.1	1934.9	1926.5	1914.9	1912.8
7.5°	1916.9	1919.1	1928.6	1935.2	1933.0	1930.9	1933.0	1935.2	1928.6	1919.1	1916.9
10°	1916.3	1917.0	1926.8	1933.6	1931.5	1929.4	1931.5	1933.6	1926.8	1917.0	1916.3
12.5°	1916.4	1913.6	1921.4	1926.3	1922.4	1918.6	1922.4	1926.3	1921.4	1913.6	1916.4
15°	1910.6	1901.2	1902.4	1902.0	1896.4	1890.9	1896.4	1902.0	1902.4	1901.2	1910.6
17.5°	1884.1	1868.3	1863.6	1858.1	1850.3	1842.4	1850.3	1858.1	1863.6	1868.3	1884.1
20°	1854.7	1835.9	1827.7	1819.9	1813.1	1806.3	1813.1	1819.9	1827.7	1835.9	1854.7
22.5°	1814.7	1795.6	1785.4	1776.4	1770.9	1765.5	1770.9	1776.4	1785.4	1795.6	1814.7
25°	1736.3	1718.7	1711.0	1704.5	1701.5	1698.5	1701.5	1704.5	1711.0	1718.7	1736.3
27.5°	1635.1	1620.1	1610.5	1602.4	1598.5	1594.7	1598.5	1602.4	1610.5	1620.1	1635.1
30°	1561.0	1548.2	1537.9	1528.4	1521.1	1513.9	1521.1	1528.4	1537.9	1548.2	1561.0
32.5°	1474.9	1463.8	1452.5	1442.2	1435.0	1427.7	1435.0	1442.2	1452.5	1463.8	1474.9
35°	1327.2	1316.9	1305.8	1295.9	1289.4	1283.0	1289.4	1295.9	1305.8	1316.9	1327.2
37.5°	1147.9	1138.4	1126.4	1116.1	1110.7	1105.3	1110.7	1116.1	1126.4	1138.4	1147.9
40°	1009.1	1000.8	992.3	983.8	975.7	967.6	975.7	983.8	992.3	1000.8	1009.1
42.5°	872.0	861.3	847.6	836.5	833.2	829.8	833.2	836.5	847.6	861.3	872.0
45°	658.7	654.0	638.6	616.1	572.1	528.0	572.1	616.1	638.6	654.0	658.7
47.5°	438.3	430.3	386.4	341.9	295.3	248.7	295.3	341.9	386.4	430.3	438.3
50°	309.2	301.0	235.6	182.6	166.8	151.0	166.8	182.6	235.6	301.0	309.2
52.5°	209.9	207.1	158.4	119.7	110.7	101.8	110.7	119.7	158.4	207.1	209.9
55°	96.0	95.5	75.0	59.0	56.4	53.9	56.4	59.0	75.0	95.5	96.0
57.5°	42.1	42.3	35.1	28.6	24.4	20.2	24.4	28.6	35.1	42.3	42.1
60°	23.0	22.3	15.1	8.7	4.8	1.0	4.8	8.7	15.1	22.3	23.0
62.5°	13.1	13.0	7.1	2.4	1.3	0.2	1.3	2.4	7.1	13.0	13.1
65°	0.7	0.7	0.3	0.0	0.0	0.0	0.0	0.0	0.3	0.7	0.7
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	8.9	11.6	14.3	15.9	17.4	16.6	17.4	15.9	14.3	11.6	8.9
90°	44.5	58.0	71.6	79.3	87.1	83.2	87.1	79.3	71.6	58.0	44.5
92.5°	89.4	112.2	128.8	142.8	149.0	148.2	149.0	142.8	128.8	112.2	89.4
95°	179.9	207.0	234.1	253.4	265.0	261.2	265.0	253.4	234.1	207.0	179.9
97.5°	277.4	313.8	344.0	362.2	373.8	381.5	373.8	362.2	344.0	313.8	277.4
100°	342.4	377.3	412.1	433.4	452.7	460.4	452.7	433.4	412.1	377.3	342.4
102.5°	395.1	440.7	478.6	501.5	517.7	525.4	517.7	501.5	478.6	440.7	395.1
105°	481.7	530.1	570.7	599.7	617.2	623.0	617.2	599.7	570.7	530.1	481.7
107.5°	568.4	618.3	655.8	688.0	709.2	721.6	709.2	688.0	655.8	618.3	568.4
110°	636.5	677.1	717.8	746.8	768.1	775.8	768.1	746.8	717.8	677.1	636.5



TEST NUMBER: P1427558

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	693.8	739.0	779.7	808.7	833.1	843.9	833.1	808.7	779.7	739.0	693.8
115°	773.9	833.8	870.6	897.7	915.1	924.8	915.1	897.7	870.6	833.8	773.9
117.5°	840.4	903.1	943.3	964.2	972.4	979.3	972.4	964.2	943.3	903.1	840.4
120°	882.2	940.2	986.7	1013.8	1023.4	1027.3	1023.4	1013.8	986.7	940.2	882.2
122.5°	920.9	975.8	1020.7	1054.0	1069.9	1073.7	1069.9	1054.0	1020.7	975.8	920.9
125°	975.1	1027.3	1073.7	1106.6	1124.0	1133.7	1124.0	1106.6	1073.7	1027.3	975.1
127.5°	1022.3	1078.8	1121.3	1151.1	1168.1	1175.9	1168.1	1151.1	1121.3	1078.8	1022.3
130°	1048.6	1106.6	1149.2	1182.1	1197.5	1205.3	1197.5	1182.1	1149.2	1106.6	1048.6
132.5°	1068.7	1129.8	1173.9	1203.7	1220.8	1228.5	1220.8	1203.7	1173.9	1129.8	1068.7
135°	1093.1	1156.9	1203.3	1232.4	1247.8	1255.6	1247.8	1232.4	1203.3	1156.9	1093.1
137.5°	1114.4	1172.4	1220.8	1251.3	1265.3	1270.3	1265.3	1251.3	1220.8	1172.4	1114.4
140°	1129.8	1180.1	1228.5	1257.5	1273.0	1274.9	1273.0	1257.5	1228.5	1180.1	1129.8
142.5°	1150.0	1189.4	1231.6	1260.6	1276.1	1279.6	1276.1	1260.6	1231.6	1189.4	1150.0
145°	1185.9	1209.2	1238.2	1265.3	1278.8	1282.7	1278.8	1265.3	1238.2	1209.2	1185.9
147.5°	1231.2	1238.6	1253.6	1271.4	1284.6	1287.3	1284.6	1271.4	1253.6	1238.6	1231.2
150°	1265.3	1263.3	1269.1	1280.7	1292.3	1290.4	1292.3	1280.7	1269.1	1263.3	1265.3
152.5°	1303.9	1292.7	1292.3	1297.8	1303.2	1302.8	1303.2	1297.8	1292.3	1292.7	1303.9
155°	1369.7	1348.4	1336.8	1333.0	1333.0	1331.0	1333.0	1333.0	1336.8	1348.4	1369.7
157.5°	1442.1	1412.3	1394.9	1385.6	1382.9	1378.6	1382.9	1385.6	1394.9	1412.3	1442.1
160°	1491.6	1458.7	1441.3	1425.8	1420.0	1414.2	1420.0	1425.8	1441.3	1458.7	1491.6
162.5°	1538.0	1506.7	1487.7	1473.8	1468.0	1459.1	1468.0	1473.8	1487.7	1506.7	1538.0
165°	1613.5	1580.6	1559.3	1547.7	1540.0	1532.2	1540.0	1547.7	1559.3	1580.6	1613.5
167.5°	1688.9	1653.0	1639.0	1625.9	1618.5	1604.6	1618.5	1625.9	1639.0	1653.0	1688.9
170°	1735.4	1702.5	1694.7	1683.1	1669.6	1654.1	1669.6	1683.1	1694.7	1702.5	1735.4
172.5°	1775.6	1753.6	1745.8	1734.2	1730.0	1717.6	1730.0	1734.2	1745.8	1753.6	1775.6
175°	1834.0	1816.6	1816.6	1814.7	1808.9	1797.3	1808.9	1814.7	1816.6	1816.6	1834.0
177.5°	1882.8	1873.5	1879.7	1879.7	1878.1	1867.3	1878.1	1879.7	1879.7	1873.5	1882.8
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1427558

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	1922.6	1922.6	1922.6	1922.6
2.5°	1920.6	1926.3	1928.7	1931.1
5°	1920.1	1926.1	1928.2	1930.3
7.5°	1922.1	1926.3	1927.7	1929.2
10°	1924.9	1931.4	1931.8	1932.2
12.5°	1929.7	1939.1	1936.4	1933.8
15°	1930.6	1943.9	1936.6	1929.4
17.5°	1910.8	1928.3	1918.1	1907.8
20°	1884.2	1903.3	1891.3	1879.4
22.5°	1842.9	1861.2	1850.3	1839.3
25°	1763.6	1782.3	1775.0	1767.8
27.5°	1655.6	1670.5	1668.5	1666.4
30°	1576.4	1587.9	1587.9	1587.9
32.5°	1485.8	1494.3	1495.3	1496.4
35°	1336.6	1342.5	1337.8	1333.1
37.5°	1155.0	1159.9	1158.1	1156.3
40°	1017.3	1023.2	1022.8	1022.4
42.5°	879.8	883.5	874.8	866.2
45°	652.7	638.7	600.7	562.7
47.5°	410.3	377.5	330.1	282.8
50°	260.0	216.1	187.9	159.7
52.5°	166.9	131.5	119.0	106.6
55°	76.3	60.7	57.3	53.9
57.5°	34.4	27.5	22.9	18.3
60°	17.0	11.4	7.2	2.9
62.5°	7.5	3.0	1.8	0.6
65°	0.3	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	7.0	4.3	2.7	1.2
90°	34.8	21.3	13.5	5.8
92.5°	75.1	52.2	36.8	21.3
95°	150.9	119.9	85.1	60.0
97.5°	240.3	190.4	155.9	114.5
100°	288.3	239.9	207.0	162.5
102.5°	340.9	300.3	255.0	210.5
105°	435.3	385.0	332.8	282.5
107.5°	522.7	467.4	404.7	359.5
110°	578.5	518.5	452.7	412.1



TEST NUMBER: P1427558

CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	632.6	571.1	503.8	463.2
115°	706.1	638.4	576.5	541.7
117.5°	777.0	707.3	641.9	614.4
120°	820.3	750.6	686.8	665.5
122.5°	855.9	787.8	728.6	719.7
125°	909.3	839.6	789.3	800.9
127.5°	952.6	888.8	857.0	883.0
130°	978.9	922.8	903.5	940.2
132.5°	1002.1	958.4	949.9	1000.6
135°	1037.0	1011.8	1019.6	1089.2
137.5°	1078.4	1068.7	1094.6	1182.5
140°	1104.7	1110.5	1147.2	1245.9
142.5°	1140.3	1153.8	1201.4	1306.3
145°	1195.6	1224.6	1286.5	1391.0
147.5°	1258.3	1295.8	1372.4	1479.6
150°	1300.1	1348.4	1429.7	1532.2
152.5°	1348.1	1398.0	1479.2	1583.3
155°	1422.0	1478.1	1563.2	1652.2
157.5°	1497.4	1554.7	1635.9	1713.7
160°	1543.8	1605.8	1679.3	1750.8
162.5°	1596.5	1653.7	1718.0	1781.8
165°	1673.5	1719.9	1772.1	1826.3
167.5°	1738.1	1776.8	1817.8	1860.0
170°	1779.9	1810.8	1845.6	1878.5
172.5°	1815.5	1840.2	1865.8	1894.0
175°	1863.1	1876.6	1892.1	1909.5
177.5°	1899.8	1904.5	1909.1	1916.8
180°	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1427558  
 CATALOG NUMBER: SQ2W-BBM-K-150U-075D-L930-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00