

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427771

Luminaire Tested: SQ2W-F-K-125U-050D-L830-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427771
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-20)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-F-K-125U-050D-L830-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7879.9 lumens
Efficiency: N/A
Efficacy: 127.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 61.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427771

CATALOG NUMBER: SQ2W-F-K-125U-050D-L830-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427771

CATALOG NUMBER: SQ2W-F-K-125U-050D-L830-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	30
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	77	71	66	76	70	65	60	55	51	48	41	39	37	29	27	26	21
3	77	68	61	55	69	61	55	50	48	44	40	36	34	31	25	24	22	17
4	70	60	52	46	63	54	47	42	43	38	34	32	29	27	23	21	19	15
5	64	53	45	39	58	48	41	36	38	33	29	29	26	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	25	26	23	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	24	20	17	17	14	13	10
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11	9
9	47	35	28	23	42	32	25	21	26	21	17	20	16	14	14	12	10	8
10	44	32	25	20	39	29	23	19	23	19	16	18	15	12	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13365	13365	13365	13365
5°	13283	13434	13283	13434
10°	13237	13389	13237	13389
15°	13165	13330	13165	13330
20°	13080	13211	13080	13211
25°	12939	13055	12939	13055
30°	12802	12890	12802	12890
35°	12638	12719	12638	12719
40°	12496	12532	12496	12532
45°	12312	12312	12312	12312
50°	12064	12094	12064	12094
55°	11783	11797	11783	11797
60°	11463	11463	11463	11463
65°	11091	11045	11091	11045
70°	10565	10456	10565	10456
75°	9856	9638	9856	9638
80°	8777	8349	8777	8349
85°	7021	5947	7021	5947

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 12394 cd/sqm



TEST NUMBER: P1427771

CATALOG NUMBER: SQ2W-F-K-125U-050D-L830-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.3	1.0
10°-20°	223.8	2.8
20°-30°	336.9	4.3
30°-40°	402.8	5.1
40°-50°	416.0	5.3
50°-60°	375.2	4.8
60°-70°	287.4	3.6
70°-80°	166.1	2.1
80°-90°	51.0	0.6
90°-100°	151.1	1.9
100°-110°	440.5	5.6
110°-120°	719.0	9.1
120°-130°	912.3	11.6
130°-140°	976.2	12.4
140°-150°	911.5	11.6
150°-160°	750.1	9.5
160°-170°	503.1	6.4
170°-180°	178.6	2.3
0°-30°	639.0	8.1
0°-40°	1041.8	13.2
0°-60°	1833.0	23.3
0°-90°	2337.5	29.7
90°-120°	1310.6	16.6
90°-150°	4110.6	52.2
90°-180°	5542.0	70.3
0°-180°	7879.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	828	828	828	828	828	
5°	820	829	820	829	820	78
15°	788	798	788	798	788	222
25°	726	733	726	733	726	335
35°	641	645	641	645	641	401
45°	539	539	539	539	539	416
55°	419	419	419	419	419	374
65°	290	289	290	289	290	287
75°	158	154	158	154	158	167
85°	38	32	38	32	38	44
90°	6	42	6	82	6	6
95°	59	44	59	259	59	72
105°	280	449	280	617	280	298
115°	537	744	537	916	537	529
125°	794	1179	794	1124	794	710
135°	1080	1544	1080	1244	1080	834
145°	1379	1779	1379	1271	1379	863
155°	1637	1933	1637	1319	1637	753
165°	1810	2015	1810	1519	1810	510
175°	1892	1973	1892	1781	1892	180
180°	1898	1898	1898	1898	1898	



TEST NUMBER: P1427771

CATALOG NUMBER: SQ2W-F-K-125U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	827.8	827.8	827.8	827.8	827.8	827.8	827.8	827.8	827.8	827.8	827.8
2.5°	823.6	827.5	831.5	829.8	826.3	824.9	825.8	826.5	826.9	827.3	826.9
5°	819.6	824.8	830.0	828.2	824.0	822.2	822.7	823.8	826.4	828.9	826.4
7.5°	813.0	818.2	823.3	821.7	817.7	816.1	816.7	817.8	820.5	823.2	820.5
10°	807.4	812.6	817.7	815.9	811.8	810.2	811.3	812.6	814.6	816.7	814.6
12.5°	800.4	805.6	810.7	809.2	805.5	804.0	804.6	805.6	807.9	810.2	807.9
15°	787.6	792.7	797.9	796.5	792.9	791.4	792.2	793.3	795.4	797.5	795.4
17.5°	772.0	776.9	781.8	780.5	777.1	775.9	776.8	777.9	779.7	781.5	779.7
20°	761.3	766.0	770.6	769.3	765.9	764.4	764.6	765.3	767.1	768.9	767.1
22.5°	748.3	752.9	757.6	756.4	753.2	751.4	750.8	750.9	753.1	755.4	753.1
25°	726.3	731.0	735.7	734.7	731.9	730.0	729.3	729.1	730.9	732.8	730.9
27.5°	703.5	707.4	711.3	710.5	708.1	706.6	706.1	706.0	707.3	708.6	707.3
30°	686.7	690.6	694.5	693.5	690.9	689.4	688.8	688.8	690.1	691.4	690.1
32.5°	669.0	672.7	676.3	675.0	672.0	670.4	670.3	670.6	672.1	673.6	672.1
35°	641.2	644.3	647.5	646.1	643.2	641.9	642.2	642.7	644.0	645.3	644.0
37.5°	613.4	615.8	618.1	616.8	614.1	612.8	612.7	612.9	614.0	615.1	614.0
40°	592.9	595.4	598.0	596.5	593.7	592.1	591.9	592.0	593.3	594.6	593.3
42.5°	571.9	573.8	575.8	574.5	572.0	570.9	571.0	571.3	572.0	572.7	572.0
45°	539.2	541.0	542.8	541.6	539.2	538.1	538.1	538.2	538.7	539.2	538.7
47.5°	505.1	506.5	507.9	506.8	505.0	504.0	503.7	503.6	504.5	505.3	504.5
50°	480.3	482.2	484.0	483.1	481.3	480.1	479.6	479.4	480.5	481.5	480.5
52.5°	456.1	458.1	460.1	459.3	457.5	456.2	455.5	455.1	456.0	456.8	456.0
55°	418.6	420.9	423.2	422.6	421.1	419.8	418.7	418.1	418.6	419.1	418.6
57.5°	380.2	382.5	384.8	384.3	383.0	381.7	380.4	379.7	380.4	381.1	380.4
60°	355.0	357.1	359.2	358.5	357.0	355.7	354.6	354.0	354.5	355.0	354.5
62.5°	329.4	331.4	333.5	332.7	330.9	329.5	328.5	327.9	328.4	328.9	328.4
65°	290.3	292.1	293.9	293.2	291.7	290.4	289.3	288.6	288.9	289.1	288.9
67.5°	250.9	252.5	254.0	253.3	251.8	250.3	248.8	247.7	248.2	248.6	248.2
70°	223.8	225.4	227.0	226.4	225.1	223.8	222.5	221.5	221.5	221.5	221.5
72.5°	197.7	199.1	200.4	199.6	198.1	196.8	195.8	194.9	194.9	194.9	194.9
75°	158.0	158.8	159.5	159.1	158.4	157.3	156.0	155.0	154.7	154.5	154.7
77.5°	119.6	119.6	119.6	118.9	117.9	116.9	115.9	115.1	114.8	114.5	114.8
80°	94.4	94.4	94.4	93.9	93.1	92.3	91.5	90.8	90.3	89.8	90.3
82.5°	71.1	70.7	70.3	69.6	68.8	67.8	66.6	65.9	66.4	66.9	66.4
85°	37.9	37.4	36.9	36.1	35.4	34.5	33.4	32.6	32.3	32.1	32.3
87.5°	12.8	13.9	15.4	16.4	16.9	16.6	15.8	15.5	15.6	15.4	15.6
90°	5.8	13.4	23.0	30.7	36.4	38.3	38.3	40.3	42.2	42.2	42.2
92.5°	21.1	33.4	33.7	33.7	41.0	44.5	47.6	47.9	49.9	49.9	49.9
95°	59.4	65.2	97.8	95.9	65.2	51.8	44.1	44.1	44.1	44.1	44.1
97.5°	113.5	121.9	127.3	170.6	180.2	174.1	141.9	119.3	106.6	100.9	106.6
100°	161.1	164.9	176.4	178.3	226.2	272.3	249.3	220.5	210.9	205.2	210.9
102.5°	208.6	210.9	228.5	236.6	247.7	273.8	353.6	344.7	338.2	337.1	338.2
105°	279.9	281.9	314.4	329.8	337.5	337.5	335.5	373.9	435.2	448.7	435.2
107.5°	356.2	365.1	403.4	444.4	453.3	455.6	445.6	439.8	437.5	439.1	437.5
110°	408.4	421.8	467.8	519.6	533.0	536.9	533.0	527.3	523.4	523.4	523.4

TEST NUMBER: P1427771

CATALOG NUMBER: SQ2W-F-K-125U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	459.0	478.6	530.7	590.2	612.8	624.3	615.9	611.6	607.8	610.9	607.8
115°	536.9	565.6	634.6	696.0	742.0	747.8	745.9	745.9	743.9	743.9	743.9
117.5°	609.0	655.0	732.4	803.8	857.1	872.4	880.1	877.8	875.5	879.3	875.5
120°	659.6	713.3	801.5	882.0	933.8	956.8	964.4	960.6	964.4	960.6	964.4
122.5°	713.3	779.2	865.9	949.5	1010.5	1036.5	1045.7	1046.5	1047.3	1045.0	1047.3
125°	793.8	874.3	975.9	1062.2	1125.5	1156.2	1163.8	1165.8	1169.6	1179.2	1169.6
127.5°	875.1	966.4	1077.9	1161.2	1226.0	1263.2	1275.0	1279.3	1287.3	1291.5	1287.3
130°	931.8	1035.4	1148.5	1227.1	1290.4	1330.7	1351.7	1357.5	1367.1	1365.2	1367.1
132.5°	991.7	1099.8	1214.5	1296.1	1354.8	1398.1	1416.2	1432.7	1436.1	1438.8	1436.1
135°	1079.5	1196.4	1311.5	1392.0	1447.6	1489.8	1512.8	1528.1	1537.7	1543.5	1537.7
137.5°	1171.9	1295.4	1405.8	1477.5	1533.5	1569.9	1596.0	1612.1	1622.1	1626.7	1622.1
140°	1234.8	1353.7	1461.0	1535.8	1585.7	1622.1	1645.1	1664.3	1675.8	1675.8	1675.8
142.5°	1294.6	1411.9	1516.3	1591.0	1634.7	1668.1	1692.6	1707.2	1720.3	1720.3	1720.3
145°	1378.6	1495.5	1591.4	1666.2	1702.6	1733.3	1760.1	1771.6	1779.3	1779.3	1779.3
147.5°	1466.4	1569.9	1657.4	1729.1	1759.8	1795.8	1816.9	1826.1	1835.7	1831.5	1835.7
150°	1518.6	1614.4	1698.8	1765.9	1796.6	1831.1	1852.2	1859.8	1869.4	1863.7	1869.4
152.5°	1569.2	1660.4	1737.1	1799.6	1825.7	1860.2	1884.4	1892.1	1898.6	1894.4	1898.6
155°	1637.4	1718.0	1788.9	1846.4	1869.4	1902.0	1925.0	1934.6	1942.3	1932.7	1942.3
157.5°	1698.4	1767.8	1829.5	1882.5	1907.0	1935.0	1956.5	1968.4	1976.0	1971.8	1976.0
160°	1735.2	1798.5	1854.1	1903.9	1927.0	1951.9	1974.9	1988.3	1996.0	1990.2	1996.0
162.5°	1765.9	1823.0	1875.6	1920.8	1940.8	1962.6	1990.2	2002.1	2009.8	2002.5	2009.8
165°	1810.0	1856.0	1902.0	1940.4	1957.6	1974.9	2003.6	2017.1	2022.8	2015.1	2022.8
167.5°	1843.4	1878.6	1915.8	1948.8	1961.5	1978.3	2007.1	2018.2	2025.5	2015.9	2025.5
170°	1861.8	1892.4	1925.0	1951.9	1961.5	1976.8	2005.6	2015.1	2020.9	2011.3	2020.9
172.5°	1877.1	1900.1	1926.6	1950.3	1955.3	1967.6	1994.8	2004.4	2008.6	2000.6	2008.6
175°	1892.4	1905.9	1925.0	1940.4	1938.5	1946.1	1969.1	1976.8	1984.5	1973.0	1984.5
177.5°	1899.7	1905.9	1912.0	1921.2	1915.1	1915.1	1931.9	1936.5	1938.1	1931.9	1938.1
180°	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2



TEST NUMBER: P1427771

CATALOG NUMBER: SQ2W-F-K-125U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	827.8	827.8	827.8	827.8	827.8	827.8	827.8	827.8	827.8	827.8	827.8
2.5°	826.5	825.8	824.9	826.3	829.8	831.5	827.5	823.6	827.5	831.5	829.8
5°	823.8	822.7	822.2	824.0	828.2	830.0	824.8	819.6	824.8	830.0	828.2
7.5°	817.8	816.7	816.1	817.7	821.7	823.3	818.2	813.0	818.2	823.3	821.7
10°	812.6	811.3	810.2	811.8	815.9	817.7	812.6	807.4	812.6	817.7	815.9
12.5°	805.6	804.6	804.0	805.5	809.2	810.7	805.6	800.4	805.6	810.7	809.2
15°	793.3	792.2	791.4	792.9	796.5	797.9	792.7	787.6	792.7	797.9	796.5
17.5°	777.9	776.8	775.9	777.1	780.5	781.8	776.9	772.0	776.9	781.8	780.5
20°	765.3	764.6	764.4	765.9	769.3	770.6	766.0	761.3	766.0	770.6	769.3
22.5°	750.9	750.8	751.4	753.2	756.4	757.6	752.9	748.3	752.9	757.6	756.4
25°	729.1	729.3	730.0	731.9	734.7	735.7	731.0	726.3	731.0	735.7	734.7
27.5°	706.0	706.1	706.6	708.1	710.5	711.3	707.4	703.5	707.4	711.3	710.5
30°	688.8	688.8	689.4	690.9	693.5	694.5	690.6	686.7	690.6	694.5	693.5
32.5°	670.6	670.3	670.4	672.0	675.0	676.3	672.7	669.0	672.7	676.3	675.0
35°	642.7	642.2	641.9	643.2	646.1	647.5	644.3	641.2	644.3	647.5	646.1
37.5°	612.9	612.7	612.8	614.1	616.8	618.1	615.8	613.4	615.8	618.1	616.8
40°	592.0	591.9	592.1	593.7	596.5	598.0	595.4	592.9	595.4	598.0	596.5
42.5°	571.3	571.0	570.9	572.0	574.5	575.8	573.8	571.9	573.8	575.8	574.5
45°	538.2	538.1	538.1	539.2	541.6	542.8	541.0	539.2	541.0	542.8	541.6
47.5°	503.6	503.7	504.0	505.0	506.8	507.9	506.5	505.1	506.5	507.9	506.8
50°	479.4	479.6	480.1	481.3	483.1	484.0	482.2	480.3	482.2	484.0	483.1
52.5°	455.1	455.5	456.2	457.5	459.3	460.1	458.1	456.1	458.1	460.1	459.3
55°	418.1	418.7	419.8	421.1	422.6	423.2	420.9	418.6	420.9	423.2	422.6
57.5°	379.7	380.4	381.7	383.0	384.3	384.8	382.5	380.2	382.5	384.8	384.3
60°	354.0	354.6	355.7	357.0	358.5	359.2	357.1	355.0	357.1	359.2	358.5
62.5°	327.9	328.5	329.5	330.9	332.7	333.5	331.4	329.4	331.4	333.5	332.7
65°	288.6	289.3	290.4	291.7	293.2	293.9	292.1	290.3	292.1	293.9	293.2
67.5°	247.7	248.8	250.3	251.8	253.3	254.0	252.5	250.9	252.5	254.0	253.3
70°	221.5	222.5	223.8	225.1	226.4	227.0	225.4	223.8	225.4	227.0	226.4
72.5°	194.9	195.8	196.8	198.1	199.6	200.4	199.1	197.7	199.1	200.4	199.6
75°	155.0	156.0	157.3	158.4	159.1	159.5	158.8	158.0	158.8	159.5	159.1
77.5°	115.1	115.9	116.9	117.9	118.9	119.6	119.6	119.6	119.6	119.6	118.9
80°	90.8	91.5	92.3	93.1	93.9	94.4	94.4	94.4	94.4	94.4	93.9
82.5°	65.9	66.6	67.8	68.8	69.6	70.3	70.7	71.1	70.7	70.3	69.6
85°	32.6	33.4	34.5	35.4	36.1	36.9	37.4	37.9	37.4	36.9	36.1
87.5°	15.5	15.8	16.6	16.9	16.4	15.4	13.9	12.8	13.9	15.0	17.2
90°	40.3	38.3	38.3	36.4	30.7	23.0	13.4	5.8	13.4	21.1	34.5
92.5°	47.9	47.6	44.5	41.0	33.7	33.7	33.4	21.1	36.4	51.8	74.4
95°	44.1	44.1	51.8	65.2	95.9	97.8	65.2	59.4	84.4	118.9	149.6
97.5°	119.3	141.9	174.1	180.2	170.6	127.3	121.9	113.5	154.5	188.7	238.1
100°	220.5	249.3	272.3	226.2	178.3	176.4	164.9	161.1	205.2	237.8	285.7
102.5°	344.7	353.6	273.8	247.7	236.6	228.5	210.9	208.6	252.7	297.6	337.8
105°	373.9	335.5	337.5	337.5	329.8	314.4	281.9	279.9	329.8	381.6	431.4
107.5°	439.8	445.6	455.6	453.3	444.4	403.4	365.1	356.2	401.1	463.2	518.1
110°	527.3	533.0	536.9	533.0	519.6	467.8	421.8	408.4	448.7	513.9	573.3



TEST NUMBER: P1427771

CATALOG NUMBER: SQ2W-F-K-125U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	611.6	615.9	624.3	612.8	590.2	530.7	478.6	459.0	499.3	566.0	627.0
115°	745.9	745.9	747.8	742.0	696.0	634.6	565.6	536.9	571.4	632.7	699.8
117.5°	877.8	880.1	872.4	857.1	803.8	732.4	655.0	609.0	636.2	701.0	770.0
120°	960.6	964.4	956.8	933.8	882.0	801.5	713.3	659.6	680.7	743.9	813.0
122.5°	1046.5	1045.7	1036.5	1010.5	949.5	865.9	779.2	713.3	722.1	780.8	848.2
125°	1165.8	1163.8	1156.2	1125.5	1062.2	975.9	874.3	793.8	782.3	832.1	901.2
127.5°	1279.3	1275.0	1263.2	1226.0	1161.2	1077.9	966.4	875.1	849.4	880.8	944.1
130°	1357.5	1351.7	1330.7	1290.4	1227.1	1148.5	1035.4	931.8	895.4	914.6	970.2
132.5°	1432.7	1416.2	1398.1	1354.8	1296.1	1214.5	1099.8	991.7	941.4	949.9	993.2
135°	1528.1	1512.8	1489.8	1447.6	1392.0	1311.5	1196.4	1079.5	1010.5	1002.8	1027.7
137.5°	1612.1	1596.0	1569.9	1533.5	1477.5	1405.8	1295.4	1171.9	1084.8	1059.2	1068.7
140°	1664.3	1645.1	1622.1	1585.7	1535.8	1461.0	1353.7	1234.8	1137.0	1100.6	1094.8
142.5°	1707.2	1692.6	1668.1	1634.7	1591.0	1516.3	1411.9	1294.6	1190.7	1143.5	1130.1
145°	1771.6	1760.1	1733.3	1702.6	1666.2	1591.4	1495.5	1378.6	1275.0	1213.7	1184.9
147.5°	1826.1	1816.9	1795.8	1759.8	1729.1	1657.4	1569.9	1466.4	1360.2	1284.3	1247.1
150°	1859.8	1852.2	1831.1	1796.6	1765.9	1698.8	1614.4	1518.6	1416.9	1336.4	1288.5
152.5°	1892.1	1884.4	1860.2	1825.7	1799.6	1737.1	1660.4	1569.2	1466.0	1385.5	1336.0
155°	1934.6	1925.0	1902.0	1869.4	1846.4	1788.9	1718.0	1637.4	1549.2	1464.9	1409.3
157.5°	1968.4	1956.5	1935.0	1907.0	1882.5	1829.5	1767.8	1698.4	1621.3	1540.8	1484.0
160°	1988.3	1974.9	1951.9	1927.0	1903.9	1854.1	1798.5	1735.2	1664.3	1591.4	1530.1
162.5°	2002.1	1990.2	1962.6	1940.8	1920.8	1875.6	1823.0	1765.9	1702.6	1639.0	1582.2
165°	2017.1	2003.6	1974.9	1957.6	1940.4	1902.0	1856.0	1810.0	1756.3	1704.5	1658.5
167.5°	2018.2	2007.1	1978.3	1961.5	1948.8	1915.8	1878.6	1843.4	1801.6	1760.9	1722.6
170°	2015.1	2005.6	1976.8	1961.5	1951.9	1925.0	1892.4	1861.8	1829.2	1794.7	1764.0
172.5°	2004.4	1994.8	1967.6	1955.3	1950.3	1926.6	1900.1	1877.1	1849.1	1823.8	1799.3
175°	1976.8	1969.1	1946.1	1938.5	1940.4	1925.0	1905.9	1892.4	1875.2	1859.8	1846.4
177.5°	1936.5	1931.9	1915.1	1915.1	1921.2	1912.0	1905.9	1899.7	1892.1	1887.5	1882.9
180°	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2



TEST NUMBER: P1427771

CATALOG NUMBER: SQ2W-F-K-125U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	827.8	827.8	827.8	827.8	827.8	827.8	827.8	827.8	827.8	827.8	827.8
2.5°	826.3	824.9	825.8	826.5	826.9	827.3	826.9	826.5	825.8	824.9	826.3
5°	824.0	822.2	822.7	823.8	826.4	828.9	826.4	823.8	822.7	822.2	824.0
7.5°	817.7	816.1	816.7	817.8	820.5	823.2	820.5	817.8	816.7	816.1	817.7
10°	811.8	810.2	811.3	812.6	814.6	816.7	814.6	812.6	811.3	810.2	811.8
12.5°	805.5	804.0	804.6	805.6	807.9	810.2	807.9	805.6	804.6	804.0	805.5
15°	792.9	791.4	792.2	793.3	795.4	797.5	795.4	793.3	792.2	791.4	792.9
17.5°	777.1	775.9	776.8	777.9	779.7	781.5	779.7	777.9	776.8	775.9	777.1
20°	765.9	764.4	764.6	765.3	767.1	768.9	767.1	765.3	764.6	764.4	765.9
22.5°	753.2	751.4	750.8	750.9	753.1	755.4	753.1	750.9	750.8	751.4	753.2
25°	731.9	730.0	729.3	729.1	730.9	732.8	730.9	729.1	729.3	730.0	731.9
27.5°	708.1	706.6	706.1	706.0	707.3	708.6	707.3	706.0	706.1	706.6	708.1
30°	690.9	689.4	688.8	688.8	690.1	691.4	690.1	688.8	688.8	689.4	690.9
32.5°	672.0	670.4	670.3	670.6	672.1	673.6	672.1	670.6	670.3	670.4	672.0
35°	643.2	641.9	642.2	642.7	644.0	645.3	644.0	642.7	642.2	641.9	643.2
37.5°	614.1	612.8	612.7	612.9	614.0	615.1	614.0	612.9	612.7	612.8	614.1
40°	593.7	592.1	591.9	592.0	593.3	594.6	593.3	592.0	591.9	592.1	593.7
42.5°	572.0	570.9	571.0	571.3	572.0	572.7	572.0	571.3	571.0	570.9	572.0
45°	539.2	538.1	538.1	538.2	538.7	539.2	538.7	538.2	538.1	538.1	539.2
47.5°	505.0	504.0	503.7	503.6	504.5	505.3	504.5	503.6	503.7	504.0	505.0
50°	481.3	480.1	479.6	479.4	480.5	481.5	480.5	479.4	479.6	480.1	481.3
52.5°	457.5	456.2	455.5	455.1	456.0	456.8	456.0	455.1	455.5	456.2	457.5
55°	421.1	419.8	418.7	418.1	418.6	419.1	418.6	418.1	418.7	419.8	421.1
57.5°	383.0	381.7	380.4	379.7	380.4	381.1	380.4	379.7	380.4	381.7	383.0
60°	357.0	355.7	354.6	354.0	354.5	355.0	354.5	354.0	354.6	355.7	357.0
62.5°	330.9	329.5	328.5	327.9	328.4	328.9	328.4	327.9	328.5	329.5	330.9
65°	291.7	290.4	289.3	288.6	288.9	289.1	288.9	288.6	289.3	290.4	291.7
67.5°	251.8	250.3	248.8	247.7	248.2	248.6	248.2	247.7	248.8	250.3	251.8
70°	225.1	223.8	222.5	221.5	221.5	221.5	221.5	221.5	222.5	223.8	225.1
72.5°	198.1	196.8	195.8	194.9	194.9	194.9	194.9	194.9	195.8	196.8	198.1
75°	158.4	157.3	156.0	155.0	154.7	154.5	154.7	155.0	156.0	157.3	158.4
77.5°	117.9	116.9	115.9	115.1	114.8	114.5	114.8	115.1	115.9	116.9	117.9
80°	93.1	92.3	91.5	90.8	90.3	89.8	90.3	90.8	91.5	92.3	93.1
82.5°	68.8	67.8	66.6	65.9	66.4	66.9	66.4	65.9	66.6	67.8	68.8
85°	35.4	34.5	33.4	32.6	32.3	32.1	32.3	32.6	33.4	34.5	35.4
87.5°	18.5	20.4	22.3	23.1	24.5	23.5	24.5	23.1	22.3	20.4	18.5
90°	44.1	57.5	70.9	78.6	86.3	82.4	86.3	78.6	70.9	57.5	44.1
92.5°	88.6	111.2	127.7	141.5	147.6	146.9	147.6	141.5	127.7	111.2	88.6
95°	178.3	205.2	232.0	251.2	262.7	258.8	262.7	251.2	232.0	205.2	178.3
97.5°	275.0	311.0	340.9	358.9	370.4	378.1	370.4	358.9	340.9	311.0	275.0
100°	339.4	373.9	408.4	429.5	448.7	456.3	448.7	429.5	408.4	373.9	339.4
102.5°	391.5	436.8	474.4	497.0	513.1	520.8	513.1	497.0	474.4	436.8	391.5
105°	477.4	525.4	565.6	594.4	611.6	617.4	611.6	594.4	565.6	525.4	477.4
107.5°	563.3	612.8	650.0	681.8	702.9	715.2	702.9	681.8	650.0	612.8	563.3
110°	630.8	671.1	711.3	740.1	761.2	768.9	761.2	740.1	711.3	671.1	630.8



TEST NUMBER: P1427771

CATALOG NUMBER: SQ2W-F-K-125U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	687.6	732.4	772.7	801.5	825.6	836.4	825.6	801.5	772.7	732.4	687.6
115°	766.9	826.4	862.8	889.7	906.9	916.5	906.9	889.7	862.8	826.4	766.9
117.5°	832.9	895.0	934.9	955.6	963.7	970.6	963.7	955.6	934.9	895.0	832.9
120°	874.3	931.8	977.9	1004.7	1014.3	1018.1	1014.3	1004.7	977.9	931.8	874.3
122.5°	912.7	967.1	1011.6	1044.6	1060.3	1064.1	1060.3	1044.6	1011.6	967.1	912.7
125°	966.4	1018.1	1064.1	1096.7	1114.0	1123.6	1114.0	1096.7	1064.1	1018.1	966.4
127.5°	1013.1	1069.1	1111.3	1140.8	1157.7	1165.4	1157.7	1140.8	1111.3	1069.1	1013.1
130°	1039.2	1096.7	1138.9	1171.5	1186.8	1194.5	1186.8	1171.5	1138.9	1096.7	1039.2
132.5°	1059.2	1119.7	1163.5	1193.0	1209.9	1217.5	1209.9	1193.0	1163.5	1119.7	1059.2
135°	1083.3	1146.6	1192.6	1221.4	1236.7	1244.4	1236.7	1221.4	1192.6	1146.6	1083.3
137.5°	1104.4	1161.9	1209.9	1240.2	1254.0	1258.9	1254.0	1240.2	1209.9	1161.9	1104.4
140°	1119.7	1169.6	1217.5	1246.3	1261.6	1263.5	1261.6	1246.3	1217.5	1169.6	1119.7
142.5°	1139.7	1178.8	1220.6	1249.4	1264.7	1268.1	1264.7	1249.4	1220.6	1178.8	1139.7
145°	1175.3	1198.4	1227.1	1254.0	1267.4	1271.2	1267.4	1254.0	1227.1	1198.4	1175.3
147.5°	1220.2	1227.5	1242.5	1260.1	1273.1	1275.8	1273.1	1260.1	1242.5	1227.5	1220.2
150°	1254.0	1252.0	1257.8	1269.3	1280.8	1278.9	1280.8	1269.3	1257.8	1252.0	1254.0
152.5°	1292.3	1281.2	1280.8	1286.2	1291.5	1291.2	1291.5	1286.2	1280.8	1281.2	1292.3
155°	1357.5	1336.4	1324.9	1321.1	1321.1	1319.1	1321.1	1321.1	1324.9	1336.4	1357.5
157.5°	1429.2	1399.7	1382.4	1373.2	1370.5	1366.3	1370.5	1373.2	1382.4	1399.7	1429.2
160°	1478.3	1445.7	1428.4	1413.1	1407.3	1401.6	1407.3	1413.1	1428.4	1445.7	1478.3
162.5°	1524.3	1493.2	1474.5	1460.6	1454.9	1446.1	1454.9	1460.6	1474.5	1493.2	1524.3
165°	1599.1	1566.5	1545.4	1533.9	1526.2	1518.6	1526.2	1533.9	1545.4	1566.5	1599.1
167.5°	1673.9	1638.2	1624.4	1611.4	1604.1	1590.3	1604.1	1611.4	1624.4	1638.2	1673.9
170°	1719.9	1687.3	1679.6	1668.1	1654.7	1639.3	1654.7	1668.1	1679.6	1687.3	1719.9
172.5°	1759.8	1737.9	1730.2	1718.7	1714.5	1702.2	1714.5	1718.7	1730.2	1737.9	1759.8
175°	1817.7	1800.4	1800.4	1798.5	1792.7	1781.2	1792.7	1798.5	1800.4	1800.4	1817.7
177.5°	1866.0	1856.8	1862.9	1862.9	1861.4	1850.6	1861.4	1862.9	1862.9	1856.8	1866.0
180°	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2



TEST NUMBER: P1427771

CATALOG NUMBER: SQ2W-F-K-125U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	827.8	827.8	827.8	827.8
2.5°	829.8	831.5	827.5	823.6
5°	828.2	830.0	824.8	819.6
7.5°	821.7	823.3	818.2	813.0
10°	815.9	817.7	812.6	807.4
12.5°	809.2	810.7	805.6	800.4
15°	796.5	797.9	792.7	787.6
17.5°	780.5	781.8	776.9	772.0
20°	769.3	770.6	766.0	761.3
22.5°	756.4	757.6	752.9	748.3
25°	734.7	735.7	731.0	726.3
27.5°	710.5	711.3	707.4	703.5
30°	693.5	694.5	690.6	686.7
32.5°	675.0	676.3	672.7	669.0
35°	646.1	647.5	644.3	641.2
37.5°	616.8	618.1	615.8	613.4
40°	596.5	598.0	595.4	592.9
42.5°	574.5	575.8	573.8	571.9
45°	541.6	542.8	541.0	539.2
47.5°	506.8	507.9	506.5	505.1
50°	483.1	484.0	482.2	480.3
52.5°	459.3	460.1	458.1	456.1
55°	422.6	423.2	420.9	418.6
57.5°	384.3	384.8	382.5	380.2
60°	358.5	359.2	357.1	355.0
62.5°	332.7	333.5	331.4	329.4
65°	293.2	293.9	292.1	290.3
67.5°	253.3	254.0	252.5	250.9
70°	226.4	227.0	225.4	223.8
72.5°	199.6	200.4	199.1	197.7
75°	159.1	159.5	158.8	158.0
77.5°	118.9	119.6	119.6	119.6
80°	93.9	94.4	94.4	94.4
82.5°	69.6	70.3	70.7	71.1
85°	36.1	36.9	37.4	37.9
87.5°	17.2	15.0	13.9	12.8
90°	34.5	21.1	13.4	5.8
92.5°	74.4	51.8	36.4	21.1
95°	149.6	118.9	84.4	59.4
97.5°	238.1	188.7	154.5	113.5
100°	285.7	237.8	205.2	161.1
102.5°	337.8	297.6	252.7	208.6
105°	431.4	381.6	329.8	279.9
107.5°	518.1	463.2	401.1	356.2
110°	573.3	513.9	448.7	408.4

TEST NUMBER: P1427771

CATALOG NUMBER: SQ2W-F-K-125U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	627.0	566.0	499.3	459.0
115°	699.8	632.7	571.4	536.9
117.5°	770.0	701.0	636.2	609.0
120°	813.0	743.9	680.7	659.6
122.5°	848.2	780.8	722.1	713.3
125°	901.2	832.1	782.3	793.8
127.5°	944.1	880.8	849.4	875.1
130°	970.2	914.6	895.4	931.8
132.5°	993.2	949.9	941.4	991.7
135°	1027.7	1002.8	1010.5	1079.5
137.5°	1068.7	1059.2	1084.8	1171.9
140°	1094.8	1100.6	1137.0	1234.8
142.5°	1130.1	1143.5	1190.7	1294.6
145°	1184.9	1213.7	1275.0	1378.6
147.5°	1247.1	1284.3	1360.2	1466.4
150°	1288.5	1336.4	1416.9	1518.6
152.5°	1336.0	1385.5	1466.0	1569.2
155°	1409.3	1464.9	1549.2	1637.4
157.5°	1484.0	1540.8	1621.3	1698.4
160°	1530.1	1591.4	1664.3	1735.2
162.5°	1582.2	1639.0	1702.6	1765.9
165°	1658.5	1704.5	1756.3	1810.0
167.5°	1722.6	1760.9	1801.6	1843.4
170°	1764.0	1794.7	1829.2	1861.8
172.5°	1799.3	1823.8	1849.1	1877.1
175°	1846.4	1859.8	1875.2	1892.4
177.5°	1882.9	1887.5	1892.1	1899.7
180°	1898.2	1898.2	1898.2	1898.2



TEST NUMBER: P1427771
 CATALOG NUMBER: SQ2W-F-K-125U-050D-L830-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.61	15.32	15.72	16.43	17.97	14.53	15.24	15.64	16.35	17.88
	3H	16.39	17.03	17.51	18.14	19.69	16.29	16.92	17.41	18.04	19.59
	4H	17.08	17.68	18.21	18.80	20.36	16.96	17.57	18.09	18.69	20.24
	6H	17.51	18.07	18.65	19.19	20.75	17.37	17.92	18.51	19.04	20.61
	8H	17.66	18.19	18.81	19.33	20.89	17.51	18.04	18.65	19.17	20.73
	12H	17.74	18.25	18.89	19.38	20.96	17.57	18.07	18.71	19.20	20.78
4H	2H	15.17	15.78	16.31	16.90	18.45	15.11	15.71	16.25	16.83	18.39
	3H	17.18	17.69	18.33	18.83	20.40	17.09	17.59	18.23	18.74	20.31
	4H	17.99	18.45	19.14	19.59	21.17	17.88	18.34	19.02	19.47	21.06
	6H	18.53	18.93	19.69	20.09	21.66	18.39	18.79	19.54	19.95	21.52
	8H	18.74	19.11	19.90	20.26	21.86	18.58	18.96	19.74	20.10	21.70
	12H	18.85	19.19	20.02	20.35	21.95	18.66	19.00	19.83	20.16	21.76
8H	4H	18.22	18.59	19.37	19.74	21.34	18.12	18.49	19.27	19.64	21.24
	6H	18.90	19.21	20.08	20.40	21.99	18.77	19.08	19.94	20.27	21.86
	8H	19.21	19.47	20.38	20.64	22.25	19.05	19.32	20.23	20.49	22.10
	12H	19.38	19.62	20.56	20.78	22.43	19.19	19.43	20.37	20.59	22.24
12H	4H	18.21	18.54	19.38	19.70	21.30	18.11	18.45	19.28	19.61	21.21
	6H	18.95	19.22	20.13	20.39	22.00	18.83	19.09	20.00	20.26	21.87
	8H	19.28	19.51	20.46	20.68	22.32	19.13	19.36	20.31	20.53	22.17