

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427606

Luminaire Tested: SQ2W-BBN-K-075U-075D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2024
Report Number: P1427606
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2308-130-1)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-BBN-K-075U-075D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - BLACK DISCREET BAFFLE, NARROW 35-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5668.3 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.62
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 51.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427606

CATALOG NUMBER: SQ2W-BBN-K-075U-075D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427606

CATALOG NUMBER: SQ2W-BBN-K-075U-075D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51		
1	100	97	94	91	93	90	88	85	77	75	74	65	64	63	54	54	53	48		
2	94	88	84	80	87	82	78	75	71	68	66	61	59	57	51	50	49	45		
3	88	81	75	70	82	75	71	67	66	62	59	57	54	52	49	47	46	42		
4	82	74	68	63	77	69	64	60	61	57	54	53	50	48	46	44	43	39		
5	77	68	61	57	72	64	58	54	57	52	49	50	47	45	43	41	40	37		
6	72	63	56	52	68	59	54	49	53	49	45	47	44	41	41	39	37	35		
7	68	58	52	47	64	55	50	45	50	45	42	44	41	39	39	37	35	33		
8	64	54	48	44	60	52	46	42	46	42	39	42	38	36	37	35	33	31		
9	61	51	45	40	57	48	43	39	44	39	36	39	36	34	35	33	31	29		
10	58	48	42	38	54	46	40	36	41	37	34	37	34	32	34	31	30	28		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	86235	86235	86235	86235
5°	83351	83398	83351	83398
10°	71533	71533	71533	71533
15°	55523	55394	55523	55394
20°	40071	39212	40071	39212
25°	28413	27333	28413	27333
30°	21140	20403	21140	20403
35°	16448	15689	16448	15689
40°	12172	11118	12172	11118
45°	6220	5012	6220	5012
50°	1354	992	1354	992
55°	380	298	380	298
60°	61	32	61	32
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 7587 cd/sqm



TEST NUMBER: P1427606

CATALOG NUMBER: SQ2W-BBN-K-075U-075D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	461.9	8.1
10°-20°	910.6	16.1
20°-30°	734.5	13.0
30°-40°	510.3	9.0
40°-50°	235.7	4.2
50°-60°	33.0	0.6
60°-70°	1.1	0.0
70°-80°	0.0	0.0
80°-90°	5.0	0.1
90°-100°	75.7	1.3
100°-110°	220.8	3.9
110°-120°	360.3	6.4
120°-130°	457.2	8.1
130°-140°	489.2	8.6
140°-150°	456.8	8.1
150°-160°	375.9	6.6
160°-170°	252.1	4.4
170°-180°	89.5	1.6
0°-30°	2107.0	37.2
0°-40°	2617.3	46.2
0°-60°	2886.0	50.9
0°-90°	2892.1	51.0
90°-120°	656.7	11.6
90°-150°	2059.9	36.3
90°-180°	2777.0	49.0
0°-180°	5668.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	5341	5341	5341	5341	5341	
5°	5143	5146	5143	5146	5143	462
15°	3322	3314	3322	3314	3322	914
25°	1595	1534	1595	1534	1595	747
35°	834	796	834	796	834	522
45°	272	220	272	220	272	220
55°	14	11	14	11	14	17
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	3	21	3	41	3	2
95°	30	22	30	130	30	36
105°	140	225	140	309	140	149
115°	269	373	269	459	269	265
125°	398	591	398	563	398	356
135°	541	773	541	624	541	418
145°	691	892	691	637	691	432
155°	820	968	820	661	820	377
165°	907	1010	907	761	907	255
175°	948	989	948	893	948	90
180°	951	951	951	951	951	



TEST NUMBER: P1427606

CATALOG NUMBER: SQ2W-BBN-K-075U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	5341.1	5341.1	5341.1	5341.1	5341.1	5341.1	5341.1	5341.1	5341.1	5341.1	5341.1
2.5°	5338.0	5329.1	5320.2	5302.6	5282.1	5281.2	5300.0	5312.7	5306.9	5301.1	5306.9
5°	5142.8	5130.4	5118.0	5103.0	5087.2	5093.2	5121.0	5142.3	5144.0	5145.7	5144.0
7.5°	4712.0	4716.0	4720.0	4709.8	4694.7	4702.6	4733.4	4755.6	4752.3	4749.0	4752.3
10°	4363.2	4366.2	4369.2	4368.6	4366.9	4371.2	4381.5	4386.3	4374.7	4363.2	4374.7
12.5°	3958.9	3970.8	3982.7	3969.0	3946.7	3943.3	3958.7	3971.5	3976.4	3981.2	3976.4
15°	3321.7	3341.0	3360.2	3332.9	3290.2	3279.0	3299.6	3314.9	3314.4	3314.0	3314.4
17.5°	2724.2	2722.2	2720.2	2703.4	2681.6	2672.6	2676.4	2679.0	2677.7	2676.4	2677.7
20°	2332.2	2329.2	2326.2	2311.7	2293.3	2282.6	2279.6	2277.9	2280.0	2282.2	2280.0
22.5°	1996.5	1991.4	1986.4	1980.3	1973.9	1967.0	1959.5	1954.7	1957.5	1960.3	1957.5
25°	1594.9	1578.7	1562.4	1549.4	1537.4	1536.5	1546.8	1552.2	1543.3	1534.3	1543.3
27.5°	1280.2	1279.9	1279.7	1272.0	1261.8	1257.2	1258.4	1259.6	1261.3	1263.0	1261.3
30°	1133.9	1130.9	1127.9	1119.7	1109.9	1105.2	1105.6	1104.7	1099.5	1094.4	1099.5
32.5°	1003.7	1005.9	1008.0	999.4	987.1	979.9	977.6	974.5	969.4	964.3	969.4
35°	834.5	834.5	834.5	827.5	818.0	810.1	803.7	798.6	797.3	796.0	797.3
37.5°	677.6	676.9	676.1	670.9	664.2	656.3	647.3	639.6	636.3	633.0	636.3
40°	577.5	575.4	573.2	569.5	565.2	557.5	546.4	536.9	532.2	527.5	532.2
42.5°	463.6	469.3	475.0	473.2	469.0	461.3	450.1	440.0	432.9	425.8	432.9
45°	272.4	296.4	320.3	328.9	332.3	327.6	314.7	295.6	257.5	219.5	257.5
47.5°	117.0	143.4	169.7	191.9	212.6	206.0	172.2	139.0	107.3	75.7	107.3
50°	53.9	74.4	95.0	122.6	152.5	146.3	104.0	68.6	54.0	39.5	54.0
52.5°	31.6	41.8	52.1	77.9	108.9	106.1	69.6	40.2	32.5	24.8	32.5
55°	13.5	16.9	20.3	34.3	51.9	51.0	31.8	16.6	13.6	10.6	13.6
57.5°	5.0	6.9	8.8	13.8	19.9	19.5	12.6	7.1	5.6	4.0	5.6
60°	1.9	2.8	3.6	6.1	9.1	8.9	5.5	2.7	1.8	1.0	1.8
62.5°	0.4	0.9	1.4	2.8	4.4	4.3	2.6	1.2	0.7	0.2	0.7
65°	0.0	0.0	0.0	0.3	0.7	0.7	0.3	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.6	1.3	2.3	3.1	3.7	3.8	3.8	4.0	4.2	4.2	4.2
90°	2.9	6.7	11.5	15.4	18.3	19.2	19.2	20.2	21.1	21.1	21.1
92.5°	10.6	16.7	16.9	16.9	20.6	22.3	23.8	24.0	25.0	25.0	25.0
95°	29.8	32.7	49.0	48.0	32.7	25.9	22.1	22.1	22.1	22.1	22.1
97.5°	56.9	61.1	63.8	85.5	90.3	87.2	71.1	59.8	53.4	50.5	53.4
100°	80.7	82.6	88.4	89.4	113.4	136.4	124.9	110.5	105.7	102.8	105.7
102.5°	104.5	105.7	114.5	118.6	124.1	137.2	177.2	172.8	169.5	168.9	169.5
105°	140.3	141.2	157.6	165.3	169.1	169.1	168.1	187.4	218.1	224.8	218.1
107.5°	178.5	182.9	202.2	222.7	227.1	228.3	223.3	220.4	219.3	220.0	219.3
110°	204.7	211.4	234.4	260.4	267.1	269.0	267.1	264.2	262.3	262.3	262.3



TEST NUMBER: P1427606

CATALOG NUMBER: SQ2W-BBN-K-075U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	230.0	239.8	266.0	295.7	307.1	312.8	308.6	306.5	304.6	306.1	304.6
115°	269.0	283.4	318.0	348.8	371.8	374.7	373.8	373.8	372.8	372.8	372.8
117.5°	305.2	328.2	367.0	402.8	429.5	437.2	441.0	439.9	438.7	440.6	438.7
120°	330.5	357.4	401.6	442.0	467.9	479.4	483.3	481.4	483.3	481.4	483.3
122.5°	357.4	390.5	433.9	475.8	506.3	519.4	524.0	524.4	524.8	523.6	524.8
125°	397.8	438.1	489.1	532.3	564.0	579.4	583.2	584.2	586.1	590.9	586.1
127.5°	438.5	484.2	540.2	581.9	614.3	633.0	638.9	641.0	645.1	647.2	645.1
130°	467.0	518.8	575.5	614.9	646.6	666.8	677.4	680.3	685.1	684.1	685.1
132.5°	496.9	551.1	608.6	649.5	678.9	700.6	709.7	717.9	719.6	721.0	719.6
135°	540.9	599.5	657.2	697.5	725.4	746.5	758.1	765.8	770.6	773.4	770.6
137.5°	587.2	649.1	704.5	740.4	768.5	786.7	799.8	807.8	812.8	815.1	812.8
140°	618.8	678.3	732.1	769.6	794.6	812.8	824.4	834.0	839.7	839.7	839.7
142.5°	648.7	707.5	759.8	797.3	819.2	835.9	848.2	855.5	862.0	862.0	862.0
145°	690.8	749.4	797.5	834.9	853.2	868.6	882.0	887.8	891.6	891.6	891.6
147.5°	734.8	786.7	830.5	866.5	881.8	899.9	910.5	915.1	919.9	917.8	919.9
150°	761.0	809.0	851.3	884.9	900.3	917.6	928.1	932.0	936.8	933.9	936.8
152.5°	786.3	832.1	870.5	901.8	914.9	932.2	944.3	948.1	951.4	949.3	951.4
155°	820.5	860.9	896.4	925.3	936.8	953.1	964.6	969.5	973.3	968.5	973.3
157.5°	851.1	885.9	916.8	943.3	955.6	969.6	980.4	986.4	990.2	988.1	990.2
160°	869.5	901.2	929.1	954.1	965.6	978.1	989.6	996.4	1000.2	997.3	1000.2
162.5°	884.9	913.5	939.9	962.5	972.5	983.5	997.3	1003.3	1007.1	1003.5	1007.1
165°	907.0	930.1	953.1	972.3	981.0	989.6	1004.0	1010.8	1013.7	1009.8	1013.7
167.5°	923.7	941.4	960.0	976.6	982.9	991.4	1005.8	1011.3	1015.0	1010.2	1015.0
170°	932.9	948.3	964.6	978.1	982.9	990.6	1005.0	1009.8	1012.7	1007.9	1012.7
172.5°	940.6	952.2	965.4	977.3	979.8	986.0	999.6	1004.4	1006.5	1002.5	1006.5
175°	948.3	955.0	964.6	972.3	971.4	975.2	986.7	990.6	994.4	988.7	994.4
177.5°	952.0	955.0	958.1	962.7	959.7	959.7	968.1	970.4	971.2	968.1	971.2
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1427606

CATALOG NUMBER: SQ2W-BBN-K-075U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	5341.1	5341.1	5341.1	5341.1	5341.1	5341.1	5341.1	5341.1	5341.1	5341.1	5341.1
2.5°	5312.7	5300.0	5281.2	5282.1	5302.6	5320.2	5329.1	5338.0	5329.1	5320.2	5302.6
5°	5142.3	5121.0	5093.2	5087.2	5103.0	5118.0	5130.4	5142.8	5130.4	5118.0	5103.0
7.5°	4755.6	4733.4	4702.6	4694.7	4709.8	4720.0	4716.0	4712.0	4716.0	4720.0	4709.8
10°	4386.3	4381.5	4371.2	4366.9	4368.6	4369.2	4366.2	4363.2	4366.2	4369.2	4368.6
12.5°	3971.5	3958.7	3943.3	3946.7	3969.0	3982.7	3970.8	3958.9	3970.8	3982.7	3969.0
15°	3314.9	3299.6	3279.0	3290.2	3332.9	3360.2	3341.0	3321.7	3341.0	3360.2	3332.9
17.5°	2679.0	2676.4	2672.6	2681.6	2703.4	2720.2	2722.2	2724.2	2722.2	2720.2	2703.4
20°	2277.9	2279.6	2282.6	2293.3	2311.7	2326.2	2329.2	2332.2	2329.2	2326.2	2311.7
22.5°	1954.7	1959.5	1967.0	1973.9	1980.3	1986.4	1991.4	1996.5	1991.4	1986.4	1980.3
25°	1552.2	1546.8	1536.5	1537.4	1549.4	1562.4	1578.7	1594.9	1578.7	1562.4	1549.4
27.5°	1259.6	1258.4	1257.2	1261.8	1272.0	1279.7	1279.9	1280.2	1279.9	1279.7	1272.0
30°	1104.7	1105.6	1105.2	1109.9	1119.7	1127.9	1130.9	1133.9	1130.9	1127.9	1119.7
32.5°	974.5	977.6	979.9	987.1	999.4	1008.0	1005.9	1003.7	1005.9	1008.0	999.4
35°	798.6	803.7	810.1	818.0	827.5	834.5	834.5	834.5	834.5	834.5	827.5
37.5°	639.6	647.3	656.3	664.2	670.9	676.1	676.9	677.6	676.9	676.1	670.9
40°	536.9	546.4	557.5	565.2	569.5	573.2	575.4	577.5	575.4	573.2	569.5
42.5°	440.0	450.1	461.3	469.0	473.2	475.0	469.3	463.6	469.3	475.0	473.2
45°	295.6	314.7	327.6	332.3	328.9	320.3	296.4	272.4	296.4	320.3	328.9
47.5°	139.0	172.2	206.0	212.6	191.9	169.7	143.4	117.0	143.4	169.7	191.9
50°	68.6	104.0	146.3	152.5	122.6	95.0	74.4	53.9	74.4	95.0	122.6
52.5°	40.2	69.6	106.1	108.9	77.9	52.1	41.8	31.6	41.8	52.1	77.9
55°	16.6	31.8	51.0	51.9	34.3	20.3	16.9	13.5	16.9	20.3	34.3
57.5°	7.1	12.6	19.5	19.9	13.8	8.8	6.9	5.0	6.9	8.8	13.8
60°	2.7	5.5	8.9	9.1	6.1	3.6	2.8	1.9	2.8	3.6	6.1
62.5°	1.2	2.6	4.3	4.4	2.8	1.4	0.9	0.4	0.9	1.4	2.8
65°	0.0	0.3	0.7	0.7	0.3	0.0	0.0	0.0	0.0	0.0	0.3
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	4.0	3.8	3.8	3.7	3.1	2.3	1.3	0.6	1.3	2.1	3.5
90°	20.2	19.2	19.2	18.3	15.4	11.5	6.7	2.9	6.7	10.6	17.3
92.5°	24.0	23.8	22.3	20.6	16.9	16.9	16.7	10.6	18.3	25.9	37.3
95°	22.1	22.1	25.9	32.7	48.0	49.0	32.7	29.8	42.3	59.6	74.9
97.5°	59.8	71.1	87.2	90.3	85.5	63.8	61.1	56.9	77.4	94.5	119.3
100°	110.5	124.9	136.4	113.4	89.4	88.4	82.6	80.7	102.8	119.1	143.2
102.5°	172.8	177.2	137.2	124.1	118.6	114.5	105.7	104.5	126.6	149.1	169.3
105°	187.4	168.1	169.1	169.1	165.3	157.6	141.2	140.3	165.3	191.2	216.2
107.5°	220.4	223.3	228.3	227.1	222.7	202.2	182.9	178.5	201.0	232.1	259.6
110°	264.2	267.1	269.0	267.1	260.4	234.4	211.4	204.7	224.8	257.5	287.3



TEST NUMBER: P1427606

CATALOG NUMBER: SQ2W-BBN-K-075U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	306.5	308.6	312.8	307.1	295.7	266.0	239.8	230.0	250.2	283.6	314.2
115°	373.8	373.8	374.7	371.8	348.8	318.0	283.4	269.0	286.3	317.1	350.7
117.5°	439.9	441.0	437.2	429.5	402.8	367.0	328.2	305.2	318.8	351.3	385.9
120°	481.4	483.3	479.4	467.9	442.0	401.6	357.4	330.5	341.1	372.8	407.4
122.5°	524.4	524.0	519.4	506.3	475.8	433.9	390.5	357.4	361.8	391.2	425.1
125°	584.2	583.2	579.4	564.0	532.3	489.1	438.1	397.8	392.0	417.0	451.6
127.5°	641.0	638.9	633.0	614.3	581.9	540.2	484.2	438.5	425.6	441.4	473.1
130°	680.3	677.4	666.8	646.6	614.9	575.5	518.8	467.0	448.7	458.3	486.2
132.5°	717.9	709.7	700.6	678.9	649.5	608.6	551.1	496.9	471.8	476.0	497.7
135°	765.8	758.1	746.5	725.4	697.5	657.2	599.5	540.9	506.3	502.5	515.0
137.5°	807.8	799.8	786.7	768.5	740.4	704.5	649.1	587.2	543.6	530.7	535.6
140°	834.0	824.4	812.8	794.6	769.6	732.1	678.3	618.8	569.8	551.5	548.6
142.5°	855.5	848.2	835.9	819.2	797.3	759.8	707.5	648.7	596.7	573.0	566.3
145°	887.8	882.0	868.6	853.2	834.9	797.5	749.4	690.8	638.9	608.2	593.8
147.5°	915.1	910.5	899.9	881.8	866.5	830.5	786.7	734.8	681.6	643.5	624.9
150°	932.0	928.1	917.6	900.3	884.9	851.3	809.0	761.0	710.0	669.7	645.7
152.5°	948.1	944.3	932.2	914.9	901.8	870.5	832.1	786.3	734.6	694.3	669.5
155°	969.5	964.6	953.1	936.8	925.3	896.4	860.9	820.5	776.3	734.1	706.2
157.5°	986.4	980.4	969.6	955.6	943.3	916.8	885.9	851.1	812.5	772.1	743.7
160°	996.4	989.6	978.1	965.6	954.1	929.1	901.2	869.5	834.0	797.5	766.7
162.5°	1003.3	997.3	983.5	972.5	962.5	939.9	913.5	884.9	853.2	821.3	792.9
165°	1010.8	1004.0	989.6	981.0	972.3	953.1	930.1	907.0	880.1	854.2	831.1
167.5°	1011.3	1005.8	991.4	982.9	976.6	960.0	941.4	923.7	902.8	882.4	863.2
170°	1009.8	1005.0	990.6	982.9	978.1	964.6	948.3	932.9	916.6	899.3	883.9
172.5°	1004.4	999.6	986.0	979.8	977.3	965.4	952.2	940.6	926.6	913.9	901.6
175°	990.6	986.7	975.2	971.4	972.3	964.6	955.0	948.3	939.7	932.0	925.3
177.5°	970.4	968.1	959.7	959.7	962.7	958.1	955.0	952.0	948.1	945.8	943.5
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1427606

CATALOG NUMBER: SQ2W-BBN-K-075U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	5341.1	5341.1	5341.1	5341.1	5341.1	5341.1	5341.1	5341.1	5341.1	5341.1	5341.1
2.5°	5282.1	5281.2	5300.0	5312.7	5306.9	5301.1	5306.9	5312.7	5300.0	5281.2	5282.1
5°	5087.2	5093.2	5121.0	5142.3	5144.0	5145.7	5144.0	5142.3	5121.0	5093.2	5087.2
7.5°	4694.7	4702.6	4733.4	4755.6	4752.3	4749.0	4752.3	4755.6	4733.4	4702.6	4694.7
10°	4366.9	4371.2	4381.5	4386.3	4374.7	4363.2	4374.7	4386.3	4381.5	4371.2	4366.9
12.5°	3946.7	3943.3	3958.7	3971.5	3976.4	3981.2	3976.4	3971.5	3958.7	3943.3	3946.7
15°	3290.2	3279.0	3299.6	3314.9	3314.4	3314.0	3314.4	3314.9	3299.6	3279.0	3290.2
17.5°	2681.6	2672.6	2676.4	2679.0	2677.7	2676.4	2677.7	2679.0	2676.4	2672.6	2681.6
20°	2293.3	2282.6	2279.6	2277.9	2280.0	2282.2	2280.0	2277.9	2279.6	2282.6	2293.3
22.5°	1973.9	1967.0	1959.5	1954.7	1957.5	1960.3	1957.5	1954.7	1959.5	1967.0	1973.9
25°	1537.4	1536.5	1546.8	1552.2	1543.3	1534.3	1543.3	1552.2	1546.8	1536.5	1537.4
27.5°	1261.8	1257.2	1258.4	1259.6	1261.3	1263.0	1261.3	1259.6	1258.4	1257.2	1261.8
30°	1109.9	1105.2	1105.6	1104.7	1099.5	1094.4	1099.5	1104.7	1105.6	1105.2	1109.9
32.5°	987.1	979.9	977.6	974.5	969.4	964.3	969.4	974.5	977.6	979.9	987.1
35°	818.0	810.1	803.7	798.6	797.3	796.0	797.3	798.6	803.7	810.1	818.0
37.5°	664.2	656.3	647.3	639.6	636.3	633.0	636.3	639.6	647.3	656.3	664.2
40°	565.2	557.5	546.4	536.9	532.2	527.5	532.2	536.9	546.4	557.5	565.2
42.5°	469.0	461.3	450.1	440.0	432.9	425.8	432.9	440.0	450.1	461.3	469.0
45°	332.3	327.6	314.7	295.6	257.5	219.5	257.5	295.6	314.7	327.6	332.3
47.5°	212.6	206.0	172.2	139.0	107.3	75.7	107.3	139.0	172.2	206.0	212.6
50°	152.5	146.3	104.0	68.6	54.0	39.5	54.0	68.6	104.0	146.3	152.5
52.5°	108.9	106.1	69.6	40.2	32.5	24.8	32.5	40.2	69.6	106.1	108.9
55°	51.9	51.0	31.8	16.6	13.6	10.6	13.6	16.6	31.8	51.0	51.9
57.5°	19.9	19.5	12.6	7.1	5.6	4.0	5.6	7.1	12.6	19.5	19.9
60°	9.1	8.9	5.5	2.7	1.8	1.0	1.8	2.7	5.5	8.9	9.1
62.5°	4.4	4.3	2.6	1.2	0.7	0.2	0.7	1.2	2.6	4.3	4.4
65°	0.7	0.7	0.3	0.0	0.0	0.0	0.0	0.3	0.7	0.7	0.7
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	4.4	5.8	7.1	7.9	8.6	8.3	8.6	7.9	7.1	5.8	4.4
90°	22.1	28.8	35.5	39.4	43.2	41.3	43.2	39.4	35.5	28.8	22.1
92.5°	44.4	55.7	64.0	70.9	74.0	73.6	74.0	70.9	64.0	55.7	44.4
95°	89.4	102.8	116.3	125.9	131.6	129.7	131.6	125.9	116.3	102.8	89.4
97.5°	137.8	155.8	170.8	179.9	185.6	189.5	185.6	179.9	170.8	155.8	137.8
100°	170.1	187.4	204.7	215.2	224.8	228.7	224.8	215.2	204.7	187.4	170.1
102.5°	196.2	218.9	237.7	249.0	257.1	261.0	257.1	249.0	237.7	218.9	196.2
105°	239.2	263.3	283.4	297.8	306.5	309.4	306.5	297.8	283.4	263.3	239.2
107.5°	282.3	307.1	325.7	341.7	352.2	358.4	352.2	341.7	325.7	307.1	282.3
110°	316.1	336.3	356.5	370.9	381.4	385.3	381.4	370.9	356.5	336.3	316.1



TEST NUMBER: P1427606

CATALOG NUMBER: SQ2W-BBN-K-075U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	344.5	367.0	387.2	401.6	413.7	419.1	413.7	401.6	387.2	367.0	344.5
115°	384.3	414.1	432.4	445.8	454.5	459.3	454.5	445.8	432.4	414.1	384.3
117.5°	417.4	448.5	468.5	478.9	482.9	486.4	482.9	478.9	468.5	448.5	417.4
120°	438.1	467.0	490.0	503.5	508.3	510.2	508.3	503.5	490.0	467.0	438.1
122.5°	457.3	484.6	506.9	523.4	531.3	533.2	531.3	523.4	506.9	484.6	457.3
125°	484.2	510.2	533.2	549.6	558.2	563.0	558.2	549.6	533.2	510.2	484.2
127.5°	507.7	535.7	556.9	571.7	580.1	584.0	580.1	571.7	556.9	535.7	507.7
130°	520.8	549.6	570.7	587.1	594.7	598.6	594.7	587.1	570.7	549.6	520.8
132.5°	530.7	561.1	583.0	597.8	606.3	610.1	606.3	597.8	583.0	561.1	530.7
135°	542.9	574.6	597.6	612.0	619.7	623.6	619.7	612.0	597.6	574.6	542.9
137.5°	553.4	582.2	606.3	621.4	628.4	630.9	628.4	621.4	606.3	582.2	553.4
140°	561.1	586.1	610.1	624.5	632.2	633.2	632.2	624.5	610.1	586.1	561.1
142.5°	571.1	590.7	611.6	626.1	633.7	635.5	633.7	626.1	611.6	590.7	571.1
145°	589.0	600.5	614.9	628.4	635.1	637.0	635.1	628.4	614.9	600.5	589.0
147.5°	611.5	615.1	622.6	631.4	638.0	639.3	638.0	631.4	622.6	615.1	611.5
150°	628.4	627.4	630.3	636.1	641.8	640.9	641.8	636.1	630.3	627.4	628.4
152.5°	647.6	642.0	641.8	644.5	647.2	647.0	647.2	644.5	641.8	642.0	647.6
155°	680.3	669.7	663.9	662.0	662.0	661.0	662.0	662.0	663.9	669.7	680.3
157.5°	716.2	701.4	692.7	688.1	686.8	684.7	686.8	688.1	692.7	701.4	716.2
160°	740.8	724.4	715.8	708.1	705.2	702.3	705.2	708.1	715.8	724.4	740.8
162.5°	763.8	748.3	738.9	731.9	729.1	724.6	729.1	731.9	738.9	748.3	763.8
165°	801.3	785.0	774.4	768.6	764.8	761.0	764.8	768.6	774.4	785.0	801.3
167.5°	838.8	820.9	814.0	807.5	803.8	796.9	803.8	807.5	814.0	820.9	838.8
170°	861.8	845.5	841.7	835.9	829.2	821.5	829.2	835.9	841.7	845.5	861.8
172.5°	881.8	870.9	867.0	861.3	859.2	853.0	859.2	861.3	867.0	870.9	881.8
175°	910.8	902.2	902.2	901.2	898.4	892.6	898.4	901.2	902.2	902.2	910.8
177.5°	935.1	930.4	933.5	933.5	932.8	927.4	932.8	933.5	933.5	930.4	935.1
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1427606

CATALOG NUMBER: SQ2W-BBN-K-075U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	5341.1	5341.1	5341.1	5341.1
2.5°	5302.6	5320.2	5329.1	5338.0
5°	5103.0	5118.0	5130.4	5142.8
7.5°	4709.8	4720.0	4716.0	4712.0
10°	4368.6	4369.2	4366.2	4363.2
12.5°	3969.0	3982.7	3970.8	3958.9
15°	3332.9	3360.2	3341.0	3321.7
17.5°	2703.4	2720.2	2722.2	2724.2
20°	2311.7	2326.2	2329.2	2332.2
22.5°	1980.3	1986.4	1991.4	1996.5
25°	1549.4	1562.4	1578.7	1594.9
27.5°	1272.0	1279.7	1279.9	1280.2
30°	1119.7	1127.9	1130.9	1133.9
32.5°	999.4	1008.0	1005.9	1003.7
35°	827.5	834.5	834.5	834.5
37.5°	670.9	676.1	676.9	677.6
40°	569.5	573.2	575.4	577.5
42.5°	473.2	475.0	469.3	463.6
45°	328.9	320.3	296.4	272.4
47.5°	191.9	169.7	143.4	117.0
50°	122.6	95.0	74.4	53.9
52.5°	77.9	52.1	41.8	31.6
55°	34.3	20.3	16.9	13.5
57.5°	13.8	8.8	6.9	5.0
60°	6.1	3.6	2.8	1.9
62.5°	2.8	1.4	0.9	0.4
65°	0.3	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	3.5	2.1	1.3	0.6
90°	17.3	10.6	6.7	2.9
92.5°	37.3	25.9	18.3	10.6
95°	74.9	59.6	42.3	29.8
97.5°	119.3	94.5	77.4	56.9
100°	143.2	119.1	102.8	80.7
102.5°	169.3	149.1	126.6	104.5
105°	216.2	191.2	165.3	140.3
107.5°	259.6	232.1	201.0	178.5
110°	287.3	257.5	224.8	204.7



TEST NUMBER: P1427606

CATALOG NUMBER: SQ2W-BBN-K-075U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	314.2	283.6	250.2	230.0
115°	350.7	317.1	286.3	269.0
117.5°	385.9	351.3	318.8	305.2
120°	407.4	372.8	341.1	330.5
122.5°	425.1	391.2	361.8	357.4
125°	451.6	417.0	392.0	397.8
127.5°	473.1	441.4	425.6	438.5
130°	486.2	458.3	448.7	467.0
132.5°	497.7	476.0	471.8	496.9
135°	515.0	502.5	506.3	540.9
137.5°	535.6	530.7	543.6	587.2
140°	548.6	551.5	569.8	618.8
142.5°	566.3	573.0	596.7	648.7
145°	593.8	608.2	638.9	690.8
147.5°	624.9	643.5	681.6	734.8
150°	645.7	669.7	710.0	761.0
152.5°	669.5	694.3	734.6	786.3
155°	706.2	734.1	776.3	820.5
157.5°	743.7	772.1	812.5	851.1
160°	766.7	797.5	834.0	869.5
162.5°	792.9	821.3	853.2	884.9
165°	831.1	854.2	880.1	907.0
167.5°	863.2	882.4	902.8	923.7
170°	883.9	899.3	916.6	932.9
172.5°	901.6	913.9	926.6	940.6
175°	925.3	932.0	939.7	948.3
177.5°	943.5	945.8	948.1	952.0
180°	951.2	951.2	951.2	951.2



TEST NUMBER: P1427606
 CATALOG NUMBER: SQ2W-BBN-K-075U-075D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00