

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427813

Luminaire Tested: SQ2W-F-K-150U-125D-L830-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427813
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-20)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-F-K-150U-125D-L830-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12209.6 lumens
Efficiency: N/A
Efficacy: 117.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 104.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427813

CATALOG NUMBER: SQ2W-F-K-150U-125D-L830-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427813

CATALOG NUMBER: SQ2W-F-K-150U-125D-L830-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53	46				46
1	97	92	88	85	89	85	82	79	71	69	66	58	56	55	46	45	44				39	
2	88	80	74	69	80	74	69	64	62	58	55	51	48	46	40	39	37				32	
3	80	71	63	57	73	65	59	53	54	50	46	45	41	38	36	33	31				27	
4	73	62	54	48	67	57	51	45	48	43	39	40	36	33	32	29	27				23	
5	67	55	47	41	61	51	44	39	43	38	33	36	31	28	29	26	23				20	
6	62	50	42	36	56	46	39	33	39	33	29	32	28	25	26	23	20				17	
7	57	45	37	31	52	41	34	29	35	30	25	29	25	22	24	20	18				15	
8	53	41	33	27	48	38	31	26	32	26	23	27	22	19	22	18	16				14	
9	49	37	29	24	45	34	28	23	29	24	20	24	20	17	20	17	14				12	
10	46	34	27	22	42	31	25	21	27	22	18	23	18	16	18	15	13				11	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	32277	32277	32277	32277
5°	32081	32445	32081	32445
10°	31966	32337	31966	32337
15°	31792	32192	31792	32192
20°	31590	31905	31590	31905
25°	31249	31525	31249	31525
30°	30918	31129	30918	31129
35°	30523	30718	30523	30718
40°	30177	30266	30177	30266
45°	29733	29733	29733	29733
50°	29137	29210	29137	29210
55°	28453	28492	28453	28492
60°	27686	27686	27686	27686
65°	26785	26678	26785	26678
70°	25520	25255	25520	25255
75°	23799	23275	23799	23275
80°	21208	20158	21208	20158
85°	16950	14338	16950	14338

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 29934 cd/sqm



TEST NUMBER: P1427813

CATALOG NUMBER: SQ2W-F-K-150U-125D-L830-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.2	1.5
10°-20°	540.5	4.4
20°-30°	813.5	6.7
30°-40°	972.9	8.0
40°-50°	1004.6	8.2
50°-60°	906.1	7.4
60°-70°	694.1	5.7
70°-80°	401.2	3.3
80°-90°	113.5	0.9
90°-100°	179.2	1.5
100°-110°	522.6	4.3
110°-120°	852.8	7.0
120°-130°	1082.1	8.9
130°-140°	1157.9	9.5
140°-150°	1081.2	8.9
150°-160°	889.7	7.3
160°-170°	596.7	4.9
170°-180°	211.9	1.7
0°-30°	1543.2	12.6
0°-40°	2516.1	20.6
0°-60°	4426.8	36.3
0°-90°	5635.6	46.2
90°-120°	1554.5	12.7
90°-150°	4875.8	39.9
90°-180°	6574.0	53.8
0°-180°	12209.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1999	1999	1999	1999	1999	
5°	1979	2002	1979	2002	1979	188
15°	1902	1926	1902	1926	1902	536
25°	1754	1770	1754	1770	1754	808
35°	1549	1558	1549	1558	1549	969
45°	1302	1302	1302	1302	1302	1003
55°	1011	1012	1011	1012	1011	903
65°	701	698	701	698	701	693
75°	382	373	382	373	382	404
85°	92	77	92	77	92	107
90°	7	50	7	98	7	9
95°	70	52	70	307	70	85
105°	332	532	332	732	332	353
115°	637	882	637	1087	637	628
125°	942	1399	942	1333	942	842
135°	1280	1831	1280	1476	1280	989
145°	1635	2110	1635	1508	1635	1023
155°	1942	2292	1942	1565	1942	893
165°	2147	2390	2147	1801	2147	604
175°	2245	2340	2245	2113	2245	213
180°	2252	2252	2252	2252	2252	



TEST NUMBER: P1427813

CATALOG NUMBER: SQ2W-F-K-150U-125D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1999.1	1999.1	1999.1	1999.1	1999.1	1999.1	1999.1	1999.1	1999.1	1999.1	1999.1
2.5°	1989.0	1998.5	2008.0	2004.0	1995.5	1992.2	1994.2	1996.0	1997.0	1998.0	1997.0
5°	1979.4	1991.9	2004.4	2000.0	1990.0	1985.7	1986.9	1989.4	1995.7	2001.9	1995.7
7.5°	1963.4	1975.9	1988.4	1984.4	1974.9	1970.9	1972.4	1975.1	1981.6	1988.1	1981.6
10°	1949.8	1962.4	1974.9	1970.5	1960.5	1956.7	1959.2	1962.4	1967.4	1972.4	1967.4
12.5°	1932.9	1945.5	1958.0	1954.3	1945.3	1941.6	1943.1	1945.6	1951.1	1956.6	1951.1
15°	1902.0	1914.5	1927.0	1923.6	1914.8	1911.4	1913.2	1915.9	1920.9	1925.9	1920.9
17.5°	1864.5	1876.3	1888.0	1884.9	1876.8	1873.8	1875.9	1878.6	1883.0	1887.3	1883.0
20°	1838.6	1849.9	1861.1	1857.9	1849.7	1846.0	1846.6	1848.2	1852.5	1856.9	1852.5
22.5°	1807.1	1818.3	1829.6	1826.7	1819.1	1814.6	1813.2	1813.5	1818.9	1824.3	1818.9
25°	1754.1	1765.4	1776.7	1774.3	1767.4	1763.1	1761.2	1760.9	1765.3	1769.6	1765.3
27.5°	1699.0	1708.3	1717.7	1715.8	1710.0	1706.5	1705.3	1705.1	1708.2	1711.4	1708.2
30°	1658.4	1667.8	1677.2	1674.8	1668.6	1664.8	1663.6	1663.4	1666.6	1669.7	1666.6
32.5°	1615.6	1624.5	1633.4	1630.2	1622.9	1619.2	1618.9	1619.6	1623.3	1626.9	1623.3
35°	1548.6	1556.1	1563.6	1560.3	1553.5	1550.3	1551.0	1552.2	1555.3	1558.5	1555.3
37.5°	1481.3	1487.1	1492.8	1489.5	1483.1	1479.8	1479.7	1480.3	1482.9	1485.5	1482.9
40°	1431.8	1438.0	1444.3	1440.7	1433.8	1430.0	1429.4	1429.7	1432.9	1436.0	1432.9
42.5°	1381.1	1385.8	1390.6	1387.4	1381.5	1378.7	1379.1	1379.8	1381.4	1383.0	1381.4
45°	1302.2	1306.6	1311.0	1307.9	1302.2	1299.4	1299.4	1299.7	1301.0	1302.2	1301.0
47.5°	1219.7	1223.1	1226.5	1224.1	1219.7	1217.1	1216.4	1216.3	1218.3	1220.3	1218.3
50°	1160.0	1164.4	1168.8	1166.6	1162.2	1159.4	1158.2	1157.9	1160.4	1162.9	1160.4
52.5°	1101.5	1106.4	1111.2	1109.2	1104.8	1101.7	1100.0	1099.2	1101.2	1103.2	1101.2
55°	1010.8	1016.4	1022.1	1020.7	1016.9	1013.8	1011.3	1009.7	1011.0	1012.2	1011.0
57.5°	918.2	923.7	929.2	928.1	924.9	921.7	918.7	916.9	918.7	920.4	918.7
60°	857.4	862.4	867.4	865.8	862.1	858.9	856.4	854.9	856.1	857.4	856.1
62.5°	795.4	800.4	805.4	803.5	799.2	795.9	793.4	791.8	793.0	794.3	793.0
65°	701.1	705.5	709.9	708.1	704.4	701.3	698.8	697.0	697.7	698.3	697.7
67.5°	605.9	609.7	613.4	611.7	608.0	604.4	600.8	598.3	599.3	600.3	599.3
70°	540.6	544.4	548.1	546.7	543.6	540.4	537.3	535.0	535.0	535.0	535.0
72.5°	477.5	480.8	484.0	482.1	478.5	475.4	472.7	470.8	470.8	470.8	470.8
75°	381.5	383.4	385.3	384.3	382.5	380.0	376.8	374.3	373.7	373.1	373.7
77.5°	288.9	288.9	288.9	287.1	284.7	282.3	280.0	278.0	277.2	276.5	277.2
80°	228.1	228.1	228.1	226.7	224.8	222.9	221.0	219.3	218.1	216.8	218.1
82.5°	171.8	170.8	169.8	168.1	166.2	163.8	161.0	159.1	160.4	161.6	160.4
85°	91.5	90.3	89.0	87.3	85.4	83.2	80.7	78.7	78.1	77.4	78.1
87.5°	29.5	30.3	31.6	32.1	31.9	30.6	28.6	27.4	27.4	26.9	27.4
90°	6.8	15.9	27.3	36.4	43.2	45.5	45.5	47.8	50.0	50.0	50.0
92.5°	25.0	39.6	40.0	40.0	48.7	52.8	56.4	56.9	59.1	59.1	59.1
95°	70.5	77.3	116.0	113.7	77.3	61.4	52.3	52.3	52.3	52.3	52.3
97.5°	134.6	144.6	151.0	202.4	213.8	206.5	168.3	141.5	126.4	119.6	126.4
100°	191.0	195.6	209.2	211.5	268.4	322.9	295.7	261.5	250.2	243.3	250.2
102.5°	247.4	250.2	271.1	280.6	293.8	324.8	419.4	408.9	401.2	399.8	401.2
105°	332.0	334.3	373.0	391.2	400.3	400.3	398.0	443.5	516.3	532.2	516.3
107.5°	422.6	433.0	478.5	527.2	537.6	540.4	528.5	521.7	519.0	520.8	519.0
110°	484.4	500.3	554.9	616.3	632.2	636.8	632.2	625.4	620.9	620.9	620.9



TEST NUMBER: P1427813

CATALOG NUMBER: SQ2W-F-K-150U-125D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	544.5	567.7	629.5	700.0	726.9	740.5	730.5	725.5	720.9	724.6	720.9
115°	636.8	670.9	752.8	825.6	880.1	887.0	884.7	884.7	882.4	882.4	882.4
117.5°	722.3	776.9	868.8	953.4	1016.6	1034.8	1043.9	1041.2	1038.4	1043.0	1038.4
120°	782.3	846.0	950.6	1046.2	1107.6	1134.9	1144.0	1139.4	1144.0	1139.4	1144.0
122.5°	846.0	924.3	1027.1	1126.2	1198.5	1229.5	1240.4	1241.3	1242.2	1239.5	1242.2
125°	941.5	1037.1	1157.6	1259.9	1335.0	1371.4	1380.5	1382.8	1387.3	1398.7	1387.3
127.5°	1038.0	1146.2	1278.6	1377.3	1454.2	1498.3	1512.4	1517.4	1526.9	1531.9	1526.9
130°	1105.3	1228.1	1362.3	1455.5	1530.6	1578.3	1603.4	1610.2	1621.6	1619.3	1621.6
132.5°	1176.3	1304.5	1440.5	1537.4	1607.0	1658.4	1679.8	1699.3	1703.4	1706.6	1703.4
135°	1280.4	1419.1	1555.6	1651.1	1717.1	1767.1	1794.4	1812.6	1824.0	1830.8	1824.0
137.5°	1390.0	1536.5	1667.5	1752.6	1819.0	1862.2	1893.1	1912.2	1924.0	1929.5	1924.0
140°	1464.6	1605.6	1733.0	1821.7	1880.8	1924.0	1951.3	1974.1	1987.7	1987.7	1987.7
142.5°	1535.6	1674.8	1798.5	1887.2	1939.0	1978.6	2007.7	2025.0	2040.5	2040.5	2040.5
145°	1635.2	1773.9	1887.6	1976.3	2019.6	2055.9	2087.8	2101.4	2110.5	2110.5	2110.5
147.5°	1739.4	1862.2	1965.9	2050.9	2087.3	2130.1	2155.1	2166.0	2177.4	2172.4	2177.4
150°	1801.2	1914.9	2015.0	2094.6	2131.0	2171.9	2196.9	2206.0	2217.4	2210.6	2217.4
152.5°	1861.3	1969.5	2060.5	2134.6	2165.6	2206.5	2235.2	2244.2	2252.0	2247.0	2252.0
155°	1942.2	2037.7	2121.9	2190.1	2217.4	2256.1	2283.4	2294.7	2303.8	2292.5	2303.8
157.5°	2014.5	2096.9	2170.1	2232.9	2262.0	2295.2	2320.7	2334.8	2343.9	2338.9	2343.9
160°	2058.2	2133.3	2199.2	2258.3	2285.6	2315.2	2342.5	2358.4	2367.5	2360.7	2367.5
162.5°	2094.6	2162.4	2224.7	2278.4	2302.0	2327.9	2360.7	2374.8	2383.9	2375.2	2383.9
165°	2146.9	2201.5	2256.1	2301.6	2322.0	2342.5	2376.6	2392.5	2399.4	2390.3	2399.4
167.5°	2186.5	2228.3	2272.5	2311.6	2326.6	2346.6	2380.7	2393.9	2402.5	2391.2	2402.5
170°	2208.3	2244.7	2283.4	2315.2	2326.6	2344.8	2378.9	2390.3	2397.1	2385.7	2397.1
172.5°	2226.5	2253.8	2285.2	2313.4	2319.3	2333.9	2366.2	2377.5	2382.5	2373.0	2382.5
175°	2244.7	2260.6	2283.4	2301.6	2299.3	2308.4	2335.7	2344.8	2353.9	2340.2	2353.9
177.5°	2253.3	2260.6	2267.9	2278.8	2271.5	2271.5	2291.6	2297.0	2298.8	2291.6	2298.8
180°	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5



TEST NUMBER: P1427813

CATALOG NUMBER: SQ2W-F-K-150U-125D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1999.1	1999.1	1999.1	1999.1	1999.1	1999.1	1999.1	1999.1	1999.1	1999.1	1999.1
2.5°	1996.0	1994.2	1992.2	1995.5	2004.0	2008.0	1998.5	1989.0	1998.5	2008.0	2004.0
5°	1989.4	1986.9	1985.7	1990.0	2000.0	2004.4	1991.9	1979.4	1991.9	2004.4	2000.0
7.5°	1975.1	1972.4	1970.9	1974.9	1984.4	1988.4	1975.9	1963.4	1975.9	1988.4	1984.4
10°	1962.4	1959.2	1956.7	1960.5	1970.5	1974.9	1962.4	1949.8	1962.4	1974.9	1970.5
12.5°	1945.6	1943.1	1941.6	1945.3	1954.3	1958.0	1945.5	1932.9	1945.5	1958.0	1954.3
15°	1915.9	1913.2	1911.4	1914.8	1923.6	1927.0	1914.5	1902.0	1914.5	1927.0	1923.6
17.5°	1878.6	1875.9	1873.8	1876.8	1884.9	1888.0	1876.3	1864.5	1876.3	1888.0	1884.9
20°	1848.2	1846.6	1846.0	1849.7	1857.9	1861.1	1849.9	1838.6	1849.9	1861.1	1857.9
22.5°	1813.5	1813.2	1814.6	1819.1	1826.7	1829.6	1818.3	1807.1	1818.3	1829.6	1826.7
25°	1760.9	1761.2	1763.1	1767.4	1774.3	1776.7	1765.4	1754.1	1765.4	1776.7	1774.3
27.5°	1705.1	1705.3	1706.5	1710.0	1715.8	1717.7	1708.3	1699.0	1708.3	1717.7	1715.8
30°	1663.4	1663.6	1664.8	1668.6	1674.8	1677.2	1667.8	1658.4	1667.8	1677.2	1674.8
32.5°	1619.6	1618.9	1619.2	1622.9	1630.2	1633.4	1624.5	1615.6	1624.5	1633.4	1630.2
35°	1552.2	1551.0	1550.3	1553.5	1560.3	1563.6	1556.1	1548.6	1556.1	1563.6	1560.3
37.5°	1480.3	1479.7	1479.8	1483.1	1489.5	1492.8	1487.1	1481.3	1487.1	1492.8	1489.5
40°	1429.7	1429.4	1430.0	1433.8	1440.7	1444.3	1438.0	1431.8	1438.0	1444.3	1440.7
42.5°	1379.8	1379.1	1378.7	1381.5	1387.4	1390.6	1385.8	1381.1	1385.8	1390.6	1387.4
45°	1299.7	1299.4	1299.4	1302.2	1307.9	1311.0	1306.6	1302.2	1306.6	1311.0	1307.9
47.5°	1216.3	1216.4	1217.1	1219.7	1224.1	1226.5	1223.1	1219.7	1223.1	1226.5	1224.1
50°	1157.9	1158.2	1159.4	1162.2	1166.6	1168.8	1164.4	1160.0	1164.4	1168.8	1166.6
52.5°	1099.2	1100.0	1101.7	1104.8	1109.2	1111.2	1106.4	1101.5	1106.4	1111.2	1109.2
55°	1009.7	1011.3	1013.8	1016.9	1020.7	1022.1	1016.4	1010.8	1016.4	1022.1	1020.7
57.5°	916.9	918.7	921.7	924.9	928.1	929.2	923.7	918.2	923.7	929.2	928.1
60°	854.9	856.4	858.9	862.1	865.8	867.4	862.4	857.4	862.4	867.4	865.8
62.5°	791.8	793.4	795.9	799.2	803.5	805.4	800.4	795.4	800.4	805.4	803.5
65°	697.0	698.8	701.3	704.4	708.1	709.9	705.5	701.1	705.5	709.9	708.1
67.5°	598.3	600.8	604.4	608.0	611.7	613.4	609.7	605.9	609.7	613.4	611.7
70°	535.0	537.3	540.4	543.6	546.7	548.1	544.4	540.6	544.4	548.1	546.7
72.5°	470.8	472.7	475.4	478.5	482.1	484.0	480.8	477.5	480.8	484.0	482.1
75°	374.3	376.8	380.0	382.5	384.3	385.3	383.4	381.5	383.4	385.3	384.3
77.5°	278.0	280.0	282.3	284.7	287.1	288.9	288.9	288.9	288.9	288.9	287.1
80°	219.3	221.0	222.9	224.8	226.7	228.1	228.1	228.1	228.1	228.1	226.7
82.5°	159.1	161.0	163.8	166.2	168.1	169.8	170.8	171.8	170.8	169.8	168.1
85°	78.7	80.7	83.2	85.4	87.3	89.0	90.3	91.5	90.3	89.0	87.3
87.5°	27.4	28.6	30.6	31.9	32.1	31.6	30.3	29.5	30.3	31.2	33.0
90°	47.8	45.5	45.5	43.2	36.4	27.3	15.9	6.8	15.9	25.0	40.9
92.5°	56.9	56.4	52.8	48.7	40.0	40.0	39.6	25.0	43.2	61.4	88.2
95°	52.3	52.3	61.4	77.3	113.7	116.0	77.3	70.5	100.1	141.0	177.4
97.5°	141.5	168.3	206.5	213.8	202.4	151.0	144.6	134.6	183.3	223.8	282.5
100°	261.5	295.7	322.9	268.4	211.5	209.2	195.6	191.0	243.3	282.0	338.9
102.5°	408.9	419.4	324.8	293.8	280.6	271.1	250.2	247.4	299.7	353.0	400.7
105°	443.5	398.0	400.3	400.3	391.2	373.0	334.3	332.0	391.2	452.6	511.7
107.5°	521.7	528.5	540.4	537.6	527.2	478.5	433.0	422.6	475.8	549.5	614.5
110°	625.4	632.2	636.8	632.2	616.3	554.9	500.3	484.4	532.2	609.5	680.0



TEST NUMBER: P1427813

CATALOG NUMBER: SQ2W-F-K-150U-125D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	725.5	730.5	740.5	726.9	700.0	629.5	567.7	544.5	592.2	671.4	743.7
115°	884.7	884.7	887.0	880.1	825.6	752.8	670.9	636.8	677.7	750.5	830.1
117.5°	1041.2	1043.9	1034.8	1016.6	953.4	868.8	776.9	722.3	754.6	831.5	913.3
120°	1139.4	1144.0	1134.9	1107.6	1046.2	950.6	846.0	782.3	807.4	882.4	964.3
122.5°	1241.3	1240.4	1229.5	1198.5	1126.2	1027.1	924.3	846.0	856.5	926.1	1006.1
125°	1382.8	1380.5	1371.4	1335.0	1259.9	1157.6	1037.1	941.5	927.9	987.0	1068.9
127.5°	1517.4	1512.4	1498.3	1454.2	1377.3	1278.6	1146.2	1038.0	1007.5	1044.8	1119.9
130°	1610.2	1603.4	1578.3	1530.6	1455.5	1362.3	1228.1	1105.3	1062.1	1084.8	1150.8
132.5°	1699.3	1679.8	1658.4	1607.0	1537.4	1440.5	1304.5	1176.3	1116.7	1126.7	1178.1
135°	1812.6	1794.4	1767.1	1717.1	1651.1	1555.6	1419.1	1280.4	1198.5	1189.4	1219.0
137.5°	1912.2	1893.1	1862.2	1819.0	1752.6	1667.5	1536.5	1390.0	1286.8	1256.3	1267.7
140°	1974.1	1951.3	1924.0	1880.8	1821.7	1733.0	1605.6	1464.6	1348.6	1305.4	1298.6
142.5°	2025.0	2007.7	1978.6	1939.0	1887.2	1798.5	1674.8	1535.6	1412.3	1356.4	1340.5
145°	2101.4	2087.8	2055.9	2019.6	1976.3	1887.6	1773.9	1635.2	1512.4	1439.6	1405.5
147.5°	2166.0	2155.1	2130.1	2087.3	2050.9	1965.9	1862.2	1739.4	1613.4	1523.3	1479.2
150°	2206.0	2196.9	2171.9	2131.0	2094.6	2015.0	1914.9	1801.2	1680.7	1585.2	1528.3
152.5°	2244.2	2235.2	2206.5	2165.6	2134.6	2060.5	1969.5	1861.3	1738.9	1643.4	1584.7
155°	2294.7	2283.4	2256.1	2217.4	2190.1	2121.9	2037.7	1942.2	1837.6	1737.5	1671.6
157.5°	2334.8	2320.7	2295.2	2262.0	2232.9	2170.1	2096.9	2014.5	1923.1	1827.6	1760.3
160°	2358.4	2342.5	2315.2	2285.6	2258.3	2199.2	2133.3	2058.2	1974.1	1887.6	1814.9
162.5°	2374.8	2360.7	2327.9	2302.0	2278.4	2224.7	2162.4	2094.6	2019.6	1944.0	1876.7
165°	2392.5	2376.6	2342.5	2322.0	2301.6	2256.1	2201.5	2146.9	2083.2	2021.8	1967.2
167.5°	2393.9	2380.7	2346.6	2326.6	2311.6	2272.5	2228.3	2186.5	2136.9	2088.7	2043.2
170°	2390.3	2378.9	2344.8	2326.6	2315.2	2283.4	2244.7	2208.3	2169.7	2128.7	2092.3
172.5°	2377.5	2366.2	2333.9	2319.3	2313.4	2285.2	2253.8	2226.5	2193.3	2163.3	2134.2
175°	2344.8	2335.7	2308.4	2299.3	2301.6	2283.4	2260.6	2244.7	2224.2	2206.0	2190.1
177.5°	2297.0	2291.6	2271.5	2271.5	2278.8	2267.9	2260.6	2253.3	2244.2	2238.8	2233.3
180°	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5



TEST NUMBER: P1427813

CATALOG NUMBER: SQ2W-F-K-150U-125D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1999.1	1999.1	1999.1	1999.1	1999.1	1999.1	1999.1	1999.1	1999.1	1999.1	1999.1
2.5°	1995.5	1992.2	1994.2	1996.0	1997.0	1998.0	1997.0	1996.0	1994.2	1992.2	1995.5
5°	1990.0	1985.7	1986.9	1989.4	1995.7	2001.9	1995.7	1989.4	1986.9	1985.7	1990.0
7.5°	1974.9	1970.9	1972.4	1975.1	1981.6	1988.1	1981.6	1975.1	1972.4	1970.9	1974.9
10°	1960.5	1956.7	1959.2	1962.4	1967.4	1972.4	1967.4	1962.4	1959.2	1956.7	1960.5
12.5°	1945.3	1941.6	1943.1	1945.6	1951.1	1956.6	1951.1	1945.6	1943.1	1941.6	1945.3
15°	1914.8	1911.4	1913.2	1915.9	1920.9	1925.9	1920.9	1915.9	1913.2	1911.4	1914.8
17.5°	1876.8	1873.8	1875.9	1878.6	1883.0	1887.3	1883.0	1878.6	1875.9	1873.8	1876.8
20°	1849.7	1846.0	1846.6	1848.2	1852.5	1856.9	1852.5	1848.2	1846.6	1846.0	1849.7
22.5°	1819.1	1814.6	1813.2	1813.5	1818.9	1824.3	1818.9	1813.5	1813.2	1814.6	1819.1
25°	1767.4	1763.1	1761.2	1760.9	1765.3	1769.6	1765.3	1760.9	1761.2	1763.1	1767.4
27.5°	1710.0	1706.5	1705.3	1705.1	1708.2	1711.4	1708.2	1705.1	1705.3	1706.5	1710.0
30°	1668.6	1664.8	1663.6	1663.4	1666.6	1669.7	1666.6	1663.4	1663.6	1664.8	1668.6
32.5°	1622.9	1619.2	1618.9	1619.6	1623.3	1626.9	1623.3	1619.6	1618.9	1619.2	1622.9
35°	1553.5	1550.3	1551.0	1552.2	1555.3	1558.5	1555.3	1552.2	1551.0	1550.3	1553.5
37.5°	1483.1	1479.8	1479.7	1480.3	1482.9	1485.5	1482.9	1480.3	1479.7	1479.8	1483.1
40°	1433.8	1430.0	1429.4	1429.7	1432.9	1436.0	1432.9	1429.7	1429.4	1430.0	1433.8
42.5°	1381.5	1378.7	1379.1	1379.8	1381.4	1383.0	1381.4	1379.8	1379.1	1378.7	1381.5
45°	1302.2	1299.4	1299.4	1299.7	1301.0	1302.2	1301.0	1299.7	1299.4	1299.4	1302.2
47.5°	1219.7	1217.1	1216.4	1216.3	1218.3	1220.3	1218.3	1216.3	1216.4	1217.1	1219.7
50°	1162.2	1159.4	1158.2	1157.9	1160.4	1162.9	1160.4	1157.9	1158.2	1159.4	1162.2
52.5°	1104.8	1101.7	1100.0	1099.2	1101.2	1103.2	1101.2	1099.2	1100.0	1101.7	1104.8
55°	1016.9	1013.8	1011.3	1009.7	1011.0	1012.2	1011.0	1009.7	1011.3	1013.8	1016.9
57.5°	924.9	921.7	918.7	916.9	918.7	920.4	918.7	916.9	918.7	921.7	924.9
60°	862.1	858.9	856.4	854.9	856.1	857.4	856.1	854.9	856.4	858.9	862.1
62.5°	799.2	795.9	793.4	791.8	793.0	794.3	793.0	791.8	793.4	795.9	799.2
65°	704.4	701.3	698.8	697.0	697.7	698.3	697.7	697.0	698.8	701.3	704.4
67.5°	608.0	604.4	600.8	598.3	599.3	600.3	599.3	598.3	600.8	604.4	608.0
70°	543.6	540.4	537.3	535.0	535.0	535.0	535.0	535.0	537.3	540.4	543.6
72.5°	478.5	475.4	472.7	470.8	470.8	470.8	470.8	470.8	472.7	475.4	478.5
75°	382.5	380.0	376.8	374.3	373.7	373.1	373.7	374.3	376.8	380.0	382.5
77.5°	284.7	282.3	280.0	278.0	277.2	276.5	277.2	278.0	280.0	282.3	284.7
80°	224.8	222.9	221.0	219.3	218.1	216.8	218.1	219.3	221.0	222.9	224.8
82.5°	166.2	163.8	161.0	159.1	160.4	161.6	160.4	159.1	161.0	163.8	166.2
85°	85.4	83.2	80.7	78.7	78.1	77.4	78.1	78.7	80.7	83.2	85.4
87.5°	33.7	35.2	36.4	36.5	37.9	36.5	37.9	36.5	36.4	35.2	33.7
90°	52.3	68.2	84.1	93.2	102.3	97.8	102.3	93.2	84.1	68.2	52.3
92.5°	105.1	131.9	151.5	167.8	175.1	174.2	175.1	167.8	151.5	131.9	105.1
95°	211.5	243.3	275.2	297.9	311.6	307.0	311.6	297.9	275.2	243.3	211.5
97.5°	326.1	368.9	404.4	425.7	439.4	448.5	439.4	425.7	404.4	368.9	326.1
100°	402.5	443.5	484.4	509.4	532.2	541.3	532.2	509.4	484.4	443.5	402.5
102.5°	464.4	518.1	562.7	589.5	608.6	617.7	608.6	589.5	562.7	518.1	464.4
105°	566.3	623.1	670.9	705.0	725.5	732.3	725.5	705.0	670.9	623.1	566.3
107.5°	668.2	726.9	771.0	808.7	833.7	848.3	833.7	808.7	771.0	726.9	668.2
110°	748.2	796.0	843.8	877.9	902.9	912.0	902.9	877.9	843.8	796.0	748.2



TEST NUMBER: P1427813

CATALOG NUMBER: SQ2W-F-K-150U-125D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	815.6	868.8	916.5	950.6	979.3	992.0	979.3	950.6	916.5	868.8	815.6
115°	909.7	980.2	1023.4	1055.3	1075.7	1087.1	1075.7	1055.3	1023.4	980.2	909.7
117.5°	987.9	1061.6	1108.9	1133.5	1143.0	1151.2	1143.0	1133.5	1108.9	1061.6	987.9
120°	1037.1	1105.3	1159.9	1191.7	1203.1	1207.6	1203.1	1191.7	1159.9	1105.3	1037.1
122.5°	1082.6	1147.1	1199.9	1239.0	1257.7	1262.2	1257.7	1239.0	1199.9	1147.1	1082.6
125°	1146.2	1207.6	1262.2	1300.9	1321.4	1332.7	1321.4	1300.9	1262.2	1207.6	1146.2
127.5°	1201.7	1268.1	1318.2	1353.2	1373.2	1382.3	1373.2	1353.2	1318.2	1268.1	1201.7
130°	1232.7	1300.9	1350.9	1389.6	1407.8	1416.9	1407.8	1389.6	1350.9	1300.9	1232.7
132.5°	1256.3	1328.2	1380.0	1415.1	1435.1	1444.2	1435.1	1415.1	1380.0	1328.2	1256.3
135°	1285.0	1360.0	1414.6	1448.7	1466.9	1476.0	1466.9	1448.7	1414.6	1360.0	1285.0
137.5°	1310.0	1378.2	1435.1	1471.0	1487.4	1493.3	1487.4	1471.0	1435.1	1378.2	1310.0
140°	1328.2	1387.3	1444.2	1478.3	1496.5	1498.7	1496.5	1478.3	1444.2	1387.3	1328.2
142.5°	1351.8	1398.2	1447.8	1481.9	1500.1	1504.2	1500.1	1481.9	1447.8	1398.2	1351.8
145°	1394.1	1421.4	1455.5	1487.4	1503.3	1507.8	1503.3	1487.4	1455.5	1421.4	1394.1
147.5°	1447.3	1456.0	1473.7	1494.6	1510.1	1513.3	1510.1	1494.6	1473.7	1456.0	1447.3
150°	1487.4	1485.1	1491.9	1505.6	1519.2	1516.9	1519.2	1505.6	1491.9	1485.1	1487.4
152.5°	1532.9	1519.7	1519.2	1525.6	1531.9	1531.5	1531.9	1525.6	1519.2	1519.7	1532.9
155°	1610.2	1585.2	1571.5	1567.0	1567.0	1564.7	1567.0	1567.0	1571.5	1585.2	1610.2
157.5°	1695.2	1660.2	1639.7	1628.8	1625.6	1620.6	1625.6	1628.8	1639.7	1660.2	1695.2
160°	1753.5	1714.8	1694.3	1676.1	1669.3	1662.5	1669.3	1676.1	1694.3	1714.8	1753.5
162.5°	1808.0	1771.2	1748.9	1732.5	1725.7	1715.3	1725.7	1732.5	1748.9	1771.2	1808.0
165°	1896.7	1858.1	1833.1	1819.4	1810.3	1801.2	1810.3	1819.4	1833.1	1858.1	1896.7
167.5°	1985.4	1943.1	1926.8	1911.3	1902.7	1886.3	1902.7	1911.3	1926.8	1943.1	1985.4
170°	2040.0	2001.4	1992.3	1978.6	1962.7	1944.5	1962.7	1978.6	1992.3	2001.4	2040.0
172.5°	2087.3	2061.4	2052.3	2038.7	2033.7	2019.1	2033.7	2038.7	2052.3	2061.4	2087.3
175°	2156.0	2135.5	2135.5	2133.3	2126.4	2112.8	2126.4	2133.3	2135.5	2135.5	2156.0
177.5°	2213.3	2202.4	2209.7	2209.7	2207.9	2195.1	2207.9	2209.7	2209.7	2202.4	2213.3
180°	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5



TEST NUMBER: P1427813

CATALOG NUMBER: SQ2W-F-K-150U-125D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1999.1	1999.1	1999.1	1999.1
2.5°	2004.0	2008.0	1998.5	1989.0
5°	2000.0	2004.4	1991.9	1979.4
7.5°	1984.4	1988.4	1975.9	1963.4
10°	1970.5	1974.9	1962.4	1949.8
12.5°	1954.3	1958.0	1945.5	1932.9
15°	1923.6	1927.0	1914.5	1902.0
17.5°	1884.9	1888.0	1876.3	1864.5
20°	1857.9	1861.1	1849.9	1838.6
22.5°	1826.7	1829.6	1818.3	1807.1
25°	1774.3	1776.7	1765.4	1754.1
27.5°	1715.8	1717.7	1708.3	1699.0
30°	1674.8	1677.2	1667.8	1658.4
32.5°	1630.2	1633.4	1624.5	1615.6
35°	1560.3	1563.6	1556.1	1548.6
37.5°	1489.5	1492.8	1487.1	1481.3
40°	1440.7	1444.3	1438.0	1431.8
42.5°	1387.4	1390.6	1385.8	1381.1
45°	1307.9	1311.0	1306.6	1302.2
47.5°	1224.1	1226.5	1223.1	1219.7
50°	1166.6	1168.8	1164.4	1160.0
52.5°	1109.2	1111.2	1106.4	1101.5
55°	1020.7	1022.1	1016.4	1010.8
57.5°	928.1	929.2	923.7	918.2
60°	865.8	867.4	862.4	857.4
62.5°	803.5	805.4	800.4	795.4
65°	708.1	709.9	705.5	701.1
67.5°	611.7	613.4	609.7	605.9
70°	546.7	548.1	544.4	540.6
72.5°	482.1	484.0	480.8	477.5
75°	384.3	385.3	383.4	381.5
77.5°	287.1	288.9	288.9	288.9
80°	226.7	228.1	228.1	228.1
82.5°	168.1	169.8	170.8	171.8
85°	87.3	89.0	90.3	91.5
87.5°	33.0	31.2	30.3	29.5
90°	40.9	25.0	15.9	6.8
92.5°	88.2	61.4	43.2	25.0
95°	177.4	141.0	100.1	70.5
97.5°	282.5	223.8	183.3	134.6
100°	338.9	282.0	243.3	191.0
102.5°	400.7	353.0	299.7	247.4
105°	511.7	452.6	391.2	332.0
107.5°	614.5	549.5	475.8	422.6
110°	680.0	609.5	532.2	484.4



TEST NUMBER: P1427813

CATALOG NUMBER: SQ2W-F-K-150U-125D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	743.7	671.4	592.2	544.5
115°	830.1	750.5	677.7	636.8
117.5°	913.3	831.5	754.6	722.3
120°	964.3	882.4	807.4	782.3
122.5°	1006.1	926.1	856.5	846.0
125°	1068.9	987.0	927.9	941.5
127.5°	1119.9	1044.8	1007.5	1038.0
130°	1150.8	1084.8	1062.1	1105.3
132.5°	1178.1	1126.7	1116.7	1176.3
135°	1219.0	1189.4	1198.5	1280.4
137.5°	1267.7	1256.3	1286.8	1390.0
140°	1298.6	1305.4	1348.6	1464.6
142.5°	1340.5	1356.4	1412.3	1535.6
145°	1405.5	1439.6	1512.4	1635.2
147.5°	1479.2	1523.3	1613.4	1739.4
150°	1528.3	1585.2	1680.7	1801.2
152.5°	1584.7	1643.4	1738.9	1861.3
155°	1671.6	1737.5	1837.6	1942.2
157.5°	1760.3	1827.6	1923.1	2014.5
160°	1814.9	1887.6	1974.1	2058.2
162.5°	1876.7	1944.0	2019.6	2094.6
165°	1967.2	2021.8	2083.2	2146.9
167.5°	2043.2	2088.7	2136.9	2186.5
170°	2092.3	2128.7	2169.7	2208.3
172.5°	2134.2	2163.3	2193.3	2226.5
175°	2190.1	2206.0	2224.2	2244.7
177.5°	2233.3	2238.8	2244.2	2253.3
180°	2251.5	2251.5	2251.5	2251.5



TEST NUMBER: P1427813
 CATALOG NUMBER: SQ2W-F-K-150U-125D-L830-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.57	20.41	20.55	21.41	22.73	19.48	20.32	20.47	21.32	22.65
	3H	21.36	22.11	22.35	23.12	24.46	21.25	22.00	22.25	23.01	24.36
	4H	22.05	22.76	23.06	23.78	25.13	21.94	22.65	22.95	23.66	25.01
	6H	22.49	23.14	23.51	24.16	25.53	22.34	23.00	23.37	24.02	25.39
	8H	22.65	23.27	23.67	24.31	25.67	22.49	23.12	23.52	24.15	25.51
	12H	22.73	23.32	23.76	24.35	25.74	22.55	23.15	23.58	24.18	25.56
4H	2H	20.14	20.86	21.16	21.87	23.22	20.08	20.79	21.09	21.80	23.16
	3H	22.16	22.76	23.19	23.80	25.17	22.07	22.67	23.10	23.71	25.07
	4H	22.98	23.52	24.01	24.56	25.95	22.87	23.41	23.90	24.45	25.83
	6H	23.53	24.00	24.57	25.06	26.44	23.39	23.86	24.43	24.91	26.30
	8H	23.74	24.18	24.79	25.23	26.63	23.58	24.02	24.63	25.07	26.47
	12H	23.85	24.25	24.92	25.32	26.72	23.67	24.07	24.73	25.13	26.54
8H	4H	23.22	23.66	24.26	24.71	26.11	23.12	23.56	24.17	24.61	26.01
	6H	23.91	24.27	24.98	25.36	26.76	23.78	24.14	24.84	25.23	26.63
	8H	24.21	24.53	25.29	25.61	27.02	24.06	24.38	25.13	25.45	26.87
	12H	24.39	24.68	25.47	25.75	27.20	24.20	24.48	25.28	25.55	27.01
12H	4H	23.21	23.61	24.28	24.67	26.08	23.12	23.52	24.18	24.58	25.99
	6H	23.96	24.28	25.03	25.35	26.77	23.83	24.15	24.91	25.23	26.64
	8H	24.29	24.57	25.37	25.64	27.10	24.14	24.42	25.22	25.49	26.95