

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427636

Luminaire Tested: SQ2W-BBN-K-125U-125D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1427636  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2308-130-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-BBN-K-125U-125D-L930-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - BLACK DISCREET BAFFLE, NARROW 35-DEGREE OPTIC  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9549.2 lumens  
Efficiency: N/A  
Efficacy: 101.8 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.62  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 93.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1427636

CATALOG NUMBER: SQ2W-BBN-K-125U-125D-L930-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1427636

CATALOG NUMBER: SQ2W-BBN-K-125U-125D-L930-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	100	97	94	91	93	90	88	85	77	75	74	65	64	63	54	53	53	48
2	94	88	83	79	87	82	78	75	71	68	66	61	59	57	51	50	49	45
3	88	80	75	70	81	75	70	66	66	62	59	57	54	52	48	47	45	42
4	82	74	67	63	76	69	64	60	61	57	54	53	50	48	46	44	42	39
5	77	68	61	57	72	64	58	54	56	52	49	50	47	44	43	41	40	37
6	72	63	56	51	68	59	53	49	53	48	45	47	43	41	41	39	37	35
7	68	58	52	47	64	55	49	45	49	45	42	44	41	38	39	37	35	33
8	64	54	48	43	60	51	46	42	46	42	39	41	38	36	37	35	33	31
9	61	51	44	40	57	48	43	39	44	39	36	39	36	34	35	33	31	29
10	58	48	41	37	54	45	40	36	41	37	34	37	34	32	34	31	29	28

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	144202	144202	144202	144202
5°	139380	139458	139380	139458
10°	119617	119617	119617	119617
15°	92846	92630	92846	92630
20°	67009	65571	67009	65571
25°	47512	45705	47512	45705
30°	35350	34119	35350	34119
35°	27505	26236	27505	26236
40°	20354	18589	20354	18589
45°	10401	8380	10401	8380
50°	2263	1658	2263	1658
55°	633	498	633	498
60°	103	52	103	52
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 12688 cd/sqm



TEST NUMBER: P1427636

CATALOG NUMBER: SQ2W-BBN-K-125U-125D-L930-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	772.3	8.1
10°-20°	1522.7	15.9
20°-30°	1228.3	12.9
30°-40°	853.3	8.9
40°-50°	394.1	4.1
50°-60°	55.2	0.6
60°-70°	1.9	0.0
70°-80°	0.0	0.0
80°-90°	8.6	0.1
90°-100°	128.5	1.3
100°-110°	374.8	3.9
110°-120°	611.6	6.4
120°-130°	776.1	8.1
130°-140°	830.4	8.7
140°-150°	775.4	8.1
150°-160°	638.1	6.7
160°-170°	427.9	4.5
170°-180°	151.9	1.6
0°-30°	3523.3	36.9
0°-40°	4376.6	45.8
0°-60°	4825.9	50.5
0°-90°	4836.4	50.6
90°-120°	1114.9	11.7
90°-150°	3496.8	36.6
90°-180°	4715.0	49.4
0°-180°	9549.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	8931	8931	8931	8931	8931	
5°	8600	8605	8600	8605	8600	773
15°	5555	5542	5555	5542	5555	1529
25°	2667	2566	2667	2566	2667	1249
35°	1396	1331	1396	1331	1396	873
45°	456	367	456	367	456	368
55°	22	18	22	18	22	28
65°	0	0	0	0	0	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	5	36	5	70	5	4
95°	51	38	51	220	51	61
105°	238	382	238	525	238	253
115°	457	633	457	780	457	450
125°	675	1003	675	956	675	604
135°	918	1313	918	1058	918	710
145°	1173	1514	1173	1081	1173	734
155°	1393	1644	1393	1122	1393	640
165°	1540	1714	1540	1292	1540	433
175°	1610	1678	1610	1515	1610	153
180°	1615	1615	1615	1615	1615	



TEST NUMBER: P1427636

CATALOG NUMBER: SQ2W-BBN-K-125U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	8931.4	8931.4	8931.4	8931.4	8931.4	8931.4	8931.4	8931.4	8931.4	8931.4	8931.4
2.5°	8926.3	8911.4	8896.5	8867.1	8832.7	8831.3	8862.8	8883.9	8874.2	8864.5	8874.2
5°	8599.9	8579.1	8558.4	8533.3	8506.9	8516.9	8563.4	8599.0	8601.8	8604.7	8601.8
7.5°	7879.4	7886.2	7892.9	7875.7	7850.5	7863.7	7915.2	7952.4	7946.8	7941.2	7946.8
10°	7296.1	7301.1	7306.1	7305.2	7302.4	7309.5	7326.7	7334.8	7315.4	7296.1	7315.4
12.5°	6620.1	6640.0	6659.9	6637.0	6599.8	6594.0	6619.8	6641.1	6649.3	6657.5	6649.3
15°	5554.6	5586.8	5619.0	5573.4	5501.8	5483.2	5517.6	5543.1	5542.4	5541.7	5542.4
17.5°	4555.4	4552.1	4548.8	4520.6	4484.1	4469.1	4475.5	4479.8	4477.7	4475.5	4477.7
20°	3900.0	3895.0	3889.9	3865.6	3834.9	3817.0	3812.0	3809.1	3812.7	3816.3	3812.7
22.5°	3338.5	3330.1	3321.7	3311.5	3300.8	3289.2	3276.7	3268.6	3273.3	3278.0	3273.3
25°	2667.0	2639.9	2612.7	2590.9	2570.8	2569.4	2586.6	2595.7	2580.7	2565.6	2580.7
27.5°	2140.7	2140.3	2139.9	2127.0	2110.0	2102.4	2104.2	2106.3	2109.2	2112.1	2109.2
30°	1896.1	1891.1	1886.0	1872.5	1856.0	1848.1	1848.8	1847.2	1838.7	1830.1	1838.7
32.5°	1678.4	1682.0	1685.6	1671.2	1650.7	1638.5	1634.7	1629.6	1621.0	1612.5	1621.0
35°	1395.5	1395.5	1395.5	1383.7	1367.9	1354.7	1344.0	1335.4	1333.3	1331.1	1333.3
37.5°	1133.1	1131.8	1130.6	1121.9	1110.7	1097.5	1082.4	1069.6	1064.0	1058.4	1064.0
40°	965.7	962.2	958.6	952.3	945.2	932.3	913.7	897.8	889.9	882.0	889.9
42.5°	775.2	784.7	794.3	791.4	784.2	771.3	752.7	735.8	723.9	712.1	723.9
45°	455.5	495.6	535.6	549.9	555.7	547.8	526.3	494.3	430.6	367.0	430.6
47.5°	195.7	239.8	283.9	320.8	355.5	344.5	288.0	232.4	179.4	126.5	179.4
50°	90.1	124.5	158.8	205.0	255.0	244.7	173.8	114.6	90.3	66.0	90.3
52.5°	52.8	70.0	87.1	130.3	182.1	177.4	116.3	67.3	54.4	41.5	54.4
55°	22.5	28.3	34.0	57.4	86.7	85.3	53.1	27.7	22.7	17.7	22.7
57.5°	8.4	11.5	14.7	23.1	33.2	32.6	21.1	11.9	9.3	6.8	9.3
60°	3.2	4.6	6.1	10.2	15.2	14.8	9.1	4.5	3.0	1.6	3.0
62.5°	0.6	1.5	2.4	4.6	7.3	7.3	4.4	2.0	1.2	0.3	1.2
65°	0.0	0.0	0.0	0.5	1.3	1.3	0.5	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	1.0	2.3	3.9	5.2	6.2	6.5	6.5	6.9	7.2	7.2	7.2
90°	4.9	11.4	19.6	26.1	31.0	32.6	32.6	34.3	35.9	35.9	35.9
92.5°	17.9	28.4	28.7	28.7	34.9	37.8	40.4	40.8	42.4	42.4	42.4
95°	50.6	55.5	83.2	81.6	55.5	44.0	37.5	37.5	37.5	37.5	37.5
97.5°	96.6	103.7	108.3	145.2	153.3	148.1	120.7	101.5	90.7	85.8	90.7
100°	137.0	140.3	150.1	151.7	192.5	231.6	212.0	187.6	179.4	174.5	179.4
102.5°	177.5	179.4	194.4	201.3	210.7	232.9	300.8	293.3	287.7	286.7	287.7
105°	238.1	239.8	267.5	280.5	287.1	287.1	285.4	318.1	370.2	381.7	370.2
107.5°	303.0	310.5	343.2	378.1	385.6	387.5	379.1	374.2	372.2	373.5	372.2
110°	347.4	358.8	398.0	442.0	453.4	456.7	453.4	448.5	445.3	445.3	445.3



TEST NUMBER: P1427636

CATALOG NUMBER: SQ2W-BBN-K-125U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	390.5	407.1	451.5	502.0	521.3	531.1	523.9	520.3	517.0	519.6	517.0
115°	456.7	481.2	539.9	592.1	631.2	636.1	634.5	634.5	632.8	632.8	632.8
117.5°	518.0	557.2	623.1	683.7	729.1	742.1	748.6	746.7	744.7	748.0	744.7
120°	561.1	606.7	681.8	750.3	794.3	813.9	820.4	817.1	820.4	817.1	820.4
122.5°	606.7	662.9	736.6	807.7	859.6	881.7	889.6	890.2	890.9	888.9	890.9
125°	675.2	743.8	830.2	903.6	957.4	983.5	990.0	991.7	994.9	1003.1	994.9
127.5°	744.4	822.0	917.0	987.8	1042.9	1074.5	1084.6	1088.2	1095.1	1098.7	1095.1
130°	792.7	880.8	977.0	1043.9	1097.7	1131.9	1149.9	1154.8	1162.9	1161.3	1162.9
132.5°	843.6	935.6	1033.1	1102.6	1152.5	1189.3	1204.7	1218.7	1221.6	1223.9	1221.6
135°	918.3	1017.8	1115.6	1184.1	1231.4	1267.3	1286.9	1299.9	1308.1	1313.0	1308.1
137.5°	996.9	1101.9	1195.9	1256.9	1304.5	1335.5	1357.7	1371.4	1379.9	1383.8	1379.9
140°	1050.4	1151.5	1242.8	1306.5	1348.9	1379.9	1399.4	1415.7	1425.5	1425.5	1425.5
142.5°	1101.3	1201.1	1289.8	1353.4	1390.6	1419.0	1439.9	1452.3	1463.4	1463.4	1463.4
145°	1172.7	1272.2	1353.8	1417.4	1448.4	1474.5	1497.3	1507.1	1513.6	1513.6	1513.6
147.5°	1247.4	1335.5	1409.9	1470.9	1497.0	1527.6	1545.6	1553.4	1561.6	1558.0	1561.6
150°	1291.8	1373.3	1445.1	1502.2	1528.3	1557.6	1575.6	1582.1	1590.3	1585.4	1590.3
152.5°	1334.8	1412.5	1477.7	1530.9	1553.1	1582.4	1603.0	1609.5	1615.0	1611.5	1615.0
155°	1392.9	1461.4	1521.8	1570.7	1590.3	1618.0	1637.6	1645.7	1652.2	1644.1	1652.2
157.5°	1444.8	1503.8	1556.3	1601.3	1622.2	1646.0	1664.3	1674.4	1680.9	1677.4	1680.9
160°	1476.1	1529.9	1577.2	1619.6	1639.2	1660.4	1680.0	1691.4	1697.9	1693.0	1697.9
162.5°	1502.2	1550.8	1595.5	1634.0	1650.9	1669.5	1693.0	1703.1	1709.6	1703.5	1709.6
165°	1539.7	1578.8	1618.0	1650.6	1665.3	1680.0	1704.4	1715.8	1720.7	1714.2	1720.7
167.5°	1568.1	1598.1	1629.7	1657.8	1668.5	1682.9	1707.4	1716.8	1723.0	1714.9	1723.0
170°	1583.7	1609.8	1637.6	1660.4	1668.5	1681.6	1706.1	1714.2	1719.1	1711.0	1719.1
172.5°	1596.8	1616.4	1638.9	1659.1	1663.3	1673.8	1696.9	1705.1	1708.7	1701.8	1708.7
175°	1609.8	1621.2	1637.6	1650.6	1649.0	1655.5	1675.1	1681.6	1688.1	1678.3	1688.1
177.5°	1616.0	1621.2	1626.5	1634.3	1629.1	1629.1	1643.4	1647.3	1648.6	1643.4	1648.6
180°	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7



TEST NUMBER: P1427636

CATALOG NUMBER: SQ2W-BBN-K-125U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	8931.4	8931.4	8931.4	8931.4	8931.4	8931.4	8931.4	8931.4	8931.4	8931.4	8931.4
2.5°	8883.9	8862.8	8831.3	8832.7	8867.1	8896.5	8911.4	8926.3	8911.4	8896.5	8867.1
5°	8599.0	8563.4	8516.9	8506.9	8533.3	8558.4	8579.1	8599.9	8579.1	8558.4	8533.3
7.5°	7952.4	7915.2	7863.7	7850.5	7875.7	7892.9	7886.2	7879.4	7886.2	7892.9	7875.7
10°	7334.8	7326.7	7309.5	7302.4	7305.2	7306.1	7301.1	7296.1	7301.1	7306.1	7305.2
12.5°	6641.1	6619.8	6594.0	6599.8	6637.0	6659.9	6640.0	6620.1	6640.0	6659.9	6637.0
15°	5543.1	5517.6	5483.2	5501.8	5573.4	5619.0	5586.8	5554.6	5586.8	5619.0	5573.4
17.5°	4479.8	4475.5	4469.1	4484.1	4520.6	4548.8	4552.1	4555.4	4552.1	4548.8	4520.6
20°	3809.1	3812.0	3817.0	3834.9	3865.6	3889.9	3895.0	3900.0	3895.0	3889.9	3865.6
22.5°	3268.6	3276.7	3289.2	3300.8	3311.5	3321.7	3330.1	3338.5	3330.1	3321.7	3311.5
25°	2595.7	2586.6	2569.4	2570.8	2590.9	2612.7	2639.9	2667.0	2639.9	2612.7	2590.9
27.5°	2106.3	2104.2	2102.4	2110.0	2127.0	2139.9	2140.3	2140.7	2140.3	2139.9	2127.0
30°	1847.2	1848.8	1848.1	1856.0	1872.5	1886.0	1891.1	1896.1	1891.1	1886.0	1872.5
32.5°	1629.6	1634.7	1638.5	1650.7	1671.2	1685.6	1682.0	1678.4	1682.0	1685.6	1671.2
35°	1335.4	1344.0	1354.7	1367.9	1383.7	1395.5	1395.5	1395.5	1395.5	1395.5	1383.7
37.5°	1069.6	1082.4	1097.5	1110.7	1121.9	1130.6	1131.8	1133.1	1131.8	1130.6	1121.9
40°	897.8	913.7	932.3	945.2	952.3	958.6	962.2	965.7	962.2	958.6	952.3
42.5°	735.8	752.7	771.3	784.2	791.4	794.3	784.7	775.2	784.7	794.3	791.4
45°	494.3	526.3	547.8	555.7	549.9	535.6	495.6	455.5	495.6	535.6	549.9
47.5°	232.4	288.0	344.5	355.5	320.8	283.9	239.8	195.7	239.8	283.9	320.8
50°	114.6	173.8	244.7	255.0	205.0	158.8	124.5	90.1	124.5	158.8	205.0
52.5°	67.3	116.3	177.4	182.1	130.3	87.1	70.0	52.8	70.0	87.1	130.3
55°	27.7	53.1	85.3	86.7	57.4	34.0	28.3	22.5	28.3	34.0	57.4
57.5°	11.9	21.1	32.6	33.2	23.1	14.7	11.5	8.4	11.5	14.7	23.1
60°	4.5	9.1	14.8	15.2	10.2	6.1	4.6	3.2	4.6	6.1	10.2
62.5°	2.0	4.4	7.3	7.3	4.6	2.4	1.5	0.6	1.5	2.4	4.6
65°	0.0	0.5	1.3	1.3	0.5	0.0	0.0	0.0	0.0	0.0	0.5
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	6.9	6.5	6.5	6.2	5.2	3.9	2.3	1.0	2.3	3.6	5.9
90°	34.3	32.6	32.6	31.0	26.1	19.6	11.4	4.9	11.4	17.9	29.4
92.5°	40.8	40.4	37.8	34.9	28.7	28.7	28.4	17.9	31.0	44.0	63.3
95°	37.5	37.5	44.0	55.5	81.6	83.2	55.5	50.6	71.8	101.1	127.2
97.5°	101.5	120.7	148.1	153.3	145.2	108.3	103.7	96.6	131.5	160.5	202.6
100°	187.6	212.0	231.6	192.5	151.7	150.1	140.3	137.0	174.5	202.2	243.0
102.5°	293.3	300.8	232.9	210.7	201.3	194.4	179.4	177.5	215.0	253.1	287.4
105°	318.1	285.4	287.1	287.1	280.5	267.5	239.8	238.1	280.5	324.6	367.0
107.5°	374.2	379.1	387.5	385.6	378.1	343.2	310.5	303.0	341.2	394.1	440.7
110°	448.5	453.4	456.7	453.4	442.0	398.0	358.8	347.4	381.7	437.1	487.7



TEST NUMBER: P1427636

CATALOG NUMBER: SQ2W-BBN-K-125U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	520.3	523.9	531.1	521.3	502.0	451.5	407.1	390.5	424.7	481.5	533.3
115°	634.5	634.5	636.1	631.2	592.1	539.9	481.2	456.7	486.0	538.2	595.3
117.5°	746.7	748.6	742.1	729.1	683.7	623.1	557.2	518.0	541.2	596.3	655.0
120°	817.1	820.4	813.9	794.3	750.3	681.8	606.7	561.1	579.0	632.8	691.6
122.5°	890.2	889.6	881.7	859.6	807.7	736.6	662.9	606.7	614.2	664.2	721.6
125°	991.7	990.0	983.5	957.4	903.6	830.2	743.8	675.2	665.5	707.9	766.6
127.5°	1088.2	1084.6	1074.5	1042.9	987.8	917.0	822.0	744.4	722.5	749.3	803.1
130°	1154.8	1149.9	1131.9	1097.7	1043.9	977.0	880.8	792.7	761.7	778.0	825.3
132.5°	1218.7	1204.7	1189.3	1152.5	1102.6	1033.1	935.6	843.6	800.8	808.0	844.9
135°	1299.9	1286.9	1267.3	1231.4	1184.1	1115.6	1017.8	918.3	859.6	853.0	874.2
137.5°	1371.4	1357.7	1335.5	1304.5	1256.9	1195.9	1101.9	996.9	922.8	901.0	909.1
140°	1415.7	1399.4	1379.9	1348.9	1306.5	1242.8	1151.5	1050.4	967.2	936.2	931.3
142.5°	1452.3	1439.9	1419.0	1390.6	1353.4	1289.8	1201.1	1101.3	1012.9	972.7	961.3
145°	1507.1	1497.3	1474.5	1448.4	1417.4	1353.8	1272.2	1172.7	1084.6	1032.4	1008.0
147.5°	1553.4	1545.6	1527.6	1497.0	1470.9	1409.9	1335.5	1247.4	1157.1	1092.5	1060.8
150°	1582.1	1575.6	1557.6	1528.3	1502.2	1445.1	1373.3	1291.8	1205.3	1136.8	1096.1
152.5°	1609.5	1603.0	1582.4	1553.1	1530.9	1477.7	1412.5	1334.8	1247.1	1178.6	1136.5
155°	1645.7	1637.6	1618.0	1590.3	1570.7	1521.8	1461.4	1392.9	1317.9	1246.1	1198.8
157.5°	1674.4	1664.3	1646.0	1622.2	1601.3	1556.3	1503.8	1444.8	1379.2	1310.7	1262.4
160°	1691.4	1680.0	1660.4	1639.2	1619.6	1577.2	1529.9	1476.1	1415.7	1353.8	1301.6
162.5°	1703.1	1693.0	1669.5	1650.9	1634.0	1595.5	1550.8	1502.2	1448.4	1394.2	1345.9
165°	1715.8	1704.4	1680.0	1665.3	1650.6	1618.0	1578.8	1539.7	1494.0	1450.0	1410.8
167.5°	1716.8	1707.4	1682.9	1668.5	1657.8	1629.7	1598.1	1568.1	1532.5	1497.9	1465.3
170°	1714.2	1706.1	1681.6	1668.5	1660.4	1637.6	1609.8	1583.7	1556.0	1526.6	1500.6
172.5°	1705.1	1696.9	1673.8	1663.3	1659.1	1638.9	1616.4	1596.8	1573.0	1551.4	1530.6
175°	1681.6	1675.1	1655.5	1649.0	1650.6	1637.6	1621.2	1609.8	1595.2	1582.1	1570.7
177.5°	1647.3	1643.4	1629.1	1629.1	1634.3	1626.5	1621.2	1616.0	1609.5	1605.6	1601.7
180°	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7



TEST NUMBER: P1427636

CATALOG NUMBER: SQ2W-BBN-K-125U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	8931.4	8931.4	8931.4	8931.4	8931.4	8931.4	8931.4	8931.4	8931.4	8931.4	8931.4
2.5°	8832.7	8831.3	8862.8	8883.9	8874.2	8864.5	8874.2	8883.9	8862.8	8831.3	8832.7
5°	8506.9	8516.9	8563.4	8599.0	8601.8	8604.7	8601.8	8599.0	8563.4	8516.9	8506.9
7.5°	7850.5	7863.7	7915.2	7952.4	7946.8	7941.2	7946.8	7952.4	7915.2	7863.7	7850.5
10°	7302.4	7309.5	7326.7	7334.8	7315.4	7296.1	7315.4	7334.8	7326.7	7309.5	7302.4
12.5°	6599.8	6594.0	6619.8	6641.1	6649.3	6657.5	6649.3	6641.1	6619.8	6594.0	6599.8
15°	5501.8	5483.2	5517.6	5543.1	5542.4	5541.7	5542.4	5543.1	5517.6	5483.2	5501.8
17.5°	4484.1	4469.1	4475.5	4479.8	4477.7	4475.5	4477.7	4479.8	4475.5	4469.1	4484.1
20°	3834.9	3817.0	3812.0	3809.1	3812.7	3816.3	3812.7	3809.1	3812.0	3817.0	3834.9
22.5°	3300.8	3289.2	3276.7	3268.6	3273.3	3278.0	3273.3	3268.6	3276.7	3289.2	3300.8
25°	2570.8	2569.4	2586.6	2595.7	2580.7	2565.6	2580.7	2595.7	2586.6	2569.4	2570.8
27.5°	2110.0	2102.4	2104.2	2106.3	2109.2	2112.1	2109.2	2106.3	2104.2	2102.4	2110.0
30°	1856.0	1848.1	1848.8	1847.2	1838.7	1830.1	1838.7	1847.2	1848.8	1848.1	1856.0
32.5°	1650.7	1638.5	1634.7	1629.6	1621.0	1612.5	1621.0	1629.6	1634.7	1638.5	1650.7
35°	1367.9	1354.7	1344.0	1335.4	1333.3	1331.1	1333.3	1335.4	1344.0	1354.7	1367.9
37.5°	1110.7	1097.5	1082.4	1069.6	1064.0	1058.4	1064.0	1069.6	1082.4	1097.5	1110.7
40°	945.2	932.3	913.7	897.8	889.9	882.0	889.9	897.8	913.7	932.3	945.2
42.5°	784.2	771.3	752.7	735.8	723.9	712.1	723.9	735.8	752.7	771.3	784.2
45°	555.7	547.8	526.3	494.3	430.6	367.0	430.6	494.3	526.3	547.8	555.7
47.5°	355.5	344.5	288.0	232.4	179.4	126.5	179.4	232.4	288.0	344.5	355.5
50°	255.0	244.7	173.8	114.6	90.3	66.0	90.3	114.6	173.8	244.7	255.0
52.5°	182.1	177.4	116.3	67.3	54.4	41.5	54.4	67.3	116.3	177.4	182.1
55°	86.7	85.3	53.1	27.7	22.7	17.7	22.7	27.7	53.1	85.3	86.7
57.5°	33.2	32.6	21.1	11.9	9.3	6.8	9.3	11.9	21.1	32.6	33.2
60°	15.2	14.8	9.1	4.5	3.0	1.6	3.0	4.5	9.1	14.8	15.2
62.5°	7.3	7.3	4.4	2.0	1.2	0.3	1.2	2.0	4.4	7.3	7.3
65°	1.3	1.3	0.5	0.0	0.0	0.0	0.0	0.0	0.5	1.3	1.3
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	7.5	9.8	12.1	13.4	14.7	14.0	14.7	13.4	12.1	9.8	7.5
90°	37.5	48.9	60.3	66.9	73.4	70.1	73.4	66.9	60.3	48.9	37.5
92.5°	75.4	94.6	108.6	120.4	125.6	124.9	125.6	120.4	108.6	94.6	75.4
95°	151.7	174.5	197.4	213.7	223.5	220.2	223.5	213.7	197.4	174.5	151.7
97.5°	233.9	264.6	290.0	305.3	315.1	321.6	315.1	305.3	290.0	264.6	233.9
100°	288.7	318.1	347.4	365.4	381.7	388.2	381.7	365.4	347.4	318.1	288.7
102.5°	333.1	371.5	403.5	422.8	436.5	443.0	436.5	422.8	403.5	371.5	333.1
105°	406.1	446.9	481.2	505.6	520.3	525.2	520.3	505.6	481.2	446.9	406.1
107.5°	479.2	521.3	552.9	580.0	597.9	608.4	597.9	580.0	552.9	521.3	479.2
110°	536.6	570.9	605.1	629.6	647.5	654.0	647.5	629.6	605.1	570.9	536.6



TEST NUMBER: P1427636

CATALOG NUMBER: SQ2W-BBN-K-125U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	584.9	623.1	657.3	681.8	702.3	711.5	702.3	681.8	657.3	623.1	584.9
115°	652.4	703.0	734.0	756.8	771.5	779.6	771.5	756.8	734.0	703.0	652.4
117.5°	708.5	761.4	795.3	812.9	819.8	825.6	819.8	812.9	795.3	761.4	708.5
120°	743.8	792.7	831.8	854.7	862.8	866.1	862.8	854.7	831.8	792.7	743.8
122.5°	776.4	822.7	860.5	888.6	902.0	905.2	902.0	888.6	860.5	822.7	776.4
125°	822.0	866.1	905.2	933.0	947.6	955.8	947.6	933.0	905.2	866.1	822.0
127.5°	861.8	909.5	945.3	970.5	984.8	991.3	984.8	970.5	945.3	909.5	861.8
130°	884.0	933.0	968.8	996.6	1009.6	1016.1	1009.6	996.6	968.8	933.0	884.0
132.5°	901.0	952.5	989.7	1014.8	1029.2	1035.7	1029.2	1014.8	989.7	952.5	901.0
135°	921.5	975.4	1014.5	1039.0	1052.0	1058.5	1052.0	1039.0	1014.5	975.4	921.5
137.5°	939.5	988.4	1029.2	1055.0	1066.7	1070.9	1066.7	1055.0	1029.2	988.4	939.5
140°	952.5	994.9	1035.7	1060.2	1073.2	1074.9	1073.2	1060.2	1035.7	994.9	952.5
142.5°	969.5	1002.8	1038.3	1062.8	1075.8	1078.8	1075.8	1062.8	1038.3	1002.8	969.5
145°	999.8	1019.4	1043.9	1066.7	1078.1	1081.4	1078.1	1066.7	1043.9	1019.4	999.8
147.5°	1038.0	1044.2	1056.9	1071.9	1083.0	1085.3	1083.0	1071.9	1056.9	1044.2	1038.0
150°	1066.7	1065.1	1070.0	1079.7	1089.5	1087.9	1089.5	1079.7	1070.0	1065.1	1066.7
152.5°	1099.3	1089.9	1089.5	1094.1	1098.7	1098.3	1098.7	1094.1	1089.5	1089.9	1099.3
155°	1154.8	1136.8	1127.0	1123.8	1123.8	1122.2	1123.8	1123.8	1127.0	1136.8	1154.8
157.5°	1215.8	1190.7	1176.0	1168.1	1165.9	1162.3	1165.9	1168.1	1176.0	1190.7	1215.8
160°	1257.5	1229.8	1215.1	1202.1	1197.2	1192.3	1197.2	1202.1	1215.1	1229.8	1257.5
162.5°	1296.7	1270.2	1254.3	1242.5	1237.6	1230.1	1237.6	1242.5	1254.3	1270.2	1296.7
165°	1360.3	1332.6	1314.6	1304.8	1298.3	1291.8	1298.3	1304.8	1314.6	1332.6	1360.3
167.5°	1423.9	1393.6	1381.8	1370.7	1364.5	1352.8	1364.5	1370.7	1381.8	1393.6	1423.9
170°	1463.0	1435.3	1428.8	1419.0	1407.6	1394.5	1407.6	1419.0	1428.8	1435.3	1463.0
172.5°	1497.0	1478.4	1471.8	1462.1	1458.5	1448.0	1458.5	1462.1	1471.8	1478.4	1497.0
175°	1546.2	1531.5	1531.5	1529.9	1525.0	1515.2	1525.0	1529.9	1531.5	1531.5	1546.2
177.5°	1587.3	1579.5	1584.7	1584.7	1583.4	1574.3	1583.4	1584.7	1584.7	1579.5	1587.3
180°	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7	1614.7



TEST NUMBER: P1427636

CATALOG NUMBER: SQ2W-BBN-K-125U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	8931.4	8931.4	8931.4	8931.4
2.5°	8867.1	8896.5	8911.4	8926.3
5°	8533.3	8558.4	8579.1	8599.9
7.5°	7875.7	7892.9	7886.2	7879.4
10°	7305.2	7306.1	7301.1	7296.1
12.5°	6637.0	6659.9	6640.0	6620.1
15°	5573.4	5619.0	5586.8	5554.6
17.5°	4520.6	4548.8	4552.1	4555.4
20°	3865.6	3889.9	3895.0	3900.0
22.5°	3311.5	3321.7	3330.1	3338.5
25°	2590.9	2612.7	2639.9	2667.0
27.5°	2127.0	2139.9	2140.3	2140.7
30°	1872.5	1886.0	1891.1	1896.1
32.5°	1671.2	1685.6	1682.0	1678.4
35°	1383.7	1395.5	1395.5	1395.5
37.5°	1121.9	1130.6	1131.8	1133.1
40°	952.3	958.6	962.2	965.7
42.5°	791.4	794.3	784.7	775.2
45°	549.9	535.6	495.6	455.5
47.5°	320.8	283.9	239.8	195.7
50°	205.0	158.8	124.5	90.1
52.5°	130.3	87.1	70.0	52.8
55°	57.4	34.0	28.3	22.5
57.5°	23.1	14.7	11.5	8.4
60°	10.2	6.1	4.6	3.2
62.5°	4.6	2.4	1.5	0.6
65°	0.5	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	5.9	3.6	2.3	1.0
90°	29.4	17.9	11.4	4.9
92.5°	63.3	44.0	31.0	17.9
95°	127.2	101.1	71.8	50.6
97.5°	202.6	160.5	131.5	96.6
100°	243.0	202.2	174.5	137.0
102.5°	287.4	253.1	215.0	177.5
105°	367.0	324.6	280.5	238.1
107.5°	440.7	394.1	341.2	303.0
110°	487.7	437.1	381.7	347.4



TEST NUMBER: P1427636

CATALOG NUMBER: SQ2W-BBN-K-125U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	533.3	481.5	424.7	390.5
115°	595.3	538.2	486.0	456.7
117.5°	655.0	596.3	541.2	518.0
120°	691.6	632.8	579.0	561.1
122.5°	721.6	664.2	614.2	606.7
125°	766.6	707.9	665.5	675.2
127.5°	803.1	749.3	722.5	744.4
130°	825.3	778.0	761.7	792.7
132.5°	844.9	808.0	800.8	843.6
135°	874.2	853.0	859.6	918.3
137.5°	909.1	901.0	922.8	996.9
140°	931.3	936.2	967.2	1050.4
142.5°	961.3	972.7	1012.9	1101.3
145°	1008.0	1032.4	1084.6	1172.7
147.5°	1060.8	1092.5	1157.1	1247.4
150°	1096.1	1136.8	1205.3	1291.8
152.5°	1136.5	1178.6	1247.1	1334.8
155°	1198.8	1246.1	1317.9	1392.9
157.5°	1262.4	1310.7	1379.2	1444.8
160°	1301.6	1353.8	1415.7	1476.1
162.5°	1345.9	1394.2	1448.4	1502.2
165°	1410.8	1450.0	1494.0	1539.7
167.5°	1465.3	1497.9	1532.5	1568.1
170°	1500.6	1526.6	1556.0	1583.7
172.5°	1530.6	1551.4	1573.0	1596.8
175°	1570.7	1582.1	1595.2	1609.8
177.5°	1601.7	1605.6	1609.5	1616.0
180°	1614.7	1614.7	1614.7	1614.7



TEST NUMBER: P1427636

CATALOG NUMBER: SQ2W-BBN-K-125U-125D-L930-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00