

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435823

Luminaire Tested: SQ2W-FA-K-100U-100D-L830-UNV-STD-W-WM-4

Issue Date: 3/24/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1435823  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2502-345-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/24/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-FA-K-100U-100D-L830-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - FROSTED CONTINUOUS ASYMMETRIC ROLL LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8616.9 lumens  
Efficiency: N/A  
Efficacy: 121.9 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.23 / 1.34  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 70.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1435823

CATALOG NUMBER: SQ2W-FA-K-100U-100D-L830-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1435823

CATALOG NUMBER: SQ2W-FA-K-100U-100D-L830-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49				49
1	98	93	90	86	90	86	83	80	73	71	68	61	59	57	49	48	47				42	
2	89	82	76	70	82	75	70	66	64	60	57	53	50	48	43	41	40				35	
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	38	36	34				30	
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29				25	
5	68	57	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25				22	
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22				19	
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20				17	
8	54	42	34	28	50	39	32	27	33	28	24	28	24	21	23	20	18				15	
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	22	18	16				14	
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	14				13	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	27560	27560	27560	27560
5°	27238	28525	27238	22734
10°	27118	28855	27118	20610
15°	26652	29086	26652	22783
20°	25919	28876	25919	23759
25°	24634	28642	24634	24044
30°	22696	28000	22696	24300
35°	20083	27385	20083	23865
40°	17291	26634	17291	24124
45°	17070	25683	17070	24171
50°	16287	24430	16287	24264
55°	16203	22536	16203	24025
60°	14528	20082	14528	23928
65°	12386	17692	12386	23255
70°	9994	14993	9994	21550
75°	8665	12383	8665	19812
80°	7382	9223	7382	15992
85°	4909	4909	4909	9800

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 26489 cd/sqm



TEST NUMBER: P1435823

CATALOG NUMBER: SQ2W-FA-K-100U-100D-L830-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	153.6	1.8
10°-20°	429.2	5.0
20°-30°	651.8	7.6
30°-40°	765.2	8.9
40°-50°	776.5	9.0
50°-60°	680.2	7.9
60°-70°	482.4	5.6
70°-80°	248.4	2.9
80°-90°	58.3	0.7
90°-100°	119.2	1.4
100°-110°	347.5	4.0
110°-120°	567.1	6.6
120°-130°	719.6	8.4
130°-140°	770.0	8.9
140°-150°	719.0	8.3
150°-160°	591.6	6.9
160°-170°	396.8	4.6
170°-180°	140.9	1.6
0°-30°	1234.5	14.3
0°-40°	1999.7	23.2
0°-60°	3456.4	40.1
0°-90°	4245.5	49.3
90°-120°	1033.7	12.0
90°-150°	3242.2	37.6
90°-180°	4371.0	50.7
0°-180°	8616.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1707	1707	1707	1707	1707	
5°	1681	1760	1681	1403	1681	160
15°	1594	1740	1594	1363	1594	448
25°	1383	1608	1383	1350	1383	631
35°	1019	1389	1019	1211	1019	635
45°	748	1125	748	1059	748	572
55°	576	801	576	854	576	498
65°	324	463	324	609	324	324
75°	139	198	139	318	139	150
85°	26	26	26	53	26	33
90°	4	33	4	65	4	4
95°	47	35	47	204	47	57
105°	221	354	221	487	221	235
115°	423	587	423	723	423	417
125°	626	930	626	886	626	560
135°	851	1217	851	982	851	658
145°	1087	1403	1087	1003	1087	680
155°	1292	1524	1292	1040	1292	594
165°	1428	1589	1428	1198	1428	402
175°	1493	1556	1493	1405	1493	142
180°	1497	1497	1497	1497	1497	



TEST NUMBER: P1435823

CATALOG NUMBER: SQ2W-FA-K-100U-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1707.0	1707.0	1707.0	1707.0	1707.0	1707.0	1707.0	1707.0	1707.0	1707.0	1707.0
2.5°	1696.4	1708.2	1720.0	1722.9	1722.9	1722.9	1722.9	1722.9	1722.9	1722.9	1722.9
5°	1680.6	1701.1	1721.7	1731.3	1737.2	1741.6	1744.5	1748.2	1754.1	1760.0	1754.1
7.5°	1664.7	1692.3	1720.0	1733.5	1742.3	1749.4	1754.7	1759.4	1762.3	1765.2	1762.3
10°	1654.1	1686.4	1718.8	1733.5	1742.3	1748.2	1751.1	1754.1	1757.0	1760.0	1757.0
12.5°	1638.2	1672.9	1707.6	1724.7	1735.8	1742.9	1745.8	1748.8	1751.7	1754.7	1751.7
15°	1594.5	1641.6	1688.6	1707.0	1715.8	1723.2	1729.1	1734.2	1737.2	1740.1	1737.2
17.5°	1540.3	1597.3	1654.4	1677.5	1689.2	1697.8	1703.1	1707.6	1710.0	1712.3	1710.0
20°	1508.5	1570.3	1632.0	1656.3	1668.1	1675.4	1678.4	1680.6	1680.6	1680.6	1680.6
22.5°	1466.2	1535.0	1603.8	1629.8	1641.6	1647.8	1648.4	1649.4	1651.7	1654.1	1651.7
25°	1382.8	1462.2	1541.6	1574.7	1592.3	1599.7	1596.7	1596.0	1601.9	1607.8	1601.9
27.5°	1280.9	1380.9	1480.9	1514.7	1526.5	1533.8	1536.8	1539.0	1539.0	1539.0	1539.0
30°	1217.4	1329.2	1440.9	1477.7	1489.4	1496.8	1499.7	1501.9	1501.9	1501.9	1501.9
32.5°	1138.0	1270.9	1403.8	1444.1	1453.5	1458.5	1459.1	1459.6	1459.6	1459.6	1459.6
35°	1018.9	1180.7	1342.4	1387.2	1393.1	1396.1	1396.1	1395.3	1392.4	1389.4	1392.4
37.5°	899.8	1083.3	1266.8	1319.3	1328.1	1330.5	1326.4	1322.5	1319.6	1316.7	1319.6
40°	820.4	1020.4	1220.4	1277.0	1285.8	1285.8	1277.0	1269.6	1266.7	1263.7	1266.7
42.5°	778.1	975.7	1173.3	1229.3	1238.1	1237.0	1225.8	1216.7	1213.7	1210.8	1213.7
45°	747.6	924.1	1100.5	1151.2	1160.1	1158.6	1146.8	1136.5	1130.7	1124.8	1130.7
47.5°	701.3	856.6	1011.9	1061.7	1076.4	1074.9	1057.3	1042.6	1036.7	1030.8	1036.7
50°	648.4	801.3	954.2	1003.5	1018.2	1016.7	999.1	984.4	978.5	972.6	978.5
52.5°	611.4	754.9	898.4	943.5	955.8	952.0	932.0	915.6	909.7	903.8	909.7
55°	575.6	696.2	816.8	853.5	862.3	856.5	835.9	818.2	809.4	800.6	809.4
57.5°	492.3	606.9	721.6	757.4	766.8	759.7	736.2	716.0	706.0	696.0	706.0
60°	449.9	552.8	655.8	690.3	702.1	696.2	672.7	651.3	636.6	621.9	636.6
62.5°	402.3	493.4	584.6	619.7	636.2	632.7	609.1	587.8	573.1	558.4	573.1
65°	324.2	403.6	483.0	518.3	538.9	537.4	513.9	492.6	477.8	463.1	477.8
67.5°	254.1	322.3	390.5	425.2	448.7	447.6	421.7	399.3	387.6	375.8	387.6
70°	211.7	270.5	329.3	361.7	385.2	385.2	361.7	341.1	329.3	317.6	329.3
72.5°	185.3	230.0	274.7	305.2	331.1	331.1	305.2	283.5	274.1	264.7	274.1
75°	138.9	165.4	191.9	220.5	250.0	252.9	229.4	210.3	204.4	198.5	204.4
77.5°	100.6	112.9	125.3	147.8	173.6	176.6	156.6	141.0	138.6	136.3	138.6
80°	79.4	82.3	85.3	103.7	127.2	130.1	112.5	99.2	99.2	99.2	99.2
82.5°	52.9	55.9	58.8	71.9	88.4	90.1	77.2	66.9	64.5	62.2	64.5
85°	26.5	26.5	26.5	30.9	36.8	36.8	30.9	26.5	26.5	26.5	26.5
87.5°	6.2	7.4	8.9	11.9	15.2	15.5	13.1	11.6	11.9	11.9	11.9
90°	4.5	10.6	18.1	24.2	28.7	30.2	30.2	31.8	33.3	33.3	33.3
92.5°	16.6	26.3	26.6	26.6	32.4	35.1	37.5	37.8	39.3	39.3	39.3
95°	46.9	51.4	77.1	75.6	51.4	40.8	34.8	34.8	34.8	34.8	34.8
97.5°	89.5	96.2	100.4	134.6	142.2	137.3	111.9	94.1	84.1	79.5	84.1
100°	127.0	130.1	139.1	140.6	178.4	214.7	196.6	173.9	166.4	161.8	166.4
102.5°	164.5	166.4	180.3	186.6	195.4	216.0	278.9	271.9	266.8	265.9	266.8
105°	220.8	222.3	248.0	260.1	266.2	266.2	264.7	294.9	343.3	353.9	343.3
107.5°	281.0	287.9	318.2	350.5	357.5	359.3	351.5	346.9	345.1	346.3	345.1
110°	322.1	332.7	369.0	409.8	420.4	423.4	420.4	415.9	412.9	412.9	412.9



TEST NUMBER: P1435823

CATALOG NUMBER: SQ2W-FA-K-100U-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	362.0	377.5	418.6	465.5	483.3	492.4	485.7	482.4	479.4	481.8	479.4
115°	423.4	446.1	500.6	549.0	585.3	589.8	588.3	588.3	586.8	586.8	586.8
117.5°	480.3	516.6	577.7	634.0	676.0	688.1	694.1	692.3	690.5	693.5	690.5
120°	520.2	562.6	632.1	695.7	736.5	754.6	760.7	757.7	760.7	757.7	760.7
122.5°	562.6	614.6	682.9	748.9	797.0	817.5	824.8	825.4	826.0	824.2	826.0
125°	626.1	689.6	769.8	837.8	887.7	911.9	918.0	919.5	922.5	930.1	922.5
127.5°	690.2	762.2	850.2	915.8	967.0	996.3	1005.7	1009.0	1015.3	1018.7	1015.3
130°	735.0	816.6	905.9	967.9	1017.8	1049.5	1066.2	1070.7	1078.3	1076.7	1078.3
132.5°	782.2	867.4	957.9	1022.3	1068.6	1102.8	1117.0	1130.0	1132.7	1134.8	1132.7
135°	851.4	943.7	1034.4	1097.9	1141.8	1175.0	1193.2	1205.3	1212.9	1217.4	1212.9
137.5°	924.3	1021.7	1108.8	1165.4	1209.5	1238.3	1258.8	1271.5	1279.4	1283.0	1279.4
140°	973.9	1067.7	1152.4	1211.3	1250.7	1279.4	1297.5	1312.7	1321.7	1321.7	1321.7
142.5°	1021.1	1113.6	1195.9	1254.9	1289.4	1315.7	1335.0	1346.5	1356.8	1356.8	1356.8
145°	1087.3	1179.6	1255.2	1314.2	1342.9	1367.1	1388.3	1397.4	1403.4	1403.4	1403.4
147.5°	1156.6	1238.3	1307.2	1363.8	1388.0	1416.4	1433.0	1440.3	1447.9	1444.5	1447.9
150°	1197.7	1273.3	1339.9	1392.8	1417.0	1444.2	1460.9	1466.9	1474.5	1469.9	1474.5
152.5°	1237.7	1309.6	1370.1	1419.4	1440.0	1467.2	1486.3	1492.3	1497.5	1494.1	1497.5
155°	1291.5	1355.0	1411.0	1456.3	1474.5	1500.2	1518.3	1525.9	1531.9	1524.4	1531.9
157.5°	1339.6	1394.3	1443.0	1484.8	1504.1	1526.2	1543.1	1552.5	1558.6	1555.2	1558.6
160°	1368.6	1418.5	1462.4	1501.7	1519.8	1539.5	1557.7	1568.2	1574.3	1569.8	1574.3
162.5°	1392.8	1437.9	1479.3	1515.0	1530.7	1548.0	1569.8	1579.1	1585.2	1579.4	1585.2
165°	1427.6	1463.9	1500.2	1530.4	1544.0	1557.7	1580.3	1590.9	1595.5	1589.4	1595.5
167.5°	1453.9	1481.7	1511.1	1537.1	1547.1	1560.4	1583.1	1591.8	1597.6	1590.0	1597.6
170°	1468.4	1492.6	1518.3	1539.5	1547.1	1559.2	1581.9	1589.4	1593.9	1586.4	1593.9
172.5°	1480.5	1498.7	1519.5	1538.3	1542.2	1551.9	1573.4	1580.9	1584.3	1577.9	1584.3
175°	1492.6	1503.2	1518.3	1530.4	1528.9	1535.0	1553.1	1559.2	1565.2	1556.1	1565.2
177.5°	1498.4	1503.2	1508.1	1515.3	1510.5	1510.5	1523.8	1527.4	1528.6	1523.8	1528.6
180°	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2



TEST NUMBER: P1435823

CATALOG NUMBER: SQ2W-FA-K-100U-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1707.0	1707.0	1707.0	1707.0	1707.0	1707.0	1707.0	1707.0	1707.0	1707.0	1707.0
2.5°	1722.9	1722.9	1722.9	1722.9	1722.9	1720.0	1708.2	1696.4	1696.4	1696.4	1687.6
5°	1748.2	1744.5	1741.6	1737.2	1731.3	1721.7	1701.1	1680.6	1671.7	1662.9	1625.4
7.5°	1759.4	1754.7	1749.4	1742.3	1733.5	1720.0	1692.3	1664.7	1625.3	1585.9	1502.4
10°	1754.1	1751.1	1748.2	1742.3	1733.5	1718.8	1686.4	1654.1	1574.7	1495.3	1415.9
12.5°	1748.8	1745.8	1742.9	1735.8	1724.7	1707.6	1672.9	1638.2	1525.9	1413.5	1341.8
15°	1734.2	1729.1	1723.2	1715.8	1707.0	1688.6	1641.6	1594.5	1468.1	1341.7	1281.4
17.5°	1707.6	1703.1	1697.8	1689.2	1677.5	1654.4	1597.3	1540.3	1408.0	1275.6	1236.8
20°	1680.6	1678.4	1675.4	1668.1	1656.3	1632.0	1570.3	1508.5	1376.2	1243.9	1226.2
22.5°	1649.4	1648.4	1647.8	1641.6	1629.8	1603.8	1535.0	1466.2	1336.2	1206.2	1206.8
25°	1596.0	1596.7	1599.7	1592.3	1574.7	1541.6	1462.2	1382.8	1268.1	1153.5	1173.3
27.5°	1539.0	1536.8	1533.8	1526.5	1514.7	1480.9	1380.9	1280.9	1190.4	1099.8	1132.7
30°	1501.9	1499.7	1496.8	1489.4	1477.7	1440.9	1329.2	1217.4	1141.0	1064.5	1102.7
32.5°	1459.6	1459.1	1458.5	1453.5	1444.1	1403.8	1270.9	1138.0	1082.7	1027.4	1067.4
35°	1395.3	1396.1	1396.1	1393.1	1387.2	1342.4	1180.7	1018.9	995.4	971.9	1018.9
37.5°	1322.5	1326.4	1330.5	1328.1	1319.3	1266.8	1083.3	899.8	907.5	915.1	972.2
40°	1269.6	1277.0	1285.8	1285.8	1277.0	1220.4	1020.4	820.4	846.9	873.4	935.1
42.5°	1216.7	1225.8	1237.0	1238.1	1229.3	1173.3	975.7	778.1	806.9	835.7	899.8
45°	1136.5	1146.8	1158.6	1160.1	1151.2	1100.5	924.1	747.6	765.3	782.9	844.7
47.5°	1042.6	1057.3	1074.9	1076.4	1061.7	1011.9	856.6	701.3	714.3	727.2	790.4
50°	984.4	999.1	1016.7	1018.2	1003.5	954.2	801.3	648.4	666.0	683.7	749.9
52.5°	915.6	932.0	952.0	955.8	943.5	898.4	754.9	611.4	621.9	632.5	704.0
55°	818.2	835.9	856.5	862.3	853.5	816.8	696.2	575.6	566.8	558.0	630.8
57.5°	716.0	736.2	759.7	766.8	757.4	721.6	606.9	492.3	484.6	477.0	555.8
60°	651.3	672.7	696.2	702.1	690.3	655.8	552.8	449.9	435.2	420.5	502.8
62.5°	587.8	609.1	632.7	636.2	619.7	584.6	493.4	402.3	392.3	382.3	462.3
65°	492.6	513.9	537.4	538.9	518.3	483.0	403.6	324.2	330.1	336.0	408.0
67.5°	399.3	421.7	447.6	448.7	425.2	390.5	322.3	254.1	273.5	292.9	357.7
70°	341.1	361.7	385.2	385.2	361.7	329.3	270.5	211.7	238.2	264.7	324.2
72.5°	283.5	305.2	331.1	331.1	305.2	274.7	230.0	185.3	211.7	238.2	287.2
75°	210.3	229.4	252.9	250.0	220.5	191.9	165.4	138.9	165.4	191.9	229.4
77.5°	141.0	156.6	176.6	173.6	147.8	125.3	112.9	100.6	122.3	144.1	170.3
80°	99.2	112.5	130.1	127.2	103.7	85.3	82.3	79.4	94.1	108.8	127.9
82.5°	66.9	77.2	90.1	88.4	71.9	58.8	55.9	52.9	65.3	77.6	90.9
85°	26.5	30.9	36.8	36.8	30.9	26.5	26.5	26.5	32.3	38.2	44.1
87.5°	11.6	13.1	15.5	15.2	11.9	8.9	7.4	6.2	9.8	13.3	16.0
90°	31.8	30.2	30.2	28.7	24.2	18.1	10.6	4.5	10.6	16.6	27.2
92.5°	37.8	37.5	35.1	32.4	26.6	26.6	26.3	16.6	28.7	40.8	58.7
95°	34.8	34.8	40.8	51.4	75.6	77.1	51.4	46.9	66.5	93.8	118.0
97.5°	94.1	111.9	137.3	142.2	134.6	100.4	96.2	89.5	121.9	148.8	187.8
100°	173.9	196.6	214.7	178.4	140.6	139.1	130.1	127.0	161.8	187.5	225.3
102.5°	271.9	278.9	216.0	195.4	186.6	180.3	166.4	164.5	199.3	234.7	266.5
105°	294.9	264.7	266.2	266.2	260.1	248.0	222.3	220.8	260.1	300.9	340.3
107.5°	346.9	351.5	359.3	357.5	350.5	318.2	287.9	281.0	316.4	365.4	408.6
110°	415.9	420.4	423.4	420.4	409.8	369.0	332.7	322.1	353.9	405.3	452.2



TEST NUMBER: P1435823

CATALOG NUMBER: SQ2W-FA-K-100U-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	482.4	485.7	492.4	483.3	465.5	418.6	377.5	362.0	393.8	446.4	494.5
115°	588.3	588.3	589.8	585.3	549.0	500.6	446.1	423.4	450.7	499.1	552.0
117.5°	692.3	694.1	688.1	676.0	634.0	577.7	516.6	480.3	501.8	552.9	607.3
120°	757.7	760.7	754.6	736.5	695.7	632.1	562.6	520.2	536.9	586.8	641.2
122.5°	825.4	824.8	817.5	797.0	748.9	682.9	614.6	562.6	569.5	615.8	669.0
125°	919.5	918.0	911.9	887.7	837.8	769.8	689.6	626.1	617.0	656.3	710.8
127.5°	1009.0	1005.7	996.3	967.0	915.8	850.2	762.2	690.2	669.9	694.7	744.6
130°	1070.7	1066.2	1049.5	1017.8	967.9	905.9	816.6	735.0	706.2	721.4	765.2
132.5°	1130.0	1117.0	1102.8	1068.6	1022.3	957.9	867.4	782.2	742.5	749.2	783.4
135°	1205.3	1193.2	1175.0	1141.8	1097.9	1034.4	943.7	851.4	797.0	790.9	810.6
137.5°	1271.5	1258.8	1238.3	1209.5	1165.4	1108.8	1021.7	924.3	855.7	835.4	842.9
140°	1312.7	1297.5	1279.4	1250.7	1211.3	1152.4	1067.7	973.9	896.8	868.1	863.5
142.5°	1346.5	1335.0	1315.7	1289.4	1254.9	1195.9	1113.6	1021.1	939.1	901.9	891.3
145°	1397.4	1388.3	1367.1	1342.9	1314.2	1255.2	1179.6	1087.3	1005.7	957.3	934.6
147.5°	1440.3	1433.0	1416.4	1388.0	1363.8	1307.2	1238.3	1156.6	1072.8	1012.9	983.6
150°	1466.9	1460.9	1444.2	1417.0	1392.8	1339.9	1273.3	1197.7	1117.6	1054.1	1016.3
152.5°	1492.3	1486.3	1467.2	1440.0	1419.4	1370.1	1309.6	1237.7	1156.3	1092.8	1053.8
155°	1525.9	1518.3	1500.2	1474.5	1456.3	1411.0	1355.0	1291.5	1221.9	1155.4	1111.5
157.5°	1552.5	1543.1	1526.2	1504.1	1484.8	1443.0	1394.3	1339.6	1278.8	1215.3	1170.5
160°	1568.2	1557.7	1539.5	1519.8	1501.7	1462.4	1418.5	1368.6	1312.7	1255.2	1206.8
162.5°	1579.1	1569.8	1548.0	1530.7	1515.0	1479.3	1437.9	1392.8	1342.9	1292.7	1247.9
165°	1590.9	1580.3	1557.7	1544.0	1530.4	1500.2	1463.9	1427.6	1385.3	1344.4	1308.1
167.5°	1591.8	1583.1	1560.4	1547.1	1537.1	1511.1	1481.7	1453.9	1420.9	1388.9	1358.6
170°	1589.4	1581.9	1559.2	1547.1	1539.5	1518.3	1492.6	1468.4	1442.7	1415.5	1391.3
172.5°	1580.9	1573.4	1551.9	1542.2	1538.3	1519.5	1498.7	1480.5	1458.4	1438.5	1419.1
175°	1559.2	1553.1	1535.0	1528.9	1530.4	1518.3	1503.2	1492.6	1479.0	1466.9	1456.3
177.5°	1527.4	1523.8	1510.5	1510.5	1515.3	1508.1	1503.2	1498.4	1492.3	1488.7	1485.1
180°	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2



TEST NUMBER: P1435823

CATALOG NUMBER: SQ2W-FA-K-100U-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1707.0	1707.0	1707.0	1707.0	1707.0	1707.0	1707.0	1707.0	1707.0	1707.0	1707.0
2.5°	1675.9	1666.4	1659.4	1653.5	1651.1	1648.8	1651.1	1653.5	1659.4	1666.4	1675.9
5°	1578.4	1528.4	1475.4	1432.1	1417.4	1402.7	1417.4	1432.1	1475.4	1528.4	1578.4
7.5°	1404.1	1343.9	1321.5	1303.6	1298.9	1294.2	1298.9	1303.6	1321.5	1343.9	1404.1
10°	1336.5	1288.0	1270.3	1257.1	1257.1	1257.1	1257.1	1257.1	1270.3	1288.0	1336.5
12.5°	1283.6	1253.9	1252.7	1254.8	1266.5	1278.3	1266.5	1254.8	1252.7	1253.9	1283.6
15°	1243.1	1247.6	1294.6	1333.6	1348.3	1363.0	1348.3	1333.6	1294.6	1247.6	1243.1
17.5°	1229.2	1254.5	1312.7	1359.3	1371.1	1382.8	1371.1	1359.3	1312.7	1254.5	1229.2
20°	1246.8	1279.2	1323.3	1359.3	1371.1	1382.8	1371.1	1359.3	1323.3	1279.2	1246.8
22.5°	1250.9	1290.3	1325.0	1354.0	1365.8	1377.5	1365.8	1354.0	1325.0	1290.3	1250.9
25°	1238.0	1285.0	1314.5	1338.0	1343.9	1349.7	1343.9	1338.0	1314.5	1285.0	1238.0
27.5°	1206.8	1258.6	1288.0	1311.1	1315.2	1319.3	1315.2	1311.1	1288.0	1258.6	1206.8
30°	1179.2	1232.1	1261.5	1285.8	1294.6	1303.4	1294.6	1285.8	1261.5	1232.1	1179.2
32.5°	1139.2	1193.3	1229.8	1257.5	1259.3	1261.1	1259.3	1257.5	1229.8	1193.3	1139.2
35°	1089.5	1145.4	1186.5	1216.7	1213.7	1210.8	1213.7	1216.7	1186.5	1145.4	1089.5
37.5°	1045.7	1100.4	1136.2	1164.0	1167.6	1171.1	1167.6	1164.0	1136.2	1100.4	1045.7
40°	1008.6	1064.5	1102.7	1132.9	1138.7	1144.6	1138.7	1132.9	1102.7	1064.5	1008.6
42.5°	975.7	1032.7	1071.0	1101.1	1107.0	1112.9	1107.0	1101.1	1071.0	1032.7	975.7
45°	921.1	980.0	1021.1	1052.7	1055.7	1058.6	1055.7	1052.7	1021.1	980.0	921.1
47.5°	870.4	929.5	967.8	997.2	1000.1	1003.0	1000.1	997.2	967.8	929.5	870.4
50°	832.2	892.5	930.7	960.1	963.0	966.0	963.0	960.1	930.7	892.5	832.2
52.5°	795.7	858.4	891.9	917.8	920.7	923.6	920.7	917.8	891.9	858.4	795.7
55°	730.7	796.9	829.3	853.5	853.5	853.5	853.5	829.3	796.9	730.7	730.7
57.5°	663.4	731.3	759.6	781.6	785.1	788.7	785.1	781.6	759.6	731.3	663.4
60°	617.5	686.6	710.2	729.3	735.2	741.0	735.2	729.3	710.2	686.6	617.5
62.5°	572.2	639.0	662.5	681.0	684.6	688.1	684.6	681.0	662.5	639.0	572.2
65°	502.1	560.9	584.4	602.8	605.8	608.7	605.8	602.8	584.4	560.9	502.1
67.5°	437.7	485.9	502.4	515.3	517.7	520.0	517.7	515.3	502.4	485.9	437.7
70°	394.8	435.9	447.7	456.5	456.5	456.5	456.5	447.7	435.9	394.8	394.8
72.5°	343.6	377.7	389.5	398.9	401.2	403.6	401.2	398.9	389.5	377.7	343.6
75°	270.5	295.5	304.4	311.7	314.6	317.6	314.6	311.7	304.4	295.5	270.5
77.5°	197.9	214.4	219.7	224.4	227.3	230.2	227.3	224.4	219.7	214.4	197.9
80°	148.5	160.3	163.2	166.1	169.1	172.0	169.1	166.1	163.2	160.3	148.5
82.5°	104.4	112.6	115.6	117.9	118.5	119.1	118.5	117.9	115.6	112.6	104.4
85°	50.0	52.9	52.9	52.9	52.9	52.9	52.9	52.9	52.9	52.9	50.0
87.5°	17.5	19.7	21.8	23.0	24.2	23.6	24.2	23.0	21.8	19.7	17.5
90°	34.8	45.4	56.0	62.0	68.1	65.0	68.1	62.0	56.0	45.4	34.8
92.5°	69.9	87.7	100.7	111.6	116.4	115.8	116.4	111.6	100.7	87.7	69.9
95°	140.6	161.8	183.0	198.1	207.2	204.2	207.2	198.1	183.0	161.8	140.6
97.5°	216.9	245.3	268.9	283.1	292.2	298.2	292.2	283.1	268.9	245.3	216.9
100°	267.7	294.9	322.1	338.8	353.9	359.9	353.9	338.8	322.1	294.9	267.7
102.5°	308.8	344.5	374.1	392.0	404.7	410.7	404.7	392.0	374.1	344.5	308.8
105°	376.6	414.4	446.1	468.8	482.4	487.0	482.4	468.8	446.1	414.4	376.6
107.5°	444.3	483.3	512.7	537.8	554.4	564.1	554.4	537.8	512.7	483.3	444.3
110°	497.5	529.3	561.1	583.7	600.4	606.4	600.4	583.7	561.1	529.3	497.5



TEST NUMBER: P1435823

CATALOG NUMBER: SQ2W-FA-K-100U-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	542.3	577.7	609.5	632.1	651.2	659.7	651.2	632.1	609.5	577.7	542.3
115°	604.9	651.8	680.5	701.7	715.3	722.9	715.3	701.7	680.5	651.8	604.9
117.5°	656.9	705.9	737.4	753.7	760.1	765.5	760.1	753.7	737.4	705.9	656.9
120°	689.6	735.0	771.3	792.4	800.0	803.0	800.0	792.4	771.3	735.0	689.6
122.5°	719.8	762.8	797.9	823.9	836.3	839.3	836.3	823.9	797.9	762.8	719.8
125°	762.2	803.0	839.3	865.0	878.6	886.2	878.6	865.0	839.3	803.0	762.2
127.5°	799.1	843.3	876.5	899.8	913.1	919.2	913.1	899.8	876.5	843.3	799.1
130°	819.7	865.0	898.3	924.0	936.1	942.2	936.1	924.0	898.3	865.0	819.7
132.5°	835.4	883.2	917.7	940.9	954.3	960.3	954.3	940.9	917.7	883.2	835.4
135°	854.4	904.3	940.6	963.3	975.4	981.5	975.4	963.3	940.6	904.3	854.4
137.5°	871.1	916.4	954.3	978.1	989.0	993.0	989.0	978.1	954.3	916.4	871.1
140°	883.2	922.5	960.3	983.0	995.1	996.6	995.1	983.0	960.3	922.5	883.2
142.5°	898.9	929.8	962.7	985.4	997.5	1000.2	997.5	985.4	962.7	929.8	898.9
145°	927.0	945.2	967.9	989.0	999.6	1002.6	999.6	989.0	967.9	945.2	927.0
147.5°	962.4	968.2	980.0	993.9	1004.2	1006.3	1004.2	993.9	980.0	968.2	962.4
150°	989.0	987.5	992.1	1001.1	1010.2	1008.7	1010.2	1001.1	992.1	987.5	989.0
152.5°	1019.3	1010.5	1010.2	1014.4	1018.7	1018.4	1018.7	1014.4	1010.2	1010.5	1019.3
155°	1070.7	1054.1	1045.0	1042.0	1042.0	1040.5	1042.0	1042.0	1045.0	1054.1	1070.7
157.5°	1127.3	1104.0	1090.4	1083.1	1081.0	1077.7	1081.0	1083.1	1090.4	1104.0	1127.3
160°	1166.0	1140.3	1126.7	1114.6	1110.0	1105.5	1110.0	1114.6	1126.7	1140.3	1166.0
162.5°	1202.3	1177.8	1162.9	1152.1	1147.5	1140.6	1147.5	1152.1	1162.9	1177.8	1202.3
165°	1261.2	1235.5	1218.9	1209.8	1203.8	1197.7	1203.8	1209.8	1218.9	1235.5	1261.2
167.5°	1320.2	1292.1	1281.2	1270.9	1265.2	1254.3	1265.2	1270.9	1281.2	1292.1	1320.2
170°	1356.5	1330.8	1324.8	1315.7	1305.1	1293.0	1305.1	1315.7	1324.8	1330.8	1356.5
172.5°	1388.0	1370.7	1364.7	1355.6	1352.3	1342.6	1352.3	1355.6	1364.7	1370.7	1388.0
175°	1433.6	1420.0	1420.0	1418.5	1414.0	1404.9	1414.0	1418.5	1420.0	1420.0	1433.6
177.5°	1471.8	1464.5	1469.3	1469.3	1468.1	1459.7	1468.1	1469.3	1469.3	1464.5	1471.8
180°	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2



TEST NUMBER: P1435823

CATALOG NUMBER: SQ2W-FA-K-100U-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	1707.0	1707.0	1707.0	1707.0
2.5°	1687.6	1696.4	1696.4	1696.4
5°	1625.4	1662.9	1671.7	1680.6
7.5°	1502.4	1585.9	1625.3	1664.7
10°	1415.9	1495.3	1574.7	1654.1
12.5°	1341.8	1413.5	1525.9	1638.2
15°	1281.4	1341.7	1468.1	1594.5
17.5°	1236.8	1275.6	1408.0	1540.3
20°	1226.2	1243.9	1376.2	1508.5
22.5°	1206.8	1206.2	1336.2	1466.2
25°	1173.3	1153.5	1268.1	1382.8
27.5°	1132.7	1099.8	1190.4	1280.9
30°	1102.7	1064.5	1141.0	1217.4
32.5°	1067.4	1027.4	1082.7	1138.0
35°	1018.9	971.9	995.4	1018.9
37.5°	972.2	915.1	907.5	899.8
40°	935.1	873.4	846.9	820.4
42.5°	899.8	835.7	806.9	778.1
45°	844.7	782.9	765.3	747.6
47.5°	790.4	727.2	714.3	701.3
50°	749.9	683.7	666.0	648.4
52.5°	704.0	632.5	621.9	611.4
55°	630.8	558.0	566.8	575.6
57.5°	555.8	477.0	484.6	492.3
60°	502.8	420.5	435.2	449.9
62.5°	462.3	382.3	392.3	402.3
65°	408.0	336.0	330.1	324.2
67.5°	357.7	292.9	273.5	254.1
70°	324.2	264.7	238.2	211.7
72.5°	287.2	238.2	211.7	185.3
75°	229.4	191.9	165.4	138.9
77.5°	170.3	144.1	122.3	100.6
80°	127.9	108.8	94.1	79.4
82.5°	90.9	77.6	65.3	52.9
85°	44.1	38.2	32.3	26.5
87.5°	16.0	13.3	9.8	6.2
90°	27.2	16.6	10.6	4.5
92.5°	58.7	40.8	28.7	16.6
95°	118.0	93.8	66.5	46.9
97.5°	187.8	148.8	121.9	89.5
100°	225.3	187.5	161.8	127.0
102.5°	266.5	234.7	199.3	164.5
105°	340.3	300.9	260.1	220.8
107.5°	408.6	365.4	316.4	281.0
110°	452.2	405.3	353.9	322.1

TEST NUMBER: P1435823

CATALOG NUMBER: SQ2W-FA-K-100U-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	494.5	446.4	393.8	362.0
115°	552.0	499.1	450.7	423.4
117.5°	607.3	552.9	501.8	480.3
120°	641.2	586.8	536.9	520.2
122.5°	669.0	615.8	569.5	562.6
125°	710.8	656.3	617.0	626.1
127.5°	744.6	694.7	669.9	690.2
130°	765.2	721.4	706.2	735.0
132.5°	783.4	749.2	742.5	782.2
135°	810.6	790.9	797.0	851.4
137.5°	842.9	835.4	855.7	924.3
140°	863.5	868.1	896.8	973.9
142.5°	891.3	901.9	939.1	1021.1
145°	934.6	957.3	1005.7	1087.3
147.5°	983.6	1012.9	1072.8	1156.6
150°	1016.3	1054.1	1117.6	1197.7
152.5°	1053.8	1092.8	1156.3	1237.7
155°	1111.5	1155.4	1221.9	1291.5
157.5°	1170.5	1215.3	1278.8	1339.6
160°	1206.8	1255.2	1312.7	1368.6
162.5°	1247.9	1292.7	1342.9	1392.8
165°	1308.1	1344.4	1385.3	1427.6
167.5°	1358.6	1388.9	1420.9	1453.9
170°	1391.3	1415.5	1442.7	1468.4
172.5°	1419.1	1438.5	1458.4	1480.5
175°	1456.3	1466.9	1479.0	1492.6
177.5°	1485.1	1488.7	1492.3	1498.4
180°	1497.2	1497.2	1497.2	1497.2



TEST NUMBER: P1435823  
 CATALOG NUMBER: SQ2W-FA-K-100U-100D-L830-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.83	18.68	18.79	19.66	20.94	19.03	19.88	19.99	20.86	22.14
	3H	18.92	19.68	19.89	20.67	21.97	20.27	21.04	21.25	22.02	23.33
	4H	19.27	19.99	20.26	20.99	22.30	20.66	21.39	21.65	22.38	23.69
	6H	19.43	20.10	20.43	21.09	22.42	20.82	21.49	21.82	22.48	23.81
	8H	19.47	20.10	20.47	21.11	22.43	20.85	21.48	21.85	22.49	23.82
	12H	19.46	20.07	20.47	21.07	22.42	20.83	21.43	21.84	22.44	23.79
4H	2H	18.70	19.42	19.69	20.41	21.72	19.61	20.34	20.61	21.33	22.64
	3H	20.09	20.69	21.09	21.71	23.03	21.08	21.68	22.08	22.70	24.02
	4H	20.54	21.09	21.55	22.10	23.45	21.55	22.10	22.56	23.11	24.46
	6H	20.77	21.24	21.79	22.28	23.63	21.77	22.25	22.80	23.28	24.63
	8H	20.83	21.27	21.85	22.30	23.66	21.82	22.26	22.84	23.29	24.65
	12H	20.83	21.23	21.87	22.27	23.64	21.81	22.21	22.85	23.25	24.62
8H	4H	20.92	21.37	21.95	22.39	23.76	21.75	22.19	22.77	23.22	24.58
	6H	21.27	21.64	22.32	22.71	24.07	22.06	22.42	23.11	23.50	24.85
	8H	21.39	21.71	22.45	22.77	24.15	22.16	22.48	23.21	23.53	24.91
	12H	21.43	21.71	22.49	22.76	24.18	22.17	22.45	23.23	23.50	24.92
12H	4H	20.93	21.33	21.97	22.37	23.74	21.71	22.11	22.76	23.16	24.52
	6H	21.34	21.67	22.40	22.72	24.10	22.08	22.40	23.13	23.46	24.83
	8H	21.49	21.77	22.55	22.82	24.24	22.19	22.47	23.25	23.52	24.95