

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435853

Luminaire Tested: SQ2W-FA-K-125U-125D-L830-UNV-STD-W-WM-4

Issue Date: 3/24/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1435853  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2502-345-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/24/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-FA-K-125U-125D-L830-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - FROSTED CONTINUOUS ASYMMETRIC ROLL LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10828.8 lumens  
Efficiency: N/A  
Efficacy: 116.2 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.23 / 1.34  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 93.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1435853

CATALOG NUMBER: SQ2W-FA-K-125U-125D-L830-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1435853

CATALOG NUMBER: SQ2W-FA-K-125U-125D-L830-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41
2	89	82	75	70	82	75	70	66	64	60	56	53	50	48	43	41	39	35
3	81	72	64	59	74	66	60	55	56	51	47	47	43	40	38	36	34	29
4	74	63	56	50	68	59	52	46	50	45	40	42	38	35	34	31	29	25
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	30	34	29	26	28	25	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	34317	34317	34317	34317
5°	33914	35517	33914	28306
10°	33766	35927	33766	25662
15°	33188	36217	33188	28367
20°	32274	35953	32274	29584
25°	30673	35663	30673	29939
30°	28261	34865	28261	30258
35°	25006	34100	25006	29715
40°	21532	33164	21532	30038
45°	21255	31978	21255	30097
50°	20280	30418	20280	30212
55°	20174	28059	20174	29917
60°	18089	25006	18089	29795
65°	15423	22032	15423	28955
70°	12444	18665	12444	26832
75°	10792	15421	10792	24666
80°	9196	11492	9196	19916
85°	6113	6113	6113	12208

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 32983 cd/sqm



TEST NUMBER: P1435853

CATALOG NUMBER: SQ2W-FA-K-125U-125D-L830-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	191.2	1.8
10°-20°	534.4	4.9
20°-30°	811.5	7.5
30°-40°	952.8	8.8
40°-50°	966.9	8.9
50°-60°	846.9	7.8
60°-70°	600.7	5.5
70°-80°	309.3	2.9
80°-90°	72.7	0.7
90°-100°	151.1	1.4
100°-110°	440.5	4.1
110°-120°	719.0	6.6
120°-130°	912.3	8.4
130°-140°	976.2	9.0
140°-150°	911.5	8.4
150°-160°	750.1	6.9
160°-170°	503.1	4.6
170°-180°	178.6	1.6
0°-30°	1537.1	14.2
0°-40°	2489.9	23.0
0°-60°	4303.7	39.7
0°-90°	5286.4	48.8
90°-120°	1310.6	12.1
90°-150°	4110.6	38.0
90°-180°	5542.0	51.2
0°-180°	10828.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2126	2126	2126	2126	2126	
5°	2092	2191	2092	1746	2092	199
15°	1986	2167	1986	1697	1986	558
25°	1722	2002	1722	1681	1722	786
35°	1269	1730	1269	1508	1269	790
45°	931	1400	931	1318	931	712
55°	717	997	717	1063	717	620
65°	404	577	404	758	404	403
75°	173	247	173	395	173	187
85°	33	33	33	66	33	41
90°	6	42	6	82	6	6
95°	59	44	59	259	59	72
105°	280	449	280	617	280	298
115°	537	744	537	916	537	529
125°	794	1179	794	1124	794	710
135°	1080	1544	1080	1244	1080	834
145°	1379	1779	1379	1271	1379	863
155°	1637	1933	1637	1319	1637	753
165°	1810	2015	1810	1519	1810	510
175°	1892	1973	1892	1781	1892	180
180°	1898	1898	1898	1898	1898	



TEST NUMBER: P1435853

CATALOG NUMBER: SQ2W-FA-K-125U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2125.5	2125.5	2125.5	2125.5	2125.5	2125.5	2125.5	2125.5	2125.5	2125.5	2125.5
2.5°	2112.3	2127.0	2141.6	2145.3	2145.3	2145.3	2145.3	2145.3	2145.3	2145.3	2145.3
5°	2092.5	2118.2	2143.8	2155.7	2163.0	2168.5	2172.2	2176.8	2184.1	2191.4	2184.1
7.5°	2072.8	2107.2	2141.6	2158.5	2169.4	2178.2	2184.8	2190.7	2194.3	2198.0	2194.3
10°	2059.6	2099.9	2140.1	2158.5	2169.4	2176.8	2180.4	2184.1	2187.7	2191.4	2187.7
12.5°	2039.8	2083.0	2126.2	2147.5	2161.4	2170.2	2173.8	2177.5	2181.2	2184.8	2181.2
15°	1985.5	2044.0	2102.6	2125.5	2136.5	2145.6	2153.0	2159.4	2163.0	2166.7	2163.0
17.5°	1917.9	1988.9	2060.0	2088.7	2103.4	2114.0	2120.6	2126.2	2129.2	2132.1	2129.2
20°	1878.4	1955.2	2032.1	2062.3	2077.0	2086.1	2089.8	2092.5	2092.5	2092.5	2092.5
22.5°	1825.6	1911.3	1997.0	2029.4	2044.0	2051.7	2052.5	2053.7	2056.7	2059.6	2056.7
25°	1721.8	1820.7	1919.5	1960.7	1982.7	1991.9	1988.2	1987.3	1994.6	2001.9	1994.6
27.5°	1595.0	1719.4	1843.9	1886.0	1900.7	1909.8	1913.5	1916.2	1916.2	1916.2	1916.2
30°	1515.9	1655.0	1794.1	1839.9	1854.6	1863.7	1867.4	1870.1	1870.1	1870.1	1870.1
32.5°	1417.0	1582.5	1748.0	1798.2	1809.9	1816.1	1816.8	1817.4	1817.4	1817.4	1817.4
35°	1268.7	1470.1	1671.5	1727.3	1734.6	1738.3	1738.3	1737.4	1733.7	1730.1	1733.7
37.5°	1120.4	1348.9	1577.4	1642.7	1653.7	1656.6	1651.5	1646.8	1643.1	1639.4	1643.1
40°	1021.6	1270.5	1519.5	1590.0	1601.0	1601.0	1590.0	1580.9	1577.2	1573.5	1577.2
42.5°	968.8	1214.9	1460.9	1530.7	1541.7	1540.2	1526.3	1514.9	1511.3	1507.6	1511.3
45°	930.9	1150.6	1370.3	1433.5	1444.5	1442.6	1428.0	1415.2	1407.8	1400.5	1407.8
47.5°	873.3	1066.6	1259.9	1322.0	1340.3	1338.5	1316.5	1298.2	1290.9	1283.5	1290.9
50°	807.4	997.8	1188.2	1249.5	1267.8	1266.0	1244.0	1225.7	1218.4	1211.0	1218.4
52.5°	761.2	939.9	1118.6	1174.8	1190.2	1185.4	1160.5	1140.0	1132.7	1125.4	1132.7
55°	716.7	866.9	1017.0	1062.8	1073.7	1066.4	1040.8	1018.8	1007.8	996.8	1007.8
57.5°	612.9	755.7	898.5	943.0	954.7	945.9	916.7	891.6	879.1	866.7	879.1
60°	560.2	688.4	816.5	859.5	874.2	866.9	837.6	811.0	792.7	774.4	792.7
62.5°	500.9	614.4	727.9	771.7	792.2	787.8	758.5	731.9	713.6	695.3	713.6
65°	403.7	502.5	601.4	645.3	671.0	669.1	639.8	613.3	595.0	576.7	595.0
67.5°	316.4	401.3	486.2	529.5	558.7	557.3	525.1	497.2	482.6	467.9	482.6
70°	263.6	336.9	410.1	450.4	479.7	479.7	450.4	424.7	410.1	395.4	410.1
72.5°	230.7	286.3	342.0	380.1	412.3	412.3	380.1	353.0	341.3	329.5	341.3
75°	173.0	206.0	238.9	274.6	311.2	314.9	285.6	261.8	254.5	247.2	254.5
77.5°	125.2	140.6	156.0	184.0	216.2	219.9	195.0	175.6	172.6	169.7	172.6
80°	98.9	102.5	106.2	129.1	158.4	162.0	140.1	123.6	123.6	123.6	123.6
82.5°	65.9	69.6	73.2	89.5	110.0	112.2	96.1	83.3	80.4	77.4	80.4
85°	33.0	33.0	33.0	38.4	45.8	45.8	38.4	33.0	33.0	33.0	33.0
87.5°	7.7	9.3	11.2	14.9	19.0	19.4	16.5	14.6	15.0	15.0	15.0
90°	5.8	13.4	23.0	30.7	36.4	38.3	38.3	40.3	42.2	42.2	42.2
92.5°	21.1	33.4	33.7	33.7	41.0	44.5	47.6	47.9	49.9	49.9	49.9
95°	59.4	65.2	97.8	95.9	65.2	51.8	44.1	44.1	44.1	44.1	44.1
97.5°	113.5	121.9	127.3	170.6	180.2	174.1	141.9	119.3	106.6	100.9	106.6
100°	161.1	164.9	176.4	178.3	226.2	272.3	249.3	220.5	210.9	205.2	210.9
102.5°	208.6	210.9	228.5	236.6	247.7	273.8	353.6	344.7	338.2	337.1	338.2
105°	279.9	281.9	314.4	329.8	337.5	337.5	335.5	373.9	435.2	448.7	435.2
107.5°	356.2	365.1	403.4	444.4	453.3	455.6	445.6	439.8	437.5	439.1	437.5
110°	408.4	421.8	467.8	519.6	533.0	536.9	533.0	527.3	523.4	523.4	523.4



TEST NUMBER: P1435853

CATALOG NUMBER: SQ2W-FA-K-125U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	459.0	478.6	530.7	590.2	612.8	624.3	615.9	611.6	607.8	610.9	607.8
115°	536.9	565.6	634.6	696.0	742.0	747.8	745.9	745.9	743.9	743.9	743.9
117.5°	609.0	655.0	732.4	803.8	857.1	872.4	880.1	877.8	875.5	879.3	875.5
120°	659.6	713.3	801.5	882.0	933.8	956.8	964.4	960.6	964.4	960.6	964.4
122.5°	713.3	779.2	865.9	949.5	1010.5	1036.5	1045.7	1046.5	1047.3	1045.0	1047.3
125°	793.8	874.3	975.9	1062.2	1125.5	1156.2	1163.8	1165.8	1169.6	1179.2	1169.6
127.5°	875.1	966.4	1077.9	1161.2	1226.0	1263.2	1275.0	1279.3	1287.3	1291.5	1287.3
130°	931.8	1035.4	1148.5	1227.1	1290.4	1330.7	1351.7	1357.5	1367.1	1365.2	1367.1
132.5°	991.7	1099.8	1214.5	1296.1	1354.8	1398.1	1416.2	1432.7	1436.1	1438.8	1436.1
135°	1079.5	1196.4	1311.5	1392.0	1447.6	1489.8	1512.8	1528.1	1537.7	1543.5	1537.7
137.5°	1171.9	1295.4	1405.8	1477.5	1533.5	1569.9	1596.0	1612.1	1622.1	1626.7	1622.1
140°	1234.8	1353.7	1461.0	1535.8	1585.7	1622.1	1645.1	1664.3	1675.8	1675.8	1675.8
142.5°	1294.6	1411.9	1516.3	1591.0	1634.7	1668.1	1692.6	1707.2	1720.3	1720.3	1720.3
145°	1378.6	1495.5	1591.4	1666.2	1702.6	1733.3	1760.1	1771.6	1779.3	1779.3	1779.3
147.5°	1466.4	1569.9	1657.4	1729.1	1759.8	1795.8	1816.9	1826.1	1835.7	1831.5	1835.7
150°	1518.6	1614.4	1698.8	1765.9	1796.6	1831.1	1852.2	1859.8	1869.4	1863.7	1869.4
152.5°	1569.2	1660.4	1737.1	1799.6	1825.7	1860.2	1884.4	1892.1	1898.6	1894.4	1898.6
155°	1637.4	1718.0	1788.9	1846.4	1869.4	1902.0	1925.0	1934.6	1942.3	1932.7	1942.3
157.5°	1698.4	1767.8	1829.5	1882.5	1907.0	1935.0	1956.5	1968.4	1976.0	1971.8	1976.0
160°	1735.2	1798.5	1854.1	1903.9	1927.0	1951.9	1974.9	1988.3	1996.0	1990.2	1996.0
162.5°	1765.9	1823.0	1875.6	1920.8	1940.8	1962.6	1990.2	2002.1	2009.8	2002.5	2009.8
165°	1810.0	1856.0	1902.0	1940.4	1957.6	1974.9	2003.6	2017.1	2022.8	2015.1	2022.8
167.5°	1843.4	1878.6	1915.8	1948.8	1961.5	1978.3	2007.1	2018.2	2025.5	2015.9	2025.5
170°	1861.8	1892.4	1925.0	1951.9	1961.5	1976.8	2005.6	2015.1	2020.9	2011.3	2020.9
172.5°	1877.1	1900.1	1926.6	1950.3	1955.3	1967.6	1994.8	2004.4	2008.6	2000.6	2008.6
175°	1892.4	1905.9	1925.0	1940.4	1938.5	1946.1	1969.1	1976.8	1984.5	1973.0	1984.5
177.5°	1899.7	1905.9	1912.0	1921.2	1915.1	1915.1	1931.9	1936.5	1938.1	1931.9	1938.1
180°	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2



TEST NUMBER: P1435853

CATALOG NUMBER: SQ2W-FA-K-125U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2125.5	2125.5	2125.5	2125.5	2125.5	2125.5	2125.5	2125.5	2125.5	2125.5	2125.5
2.5°	2145.3	2145.3	2145.3	2145.3	2145.3	2141.6	2127.0	2112.3	2112.3	2112.3	2101.3
5°	2176.8	2172.2	2168.5	2163.0	2155.7	2143.8	2118.2	2092.5	2081.6	2070.6	2023.9
7.5°	2190.7	2184.8	2178.2	2169.4	2158.5	2141.6	2107.2	2072.8	2023.7	1974.6	1870.7
10°	2184.1	2180.4	2176.8	2169.4	2158.5	2140.1	2099.9	2059.6	1960.7	1861.9	1763.0
12.5°	2177.5	2173.8	2170.2	2161.4	2147.5	2126.2	2083.0	2039.8	1900.0	1760.1	1670.7
15°	2159.4	2153.0	2145.6	2136.5	2125.5	2102.6	2044.0	1985.5	1828.0	1670.6	1595.5
17.5°	2126.2	2120.6	2114.0	2103.4	2088.7	2060.0	1988.9	1917.9	1753.1	1588.4	1540.0
20°	2092.5	2089.8	2086.1	2077.0	2062.3	2032.1	1955.2	1878.4	1713.6	1548.8	1526.8
22.5°	2053.7	2052.5	2051.7	2044.0	2029.4	1997.0	1911.3	1825.6	1663.8	1501.9	1502.7
25°	1987.3	1988.2	1991.9	1982.7	1960.7	1919.5	1820.7	1721.8	1579.0	1436.2	1460.9
27.5°	1916.2	1913.5	1909.8	1900.7	1886.0	1843.9	1719.4	1595.0	1482.2	1369.4	1410.4
30°	1870.1	1867.4	1863.7	1854.6	1839.9	1794.1	1655.0	1515.9	1420.7	1325.5	1373.1
32.5°	1817.4	1816.8	1816.1	1809.9	1798.2	1748.0	1582.5	1417.0	1348.2	1279.3	1329.1
35°	1737.4	1738.3	1738.3	1734.6	1727.3	1671.5	1470.1	1268.7	1239.4	1210.1	1268.7
37.5°	1646.8	1651.5	1656.6	1653.7	1642.7	1577.4	1348.9	1120.4	1129.9	1139.5	1210.5
40°	1580.9	1590.0	1601.0	1601.0	1590.0	1519.5	1270.5	1021.6	1054.5	1087.5	1164.4
42.5°	1514.9	1526.3	1540.2	1541.7	1530.7	1460.9	1214.9	968.8	1004.7	1040.6	1120.4
45°	1415.2	1428.0	1442.6	1444.5	1433.5	1370.3	1150.6	930.9	952.9	974.9	1051.8
47.5°	1298.2	1316.5	1338.5	1340.3	1322.0	1259.9	1066.6	873.3	889.4	905.5	984.2
50°	1225.7	1244.0	1266.0	1267.8	1249.5	1188.2	997.8	807.4	829.3	851.3	933.7
52.5°	1140.0	1160.5	1185.4	1190.2	1174.8	1118.6	939.9	761.2	774.4	787.6	876.6
55°	1018.8	1040.8	1066.4	1073.7	1062.8	1017.0	866.9	716.7	705.8	694.8	785.4
57.5°	891.6	916.7	945.9	954.7	943.0	898.5	755.7	612.9	603.4	593.9	692.0
60°	811.0	837.6	866.9	874.2	859.5	816.5	688.4	560.2	541.9	523.6	626.1
62.5°	731.9	758.5	787.8	792.2	771.7	727.9	614.4	500.9	488.4	476.0	575.6
65°	613.3	639.8	669.1	671.0	645.3	601.4	502.5	403.7	411.0	418.3	508.0
67.5°	497.2	525.1	557.3	558.7	529.5	486.2	401.3	316.4	340.5	364.7	445.4
70°	424.7	450.4	479.7	479.7	450.4	410.1	336.9	263.6	296.6	329.5	403.7
72.5°	353.0	380.1	412.3	412.3	380.1	342.0	286.3	230.7	263.6	296.6	357.5
75°	261.8	285.6	314.9	311.2	274.6	238.9	206.0	173.0	206.0	238.9	285.6
77.5°	175.6	195.0	219.9	216.2	184.0	156.0	140.6	125.2	152.3	179.4	212.0
80°	123.6	140.1	162.0	158.4	129.1	106.2	102.5	98.9	117.2	135.5	159.3
82.5°	83.3	96.1	112.2	110.0	89.5	73.2	69.6	65.9	81.3	96.7	113.1
85°	33.0	38.4	45.8	45.8	38.4	33.0	33.0	33.0	40.3	47.6	54.9
87.5°	14.6	16.5	19.4	19.0	14.9	11.2	9.3	7.7	12.2	16.7	20.1
90°	40.3	38.3	38.3	36.4	30.7	23.0	13.4	5.8	13.4	21.1	34.5
92.5°	47.9	47.6	44.5	41.0	33.7	33.7	33.4	21.1	36.4	51.8	74.4
95°	44.1	44.1	51.8	65.2	95.9	97.8	65.2	59.4	84.4	118.9	149.6
97.5°	119.3	141.9	174.1	180.2	170.6	127.3	121.9	113.5	154.5	188.7	238.1
100°	220.5	249.3	272.3	226.2	178.3	176.4	164.9	161.1	205.2	237.8	285.7
102.5°	344.7	353.6	273.8	247.7	236.6	228.5	210.9	208.6	252.7	297.6	337.8
105°	373.9	335.5	337.5	337.5	329.8	314.4	281.9	279.9	329.8	381.6	431.4
107.5°	439.8	445.6	455.6	453.3	444.4	403.4	365.1	356.2	401.1	463.2	518.1
110°	527.3	533.0	536.9	533.0	519.6	467.8	421.8	408.4	448.7	513.9	573.3



TEST NUMBER: P1435853

CATALOG NUMBER: SQ2W-FA-K-125U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	611.6	615.9	624.3	612.8	590.2	530.7	478.6	459.0	499.3	566.0	627.0
115°	745.9	745.9	747.8	742.0	696.0	634.6	565.6	536.9	571.4	632.7	699.8
117.5°	877.8	880.1	872.4	857.1	803.8	732.4	655.0	609.0	636.2	701.0	770.0
120°	960.6	964.4	956.8	933.8	882.0	801.5	713.3	659.6	680.7	743.9	813.0
122.5°	1046.5	1045.7	1036.5	1010.5	949.5	865.9	779.2	713.3	722.1	780.8	848.2
125°	1165.8	1163.8	1156.2	1125.5	1062.2	975.9	874.3	793.8	782.3	832.1	901.2
127.5°	1279.3	1275.0	1263.2	1226.0	1161.2	1077.9	966.4	875.1	849.4	880.8	944.1
130°	1357.5	1351.7	1330.7	1290.4	1227.1	1148.5	1035.4	931.8	895.4	914.6	970.2
132.5°	1432.7	1416.2	1398.1	1354.8	1296.1	1214.5	1099.8	991.7	941.4	949.9	993.2
135°	1528.1	1512.8	1489.8	1447.6	1392.0	1311.5	1196.4	1079.5	1010.5	1002.8	1027.7
137.5°	1612.1	1596.0	1569.9	1533.5	1477.5	1405.8	1295.4	1171.9	1084.8	1059.2	1068.7
140°	1664.3	1645.1	1622.1	1585.7	1535.8	1461.0	1353.7	1234.8	1137.0	1100.6	1094.8
142.5°	1707.2	1692.6	1668.1	1634.7	1591.0	1516.3	1411.9	1294.6	1190.7	1143.5	1130.1
145°	1771.6	1760.1	1733.3	1702.6	1666.2	1591.4	1495.5	1378.6	1275.0	1213.7	1184.9
147.5°	1826.1	1816.9	1795.8	1759.8	1729.1	1657.4	1569.9	1466.4	1360.2	1284.3	1247.1
150°	1859.8	1852.2	1831.1	1796.6	1765.9	1698.8	1614.4	1518.6	1416.9	1336.4	1288.5
152.5°	1892.1	1884.4	1860.2	1825.7	1799.6	1737.1	1660.4	1569.2	1466.0	1385.5	1336.0
155°	1934.6	1925.0	1902.0	1869.4	1846.4	1788.9	1718.0	1637.4	1549.2	1464.9	1409.3
157.5°	1968.4	1956.5	1935.0	1907.0	1882.5	1829.5	1767.8	1698.4	1621.3	1540.8	1484.0
160°	1988.3	1974.9	1951.9	1927.0	1903.9	1854.1	1798.5	1735.2	1664.3	1591.4	1530.1
162.5°	2002.1	1990.2	1962.6	1940.8	1920.8	1875.6	1823.0	1765.9	1702.6	1639.0	1582.2
165°	2017.1	2003.6	1974.9	1957.6	1940.4	1902.0	1856.0	1810.0	1756.3	1704.5	1658.5
167.5°	2018.2	2007.1	1978.3	1961.5	1948.8	1915.8	1878.6	1843.4	1801.6	1760.9	1722.6
170°	2015.1	2005.6	1976.8	1961.5	1951.9	1925.0	1892.4	1861.8	1829.2	1794.7	1764.0
172.5°	2004.4	1994.8	1967.6	1955.3	1950.3	1926.6	1900.1	1877.1	1849.1	1823.8	1799.3
175°	1976.8	1969.1	1946.1	1938.5	1940.4	1925.0	1905.9	1892.4	1875.2	1859.8	1846.4
177.5°	1936.5	1931.9	1915.1	1915.1	1921.2	1912.0	1905.9	1899.7	1892.1	1887.5	1882.9
180°	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2



TEST NUMBER: P1435853

CATALOG NUMBER: SQ2W-FA-K-125U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2125.5	2125.5	2125.5	2125.5	2125.5	2125.5	2125.5	2125.5	2125.5	2125.5	2125.5
2.5°	2086.7	2075.0	2066.2	2058.9	2055.9	2053.0	2055.9	2058.9	2066.2	2075.0	2086.7
5°	1965.3	1903.1	1837.2	1783.2	1764.8	1746.5	1764.8	1783.2	1837.2	1903.1	1965.3
7.5°	1748.4	1673.3	1645.5	1623.1	1617.3	1611.4	1617.3	1623.1	1645.5	1673.3	1748.4
10°	1664.2	1603.7	1581.8	1565.3	1565.3	1565.3	1565.3	1565.3	1581.8	1603.7	1664.2
12.5°	1598.2	1561.3	1559.8	1562.4	1577.0	1591.7	1577.0	1562.4	1559.8	1561.3	1598.2
15°	1547.9	1553.4	1612.0	1660.5	1678.8	1697.1	1678.8	1660.5	1612.0	1553.4	1547.9
17.5°	1530.5	1562.0	1634.5	1692.5	1707.2	1721.8	1707.2	1692.5	1634.5	1562.0	1530.5
20°	1552.5	1592.8	1647.7	1692.5	1707.2	1721.8	1707.2	1692.5	1647.7	1592.8	1552.5
22.5°	1557.6	1606.7	1649.9	1685.9	1700.6	1715.2	1700.6	1685.9	1649.9	1606.7	1557.6
25°	1541.5	1600.1	1636.7	1666.0	1673.3	1680.6	1673.3	1666.0	1636.7	1600.1	1541.5
27.5°	1502.7	1567.1	1603.7	1632.5	1637.6	1642.7	1637.6	1632.5	1603.7	1567.1	1502.7
30°	1468.3	1534.2	1570.8	1601.0	1612.0	1623.0	1612.0	1601.0	1570.8	1534.2	1468.3
32.5°	1418.5	1485.8	1531.2	1565.8	1568.0	1570.2	1568.0	1565.8	1531.2	1485.8	1418.5
35°	1356.6	1426.2	1477.4	1514.9	1511.3	1507.6	1511.3	1514.9	1477.4	1426.2	1356.6
37.5°	1302.0	1370.1	1414.8	1449.4	1453.8	1458.2	1453.8	1449.4	1414.8	1370.1	1302.0
40°	1255.9	1325.5	1373.1	1410.6	1417.9	1425.2	1417.9	1410.6	1373.1	1325.5	1255.9
42.5°	1214.9	1285.9	1333.5	1371.1	1378.4	1385.7	1378.4	1371.1	1333.5	1285.9	1214.9
45°	1147.0	1220.2	1271.5	1310.8	1314.5	1318.1	1314.5	1310.8	1271.5	1220.2	1147.0
47.5°	1083.8	1157.4	1205.0	1241.6	1245.3	1248.9	1245.3	1241.6	1205.0	1157.4	1083.8
50°	1036.2	1111.3	1158.9	1195.5	1199.1	1202.8	1199.1	1195.5	1158.9	1111.3	1036.2
52.5°	990.8	1068.8	1110.5	1142.8	1146.4	1150.1	1146.4	1142.8	1110.5	1068.8	990.8
55°	909.9	992.3	1032.5	1062.8	1062.8	1062.8	1062.8	1062.8	1032.5	992.3	909.9
57.5°	826.0	910.6	945.8	973.2	977.6	982.0	977.6	973.2	945.8	910.6	826.0
60°	768.9	855.0	884.3	908.1	915.4	922.7	915.4	908.1	884.3	855.0	768.9
62.5°	712.5	795.6	824.9	848.0	852.4	856.8	852.4	848.0	824.9	795.6	712.5
65°	625.2	698.4	727.7	750.6	754.3	757.9	754.3	750.6	727.7	698.4	625.2
67.5°	545.0	605.1	625.6	641.7	644.6	647.5	644.6	641.7	625.6	605.1	545.0
70°	491.6	542.8	557.5	568.4	568.4	568.4	568.4	568.4	557.5	542.8	491.6
72.5°	427.8	470.3	485.0	496.7	499.6	502.5	499.6	496.7	485.0	470.3	427.8
75°	336.9	368.0	379.0	388.1	391.8	395.4	391.8	388.1	379.0	368.0	336.9
77.5°	246.4	266.9	273.5	279.4	283.0	286.7	283.0	279.4	273.5	266.9	246.4
80°	184.9	199.6	203.2	206.9	210.5	214.2	210.5	206.9	203.2	199.6	184.9
82.5°	130.0	140.2	143.9	146.8	147.6	148.3	147.6	146.8	143.9	140.2	130.0
85°	62.2	65.9	65.9	65.9	65.9	65.9	65.9	65.9	65.9	65.9	62.2
87.5°	22.0	24.7	27.4	28.9	30.4	29.7	30.4	28.9	27.4	24.7	22.0
90°	44.1	57.5	70.9	78.6	86.3	82.4	86.3	78.6	70.9	57.5	44.1
92.5°	88.6	111.2	127.7	141.5	147.6	146.9	147.6	141.5	127.7	111.2	88.6
95°	178.3	205.2	232.0	251.2	262.7	258.8	262.7	251.2	232.0	205.2	178.3
97.5°	275.0	311.0	340.9	358.9	370.4	378.1	370.4	358.9	340.9	311.0	275.0
100°	339.4	373.9	408.4	429.5	448.7	456.3	448.7	429.5	408.4	373.9	339.4
102.5°	391.5	436.8	474.4	497.0	513.1	520.8	513.1	497.0	474.4	436.8	391.5
105°	477.4	525.4	565.6	594.4	611.6	617.4	611.6	594.4	565.6	525.4	477.4
107.5°	563.3	612.8	650.0	681.8	702.9	715.2	702.9	681.8	650.0	612.8	563.3
110°	630.8	671.1	711.3	740.1	761.2	768.9	761.2	740.1	711.3	671.1	630.8



TEST NUMBER: P1435853

CATALOG NUMBER: SQ2W-FA-K-125U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	687.6	732.4	772.7	801.5	825.6	836.4	825.6	801.5	772.7	732.4	687.6
115°	766.9	826.4	862.8	889.7	906.9	916.5	906.9	889.7	862.8	826.4	766.9
117.5°	832.9	895.0	934.9	955.6	963.7	970.6	963.7	955.6	934.9	895.0	832.9
120°	874.3	931.8	977.9	1004.7	1014.3	1018.1	1014.3	1004.7	977.9	931.8	874.3
122.5°	912.7	967.1	1011.6	1044.6	1060.3	1064.1	1060.3	1044.6	1011.6	967.1	912.7
125°	966.4	1018.1	1064.1	1096.7	1114.0	1123.6	1114.0	1096.7	1064.1	1018.1	966.4
127.5°	1013.1	1069.1	1111.3	1140.8	1157.7	1165.4	1157.7	1140.8	1111.3	1069.1	1013.1
130°	1039.2	1096.7	1138.9	1171.5	1186.8	1194.5	1186.8	1171.5	1138.9	1096.7	1039.2
132.5°	1059.2	1119.7	1163.5	1193.0	1209.9	1217.5	1209.9	1193.0	1163.5	1119.7	1059.2
135°	1083.3	1146.6	1192.6	1221.4	1236.7	1244.4	1236.7	1221.4	1192.6	1146.6	1083.3
137.5°	1104.4	1161.9	1209.9	1240.2	1254.0	1258.9	1254.0	1240.2	1209.9	1161.9	1104.4
140°	1119.7	1169.6	1217.5	1246.3	1261.6	1263.5	1261.6	1246.3	1217.5	1169.6	1119.7
142.5°	1139.7	1178.8	1220.6	1249.4	1264.7	1268.1	1264.7	1249.4	1220.6	1178.8	1139.7
145°	1175.3	1198.4	1227.1	1254.0	1267.4	1271.2	1267.4	1254.0	1227.1	1198.4	1175.3
147.5°	1220.2	1227.5	1242.5	1260.1	1273.1	1275.8	1273.1	1260.1	1242.5	1227.5	1220.2
150°	1254.0	1252.0	1257.8	1269.3	1280.8	1278.9	1280.8	1269.3	1257.8	1252.0	1254.0
152.5°	1292.3	1281.2	1280.8	1286.2	1291.5	1291.2	1291.5	1286.2	1280.8	1281.2	1292.3
155°	1357.5	1336.4	1324.9	1321.1	1321.1	1319.1	1321.1	1321.1	1324.9	1336.4	1357.5
157.5°	1429.2	1399.7	1382.4	1373.2	1370.5	1366.3	1370.5	1373.2	1382.4	1399.7	1429.2
160°	1478.3	1445.7	1428.4	1413.1	1407.3	1401.6	1407.3	1413.1	1428.4	1445.7	1478.3
162.5°	1524.3	1493.2	1474.5	1460.6	1454.9	1446.1	1454.9	1460.6	1474.5	1493.2	1524.3
165°	1599.1	1566.5	1545.4	1533.9	1526.2	1518.6	1526.2	1533.9	1545.4	1566.5	1599.1
167.5°	1673.9	1638.2	1624.4	1611.4	1604.1	1590.3	1604.1	1611.4	1624.4	1638.2	1673.9
170°	1719.9	1687.3	1679.6	1668.1	1654.7	1639.3	1654.7	1668.1	1679.6	1687.3	1719.9
172.5°	1759.8	1737.9	1730.2	1718.7	1714.5	1702.2	1714.5	1718.7	1730.2	1737.9	1759.8
175°	1817.7	1800.4	1800.4	1798.5	1792.7	1781.2	1792.7	1798.5	1800.4	1800.4	1817.7
177.5°	1866.0	1856.8	1862.9	1862.9	1861.4	1850.6	1861.4	1862.9	1862.9	1856.8	1866.0
180°	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2



TEST NUMBER: P1435853

CATALOG NUMBER: SQ2W-FA-K-125U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	2125.5	2125.5	2125.5	2125.5
2.5°	2101.3	2112.3	2112.3	2112.3
5°	2023.9	2070.6	2081.6	2092.5
7.5°	1870.7	1974.6	2023.7	2072.8
10°	1763.0	1861.9	1960.7	2059.6
12.5°	1670.7	1760.1	1900.0	2039.8
15°	1595.5	1670.6	1828.0	1985.5
17.5°	1540.0	1588.4	1753.1	1917.9
20°	1526.8	1548.8	1713.6	1878.4
22.5°	1502.7	1501.9	1663.8	1825.6
25°	1460.9	1436.2	1579.0	1721.8
27.5°	1410.4	1369.4	1482.2	1595.0
30°	1373.1	1325.5	1420.7	1515.9
32.5°	1329.1	1279.3	1348.2	1417.0
35°	1268.7	1210.1	1239.4	1268.7
37.5°	1210.5	1139.5	1129.9	1120.4
40°	1164.4	1087.5	1054.5	1021.6
42.5°	1120.4	1040.6	1004.7	968.8
45°	1051.8	974.9	952.9	930.9
47.5°	984.2	905.5	889.4	873.3
50°	933.7	851.3	829.3	807.4
52.5°	876.6	787.6	774.4	761.2
55°	785.4	694.8	705.8	716.7
57.5°	692.0	593.9	603.4	612.9
60°	626.1	523.6	541.9	560.2
62.5°	575.6	476.0	488.4	500.9
65°	508.0	418.3	411.0	403.7
67.5°	445.4	364.7	340.5	316.4
70°	403.7	329.5	296.6	263.6
72.5°	357.5	296.6	263.6	230.7
75°	285.6	238.9	206.0	173.0
77.5°	212.0	179.4	152.3	125.2
80°	159.3	135.5	117.2	98.9
82.5°	113.1	96.7	81.3	65.9
85°	54.9	47.6	40.3	33.0
87.5°	20.1	16.7	12.2	7.7
90°	34.5	21.1	13.4	5.8
92.5°	74.4	51.8	36.4	21.1
95°	149.6	118.9	84.4	59.4
97.5°	238.1	188.7	154.5	113.5
100°	285.7	237.8	205.2	161.1
102.5°	337.8	297.6	252.7	208.6
105°	431.4	381.6	329.8	279.9
107.5°	518.1	463.2	401.1	356.2
110°	573.3	513.9	448.7	408.4



TEST NUMBER: P1435853

CATALOG NUMBER: SQ2W-FA-K-125U-125D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	627.0	566.0	499.3	459.0
115°	699.8	632.7	571.4	536.9
117.5°	770.0	701.0	636.2	609.0
120°	813.0	743.9	680.7	659.6
122.5°	848.2	780.8	722.1	713.3
125°	901.2	832.1	782.3	793.8
127.5°	944.1	880.8	849.4	875.1
130°	970.2	914.6	895.4	931.8
132.5°	993.2	949.9	941.4	991.7
135°	1027.7	1002.8	1010.5	1079.5
137.5°	1068.7	1059.2	1084.8	1171.9
140°	1094.8	1100.6	1137.0	1234.8
142.5°	1130.1	1143.5	1190.7	1294.6
145°	1184.9	1213.7	1275.0	1378.6
147.5°	1247.1	1284.3	1360.2	1466.4
150°	1288.5	1336.4	1416.9	1518.6
152.5°	1336.0	1385.5	1466.0	1569.2
155°	1409.3	1464.9	1549.2	1637.4
157.5°	1484.0	1540.8	1621.3	1698.4
160°	1530.1	1591.4	1664.3	1735.2
162.5°	1582.2	1639.0	1702.6	1765.9
165°	1658.5	1704.5	1756.3	1810.0
167.5°	1722.6	1760.9	1801.6	1843.4
170°	1764.0	1794.7	1829.2	1861.8
172.5°	1799.3	1823.8	1849.1	1877.1
175°	1846.4	1859.8	1875.2	1892.4
177.5°	1882.9	1887.5	1892.1	1899.7
180°	1898.2	1898.2	1898.2	1898.2



TEST NUMBER: P1435853  
 CATALOG NUMBER: SQ2W-FA-K-125U-125D-L830-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.55	19.40	19.52	20.38	21.67	19.75	20.60	20.72	21.58	22.87
	3H	19.64	20.40	20.62	21.39	22.70	20.99	21.75	21.97	22.74	24.05
	4H	19.99	20.71	20.98	21.70	23.02	21.38	22.10	22.37	23.10	24.41
	6H	20.15	20.81	21.15	21.81	23.14	21.54	22.20	22.54	23.20	24.53
	8H	20.18	20.82	21.19	21.83	23.16	21.57	22.20	22.57	23.21	24.54
	12H	20.18	20.78	21.19	21.79	23.14	21.55	22.15	22.56	23.16	24.51
4H	2H	19.42	20.14	20.41	21.13	22.45	20.33	21.05	21.33	22.05	23.36
	3H	20.80	21.40	21.81	22.43	23.76	21.79	22.39	22.80	23.42	24.75
	4H	21.26	21.81	22.27	22.82	24.18	22.27	22.82	23.29	23.83	25.19
	6H	21.49	21.96	22.51	23.00	24.35	22.49	22.96	23.52	24.00	25.35
	8H	21.54	21.99	22.57	23.02	24.38	22.54	22.98	23.57	24.01	25.38
	12H	21.55	21.94	22.59	22.99	24.36	22.53	22.92	23.57	23.97	25.34
8H	4H	21.64	22.08	22.67	23.11	24.48	22.46	22.90	23.49	23.94	25.30
	6H	21.99	22.36	23.04	23.43	24.79	22.78	23.14	23.83	24.22	25.58
	8H	22.11	22.43	23.17	23.49	24.87	22.87	23.19	23.93	24.25	25.64
	12H	22.15	22.43	23.21	23.48	24.91	22.89	23.17	23.95	24.22	25.65
12H	4H	21.64	22.04	22.69	23.09	24.46	22.43	22.83	23.48	23.88	25.25
	6H	22.06	22.38	23.12	23.44	24.82	22.80	23.12	23.86	24.18	25.56
	8H	22.21	22.49	23.27	23.54	24.97	22.91	23.19	23.97	24.24	25.67