

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435907

Luminaire Tested: SQ2W-FB-K-025U-050D-L830-UNV-STD-W-WM-4

Issue Date: 3/24/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1435907  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/24/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-FB-K-025U-050D-L830-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3418.7 lumens  
Efficiency: N/A  
Efficacy: 135.1 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 25.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1435907

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L830-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1435907

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L830-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73	68				
1	102	97	93	89	96	92	88	85	82	79	76	72	70	68	64	62	61	57				
2	92	84	78	72	87	80	74	69	71	66	62	63	59	56	56	53	51	47				
3	84	73	66	59	78	69	62	57	62	56	52	55	51	47	49	45	42	39				
4	76	65	56	50	71	61	53	48	55	48	43	49	44	40	43	39	36	33				
5	70	57	48	42	65	54	46	40	49	42	37	43	38	34	38	34	31	28				
6	64	51	42	36	60	48	40	35	43	37	32	39	33	29	34	30	27	24				
7	59	46	37	31	55	44	36	30	39	33	28	35	30	26	31	27	23	21				
8	55	41	33	28	51	39	32	27	35	29	24	32	26	22	28	24	21	18				
9	51	38	30	24	48	36	29	23	32	26	22	29	24	20	26	22	18	16				
10	47	34	27	22	45	33	26	21	30	24	19	27	22	18	24	20	16	14				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3797	3797	3797	3797
5°	3702	6724	3702	6724
10°	3466	13086	3466	13086
15°	3137	15062	3137	15062
20°	2778	15775	2778	15775
25°	2457	16033	2457	16033
30°	2172	16231	2172	16231
35°	1939	17449	1939	17449
40°	1764	18539	1764	18539
45°	1626	19415	1626	19415
50°	1535	19765	1535	19765
55°	1495	19924	1495	19924
60°	1534	19824	1534	19824
65°	1597	19266	1597	19266
70°	1657	14573	1657	14573
75°	1834	8041	1834	8041
80°	1897	7466	1897	7466
85°	1890	3149	1890	3149

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 52.5°  
 Luminance: 20104 cd/sqm



TEST NUMBER: P1435907

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L830-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	39.4	1.2
10°-20°	179.8	5.3
20°-30°	316.4	9.3
30°-40°	409.5	12.0
40°-50°	451.6	13.2
50°-60°	421.5	12.3
60°-70°	325.7	9.5
70°-80°	150.1	4.4
80°-90°	30.3	0.9
90°-100°	29.8	0.9
100°-110°	87.0	2.5
110°-120°	142.0	4.2
120°-130°	180.2	5.3
130°-140°	192.8	5.6
140°-150°	180.0	5.3
150°-160°	148.1	4.3
160°-170°	99.3	2.9
170°-180°	35.3	1.0
0°-30°	535.5	15.7
0°-40°	945.1	27.6
0°-60°	1818.2	53.2
0°-90°	2324.3	68.0
90°-120°	258.8	7.6
90°-150°	811.7	23.7
90°-180°	1094.0	32.0
0°-180°	3418.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	235	235	235	235	235	
5°	228	415	228	415	228	21
15°	188	901	188	901	188	52
25°	138	900	138	900	138	63
35°	98	885	98	885	98	62
45°	71	850	71	850	71	55
55°	53	708	53	708	53	48
65°	42	504	42	504	42	41
75°	29	129	29	129	29	30
85°	10	17	10	17	10	11
90°	1	8	1	16	1	1
95°	12	9	12	51	12	14
105°	55	89	55	122	55	59
115°	106	147	106	181	106	104
125°	157	233	157	222	157	140
135°	213	305	213	246	213	165
145°	272	351	272	251	272	170
155°	323	382	323	260	323	149
165°	357	398	357	300	357	101
175°	374	390	374	352	374	35
180°	375	375	375	375	375	



TEST NUMBER: P1435907

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2
2.5°	233.4	237.8	242.2	246.9	251.8	257.0	262.6	267.4	269.8	272.3	269.8
5°	228.4	243.5	258.5	280.4	304.5	331.9	362.6	388.8	401.9	414.9	401.9
7.5°	219.6	250.2	280.9	345.8	422.2	501.5	583.7	651.9	678.0	704.2	678.0
10°	211.4	254.1	296.9	407.0	539.7	641.7	713.1	770.1	784.2	798.2	784.2
12.5°	202.4	260.4	318.4	454.4	616.4	722.4	772.5	813.6	828.1	842.6	828.1
15°	187.7	270.6	353.5	507.3	684.7	793.7	834.4	869.0	885.0	901.1	885.0
17.5°	172.5	282.9	393.2	550.1	722.5	828.8	869.1	901.5	910.2	919.0	910.2
20°	161.7	291.3	421.0	578.1	744.5	845.0	879.6	907.0	912.6	918.1	912.6
22.5°	151.7	296.7	441.6	598.9	760.5	854.3	880.6	901.7	907.6	913.6	907.6
25°	137.9	301.3	464.6	621.5	776.3	861.9	878.5	892.0	896.0	900.0	896.0
27.5°	124.6	297.2	469.7	624.6	773.7	853.6	864.5	873.6	877.5	881.5	877.5
30°	116.5	291.8	467.2	620.7	767.0	844.1	852.1	859.5	865.1	870.6	865.1
32.5°	109.2	285.4	461.6	613.2	756.6	832.1	839.8	848.5	860.5	872.4	860.5
35°	98.4	271.7	445.1	595.1	737.3	814.4	826.5	841.1	863.2	885.3	863.2
37.5°	89.1	254.2	419.3	567.8	710.7	794.8	820.0	844.3	865.6	886.9	865.6
40°	83.7	242.0	400.3	547.6	691.3	780.0	813.7	843.5	861.6	879.6	861.6
42.5°	78.2	228.1	377.9	524.1	669.0	761.1	800.4	834.4	852.5	870.6	852.5
45°	71.2	205.9	340.6	485.4	633.7	730.9	777.1	816.1	833.2	850.3	833.2
47.5°	64.7	181.7	298.6	444.1	599.1	701.1	750.1	790.0	802.5	815.0	802.5
50°	61.1	165.6	270.1	416.1	575.9	679.9	728.1	766.8	776.9	786.9	776.9
52.5°	57.4	149.9	242.4	388.6	552.9	657.7	703.1	739.5	748.7	758.0	748.7
55°	53.1	128.5	203.9	348.6	516.5	620.2	659.9	691.7	699.7	707.8	699.7
57.5°	49.3	110.1	170.9	311.1	477.7	578.0	611.8	638.9	645.4	651.9	645.4
60°	47.5	100.3	153.0	287.6	449.4	545.6	576.3	600.9	607.4	613.9	607.4
62.5°	44.8	90.7	136.6	264.0	418.6	510.0	538.3	561.0	567.1	573.2	567.1
65°	41.8	79.0	116.2	231.0	371.7	453.9	477.5	496.2	500.3	504.3	500.3
67.5°	37.8	69.3	100.9	200.8	323.5	392.2	406.9	416.0	408.5	400.9	408.5
70°	35.1	64.2	93.3	182.4	291.5	348.5	353.5	351.9	330.3	308.7	330.3
72.5°	33.2	59.2	85.1	162.2	256.4	297.9	286.9	268.4	227.5	186.6	227.5
75°	29.4	50.5	71.6	129.6	200.0	211.1	162.8	126.9	127.9	128.9	127.9
77.5°	24.0	39.7	55.5	91.2	133.5	141.9	116.4	97.5	98.4	99.3	98.4
80°	20.4	32.9	45.5	59.5	74.1	80.9	79.9	79.3	79.8	80.3	79.8
82.5°	16.7	26.1	35.4	43.9	52.0	56.6	57.6	58.2	57.5	56.8	57.5
85°	10.2	15.7	21.2	24.5	27.0	26.3	22.2	19.0	18.0	17.0	18.0
87.5°	3.8	6.2	8.5	8.1	6.8	6.0	6.0	6.1	6.2	6.2	6.2
90°	1.1	2.7	4.5	6.1	7.2	7.6	7.6	8.0	8.3	8.3	8.3
92.5°	4.2	6.6	6.7	6.7	8.1	8.8	9.4	9.5	9.8	9.8	9.8
95°	11.7	12.9	19.3	18.9	12.9	10.2	8.7	8.7	8.7	8.7	8.7
97.5°	22.4	24.1	25.1	33.7	35.6	34.4	28.0	23.6	21.1	19.9	21.1
100°	31.8	32.6	34.8	35.2	44.7	53.8	49.2	43.5	41.6	40.5	41.6
102.5°	41.2	41.6	45.1	46.7	48.9	54.1	69.8	68.1	66.8	66.6	66.8
105°	55.3	55.7	62.1	65.1	66.6	66.6	66.3	73.8	85.9	88.6	85.9
107.5°	70.3	72.1	79.7	87.8	89.5	90.0	88.0	86.9	86.4	86.7	86.4
110°	80.6	83.3	92.4	102.6	105.3	106.0	105.3	104.1	103.4	103.4	103.4



TEST NUMBER: P1435907

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	90.6	94.5	104.8	116.5	121.0	123.3	121.6	120.8	120.0	120.6	120.0
115°	106.0	111.7	125.3	137.4	146.5	147.7	147.3	147.3	146.9	146.9	146.9
117.5°	120.3	129.3	144.6	158.7	169.2	172.3	173.8	173.3	172.9	173.6	172.9
120°	130.2	140.8	158.3	174.2	184.4	188.9	190.4	189.7	190.4	189.7	190.4
122.5°	140.8	153.9	171.0	187.5	199.5	204.7	206.5	206.7	206.8	206.4	206.8
125°	156.8	172.7	192.7	209.8	222.3	228.3	229.8	230.2	231.0	232.9	231.0
127.5°	172.8	190.8	212.9	229.3	242.1	249.4	251.8	252.6	254.2	255.0	254.2
130°	184.0	204.5	226.8	242.3	254.8	262.8	266.9	268.1	270.0	269.6	270.0
132.5°	195.8	217.2	239.8	256.0	267.5	276.1	279.7	282.9	283.6	284.1	283.6
135°	213.2	236.3	259.0	274.9	285.9	294.2	298.7	301.8	303.7	304.8	303.7
137.5°	231.4	255.8	277.6	291.8	302.8	310.0	315.2	318.4	320.3	321.2	320.3
140°	243.8	267.3	288.5	303.3	313.1	320.3	324.9	328.6	330.9	330.9	330.9
142.5°	255.6	278.8	299.4	314.2	322.8	329.4	334.3	337.1	339.7	339.7	339.7
145°	272.2	295.3	314.3	329.0	336.2	342.3	347.6	349.9	351.4	351.4	351.4
147.5°	289.6	310.0	327.3	341.4	347.5	354.6	358.8	360.6	362.5	361.7	362.5
150°	299.9	318.8	335.5	348.7	354.8	361.6	365.8	367.3	369.2	368.0	369.2
152.5°	309.9	327.9	343.0	355.4	360.5	367.3	372.1	373.6	374.9	374.1	374.9
155°	323.3	339.3	353.3	364.6	369.2	375.6	380.1	382.0	383.6	381.7	383.6
157.5°	335.4	349.1	361.3	371.7	376.6	382.1	386.4	388.7	390.2	389.4	390.2
160°	342.7	355.2	366.1	376.0	380.5	385.4	390.0	392.6	394.2	393.0	394.2
162.5°	348.7	360.0	370.4	379.3	383.2	387.6	393.0	395.4	396.9	395.4	396.9
165°	357.4	366.5	375.6	383.2	386.6	390.0	395.7	398.3	399.5	397.9	399.5
167.5°	364.0	371.0	378.3	384.8	387.3	390.7	396.3	398.5	400.0	398.1	400.0
170°	367.6	373.7	380.1	385.4	387.3	390.4	396.0	397.9	399.1	397.2	399.1
172.5°	370.7	375.2	380.4	385.1	386.1	388.5	393.9	395.8	396.7	395.1	396.7
175°	373.7	376.4	380.1	383.2	382.8	384.3	388.9	390.4	391.9	389.6	391.9
177.5°	375.1	376.4	377.6	379.4	378.2	378.2	381.5	382.4	382.7	381.5	382.7
180°	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8



TEST NUMBER: P1435907

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2
2.5°	267.4	262.6	257.0	251.8	246.9	242.2	237.8	233.4	237.8	242.2	246.9
5°	388.8	362.6	331.9	304.5	280.4	258.5	243.5	228.4	243.5	258.5	280.4
7.5°	651.9	583.7	501.5	422.2	345.8	280.9	250.2	219.6	250.2	280.9	345.8
10°	770.1	713.1	641.7	539.7	407.0	296.9	254.1	211.4	254.1	296.9	407.0
12.5°	813.6	772.5	722.4	616.4	454.4	318.4	260.4	202.4	260.4	318.4	454.4
15°	869.0	834.4	793.7	684.7	507.3	353.5	270.6	187.7	270.6	353.5	507.3
17.5°	901.5	869.1	828.8	722.5	550.1	393.2	282.9	172.5	282.9	393.2	550.1
20°	907.0	879.6	845.0	744.5	578.1	421.0	291.3	161.7	291.3	421.0	578.1
22.5°	901.7	880.6	854.3	760.5	598.9	441.6	296.7	151.7	296.7	441.6	598.9
25°	892.0	878.5	861.9	776.3	621.5	464.6	301.3	137.9	301.3	464.6	621.5
27.5°	873.6	864.5	853.6	773.7	624.6	469.7	297.2	124.6	297.2	469.7	624.6
30°	859.5	852.1	844.1	767.0	620.7	467.2	291.8	116.5	291.8	467.2	620.7
32.5°	848.5	839.8	832.1	756.6	613.2	461.6	285.4	109.2	285.4	461.6	613.2
35°	841.1	826.5	814.4	737.3	595.1	445.1	271.7	98.4	271.7	445.1	595.1
37.5°	844.3	820.0	794.8	710.7	567.8	419.3	254.2	89.1	254.2	419.3	567.8
40°	843.5	813.7	780.0	691.3	547.6	400.3	242.0	83.7	242.0	400.3	547.6
42.5°	834.4	800.4	761.1	669.0	524.1	377.9	228.1	78.2	228.1	377.9	524.1
45°	816.1	777.1	730.9	633.7	485.4	340.6	205.9	71.2	205.9	340.6	485.4
47.5°	790.0	750.1	701.1	599.1	444.1	298.6	181.7	64.7	181.7	298.6	444.1
50°	766.8	728.1	679.9	575.9	416.1	270.1	165.6	61.1	165.6	270.1	416.1
52.5°	739.5	703.1	657.7	552.9	388.6	242.4	149.9	57.4	149.9	242.4	388.6
55°	691.7	659.9	620.2	516.5	348.6	203.9	128.5	53.1	128.5	203.9	348.6
57.5°	638.9	611.8	578.0	477.7	311.1	170.9	110.1	49.3	110.1	170.9	311.1
60°	600.9	576.3	545.6	449.4	287.6	153.0	100.3	47.5	100.3	153.0	287.6
62.5°	561.0	538.3	510.0	418.6	264.0	136.6	90.7	44.8	90.7	136.6	264.0
65°	496.2	477.5	453.9	371.7	231.0	116.2	79.0	41.8	79.0	116.2	231.0
67.5°	416.0	406.9	392.2	323.5	200.8	100.9	69.3	37.8	69.3	100.9	200.8
70°	351.9	353.5	348.5	291.5	182.4	93.3	64.2	35.1	64.2	93.3	182.4
72.5°	268.4	286.9	297.9	256.4	162.2	85.1	59.2	33.2	59.2	85.1	162.2
75°	126.9	162.8	211.1	200.0	129.6	71.6	50.5	29.4	50.5	71.6	129.6
77.5°	97.5	116.4	141.9	133.5	91.2	55.5	39.7	24.0	39.7	55.5	91.2
80°	79.3	79.9	80.9	74.1	59.5	45.5	32.9	20.4	32.9	45.5	59.5
82.5°	58.2	57.6	56.6	52.0	43.9	35.4	26.1	16.7	26.1	35.4	43.9
85°	19.0	22.2	26.3	27.0	24.5	21.2	15.7	10.2	15.7	21.2	24.5
87.5°	6.1	6.0	6.0	6.8	8.1	8.5	6.2	3.8	6.2	8.5	8.3
90°	8.0	7.6	7.6	7.2	6.1	4.5	2.7	1.1	2.7	4.2	6.8
92.5°	9.5	9.4	8.8	8.1	6.7	6.7	6.6	4.2	7.2	10.2	14.7
95°	8.7	8.7	10.2	12.9	18.9	19.3	12.9	11.7	16.7	23.5	29.5
97.5°	23.6	28.0	34.4	35.6	33.7	25.1	24.1	22.4	30.5	37.3	47.0
100°	43.5	49.2	53.8	44.7	35.2	34.8	32.6	31.8	40.5	46.9	56.4
102.5°	68.1	69.8	54.1	48.9	46.7	45.1	41.6	41.2	49.9	58.8	66.7
105°	73.8	66.3	66.6	66.6	65.1	62.1	55.7	55.3	65.1	75.3	85.2
107.5°	86.9	88.0	90.0	89.5	87.8	79.7	72.1	70.3	79.2	91.5	102.3
110°	104.1	105.3	106.0	105.3	102.6	92.4	83.3	80.6	88.6	101.5	113.2



TEST NUMBER: P1435907

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	120.8	121.6	123.3	121.0	116.5	104.8	94.5	90.6	98.6	111.8	123.8
115°	147.3	147.3	147.7	146.5	137.4	125.3	111.7	106.0	112.8	124.9	138.2
117.5°	173.3	173.8	172.3	169.2	158.7	144.6	129.3	120.3	125.6	138.4	152.1
120°	189.7	190.4	188.9	184.4	174.2	158.3	140.8	130.2	134.4	146.9	160.5
122.5°	206.7	206.5	204.7	199.5	187.5	171.0	153.9	140.8	142.6	154.2	167.5
125°	230.2	229.8	228.3	222.3	209.8	192.7	172.7	156.8	154.5	164.3	178.0
127.5°	252.6	251.8	249.4	242.1	229.3	212.9	190.8	172.8	167.7	173.9	186.4
130°	268.1	266.9	262.8	254.8	242.3	226.8	204.5	184.0	176.8	180.6	191.6
132.5°	282.9	279.7	276.1	267.5	256.0	239.8	217.2	195.8	185.9	187.6	196.1
135°	301.8	298.7	294.2	285.9	274.9	259.0	236.3	213.2	199.5	198.0	202.9
137.5°	318.4	315.2	310.0	302.8	291.8	277.6	255.8	231.4	214.2	209.2	211.0
140°	328.6	324.9	320.3	313.1	303.3	288.5	267.3	243.8	224.5	217.3	216.2
142.5°	337.1	334.3	329.4	322.8	314.2	299.4	278.8	255.6	235.1	225.8	223.2
145°	349.9	347.6	342.3	336.2	329.0	314.3	295.3	272.2	251.8	239.7	234.0
147.5°	360.6	358.8	354.6	347.5	341.4	327.3	310.0	289.6	268.6	253.6	246.3
150°	367.3	365.8	361.6	354.8	348.7	335.5	318.8	299.9	279.8	263.9	254.4
152.5°	373.6	372.1	367.3	360.5	355.4	343.0	327.9	309.9	289.5	273.6	263.8
155°	382.0	380.1	375.6	369.2	364.6	353.3	339.3	323.3	305.9	289.3	278.3
157.5°	388.7	386.4	382.1	376.6	371.7	361.3	349.1	335.4	320.2	304.3	293.1
160°	392.6	390.0	385.4	380.5	376.0	366.1	355.2	342.7	328.6	314.3	302.1
162.5°	395.4	393.0	387.6	383.2	379.3	370.4	360.0	348.7	336.2	323.7	312.4
165°	398.3	395.7	390.0	386.6	383.2	375.6	366.5	357.4	346.8	336.6	327.5
167.5°	398.5	396.3	390.7	387.3	384.8	378.3	371.0	364.0	355.8	347.7	340.2
170°	397.9	396.0	390.4	387.3	385.4	380.1	373.7	367.6	361.2	354.4	348.3
172.5°	395.8	393.9	388.5	386.1	385.1	380.4	375.2	370.7	365.1	360.2	355.3
175°	390.4	388.9	384.3	382.8	383.2	380.1	376.4	373.7	370.3	367.3	364.6
177.5°	382.4	381.5	378.2	378.2	379.4	377.6	376.4	375.1	373.6	372.7	371.8
180°	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8



TEST NUMBER: P1435907

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2
2.5°	251.8	257.0	262.6	267.4	269.8	272.3	269.8	267.4	262.6	257.0	251.8
5°	304.5	331.9	362.6	388.8	401.9	414.9	401.9	388.8	362.6	331.9	304.5
7.5°	422.2	501.5	583.7	651.9	678.0	704.2	678.0	651.9	583.7	501.5	422.2
10°	539.7	641.7	713.1	770.1	784.2	798.2	784.2	770.1	713.1	641.7	539.7
12.5°	616.4	722.4	772.5	813.6	828.1	842.6	828.1	813.6	772.5	722.4	616.4
15°	684.7	793.7	834.4	869.0	885.0	901.1	885.0	869.0	834.4	793.7	684.7
17.5°	722.5	828.8	869.1	901.5	910.2	919.0	910.2	901.5	869.1	828.8	722.5
20°	744.5	845.0	879.6	907.0	912.6	918.1	912.6	907.0	879.6	845.0	744.5
22.5°	760.5	854.3	880.6	901.7	907.6	913.6	907.6	901.7	880.6	854.3	760.5
25°	776.3	861.9	878.5	892.0	896.0	900.0	896.0	892.0	878.5	861.9	776.3
27.5°	773.7	853.6	864.5	873.6	877.5	881.5	877.5	873.6	864.5	853.6	773.7
30°	767.0	844.1	852.1	859.5	865.1	870.6	865.1	859.5	852.1	844.1	767.0
32.5°	756.6	832.1	839.8	848.5	860.5	872.4	860.5	848.5	839.8	832.1	756.6
35°	737.3	814.4	826.5	841.1	863.2	885.3	863.2	841.1	826.5	814.4	737.3
37.5°	710.7	794.8	820.0	844.3	865.6	886.9	865.6	844.3	820.0	794.8	710.7
40°	691.3	780.0	813.7	843.5	861.6	879.6	861.6	843.5	813.7	780.0	691.3
42.5°	669.0	761.1	800.4	834.4	852.5	870.6	852.5	834.4	800.4	761.1	669.0
45°	633.7	730.9	777.1	816.1	833.2	850.3	833.2	816.1	777.1	730.9	633.7
47.5°	599.1	701.1	750.1	790.0	802.5	815.0	802.5	790.0	750.1	701.1	599.1
50°	575.9	679.9	728.1	766.8	776.9	786.9	776.9	766.8	728.1	679.9	575.9
52.5°	552.9	657.7	703.1	739.5	748.7	758.0	748.7	739.5	703.1	657.7	552.9
55°	516.5	620.2	659.9	691.7	699.7	707.8	699.7	691.7	659.9	620.2	516.5
57.5°	477.7	578.0	611.8	638.9	645.4	651.9	645.4	638.9	611.8	578.0	477.7
60°	449.4	545.6	576.3	600.9	607.4	613.9	607.4	600.9	576.3	545.6	449.4
62.5°	418.6	510.0	538.3	561.0	567.1	573.2	567.1	561.0	538.3	510.0	418.6
65°	371.7	453.9	477.5	496.2	500.3	504.3	500.3	496.2	477.5	453.9	371.7
67.5°	323.5	392.2	406.9	416.0	408.5	400.9	408.5	416.0	406.9	392.2	323.5
70°	291.5	348.5	353.5	351.9	330.3	308.7	330.3	351.9	353.5	348.5	291.5
72.5°	256.4	297.9	286.9	268.4	227.5	186.6	227.5	268.4	286.9	297.9	256.4
75°	200.0	211.1	162.8	126.9	127.9	128.9	127.9	126.9	162.8	211.1	200.0
77.5°	133.5	141.9	116.4	97.5	98.4	99.3	98.4	97.5	116.4	141.9	133.5
80°	74.1	80.9	79.9	79.3	79.8	80.3	79.8	79.3	79.9	80.9	74.1
82.5°	52.0	56.6	57.6	58.2	57.5	56.8	57.5	58.2	57.6	56.6	52.0
85°	27.0	26.3	22.2	19.0	18.0	17.0	18.0	19.0	22.2	26.3	27.0
87.5°	7.1	6.8	7.3	7.6	7.9	7.8	7.9	7.6	7.3	6.8	7.1
90°	8.7	11.4	14.0	15.5	17.0	16.3	17.0	15.5	14.0	11.4	8.7
92.5°	17.5	22.0	25.2	27.9	29.2	29.0	29.2	27.9	25.2	22.0	17.5
95°	35.2	40.5	45.8	49.6	51.9	51.1	51.9	49.6	45.8	40.5	35.2
97.5°	54.3	61.4	67.3	70.9	73.2	74.7	73.2	70.9	67.3	61.4	54.3
100°	67.0	73.8	80.6	84.8	88.6	90.1	88.6	84.8	80.6	73.8	67.0
102.5°	77.3	86.3	93.7	98.1	101.3	102.8	101.3	98.1	93.7	86.3	77.3
105°	94.3	103.7	111.7	117.4	120.8	121.9	120.8	117.4	111.7	103.7	94.3
107.5°	111.2	121.0	128.4	134.6	138.8	141.2	138.8	134.6	128.4	121.0	111.2
110°	124.6	132.5	140.5	146.2	150.3	151.8	150.3	146.2	140.5	132.5	124.6



TEST NUMBER: P1435907

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	135.8	144.6	152.6	158.3	163.0	165.2	163.0	158.3	152.6	144.6	135.8
115°	151.5	163.2	170.4	175.7	179.1	181.0	179.1	175.7	170.4	163.2	151.5
117.5°	164.5	176.7	184.6	188.7	190.3	191.7	190.3	188.7	184.6	176.7	164.5
120°	172.7	184.0	193.1	198.4	200.3	201.1	200.3	198.4	193.1	184.0	172.7
122.5°	180.2	191.0	199.8	206.3	209.4	210.1	209.4	206.3	199.8	191.0	180.2
125°	190.8	201.1	210.1	216.6	220.0	221.9	220.0	216.6	210.1	201.1	190.8
127.5°	200.1	211.1	219.5	225.3	228.6	230.1	228.6	225.3	219.5	211.1	200.1
130°	205.2	216.6	224.9	231.3	234.4	235.9	234.4	231.3	224.9	216.6	205.2
132.5°	209.2	221.1	229.8	235.6	238.9	240.4	238.9	235.6	229.8	221.1	209.2
135°	213.9	226.4	235.5	241.2	244.2	245.7	244.2	241.2	235.5	226.4	213.9
137.5°	218.1	229.4	238.9	244.9	247.6	248.6	247.6	244.9	238.9	229.4	218.1
140°	221.1	231.0	240.4	246.1	249.1	249.5	249.1	246.1	240.4	231.0	221.1
142.5°	225.1	232.8	241.0	246.7	249.7	250.4	249.7	246.7	241.0	232.8	225.1
145°	232.1	236.6	242.3	247.6	250.3	251.0	250.3	247.6	242.3	236.6	232.1
147.5°	241.0	242.4	245.4	248.8	251.4	251.9	251.4	248.8	245.4	242.4	241.0
150°	247.6	247.2	248.4	250.7	252.9	252.5	252.9	250.7	248.4	247.2	247.6
152.5°	255.2	253.0	252.9	254.0	255.0	255.0	255.0	254.0	252.9	253.0	255.2
155°	268.1	263.9	261.6	260.9	260.9	260.5	260.9	260.9	261.6	263.9	268.1
157.5°	282.2	276.4	273.0	271.2	270.6	269.8	270.6	271.2	273.0	276.4	282.2
160°	291.9	285.5	282.1	279.0	277.9	276.8	277.9	279.0	282.1	285.5	291.9
162.5°	301.0	294.9	291.2	288.4	287.3	285.6	287.3	288.4	291.2	294.9	301.0
165°	315.8	309.3	305.2	302.9	301.4	299.9	301.4	302.9	305.2	309.3	315.8
167.5°	330.5	323.5	320.8	318.2	316.8	314.0	316.8	318.2	320.8	323.5	330.5
170°	339.6	333.2	331.7	329.4	326.8	323.7	326.8	329.4	331.7	333.2	339.6
172.5°	347.5	343.2	341.7	339.4	338.6	336.1	338.6	339.4	341.7	343.2	347.5
175°	358.9	355.5	355.5	355.2	354.0	351.7	354.0	355.2	355.5	355.5	358.9
177.5°	368.5	366.7	367.9	367.9	367.6	365.5	367.6	367.9	366.7	368.5	368.5
180°	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8



TEST NUMBER: P1435907

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	235.2	235.2	235.2	235.2
2.5°	246.9	242.2	237.8	233.4
5°	280.4	258.5	243.5	228.4
7.5°	345.8	280.9	250.2	219.6
10°	407.0	296.9	254.1	211.4
12.5°	454.4	318.4	260.4	202.4
15°	507.3	353.5	270.6	187.7
17.5°	550.1	393.2	282.9	172.5
20°	578.1	421.0	291.3	161.7
22.5°	598.9	441.6	296.7	151.7
25°	621.5	464.6	301.3	137.9
27.5°	624.6	469.7	297.2	124.6
30°	620.7	467.2	291.8	116.5
32.5°	613.2	461.6	285.4	109.2
35°	595.1	445.1	271.7	98.4
37.5°	567.8	419.3	254.2	89.1
40°	547.6	400.3	242.0	83.7
42.5°	524.1	377.9	228.1	78.2
45°	485.4	340.6	205.9	71.2
47.5°	444.1	298.6	181.7	64.7
50°	416.1	270.1	165.6	61.1
52.5°	388.6	242.4	149.9	57.4
55°	348.6	203.9	128.5	53.1
57.5°	311.1	170.9	110.1	49.3
60°	287.6	153.0	100.3	47.5
62.5°	264.0	136.6	90.7	44.8
65°	231.0	116.2	79.0	41.8
67.5°	200.8	100.9	69.3	37.8
70°	182.4	93.3	64.2	35.1
72.5°	162.2	85.1	59.2	33.2
75°	129.6	71.6	50.5	29.4
77.5°	91.2	55.5	39.7	24.0
80°	59.5	45.5	32.9	20.4
82.5°	43.9	35.4	26.1	16.7
85°	24.5	21.2	15.7	10.2
87.5°	8.3	8.5	6.2	3.8
90°	6.8	4.2	2.7	1.1
92.5°	14.7	10.2	7.2	4.2
95°	29.5	23.5	16.7	11.7
97.5°	47.0	37.3	30.5	22.4
100°	56.4	46.9	40.5	31.8
102.5°	66.7	58.8	49.9	41.2
105°	85.2	75.3	65.1	55.3
107.5°	102.3	91.5	79.2	70.3
110°	113.2	101.5	88.6	80.6



TEST NUMBER: P1435907

CATALOG NUMBER: SQ2W-FB-K-025U-050D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	123.8	111.8	98.6	90.6
115°	138.2	124.9	112.8	106.0
117.5°	152.1	138.4	125.6	120.3
120°	160.5	146.9	134.4	130.2
122.5°	167.5	154.2	142.6	140.8
125°	178.0	164.3	154.5	156.8
127.5°	186.4	173.9	167.7	172.8
130°	191.6	180.6	176.8	184.0
132.5°	196.1	187.6	185.9	195.8
135°	202.9	198.0	199.5	213.2
137.5°	211.0	209.2	214.2	231.4
140°	216.2	217.3	224.5	243.8
142.5°	223.2	225.8	235.1	255.6
145°	234.0	239.7	251.8	272.2
147.5°	246.3	253.6	268.6	289.6
150°	254.4	263.9	279.8	299.9
152.5°	263.8	273.6	289.5	309.9
155°	278.3	289.3	305.9	323.3
157.5°	293.1	304.3	320.2	335.4
160°	302.1	314.3	328.6	342.7
162.5°	312.4	323.7	336.2	348.7
165°	327.5	336.6	346.8	357.4
167.5°	340.2	347.7	355.8	364.0
170°	348.3	354.4	361.2	367.6
172.5°	355.3	360.2	365.1	370.7
175°	364.6	367.3	370.3	373.7
177.5°	371.8	372.7	373.6	375.1
180°	374.8	374.8	374.8	374.8



TEST NUMBER: P1435907  
 CATALOG NUMBER: SQ2W-FB-K-025U-050D-L830-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.31	13.40	13.09	14.20	15.19	21.90	22.99	22.68	23.80	24.79
	3H	13.26	14.24	14.06	15.06	16.08	23.53	24.51	24.32	25.33	26.34
	4H	13.67	14.60	14.48	15.42	16.45	23.72	24.64	24.53	25.47	26.49
	6H	13.94	14.79	14.76	15.63	16.67	23.80	24.66	24.63	25.49	26.53
	8H	14.04	14.85	14.87	15.70	16.75	23.83	24.64	24.66	25.49	26.54
	12H	14.10	14.87	14.93	15.72	16.79	23.81	24.59	24.65	25.44	26.50
4H	2H	17.06	17.98	17.87	18.81	19.83	22.30	23.22	23.11	24.05	25.08
	3H	18.21	18.98	19.03	19.84	20.88	24.21	24.98	25.04	25.84	26.88
	4H	18.50	19.20	19.34	20.06	21.13	24.44	25.14	25.28	26.00	27.07
	6H	18.65	19.25	19.51	20.14	21.21	24.59	25.19	25.44	26.07	27.15
	8H	18.69	19.26	19.55	20.14	21.22	24.64	25.20	25.50	26.08	27.17
	12H	18.71	19.22	19.59	20.11	21.21	24.63	25.14	25.51	26.04	27.13
8H	4H	19.71	20.28	20.57	21.15	22.24	24.55	25.12	25.41	25.99	27.08
	6H	19.98	20.45	20.87	21.37	22.45	24.76	25.23	25.65	26.15	27.23
	8H	20.08	20.50	20.98	21.41	22.51	24.85	25.27	25.75	26.18	27.29
	12H	20.13	20.50	21.04	21.40	22.56	24.87	25.23	25.77	26.14	27.30
12H	4H	19.75	20.26	20.63	21.15	22.25	24.51	25.03	25.40	25.92	27.02
	6H	20.09	20.51	20.99	21.42	22.52	24.75	25.16	25.65	26.07	27.18
	8H	20.24	20.60	21.14	21.51	22.66	24.86	25.22	25.76	26.13	27.28