

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435937

Luminaire Tested: SQ2W-FB-K-050U-075D-L830-UNV-STD-W-WM-4

Issue Date: 3/24/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1435937  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/24/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-FB-K-050U-075D-L830-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5502.7 lumens  
Efficiency: N/A  
Efficacy: 132.3 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 41.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1435937

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L830-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1435937

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L830-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	91	88	93	89	86	83	78	76	73	68	66	64	58	57	55	51
2	91	83	76	71	85	78	72	67	68	64	60	59	56	53	51	48	46	42
3	82	72	65	58	77	68	61	55	59	54	50	52	47	44	44	41	38	35
4	75	64	55	49	70	60	52	46	52	46	42	46	41	37	39	36	33	29
5	69	56	48	41	64	53	45	39	46	40	36	40	36	32	35	31	28	25
6	63	50	42	36	59	47	40	34	42	35	31	36	31	27	31	27	24	21
7	58	45	37	31	54	43	35	29	37	31	27	33	28	24	28	24	21	19
8	54	41	33	27	50	38	31	26	34	28	23	30	25	21	26	22	19	16
9	50	37	29	24	47	35	28	23	31	25	21	27	22	19	24	20	17	14
10	47	34	26	21	43	32	25	20	28	23	19	25	20	17	22	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5478	5478	5478	5478
5°	5340	9702	5340	9702
10°	5000	18878	5000	18878
15°	4526	21728	4526	21728
20°	4007	22755	4007	22755
25°	3545	23129	3545	23129
30°	3132	23414	3132	23414
35°	2797	25172	2797	25172
40°	2544	26746	2544	26746
45°	2347	28005	2347	28005
50°	2213	28514	2213	28514
55°	2159	28740	2159	28740
60°	2212	28600	2212	28600
65°	2304	27789	2304	27789
70°	2389	21021	2389	21021
75°	2645	11597	2645	11597
80°	2734	10767	2734	10767
85°	2723	4539	2723	4539

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 52.5°  
 Luminance: 29002 cd/sqm



TEST NUMBER: P1435937

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L830-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.8	1.0
10°-20°	259.3	4.7
20°-30°	456.4	8.3
30°-40°	590.8	10.7
40°-50°	651.5	11.8
50°-60°	608.1	11.1
60°-70°	469.8	8.5
70°-80°	216.6	3.9
80°-90°	44.5	0.8
90°-100°	58.6	1.1
100°-110°	170.8	3.1
110°-120°	278.8	5.1
120°-130°	353.7	6.4
130°-140°	378.5	6.9
140°-150°	353.4	6.4
150°-160°	290.8	5.3
160°-170°	195.1	3.5
170°-180°	69.3	1.3
0°-30°	772.6	14.0
0°-40°	1363.3	24.8
0°-60°	2622.9	47.7
0°-90°	3353.7	60.9
90°-120°	508.2	9.2
90°-150°	1593.8	29.0
90°-180°	2149.0	39.1
0°-180°	5502.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	339	339	339	339	339	
5°	330	599	330	599	330	31
15°	271	1300	271	1300	271	75
25°	199	1298	199	1298	199	91
35°	142	1277	142	1277	142	89
45°	103	1226	103	1226	103	80
55°	77	1021	77	1021	77	69
65°	60	727	60	727	60	59
75°	42	186	42	186	42	44
85°	15	24	15	24	15	15
90°	2	16	2	32	2	3
95°	23	17	23	100	23	28
105°	108	174	108	239	108	115
115°	208	288	208	355	208	205
125°	308	457	308	436	308	275
135°	418	598	418	482	418	323
145°	534	690	534	493	534	334
155°	635	749	635	512	635	292
165°	702	781	702	589	702	198
175°	734	765	734	691	734	70
180°	736	736	736	736	736	



TEST NUMBER: P1435937

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3
2.5°	336.6	343.0	349.4	356.2	363.2	370.7	378.8	385.8	389.3	392.8	389.3
5°	329.5	351.2	373.0	404.5	439.3	478.8	523.0	560.9	579.7	598.6	579.7
7.5°	316.7	361.0	405.2	498.9	609.1	723.5	842.1	940.4	978.1	1015.8	978.1
10°	305.0	366.6	428.2	587.2	778.6	925.7	1028.6	1110.9	1131.2	1151.5	1131.2
12.5°	292.0	375.6	459.3	655.5	889.2	1042.1	1114.3	1173.7	1194.6	1215.5	1194.6
15°	270.8	390.4	510.0	731.8	987.7	1145.0	1203.7	1253.5	1276.7	1299.9	1276.7
17.5°	248.9	408.1	567.3	793.6	1042.2	1195.6	1253.7	1300.5	1313.1	1325.7	1313.1
20°	233.2	420.3	607.3	834.0	1074.0	1218.9	1269.0	1308.5	1316.4	1324.4	1316.4
22.5°	218.9	427.9	637.0	864.0	1097.0	1232.4	1270.3	1300.8	1309.3	1317.9	1309.3
25°	199.0	434.6	670.2	896.5	1119.8	1243.4	1267.3	1286.7	1292.5	1298.3	1292.5
27.5°	179.7	428.7	677.6	901.1	1116.1	1231.4	1247.1	1260.3	1265.9	1271.6	1265.9
30°	168.0	421.0	674.0	895.4	1106.4	1217.7	1229.3	1240.0	1247.9	1255.9	1247.9
32.5°	157.6	411.7	665.9	884.6	1091.5	1200.4	1211.4	1224.0	1241.3	1258.5	1241.3
35°	141.9	392.0	642.1	858.5	1063.6	1174.9	1192.3	1213.3	1245.2	1277.1	1245.2
37.5°	128.5	366.7	604.9	819.1	1025.3	1146.5	1182.9	1217.9	1248.7	1279.4	1248.7
40°	120.7	349.0	577.4	790.0	997.3	1125.2	1173.8	1216.8	1242.9	1269.0	1242.9
42.5°	112.9	329.0	545.2	756.0	965.1	1098.0	1154.7	1203.7	1229.8	1255.9	1229.8
45°	102.8	297.0	491.3	700.3	914.1	1054.4	1121.1	1177.2	1201.9	1226.5	1201.9
47.5°	93.3	262.1	430.8	640.7	864.2	1011.4	1082.1	1139.7	1157.7	1175.7	1157.7
50°	88.1	238.9	389.6	600.2	830.7	980.8	1050.4	1106.2	1120.7	1135.2	1120.7
52.5°	82.9	216.2	349.6	560.6	797.5	948.8	1014.3	1066.8	1080.1	1093.5	1080.1
55°	76.7	185.4	294.1	502.9	745.0	894.7	952.0	997.8	1009.4	1021.0	1009.4
57.5°	71.1	158.8	246.5	448.8	689.1	833.8	882.6	921.6	931.0	940.5	931.0
60°	68.5	144.6	220.7	414.8	648.2	787.1	831.3	866.8	876.2	885.7	876.2
62.5°	64.6	130.8	197.1	380.9	603.9	735.7	776.5	809.3	818.1	826.9	818.1
65°	60.3	114.0	167.6	333.3	536.3	654.8	688.8	715.8	721.6	727.4	721.6
67.5°	54.5	100.0	145.5	289.7	466.7	565.8	587.0	600.1	589.2	578.4	589.2
70°	50.6	92.6	134.7	263.1	420.4	502.7	510.0	507.6	476.4	445.3	476.4
72.5°	48.0	85.4	122.8	234.0	369.8	429.8	413.8	387.1	328.1	269.1	328.1
75°	42.4	72.9	103.3	187.0	288.5	304.5	234.9	183.0	184.5	185.9	184.5
77.5°	34.6	57.3	80.1	131.6	192.6	204.7	167.9	140.6	141.9	143.2	141.9
80°	29.4	47.5	65.6	85.9	106.9	116.7	115.3	114.4	115.1	115.8	115.1
82.5°	24.1	37.6	51.1	63.3	75.0	81.6	83.1	83.9	82.9	81.9	82.9
85°	14.7	22.7	30.6	35.3	39.0	37.9	32.1	27.4	25.9	24.5	25.9
87.5°	5.7	9.2	12.8	12.4	10.5	9.5	9.5	9.6	9.8	9.8	9.8
90°	2.2	5.2	8.9	11.9	14.1	14.9	14.9	15.6	16.4	16.4	16.4
92.5°	8.2	12.9	13.1	13.1	15.9	17.2	18.4	18.6	19.3	19.3	19.3
95°	23.0	25.3	37.9	37.2	25.3	20.1	17.1	17.1	17.1	17.1	17.1
97.5°	44.0	47.3	49.4	66.2	69.9	67.5	55.0	46.2	41.3	39.1	41.3
100°	62.4	63.9	68.4	69.1	87.7	105.6	96.6	85.5	81.8	79.5	81.8
102.5°	80.9	81.8	88.6	91.7	96.1	106.2	137.1	133.7	131.1	130.7	131.1
105°	108.5	109.3	121.9	127.9	130.8	130.8	130.1	145.0	168.8	174.0	168.8
107.5°	138.1	141.5	156.4	172.3	175.7	176.6	172.8	170.5	169.6	170.2	169.6
110°	158.3	163.6	181.4	201.5	206.7	208.2	206.7	204.4	203.0	203.0	203.0



TEST NUMBER: P1435937

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	178.0	185.6	205.8	228.8	237.6	242.1	238.8	237.2	235.7	236.9	235.7
115°	208.2	219.3	246.1	269.9	287.7	289.9	289.2	289.2	288.4	288.4	288.4
117.5°	236.1	254.0	284.0	311.6	332.3	338.3	341.2	340.3	339.4	340.9	339.4
120°	255.7	276.6	310.8	342.0	362.0	371.0	373.9	372.5	373.9	372.5	373.9
122.5°	276.6	302.1	335.7	368.1	391.8	401.9	405.5	405.8	406.1	405.2	406.1
125°	307.8	339.0	378.4	411.9	436.4	448.3	451.3	452.0	453.5	457.2	453.5
127.5°	339.3	374.7	418.0	450.2	475.3	489.8	494.4	496.0	499.1	500.8	499.1
130°	361.3	401.4	445.3	475.8	500.3	515.9	524.1	526.3	530.1	529.3	530.1
132.5°	384.5	426.4	470.9	502.6	525.3	542.1	549.1	555.5	556.8	557.9	556.8
135°	418.5	463.9	508.5	539.7	561.3	577.6	586.6	592.5	596.2	598.5	596.2
137.5°	454.4	502.3	545.1	572.9	594.6	608.7	618.8	625.1	628.9	630.7	628.9
140°	478.8	524.9	566.5	595.5	614.8	628.9	637.9	645.3	649.8	649.8	649.8
142.5°	502.0	547.5	587.9	616.9	633.8	646.8	656.3	661.9	667.0	667.0	667.0
145°	534.5	579.9	617.0	646.0	660.2	672.1	682.5	686.9	689.9	689.9	689.9
147.5°	568.6	608.7	642.6	670.4	682.3	696.3	704.5	708.0	711.8	710.1	711.8
150°	588.8	626.0	658.7	684.7	696.6	710.0	718.1	721.1	724.8	722.6	724.8
152.5°	608.4	643.8	673.5	697.8	707.9	721.3	730.6	733.6	736.1	734.5	736.1
155°	634.9	666.1	693.6	715.9	724.8	737.5	746.4	750.1	753.1	749.4	753.1
157.5°	658.5	685.4	709.4	729.9	739.4	750.3	758.6	763.2	766.2	764.5	766.2
160°	672.8	697.3	718.9	738.2	747.1	756.8	765.7	770.9	773.9	771.7	773.9
162.5°	684.7	706.8	727.2	744.8	752.5	761.0	771.7	776.3	779.3	776.4	779.3
165°	701.8	719.6	737.5	752.3	759.0	765.7	776.9	782.1	784.3	781.3	784.3
167.5°	714.7	728.4	742.8	755.6	760.5	767.1	778.2	782.5	785.4	781.6	785.4
170°	721.9	733.8	746.4	756.8	760.5	766.5	777.6	781.3	783.6	779.9	783.6
172.5°	727.8	736.7	747.0	756.2	758.1	762.9	773.5	777.2	778.8	775.7	778.8
175°	733.8	739.0	746.4	752.3	751.6	754.6	763.5	766.5	769.4	765.0	769.4
177.5°	736.6	739.0	741.3	744.9	742.5	742.5	749.1	750.9	751.5	749.1	751.5
180°	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0



TEST NUMBER: P1435937

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3
2.5°	385.8	378.8	370.7	363.2	356.2	349.4	343.0	336.6	343.0	349.4	356.2
5°	560.9	523.0	478.8	439.3	404.5	373.0	351.2	329.5	351.2	373.0	404.5
7.5°	940.4	842.1	723.5	609.1	498.9	405.2	361.0	316.7	361.0	405.2	498.9
10°	1110.9	1028.6	925.7	778.6	587.2	428.2	366.6	305.0	366.6	428.2	587.2
12.5°	1173.7	1114.3	1042.1	889.2	655.5	459.3	375.6	292.0	375.6	459.3	655.5
15°	1253.5	1203.7	1145.0	987.7	731.8	510.0	390.4	270.8	390.4	510.0	731.8
17.5°	1300.5	1253.7	1195.6	1042.2	793.6	567.3	408.1	248.9	408.1	567.3	793.6
20°	1308.5	1269.0	1218.9	1074.0	834.0	607.3	420.3	233.2	420.3	607.3	834.0
22.5°	1300.8	1270.3	1232.4	1097.0	864.0	637.0	427.9	218.9	427.9	637.0	864.0
25°	1286.7	1267.3	1243.4	1119.8	896.5	670.2	434.6	199.0	434.6	670.2	896.5
27.5°	1260.3	1247.1	1231.4	1116.1	901.1	677.6	428.7	179.7	428.7	677.6	901.1
30°	1240.0	1229.3	1217.7	1106.4	895.4	674.0	421.0	168.0	421.0	674.0	895.4
32.5°	1224.0	1211.4	1200.4	1091.5	884.6	665.9	411.7	157.6	411.7	665.9	884.6
35°	1213.3	1192.3	1174.9	1063.6	858.5	642.1	392.0	141.9	392.0	642.1	858.5
37.5°	1217.9	1182.9	1146.5	1025.3	819.1	604.9	366.7	128.5	366.7	604.9	819.1
40°	1216.8	1173.8	1125.2	997.3	790.0	577.4	349.0	120.7	349.0	577.4	790.0
42.5°	1203.7	1154.7	1098.0	965.1	756.0	545.2	329.0	112.9	329.0	545.2	756.0
45°	1177.2	1121.1	1054.4	914.1	700.3	491.3	297.0	102.8	297.0	491.3	700.3
47.5°	1139.7	1082.1	1011.4	864.2	640.7	430.8	262.1	93.3	262.1	430.8	640.7
50°	1106.2	1050.4	980.8	830.7	600.2	389.6	238.9	88.1	238.9	389.6	600.2
52.5°	1066.8	1014.3	948.8	797.5	560.6	349.6	216.2	82.9	216.2	349.6	560.6
55°	997.8	952.0	894.7	745.0	502.9	294.1	185.4	76.7	185.4	294.1	502.9
57.5°	921.6	882.6	833.8	689.1	448.8	246.5	158.8	71.1	158.8	246.5	448.8
60°	866.8	831.3	787.1	648.2	414.8	220.7	144.6	68.5	144.6	220.7	414.8
62.5°	809.3	776.5	735.7	603.9	380.9	197.1	130.8	64.6	130.8	197.1	380.9
65°	715.8	688.8	654.8	536.3	333.3	167.6	114.0	60.3	114.0	167.6	333.3
67.5°	600.1	587.0	565.8	466.7	289.7	145.5	100.0	54.5	100.0	145.5	289.7
70°	507.6	510.0	502.7	420.4	263.1	134.7	92.6	50.6	92.6	134.7	263.1
72.5°	387.1	413.8	429.8	369.8	234.0	122.8	85.4	48.0	85.4	122.8	234.0
75°	183.0	234.9	304.5	288.5	187.0	103.3	72.9	42.4	72.9	103.3	187.0
77.5°	140.6	167.9	204.7	192.6	131.6	80.1	57.3	34.6	57.3	80.1	131.6
80°	114.4	115.3	116.7	106.9	85.9	65.6	47.5	29.4	47.5	65.6	85.9
82.5°	83.9	83.1	81.6	75.0	63.3	51.1	37.6	24.1	37.6	51.1	63.3
85°	27.4	32.1	37.9	39.0	35.3	30.6	22.7	14.7	22.7	30.6	35.3
87.5°	9.6	9.5	9.5	10.5	12.4	12.8	9.2	5.7	9.2	12.7	12.7
90°	15.6	14.9	14.9	14.1	11.9	8.9	5.2	2.2	5.2	8.2	13.4
92.5°	18.6	18.4	17.2	15.9	13.1	13.1	12.9	8.2	14.1	20.1	28.8
95°	17.1	17.1	20.1	25.3	37.2	37.9	25.3	23.0	32.7	46.1	58.0
97.5°	46.2	55.0	67.5	69.9	66.2	49.4	47.3	44.0	59.9	73.2	92.3
100°	85.5	96.6	105.6	87.7	69.1	68.4	63.9	62.4	79.5	92.2	110.8
102.5°	133.7	137.1	106.2	96.1	91.7	88.6	81.8	80.9	98.0	115.4	131.0
105°	145.0	130.1	130.8	130.8	127.9	121.9	109.3	108.5	127.9	147.9	167.3
107.5°	170.5	172.8	176.6	175.7	172.3	156.4	141.5	138.1	155.5	179.6	200.9
110°	204.4	206.7	208.2	206.7	201.5	181.4	163.6	158.3	174.0	199.2	222.3



TEST NUMBER: P1435937

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	237.2	238.8	242.1	237.6	228.8	205.8	185.6	178.0	193.6	219.5	243.1
115°	289.2	289.2	289.9	287.7	269.9	246.1	219.3	208.2	221.5	245.3	271.4
117.5°	340.3	341.2	338.3	332.3	311.6	284.0	254.0	236.1	246.7	271.8	298.6
120°	372.5	373.9	371.0	362.0	342.0	310.8	276.6	255.7	263.9	288.4	315.2
122.5°	405.8	405.5	401.9	391.8	368.1	335.7	302.1	276.6	280.0	302.7	328.9
125°	452.0	451.3	448.3	436.4	411.9	378.4	339.0	307.8	303.3	322.6	349.4
127.5°	496.0	494.4	489.8	475.3	450.2	418.0	374.7	339.3	329.3	341.5	366.1
130°	526.3	524.1	515.9	500.3	475.8	445.3	401.4	361.3	347.2	354.6	376.2
132.5°	555.5	549.1	542.1	525.3	502.6	470.9	426.4	384.5	365.0	368.3	385.1
135°	592.5	586.6	577.6	561.3	539.7	508.5	463.9	418.5	391.8	388.8	398.5
137.5°	625.1	618.8	608.7	594.6	572.9	545.1	502.3	454.4	420.6	410.7	414.4
140°	645.3	637.9	628.9	614.8	595.5	566.5	524.9	478.8	440.9	426.7	424.5
142.5°	661.9	656.3	646.8	633.8	616.9	587.9	547.5	502.0	461.7	443.4	438.2
145°	686.9	682.5	672.1	660.2	646.0	617.0	579.9	534.5	494.4	470.6	459.4
147.5°	708.0	704.5	696.3	682.3	670.4	642.6	608.7	568.6	527.4	497.9	483.5
150°	721.1	718.1	710.0	696.6	684.7	658.7	626.0	588.8	549.4	518.2	499.6
152.5°	733.6	730.6	721.3	707.9	697.8	673.5	643.8	608.4	568.4	537.2	518.0
155°	750.1	746.4	737.5	724.8	715.9	693.6	666.1	634.9	600.7	568.0	546.4
157.5°	763.2	758.6	750.3	739.4	729.9	709.4	685.4	658.5	628.6	597.4	575.4
160°	770.9	765.7	756.8	747.1	738.2	718.9	697.3	672.8	645.3	617.0	593.3
162.5°	776.3	771.7	761.0	752.5	744.8	727.2	706.8	684.7	660.2	635.5	613.5
165°	782.1	776.9	765.7	759.0	752.3	737.5	719.6	701.8	681.0	660.9	643.1
167.5°	782.5	778.2	767.1	760.5	755.6	742.8	728.4	714.7	698.5	682.8	667.9
170°	781.3	777.6	766.5	760.5	756.8	746.4	733.8	721.9	709.2	695.8	684.0
172.5°	777.2	773.5	762.9	758.1	756.2	747.0	736.7	727.8	717.0	707.1	697.6
175°	766.5	763.5	754.6	751.6	752.3	746.4	739.0	733.8	727.1	721.1	715.9
177.5°	750.9	749.1	742.5	742.5	744.9	741.3	739.0	736.6	733.6	731.8	730.0
180°	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0



TEST NUMBER: P1435937

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3
2.5°	363.2	370.7	378.8	385.8	389.3	392.8	389.3	385.8	378.8	370.7	363.2
5°	439.3	478.8	523.0	560.9	579.7	598.6	579.7	560.9	523.0	478.8	439.3
7.5°	609.1	723.5	842.1	940.4	978.1	1015.8	978.1	940.4	842.1	723.5	609.1
10°	778.6	925.7	1028.6	1110.9	1131.2	1151.5	1131.2	1110.9	1028.6	925.7	778.6
12.5°	889.2	1042.1	1114.3	1173.7	1194.6	1215.5	1194.6	1173.7	1114.3	1042.1	889.2
15°	987.7	1145.0	1203.7	1253.5	1276.7	1299.9	1276.7	1253.5	1203.7	1145.0	987.7
17.5°	1042.2	1195.6	1253.7	1300.5	1313.1	1325.7	1313.1	1300.5	1253.7	1195.6	1042.2
20°	1074.0	1218.9	1269.0	1308.5	1316.4	1324.4	1316.4	1308.5	1269.0	1218.9	1074.0
22.5°	1097.0	1232.4	1270.3	1300.8	1309.3	1317.9	1309.3	1300.8	1270.3	1232.4	1097.0
25°	1119.8	1243.4	1267.3	1286.7	1292.5	1298.3	1292.5	1286.7	1267.3	1243.4	1119.8
27.5°	1116.1	1231.4	1247.1	1260.3	1265.9	1271.6	1265.9	1260.3	1247.1	1231.4	1116.1
30°	1106.4	1217.7	1229.3	1240.0	1247.9	1255.9	1247.9	1240.0	1229.3	1217.7	1106.4
32.5°	1091.5	1200.4	1211.4	1224.0	1241.3	1258.5	1241.3	1224.0	1211.4	1200.4	1091.5
35°	1063.6	1174.9	1192.3	1213.3	1245.2	1277.1	1245.2	1213.3	1192.3	1174.9	1063.6
37.5°	1025.3	1146.5	1182.9	1217.9	1248.7	1279.4	1248.7	1217.9	1182.9	1146.5	1025.3
40°	997.3	1125.2	1173.8	1216.8	1242.9	1269.0	1242.9	1216.8	1173.8	1125.2	997.3
42.5°	965.1	1098.0	1154.7	1203.7	1229.8	1255.9	1229.8	1203.7	1154.7	1098.0	965.1
45°	914.1	1054.4	1121.1	1177.2	1201.9	1226.5	1201.9	1177.2	1121.1	1054.4	914.1
47.5°	864.2	1011.4	1082.1	1139.7	1157.7	1175.7	1157.7	1139.7	1082.1	1011.4	864.2
50°	830.7	980.8	1050.4	1106.2	1120.7	1135.2	1120.7	1106.2	1050.4	980.8	830.7
52.5°	797.5	948.8	1014.3	1066.8	1080.1	1093.5	1080.1	1066.8	1014.3	948.8	797.5
55°	745.0	894.7	952.0	997.8	1009.4	1021.0	1009.4	997.8	952.0	894.7	745.0
57.5°	689.1	833.8	882.6	921.6	931.0	940.5	931.0	921.6	882.6	833.8	689.1
60°	648.2	787.1	831.3	866.8	876.2	885.7	876.2	866.8	831.3	787.1	648.2
62.5°	603.9	735.7	776.5	809.3	818.1	826.9	818.1	809.3	776.5	735.7	603.9
65°	536.3	654.8	688.8	715.8	721.6	727.4	721.6	715.8	688.8	654.8	536.3
67.5°	466.7	565.8	587.0	600.1	589.2	578.4	589.2	600.1	587.0	565.8	466.7
70°	420.4	502.7	510.0	507.6	476.4	445.3	476.4	507.6	510.0	502.7	420.4
72.5°	369.8	429.8	413.8	387.1	328.1	269.1	328.1	413.8	429.8	429.8	369.8
75°	288.5	304.5	234.9	183.0	184.5	185.9	184.5	183.0	234.9	304.5	288.5
77.5°	192.6	204.7	167.9	140.6	141.9	143.2	141.9	140.6	167.9	204.7	192.6
80°	106.9	116.7	115.3	114.4	115.1	115.8	115.1	114.4	115.3	116.7	106.9
82.5°	75.0	81.6	83.1	83.9	82.9	81.9	82.9	83.9	83.1	81.6	75.0
85°	39.0	37.9	32.1	27.4	25.9	24.5	25.9	27.4	32.1	37.9	39.0
87.5°	11.1	11.0	12.0	12.6	13.2	12.9	13.2	12.6	12.0	11.0	11.1
90°	17.1	22.3	27.5	30.5	33.5	32.0	33.5	30.5	22.3	17.1	17.1
92.5°	34.3	43.1	49.5	54.9	57.2	56.9	57.2	49.5	43.1	34.3	34.3
95°	69.1	79.5	90.0	97.4	101.8	100.4	101.8	97.4	90.0	79.5	69.1
97.5°	106.6	120.6	132.2	139.2	143.6	146.6	143.6	139.2	132.2	120.6	106.6
100°	131.6	145.0	158.3	166.5	174.0	176.9	174.0	166.5	158.3	145.0	131.6
102.5°	151.8	169.4	183.9	192.7	198.9	201.9	198.9	192.7	183.9	169.4	151.8
105°	185.1	203.7	219.3	230.5	237.2	239.4	237.2	230.5	219.3	203.7	185.1
107.5°	218.4	237.6	252.0	264.4	272.5	277.3	272.5	264.4	252.0	237.6	218.4
110°	244.6	260.2	275.8	287.0	295.1	298.1	295.1	287.0	275.8	260.2	244.6



TEST NUMBER: P1435937

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	266.6	284.0	299.6	310.8	320.1	324.3	320.1	310.8	299.6	284.0	266.6
115°	297.4	320.4	334.5	344.9	351.6	355.4	351.6	344.9	334.5	320.4	297.4
117.5°	322.9	347.0	362.5	370.5	373.6	376.3	373.6	370.5	362.5	347.0	322.9
120°	339.0	361.3	379.1	389.6	393.3	394.8	393.3	389.6	379.1	361.3	339.0
122.5°	353.9	375.0	392.2	405.0	411.1	412.6	411.1	405.0	392.2	375.0	353.9
125°	374.7	394.8	412.6	425.2	431.9	435.6	431.9	425.2	412.6	394.8	374.7
127.5°	392.8	414.5	430.9	442.3	448.9	451.9	448.9	442.3	430.9	414.5	392.8
130°	402.9	425.2	441.6	454.2	460.2	463.2	460.2	454.2	441.6	425.2	402.9
132.5°	410.7	434.2	451.1	462.6	469.1	472.1	469.1	462.6	451.1	434.2	410.7
135°	420.0	444.6	462.4	473.6	479.5	482.5	479.5	473.6	462.4	444.6	420.0
137.5°	428.2	450.5	469.1	480.8	486.2	488.1	486.2	480.8	469.1	450.5	428.2
140°	434.2	453.5	472.1	483.2	489.2	489.9	489.2	483.2	472.1	453.5	434.2
142.5°	441.9	457.1	473.3	484.4	490.4	491.7	490.4	484.4	473.3	457.1	441.9
145°	455.7	464.6	475.8	486.2	491.4	492.9	491.4	486.2	475.8	464.6	455.7
147.5°	473.1	475.9	481.7	488.6	493.6	494.7	493.6	488.6	481.7	475.9	473.1
150°	486.2	485.5	487.7	492.1	496.6	495.9	496.6	492.1	487.7	485.5	486.2
152.5°	501.1	496.8	496.6	498.7	500.8	500.6	500.8	498.7	496.6	496.8	501.1
155°	526.3	518.2	513.7	512.2	512.2	511.5	512.2	512.2	513.7	518.2	526.3
157.5°	554.1	542.7	536.0	532.4	531.4	529.8	531.4	532.4	536.0	542.7	554.1
160°	573.2	560.5	553.9	547.9	545.7	543.4	545.7	547.9	553.9	560.5	573.2
162.5°	591.0	579.0	571.7	566.3	564.1	560.7	564.1	566.3	571.7	579.0	591.0
165°	620.0	607.4	599.2	594.7	591.8	588.8	591.8	594.7	599.2	607.4	620.0
167.5°	649.0	635.2	629.8	624.8	621.9	616.6	621.9	624.8	629.8	635.2	649.0
170°	666.9	654.2	651.2	646.8	641.6	635.6	641.6	646.8	651.2	654.2	666.9
172.5°	682.3	673.8	670.9	666.4	664.8	660.0	664.8	666.4	670.9	673.8	682.3
175°	704.8	698.1	698.1	697.3	695.1	690.6	695.1	697.3	698.1	698.1	704.8
177.5°	723.5	719.9	722.3	722.3	721.7	717.6	721.7	722.3	722.3	719.9	723.5
180°	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0



TEST NUMBER: P1435937

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	339.3	339.3	339.3	339.3
2.5°	356.2	349.4	343.0	336.6
5°	404.5	373.0	351.2	329.5
7.5°	498.9	405.2	361.0	316.7
10°	587.2	428.2	366.6	305.0
12.5°	655.5	459.3	375.6	292.0
15°	731.8	510.0	390.4	270.8
17.5°	793.6	567.3	408.1	248.9
20°	834.0	607.3	420.3	233.2
22.5°	864.0	637.0	427.9	218.9
25°	896.5	670.2	434.6	199.0
27.5°	901.1	677.6	428.7	179.7
30°	895.4	674.0	421.0	168.0
32.5°	884.6	665.9	411.7	157.6
35°	858.5	642.1	392.0	141.9
37.5°	819.1	604.9	366.7	128.5
40°	790.0	577.4	349.0	120.7
42.5°	756.0	545.2	329.0	112.9
45°	700.3	491.3	297.0	102.8
47.5°	640.7	430.8	262.1	93.3
50°	600.2	389.6	238.9	88.1
52.5°	560.6	349.6	216.2	82.9
55°	502.9	294.1	185.4	76.7
57.5°	448.8	246.5	158.8	71.1
60°	414.8	220.7	144.6	68.5
62.5°	380.9	197.1	130.8	64.6
65°	333.3	167.6	114.0	60.3
67.5°	289.7	145.5	100.0	54.5
70°	263.1	134.7	92.6	50.6
72.5°	234.0	122.8	85.4	48.0
75°	187.0	103.3	72.9	42.4
77.5°	131.6	80.1	57.3	34.6
80°	85.9	65.6	47.5	29.4
82.5°	63.3	51.1	37.6	24.1
85°	35.3	30.6	22.7	14.7
87.5°	12.7	12.7	9.2	5.7
90°	13.4	8.2	5.2	2.2
92.5°	28.8	20.1	14.1	8.2
95°	58.0	46.1	32.7	23.0
97.5°	92.3	73.2	59.9	44.0
100°	110.8	92.2	79.5	62.4
102.5°	131.0	115.4	98.0	80.9
105°	167.3	147.9	127.9	108.5
107.5°	200.9	179.6	155.5	138.1
110°	222.3	199.2	174.0	158.3



TEST NUMBER: P1435937

CATALOG NUMBER: SQ2W-FB-K-050U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	243.1	219.5	193.6	178.0
115°	271.4	245.3	221.5	208.2
117.5°	298.6	271.8	246.7	236.1
120°	315.2	288.4	263.9	255.7
122.5°	328.9	302.7	280.0	276.6
125°	349.4	322.6	303.3	307.8
127.5°	366.1	341.5	329.3	339.3
130°	376.2	354.6	347.2	361.3
132.5°	385.1	368.3	365.0	384.5
135°	398.5	388.8	391.8	418.5
137.5°	414.4	410.7	420.6	454.4
140°	424.5	426.7	440.9	478.8
142.5°	438.2	443.4	461.7	502.0
145°	459.4	470.6	494.4	534.5
147.5°	483.5	497.9	527.4	568.6
150°	499.6	518.2	549.4	588.8
152.5°	518.0	537.2	568.4	608.4
155°	546.4	568.0	600.7	634.9
157.5°	575.4	597.4	628.6	658.5
160°	593.3	617.0	645.3	672.8
162.5°	613.5	635.5	660.2	684.7
165°	643.1	660.9	681.0	701.8
167.5°	667.9	682.8	698.5	714.7
170°	684.0	695.8	709.2	721.9
172.5°	697.6	707.1	717.0	727.8
175°	715.9	721.1	727.1	733.8
177.5°	730.0	731.8	733.6	736.6
180°	736.0	736.0	736.0	736.0



TEST NUMBER: P1435937  
 CATALOG NUMBER: SQ2W-FB-K-050U-075D-L830-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.03	14.03	13.88	14.91	16.01	22.62	23.63	23.47	24.50	25.61
	3H	13.98	14.88	14.84	15.76	16.89	24.24	25.14	25.10	26.03	27.16
	4H	14.38	15.23	15.26	16.13	17.27	24.42	25.28	25.30	26.17	27.31
	6H	14.64	15.43	15.54	16.33	17.48	24.51	25.29	25.40	26.19	27.35
	8H	14.74	15.49	15.64	16.41	17.56	24.53	25.28	25.43	26.20	27.35
	12H	14.79	15.51	15.70	16.42	17.60	24.51	25.22	25.42	26.14	27.32
4H	2H	17.76	18.62	18.65	19.51	20.65	23.01	23.86	23.89	24.75	25.89
	3H	18.91	19.62	19.80	20.54	21.70	24.91	25.62	25.80	26.54	27.70
	4H	19.19	19.84	20.10	20.76	21.94	25.14	25.78	26.04	26.70	27.89
	6H	19.34	19.90	20.26	20.84	22.02	25.28	25.84	26.20	26.78	27.96
	8H	19.38	19.90	20.31	20.84	22.04	25.33	25.85	26.25	26.79	27.98
	12H	19.39	19.86	20.34	20.82	22.02	25.31	25.78	26.26	26.74	27.94
8H	4H	20.40	20.92	21.33	21.86	23.06	25.24	25.76	26.17	26.70	27.90
	6H	20.66	21.10	21.62	22.08	23.27	25.44	25.87	26.40	26.85	28.05
	8H	20.76	21.15	21.73	22.12	23.33	25.54	25.92	26.50	26.89	28.10
	12H	20.81	21.15	21.78	22.11	23.37	25.55	25.88	26.51	26.85	28.11
12H	4H	20.43	20.90	21.38	21.86	23.06	25.20	25.67	26.14	26.63	27.83
	6H	20.77	21.16	21.74	22.13	23.34	25.43	25.81	26.39	26.78	27.99
	8H	20.92	21.25	21.88	22.22	23.48	25.54	25.87	26.50	26.83	28.10