

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435985

Luminaire Tested: SQ2W-FB-K-100U-075D-L830-UNV-STD-W-WM-4

Issue Date: 3/24/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1435985  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/24/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-FB-K-100U-075D-L830-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7728.3 lumens  
Efficiency: N/A  
Efficacy: 129.2 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1435985

CATALOG NUMBER: SQ2W-FB-K-100U-075D-L830-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1435985

CATALOG NUMBER: SQ2W-FB-K-100U-075D-L830-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	96	92	88	84	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	87	80	74	68	79	73	68	63	61	57	53	49	46	44	38	36	35	30
3	79	70	62	56	72	64	57	52	53	48	44	43	39	37	34	31	29	25
4	72	61	53	47	66	56	49	44	47	41	37	38	34	31	30	27	25	21
5	66	54	46	40	60	50	43	37	41	36	32	34	30	26	26	23	21	18
6	61	48	40	34	55	45	37	32	37	31	27	30	26	23	24	21	18	15
7	56	43	35	30	51	40	33	28	33	28	24	27	23	20	21	18	16	13
8	52	39	31	26	47	36	29	24	30	25	21	25	21	17	20	16	14	12
9	48	36	28	23	44	33	26	21	28	22	18	23	18	15	18	15	13	10
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	16	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5478	5478	5478	5478
5°	5340	9702	5340	9702
10°	5000	18878	5000	18878
15°	4526	21728	4526	21728
20°	4007	22755	4007	22755
25°	3545	23129	3545	23129
30°	3132	23414	3132	23414
35°	2797	25172	2797	25172
40°	2544	26746	2544	26746
45°	2347	28005	2347	28005
50°	2213	28514	2213	28514
55°	2159	28740	2159	28740
60°	2212	28600	2212	28600
65°	2304	27789	2304	27789
70°	2389	21021	2389	21021
75°	2645	11597	2645	11597
80°	2734	10767	2734	10767
85°	2723	4539	2723	4539

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 52.5°  
 Luminance: 29002 cd/sqm



TEST NUMBER: P1435985

CATALOG NUMBER: SQ2W-FB-K-100U-075D-L830-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.8	0.7
10°-20°	259.3	3.4
20°-30°	456.4	5.9
30°-40°	590.8	7.6
40°-50°	651.5	8.4
50°-60°	608.1	7.9
60°-70°	469.8	6.1
70°-80°	216.6	2.8
80°-90°	47.6	0.6
90°-100°	119.2	1.5
100°-110°	347.5	4.5
110°-120°	567.1	7.3
120°-130°	719.6	9.3
130°-140°	770.0	10.0
140°-150°	719.0	9.3
150°-160°	591.6	7.7
160°-170°	396.8	5.1
170°-180°	140.9	1.8
0°-30°	772.6	10.0
0°-40°	1363.3	17.6
0°-60°	2622.9	33.9
0°-90°	3356.9	43.4
90°-120°	1033.7	13.4
90°-150°	3242.2	42.0
90°-180°	4371.0	56.6
0°-180°	7728.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	339	339	339	339	339	
5°	330	599	330	599	330	31
15°	271	1300	271	1300	271	75
25°	199	1298	199	1298	199	91
35°	142	1277	142	1277	142	89
45°	103	1226	103	1226	103	80
55°	77	1021	77	1021	77	69
65°	60	727	60	727	60	59
75°	42	186	42	186	42	44
85°	15	24	15	24	15	15
90°	4	33	4	65	4	4
95°	47	35	47	204	47	57
105°	221	354	221	487	221	235
115°	423	587	423	723	423	417
125°	626	930	626	886	626	560
135°	851	1217	851	982	851	658
145°	1087	1403	1087	1003	1087	680
155°	1292	1524	1292	1040	1292	594
165°	1428	1589	1428	1198	1428	402
175°	1493	1556	1493	1405	1493	142
180°	1497	1497	1497	1497	1497	



TEST NUMBER: P1435985

CATALOG NUMBER: SQ2W-FB-K-100U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3
2.5°	336.6	343.0	349.4	356.2	363.2	370.7	378.8	385.8	389.3	392.8	389.3
5°	329.5	351.2	373.0	404.5	439.3	478.8	523.0	560.9	579.7	598.6	579.7
7.5°	316.7	361.0	405.2	498.9	609.1	723.5	842.1	940.4	978.1	1015.8	978.1
10°	305.0	366.6	428.2	587.2	778.6	925.7	1028.6	1110.9	1131.2	1151.5	1131.2
12.5°	292.0	375.6	459.3	655.5	889.2	1042.1	1114.3	1173.7	1194.6	1215.5	1194.6
15°	270.8	390.4	510.0	731.8	987.7	1145.0	1203.7	1253.5	1276.7	1299.9	1276.7
17.5°	248.9	408.1	567.3	793.6	1042.2	1195.6	1253.7	1300.5	1313.1	1325.7	1313.1
20°	233.2	420.3	607.3	834.0	1074.0	1218.9	1269.0	1308.5	1316.4	1324.4	1316.4
22.5°	218.9	427.9	637.0	864.0	1097.0	1232.4	1270.3	1300.8	1309.3	1317.9	1309.3
25°	199.0	434.6	670.2	896.5	1119.8	1243.4	1267.3	1286.7	1292.5	1298.3	1292.5
27.5°	179.7	428.7	677.6	901.1	1116.1	1231.4	1247.1	1260.3	1265.9	1271.6	1265.9
30°	168.0	421.0	674.0	895.4	1106.4	1217.7	1229.3	1240.0	1247.9	1255.9	1247.9
32.5°	157.6	411.7	665.9	884.6	1091.5	1200.4	1211.4	1224.0	1241.3	1258.5	1241.3
35°	141.9	392.0	642.1	858.5	1063.6	1174.9	1192.3	1213.3	1245.2	1277.1	1245.2
37.5°	128.5	366.7	604.9	819.1	1025.3	1146.5	1182.9	1217.9	1248.7	1279.4	1248.7
40°	120.7	349.0	577.4	790.0	997.3	1125.2	1173.8	1216.8	1242.9	1269.0	1242.9
42.5°	112.9	329.0	545.2	756.0	965.1	1098.0	1154.7	1203.7	1229.8	1255.9	1229.8
45°	102.8	297.0	491.3	700.3	914.1	1054.4	1121.1	1177.2	1201.9	1226.5	1201.9
47.5°	93.3	262.1	430.8	640.7	864.2	1011.4	1082.1	1139.7	1157.7	1175.7	1157.7
50°	88.1	238.9	389.6	600.2	830.7	980.8	1050.4	1106.2	1120.7	1135.2	1120.7
52.5°	82.9	216.2	349.6	560.6	797.5	948.8	1014.3	1066.8	1080.1	1093.5	1080.1
55°	76.7	185.4	294.1	502.9	745.0	894.7	952.0	997.8	1009.4	1021.0	1009.4
57.5°	71.1	158.8	246.5	448.8	689.1	833.8	882.6	921.6	931.0	940.5	931.0
60°	68.5	144.6	220.7	414.8	648.2	787.1	831.3	866.8	876.2	885.7	876.2
62.5°	64.6	130.8	197.1	380.9	603.9	735.7	776.5	809.3	818.1	826.9	818.1
65°	60.3	114.0	167.6	333.3	536.3	654.8	688.8	715.8	721.6	727.4	721.6
67.5°	54.5	100.0	145.5	289.7	466.7	565.8	587.0	600.1	589.2	578.4	589.2
70°	50.6	92.6	134.7	263.1	420.4	502.7	510.0	507.6	476.4	445.3	476.4
72.5°	48.0	85.4	122.8	234.0	369.8	429.8	413.8	387.1	328.1	269.1	328.1
75°	42.4	72.9	103.3	187.0	288.5	304.5	234.9	183.0	184.5	185.9	184.5
77.5°	34.6	57.3	80.1	131.6	192.6	204.7	167.9	140.6	141.9	143.2	141.9
80°	29.4	47.5	65.6	85.9	106.9	116.7	115.3	114.4	115.1	115.8	115.1
82.5°	24.1	37.6	51.1	63.3	75.0	81.6	83.1	83.9	82.9	81.9	82.9
85°	14.7	22.7	30.6	35.3	39.0	37.9	32.1	27.4	25.9	24.5	25.9
87.5°	6.1	10.2	14.6	14.8	13.4	12.6	12.6	12.9	13.2	13.2	13.2
90°	4.5	10.6	18.1	24.2	28.7	30.2	30.2	31.8	33.3	33.3	33.3
92.5°	16.6	26.3	26.6	26.6	32.4	35.1	37.5	37.8	39.3	39.3	39.3
95°	46.9	51.4	77.1	75.6	51.4	40.8	34.8	34.8	34.8	34.8	34.8
97.5°	89.5	96.2	100.4	134.6	142.2	137.3	111.9	94.1	84.1	79.5	84.1
100°	127.0	130.1	139.1	140.6	178.4	214.7	196.6	173.9	166.4	161.8	166.4
102.5°	164.5	166.4	180.3	186.6	195.4	216.0	278.9	271.9	266.8	265.9	266.8
105°	220.8	222.3	248.0	260.1	266.2	266.2	264.7	294.9	343.3	353.9	343.3
107.5°	281.0	287.9	318.2	350.5	357.5	359.3	351.5	346.9	345.1	346.3	345.1
110°	322.1	332.7	369.0	409.8	420.4	423.4	420.4	415.9	412.9	412.9	412.9



TEST NUMBER: P1435985

CATALOG NUMBER: SQ2W-FB-K-100U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	362.0	377.5	418.6	465.5	483.3	492.4	485.7	482.4	479.4	481.8	479.4
115°	423.4	446.1	500.6	549.0	585.3	589.8	588.3	588.3	586.8	586.8	586.8
117.5°	480.3	516.6	577.7	634.0	676.0	688.1	694.1	692.3	690.5	693.5	690.5
120°	520.2	562.6	632.1	695.7	736.5	754.6	760.7	757.7	760.7	757.7	760.7
122.5°	562.6	614.6	682.9	748.9	797.0	817.5	824.8	825.4	826.0	824.2	826.0
125°	626.1	689.6	769.8	837.8	887.7	911.9	918.0	919.5	922.5	930.1	922.5
127.5°	690.2	762.2	850.2	915.8	967.0	996.3	1005.7	1009.0	1015.3	1018.7	1015.3
130°	735.0	816.6	905.9	967.9	1017.8	1049.5	1066.2	1070.7	1078.3	1076.7	1078.3
132.5°	782.2	867.4	957.9	1022.3	1068.6	1102.8	1117.0	1130.0	1132.7	1134.8	1132.7
135°	851.4	943.7	1034.4	1097.9	1141.8	1175.0	1193.2	1205.3	1212.9	1217.4	1212.9
137.5°	924.3	1021.7	1108.8	1165.4	1209.5	1238.3	1258.8	1271.5	1279.4	1283.0	1279.4
140°	973.9	1067.7	1152.4	1211.3	1250.7	1279.4	1297.5	1312.7	1321.7	1321.7	1321.7
142.5°	1021.1	1113.6	1195.9	1254.9	1289.4	1315.7	1335.0	1346.5	1356.8	1356.8	1356.8
145°	1087.3	1179.6	1255.2	1314.2	1342.9	1367.1	1388.3	1397.4	1403.4	1403.4	1403.4
147.5°	1156.6	1238.3	1307.2	1363.8	1388.0	1416.4	1433.0	1440.3	1447.9	1444.5	1447.9
150°	1197.7	1273.3	1339.9	1392.8	1417.0	1444.2	1460.9	1466.9	1474.5	1469.9	1474.5
152.5°	1237.7	1309.6	1370.1	1419.4	1440.0	1467.2	1486.3	1492.3	1497.5	1494.1	1497.5
155°	1291.5	1355.0	1411.0	1456.3	1474.5	1500.2	1518.3	1525.9	1531.9	1524.4	1531.9
157.5°	1339.6	1394.3	1443.0	1484.8	1504.1	1526.2	1543.1	1552.5	1558.6	1555.2	1558.6
160°	1368.6	1418.5	1462.4	1501.7	1519.8	1539.5	1557.7	1568.2	1574.3	1569.8	1574.3
162.5°	1392.8	1437.9	1479.3	1515.0	1530.7	1548.0	1569.8	1579.1	1585.2	1579.4	1585.2
165°	1427.6	1463.9	1500.2	1530.4	1544.0	1557.7	1580.3	1590.9	1595.5	1589.4	1595.5
167.5°	1453.9	1481.7	1511.1	1537.1	1547.1	1560.4	1583.1	1591.8	1597.6	1590.0	1597.6
170°	1468.4	1492.6	1518.3	1539.5	1547.1	1559.2	1581.9	1589.4	1593.9	1586.4	1593.9
172.5°	1480.5	1498.7	1519.5	1538.3	1542.2	1551.9	1573.4	1580.9	1584.3	1577.9	1584.3
175°	1492.6	1503.2	1518.3	1530.4	1528.9	1535.0	1553.1	1559.2	1565.2	1556.1	1565.2
177.5°	1498.4	1503.2	1508.1	1515.3	1510.5	1510.5	1523.8	1527.4	1528.6	1523.8	1528.6
180°	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2



TEST NUMBER: P1435985

CATALOG NUMBER: SQ2W-FB-K-100U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3
2.5°	385.8	378.8	370.7	363.2	356.2	349.4	343.0	336.6	343.0	349.4	356.2
5°	560.9	523.0	478.8	439.3	404.5	373.0	351.2	329.5	351.2	373.0	404.5
7.5°	940.4	842.1	723.5	609.1	498.9	405.2	361.0	316.7	361.0	405.2	498.9
10°	1110.9	1028.6	925.7	778.6	587.2	428.2	366.6	305.0	366.6	428.2	587.2
12.5°	1173.7	1114.3	1042.1	889.2	655.5	459.3	375.6	292.0	375.6	459.3	655.5
15°	1253.5	1203.7	1145.0	987.7	731.8	510.0	390.4	270.8	390.4	510.0	731.8
17.5°	1300.5	1253.7	1195.6	1042.2	793.6	567.3	408.1	248.9	408.1	567.3	793.6
20°	1308.5	1269.0	1218.9	1074.0	834.0	607.3	420.3	233.2	420.3	607.3	834.0
22.5°	1300.8	1270.3	1232.4	1097.0	864.0	637.0	427.9	218.9	427.9	637.0	864.0
25°	1286.7	1267.3	1243.4	1119.8	896.5	670.2	434.6	199.0	434.6	670.2	896.5
27.5°	1260.3	1247.1	1231.4	1116.1	901.1	677.6	428.7	179.7	428.7	677.6	901.1
30°	1240.0	1229.3	1217.7	1106.4	895.4	674.0	421.0	168.0	421.0	674.0	895.4
32.5°	1224.0	1211.4	1200.4	1091.5	884.6	665.9	411.7	157.6	411.7	665.9	884.6
35°	1213.3	1192.3	1174.9	1063.6	858.5	642.1	392.0	141.9	392.0	642.1	858.5
37.5°	1217.9	1182.9	1146.5	1025.3	819.1	604.9	366.7	128.5	366.7	604.9	819.1
40°	1216.8	1173.8	1125.2	997.3	790.0	577.4	349.0	120.7	349.0	577.4	790.0
42.5°	1203.7	1154.7	1098.0	965.1	756.0	545.2	329.0	112.9	329.0	545.2	756.0
45°	1177.2	1121.1	1054.4	914.1	700.3	491.3	297.0	102.8	297.0	491.3	700.3
47.5°	1139.7	1082.1	1011.4	864.2	640.7	430.8	262.1	93.3	262.1	430.8	640.7
50°	1106.2	1050.4	980.8	830.7	600.2	389.6	238.9	88.1	238.9	389.6	600.2
52.5°	1066.8	1014.3	948.8	797.5	560.6	349.6	216.2	82.9	216.2	349.6	560.6
55°	997.8	952.0	894.7	745.0	502.9	294.1	185.4	76.7	185.4	294.1	502.9
57.5°	921.6	882.6	833.8	689.1	448.8	246.5	158.8	71.1	158.8	246.5	448.8
60°	866.8	831.3	787.1	648.2	414.8	220.7	144.6	68.5	144.6	220.7	414.8
62.5°	809.3	776.5	735.7	603.9	380.9	197.1	130.8	64.6	130.8	197.1	380.9
65°	715.8	688.8	654.8	536.3	333.3	167.6	114.0	60.3	114.0	167.6	333.3
67.5°	600.1	587.0	565.8	466.7	289.7	145.5	100.0	54.5	100.0	145.5	289.7
70°	507.6	510.0	502.7	420.4	263.1	134.7	92.6	50.6	92.6	134.7	263.1
72.5°	387.1	413.8	429.8	369.8	234.0	122.8	85.4	48.0	85.4	122.8	234.0
75°	183.0	234.9	304.5	288.5	187.0	103.3	72.9	42.4	72.9	103.3	187.0
77.5°	140.6	167.9	204.7	192.6	131.6	80.1	57.3	34.6	57.3	80.1	131.6
80°	114.4	115.3	116.7	106.9	85.9	65.6	47.5	29.4	47.5	65.6	85.9
82.5°	83.9	83.1	81.6	75.0	63.3	51.1	37.6	24.1	37.6	51.1	63.3
85°	27.4	32.1	37.9	39.0	35.3	30.6	22.7	14.7	22.7	30.6	35.3
87.5°	12.9	12.6	12.6	13.4	14.8	14.6	10.2	6.1	10.2	14.3	15.4
90°	31.8	30.2	30.2	28.7	24.2	18.1	10.6	4.5	10.6	16.6	27.2
92.5°	37.8	37.5	35.1	32.4	26.6	26.6	26.3	16.6	28.7	40.8	58.7
95°	34.8	34.8	40.8	51.4	75.6	77.1	51.4	46.9	66.5	93.8	118.0
97.5°	94.1	111.9	137.3	142.2	134.6	100.4	96.2	89.5	121.9	148.8	187.8
100°	173.9	196.6	214.7	178.4	140.6	139.1	130.1	127.0	161.8	187.5	225.3
102.5°	271.9	278.9	216.0	195.4	186.6	180.3	166.4	164.5	199.3	234.7	266.5
105°	294.9	264.7	266.2	266.2	260.1	248.0	222.3	220.8	260.1	300.9	340.3
107.5°	346.9	351.5	359.3	357.5	350.5	318.2	287.9	281.0	316.4	365.4	408.6
110°	415.9	420.4	423.4	420.4	409.8	369.0	332.7	322.1	353.9	405.3	452.2



TEST NUMBER: P1435985

CATALOG NUMBER: SQ2W-FB-K-100U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	482.4	485.7	492.4	483.3	465.5	418.6	377.5	362.0	393.8	446.4	494.5
115°	588.3	588.3	589.8	585.3	549.0	500.6	446.1	423.4	450.7	499.1	552.0
117.5°	692.3	694.1	688.1	676.0	634.0	577.7	516.6	480.3	501.8	552.9	607.3
120°	757.7	760.7	754.6	736.5	695.7	632.1	562.6	520.2	536.9	586.8	641.2
122.5°	825.4	824.8	817.5	797.0	748.9	682.9	614.6	562.6	569.5	615.8	669.0
125°	919.5	918.0	911.9	887.7	837.8	769.8	689.6	626.1	617.0	656.3	710.8
127.5°	1009.0	1005.7	996.3	967.0	915.8	850.2	762.2	690.2	669.9	694.7	744.6
130°	1070.7	1066.2	1049.5	1017.8	967.9	905.9	816.6	735.0	706.2	721.4	765.2
132.5°	1130.0	1117.0	1102.8	1068.6	1022.3	957.9	867.4	782.2	742.5	749.2	783.4
135°	1205.3	1193.2	1175.0	1141.8	1097.9	1034.4	943.7	851.4	797.0	790.9	810.6
137.5°	1271.5	1258.8	1238.3	1209.5	1165.4	1108.8	1021.7	924.3	855.7	835.4	842.9
140°	1312.7	1297.5	1279.4	1250.7	1211.3	1152.4	1067.7	973.9	896.8	868.1	863.5
142.5°	1346.5	1335.0	1315.7	1289.4	1254.9	1195.9	1113.6	1021.1	939.1	901.9	891.3
145°	1397.4	1388.3	1367.1	1342.9	1314.2	1255.2	1179.6	1087.3	1005.7	957.3	934.6
147.5°	1440.3	1433.0	1416.4	1388.0	1363.8	1307.2	1238.3	1156.6	1072.8	1012.9	983.6
150°	1466.9	1460.9	1444.2	1417.0	1392.8	1339.9	1273.3	1197.7	1117.6	1054.1	1016.3
152.5°	1492.3	1486.3	1467.2	1440.0	1419.4	1370.1	1309.6	1237.7	1156.3	1092.8	1053.8
155°	1525.9	1518.3	1500.2	1474.5	1456.3	1411.0	1355.0	1291.5	1221.9	1155.4	1111.5
157.5°	1552.5	1543.1	1526.2	1504.1	1484.8	1443.0	1394.3	1339.6	1278.8	1215.3	1170.5
160°	1568.2	1557.7	1539.5	1519.8	1501.7	1462.4	1418.5	1368.6	1312.7	1255.2	1206.8
162.5°	1579.1	1569.8	1548.0	1530.7	1515.0	1479.3	1437.9	1392.8	1342.9	1292.7	1247.9
165°	1590.9	1580.3	1557.7	1544.0	1530.4	1500.2	1463.9	1427.6	1385.3	1344.4	1308.1
167.5°	1591.8	1583.1	1560.4	1547.1	1537.1	1511.1	1481.7	1453.9	1420.9	1388.9	1358.6
170°	1589.4	1581.9	1559.2	1547.1	1539.5	1518.3	1492.6	1468.4	1442.7	1415.5	1391.3
172.5°	1580.9	1573.4	1551.9	1542.2	1538.3	1519.5	1498.7	1480.5	1458.4	1438.5	1419.1
175°	1559.2	1553.1	1535.0	1528.9	1530.4	1518.3	1503.2	1492.6	1479.0	1466.9	1456.3
177.5°	1527.4	1523.8	1510.5	1510.5	1515.3	1508.1	1503.2	1498.4	1492.3	1488.7	1485.1
180°	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2



TEST NUMBER: P1435985

CATALOG NUMBER: SQ2W-FB-K-100U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3	339.3
2.5°	363.2	370.7	378.8	385.8	389.3	392.8	389.3	385.8	378.8	370.7	363.2
5°	439.3	478.8	523.0	560.9	579.7	598.6	579.7	560.9	523.0	478.8	439.3
7.5°	609.1	723.5	842.1	940.4	978.1	1015.8	978.1	940.4	842.1	723.5	609.1
10°	778.6	925.7	1028.6	1110.9	1131.2	1151.5	1131.2	1110.9	1028.6	925.7	778.6
12.5°	889.2	1042.1	1114.3	1173.7	1194.6	1215.5	1194.6	1173.7	1114.3	1042.1	889.2
15°	987.7	1145.0	1203.7	1253.5	1276.7	1299.9	1276.7	1253.5	1203.7	1145.0	987.7
17.5°	1042.2	1195.6	1253.7	1300.5	1313.1	1325.7	1313.1	1300.5	1253.7	1195.6	1042.2
20°	1074.0	1218.9	1269.0	1308.5	1316.4	1324.4	1316.4	1308.5	1269.0	1218.9	1074.0
22.5°	1097.0	1232.4	1270.3	1300.8	1309.3	1317.9	1309.3	1300.8	1270.3	1232.4	1097.0
25°	1119.8	1243.4	1267.3	1286.7	1292.5	1298.3	1292.5	1286.7	1267.3	1243.4	1119.8
27.5°	1116.1	1231.4	1247.1	1260.3	1265.9	1271.6	1265.9	1260.3	1247.1	1231.4	1116.1
30°	1106.4	1217.7	1229.3	1240.0	1247.9	1255.9	1247.9	1240.0	1229.3	1217.7	1106.4
32.5°	1091.5	1200.4	1211.4	1224.0	1241.3	1258.5	1241.3	1224.0	1211.4	1200.4	1091.5
35°	1063.6	1174.9	1192.3	1213.3	1245.2	1277.1	1245.2	1213.3	1192.3	1174.9	1063.6
37.5°	1025.3	1146.5	1182.9	1217.9	1248.7	1279.4	1248.7	1217.9	1182.9	1146.5	1025.3
40°	997.3	1125.2	1173.8	1216.8	1242.9	1269.0	1242.9	1216.8	1173.8	1125.2	997.3
42.5°	965.1	1098.0	1154.7	1203.7	1229.8	1255.9	1229.8	1203.7	1154.7	1098.0	965.1
45°	914.1	1054.4	1121.1	1177.2	1201.9	1226.5	1201.9	1177.2	1121.1	1054.4	914.1
47.5°	864.2	1011.4	1082.1	1139.7	1157.7	1175.7	1157.7	1139.7	1082.1	1011.4	864.2
50°	830.7	980.8	1050.4	1106.2	1120.7	1135.2	1120.7	1106.2	1050.4	980.8	830.7
52.5°	797.5	948.8	1014.3	1066.8	1080.1	1093.5	1080.1	1066.8	1014.3	948.8	797.5
55°	745.0	894.7	952.0	997.8	1009.4	1021.0	1009.4	997.8	952.0	894.7	745.0
57.5°	689.1	833.8	882.6	921.6	931.0	940.5	931.0	921.6	882.6	833.8	689.1
60°	648.2	787.1	831.3	866.8	876.2	885.7	876.2	866.8	831.3	787.1	648.2
62.5°	603.9	735.7	776.5	809.3	818.1	826.9	818.1	809.3	776.5	735.7	603.9
65°	536.3	654.8	688.8	715.8	721.6	727.4	721.6	715.8	688.8	654.8	536.3
67.5°	466.7	565.8	587.0	600.1	589.2	578.4	589.2	600.1	587.0	565.8	466.7
70°	420.4	502.7	510.0	507.6	476.4	445.3	476.4	510.0	502.7	420.4	420.4
72.5°	369.8	429.8	413.8	387.1	328.1	269.1	328.1	413.8	429.8	369.8	369.8
75°	288.5	304.5	234.9	183.0	184.5	185.9	184.5	234.9	304.5	288.5	288.5
77.5°	192.6	204.7	167.9	140.6	141.9	143.2	141.9	167.9	204.7	192.6	192.6
80°	106.9	116.7	115.3	114.4	115.1	115.8	115.1	114.4	115.3	116.7	106.9
82.5°	75.0	81.6	83.1	83.9	82.9	81.9	82.9	83.1	81.6	75.0	75.0
85°	39.0	37.9	32.1	27.4	25.9	24.5	25.9	32.1	37.9	39.0	39.0
87.5°	14.6	15.6	17.7	18.9	20.1	19.5	20.1	17.7	15.6	14.6	14.6
90°	34.8	45.4	56.0	62.0	68.1	65.0	68.1	62.0	45.4	34.8	34.8
92.5°	69.9	87.7	100.7	111.6	116.4	115.8	116.4	100.7	87.7	69.9	69.9
95°	140.6	161.8	183.0	198.1	207.2	204.2	207.2	183.0	161.8	140.6	140.6
97.5°	216.9	245.3	268.9	283.1	292.2	298.2	292.2	268.9	245.3	216.9	216.9
100°	267.7	294.9	322.1	338.8	353.9	359.9	353.9	322.1	294.9	267.7	267.7
102.5°	308.8	344.5	374.1	392.0	404.7	410.7	404.7	374.1	344.5	308.8	308.8
105°	376.6	414.4	446.1	468.8	482.4	487.0	482.4	446.1	414.4	376.6	376.6
107.5°	444.3	483.3	512.7	537.8	554.4	564.1	554.4	512.7	483.3	444.3	444.3
110°	497.5	529.3	561.1	583.7	600.4	606.4	600.4	561.1	529.3	497.5	497.5



TEST NUMBER: P1435985

CATALOG NUMBER: SQ2W-FB-K-100U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	542.3	577.7	609.5	632.1	651.2	659.7	651.2	632.1	609.5	577.7	542.3
115°	604.9	651.8	680.5	701.7	715.3	722.9	715.3	701.7	680.5	651.8	604.9
117.5°	656.9	705.9	737.4	753.7	760.1	765.5	760.1	753.7	737.4	705.9	656.9
120°	689.6	735.0	771.3	792.4	800.0	803.0	800.0	792.4	771.3	735.0	689.6
122.5°	719.8	762.8	797.9	823.9	836.3	839.3	836.3	823.9	797.9	762.8	719.8
125°	762.2	803.0	839.3	865.0	878.6	886.2	878.6	865.0	839.3	803.0	762.2
127.5°	799.1	843.3	876.5	899.8	913.1	919.2	913.1	899.8	876.5	843.3	799.1
130°	819.7	865.0	898.3	924.0	936.1	942.2	936.1	924.0	898.3	865.0	819.7
132.5°	835.4	883.2	917.7	940.9	954.3	960.3	954.3	940.9	917.7	883.2	835.4
135°	854.4	904.3	940.6	963.3	975.4	981.5	975.4	963.3	940.6	904.3	854.4
137.5°	871.1	916.4	954.3	978.1	989.0	993.0	989.0	978.1	954.3	916.4	871.1
140°	883.2	922.5	960.3	983.0	995.1	996.6	995.1	983.0	960.3	922.5	883.2
142.5°	898.9	929.8	962.7	985.4	997.5	1000.2	997.5	985.4	962.7	929.8	898.9
145°	927.0	945.2	967.9	989.0	999.6	1002.6	999.6	989.0	967.9	945.2	927.0
147.5°	962.4	968.2	980.0	993.9	1004.2	1006.3	1004.2	993.9	980.0	968.2	962.4
150°	989.0	987.5	992.1	1001.1	1010.2	1008.7	1010.2	1001.1	992.1	987.5	989.0
152.5°	1019.3	1010.5	1010.2	1014.4	1018.7	1018.4	1018.7	1014.4	1010.2	1010.5	1019.3
155°	1070.7	1054.1	1045.0	1042.0	1042.0	1040.5	1042.0	1042.0	1045.0	1054.1	1070.7
157.5°	1127.3	1104.0	1090.4	1083.1	1081.0	1077.7	1081.0	1083.1	1090.4	1104.0	1127.3
160°	1166.0	1140.3	1126.7	1114.6	1110.0	1105.5	1110.0	1114.6	1126.7	1140.3	1166.0
162.5°	1202.3	1177.8	1162.9	1152.1	1147.5	1140.6	1147.5	1152.1	1162.9	1177.8	1202.3
165°	1261.2	1235.5	1218.9	1209.8	1203.8	1197.7	1203.8	1209.8	1218.9	1235.5	1261.2
167.5°	1320.2	1292.1	1281.2	1270.9	1265.2	1254.3	1265.2	1270.9	1281.2	1292.1	1320.2
170°	1356.5	1330.8	1324.8	1315.7	1305.1	1293.0	1305.1	1315.7	1324.8	1330.8	1356.5
172.5°	1388.0	1370.7	1364.7	1355.6	1352.3	1342.6	1352.3	1355.6	1364.7	1370.7	1388.0
175°	1433.6	1420.0	1420.0	1418.5	1414.0	1404.9	1414.0	1418.5	1420.0	1420.0	1433.6
177.5°	1471.8	1464.5	1469.3	1469.3	1468.1	1459.7	1468.1	1469.3	1469.3	1464.5	1471.8
180°	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2	1497.2



TEST NUMBER: P1435985

CATALOG NUMBER: SQ2W-FB-K-100U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	339.3	339.3	339.3	339.3
2.5°	356.2	349.4	343.0	336.6
5°	404.5	373.0	351.2	329.5
7.5°	498.9	405.2	361.0	316.7
10°	587.2	428.2	366.6	305.0
12.5°	655.5	459.3	375.6	292.0
15°	731.8	510.0	390.4	270.8
17.5°	793.6	567.3	408.1	248.9
20°	834.0	607.3	420.3	233.2
22.5°	864.0	637.0	427.9	218.9
25°	896.5	670.2	434.6	199.0
27.5°	901.1	677.6	428.7	179.7
30°	895.4	674.0	421.0	168.0
32.5°	884.6	665.9	411.7	157.6
35°	858.5	642.1	392.0	141.9
37.5°	819.1	604.9	366.7	128.5
40°	790.0	577.4	349.0	120.7
42.5°	756.0	545.2	329.0	112.9
45°	700.3	491.3	297.0	102.8
47.5°	640.7	430.8	262.1	93.3
50°	600.2	389.6	238.9	88.1
52.5°	560.6	349.6	216.2	82.9
55°	502.9	294.1	185.4	76.7
57.5°	448.8	246.5	158.8	71.1
60°	414.8	220.7	144.6	68.5
62.5°	380.9	197.1	130.8	64.6
65°	333.3	167.6	114.0	60.3
67.5°	289.7	145.5	100.0	54.5
70°	263.1	134.7	92.6	50.6
72.5°	234.0	122.8	85.4	48.0
75°	187.0	103.3	72.9	42.4
77.5°	131.6	80.1	57.3	34.6
80°	85.9	65.6	47.5	29.4
82.5°	63.3	51.1	37.6	24.1
85°	35.3	30.6	22.7	14.7
87.5°	15.4	14.3	10.2	6.1
90°	27.2	16.6	10.6	4.5
92.5°	58.7	40.8	28.7	16.6
95°	118.0	93.8	66.5	46.9
97.5°	187.8	148.8	121.9	89.5
100°	225.3	187.5	161.8	127.0
102.5°	266.5	234.7	199.3	164.5
105°	340.3	300.9	260.1	220.8
107.5°	408.6	365.4	316.4	281.0
110°	452.2	405.3	353.9	322.1



TEST NUMBER: P1435985

CATALOG NUMBER: SQ2W-FB-K-100U-075D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	494.5	446.4	393.8	362.0
115°	552.0	499.1	450.7	423.4
117.5°	607.3	552.9	501.8	480.3
120°	641.2	586.8	536.9	520.2
122.5°	669.0	615.8	569.5	562.6
125°	710.8	656.3	617.0	626.1
127.5°	744.6	694.7	669.9	690.2
130°	765.2	721.4	706.2	735.0
132.5°	783.4	749.2	742.5	782.2
135°	810.6	790.9	797.0	851.4
137.5°	842.9	835.4	855.7	924.3
140°	863.5	868.1	896.8	973.9
142.5°	891.3	901.9	939.1	1021.1
145°	934.6	957.3	1005.7	1087.3
147.5°	983.6	1012.9	1072.8	1156.6
150°	1016.3	1054.1	1117.6	1197.7
152.5°	1053.8	1092.8	1156.3	1237.7
155°	1111.5	1155.4	1221.9	1291.5
157.5°	1170.5	1215.3	1278.8	1339.6
160°	1206.8	1255.2	1312.7	1368.6
162.5°	1247.9	1292.7	1342.9	1392.8
165°	1308.1	1344.4	1385.3	1427.6
167.5°	1358.6	1388.9	1420.9	1453.9
170°	1391.3	1415.5	1442.7	1468.4
172.5°	1419.1	1438.5	1458.4	1480.5
175°	1456.3	1466.9	1479.0	1492.6
177.5°	1485.1	1488.7	1492.3	1498.4
180°	1497.2	1497.2	1497.2	1497.2



TEST NUMBER: P1435985  
 CATALOG NUMBER: SQ2W-FB-K-100U-075D-L830-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.45	12.27	12.45	13.29	14.65	21.04	21.87	22.05	22.89	24.25
	3H	12.38	13.13	13.40	14.15	15.53	22.65	23.39	23.66	24.42	25.80
	4H	12.78	13.48	13.81	14.52	15.90	22.82	23.53	23.85	24.56	25.95
	6H	13.03	13.68	14.07	14.72	16.12	22.90	23.54	23.94	24.58	25.98
	8H	13.12	13.74	14.17	14.79	16.19	22.91	23.53	23.96	24.58	25.98
	12H	13.17	13.76	14.22	14.80	16.23	22.89	23.48	23.94	24.52	25.94
4H	2H	16.16	16.87	17.20	17.90	19.29	21.41	22.11	22.44	23.14	24.53
	3H	17.29	17.88	18.33	18.93	20.34	23.29	23.88	24.33	24.94	26.34
	4H	17.57	18.11	18.62	19.16	20.58	23.51	24.05	24.56	25.10	26.52
	6H	17.70	18.16	18.76	19.24	20.66	23.64	24.10	24.70	25.18	26.59
	8H	17.74	18.17	18.80	19.24	20.67	23.68	24.11	24.75	25.18	26.62
	12H	17.74	18.13	18.82	19.21	20.65	23.66	24.05	24.75	25.13	26.57
8H	4H	18.76	19.19	19.82	20.26	21.69	23.60	24.03	24.66	25.10	26.53
	6H	19.02	19.37	20.10	20.48	21.91	23.79	24.15	24.88	25.26	26.69
	8H	19.11	19.42	20.21	20.52	21.97	23.88	24.20	24.98	25.29	26.74
	12H	19.15	19.43	20.25	20.51	22.01	23.89	24.16	24.99	25.25	26.74
12H	4H	18.78	19.17	19.86	20.25	21.69	23.55	23.94	24.63	25.02	26.46
	6H	19.12	19.43	20.22	20.53	21.98	23.78	24.09	24.87	25.18	26.63
	8H	19.26	19.53	20.36	20.62	22.11	23.87	24.15	24.97	25.24	26.73