

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1436027

Luminaire Tested: SQ2W-FB-K-150U-050D-L830-UNV-STD-W-WM-4

Issue Date: 3/24/2026

Test Information

Test Method: LM-79-2019
Report Number: P1436027
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 3/24/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-FB-K-150U-050D-L830-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8906.1 lumens
Efficiency: N/A
Efficacy: 122.2 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 72.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1436027

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L830-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1436027

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L830-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26
1	92	88	84	81	82	79	76	73	61	59	57	45	44	42	30	29	29	22
2	84	77	71	66	75	69	64	59	53	50	47	39	37	35	26	25	24	18
3	76	67	60	54	68	60	54	49	47	42	39	34	32	29	23	21	20	15
4	70	59	51	45	62	53	46	41	41	37	33	30	27	25	20	18	17	13
5	64	52	44	39	56	47	40	35	37	32	28	27	24	21	18	16	14	11
6	58	47	39	33	52	42	35	30	33	28	24	24	21	18	16	14	13	9
7	54	42	34	29	48	37	31	26	29	24	21	22	18	16	15	13	11	8
8	50	38	30	25	44	34	27	23	27	22	18	20	16	14	13	11	10	7
9	46	34	27	22	41	31	24	20	24	19	16	18	15	12	12	10	9	6
10	43	31	24	19	38	28	22	18	22	17	14	16	13	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3797	3797	3797	3797
5°	3702	6724	3702	6724
10°	3466	13086	3466	13086
15°	3137	15062	3137	15062
20°	2778	15775	2778	15775
25°	2457	16033	2457	16033
30°	2172	16231	2172	16231
35°	1939	17449	1939	17449
40°	1764	18539	1764	18539
45°	1626	19415	1626	19415
50°	1535	19765	1535	19765
55°	1495	19924	1495	19924
60°	1534	19824	1534	19824
65°	1597	19266	1597	19266
70°	1657	14573	1657	14573
75°	1834	8041	1834	8041
80°	1897	7466	1897	7466
85°	1890	3149	1890	3149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 20104 cd/sqm



TEST NUMBER: P1436027

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L830-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.4	0.4
10°-20°	179.8	2.0
20°-30°	316.4	3.6
30°-40°	409.5	4.6
40°-50°	451.6	5.1
50°-60°	421.5	4.7
60°-70°	325.7	3.7
70°-80°	150.1	1.7
80°-90°	38.0	0.4
90°-100°	179.2	2.0
100°-110°	522.6	5.9
110°-120°	852.8	9.6
120°-130°	1082.1	12.2
130°-140°	1157.9	13.0
140°-150°	1081.2	12.1
150°-160°	889.7	10.0
160°-170°	596.7	6.7
170°-180°	211.9	2.4
0°-30°	535.5	6.0
0°-40°	945.1	10.6
0°-60°	1818.2	20.4
0°-90°	2332.0	26.2
90°-120°	1554.5	17.5
90°-150°	4875.8	54.7
90°-180°	6574.0	73.8
0°-180°	8906.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	235	235	235	235	235	
5°	228	415	228	415	228	21
15°	188	901	188	901	188	52
25°	138	900	138	900	138	63
35°	98	885	98	885	98	62
45°	71	850	71	850	71	55
55°	53	708	53	708	53	48
65°	42	504	42	504	42	41
75°	29	129	29	129	29	30
85°	10	17	10	17	10	11
90°	7	50	7	98	7	6
95°	70	52	70	307	70	85
105°	332	532	332	732	332	353
115°	637	882	637	1087	637	628
125°	942	1399	942	1333	942	842
135°	1280	1831	1280	1476	1280	989
145°	1635	2110	1635	1508	1635	1023
155°	1942	2292	1942	1565	1942	893
165°	2147	2390	2147	1801	2147	604
175°	2245	2340	2245	2113	2245	213
180°	2252	2252	2252	2252	2252	



TEST NUMBER: P1436027

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2
2.5°	233.4	237.8	242.2	246.9	251.8	257.0	262.6	267.4	269.8	272.3	269.8
5°	228.4	243.5	258.5	280.4	304.5	331.9	362.6	388.8	401.9	414.9	401.9
7.5°	219.6	250.2	280.9	345.8	422.2	501.5	583.7	651.9	678.0	704.2	678.0
10°	211.4	254.1	296.9	407.0	539.7	641.7	713.1	770.1	784.2	798.2	784.2
12.5°	202.4	260.4	318.4	454.4	616.4	722.4	772.5	813.6	828.1	842.6	828.1
15°	187.7	270.6	353.5	507.3	684.7	793.7	834.4	869.0	885.0	901.1	885.0
17.5°	172.5	282.9	393.2	550.1	722.5	828.8	869.1	901.5	910.2	919.0	910.2
20°	161.7	291.3	421.0	578.1	744.5	845.0	879.6	907.0	912.6	918.1	912.6
22.5°	151.7	296.7	441.6	598.9	760.5	854.3	880.6	901.7	907.6	913.6	907.6
25°	137.9	301.3	464.6	621.5	776.3	861.9	878.5	892.0	896.0	900.0	896.0
27.5°	124.6	297.2	469.7	624.6	773.7	853.6	864.5	873.6	877.5	881.5	877.5
30°	116.5	291.8	467.2	620.7	767.0	844.1	852.1	859.5	865.1	870.6	865.1
32.5°	109.2	285.4	461.6	613.2	756.6	832.1	839.8	848.5	860.5	872.4	860.5
35°	98.4	271.7	445.1	595.1	737.3	814.4	826.5	841.1	863.2	885.3	863.2
37.5°	89.1	254.2	419.3	567.8	710.7	794.8	820.0	844.3	865.6	886.9	865.6
40°	83.7	242.0	400.3	547.6	691.3	780.0	813.7	843.5	861.6	879.6	861.6
42.5°	78.2	228.1	377.9	524.1	669.0	761.1	800.4	834.4	852.5	870.6	852.5
45°	71.2	205.9	340.6	485.4	633.7	730.9	777.1	816.1	833.2	850.3	833.2
47.5°	64.7	181.7	298.6	444.1	599.1	701.1	750.1	790.0	802.5	815.0	802.5
50°	61.1	165.6	270.1	416.1	575.9	679.9	728.1	766.8	776.9	786.9	776.9
52.5°	57.4	149.9	242.4	388.6	552.9	657.7	703.1	739.5	748.7	758.0	748.7
55°	53.1	128.5	203.9	348.6	516.5	620.2	659.9	691.7	699.7	707.8	699.7
57.5°	49.3	110.1	170.9	311.1	477.7	578.0	611.8	638.9	645.4	651.9	645.4
60°	47.5	100.3	153.0	287.6	449.4	545.6	576.3	600.9	607.4	613.9	607.4
62.5°	44.8	90.7	136.6	264.0	418.6	510.0	538.3	561.0	567.1	573.2	567.1
65°	41.8	79.0	116.2	231.0	371.7	453.9	477.5	496.2	500.3	504.3	500.3
67.5°	37.8	69.3	100.9	200.8	323.5	392.2	406.9	416.0	408.5	400.9	408.5
70°	35.1	64.2	93.3	182.4	291.5	348.5	353.5	351.9	330.3	308.7	330.3
72.5°	33.2	59.2	85.1	162.2	256.4	297.9	286.9	268.4	227.5	186.6	227.5
75°	29.4	50.5	71.6	129.6	200.0	211.1	162.8	126.9	127.9	128.9	127.9
77.5°	24.0	39.7	55.5	91.2	133.5	141.9	116.4	97.5	98.4	99.3	98.4
80°	20.4	32.9	45.5	59.5	74.1	80.9	79.9	79.3	79.8	80.3	79.8
82.5°	16.7	26.1	35.4	43.9	52.0	56.6	57.6	58.2	57.5	56.8	57.5
85°	10.2	15.7	21.2	24.5	27.0	26.3	22.2	19.0	18.0	17.0	18.0
87.5°	5.0	8.8	13.1	14.2	14.0	13.6	13.6	14.1	14.5	14.5	14.5
90°	6.8	15.9	27.3	36.4	43.2	45.5	45.5	47.8	50.0	50.0	50.0
92.5°	25.0	39.6	40.0	40.0	48.7	52.8	56.4	56.9	59.1	59.1	59.1
95°	70.5	77.3	116.0	113.7	77.3	61.4	52.3	52.3	52.3	52.3	52.3
97.5°	134.6	144.6	151.0	202.4	213.8	206.5	168.3	141.5	126.4	119.6	126.4
100°	191.0	195.6	209.2	211.5	268.4	322.9	295.7	261.5	250.2	243.3	250.2
102.5°	247.4	250.2	271.1	280.6	293.8	324.8	419.4	408.9	401.2	399.8	401.2
105°	332.0	334.3	373.0	391.2	400.3	400.3	398.0	443.5	516.3	532.2	516.3
107.5°	422.6	433.0	478.5	527.2	537.6	540.4	528.5	521.7	519.0	520.8	519.0
110°	484.4	500.3	554.9	616.3	632.2	636.8	632.2	625.4	620.9	620.9	620.9



TEST NUMBER: P1436027

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	544.5	567.7	629.5	700.0	726.9	740.5	730.5	725.5	720.9	724.6	720.9
115°	636.8	670.9	752.8	825.6	880.1	887.0	884.7	884.7	882.4	882.4	882.4
117.5°	722.3	776.9	868.8	953.4	1016.6	1034.8	1043.9	1041.2	1038.4	1043.0	1038.4
120°	782.3	846.0	950.6	1046.2	1107.6	1134.9	1144.0	1139.4	1144.0	1139.4	1144.0
122.5°	846.0	924.3	1027.1	1126.2	1198.5	1229.5	1240.4	1241.3	1242.2	1239.5	1242.2
125°	941.5	1037.1	1157.6	1259.9	1335.0	1371.4	1380.5	1382.8	1387.3	1398.7	1387.3
127.5°	1038.0	1146.2	1278.6	1377.3	1454.2	1498.3	1512.4	1517.4	1526.9	1531.9	1526.9
130°	1105.3	1228.1	1362.3	1455.5	1530.6	1578.3	1603.4	1610.2	1621.6	1619.3	1621.6
132.5°	1176.3	1304.5	1440.5	1537.4	1607.0	1658.4	1679.8	1699.3	1703.4	1706.6	1703.4
135°	1280.4	1419.1	1555.6	1651.1	1717.1	1767.1	1794.4	1812.6	1824.0	1830.8	1824.0
137.5°	1390.0	1536.5	1667.5	1752.6	1819.0	1862.2	1893.1	1912.2	1924.0	1929.5	1924.0
140°	1464.6	1605.6	1733.0	1821.7	1880.8	1924.0	1951.3	1974.1	1987.7	1987.7	1987.7
142.5°	1535.6	1674.8	1798.5	1887.2	1939.0	1978.6	2007.7	2025.0	2040.5	2040.5	2040.5
145°	1635.2	1773.9	1887.6	1976.3	2019.6	2055.9	2087.8	2101.4	2110.5	2110.5	2110.5
147.5°	1739.4	1862.2	1965.9	2050.9	2087.3	2130.1	2155.1	2166.0	2177.4	2172.4	2177.4
150°	1801.2	1914.9	2015.0	2094.6	2131.0	2171.9	2196.9	2206.0	2217.4	2210.6	2217.4
152.5°	1861.3	1969.5	2060.5	2134.6	2165.6	2206.5	2235.2	2244.2	2252.0	2247.0	2252.0
155°	1942.2	2037.7	2121.9	2190.1	2217.4	2256.1	2283.4	2294.7	2303.8	2292.5	2303.8
157.5°	2014.5	2096.9	2170.1	2232.9	2262.0	2295.2	2320.7	2334.8	2343.9	2338.9	2343.9
160°	2058.2	2133.3	2199.2	2258.3	2285.6	2315.2	2342.5	2358.4	2367.5	2360.7	2367.5
162.5°	2094.6	2162.4	2224.7	2278.4	2302.0	2327.9	2360.7	2374.8	2383.9	2375.2	2383.9
165°	2146.9	2201.5	2256.1	2301.6	2322.0	2342.5	2376.6	2392.5	2399.4	2390.3	2399.4
167.5°	2186.5	2228.3	2272.5	2311.6	2326.6	2346.6	2380.7	2393.9	2402.5	2391.2	2402.5
170°	2208.3	2244.7	2283.4	2315.2	2326.6	2344.8	2378.9	2390.3	2397.1	2385.7	2397.1
172.5°	2226.5	2253.8	2285.2	2313.4	2319.3	2333.9	2366.2	2377.5	2382.5	2373.0	2382.5
175°	2244.7	2260.6	2283.4	2301.6	2299.3	2308.4	2335.7	2344.8	2353.9	2340.2	2353.9
177.5°	2253.3	2260.6	2267.9	2278.8	2271.5	2271.5	2291.6	2297.0	2298.8	2291.6	2298.8
180°	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5



TEST NUMBER: P1436027

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2
2.5°	267.4	262.6	257.0	251.8	246.9	242.2	237.8	233.4	237.8	242.2	246.9
5°	388.8	362.6	331.9	304.5	280.4	258.5	243.5	228.4	243.5	258.5	280.4
7.5°	651.9	583.7	501.5	422.2	345.8	280.9	250.2	219.6	250.2	280.9	345.8
10°	770.1	713.1	641.7	539.7	407.0	296.9	254.1	211.4	254.1	296.9	407.0
12.5°	813.6	772.5	722.4	616.4	454.4	318.4	260.4	202.4	260.4	318.4	454.4
15°	869.0	834.4	793.7	684.7	507.3	353.5	270.6	187.7	270.6	353.5	507.3
17.5°	901.5	869.1	828.8	722.5	550.1	393.2	282.9	172.5	282.9	393.2	550.1
20°	907.0	879.6	845.0	744.5	578.1	421.0	291.3	161.7	291.3	421.0	578.1
22.5°	901.7	880.6	854.3	760.5	598.9	441.6	296.7	151.7	296.7	441.6	598.9
25°	892.0	878.5	861.9	776.3	621.5	464.6	301.3	137.9	301.3	464.6	621.5
27.5°	873.6	864.5	853.6	773.7	624.6	469.7	297.2	124.6	297.2	469.7	624.6
30°	859.5	852.1	844.1	767.0	620.7	467.2	291.8	116.5	291.8	467.2	620.7
32.5°	848.5	839.8	832.1	756.6	613.2	461.6	285.4	109.2	285.4	461.6	613.2
35°	841.1	826.5	814.4	737.3	595.1	445.1	271.7	98.4	271.7	445.1	595.1
37.5°	844.3	820.0	794.8	710.7	567.8	419.3	254.2	89.1	254.2	419.3	567.8
40°	843.5	813.7	780.0	691.3	547.6	400.3	242.0	83.7	242.0	400.3	547.6
42.5°	834.4	800.4	761.1	669.0	524.1	377.9	228.1	78.2	228.1	377.9	524.1
45°	816.1	777.1	730.9	633.7	485.4	340.6	205.9	71.2	205.9	340.6	485.4
47.5°	790.0	750.1	701.1	599.1	444.1	298.6	181.7	64.7	181.7	298.6	444.1
50°	766.8	728.1	679.9	575.9	416.1	270.1	165.6	61.1	165.6	270.1	416.1
52.5°	739.5	703.1	657.7	552.9	388.6	242.4	149.9	57.4	149.9	242.4	388.6
55°	691.7	659.9	620.2	516.5	348.6	203.9	128.5	53.1	128.5	203.9	348.6
57.5°	638.9	611.8	578.0	477.7	311.1	170.9	110.1	49.3	110.1	170.9	311.1
60°	600.9	576.3	545.6	449.4	287.6	153.0	100.3	47.5	100.3	153.0	287.6
62.5°	561.0	538.3	510.0	418.6	264.0	136.6	90.7	44.8	90.7	136.6	264.0
65°	496.2	477.5	453.9	371.7	231.0	116.2	79.0	41.8	79.0	116.2	231.0
67.5°	416.0	406.9	392.2	323.5	200.8	100.9	69.3	37.8	69.3	100.9	200.8
70°	351.9	353.5	348.5	291.5	182.4	93.3	64.2	35.1	64.2	93.3	182.4
72.5°	268.4	286.9	297.9	256.4	162.2	85.1	59.2	33.2	59.2	85.1	162.2
75°	126.9	162.8	211.1	200.0	129.6	71.6	50.5	29.4	50.5	71.6	129.6
77.5°	97.5	116.4	141.9	133.5	91.2	55.5	39.7	24.0	39.7	55.5	91.2
80°	79.3	79.9	80.9	74.1	59.5	45.5	32.9	20.4	32.9	45.5	59.5
82.5°	58.2	57.6	56.6	52.0	43.9	35.4	26.1	16.7	26.1	35.4	43.9
85°	19.0	22.2	26.3	27.0	24.5	21.2	15.7	10.2	15.7	21.2	24.5
87.5°	14.1	13.6	13.6	14.0	14.2	13.1	8.8	5.0	8.8	12.6	15.1
90°	47.8	45.5	45.5	43.2	36.4	27.3	15.9	6.8	15.9	25.0	40.9
92.5°	56.9	56.4	52.8	48.7	40.0	40.0	39.6	25.0	43.2	61.4	88.2
95°	52.3	52.3	61.4	77.3	113.7	116.0	77.3	70.5	100.1	141.0	177.4
97.5°	141.5	168.3	206.5	213.8	202.4	151.0	144.6	134.6	183.3	223.8	282.5
100°	261.5	295.7	322.9	268.4	211.5	209.2	195.6	191.0	243.3	282.0	338.9
102.5°	408.9	419.4	324.8	293.8	280.6	271.1	250.2	247.4	299.7	353.0	400.7
105°	443.5	398.0	400.3	400.3	391.2	373.0	334.3	332.0	391.2	452.6	511.7
107.5°	521.7	528.5	540.4	537.6	527.2	478.5	433.0	422.6	475.8	549.5	614.5
110°	625.4	632.2	636.8	632.2	616.3	554.9	500.3	484.4	532.2	609.5	680.0



TEST NUMBER: P1436027

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	725.5	730.5	740.5	726.9	700.0	629.5	567.7	544.5	592.2	671.4	743.7
115°	884.7	884.7	887.0	880.1	825.6	752.8	670.9	636.8	677.7	750.5	830.1
117.5°	1041.2	1043.9	1034.8	1016.6	953.4	868.8	776.9	722.3	754.6	831.5	913.3
120°	1139.4	1144.0	1134.9	1107.6	1046.2	950.6	846.0	782.3	807.4	882.4	964.3
122.5°	1241.3	1240.4	1229.5	1198.5	1126.2	1027.1	924.3	846.0	856.5	926.1	1006.1
125°	1382.8	1380.5	1371.4	1335.0	1259.9	1157.6	1037.1	941.5	927.9	987.0	1068.9
127.5°	1517.4	1512.4	1498.3	1454.2	1377.3	1278.6	1146.2	1038.0	1007.5	1044.8	1119.9
130°	1610.2	1603.4	1578.3	1530.6	1455.5	1362.3	1228.1	1105.3	1062.1	1084.8	1150.8
132.5°	1699.3	1679.8	1658.4	1607.0	1537.4	1440.5	1304.5	1176.3	1116.7	1126.7	1178.1
135°	1812.6	1794.4	1767.1	1717.1	1651.1	1555.6	1419.1	1280.4	1198.5	1189.4	1219.0
137.5°	1912.2	1893.1	1862.2	1819.0	1752.6	1667.5	1536.5	1390.0	1286.8	1256.3	1267.7
140°	1974.1	1951.3	1924.0	1880.8	1821.7	1733.0	1605.6	1464.6	1348.6	1305.4	1298.6
142.5°	2025.0	2007.7	1978.6	1939.0	1887.2	1798.5	1674.8	1535.6	1412.3	1356.4	1340.5
145°	2101.4	2087.8	2055.9	2019.6	1976.3	1887.6	1773.9	1635.2	1512.4	1439.6	1405.5
147.5°	2166.0	2155.1	2130.1	2087.3	2050.9	1965.9	1862.2	1739.4	1613.4	1523.3	1479.2
150°	2206.0	2196.9	2171.9	2131.0	2094.6	2015.0	1914.9	1801.2	1680.7	1585.2	1528.3
152.5°	2244.2	2235.2	2206.5	2165.6	2134.6	2060.5	1969.5	1861.3	1738.9	1643.4	1584.7
155°	2294.7	2283.4	2256.1	2217.4	2190.1	2121.9	2037.7	1942.2	1837.6	1737.5	1671.6
157.5°	2334.8	2320.7	2295.2	2262.0	2232.9	2170.1	2096.9	2014.5	1923.1	1827.6	1760.3
160°	2358.4	2342.5	2315.2	2285.6	2258.3	2199.2	2133.3	2058.2	1974.1	1887.6	1814.9
162.5°	2374.8	2360.7	2327.9	2302.0	2278.4	2224.7	2162.4	2094.6	2019.6	1944.0	1876.7
165°	2392.5	2376.6	2342.5	2322.0	2301.6	2256.1	2201.5	2146.9	2083.2	2021.8	1967.2
167.5°	2393.9	2380.7	2346.6	2326.6	2311.6	2272.5	2228.3	2186.5	2136.9	2088.7	2043.2
170°	2390.3	2378.9	2344.8	2326.6	2315.2	2283.4	2244.7	2208.3	2169.7	2128.7	2092.3
172.5°	2377.5	2366.2	2333.9	2319.3	2313.4	2285.2	2253.8	2226.5	2193.3	2163.3	2134.2
175°	2344.8	2335.7	2308.4	2299.3	2301.6	2283.4	2260.6	2244.7	2224.2	2206.0	2190.1
177.5°	2297.0	2291.6	2271.5	2271.5	2278.8	2267.9	2260.6	2253.3	2244.2	2238.8	2233.3
180°	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5



TEST NUMBER: P1436027

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2	235.2
2.5°	251.8	257.0	262.6	267.4	269.8	272.3	269.8	267.4	262.6	257.0	251.8
5°	304.5	331.9	362.6	388.8	401.9	414.9	401.9	388.8	362.6	331.9	304.5
7.5°	422.2	501.5	583.7	651.9	678.0	704.2	678.0	651.9	583.7	501.5	422.2
10°	539.7	641.7	713.1	770.1	784.2	798.2	784.2	770.1	713.1	641.7	539.7
12.5°	616.4	722.4	772.5	813.6	828.1	842.6	828.1	813.6	772.5	722.4	616.4
15°	684.7	793.7	834.4	869.0	885.0	901.1	885.0	869.0	834.4	793.7	684.7
17.5°	722.5	828.8	869.1	901.5	910.2	919.0	910.2	901.5	869.1	828.8	722.5
20°	744.5	845.0	879.6	907.0	912.6	918.1	912.6	907.0	879.6	845.0	744.5
22.5°	760.5	854.3	880.6	901.7	907.6	913.6	907.6	901.7	880.6	854.3	760.5
25°	776.3	861.9	878.5	892.0	896.0	900.0	896.0	892.0	878.5	861.9	776.3
27.5°	773.7	853.6	864.5	873.6	877.5	881.5	877.5	873.6	864.5	853.6	773.7
30°	767.0	844.1	852.1	859.5	865.1	870.6	865.1	859.5	852.1	844.1	767.0
32.5°	756.6	832.1	839.8	848.5	860.5	872.4	860.5	848.5	839.8	832.1	756.6
35°	737.3	814.4	826.5	841.1	863.2	885.3	863.2	841.1	826.5	814.4	737.3
37.5°	710.7	794.8	820.0	844.3	865.6	886.9	865.6	844.3	820.0	794.8	710.7
40°	691.3	780.0	813.7	843.5	861.6	879.6	861.6	843.5	813.7	780.0	691.3
42.5°	669.0	761.1	800.4	834.4	852.5	870.6	852.5	834.4	800.4	761.1	669.0
45°	633.7	730.9	777.1	816.1	833.2	850.3	833.2	816.1	777.1	730.9	633.7
47.5°	599.1	701.1	750.1	790.0	802.5	815.0	802.5	790.0	750.1	701.1	599.1
50°	575.9	679.9	728.1	766.8	776.9	786.9	776.9	766.8	728.1	679.9	575.9
52.5°	552.9	657.7	703.1	739.5	748.7	758.0	748.7	739.5	703.1	657.7	552.9
55°	516.5	620.2	659.9	691.7	699.7	707.8	699.7	691.7	659.9	620.2	516.5
57.5°	477.7	578.0	611.8	638.9	645.4	651.9	645.4	638.9	611.8	578.0	477.7
60°	449.4	545.6	576.3	600.9	607.4	613.9	607.4	600.9	576.3	545.6	449.4
62.5°	418.6	510.0	538.3	561.0	567.1	573.2	567.1	561.0	538.3	510.0	418.6
65°	371.7	453.9	477.5	496.2	500.3	504.3	500.3	496.2	477.5	453.9	371.7
67.5°	323.5	392.2	406.9	416.0	408.5	400.9	408.5	416.0	406.9	392.2	323.5
70°	291.5	348.5	353.5	351.9	330.3	308.7	330.3	351.9	353.5	348.5	291.5
72.5°	256.4	297.9	286.9	268.4	227.5	186.6	227.5	268.4	286.9	297.9	256.4
75°	200.0	211.1	162.8	126.9	127.9	128.9	127.9	126.9	162.8	211.1	200.0
77.5°	133.5	141.9	116.4	97.5	98.4	99.3	98.4	97.5	116.4	141.9	133.5
80°	74.1	80.9	79.9	79.3	79.8	80.3	79.8	79.3	79.9	80.9	74.1
82.5°	52.0	56.6	57.6	58.2	57.5	56.8	57.5	58.2	57.6	56.6	52.0
85°	27.0	26.3	22.2	19.0	18.0	17.0	18.0	19.0	22.2	26.3	27.0
87.5°	15.8	18.2	21.4	23.2	25.0	24.1	25.0	23.2	21.4	18.2	15.8
90°	52.3	68.2	84.1	93.2	102.3	97.8	102.3	93.2	84.1	68.2	52.3
92.5°	105.1	131.9	151.5	167.8	175.1	174.2	175.1	167.8	151.5	131.9	105.1
95°	211.5	243.3	275.2	297.9	311.6	307.0	311.6	297.9	275.2	243.3	211.5
97.5°	326.1	368.9	404.4	425.7	439.4	448.5	439.4	425.7	404.4	368.9	326.1
100°	402.5	443.5	484.4	509.4	532.2	541.3	532.2	509.4	484.4	443.5	402.5
102.5°	464.4	518.1	562.7	589.5	608.6	617.7	608.6	589.5	562.7	518.1	464.4
105°	566.3	623.1	670.9	705.0	725.5	732.3	725.5	705.0	670.9	623.1	566.3
107.5°	668.2	726.9	771.0	808.7	833.7	848.3	833.7	808.7	771.0	726.9	668.2
110°	748.2	796.0	843.8	877.9	902.9	912.0	902.9	877.9	843.8	796.0	748.2



TEST NUMBER: P1436027

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	815.6	868.8	916.5	950.6	979.3	992.0	979.3	950.6	916.5	868.8	815.6
115°	909.7	980.2	1023.4	1055.3	1075.7	1087.1	1075.7	1055.3	1023.4	980.2	909.7
117.5°	987.9	1061.6	1108.9	1133.5	1143.0	1151.2	1143.0	1133.5	1108.9	1061.6	987.9
120°	1037.1	1105.3	1159.9	1191.7	1203.1	1207.6	1203.1	1191.7	1159.9	1105.3	1037.1
122.5°	1082.6	1147.1	1199.9	1239.0	1257.7	1262.2	1257.7	1239.0	1199.9	1147.1	1082.6
125°	1146.2	1207.6	1262.2	1300.9	1321.4	1332.7	1321.4	1300.9	1262.2	1207.6	1146.2
127.5°	1201.7	1268.1	1318.2	1353.2	1373.2	1382.3	1373.2	1353.2	1318.2	1268.1	1201.7
130°	1232.7	1300.9	1350.9	1389.6	1407.8	1416.9	1407.8	1389.6	1350.9	1300.9	1232.7
132.5°	1256.3	1328.2	1380.0	1415.1	1435.1	1444.2	1435.1	1415.1	1380.0	1328.2	1256.3
135°	1285.0	1360.0	1414.6	1448.7	1466.9	1476.0	1466.9	1448.7	1414.6	1360.0	1285.0
137.5°	1310.0	1378.2	1435.1	1471.0	1487.4	1493.3	1487.4	1471.0	1435.1	1378.2	1310.0
140°	1328.2	1387.3	1444.2	1478.3	1496.5	1498.7	1496.5	1478.3	1444.2	1387.3	1328.2
142.5°	1351.8	1398.2	1447.8	1481.9	1500.1	1504.2	1500.1	1481.9	1447.8	1398.2	1351.8
145°	1394.1	1421.4	1455.5	1487.4	1503.3	1507.8	1503.3	1487.4	1455.5	1421.4	1394.1
147.5°	1447.3	1456.0	1473.7	1494.6	1510.1	1513.3	1510.1	1494.6	1473.7	1456.0	1447.3
150°	1487.4	1485.1	1491.9	1505.6	1519.2	1516.9	1519.2	1505.6	1491.9	1485.1	1487.4
152.5°	1532.9	1519.7	1519.2	1525.6	1531.9	1531.5	1531.9	1525.6	1519.2	1519.7	1532.9
155°	1610.2	1585.2	1571.5	1567.0	1567.0	1564.7	1567.0	1567.0	1571.5	1585.2	1610.2
157.5°	1695.2	1660.2	1639.7	1628.8	1625.6	1620.6	1625.6	1628.8	1639.7	1660.2	1695.2
160°	1753.5	1714.8	1694.3	1676.1	1669.3	1662.5	1669.3	1676.1	1694.3	1714.8	1753.5
162.5°	1808.0	1771.2	1748.9	1732.5	1725.7	1715.3	1725.7	1732.5	1748.9	1771.2	1808.0
165°	1896.7	1858.1	1833.1	1819.4	1810.3	1801.2	1810.3	1819.4	1833.1	1858.1	1896.7
167.5°	1985.4	1943.1	1926.8	1911.3	1902.7	1886.3	1902.7	1911.3	1926.8	1943.1	1985.4
170°	2040.0	2001.4	1992.3	1978.6	1962.7	1944.5	1962.7	1978.6	1992.3	2001.4	2040.0
172.5°	2087.3	2061.4	2052.3	2038.7	2033.7	2019.1	2033.7	2038.7	2052.3	2061.4	2087.3
175°	2156.0	2135.5	2135.5	2133.3	2126.4	2112.8	2126.4	2133.3	2135.5	2135.5	2156.0
177.5°	2213.3	2202.4	2209.7	2209.7	2207.9	2195.1	2207.9	2209.7	2209.7	2202.4	2213.3
180°	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5	2251.5



TEST NUMBER: P1436027

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	235.2	235.2	235.2	235.2
2.5°	246.9	242.2	237.8	233.4
5°	280.4	258.5	243.5	228.4
7.5°	345.8	280.9	250.2	219.6
10°	407.0	296.9	254.1	211.4
12.5°	454.4	318.4	260.4	202.4
15°	507.3	353.5	270.6	187.7
17.5°	550.1	393.2	282.9	172.5
20°	578.1	421.0	291.3	161.7
22.5°	598.9	441.6	296.7	151.7
25°	621.5	464.6	301.3	137.9
27.5°	624.6	469.7	297.2	124.6
30°	620.7	467.2	291.8	116.5
32.5°	613.2	461.6	285.4	109.2
35°	595.1	445.1	271.7	98.4
37.5°	567.8	419.3	254.2	89.1
40°	547.6	400.3	242.0	83.7
42.5°	524.1	377.9	228.1	78.2
45°	485.4	340.6	205.9	71.2
47.5°	444.1	298.6	181.7	64.7
50°	416.1	270.1	165.6	61.1
52.5°	388.6	242.4	149.9	57.4
55°	348.6	203.9	128.5	53.1
57.5°	311.1	170.9	110.1	49.3
60°	287.6	153.0	100.3	47.5
62.5°	264.0	136.6	90.7	44.8
65°	231.0	116.2	79.0	41.8
67.5°	200.8	100.9	69.3	37.8
70°	182.4	93.3	64.2	35.1
72.5°	162.2	85.1	59.2	33.2
75°	129.6	71.6	50.5	29.4
77.5°	91.2	55.5	39.7	24.0
80°	59.5	45.5	32.9	20.4
82.5°	43.9	35.4	26.1	16.7
85°	24.5	21.2	15.7	10.2
87.5°	15.1	12.6	8.8	5.0
90°	40.9	25.0	15.9	6.8
92.5°	88.2	61.4	43.2	25.0
95°	177.4	141.0	100.1	70.5
97.5°	282.5	223.8	183.3	134.6
100°	338.9	282.0	243.3	191.0
102.5°	400.7	353.0	299.7	247.4
105°	511.7	452.6	391.2	332.0
107.5°	614.5	549.5	475.8	422.6
110°	680.0	609.5	532.2	484.4



TEST NUMBER: P1436027

CATALOG NUMBER: SQ2W-FB-K-150U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	743.7	671.4	592.2	544.5
115°	830.1	750.5	677.7	636.8
117.5°	913.3	831.5	754.6	722.3
120°	964.3	882.4	807.4	782.3
122.5°	1006.1	926.1	856.5	846.0
125°	1068.9	987.0	927.9	941.5
127.5°	1119.9	1044.8	1007.5	1038.0
130°	1150.8	1084.8	1062.1	1105.3
132.5°	1178.1	1126.7	1116.7	1176.3
135°	1219.0	1189.4	1198.5	1280.4
137.5°	1267.7	1256.3	1286.8	1390.0
140°	1298.6	1305.4	1348.6	1464.6
142.5°	1340.5	1356.4	1412.3	1535.6
145°	1405.5	1439.6	1512.4	1635.2
147.5°	1479.2	1523.3	1613.4	1739.4
150°	1528.3	1585.2	1680.7	1801.2
152.5°	1584.7	1643.4	1738.9	1861.3
155°	1671.6	1737.5	1837.6	1942.2
157.5°	1760.3	1827.6	1923.1	2014.5
160°	1814.9	1887.6	1974.1	2058.2
162.5°	1876.7	1944.0	2019.6	2094.6
165°	1967.2	2021.8	2083.2	2146.9
167.5°	2043.2	2088.7	2136.9	2186.5
170°	2092.3	2128.7	2169.7	2208.3
172.5°	2134.2	2163.3	2193.3	2226.5
175°	2190.1	2206.0	2224.2	2244.7
177.5°	2233.3	2238.8	2244.2	2253.3
180°	2251.5	2251.5	2251.5	2251.5



TEST NUMBER: P1436027
 CATALOG NUMBER: SQ2W-FB-K-150U-050D-L830-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.06	8.75	9.19	9.88	11.45	17.65	18.35	18.79	19.47	21.05
	3H	8.98	9.60	10.12	10.74	12.33	19.25	19.87	20.39	21.00	22.59
	4H	9.37	9.96	10.52	11.10	12.69	19.41	20.01	20.57	21.14	22.74
	6H	9.62	10.16	10.78	11.30	12.90	19.48	20.02	20.64	21.16	22.77
	8H	9.70	10.22	10.87	11.37	12.97	19.49	20.01	20.66	21.16	22.76
	12H	9.75	10.24	10.91	11.38	13.01	19.47	19.96	20.63	21.10	22.73
4H	2H	12.75	13.35	13.91	14.48	16.08	18.00	18.59	19.16	19.72	21.32
	3H	13.87	14.36	15.03	15.52	17.13	19.87	20.36	21.03	21.52	23.13
	4H	14.14	14.59	15.31	15.74	17.37	20.08	20.54	21.25	21.69	23.31
	6H	14.26	14.65	15.44	15.83	17.44	20.20	20.59	21.38	21.76	23.38
	8H	14.30	14.66	15.47	15.83	17.46	20.24	20.61	21.42	21.77	23.40
	12H	14.29	14.62	15.48	15.80	17.44	20.22	20.55	21.41	21.72	23.36
8H	4H	15.32	15.68	16.49	16.84	18.48	20.16	20.52	21.33	21.68	23.32
	6H	15.57	15.87	16.76	17.07	18.70	20.35	20.65	21.54	21.85	23.48
	8H	15.66	15.92	16.86	17.11	18.76	20.44	20.70	21.63	21.88	23.53
	12H	15.70	15.93	16.90	17.11	18.79	20.43	20.66	21.63	21.84	23.53
12H	4H	15.33	15.66	16.52	16.84	18.48	20.10	20.43	21.29	21.61	23.24
	6H	15.67	15.93	16.87	17.12	18.77	20.33	20.59	21.53	21.77	23.42
	8H	15.80	16.03	17.00	17.21	18.89	20.42	20.65	21.62	21.83	23.51