

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427816

Luminaire Tested: SQ2W-F-K-150U-125D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1427816  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-F-K-150U-125D-L930-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - FROSTED CONTINUOUS ROLL LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10386.3 lumens  
Efficiency: N/A  
Efficacy: 99.6 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 104.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1427816

CATALOG NUMBER: SQ2W-F-K-150U-125D-L930-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1427816

CATALOG NUMBER: SQ2W-F-K-150U-125D-L930-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53	46
1	97	92	88	85	89	85	82	79	71	69	66	58	56	55	46	45	44	39
2	88	80	74	69	80	74	69	64	62	58	55	51	48	46	40	39	37	32
3	80	71	63	57	73	65	59	53	54	50	46	45	41	38	36	33	31	27
4	73	62	54	48	67	57	51	45	48	43	39	40	36	33	32	29	27	23
5	67	55	47	41	61	51	44	39	43	38	33	36	31	28	29	26	23	20
6	62	50	42	36	56	46	39	33	39	33	29	32	28	25	26	23	20	17
7	57	45	37	31	52	41	34	29	35	30	25	29	25	22	24	20	18	15
8	53	41	33	27	48	38	31	26	32	26	23	27	22	19	22	18	16	14
9	49	37	29	24	45	34	28	23	29	24	20	24	20	17	20	17	14	12
10	46	34	27	22	42	31	25	21	27	22	18	23	18	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	27457	27457	27457	27457
5°	27290	27601	27290	27601
10°	27194	27507	27194	27507
15°	27043	27384	27043	27384
20°	26872	27140	26872	27140
25°	26583	26818	26583	26818
30°	26302	26479	26302	26479
35°	25964	26130	25964	26130
40°	25669	25745	25669	25745
45°	25295	25295	25295	25295
50°	24786	24847	24786	24847
55°	24205	24239	24205	24239
60°	23550	23550	23550	23550
65°	22785	22693	22785	22693
70°	21710	21484	21710	21484
75°	20243	19800	20243	19800
80°	18038	17145	18038	17145
85°	14412	12208	14412	12208

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 20°  
 Vertical Angle: 45°  
 Luminance: 25464 cd/sqm



TEST NUMBER: P1427816

CATALOG NUMBER: SQ2W-F-K-150U-125D-L930-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	160.9	1.5
10°-20°	459.8	4.4
20°-30°	692.1	6.7
30°-40°	827.6	8.0
40°-50°	854.6	8.2
50°-60°	770.8	7.4
60°-70°	590.5	5.7
70°-80°	341.2	3.3
80°-90°	96.6	0.9
90°-100°	152.4	1.5
100°-110°	444.5	4.3
110°-120°	725.4	7.0
120°-130°	920.5	8.9
130°-140°	985.0	9.5
140°-150°	919.8	8.9
150°-160°	756.8	7.3
160°-170°	507.6	4.9
170°-180°	180.2	1.7
0°-30°	1312.7	12.6
0°-40°	2140.3	20.6
0°-60°	3765.7	36.3
0°-90°	4794.0	46.2
90°-120°	1322.4	12.7
90°-150°	4147.7	39.9
90°-180°	5592.0	53.8
0°-180°	10386.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1701	1701	1701	1701	1701	
5°	1684	1703	1684	1703	1684	160
15°	1618	1638	1618	1638	1618	456
25°	1492	1505	1492	1505	1492	688
35°	1317	1326	1317	1326	1317	825
45°	1108	1108	1108	1108	1108	854
55°	860	861	860	861	860	768
65°	596	594	596	594	596	590
75°	324	317	324	317	324	344
85°	78	66	78	66	78	91
90°	6	43	6	83	6	8
95°	60	44	60	261	60	72
105°	282	453	282	623	282	300
115°	542	751	542	925	542	534
125°	801	1190	801	1134	801	717
135°	1089	1557	1089	1256	1089	842
145°	1391	1795	1391	1283	1391	870
155°	1652	1950	1652	1331	1652	759
165°	1826	2033	1826	1532	1826	514
175°	1910	1991	1910	1797	1910	181
180°	1915	1915	1915	1915	1915	



TEST NUMBER: P1427816

CATALOG NUMBER: SQ2W-F-K-150U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6
2.5°	1692.0	1700.0	1708.1	1704.7	1697.5	1694.7	1696.4	1697.9	1698.8	1699.6	1698.8
5°	1683.8	1694.5	1705.1	1701.4	1692.9	1689.1	1690.2	1692.3	1697.6	1703.0	1697.6
7.5°	1670.2	1680.8	1691.4	1688.0	1679.9	1676.5	1677.8	1680.2	1685.7	1691.2	1685.7
10°	1658.7	1669.3	1679.9	1676.2	1667.7	1664.5	1666.6	1669.3	1673.6	1677.8	1673.6
12.5°	1644.3	1654.9	1665.6	1662.5	1654.8	1651.6	1652.9	1655.0	1659.7	1664.4	1659.7
15°	1617.9	1628.6	1639.2	1636.3	1628.9	1625.9	1627.5	1629.8	1634.0	1638.3	1634.0
17.5°	1586.1	1596.1	1606.1	1603.4	1596.5	1593.9	1595.7	1598.0	1601.8	1605.5	1601.8
20°	1564.0	1573.6	1583.2	1580.4	1573.5	1570.3	1570.8	1572.2	1575.9	1579.6	1575.9
22.5°	1537.2	1546.8	1556.4	1553.9	1547.4	1543.6	1542.4	1542.7	1547.3	1551.8	1547.3
25°	1492.2	1501.8	1511.4	1509.4	1503.5	1499.8	1498.2	1497.9	1501.6	1505.4	1501.6
27.5°	1445.2	1453.2	1461.2	1459.5	1454.6	1451.7	1450.6	1450.5	1453.1	1455.8	1453.1
30°	1410.8	1418.7	1426.7	1424.7	1419.4	1416.2	1415.1	1415.0	1417.7	1420.3	1417.7
32.5°	1374.4	1381.9	1389.5	1386.7	1380.6	1377.4	1377.1	1377.8	1380.8	1383.9	1380.8
35°	1317.3	1323.7	1330.1	1327.3	1321.5	1318.8	1319.3	1320.4	1323.1	1325.7	1323.1
37.5°	1260.1	1265.0	1269.9	1267.0	1261.6	1258.8	1258.7	1259.2	1261.5	1263.7	1261.5
40°	1217.9	1223.3	1228.6	1225.5	1219.7	1216.5	1215.9	1216.2	1218.9	1221.5	1218.9
42.5°	1174.8	1178.9	1182.9	1180.2	1175.2	1172.8	1173.2	1173.7	1175.1	1176.5	1175.1
45°	1107.8	1111.5	1115.2	1112.6	1107.8	1105.4	1105.4	1105.6	1106.7	1107.8	1106.7
47.5°	1037.6	1040.5	1043.3	1041.3	1037.5	1035.4	1034.7	1034.7	1036.4	1038.1	1036.4
50°	986.8	990.5	994.3	992.4	988.7	986.3	985.2	984.9	987.1	989.2	987.1
52.5°	937.0	941.1	945.3	943.5	939.8	937.2	935.7	935.0	936.7	938.4	936.7
55°	859.9	864.7	869.4	868.3	865.1	862.4	860.3	858.9	860.0	861.1	860.0
57.5°	781.1	785.7	790.4	789.5	786.8	784.1	781.5	780.0	781.5	783.0	781.5
60°	729.3	733.6	737.8	736.5	733.3	730.7	728.5	727.2	728.3	729.3	728.3
62.5°	676.6	680.9	685.2	683.5	679.9	677.0	674.9	673.5	674.6	675.7	674.6
65°	596.4	600.1	603.8	602.4	599.2	596.5	594.4	592.9	593.5	594.0	593.5
67.5°	515.4	518.6	521.8	520.3	517.2	514.1	511.1	508.9	509.8	510.7	509.8
70°	459.9	463.1	466.3	465.1	462.4	459.7	457.1	455.1	455.1	455.1	455.1
72.5°	406.2	409.0	411.8	410.1	407.0	404.4	402.1	400.5	400.5	400.5	400.5
75°	324.5	326.1	327.7	326.9	325.3	323.2	320.6	318.4	317.9	317.4	317.9
77.5°	245.7	245.7	245.7	244.2	242.2	240.2	238.2	236.5	235.8	235.2	235.8
80°	194.0	194.0	194.0	192.8	191.2	189.6	188.0	186.6	185.5	184.4	185.5
82.5°	146.1	145.3	144.4	143.0	141.4	139.4	136.9	135.4	136.4	137.5	136.4
85°	77.8	76.8	75.7	74.3	72.7	70.8	68.7	66.9	66.4	65.9	66.4
87.5°	25.1	25.8	26.9	27.3	27.2	26.0	24.3	23.3	23.3	22.9	23.3
90°	5.8	13.5	23.2	31.0	36.8	38.7	38.7	40.6	42.6	42.6	42.6
92.5°	21.3	33.7	34.0	34.0	41.4	44.9	48.0	48.4	50.3	50.3	50.3
95°	60.0	65.8	98.7	96.7	65.8	52.2	44.5	44.5	44.5	44.5	44.5
97.5°	114.5	123.0	128.5	172.2	181.9	175.7	143.2	120.3	107.6	101.8	107.6
100°	162.5	166.4	178.0	179.9	228.3	274.7	251.5	222.5	212.8	207.0	212.8
102.5°	210.5	212.8	230.6	238.7	250.0	276.3	356.7	347.8	341.3	340.1	341.3
105°	282.5	284.4	317.3	332.8	340.5	340.5	338.6	377.3	439.2	452.7	439.2
107.5°	359.5	368.4	407.0	448.4	457.3	459.7	449.6	443.8	441.5	443.0	441.5
110°	412.1	425.6	472.1	524.3	537.8	541.7	537.8	532.0	528.2	528.2	528.2



TEST NUMBER: P1427816

CATALOG NUMBER: SQ2W-F-K-150U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	463.2	482.9	535.5	595.5	618.3	629.9	621.4	617.2	613.3	616.4	613.3
115°	541.7	570.7	640.4	702.3	748.7	754.5	752.6	752.6	750.6	750.6	750.6
117.5°	614.4	660.9	739.0	811.0	864.8	880.3	888.0	885.7	883.4	887.2	883.4
120°	665.5	719.7	808.7	889.9	942.2	965.4	973.1	969.3	973.1	969.3	973.1
122.5°	719.7	786.2	873.7	958.0	1019.6	1045.9	1055.2	1055.9	1056.7	1054.4	1056.7
125°	800.9	882.2	984.7	1071.8	1135.6	1166.6	1174.3	1176.3	1180.1	1189.8	1180.1
127.5°	883.0	975.1	1087.7	1171.6	1237.0	1274.5	1286.5	1290.8	1298.9	1303.2	1298.9
130°	940.2	1044.7	1158.8	1238.2	1302.0	1342.6	1363.9	1369.7	1379.4	1377.5	1379.4
132.5°	1000.6	1109.7	1225.4	1307.8	1367.0	1410.7	1428.9	1445.6	1449.0	1451.8	1449.0
135°	1089.2	1207.2	1323.3	1404.5	1460.7	1503.2	1526.4	1541.9	1551.6	1557.4	1551.6
137.5°	1182.5	1307.0	1418.5	1490.8	1547.3	1584.1	1610.4	1626.6	1636.7	1641.3	1636.7
140°	1245.9	1365.9	1474.2	1549.6	1599.9	1636.7	1659.9	1679.3	1690.9	1690.9	1690.9
142.5°	1306.3	1424.7	1529.9	1605.4	1649.5	1683.1	1707.9	1722.6	1735.8	1735.8	1735.8
145°	1391.0	1509.0	1605.8	1681.2	1718.0	1748.9	1776.0	1787.6	1795.3	1795.3	1795.3
147.5°	1479.6	1584.1	1672.3	1744.7	1775.6	1812.0	1833.3	1842.6	1852.2	1848.0	1852.2
150°	1532.2	1629.0	1714.1	1781.8	1812.8	1847.6	1868.9	1876.6	1886.3	1880.5	1886.3
152.5°	1583.3	1675.4	1752.8	1815.9	1842.2	1877.0	1901.4	1909.1	1915.7	1911.4	1915.7
155°	1652.2	1733.4	1805.0	1863.1	1886.3	1919.2	1942.4	1952.1	1959.8	1950.1	1959.8
157.5°	1713.7	1783.7	1846.0	1899.4	1924.2	1952.4	1974.1	1986.1	1993.8	1989.6	1993.8
160°	1750.8	1814.7	1870.8	1921.1	1944.3	1969.5	1992.7	2006.2	2014.0	2008.2	2014.0
162.5°	1781.8	1839.5	1892.5	1938.1	1958.2	1980.3	2008.2	2020.2	2027.9	2020.5	2027.9
165°	1826.3	1872.7	1919.2	1957.9	1975.3	1992.7	2021.7	2035.2	2041.0	2033.3	2041.0
167.5°	1860.0	1895.6	1933.1	1966.4	1979.1	1996.2	2025.2	2036.4	2043.8	2034.1	2043.8
170°	1878.5	1909.5	1942.4	1969.5	1979.1	1994.6	2023.6	2033.3	2039.1	2029.4	2039.1
172.5°	1894.0	1917.2	1943.9	1967.9	1972.9	1985.3	2012.8	2022.5	2026.7	2018.6	2026.7
175°	1909.5	1923.0	1942.4	1957.9	1955.9	1963.7	1986.9	1994.6	2002.4	1990.7	2002.4
177.5°	1916.8	1923.0	1929.2	1938.5	1932.3	1932.3	1949.3	1954.0	1955.5	1949.3	1955.5
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1427816

CATALOG NUMBER: SQ2W-F-K-150U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6
2.5°	1697.9	1696.4	1694.7	1697.5	1704.7	1708.1	1700.0	1692.0	1700.0	1708.1	1704.7
5°	1692.3	1690.2	1689.1	1692.9	1701.4	1705.1	1694.5	1683.8	1694.5	1705.1	1701.4
7.5°	1680.2	1677.8	1676.5	1679.9	1688.0	1691.4	1680.8	1670.2	1680.8	1691.4	1688.0
10°	1669.3	1666.6	1664.5	1667.7	1676.2	1679.9	1669.3	1658.7	1669.3	1679.9	1676.2
12.5°	1655.0	1652.9	1651.6	1654.8	1662.5	1665.6	1654.9	1644.3	1654.9	1665.6	1662.5
15°	1629.8	1627.5	1625.9	1628.9	1636.3	1639.2	1628.6	1617.9	1628.6	1639.2	1636.3
17.5°	1598.0	1595.7	1593.9	1596.5	1603.4	1606.1	1596.1	1586.1	1596.1	1606.1	1603.4
20°	1572.2	1570.8	1570.3	1573.5	1580.4	1583.2	1573.6	1564.0	1573.6	1583.2	1580.4
22.5°	1542.7	1542.4	1543.6	1547.4	1553.9	1556.4	1546.8	1537.2	1546.8	1556.4	1553.9
25°	1497.9	1498.2	1499.8	1503.5	1509.4	1511.4	1501.8	1492.2	1501.8	1511.4	1509.4
27.5°	1450.5	1450.6	1451.7	1454.6	1459.5	1461.2	1453.2	1445.2	1453.2	1461.2	1459.5
30°	1415.0	1415.1	1416.2	1419.4	1424.7	1426.7	1418.7	1410.8	1418.7	1426.7	1424.7
32.5°	1377.8	1377.1	1377.4	1380.6	1386.7	1389.5	1381.9	1374.4	1381.9	1389.5	1386.7
35°	1320.4	1319.3	1318.8	1321.5	1327.3	1330.1	1323.7	1317.3	1323.7	1330.1	1327.3
37.5°	1259.2	1258.7	1258.8	1261.6	1267.0	1269.9	1265.0	1260.1	1265.0	1269.9	1267.0
40°	1216.2	1215.9	1216.5	1219.7	1225.5	1228.6	1223.3	1217.9	1223.3	1228.6	1225.5
42.5°	1173.7	1173.2	1172.8	1175.2	1180.2	1182.9	1178.9	1174.8	1178.9	1182.9	1180.2
45°	1105.6	1105.4	1105.4	1107.8	1112.6	1115.2	1111.5	1107.8	1111.5	1115.2	1112.6
47.5°	1034.7	1034.7	1035.4	1037.5	1041.3	1043.3	1040.5	1037.6	1040.5	1043.3	1041.3
50°	984.9	985.2	986.3	988.7	992.4	994.3	990.5	986.8	990.5	994.3	992.4
52.5°	935.0	935.7	937.2	939.8	943.5	945.3	941.1	937.0	941.1	945.3	943.5
55°	858.9	860.3	862.4	865.1	868.3	869.4	864.7	859.9	864.7	869.4	868.3
57.5°	780.0	781.5	784.1	786.8	789.5	790.4	785.7	781.1	785.7	790.4	789.5
60°	727.2	728.5	730.7	733.3	736.5	737.8	733.6	729.3	733.6	737.8	736.5
62.5°	673.5	674.9	677.0	679.9	683.5	685.2	680.9	676.6	680.9	685.2	683.5
65°	592.9	594.4	596.5	599.2	602.4	603.8	600.1	596.4	600.1	603.8	602.4
67.5°	508.9	511.1	514.1	517.2	520.3	521.8	518.6	515.4	518.6	521.8	520.3
70°	455.1	457.1	459.7	462.4	465.1	466.3	463.1	459.9	463.1	466.3	465.1
72.5°	400.5	402.1	404.4	407.0	410.1	411.8	409.0	406.2	409.0	411.8	410.1
75°	318.4	320.6	323.2	325.3	326.9	327.7	326.1	324.5	326.1	327.7	326.9
77.5°	236.5	238.2	240.2	242.2	244.2	245.7	245.7	245.7	245.7	245.7	244.2
80°	186.6	188.0	189.6	191.2	192.8	194.0	194.0	194.0	194.0	194.0	192.8
82.5°	135.4	136.9	139.4	141.4	143.0	144.4	145.3	146.1	145.3	144.4	143.0
85°	66.9	68.7	70.8	72.7	74.3	75.7	76.8	77.8	76.8	75.7	74.3
87.5°	23.3	24.3	26.0	27.2	27.3	26.9	25.8	25.1	25.8	26.5	28.0
90°	40.6	38.7	38.7	36.8	31.0	23.2	13.5	5.8	13.5	21.3	34.8
92.5°	48.4	48.0	44.9	41.4	34.0	34.0	33.7	21.3	36.8	52.2	75.1
95°	44.5	44.5	52.2	65.8	96.7	98.7	65.8	60.0	85.1	119.9	150.9
97.5°	120.3	143.2	175.7	181.9	172.2	128.5	123.0	114.5	155.9	190.4	240.3
100°	222.5	251.5	274.7	228.3	179.9	178.0	166.4	162.5	207.0	239.9	288.3
102.5°	347.8	356.7	276.3	250.0	238.7	230.6	212.8	210.5	255.0	300.3	340.9
105°	377.3	338.6	340.5	340.5	332.8	317.3	284.4	282.5	332.8	385.0	435.3
107.5°	443.8	449.6	459.7	457.3	448.4	407.0	368.4	359.5	404.7	467.4	522.7
110°	532.0	537.8	541.7	537.8	524.3	472.1	425.6	412.1	452.7	518.5	578.5



TEST NUMBER: P1427816

CATALOG NUMBER: SQ2W-F-K-150U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	617.2	621.4	629.9	618.3	595.5	535.5	482.9	463.2	503.8	571.1	632.6
115°	752.6	752.6	754.5	748.7	702.3	640.4	570.7	541.7	576.5	638.4	706.1
117.5°	885.7	888.0	880.3	864.8	811.0	739.0	660.9	614.4	641.9	707.3	777.0
120°	969.3	973.1	965.4	942.2	889.9	808.7	719.7	665.5	686.8	750.6	820.3
122.5°	1055.9	1055.2	1045.9	1019.6	958.0	873.7	786.2	719.7	728.6	787.8	855.9
125°	1176.3	1174.3	1166.6	1135.6	1071.8	984.7	882.2	800.9	789.3	839.6	909.3
127.5°	1290.8	1286.5	1274.5	1237.0	1171.6	1087.7	975.1	883.0	857.0	888.8	952.6
130°	1369.7	1363.9	1342.6	1302.0	1238.2	1158.8	1044.7	940.2	903.5	922.8	978.9
132.5°	1445.6	1428.9	1410.7	1367.0	1307.8	1225.4	1109.7	1000.6	949.9	958.4	1002.1
135°	1541.9	1526.4	1503.2	1460.7	1404.5	1323.3	1207.2	1089.2	1019.6	1011.8	1037.0
137.5°	1626.6	1610.4	1584.1	1547.3	1490.8	1418.5	1307.0	1182.5	1094.6	1068.7	1078.4
140°	1679.3	1659.9	1636.7	1599.9	1549.6	1474.2	1365.9	1245.9	1147.2	1110.5	1104.7
142.5°	1722.6	1707.9	1683.1	1649.5	1605.4	1529.9	1424.7	1306.3	1201.4	1153.8	1140.3
145°	1787.6	1776.0	1748.9	1718.0	1681.2	1605.8	1509.0	1391.0	1286.5	1224.6	1195.6
147.5°	1842.6	1833.3	1812.0	1775.6	1744.7	1672.3	1584.1	1479.6	1372.4	1295.8	1258.3
150°	1876.6	1868.9	1847.6	1812.8	1781.8	1714.1	1629.0	1532.2	1429.7	1348.4	1300.1
152.5°	1909.1	1901.4	1877.0	1842.2	1815.9	1752.8	1675.4	1583.3	1479.2	1398.0	1348.1
155°	1952.1	1942.4	1919.2	1886.3	1863.1	1805.0	1733.4	1652.2	1563.2	1478.1	1422.0
157.5°	1986.1	1974.1	1952.4	1924.2	1899.4	1846.0	1783.7	1713.7	1635.9	1554.7	1497.4
160°	2006.2	1992.7	1969.5	1944.3	1921.1	1870.8	1814.7	1750.8	1679.3	1605.8	1543.8
162.5°	2020.2	2008.2	1980.3	1958.2	1938.1	1892.5	1839.5	1781.8	1718.0	1653.7	1596.5
165°	2035.2	2021.7	1992.7	1975.3	1957.9	1919.2	1872.7	1826.3	1772.1	1719.9	1673.5
167.5°	2036.4	2025.2	1996.2	1979.1	1966.4	1933.1	1895.6	1860.0	1817.8	1776.8	1738.1
170°	2033.3	2023.6	1994.6	1979.1	1969.5	1942.4	1909.5	1878.5	1845.6	1810.8	1779.9
172.5°	2022.5	2012.8	1985.3	1972.9	1967.9	1943.9	1917.2	1894.0	1865.8	1840.2	1815.5
175°	1994.6	1986.9	1963.7	1955.9	1957.9	1942.4	1923.0	1909.5	1892.1	1876.6	1863.1
177.5°	1954.0	1949.3	1932.3	1932.3	1938.5	1929.2	1923.0	1916.8	1909.1	1904.5	1899.8
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1427816

CATALOG NUMBER: SQ2W-F-K-150U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6
2.5°	1697.5	1694.7	1696.4	1697.9	1698.8	1699.6	1698.8	1697.9	1696.4	1694.7	1697.5
5°	1692.9	1689.1	1690.2	1692.3	1697.6	1703.0	1697.6	1692.3	1690.2	1689.1	1692.9
7.5°	1679.9	1676.5	1677.8	1680.2	1685.7	1691.2	1685.7	1680.2	1677.8	1676.5	1679.9
10°	1667.7	1664.5	1666.6	1669.3	1673.6	1677.8	1673.6	1669.3	1666.6	1664.5	1667.7
12.5°	1654.8	1651.6	1652.9	1655.0	1659.7	1664.4	1659.7	1655.0	1652.9	1651.6	1654.8
15°	1628.9	1625.9	1627.5	1629.8	1634.0	1638.3	1634.0	1629.8	1627.5	1625.9	1628.9
17.5°	1596.5	1593.9	1595.7	1598.0	1601.8	1605.5	1601.8	1598.0	1595.7	1593.9	1596.5
20°	1573.5	1570.3	1570.8	1572.2	1575.9	1579.6	1575.9	1572.2	1570.8	1570.3	1573.5
22.5°	1547.4	1543.6	1542.4	1542.7	1547.3	1551.8	1547.3	1542.7	1542.4	1543.6	1547.4
25°	1503.5	1499.8	1498.2	1497.9	1501.6	1505.4	1501.6	1497.9	1498.2	1499.8	1503.5
27.5°	1454.6	1451.7	1450.6	1450.5	1453.1	1455.8	1453.1	1450.5	1450.6	1451.7	1454.6
30°	1419.4	1416.2	1415.1	1415.0	1417.7	1420.3	1417.7	1415.0	1415.1	1416.2	1419.4
32.5°	1380.6	1377.4	1377.1	1377.8	1380.8	1383.9	1380.8	1377.8	1377.1	1377.4	1380.6
35°	1321.5	1318.8	1319.3	1320.4	1323.1	1325.7	1323.1	1320.4	1319.3	1318.8	1321.5
37.5°	1261.6	1258.8	1258.7	1259.2	1261.5	1263.7	1261.5	1259.2	1258.7	1258.8	1261.6
40°	1219.7	1216.5	1215.9	1216.2	1218.9	1221.5	1218.9	1216.2	1215.9	1216.5	1219.7
42.5°	1175.2	1172.8	1173.2	1173.7	1175.1	1176.5	1175.1	1173.7	1173.2	1172.8	1175.2
45°	1107.8	1105.4	1105.4	1105.6	1106.7	1107.8	1106.7	1105.6	1105.4	1105.4	1107.8
47.5°	1037.5	1035.4	1034.7	1034.7	1036.4	1038.1	1036.4	1034.7	1034.7	1035.4	1037.5
50°	988.7	986.3	985.2	984.9	987.1	989.2	987.1	984.9	985.2	986.3	988.7
52.5°	939.8	937.2	935.7	935.0	936.7	938.4	936.7	935.0	935.7	937.2	939.8
55°	865.1	862.4	860.3	858.9	860.0	861.1	860.0	858.9	860.3	862.4	865.1
57.5°	786.8	784.1	781.5	780.0	781.5	783.0	781.5	780.0	781.5	784.1	786.8
60°	733.3	730.7	728.5	727.2	728.3	729.3	728.3	727.2	728.5	730.7	733.3
62.5°	679.9	677.0	674.9	673.5	674.6	675.7	674.6	673.5	674.9	677.0	679.9
65°	599.2	596.5	594.4	592.9	593.5	594.0	593.5	592.9	594.4	596.5	599.2
67.5°	517.2	514.1	511.1	508.9	509.8	510.7	509.8	508.9	511.1	514.1	517.2
70°	462.4	459.7	457.1	455.1	455.1	455.1	455.1	455.1	457.1	459.7	462.4
72.5°	407.0	404.4	402.1	400.5	400.5	400.5	400.5	400.5	402.1	404.4	407.0
75°	325.3	323.2	320.6	318.4	317.9	317.4	317.9	318.4	320.6	323.2	325.3
77.5°	242.2	240.2	238.2	236.5	235.8	235.2	235.8	236.5	238.2	240.2	242.2
80°	191.2	189.6	188.0	186.6	185.5	184.4	185.5	186.6	188.0	189.6	191.2
82.5°	141.4	139.4	136.9	135.4	136.4	137.5	136.4	135.4	136.9	139.4	141.4
85°	72.7	70.8	68.7	66.9	66.4	65.9	66.4	66.9	68.7	70.8	72.7
87.5°	28.7	29.9	30.9	31.1	32.2	31.0	32.2	31.1	30.9	29.9	28.7
90°	44.5	58.0	71.6	79.3	87.1	83.2	87.1	79.3	71.6	58.0	44.5
92.5°	89.4	112.2	128.8	142.8	149.0	148.2	149.0	142.8	128.8	112.2	89.4
95°	179.9	207.0	234.1	253.4	265.0	261.2	265.0	253.4	234.1	207.0	179.9
97.5°	277.4	313.8	344.0	362.2	373.8	381.5	373.8	362.2	344.0	313.8	277.4
100°	342.4	377.3	412.1	433.4	452.7	460.4	452.7	433.4	412.1	377.3	342.4
102.5°	395.1	440.7	478.6	501.5	517.7	525.4	517.7	501.5	478.6	440.7	395.1
105°	481.7	530.1	570.7	599.7	617.2	623.0	617.2	599.7	570.7	530.1	481.7
107.5°	568.4	618.3	655.8	688.0	709.2	721.6	709.2	688.0	655.8	618.3	568.4
110°	636.5	677.1	717.8	746.8	768.1	775.8	768.1	746.8	717.8	677.1	636.5



TEST NUMBER: P1427816

CATALOG NUMBER: SQ2W-F-K-150U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	693.8	739.0	779.7	808.7	833.1	843.9	833.1	808.7	779.7	739.0	693.8
115°	773.9	833.8	870.6	897.7	915.1	924.8	915.1	897.7	870.6	833.8	773.9
117.5°	840.4	903.1	943.3	964.2	972.4	979.3	972.4	964.2	943.3	903.1	840.4
120°	882.2	940.2	986.7	1013.8	1023.4	1027.3	1023.4	1013.8	986.7	940.2	882.2
122.5°	920.9	975.8	1020.7	1054.0	1069.9	1073.7	1069.9	1054.0	1020.7	975.8	920.9
125°	975.1	1027.3	1073.7	1106.6	1124.0	1133.7	1124.0	1106.6	1073.7	1027.3	975.1
127.5°	1022.3	1078.8	1121.3	1151.1	1168.1	1175.9	1168.1	1151.1	1121.3	1078.8	1022.3
130°	1048.6	1106.6	1149.2	1182.1	1197.5	1205.3	1197.5	1182.1	1149.2	1106.6	1048.6
132.5°	1068.7	1129.8	1173.9	1203.7	1220.8	1228.5	1220.8	1203.7	1173.9	1129.8	1068.7
135°	1093.1	1156.9	1203.3	1232.4	1247.8	1255.6	1247.8	1232.4	1203.3	1156.9	1093.1
137.5°	1114.4	1172.4	1220.8	1251.3	1265.3	1270.3	1265.3	1251.3	1220.8	1172.4	1114.4
140°	1129.8	1180.1	1228.5	1257.5	1273.0	1274.9	1273.0	1257.5	1228.5	1180.1	1129.8
142.5°	1150.0	1189.4	1231.6	1260.6	1276.1	1279.6	1276.1	1260.6	1231.6	1189.4	1150.0
145°	1185.9	1209.2	1238.2	1265.3	1278.8	1282.7	1278.8	1265.3	1238.2	1209.2	1185.9
147.5°	1231.2	1238.6	1253.6	1271.4	1284.6	1287.3	1284.6	1271.4	1253.6	1238.6	1231.2
150°	1265.3	1263.3	1269.1	1280.7	1292.3	1290.4	1292.3	1280.7	1269.1	1263.3	1265.3
152.5°	1303.9	1292.7	1292.3	1297.8	1303.2	1302.8	1303.2	1297.8	1292.3	1292.7	1303.9
155°	1369.7	1348.4	1336.8	1333.0	1333.0	1331.0	1333.0	1333.0	1336.8	1348.4	1369.7
157.5°	1442.1	1412.3	1394.9	1385.6	1382.9	1378.6	1382.9	1385.6	1394.9	1412.3	1442.1
160°	1491.6	1458.7	1441.3	1425.8	1420.0	1414.2	1420.0	1425.8	1441.3	1458.7	1491.6
162.5°	1538.0	1506.7	1487.7	1473.8	1468.0	1459.1	1468.0	1473.8	1487.7	1506.7	1538.0
165°	1613.5	1580.6	1559.3	1547.7	1540.0	1532.2	1540.0	1547.7	1559.3	1580.6	1613.5
167.5°	1688.9	1653.0	1639.0	1625.9	1618.5	1604.6	1618.5	1625.9	1639.0	1653.0	1688.9
170°	1735.4	1702.5	1694.7	1683.1	1669.6	1654.1	1669.6	1683.1	1694.7	1702.5	1735.4
172.5°	1775.6	1753.6	1745.8	1734.2	1730.0	1717.6	1730.0	1734.2	1745.8	1753.6	1775.6
175°	1834.0	1816.6	1816.6	1814.7	1808.9	1797.3	1808.9	1814.7	1816.6	1816.6	1834.0
177.5°	1882.8	1873.5	1879.7	1879.7	1878.1	1867.3	1878.1	1879.7	1879.7	1873.5	1882.8
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1427816

CATALOG NUMBER: SQ2W-F-K-150U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	1700.6	1700.6	1700.6	1700.6
2.5°	1704.7	1708.1	1700.0	1692.0
5°	1701.4	1705.1	1694.5	1683.8
7.5°	1688.0	1691.4	1680.8	1670.2
10°	1676.2	1679.9	1669.3	1658.7
12.5°	1662.5	1665.6	1654.9	1644.3
15°	1636.3	1639.2	1628.6	1617.9
17.5°	1603.4	1606.1	1596.1	1586.1
20°	1580.4	1583.2	1573.6	1564.0
22.5°	1553.9	1556.4	1546.8	1537.2
25°	1509.4	1511.4	1501.8	1492.2
27.5°	1459.5	1461.2	1453.2	1445.2
30°	1424.7	1426.7	1418.7	1410.8
32.5°	1386.7	1389.5	1381.9	1374.4
35°	1327.3	1330.1	1323.7	1317.3
37.5°	1267.0	1269.9	1265.0	1260.1
40°	1225.5	1228.6	1223.3	1217.9
42.5°	1180.2	1182.9	1178.9	1174.8
45°	1112.6	1115.2	1111.5	1107.8
47.5°	1041.3	1043.3	1040.5	1037.6
50°	992.4	994.3	990.5	986.8
52.5°	943.5	945.3	941.1	937.0
55°	868.3	869.4	864.7	859.9
57.5°	789.5	790.4	785.7	781.1
60°	736.5	737.8	733.6	729.3
62.5°	683.5	685.2	680.9	676.6
65°	602.4	603.8	600.1	596.4
67.5°	520.3	521.8	518.6	515.4
70°	465.1	466.3	463.1	459.9
72.5°	410.1	411.8	409.0	406.2
75°	326.9	327.7	326.1	324.5
77.5°	244.2	245.7	245.7	245.7
80°	192.8	194.0	194.0	194.0
82.5°	143.0	144.4	145.3	146.1
85°	74.3	75.7	76.8	77.8
87.5°	28.0	26.5	25.8	25.1
90°	34.8	21.3	13.5	5.8
92.5°	75.1	52.2	36.8	21.3
95°	150.9	119.9	85.1	60.0
97.5°	240.3	190.4	155.9	114.5
100°	288.3	239.9	207.0	162.5
102.5°	340.9	300.3	255.0	210.5
105°	435.3	385.0	332.8	282.5
107.5°	522.7	467.4	404.7	359.5
110°	578.5	518.5	452.7	412.1



TEST NUMBER: P1427816

CATALOG NUMBER: SQ2W-F-K-150U-125D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	632.6	571.1	503.8	463.2
115°	706.1	638.4	576.5	541.7
117.5°	777.0	707.3	641.9	614.4
120°	820.3	750.6	686.8	665.5
122.5°	855.9	787.8	728.6	719.7
125°	909.3	839.6	789.3	800.9
127.5°	952.6	888.8	857.0	883.0
130°	978.9	922.8	903.5	940.2
132.5°	1002.1	958.4	949.9	1000.6
135°	1037.0	1011.8	1019.6	1089.2
137.5°	1078.4	1068.7	1094.6	1182.5
140°	1104.7	1110.5	1147.2	1245.9
142.5°	1140.3	1153.8	1201.4	1306.3
145°	1195.6	1224.6	1286.5	1391.0
147.5°	1258.3	1295.8	1372.4	1479.6
150°	1300.1	1348.4	1429.7	1532.2
152.5°	1348.1	1398.0	1479.2	1583.3
155°	1422.0	1478.1	1563.2	1652.2
157.5°	1497.4	1554.7	1635.9	1713.7
160°	1543.8	1605.8	1679.3	1750.8
162.5°	1596.5	1653.7	1718.0	1781.8
165°	1673.5	1719.9	1772.1	1826.3
167.5°	1738.1	1776.8	1817.8	1860.0
170°	1779.9	1810.8	1845.6	1878.5
172.5°	1815.5	1840.2	1865.8	1894.0
175°	1863.1	1876.6	1892.1	1909.5
177.5°	1899.8	1904.5	1909.1	1916.8
180°	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1427816  
 CATALOG NUMBER: SQ2W-F-K-150U-125D-L930-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.00	19.84	19.99	20.84	22.17	18.92	19.76	19.91	20.76	22.08
	3H	20.79	21.55	21.79	22.56	23.90	20.69	21.44	21.69	22.45	23.80
	4H	21.49	22.20	22.50	23.21	24.57	21.37	22.09	22.38	23.10	24.45
	6H	21.92	22.58	22.94	23.60	24.96	21.78	22.44	22.80	23.46	24.82
	8H	22.08	22.71	23.11	23.74	25.11	21.93	22.55	22.95	23.59	24.95
	12H	22.17	22.76	23.20	23.79	25.18	21.99	22.59	23.02	23.61	25.00
4H	2H	19.58	20.29	20.60	21.31	22.66	19.52	20.23	20.53	21.24	22.60
	3H	21.60	22.20	22.63	23.24	24.61	21.51	22.10	22.53	23.15	24.51
	4H	22.41	22.96	23.45	23.99	25.38	22.30	22.85	23.34	23.88	25.27
	6H	22.97	23.44	24.01	24.49	25.88	22.82	23.29	23.87	24.35	25.74
	8H	23.18	23.62	24.22	24.67	26.07	23.02	23.46	24.06	24.51	25.91
	12H	23.29	23.69	24.36	24.75	26.16	23.11	23.50	24.17	24.57	25.97
8H	4H	22.66	23.10	23.70	24.15	25.55	22.56	23.00	23.60	24.05	25.45
	6H	23.34	23.71	24.41	24.80	26.20	23.21	23.58	24.28	24.67	26.07
	8H	23.65	23.97	24.73	25.04	26.46	23.49	23.81	24.57	24.89	26.31
	12H	23.83	24.11	24.91	25.18	26.64	23.64	23.92	24.72	24.99	26.45
12H	4H	22.65	23.05	23.71	24.11	25.52	22.56	22.95	23.62	24.02	25.42
	6H	23.39	23.71	24.47	24.79	26.21	23.27	23.59	24.35	24.67	26.08
	8H	23.73	24.01	24.81	25.08	26.54	23.58	23.86	24.66	24.93	26.39