

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428059

Luminaire Tested: SQ2W-PP3-K-075U-050D-L830-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428059
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-7)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PP3-K-075U-050D-L830-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE PRISM LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5963.3 lumens
Efficiency: N/A
Efficacy: 144.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.41 / 1.4
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 41.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428059

CATALOG NUMBER: SQ2W-PP3-K-075U-050D-L830-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428059

CATALOG NUMBER: SQ2W-PP3-K-075U-050D-L830-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	93	89	86	89	86	82	80	71	69	67	58	57	56	46	46	45	39
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29
4	75	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25
5	68	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25	22
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	25	22	19
7	58	46	39	33	53	43	36	31	37	31	27	31	27	24	25	22	20	17
8	54	42	35	29	50	39	32	28	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17269	17269	17269	17269
5°	17134	17445	17134	17445
10°	17221	17573	17221	17573
15°	17180	17614	17180	17614
20°	17056	17970	17056	17970
25°	16960	18914	16960	18914
30°	16863	19309	16863	19309
35°	16625	19343	16625	19343
40°	16180	17873	16180	17873
45°	15696	13606	15696	13606
50°	15081	11331	15081	11331
55°	14035	8146	14035	8146
60°	12083	5841	12083	5841
65°	10193	5746	10193	5746
70°	8488	5500	8488	5500
75°	7193	5146	7193	5146
80°	6099	4621	6099	4621
85°	4816	2519	4816	2519

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 17171 cd/sqm



TEST NUMBER: P1428059

CATALOG NUMBER: SQ2W-PP3-K-075U-050D-L830-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.8	1.7
10°-20°	294.8	4.9
20°-30°	461.8	7.7
30°-40°	569.6	9.6
40°-50°	536.3	9.0
50°-60°	379.8	6.4
60°-70°	216.4	3.6
70°-80°	107.1	1.8
80°-90°	30.8	0.5
90°-100°	89.0	1.5
100°-110°	259.5	4.4
110°-120°	423.5	7.1
120°-130°	537.4	9.0
130°-140°	575.1	9.6
140°-150°	537.0	9.0
150°-160°	441.9	7.4
160°-170°	296.3	5.0
170°-180°	105.2	1.8
0°-30°	858.4	14.4
0°-40°	1428.0	23.9
0°-60°	2344.1	39.3
0°-90°	2698.4	45.3
90°-120°	772.0	12.9
90°-150°	2421.5	40.6
90°-180°	3265.0	54.8
0°-180°	5963.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1070	1070	1070	1070	1070	
5°	1057	1076	1057	1076	1057	101
15°	1028	1054	1028	1054	1028	290
25°	952	1062	952	1062	952	438
35°	844	981	844	981	844	526
45°	687	596	687	596	687	529
55°	499	289	499	289	499	440
65°	267	150	267	150	267	268
75°	115	82	115	82	115	125
85°	26	14	26	14	26	31
90°	3	25	3	49	3	4
95°	35	26	35	152	35	42
105°	165	264	165	364	165	175
115°	316	438	316	540	316	312
125°	468	695	468	662	468	418
135°	636	909	636	733	636	491
145°	812	1048	812	749	812	508
155°	965	1138	965	777	965	443
165°	1066	1187	1066	894	1066	300
175°	1115	1162	1115	1049	1115	106
180°	1118	1118	1118	1118	1118	



TEST NUMBER: P1428059

CATALOG NUMBER: SQ2W-PP3-K-075U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1069.6	1069.6	1069.6	1069.6	1069.6	1069.6	1069.6	1069.6	1069.6	1069.6	1069.6
2.5°	1061.5	1068.3	1075.1	1073.5	1069.1	1067.3	1068.1	1068.9	1069.7	1070.5	1069.7
5°	1057.2	1065.7	1074.2	1073.0	1068.5	1066.7	1067.7	1069.3	1072.9	1076.4	1072.9
7.5°	1053.1	1061.8	1070.6	1069.4	1065.0	1063.7	1065.4	1067.7	1072.1	1076.4	1072.1
10°	1050.4	1057.9	1065.5	1064.3	1060.3	1059.5	1062.1	1064.8	1068.3	1071.9	1068.3
12.5°	1042.2	1049.4	1056.5	1055.6	1052.0	1051.8	1055.1	1058.4	1061.5	1064.6	1061.5
15°	1027.8	1034.3	1040.8	1041.0	1038.9	1040.2	1044.7	1048.7	1051.3	1053.8	1051.3
17.5°	1008.1	1016.0	1024.0	1025.8	1025.6	1028.7	1035.1	1040.6	1043.2	1045.9	1043.2
20°	992.7	1002.3	1011.8	1014.9	1016.0	1020.5	1028.5	1035.8	1040.8	1045.9	1040.8
22.5°	976.4	987.6	998.7	1002.9	1004.7	1011.6	1023.7	1034.9	1043.5	1052.2	1043.5
25°	952.0	963.1	974.1	982.2	989.2	1001.5	1019.1	1035.6	1048.6	1061.7	1048.6
27.5°	923.5	934.5	945.4	959.2	974.0	991.3	1011.1	1028.5	1038.9	1049.2	1038.9
30°	904.5	915.1	925.6	941.5	959.0	978.1	998.7	1016.6	1026.1	1035.7	1026.1
32.5°	881.0	892.0	902.9	919.7	938.5	959.0	981.3	1000.1	1008.8	1017.6	1008.8
35°	843.5	854.0	864.6	884.2	906.8	929.6	952.8	971.4	976.4	981.4	976.4
37.5°	800.3	812.2	824.2	846.2	871.5	890.7	903.6	913.4	913.7	914.0	913.7
40°	767.7	783.3	798.9	820.9	845.0	858.3	860.8	861.1	854.5	848.0	854.5
42.5°	736.1	756.1	776.1	793.7	810.6	814.1	804.1	789.4	760.4	731.3	760.4
45°	687.4	711.1	734.7	745.5	752.0	729.9	679.1	636.1	616.0	595.9	616.0
47.5°	635.7	659.0	682.3	679.3	667.5	634.1	578.9	534.0	520.2	506.3	520.2
50°	600.4	622.5	644.6	628.6	600.0	562.3	515.6	477.3	464.2	451.1	464.2
52.5°	560.6	580.3	600.0	575.9	537.2	497.5	456.8	421.3	401.4	381.5	401.4
55°	498.6	512.2	525.8	499.4	459.7	416.0	368.2	327.6	308.5	289.4	308.5
57.5°	424.0	433.5	443.1	422.3	391.5	348.0	291.9	244.5	223.1	201.7	223.1
60°	374.2	381.8	389.3	370.5	342.8	301.4	246.1	202.0	191.5	180.9	191.5
62.5°	329.0	335.8	342.5	322.8	294.4	257.4	211.7	176.6	172.9	169.1	172.9
65°	266.8	273.4	279.9	259.3	229.6	200.8	172.6	151.4	150.9	150.4	150.9
67.5°	212.3	219.5	226.6	207.2	179.0	157.6	143.1	132.1	131.5	130.9	131.5
70°	179.8	187.3	194.8	176.8	150.1	132.8	124.7	118.5	117.5	116.5	117.5
72.5°	152.6	159.8	166.9	151.1	127.7	113.4	108.2	104.1	103.5	102.9	103.5
75°	115.3	120.9	126.4	114.9	97.9	88.1	85.6	83.5	83.0	82.5	83.0
77.5°	83.7	87.2	90.7	83.2	72.1	65.8	64.5	63.4	62.9	62.4	62.9
80°	65.6	67.1	68.6	63.3	55.8	51.8	51.3	50.8	50.3	49.7	50.3
82.5°	49.3	48.8	48.3	45.2	41.3	39.1	38.6	38.0	37.1	36.2	37.1
85°	26.0	25.0	24.0	23.0	22.0	20.5	18.5	16.6	15.1	13.6	15.1
87.5°	8.8	9.7	10.9	10.2	8.9	7.9	7.5	7.5	7.7	7.7	7.7
90°	3.4	7.9	13.6	18.1	21.5	22.6	22.6	23.7	24.8	24.8	24.8
92.5°	12.4	19.7	19.9	19.9	24.2	26.2	28.0	28.2	29.4	29.4	29.4
95°	35.0	38.4	57.6	56.5	38.4	30.5	26.0	26.0	26.0	26.0	26.0
97.5°	66.9	71.8	75.0	100.5	106.2	102.6	83.6	70.3	62.8	59.4	62.8
100°	94.9	97.1	103.9	105.0	133.3	160.4	146.8	129.9	124.2	120.9	124.2
102.5°	122.9	124.2	134.6	139.4	145.9	161.3	208.3	203.1	199.2	198.6	199.2
105°	164.9	166.0	185.2	194.3	198.8	198.8	197.7	220.2	256.4	264.3	256.4
107.5°	209.9	215.1	237.6	261.8	267.0	268.4	262.5	259.1	257.7	258.7	257.7
110°	240.6	248.5	275.6	306.1	314.0	316.3	314.0	310.6	308.3	308.3	308.3



TEST NUMBER: P1428059

CATALOG NUMBER: SQ2W-PP3-K-075U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	270.4	281.9	312.6	347.7	361.0	367.8	362.8	360.3	358.0	359.9	358.0
115°	316.3	333.2	373.9	410.0	437.1	440.5	439.4	439.4	438.2	438.2	438.2
117.5°	358.7	385.8	431.5	473.5	504.9	513.9	518.4	517.1	515.7	518.0	515.7
120°	388.5	420.2	472.1	519.6	550.1	563.6	568.1	565.9	568.1	565.9	568.1
122.5°	420.2	459.0	510.1	559.3	595.2	610.6	616.0	616.5	616.9	615.6	616.9
125°	467.6	515.0	574.9	625.7	663.0	681.1	685.6	686.7	689.0	694.6	689.0
127.5°	515.5	569.3	635.0	684.0	722.2	744.1	751.1	753.6	758.3	760.8	758.3
130°	548.9	609.9	676.6	722.9	760.1	783.9	796.3	799.7	805.3	804.2	805.3
132.5°	584.2	647.9	715.4	763.5	798.1	823.6	834.2	843.9	846.0	847.6	846.0
135°	635.9	704.8	772.6	820.0	852.8	877.6	891.2	900.2	905.8	909.2	905.8
137.5°	690.3	763.1	828.1	870.4	903.4	924.8	940.2	949.7	955.5	958.2	955.5
140°	727.4	797.4	860.7	904.7	934.1	955.5	969.1	980.4	987.2	987.2	987.2
142.5°	762.6	831.7	893.2	937.2	963.0	982.6	997.1	1005.7	1013.4	1013.4	1013.4
145°	812.1	881.0	937.5	981.5	1003.0	1021.0	1036.9	1043.6	1048.2	1048.2	1048.2
147.5°	863.8	924.8	976.3	1018.6	1036.6	1057.9	1070.3	1075.7	1081.4	1078.9	1081.4
150°	894.5	951.0	1000.7	1040.2	1058.3	1078.7	1091.1	1095.6	1101.2	1097.9	1101.2
152.5°	924.4	978.1	1023.3	1060.1	1075.5	1095.8	1110.1	1114.6	1118.4	1115.9	1118.4
155°	964.6	1012.0	1053.8	1087.7	1101.2	1120.4	1134.0	1139.6	1144.2	1138.5	1144.2
157.5°	1000.5	1041.4	1077.7	1108.9	1123.4	1139.9	1152.5	1159.5	1164.0	1161.6	1164.0
160°	1022.2	1059.4	1092.2	1121.6	1135.1	1149.8	1163.4	1171.3	1175.8	1172.4	1175.8
162.5°	1040.2	1073.9	1104.9	1131.5	1143.3	1156.1	1172.4	1179.4	1183.9	1179.6	1183.9
165°	1066.2	1093.3	1120.4	1143.0	1153.2	1163.4	1180.3	1188.2	1191.6	1187.1	1191.6
167.5°	1085.9	1106.7	1128.6	1148.0	1155.5	1165.4	1182.3	1188.9	1193.2	1187.5	1193.2
170°	1096.7	1114.8	1134.0	1149.8	1155.5	1164.5	1181.4	1187.1	1190.5	1184.8	1190.5
172.5°	1105.8	1119.3	1134.9	1148.9	1151.8	1159.1	1175.1	1180.8	1183.2	1178.5	1183.2
175°	1114.8	1122.7	1134.0	1143.0	1141.9	1146.4	1160.0	1164.5	1169.0	1162.2	1169.0
177.5°	1119.1	1122.7	1126.3	1131.7	1128.1	1128.1	1138.1	1140.8	1141.7	1138.1	1141.7
180°	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2



TEST NUMBER: P1428059

CATALOG NUMBER: SQ2W-PP3-K-075U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1069.6	1069.6	1069.6	1069.6	1069.6	1069.6	1069.6	1069.6	1069.6	1069.6	1069.6
2.5°	1068.9	1068.1	1067.3	1069.1	1073.5	1075.1	1068.3	1061.5	1068.3	1075.1	1073.5
5°	1069.3	1067.7	1066.7	1068.5	1073.0	1074.2	1065.7	1057.2	1065.7	1074.2	1073.0
7.5°	1067.7	1065.4	1063.7	1065.0	1069.4	1070.6	1061.8	1053.1	1061.8	1070.6	1069.4
10°	1064.8	1062.1	1059.5	1060.3	1064.3	1065.5	1057.9	1050.4	1057.9	1065.5	1064.3
12.5°	1058.4	1055.1	1051.8	1052.0	1055.6	1056.5	1049.4	1042.2	1049.4	1056.5	1055.6
15°	1048.7	1044.7	1040.2	1038.9	1041.0	1040.8	1034.3	1027.8	1034.3	1040.8	1041.0
17.5°	1040.6	1035.1	1028.7	1025.6	1025.8	1024.0	1016.0	1008.1	1016.0	1024.0	1025.8
20°	1035.8	1028.5	1020.5	1016.0	1014.9	1011.8	1002.3	992.7	1002.3	1011.8	1014.9
22.5°	1034.9	1023.7	1011.6	1004.7	1002.9	998.7	987.6	976.4	987.6	998.7	1002.9
25°	1035.6	1019.1	1001.5	989.2	982.2	974.1	963.1	952.0	963.1	974.1	982.2
27.5°	1028.5	1011.1	991.3	974.0	959.2	945.4	934.5	923.5	934.5	945.4	959.2
30°	1016.6	998.7	978.1	959.0	941.5	925.6	915.1	904.5	915.1	925.6	941.5
32.5°	1000.1	981.3	959.0	938.5	919.7	902.9	892.0	881.0	892.0	902.9	919.7
35°	971.4	952.8	929.6	906.8	884.2	864.6	854.0	843.5	854.0	864.6	884.2
37.5°	913.4	903.6	890.7	871.5	846.2	824.2	812.2	800.3	812.2	824.2	846.2
40°	861.1	860.8	858.3	845.0	820.9	798.9	783.3	767.7	783.3	798.9	820.9
42.5°	789.4	804.1	814.1	810.6	793.7	776.1	756.1	736.1	756.1	776.1	793.7
45°	636.1	679.1	729.9	752.0	745.5	734.7	711.1	687.4	711.1	734.7	745.5
47.5°	534.0	578.9	634.1	667.5	679.3	682.3	659.0	635.7	659.0	682.3	679.3
50°	477.3	515.6	562.3	600.0	628.6	644.6	622.5	600.4	622.5	644.6	628.6
52.5°	421.3	456.8	497.5	537.2	575.9	600.0	580.3	560.6	580.3	600.0	575.9
55°	327.6	368.2	416.0	459.7	499.4	525.8	512.2	498.6	512.2	525.8	499.4
57.5°	244.5	291.9	348.0	391.5	422.3	443.1	433.5	424.0	433.5	443.1	422.3
60°	202.0	246.1	301.4	342.8	370.5	389.3	381.8	374.2	381.8	389.3	370.5
62.5°	176.6	211.7	257.4	294.4	322.8	342.5	335.8	329.0	335.8	342.5	322.8
65°	151.4	172.6	200.8	229.6	259.3	279.9	273.4	266.8	273.4	279.9	259.3
67.5°	132.1	143.1	157.6	179.0	207.2	226.6	219.5	212.3	219.5	226.6	207.2
70°	118.5	124.7	132.8	150.1	176.8	194.8	187.3	179.8	187.3	194.8	176.8
72.5°	104.1	108.2	113.4	127.7	151.1	166.9	159.8	152.6	159.8	166.9	151.1
75°	83.5	85.6	88.1	97.9	114.9	126.4	120.9	115.3	120.9	126.4	114.9
77.5°	63.4	64.5	65.8	72.1	83.2	90.7	87.2	83.7	87.2	90.7	83.2
80°	50.8	51.3	51.8	55.8	63.3	68.6	67.1	65.6	67.1	68.6	63.3
82.5°	38.0	38.6	39.1	41.3	45.2	48.3	48.8	49.3	48.8	48.3	45.2
85°	16.6	18.5	20.5	22.0	23.0	24.0	25.0	26.0	25.0	24.0	23.0
87.5°	7.5	7.5	7.9	8.9	10.2	10.9	9.7	8.8	9.7	10.6	10.7
90°	23.7	22.6	22.6	21.5	18.1	13.6	7.9	3.4	7.9	12.4	20.3
92.5°	28.2	28.0	26.2	24.2	19.9	19.9	19.7	12.4	21.5	30.5	43.8
95°	26.0	26.0	30.5	38.4	56.5	57.6	38.4	35.0	49.7	70.0	88.1
97.5°	70.3	83.6	102.6	106.2	100.5	75.0	71.8	66.9	91.0	111.1	140.3
100°	129.9	146.8	160.4	133.3	105.0	103.9	97.1	94.9	120.9	140.1	168.3
102.5°	203.1	208.3	161.3	145.9	139.4	134.6	124.2	122.9	148.9	175.3	199.0
105°	220.2	197.7	198.8	198.8	194.3	185.2	166.0	164.9	194.3	224.8	254.1
107.5°	259.1	262.5	268.4	267.0	261.8	237.6	215.1	209.9	236.3	272.9	305.2
110°	310.6	314.0	316.3	314.0	306.1	275.6	248.5	240.6	264.3	302.7	337.7



TEST NUMBER: P1428059

CATALOG NUMBER: SQ2W-PP3-K-075U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	360.3	362.8	367.8	361.0	347.7	312.6	281.9	270.4	294.1	333.4	369.3
115°	439.4	439.4	440.5	437.1	410.0	373.9	333.2	316.3	336.6	372.7	412.3
117.5°	517.1	518.4	513.9	504.9	473.5	431.5	385.8	358.7	374.8	412.9	453.6
120°	565.9	568.1	563.6	550.1	519.6	472.1	420.2	388.5	401.0	438.2	478.9
122.5°	616.5	616.0	610.6	595.2	559.3	510.1	459.0	420.2	425.4	459.9	499.7
125°	686.7	685.6	681.1	663.0	625.7	574.9	515.0	467.6	460.8	490.2	530.9
127.5°	753.6	751.1	744.1	722.2	684.0	635.0	569.3	515.5	500.4	518.9	556.2
130°	799.7	796.3	783.9	760.1	722.9	676.6	609.9	548.9	527.5	538.8	571.5
132.5°	843.9	834.2	823.6	798.1	763.5	715.4	647.9	584.2	554.6	559.5	585.1
135°	900.2	891.2	877.6	852.8	820.0	772.6	704.8	635.9	595.2	590.7	605.4
137.5°	949.7	940.2	924.8	903.4	870.4	828.1	763.1	690.3	639.1	623.9	629.6
140°	980.4	969.1	955.5	934.1	904.7	860.7	797.4	727.4	669.8	648.3	644.9
142.5°	1005.7	997.1	982.6	963.0	937.2	893.2	831.7	762.6	701.4	673.6	665.7
145°	1043.6	1036.9	1021.0	1003.0	981.5	937.5	881.0	812.1	751.1	715.0	698.0
147.5°	1075.7	1070.3	1057.9	1036.6	1018.6	976.3	924.8	863.8	801.3	756.5	734.6
150°	1095.6	1091.1	1078.7	1058.3	1040.2	1000.7	951.0	894.5	834.7	787.2	759.0
152.5°	1114.6	1110.1	1095.8	1075.5	1060.1	1023.3	978.1	924.4	863.6	816.2	787.0
155°	1139.6	1134.0	1120.4	1101.2	1087.7	1053.8	1012.0	964.6	912.6	862.9	830.2
157.5°	1159.5	1152.5	1139.9	1123.4	1108.9	1077.7	1041.4	1000.5	955.1	907.6	874.2
160°	1171.3	1163.4	1149.8	1135.1	1121.6	1092.2	1059.4	1022.2	980.4	937.5	901.3
162.5°	1179.4	1172.4	1156.1	1143.3	1131.5	1104.9	1073.9	1040.2	1003.0	965.5	932.0
165°	1188.2	1180.3	1163.4	1153.2	1143.0	1120.4	1093.3	1066.2	1034.6	1004.1	977.0
167.5°	1188.9	1182.3	1165.4	1155.5	1148.0	1128.6	1106.7	1085.9	1061.3	1037.3	1014.7
170°	1187.1	1181.4	1164.5	1155.5	1149.8	1134.0	1114.8	1096.7	1077.5	1057.2	1039.1
172.5°	1180.8	1175.1	1159.1	1151.8	1148.9	1134.9	1119.3	1105.8	1089.3	1074.4	1059.9
175°	1164.5	1160.0	1146.4	1141.9	1143.0	1134.0	1122.7	1114.8	1104.6	1095.6	1087.7
177.5°	1140.8	1138.1	1128.1	1128.1	1131.7	1126.3	1122.7	1119.1	1114.6	1111.9	1109.1
180°	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2



TEST NUMBER: P1428059

CATALOG NUMBER: SQ2W-PP3-K-075U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1069.6	1069.6	1069.6	1069.6	1069.6	1069.6	1069.6	1069.6	1069.6	1069.6	1069.6
2.5°	1069.1	1067.3	1068.1	1068.9	1069.7	1070.5	1069.7	1068.9	1068.1	1067.3	1069.1
5°	1068.5	1066.7	1067.7	1069.3	1072.9	1076.4	1072.9	1069.3	1067.7	1066.7	1068.5
7.5°	1065.0	1063.7	1065.4	1067.7	1072.1	1076.4	1072.1	1067.7	1065.4	1063.7	1065.0
10°	1060.3	1059.5	1062.1	1064.8	1068.3	1071.9	1068.3	1064.8	1062.1	1059.5	1060.3
12.5°	1052.0	1051.8	1055.1	1058.4	1061.5	1064.6	1061.5	1058.4	1055.1	1051.8	1052.0
15°	1038.9	1040.2	1044.7	1048.7	1051.3	1053.8	1051.3	1048.7	1044.7	1040.2	1038.9
17.5°	1025.6	1028.7	1035.1	1040.6	1043.2	1045.9	1043.2	1040.6	1035.1	1028.7	1025.6
20°	1016.0	1020.5	1028.5	1035.8	1040.8	1045.9	1040.8	1035.8	1028.5	1020.5	1016.0
22.5°	1004.7	1011.6	1023.7	1034.9	1043.5	1052.2	1043.5	1034.9	1023.7	1011.6	1004.7
25°	989.2	1001.5	1019.1	1035.6	1048.6	1061.7	1048.6	1035.6	1019.1	1001.5	989.2
27.5°	974.0	991.3	1011.1	1028.5	1038.9	1049.2	1038.9	1028.5	1011.1	991.3	974.0
30°	959.0	978.1	998.7	1016.6	1026.1	1035.7	1026.1	1016.6	998.7	978.1	959.0
32.5°	938.5	959.0	981.3	1000.1	1008.8	1017.6	1008.8	1000.1	981.3	959.0	938.5
35°	906.8	929.6	952.8	971.4	976.4	981.4	976.4	971.4	952.8	929.6	906.8
37.5°	871.5	890.7	903.6	913.4	913.7	914.0	913.7	913.4	903.6	890.7	871.5
40°	845.0	858.3	860.8	861.1	854.5	848.0	854.5	861.1	860.8	858.3	845.0
42.5°	810.6	814.1	804.1	789.4	760.4	731.3	760.4	789.4	804.1	814.1	810.6
45°	752.0	729.9	679.1	636.1	616.0	595.9	616.0	636.1	679.1	729.9	752.0
47.5°	667.5	634.1	578.9	534.0	520.2	506.3	520.2	534.0	578.9	634.1	667.5
50°	600.0	562.3	515.6	477.3	464.2	451.1	464.2	477.3	515.6	562.3	600.0
52.5°	537.2	497.5	456.8	421.3	401.4	381.5	401.4	421.3	456.8	497.5	537.2
55°	459.7	416.0	368.2	327.6	308.5	289.4	308.5	327.6	368.2	416.0	459.7
57.5°	391.5	348.0	291.9	244.5	223.1	201.7	223.1	244.5	291.9	348.0	391.5
60°	342.8	301.4	246.1	202.0	191.5	180.9	191.5	202.0	246.1	301.4	342.8
62.5°	294.4	257.4	211.7	176.6	172.9	169.1	172.9	176.6	211.7	257.4	294.4
65°	229.6	200.8	172.6	151.4	150.9	150.4	150.9	151.4	172.6	200.8	229.6
67.5°	179.0	157.6	143.1	132.1	131.5	130.9	131.5	132.1	143.1	157.6	179.0
70°	150.1	132.8	124.7	118.5	117.5	116.5	117.5	118.5	124.7	132.8	150.1
72.5°	127.7	113.4	108.2	104.1	103.5	102.9	103.5	104.1	108.2	113.4	127.7
75°	97.9	88.1	85.6	83.5	83.0	82.5	83.0	83.5	85.6	88.1	97.9
77.5°	72.1	65.8	64.5	63.4	62.9	62.4	62.9	63.4	64.5	65.8	72.1
80°	55.8	51.8	51.3	50.8	50.3	49.7	50.3	50.8	51.3	51.8	55.8
82.5°	41.3	39.1	38.6	38.0	37.1	36.2	37.1	38.0	38.6	39.1	41.3
85°	22.0	20.5	18.5	16.6	15.1	13.6	15.1	16.6	18.5	20.5	22.0
87.5°	9.8	10.2	11.4	12.0	12.9	12.4	12.9	12.0	11.4	10.2	9.8
90°	26.0	33.9	41.8	46.3	50.8	48.6	50.8	46.3	41.8	33.9	26.0
92.5°	52.2	65.5	75.2	83.4	87.0	86.5	87.0	83.4	75.2	65.5	52.2
95°	105.0	120.9	136.7	148.0	154.7	152.5	154.7	148.0	136.7	120.9	105.0
97.5°	162.0	183.2	200.8	211.4	218.2	222.7	218.2	211.4	200.8	183.2	162.0
100°	199.9	220.2	240.6	253.0	264.3	268.8	264.3	253.0	240.6	220.2	199.9
102.5°	230.6	257.3	279.4	292.8	302.2	306.8	302.2	292.8	279.4	257.3	230.6
105°	281.2	309.5	333.2	350.1	360.3	363.7	360.3	350.1	333.2	309.5	281.2
107.5°	331.8	361.0	382.9	401.6	414.1	421.3	414.1	401.6	382.9	361.0	331.8
110°	371.6	395.3	419.0	436.0	448.4	452.9	448.4	436.0	419.0	395.3	371.6



TEST NUMBER: P1428059

CATALOG NUMBER: SQ2W-PP3-K-075U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	405.0	431.5	455.2	472.1	486.4	492.7	486.4	472.1	455.2	431.5	405.0
115°	451.8	486.8	508.3	524.1	534.2	539.9	534.2	524.1	508.3	486.8	451.8
117.5°	490.6	527.2	550.7	562.9	567.7	571.7	567.7	562.9	550.7	527.2	490.6
120°	515.0	548.9	576.0	591.8	597.5	599.8	597.5	591.8	576.0	548.9	515.0
122.5°	537.6	569.7	595.9	615.3	624.6	626.9	624.6	615.3	595.9	569.7	537.6
125°	569.3	599.8	626.9	646.1	656.2	661.9	656.2	646.1	626.9	599.8	569.3
127.5°	596.8	629.8	654.6	672.0	682.0	686.5	682.0	672.0	654.6	629.8	596.8
130°	612.2	646.1	670.9	690.1	699.1	703.7	699.1	690.1	670.9	646.1	612.2
132.5°	623.9	659.6	685.4	702.8	712.7	717.2	712.7	702.8	685.4	659.6	623.9
135°	638.2	675.4	702.5	719.5	728.5	733.0	728.5	719.5	702.5	675.4	638.2
137.5°	650.6	684.5	712.7	730.5	738.7	741.6	738.7	730.5	712.7	684.5	650.6
140°	659.6	689.0	717.2	734.2	743.2	744.3	743.2	734.2	717.2	689.0	659.6
142.5°	671.4	694.4	719.0	736.0	745.0	747.0	745.0	736.0	719.0	694.4	671.4
145°	692.4	705.9	722.9	738.7	746.6	748.8	746.6	738.7	722.9	705.9	692.4
147.5°	718.8	723.1	731.9	742.3	750.0	751.6	750.0	742.3	731.9	723.1	718.8
150°	738.7	737.5	740.9	747.7	754.5	753.4	754.5	747.7	740.9	737.5	738.7
152.5°	761.3	754.7	754.5	757.7	760.8	760.6	760.8	757.7	754.5	754.7	761.3
155°	799.7	787.2	780.5	778.2	778.2	777.1	778.2	778.2	780.5	787.2	799.7
157.5°	841.9	824.5	814.4	808.9	807.4	804.9	807.4	808.9	814.4	824.5	841.9
160°	870.8	851.6	841.5	832.4	829.0	825.6	829.0	832.4	841.5	851.6	870.8
162.5°	897.9	879.6	868.6	860.4	857.0	851.9	857.0	860.4	868.6	879.6	897.9
165°	942.0	922.8	910.4	903.6	899.1	894.5	899.1	903.6	910.4	922.8	942.0
167.5°	986.0	965.0	956.9	949.2	944.9	936.8	944.9	949.2	956.9	965.0	986.0
170°	1013.1	993.9	989.4	982.6	974.7	965.7	974.7	982.6	989.4	993.9	1013.1
172.5°	1036.6	1023.8	1019.2	1012.5	1010.0	1002.7	1010.0	1012.5	1019.2	1023.8	1036.6
175°	1070.7	1060.6	1060.6	1059.4	1056.1	1049.3	1056.1	1059.4	1060.6	1060.6	1070.7
177.5°	1099.2	1093.8	1097.4	1097.4	1096.5	1090.2	1096.5	1097.4	1097.4	1093.8	1099.2
180°	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2



TEST NUMBER: P1428059

CATALOG NUMBER: SQ2W-PP3-K-075U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1069.6	1069.6	1069.6	1069.6
2.5°	1073.5	1075.1	1068.3	1061.5
5°	1073.0	1074.2	1065.7	1057.2
7.5°	1069.4	1070.6	1061.8	1053.1
10°	1064.3	1065.5	1057.9	1050.4
12.5°	1055.6	1056.5	1049.4	1042.2
15°	1041.0	1040.8	1034.3	1027.8
17.5°	1025.8	1024.0	1016.0	1008.1
20°	1014.9	1011.8	1002.3	992.7
22.5°	1002.9	998.7	987.6	976.4
25°	982.2	974.1	963.1	952.0
27.5°	959.2	945.4	934.5	923.5
30°	941.5	925.6	915.1	904.5
32.5°	919.7	902.9	892.0	881.0
35°	884.2	864.6	854.0	843.5
37.5°	846.2	824.2	812.2	800.3
40°	820.9	798.9	783.3	767.7
42.5°	793.7	776.1	756.1	736.1
45°	745.5	734.7	711.1	687.4
47.5°	679.3	682.3	659.0	635.7
50°	628.6	644.6	622.5	600.4
52.5°	575.9	600.0	580.3	560.6
55°	499.4	525.8	512.2	498.6
57.5°	422.3	443.1	433.5	424.0
60°	370.5	389.3	381.8	374.2
62.5°	322.8	342.5	335.8	329.0
65°	259.3	279.9	273.4	266.8
67.5°	207.2	226.6	219.5	212.3
70°	176.8	194.8	187.3	179.8
72.5°	151.1	166.9	159.8	152.6
75°	114.9	126.4	120.9	115.3
77.5°	83.2	90.7	87.2	83.7
80°	63.3	68.6	67.1	65.6
82.5°	45.2	48.3	48.8	49.3
85°	23.0	24.0	25.0	26.0
87.5°	10.7	10.6	9.7	8.8
90°	20.3	12.4	7.9	3.4
92.5°	43.8	30.5	21.5	12.4
95°	88.1	70.0	49.7	35.0
97.5°	140.3	111.1	91.0	66.9
100°	168.3	140.1	120.9	94.9
102.5°	199.0	175.3	148.9	122.9
105°	254.1	224.8	194.3	164.9
107.5°	305.2	272.9	236.3	209.9
110°	337.7	302.7	264.3	240.6



TEST NUMBER: P1428059

CATALOG NUMBER: SQ2W-PP3-K-075U-050D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	369.3	333.4	294.1	270.4
115°	412.3	372.7	336.6	316.3
117.5°	453.6	412.9	374.8	358.7
120°	478.9	438.2	401.0	388.5
122.5°	499.7	459.9	425.4	420.2
125°	530.9	490.2	460.8	467.6
127.5°	556.2	518.9	500.4	515.5
130°	571.5	538.8	527.5	548.9
132.5°	585.1	559.5	554.6	584.2
135°	605.4	590.7	595.2	635.9
137.5°	629.6	623.9	639.1	690.3
140°	644.9	648.3	669.8	727.4
142.5°	665.7	673.6	701.4	762.6
145°	698.0	715.0	751.1	812.1
147.5°	734.6	756.5	801.3	863.8
150°	759.0	787.2	834.7	894.5
152.5°	787.0	816.2	863.6	924.4
155°	830.2	862.9	912.6	964.6
157.5°	874.2	907.6	955.1	1000.5
160°	901.3	937.5	980.4	1022.2
162.5°	932.0	965.5	1003.0	1040.2
165°	977.0	1004.1	1034.6	1066.2
167.5°	1014.7	1037.3	1061.3	1085.9
170°	1039.1	1057.2	1077.5	1096.7
172.5°	1059.9	1074.4	1089.3	1105.8
175°	1087.7	1095.6	1104.6	1114.8
177.5°	1109.1	1111.9	1114.6	1119.1
180°	1118.2	1118.2	1118.2	1118.2



TEST NUMBER: P1428059
 CATALOG NUMBER: SQ2W-PP3-K-075U-050D-L830-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.89	17.68	17.89	18.69	20.03	12.66	13.45	13.66	14.46	15.80
	3H	17.94	18.65	18.96	19.67	21.03	13.96	14.67	14.98	15.69	17.05
	4H	18.31	18.98	19.34	20.00	21.37	14.52	15.19	15.54	16.21	17.58
	6H	18.50	19.12	19.54	20.14	21.52	14.88	15.49	15.92	16.52	17.90
	8H	18.56	19.15	19.60	20.19	21.57	15.01	15.59	16.05	16.63	18.01
	12H	18.58	19.14	19.63	20.17	21.57	15.04	15.60	16.09	16.63	18.03
4H	2H	17.00	17.67	18.03	18.69	20.06	13.56	14.23	14.59	15.25	16.62
	3H	18.29	18.84	19.33	19.89	21.27	14.98	15.53	16.02	16.58	17.96
	4H	18.79	19.30	19.84	20.34	21.75	15.60	16.10	16.64	17.15	18.55
	6H	19.10	19.54	20.16	20.61	22.01	16.04	16.47	17.10	17.54	18.94
	8H	19.21	19.62	20.27	20.68	22.09	16.21	16.61	17.27	17.67	19.09
	12H	19.25	19.62	20.33	20.69	22.11	16.25	16.62	17.33	17.69	19.11
8H	4H	18.81	19.21	19.87	20.27	21.69	15.90	16.31	16.96	17.36	18.78
	6H	19.22	19.55	20.30	20.65	22.07	16.46	16.79	17.54	17.89	19.31
	8H	19.40	19.69	20.49	20.78	22.21	16.71	17.00	17.79	18.08	19.52
	12H	19.49	19.75	20.58	20.83	22.30	16.80	17.06	17.89	18.14	19.61
12H	4H	18.76	19.13	19.84	20.20	21.62	15.91	16.28	16.98	17.35	18.77
	6H	19.21	19.51	20.30	20.59	22.02	16.52	16.82	17.61	17.90	19.33
	8H	19.40	19.66	20.49	20.74	22.21	16.80	17.06	17.89	18.13	19.61