

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428185

Luminaire Tested: SQ2W-PR1-K-025U-075D-L830-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428185
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-9)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PR1-K-025U-075D-L830-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE RIPPLE LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4945.4 lumens
Efficiency: N/A
Efficacy: 144.6 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 34.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428185

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L830-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428185

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L830-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10	0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																			
0	114	114	114	114	109	109	109	109	99	99	99	99	90	90	90	82	82	82	78
1	105	101	97	94	100	97	93	90	88	86	83	83	81	79	77	74	72	71	68
2	96	89	83	78	92	86	80	76	79	74	71	71	72	69	66	66	64	61	58
3	89	79	72	66	84	76	70	64	70	65	61	61	65	60	57	59	56	53	50
4	82	71	63	57	78	68	61	56	63	57	52	52	58	53	49	54	50	47	44
5	75	64	56	50	72	61	54	48	57	51	46	46	53	47	43	49	44	41	39
6	70	58	49	44	66	56	48	43	52	45	41	41	48	43	39	44	40	37	34
7	65	52	44	39	62	51	43	38	47	41	36	36	44	38	34	41	36	33	31
8	60	48	40	35	58	46	39	34	43	37	32	32	40	35	31	38	33	29	27
9	56	44	36	31	54	42	35	31	40	34	29	29	37	32	28	35	30	27	25
10	53	40	33	28	50	39	32	28	37	31	27	27	34	29	25	32	28	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	25834	25834	25834	25834
5°	25800	26277	25800	26277
10°	26072	27141	26072	27141
15°	26064	26418	26064	26418
20°	25642	26903	25642	26903
25°	25569	28010	25569	28010
30°	25543	28280	25543	28280
35°	25300	26329	25300	26329
40°	24716	23169	24716	23169
45°	23388	18324	23388	18324
50°	21262	14217	21262	14217
55°	18685	11065	18685	11065
60°	16168	9113	16168	9113
65°	13960	7977	13960	7977
70°	12552	7086	12552	7086
75°	11497	6513	11497	6513
80°	10004	6369	10004	6369
85°	7243	3020	7243	3020

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 25110 cd/sqm



TEST NUMBER: P1428185

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L830-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.5	3.1
10°-20°	447.3	9.0
20°-30°	691.5	14.0
30°-40°	831.6	16.8
40°-50°	746.7	15.1
50°-60°	500.3	10.1
60°-70°	291.1	5.9
70°-80°	149.5	3.0
80°-90°	38.4	0.8
90°-100°	29.8	0.6
100°-110°	87.0	1.8
110°-120°	142.0	2.9
120°-130°	180.2	3.6
130°-140°	192.8	3.9
140°-150°	180.0	3.6
150°-160°	148.1	3.0
160°-170°	99.3	2.0
170°-180°	35.3	0.7
0°-30°	1293.3	26.2
0°-40°	2124.9	43.0
0°-60°	3372.0	68.2
0°-90°	3851.0	77.9
90°-120°	258.8	5.2
90°-150°	811.7	16.4
90°-180°	1094.0	22.1
0°-180°	4945.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1600	1600	1600	1600	1600	
5°	1592	1621	1592	1621	1592	152
15°	1559	1580	1559	1580	1559	438
25°	1435	1572	1435	1572	1435	662
35°	1284	1336	1284	1336	1284	800
45°	1024	802	1024	802	1024	784
55°	664	393	664	393	664	597
65°	365	209	365	209	365	370
75°	184	104	184	104	184	196
85°	39	16	39	16	39	49
90°	1	8	1	16	1	2
95°	12	9	12	51	12	14
105°	55	89	55	122	55	59
115°	106	147	106	181	106	104
125°	157	233	157	222	157	140
135°	213	305	213	246	213	165
145°	272	351	272	251	272	170
155°	323	382	323	260	323	149
165°	357	398	357	300	357	101
175°	374	390	374	352	374	35
180°	375	375	375	375	375	



TEST NUMBER: P1428185

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1
2.5°	1593.5	1602.2	1610.9	1607.0	1598.9	1595.1	1595.7	1596.6	1598.3	1600.1	1598.3
5°	1591.9	1604.2	1616.5	1613.6	1605.7	1602.4	1603.9	1606.8	1614.0	1621.3	1614.0
7.5°	1591.6	1609.1	1626.7	1628.0	1623.9	1624.0	1628.2	1633.8	1643.3	1652.9	1643.3
10°	1590.3	1611.3	1632.3	1635.4	1632.5	1631.4	1632.1	1635.2	1645.4	1655.5	1645.4
12.5°	1582.4	1606.9	1631.4	1628.9	1617.3	1611.0	1609.9	1610.6	1616.1	1621.6	1616.1
15°	1559.3	1588.3	1617.3	1605.5	1580.1	1568.5	1570.7	1573.2	1576.9	1580.5	1576.9
17.5°	1518.5	1548.8	1579.1	1568.5	1544.3	1536.1	1543.9	1551.6	1558.7	1565.8	1558.7
20°	1492.4	1522.1	1551.8	1544.6	1525.0	1520.3	1530.5	1541.2	1553.5	1565.8	1553.5
22.5°	1468.9	1498.6	1528.4	1523.7	1507.6	1506.7	1520.9	1535.8	1552.8	1569.7	1552.8
25°	1435.3	1461.4	1487.5	1488.1	1480.1	1488.1	1512.0	1534.6	1553.5	1572.3	1553.5
27.5°	1400.1	1415.5	1430.8	1441.0	1449.4	1469.8	1502.1	1529.6	1542.8	1556.0	1542.8
30°	1370.1	1380.2	1390.4	1409.2	1431.0	1456.0	1484.2	1506.7	1511.8	1516.9	1511.8
32.5°	1337.5	1343.5	1349.6	1376.2	1409.5	1433.7	1448.6	1458.2	1451.6	1445.1	1451.6
35°	1283.6	1288.7	1293.8	1327.7	1371.2	1387.1	1375.5	1363.4	1349.6	1335.8	1349.6
37.5°	1219.7	1230.1	1240.6	1268.2	1301.5	1301.2	1267.3	1237.9	1222.1	1206.3	1222.1
40°	1172.7	1190.1	1207.5	1226.0	1244.8	1228.9	1178.2	1135.6	1117.4	1099.3	1117.4
42.5°	1115.3	1143.1	1171.0	1175.1	1171.3	1137.1	1072.5	1018.4	996.2	974.1	996.2
45°	1024.3	1062.0	1099.7	1078.1	1036.8	981.0	910.7	851.8	827.1	802.5	827.1
47.5°	917.0	955.7	994.4	953.7	886.6	821.6	758.9	706.0	683.0	659.9	683.0
50°	846.5	877.7	908.9	862.8	791.1	725.8	667.1	616.7	591.3	566.0	591.3
52.5°	774.7	797.2	819.7	774.1	705.8	642.3	583.6	533.8	510.7	487.7	510.7
55°	663.8	675.4	687.0	644.8	584.6	526.6	470.8	425.0	409.0	393.1	409.0
57.5°	562.1	569.5	576.8	536.8	481.0	429.4	382.0	343.5	331.8	320.0	331.8
60°	500.7	505.8	510.9	470.3	414.5	368.1	331.1	301.0	291.6	282.2	291.6
62.5°	444.6	448.5	452.5	413.3	359.8	318.3	288.9	265.1	258.0	250.9	258.0
65°	365.4	369.0	372.6	339.3	293.6	259.5	237.0	218.9	213.8	208.8	213.8
67.5°	302.4	304.3	306.2	278.7	241.4	214.0	196.3	181.8	177.0	172.2	177.0
70°	265.9	266.6	267.3	243.0	210.4	186.1	170.2	157.3	153.7	150.1	153.7
72.5°	233.2	232.2	231.2	209.5	181.0	160.2	147.1	136.7	134.3	131.8	134.3
75°	184.3	182.1	180.0	162.0	138.8	122.9	114.2	107.3	105.8	104.4	105.8
77.5°	137.7	135.3	133.0	118.1	98.9	87.9	85.0	82.9	82.9	82.9	82.9
80°	107.6	104.7	101.8	90.3	75.8	68.5	68.5	68.5	68.5	68.5	68.5
82.5°	80.2	76.2	72.1	65.0	56.9	52.8	52.8	52.7	52.1	51.5	52.1
85°	39.1	35.5	31.9	31.0	31.0	28.8	24.5	20.7	18.5	16.3	18.5
87.5°	10.7	11.0	11.3	9.5	6.8	5.4	5.4	5.5	5.6	5.6	5.6
90°	1.1	2.7	4.5	6.1	7.2	7.6	7.6	8.0	8.3	8.3	8.3
92.5°	4.2	6.6	6.7	6.7	8.1	8.8	9.4	9.5	9.8	9.8	9.8
95°	11.7	12.9	19.3	18.9	12.9	10.2	8.7	8.7	8.7	8.7	8.7
97.5°	22.4	24.1	25.1	33.7	35.6	34.4	28.0	23.6	21.1	19.9	21.1
100°	31.8	32.6	34.8	35.2	44.7	53.8	49.2	43.5	41.6	40.5	41.6
102.5°	41.2	41.6	45.1	46.7	48.9	54.1	69.8	68.1	66.8	66.6	66.8
105°	55.3	55.7	62.1	65.1	66.6	66.6	66.3	73.8	85.9	88.6	85.9
107.5°	70.3	72.1	79.7	87.8	89.5	90.0	88.0	86.9	86.4	86.7	86.4
110°	80.6	83.3	92.4	102.6	105.3	106.0	105.3	104.1	103.4	103.4	103.4



TEST NUMBER: P1428185

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	90.6	94.5	104.8	116.5	121.0	123.3	121.6	120.8	120.0	120.6	120.0
115°	106.0	111.7	125.3	137.4	146.5	147.7	147.3	147.3	146.9	146.9	146.9
117.5°	120.3	129.3	144.6	158.7	169.2	172.3	173.8	173.3	172.9	173.6	172.9
120°	130.2	140.8	158.3	174.2	184.4	188.9	190.4	189.7	190.4	189.7	190.4
122.5°	140.8	153.9	171.0	187.5	199.5	204.7	206.5	206.7	206.8	206.4	206.8
125°	156.8	172.7	192.7	209.8	222.3	228.3	229.8	230.2	231.0	232.9	231.0
127.5°	172.8	190.8	212.9	229.3	242.1	249.4	251.8	252.6	254.2	255.0	254.2
130°	184.0	204.5	226.8	242.3	254.8	262.8	266.9	268.1	270.0	269.6	270.0
132.5°	195.8	217.2	239.8	256.0	267.5	276.1	279.7	282.9	283.6	284.1	283.6
135°	213.2	236.3	259.0	274.9	285.9	294.2	298.7	301.8	303.7	304.8	303.7
137.5°	231.4	255.8	277.6	291.8	302.8	310.0	315.2	318.4	320.3	321.2	320.3
140°	243.8	267.3	288.5	303.3	313.1	320.3	324.9	328.6	330.9	330.9	330.9
142.5°	255.6	278.8	299.4	314.2	322.8	329.4	334.3	337.1	339.7	339.7	339.7
145°	272.2	295.3	314.3	329.0	336.2	342.3	347.6	349.9	351.4	351.4	351.4
147.5°	289.6	310.0	327.3	341.4	347.5	354.6	358.8	360.6	362.5	361.7	362.5
150°	299.9	318.8	335.5	348.7	354.8	361.6	365.8	367.3	369.2	368.0	369.2
152.5°	309.9	327.9	343.0	355.4	360.5	367.3	372.1	373.6	374.9	374.1	374.9
155°	323.3	339.3	353.3	364.6	369.2	375.6	380.1	382.0	383.6	381.7	383.6
157.5°	335.4	349.1	361.3	371.7	376.6	382.1	386.4	388.7	390.2	389.4	390.2
160°	342.7	355.2	366.1	376.0	380.5	385.4	390.0	392.6	394.2	393.0	394.2
162.5°	348.7	360.0	370.4	379.3	383.2	387.6	393.0	395.4	396.9	395.4	396.9
165°	357.4	366.5	375.6	383.2	386.6	390.0	395.7	398.3	399.5	397.9	399.5
167.5°	364.0	371.0	378.3	384.8	387.3	390.7	396.3	398.5	400.0	398.1	400.0
170°	367.6	373.7	380.1	385.4	387.3	390.4	396.0	397.9	399.1	397.2	399.1
172.5°	370.7	375.2	380.4	385.1	386.1	388.5	393.9	395.8	396.7	395.1	396.7
175°	373.7	376.4	380.1	383.2	382.8	384.3	388.9	390.4	391.9	389.6	391.9
177.5°	375.1	376.4	377.6	379.4	378.2	378.2	381.5	382.4	382.7	381.5	382.7
180°	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8



TEST NUMBER: P1428185

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1
2.5°	1596.6	1595.7	1595.1	1598.9	1607.0	1610.9	1602.2	1593.5	1602.2	1610.9	1607.0
5°	1606.8	1603.9	1602.4	1605.7	1613.6	1616.5	1604.2	1591.9	1604.2	1616.5	1613.6
7.5°	1633.8	1628.2	1624.0	1623.9	1628.0	1626.7	1609.1	1591.6	1609.1	1626.7	1628.0
10°	1635.2	1632.1	1631.4	1632.5	1635.4	1632.3	1611.3	1590.3	1611.3	1632.3	1635.4
12.5°	1610.6	1609.9	1611.0	1617.3	1628.9	1631.4	1606.9	1582.4	1606.9	1631.4	1628.9
15°	1573.2	1570.7	1568.5	1580.1	1605.5	1617.3	1588.3	1559.3	1588.3	1617.3	1605.5
17.5°	1551.6	1543.9	1536.1	1544.3	1568.5	1579.1	1548.8	1518.5	1548.8	1579.1	1568.5
20°	1541.2	1530.5	1520.3	1525.0	1544.6	1551.8	1522.1	1492.4	1522.1	1551.8	1544.6
22.5°	1535.8	1520.9	1506.7	1507.6	1523.7	1528.4	1498.6	1468.9	1498.6	1528.4	1523.7
25°	1534.6	1512.0	1488.1	1480.1	1488.1	1487.5	1461.4	1435.3	1461.4	1487.5	1488.1
27.5°	1529.6	1502.1	1469.8	1449.4	1441.0	1430.8	1415.5	1400.1	1415.5	1430.8	1441.0
30°	1506.7	1484.2	1456.0	1431.0	1409.2	1390.4	1380.2	1370.1	1380.2	1390.4	1409.2
32.5°	1458.2	1448.6	1433.7	1409.5	1376.2	1349.6	1343.5	1337.5	1343.5	1349.6	1376.2
35°	1363.4	1375.5	1387.1	1371.2	1327.7	1293.8	1288.7	1283.6	1288.7	1293.8	1327.7
37.5°	1237.9	1267.3	1301.2	1301.5	1268.2	1240.6	1230.1	1219.7	1230.1	1240.6	1268.2
40°	1135.6	1178.2	1228.9	1244.8	1226.0	1207.5	1190.1	1172.7	1190.1	1207.5	1226.0
42.5°	1018.4	1072.5	1137.1	1171.3	1175.1	1171.0	1143.1	1115.3	1143.1	1171.0	1175.1
45°	851.8	910.7	981.0	1036.8	1078.1	1099.7	1062.0	1024.3	1062.0	1099.7	1078.1
47.5°	706.0	758.9	821.6	886.6	953.7	994.4	955.7	917.0	955.7	994.4	953.7
50°	616.7	667.1	725.8	791.1	862.8	908.9	877.7	846.5	877.7	908.9	862.8
52.5°	533.8	583.6	642.3	705.8	774.1	819.7	797.2	774.7	797.2	819.7	774.1
55°	425.0	470.8	526.6	584.6	644.8	687.0	675.4	663.8	675.4	687.0	644.8
57.5°	343.5	382.0	429.4	481.0	536.8	576.8	569.5	562.1	569.5	576.8	536.8
60°	301.0	331.1	368.1	414.5	470.3	510.9	505.8	500.7	505.8	510.9	470.3
62.5°	265.1	288.9	318.3	359.8	413.3	452.5	448.5	444.6	448.5	452.5	413.3
65°	218.9	237.0	259.5	293.6	339.3	372.6	369.0	365.4	369.0	372.6	339.3
67.5°	181.8	196.3	214.0	241.4	278.7	306.2	304.3	302.4	304.3	306.2	278.7
70°	157.3	170.2	186.1	210.4	243.0	267.3	266.6	265.9	266.6	267.3	243.0
72.5°	136.7	147.1	160.2	181.0	209.5	231.2	232.2	233.2	232.2	231.2	209.5
75°	107.3	114.2	122.9	138.8	162.0	180.0	182.1	184.3	182.1	180.0	162.0
77.5°	82.9	85.0	87.9	98.9	118.1	133.0	135.3	137.7	135.3	133.0	118.1
80°	68.5	68.5	68.5	75.8	90.3	101.8	104.7	107.6	104.7	101.8	90.3
82.5°	52.7	52.8	52.8	56.9	65.0	72.1	76.2	80.2	76.2	72.1	65.0
85°	20.7	24.5	28.8	31.0	31.0	31.9	35.5	39.1	35.5	31.9	31.0
87.5°	5.5	5.4	5.4	6.8	9.5	11.3	11.0	10.7	11.0	11.3	9.6
90°	8.0	7.6	7.6	7.2	6.1	4.5	2.7	1.1	2.7	4.2	6.8
92.5°	9.5	9.4	8.8	8.1	6.7	6.7	6.6	4.2	7.2	10.2	14.7
95°	8.7	8.7	10.2	12.9	18.9	19.3	12.9	11.7	16.7	23.5	29.5
97.5°	23.6	28.0	34.4	35.6	33.7	25.1	24.1	22.4	30.5	37.3	47.0
100°	43.5	49.2	53.8	44.7	35.2	34.8	32.6	31.8	40.5	46.9	56.4
102.5°	68.1	69.8	54.1	48.9	46.7	45.1	41.6	41.2	49.9	58.8	66.7
105°	73.8	66.3	66.6	66.6	65.1	62.1	55.7	55.3	65.1	75.3	85.2
107.5°	86.9	88.0	90.0	89.5	87.8	79.7	72.1	70.3	79.2	91.5	102.3
110°	104.1	105.3	106.0	105.3	102.6	92.4	83.3	80.6	88.6	101.5	113.2



TEST NUMBER: P1428185

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	120.8	121.6	123.3	121.0	116.5	104.8	94.5	90.6	98.6	111.8	123.8
115°	147.3	147.3	147.7	146.5	137.4	125.3	111.7	106.0	112.8	124.9	138.2
117.5°	173.3	173.8	172.3	169.2	158.7	144.6	129.3	120.3	125.6	138.4	152.1
120°	189.7	190.4	188.9	184.4	174.2	158.3	140.8	130.2	134.4	146.9	160.5
122.5°	206.7	206.5	204.7	199.5	187.5	171.0	153.9	140.8	142.6	154.2	167.5
125°	230.2	229.8	228.3	222.3	209.8	192.7	172.7	156.8	154.5	164.3	178.0
127.5°	252.6	251.8	249.4	242.1	229.3	212.9	190.8	172.8	167.7	173.9	186.4
130°	268.1	266.9	262.8	254.8	242.3	226.8	204.5	184.0	176.8	180.6	191.6
132.5°	282.9	279.7	276.1	267.5	256.0	239.8	217.2	195.8	185.9	187.6	196.1
135°	301.8	298.7	294.2	285.9	274.9	259.0	236.3	213.2	199.5	198.0	202.9
137.5°	318.4	315.2	310.0	302.8	291.8	277.6	255.8	231.4	214.2	209.2	211.0
140°	328.6	324.9	320.3	313.1	303.3	288.5	267.3	243.8	224.5	217.3	216.2
142.5°	337.1	334.3	329.4	322.8	314.2	299.4	278.8	255.6	235.1	225.8	223.2
145°	349.9	347.6	342.3	336.2	329.0	314.3	295.3	272.2	251.8	239.7	234.0
147.5°	360.6	358.8	354.6	347.5	341.4	327.3	310.0	289.6	268.6	253.6	246.3
150°	367.3	365.8	361.6	354.8	348.7	335.5	318.8	299.9	279.8	263.9	254.4
152.5°	373.6	372.1	367.3	360.5	355.4	343.0	327.9	309.9	289.5	273.6	263.8
155°	382.0	380.1	375.6	369.2	364.6	353.3	339.3	323.3	305.9	289.3	278.3
157.5°	388.7	386.4	382.1	376.6	371.7	361.3	349.1	335.4	320.2	304.3	293.1
160°	392.6	390.0	385.4	380.5	376.0	366.1	355.2	342.7	328.6	314.3	302.1
162.5°	395.4	393.0	387.6	383.2	379.3	370.4	360.0	348.7	336.2	323.7	312.4
165°	398.3	395.7	390.0	386.6	383.2	375.6	366.5	357.4	346.8	336.6	327.5
167.5°	398.5	396.3	390.7	387.3	384.8	378.3	371.0	364.0	355.8	347.7	340.2
170°	397.9	396.0	390.4	387.3	385.4	380.1	373.7	367.6	361.2	354.4	348.3
172.5°	395.8	393.9	388.5	386.1	385.1	380.4	375.2	370.7	365.1	360.2	355.3
175°	390.4	388.9	384.3	382.8	383.2	380.1	376.4	373.7	370.3	367.3	364.6
177.5°	382.4	381.5	378.2	378.2	379.4	377.6	376.4	375.1	373.6	372.7	371.8
180°	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8



TEST NUMBER: P1428185

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1
2.5°	1598.9	1595.1	1595.7	1596.6	1598.3	1600.1	1598.3	1596.6	1595.7	1595.1	1598.9
5°	1605.7	1602.4	1603.9	1606.8	1614.0	1621.3	1614.0	1606.8	1603.9	1602.4	1605.7
7.5°	1623.9	1624.0	1628.2	1633.8	1643.3	1652.9	1643.3	1633.8	1628.2	1624.0	1623.9
10°	1632.5	1631.4	1632.1	1635.2	1645.4	1655.5	1645.4	1635.2	1632.1	1631.4	1632.5
12.5°	1617.3	1611.0	1609.9	1610.6	1616.1	1621.6	1616.1	1610.6	1609.9	1611.0	1617.3
15°	1580.1	1568.5	1570.7	1573.2	1576.9	1580.5	1576.9	1573.2	1570.7	1568.5	1580.1
17.5°	1544.3	1536.1	1543.9	1551.6	1558.7	1565.8	1558.7	1551.6	1543.9	1536.1	1544.3
20°	1525.0	1520.3	1530.5	1541.2	1553.5	1565.8	1553.5	1541.2	1530.5	1520.3	1525.0
22.5°	1507.6	1506.7	1520.9	1535.8	1552.8	1569.7	1552.8	1535.8	1520.9	1506.7	1507.6
25°	1480.1	1488.1	1512.0	1534.6	1553.5	1572.3	1553.5	1534.6	1512.0	1488.1	1480.1
27.5°	1449.4	1469.8	1502.1	1529.6	1542.8	1556.0	1542.8	1529.6	1502.1	1469.8	1449.4
30°	1431.0	1456.0	1484.2	1506.7	1511.8	1516.9	1511.8	1506.7	1484.2	1456.0	1431.0
32.5°	1409.5	1433.7	1448.6	1458.2	1451.6	1445.1	1451.6	1458.2	1448.6	1433.7	1409.5
35°	1371.2	1387.1	1375.5	1363.4	1349.6	1335.8	1349.6	1363.4	1375.5	1387.1	1371.2
37.5°	1301.5	1301.2	1267.3	1237.9	1222.1	1206.3	1222.1	1237.9	1267.3	1301.2	1301.5
40°	1244.8	1228.9	1178.2	1135.6	1117.4	1099.3	1117.4	1135.6	1178.2	1228.9	1244.8
42.5°	1171.3	1137.1	1072.5	1018.4	996.2	974.1	996.2	1018.4	1072.5	1137.1	1171.3
45°	1036.8	981.0	910.7	851.8	827.1	802.5	827.1	851.8	910.7	981.0	1036.8
47.5°	886.6	821.6	758.9	706.0	683.0	659.9	683.0	706.0	758.9	821.6	886.6
50°	791.1	725.8	667.1	616.7	591.3	566.0	591.3	616.7	667.1	725.8	791.1
52.5°	705.8	642.3	583.6	533.8	510.7	487.7	510.7	533.8	583.6	642.3	705.8
55°	584.6	526.6	470.8	425.0	409.0	393.1	409.0	425.0	470.8	526.6	584.6
57.5°	481.0	429.4	382.0	343.5	331.8	320.0	331.8	343.5	382.0	429.4	481.0
60°	414.5	368.1	331.1	301.0	291.6	282.2	291.6	301.0	331.1	368.1	414.5
62.5°	359.8	318.3	288.9	265.1	258.0	250.9	258.0	265.1	288.9	318.3	359.8
65°	293.6	259.5	237.0	218.9	213.8	208.8	213.8	218.9	237.0	259.5	293.6
67.5°	241.4	214.0	196.3	181.8	177.0	172.2	177.0	181.8	196.3	214.0	241.4
70°	210.4	186.1	170.2	157.3	153.7	150.1	153.7	157.3	170.2	186.1	210.4
72.5°	181.0	160.2	147.1	136.7	134.3	131.8	134.3	136.7	147.1	160.2	181.0
75°	138.8	122.9	114.2	107.3	105.8	104.4	105.8	107.3	114.2	122.9	138.8
77.5°	98.9	87.9	85.0	82.9	82.9	82.9	82.9	82.9	85.0	87.9	98.9
80°	75.8	68.5	68.5	68.5	68.5	68.5	68.5	68.5	68.5	68.5	75.8
82.5°	56.9	52.8	52.8	52.7	52.1	51.5	52.1	52.7	52.8	52.8	56.9
85°	31.0	28.8	24.5	20.7	18.5	16.3	18.5	20.7	24.5	28.8	31.0
87.5°	7.1	6.2	6.7	7.0	7.3	7.2	7.3	7.0	6.7	6.2	7.1
90°	8.7	11.4	14.0	15.5	17.0	16.3	17.0	15.5	14.0	11.4	8.7
92.5°	17.5	22.0	25.2	27.9	29.2	29.0	29.2	27.9	25.2	22.0	17.5
95°	35.2	40.5	45.8	49.6	51.9	51.1	51.9	49.6	45.8	40.5	35.2
97.5°	54.3	61.4	67.3	70.9	73.2	74.7	73.2	70.9	67.3	61.4	54.3
100°	67.0	73.8	80.6	84.8	88.6	90.1	88.6	84.8	80.6	73.8	67.0
102.5°	77.3	86.3	93.7	98.1	101.3	102.8	101.3	98.1	93.7	86.3	77.3
105°	94.3	103.7	111.7	117.4	120.8	121.9	120.8	117.4	111.7	103.7	94.3
107.5°	111.2	121.0	128.4	134.6	138.8	141.2	138.8	134.6	128.4	121.0	111.2
110°	124.6	132.5	140.5	146.2	150.3	151.8	150.3	146.2	140.5	132.5	124.6



TEST NUMBER: P1428185

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	135.8	144.6	152.6	158.3	163.0	165.2	163.0	158.3	152.6	144.6	135.8
115°	151.5	163.2	170.4	175.7	179.1	181.0	179.1	175.7	170.4	163.2	151.5
117.5°	164.5	176.7	184.6	188.7	190.3	191.7	190.3	188.7	184.6	176.7	164.5
120°	172.7	184.0	193.1	198.4	200.3	201.1	200.3	198.4	193.1	184.0	172.7
122.5°	180.2	191.0	199.8	206.3	209.4	210.1	209.4	206.3	199.8	191.0	180.2
125°	190.8	201.1	210.1	216.6	220.0	221.9	220.0	216.6	210.1	201.1	190.8
127.5°	200.1	211.1	219.5	225.3	228.6	230.1	228.6	225.3	219.5	211.1	200.1
130°	205.2	216.6	224.9	231.3	234.4	235.9	234.4	231.3	224.9	216.6	205.2
132.5°	209.2	221.1	229.8	235.6	238.9	240.4	238.9	235.6	229.8	221.1	209.2
135°	213.9	226.4	235.5	241.2	244.2	245.7	244.2	241.2	235.5	226.4	213.9
137.5°	218.1	229.4	238.9	244.9	247.6	248.6	247.6	244.9	238.9	229.4	218.1
140°	221.1	231.0	240.4	246.1	249.1	249.5	249.1	246.1	240.4	231.0	221.1
142.5°	225.1	232.8	241.0	246.7	249.7	250.4	249.7	246.7	241.0	232.8	225.1
145°	232.1	236.6	242.3	247.6	250.3	251.0	250.3	247.6	242.3	236.6	232.1
147.5°	241.0	242.4	245.4	248.8	251.4	251.9	251.4	248.8	245.4	242.4	241.0
150°	247.6	247.2	248.4	250.7	252.9	252.5	252.9	250.7	248.4	247.2	247.6
152.5°	255.2	253.0	252.9	254.0	255.0	255.0	255.0	254.0	252.9	253.0	255.2
155°	268.1	263.9	261.6	260.9	260.9	260.5	260.9	260.9	261.6	263.9	268.1
157.5°	282.2	276.4	273.0	271.2	270.6	269.8	270.6	271.2	273.0	276.4	282.2
160°	291.9	285.5	282.1	279.0	277.9	276.8	277.9	279.0	282.1	285.5	291.9
162.5°	301.0	294.9	291.2	288.4	287.3	285.6	287.3	288.4	291.2	294.9	301.0
165°	315.8	309.3	305.2	302.9	301.4	299.9	301.4	302.9	305.2	309.3	315.8
167.5°	330.5	323.5	320.8	318.2	316.8	314.0	316.8	318.2	320.8	323.5	330.5
170°	339.6	333.2	331.7	329.4	326.8	323.7	326.8	329.4	331.7	333.2	339.6
172.5°	347.5	343.2	341.7	339.4	338.6	336.1	338.6	339.4	341.7	343.2	347.5
175°	358.9	355.5	355.5	355.2	354.0	351.7	354.0	355.2	355.5	355.5	358.9
177.5°	368.5	366.7	367.9	367.9	367.6	365.5	367.6	367.9	367.9	366.7	368.5
180°	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8	374.8



TEST NUMBER: P1428185

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1600.1	1600.1	1600.1	1600.1
2.5°	1607.0	1610.9	1602.2	1593.5
5°	1613.6	1616.5	1604.2	1591.9
7.5°	1628.0	1626.7	1609.1	1591.6
10°	1635.4	1632.3	1611.3	1590.3
12.5°	1628.9	1631.4	1606.9	1582.4
15°	1605.5	1617.3	1588.3	1559.3
17.5°	1568.5	1579.1	1548.8	1518.5
20°	1544.6	1551.8	1522.1	1492.4
22.5°	1523.7	1528.4	1498.6	1468.9
25°	1488.1	1487.5	1461.4	1435.3
27.5°	1441.0	1430.8	1415.5	1400.1
30°	1409.2	1390.4	1380.2	1370.1
32.5°	1376.2	1349.6	1343.5	1337.5
35°	1327.7	1293.8	1288.7	1283.6
37.5°	1268.2	1240.6	1230.1	1219.7
40°	1226.0	1207.5	1190.1	1172.7
42.5°	1175.1	1171.0	1143.1	1115.3
45°	1078.1	1099.7	1062.0	1024.3
47.5°	953.7	994.4	955.7	917.0
50°	862.8	908.9	877.7	846.5
52.5°	774.1	819.7	797.2	774.7
55°	644.8	687.0	675.4	663.8
57.5°	536.8	576.8	569.5	562.1
60°	470.3	510.9	505.8	500.7
62.5°	413.3	452.5	448.5	444.6
65°	339.3	372.6	369.0	365.4
67.5°	278.7	306.2	304.3	302.4
70°	243.0	267.3	266.6	265.9
72.5°	209.5	231.2	232.2	233.2
75°	162.0	180.0	182.1	184.3
77.5°	118.1	133.0	135.3	137.7
80°	90.3	101.8	104.7	107.6
82.5°	65.0	72.1	76.2	80.2
85°	31.0	31.9	35.5	39.1
87.5°	9.6	11.3	11.0	10.7
90°	6.8	4.2	2.7	1.1
92.5°	14.7	10.2	7.2	4.2
95°	29.5	23.5	16.7	11.7
97.5°	47.0	37.3	30.5	22.4
100°	56.4	46.9	40.5	31.8
102.5°	66.7	58.8	49.9	41.2
105°	85.2	75.3	65.1	55.3
107.5°	102.3	91.5	79.2	70.3
110°	113.2	101.5	88.6	80.6



TEST NUMBER: P1428185

CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	123.8	111.8	98.6	90.6
115°	138.2	124.9	112.8	106.0
117.5°	152.1	138.4	125.6	120.3
120°	160.5	146.9	134.4	130.2
122.5°	167.5	154.2	142.6	140.8
125°	178.0	164.3	154.5	156.8
127.5°	186.4	173.9	167.7	172.8
130°	191.6	180.6	176.8	184.0
132.5°	196.1	187.6	185.9	195.8
135°	202.9	198.0	199.5	213.2
137.5°	211.0	209.2	214.2	231.4
140°	216.2	217.3	224.5	243.8
142.5°	223.2	225.8	235.1	255.6
145°	234.0	239.7	251.8	272.2
147.5°	246.3	253.6	268.6	289.6
150°	254.4	263.9	279.8	299.9
152.5°	263.8	273.6	289.5	309.9
155°	278.3	289.3	305.9	323.3
157.5°	293.1	304.3	320.2	335.4
160°	302.1	314.3	328.6	342.7
162.5°	312.4	323.7	336.2	348.7
165°	327.5	336.6	346.8	357.4
167.5°	340.2	347.7	355.8	364.0
170°	348.3	354.4	361.2	367.6
172.5°	355.3	360.2	365.1	370.7
175°	364.6	367.3	370.3	373.7
177.5°	371.8	372.7	373.6	375.1
180°	374.8	374.8	374.8	374.8



TEST NUMBER: P1428185
 CATALOG NUMBER: SQ2W-PR1-K-025U-075D-L830-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.27	21.38	20.96	22.07	22.89	16.64	17.75	17.33	18.44	19.26
	3H	21.50	22.49	22.20	23.19	24.04	17.82	18.81	18.52	19.52	20.36
	4H	22.00	22.93	22.71	23.64	24.50	18.30	19.23	19.02	19.94	20.80
	6H	22.31	23.16	23.03	23.89	24.76	18.65	19.51	19.38	20.23	21.11
	8H	22.41	23.23	23.16	23.97	24.85	18.80	19.61	19.54	20.36	21.23
	12H	22.46	23.24	23.21	23.98	24.88	18.84	19.61	19.58	20.35	21.25
4H	2H	20.41	21.34	21.13	22.05	22.91	17.38	18.31	18.10	19.03	19.89
	3H	21.89	22.66	22.62	23.41	24.29	18.76	19.53	19.49	20.28	21.16
	4H	22.53	23.22	23.28	23.98	24.88	19.32	20.01	20.06	20.77	21.67
	6H	22.97	23.57	23.74	24.35	25.27	19.76	20.36	20.53	21.14	22.06
	8H	23.13	23.70	23.91	24.47	25.40	19.95	20.51	20.72	21.29	22.21
	12H	23.21	23.71	24.00	24.51	25.44	20.01	20.51	20.80	21.31	22.24
8H	4H	22.57	23.13	23.34	23.91	24.83	19.66	20.22	20.43	21.00	21.92
	6H	23.11	23.57	23.91	24.39	25.32	20.21	20.67	21.01	21.49	22.42
	8H	23.34	23.76	24.16	24.58	25.52	20.47	20.88	21.28	21.70	22.65
	12H	23.47	23.84	24.29	24.64	25.65	20.57	20.94	21.39	21.75	22.75
12H	4H	22.54	23.04	23.33	23.84	24.77	19.69	20.19	20.48	20.99	21.92
	6H	23.10	23.51	23.91	24.33	25.27	20.28	20.69	21.09	21.51	22.46
	8H	23.36	23.73	24.17	24.53	25.54	20.58	20.95	21.39	21.75	22.75