

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428233

Luminaire Tested: SQ2W-PR1-K-075U-075D-L830-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428233
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-9)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PR1-K-075U-075D-L830-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE RIPPLE LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7118.9 lumens
Efficiency: N/A
Efficacy: 141.5 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 50.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428233

CATALOG NUMBER: SQ2W-PR1-K-075U-075D-L830-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428233

CATALOG NUMBER: SQ2W-PR1-K-075U-075D-L830-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	92	88	92	89	85	83	76	74	72	65	63	62	54	53	52	47
2	91	84	78	73	84	78	73	69	67	64	60	58	55	52	48	46	45	40
3	83	74	67	62	77	69	63	58	60	55	52	51	48	45	43	41	39	35
4	77	66	59	53	71	62	55	50	54	49	44	46	42	39	39	36	34	30
5	71	59	51	46	65	55	48	43	48	43	39	42	38	34	35	32	30	27
6	65	53	45	40	60	50	43	38	44	38	34	38	34	30	32	29	27	24
7	60	48	41	35	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21	19
9	52	40	33	28	49	38	31	27	33	28	24	29	25	22	25	22	19	17
10	49	37	30	25	45	35	28	24	31	26	22	27	23	20	23	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	25834	25834	25834	25834
5°	25800	26277	25800	26277
10°	26072	27141	26072	27141
15°	26064	26418	26064	26418
20°	25642	26903	25642	26903
25°	25569	28010	25569	28010
30°	25543	28280	25543	28280
35°	25300	26329	25300	26329
40°	24716	23169	24716	23169
45°	23388	18324	23388	18324
50°	21262	14217	21262	14217
55°	18685	11065	18685	11065
60°	16168	9113	16168	9113
65°	13960	7977	13960	7977
70°	12552	7086	12552	7086
75°	11497	6513	11497	6513
80°	10004	6369	10004	6369
85°	7243	3020	7243	3020

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 25110 cd/sqm



TEST NUMBER: P1428233

CATALOG NUMBER: SQ2W-PR1-K-075U-075D-L830-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.5	2.2
10°-20°	447.3	6.3
20°-30°	691.5	9.7
30°-40°	831.6	11.7
40°-50°	746.7	10.5
50°-60°	500.3	7.0
60°-70°	291.1	4.1
70°-80°	149.5	2.1
80°-90°	41.5	0.6
90°-100°	89.0	1.3
100°-110°	259.5	3.6
110°-120°	423.5	5.9
120°-130°	537.4	7.5
130°-140°	575.1	8.1
140°-150°	537.0	7.5
150°-160°	441.9	6.2
160°-170°	296.3	4.2
170°-180°	105.2	1.5
0°-30°	1293.3	18.2
0°-40°	2124.9	29.8
0°-60°	3372.0	47.4
0°-90°	3854.0	54.1
90°-120°	772.0	10.8
90°-150°	2421.5	34.0
90°-180°	3265.0	45.9
0°-180°	7118.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1600	1600	1600	1600	1600	
5°	1592	1621	1592	1621	1592	152
15°	1559	1580	1559	1580	1559	438
25°	1435	1572	1435	1572	1435	662
35°	1284	1336	1284	1336	1284	800
45°	1024	802	1024	802	1024	784
55°	664	393	664	393	664	597
65°	365	209	365	209	365	370
75°	184	104	184	104	184	196
85°	39	16	39	16	39	49
90°	3	25	3	49	3	4
95°	35	26	35	152	35	42
105°	165	264	165	364	165	175
115°	316	438	316	540	316	312
125°	468	695	468	662	468	418
135°	636	909	636	733	636	491
145°	812	1048	812	749	812	508
155°	965	1138	965	777	965	443
165°	1066	1187	1066	894	1066	300
175°	1115	1162	1115	1049	1115	106
180°	1118	1118	1118	1118	1118	



TEST NUMBER: P1428233

CATALOG NUMBER: SQ2W-PR1-K-075U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1
2.5°	1593.5	1602.2	1610.9	1607.0	1598.9	1595.1	1595.7	1596.6	1598.3	1600.1	1598.3
5°	1591.9	1604.2	1616.5	1613.6	1605.7	1602.4	1603.9	1606.8	1614.0	1621.3	1614.0
7.5°	1591.6	1609.1	1626.7	1628.0	1623.9	1624.0	1628.2	1633.8	1643.3	1652.9	1643.3
10°	1590.3	1611.3	1632.3	1635.4	1632.5	1631.4	1632.1	1635.2	1645.4	1655.5	1645.4
12.5°	1582.4	1606.9	1631.4	1628.9	1617.3	1611.0	1609.9	1610.6	1616.1	1621.6	1616.1
15°	1559.3	1588.3	1617.3	1605.5	1580.1	1568.5	1570.7	1573.2	1576.9	1580.5	1576.9
17.5°	1518.5	1548.8	1579.1	1568.5	1544.3	1536.1	1543.9	1551.6	1558.7	1565.8	1558.7
20°	1492.4	1522.1	1551.8	1544.6	1525.0	1520.3	1530.5	1541.2	1553.5	1565.8	1553.5
22.5°	1468.9	1498.6	1528.4	1523.7	1507.6	1506.7	1520.9	1535.8	1552.8	1569.7	1552.8
25°	1435.3	1461.4	1487.5	1488.1	1480.1	1488.1	1512.0	1534.6	1553.5	1572.3	1553.5
27.5°	1400.1	1415.5	1430.8	1441.0	1449.4	1469.8	1502.1	1529.6	1542.8	1556.0	1542.8
30°	1370.1	1380.2	1390.4	1409.2	1431.0	1456.0	1484.2	1506.7	1511.8	1516.9	1511.8
32.5°	1337.5	1343.5	1349.6	1376.2	1409.5	1433.7	1448.6	1458.2	1451.6	1445.1	1451.6
35°	1283.6	1288.7	1293.8	1327.7	1371.2	1387.1	1375.5	1363.4	1349.6	1335.8	1349.6
37.5°	1219.7	1230.1	1240.6	1268.2	1301.5	1301.2	1267.3	1237.9	1222.1	1206.3	1222.1
40°	1172.7	1190.1	1207.5	1226.0	1244.8	1228.9	1178.2	1135.6	1117.4	1099.3	1117.4
42.5°	1115.3	1143.1	1171.0	1175.1	1171.3	1137.1	1072.5	1018.4	996.2	974.1	996.2
45°	1024.3	1062.0	1099.7	1078.1	1036.8	981.0	910.7	851.8	827.1	802.5	827.1
47.5°	917.0	955.7	994.4	953.7	886.6	821.6	758.9	706.0	683.0	659.9	683.0
50°	846.5	877.7	908.9	862.8	791.1	725.8	667.1	616.7	591.3	566.0	591.3
52.5°	774.7	797.2	819.7	774.1	705.8	642.3	583.6	533.8	510.7	487.7	510.7
55°	663.8	675.4	687.0	644.8	584.6	526.6	470.8	425.0	409.0	393.1	409.0
57.5°	562.1	569.5	576.8	536.8	481.0	429.4	382.0	343.5	331.8	320.0	331.8
60°	500.7	505.8	510.9	470.3	414.5	368.1	331.1	301.0	291.6	282.2	291.6
62.5°	444.6	448.5	452.5	413.3	359.8	318.3	288.9	265.1	258.0	250.9	258.0
65°	365.4	369.0	372.6	339.3	293.6	259.5	237.0	218.9	213.8	208.8	213.8
67.5°	302.4	304.3	306.2	278.7	241.4	214.0	196.3	181.8	177.0	172.2	177.0
70°	265.9	266.6	267.3	243.0	210.4	186.1	170.2	157.3	153.7	150.1	153.7
72.5°	233.2	232.2	231.2	209.5	181.0	160.2	147.1	136.7	134.3	131.8	134.3
75°	184.3	182.1	180.0	162.0	138.8	122.9	114.2	107.3	105.8	104.4	105.8
77.5°	137.7	135.3	133.0	118.1	98.9	87.9	85.0	82.9	82.9	82.9	82.9
80°	107.6	104.7	101.8	90.3	75.8	68.5	68.5	68.5	68.5	68.5	68.5
82.5°	80.2	76.2	72.1	65.0	56.9	52.8	52.8	52.7	52.1	51.5	52.1
85°	39.1	35.5	31.9	31.0	31.0	28.8	24.5	20.7	18.5	16.3	18.5
87.5°	11.1	12.0	13.1	11.9	9.7	8.4	8.4	8.7	8.9	8.9	8.9
90°	3.4	7.9	13.6	18.1	21.5	22.6	22.6	23.7	24.8	24.8	24.8
92.5°	12.4	19.7	19.9	19.9	24.2	26.2	28.0	28.2	29.4	29.4	29.4
95°	35.0	38.4	57.6	56.5	38.4	30.5	26.0	26.0	26.0	26.0	26.0
97.5°	66.9	71.8	75.0	100.5	106.2	102.6	83.6	70.3	62.8	59.4	62.8
100°	94.9	97.1	103.9	105.0	133.3	160.4	146.8	129.9	124.2	120.9	124.2
102.5°	122.9	124.2	134.6	139.4	145.9	161.3	208.3	203.1	199.2	198.6	199.2
105°	164.9	166.0	185.2	194.3	198.8	198.8	197.7	220.2	256.4	264.3	256.4
107.5°	209.9	215.1	237.6	261.8	267.0	268.4	262.5	259.1	257.7	258.7	257.7
110°	240.6	248.5	275.6	306.1	314.0	316.3	314.0	310.6	308.3	308.3	308.3

TEST NUMBER: P1428233

CATALOG NUMBER: SQ2W-PR1-K-075U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	270.4	281.9	312.6	347.7	361.0	367.8	362.8	360.3	358.0	359.9	358.0
115°	316.3	333.2	373.9	410.0	437.1	440.5	439.4	439.4	438.2	438.2	438.2
117.5°	358.7	385.8	431.5	473.5	504.9	513.9	518.4	517.1	515.7	518.0	515.7
120°	388.5	420.2	472.1	519.6	550.1	563.6	568.1	565.9	568.1	565.9	568.1
122.5°	420.2	459.0	510.1	559.3	595.2	610.6	616.0	616.5	616.9	615.6	616.9
125°	467.6	515.0	574.9	625.7	663.0	681.1	685.6	686.7	689.0	694.6	689.0
127.5°	515.5	569.3	635.0	684.0	722.2	744.1	751.1	753.6	758.3	760.8	758.3
130°	548.9	609.9	676.6	722.9	760.1	783.9	796.3	799.7	805.3	804.2	805.3
132.5°	584.2	647.9	715.4	763.5	798.1	823.6	834.2	843.9	846.0	847.6	846.0
135°	635.9	704.8	772.6	820.0	852.8	877.6	891.2	900.2	905.8	909.2	905.8
137.5°	690.3	763.1	828.1	870.4	903.4	924.8	940.2	949.7	955.5	958.2	955.5
140°	727.4	797.4	860.7	904.7	934.1	955.5	969.1	980.4	987.2	987.2	987.2
142.5°	762.6	831.7	893.2	937.2	963.0	982.6	997.1	1005.7	1013.4	1013.4	1013.4
145°	812.1	881.0	937.5	981.5	1003.0	1021.0	1036.9	1043.6	1048.2	1048.2	1048.2
147.5°	863.8	924.8	976.3	1018.6	1036.6	1057.9	1070.3	1075.7	1081.4	1078.9	1081.4
150°	894.5	951.0	1000.7	1040.2	1058.3	1078.7	1091.1	1095.6	1101.2	1097.9	1101.2
152.5°	924.4	978.1	1023.3	1060.1	1075.5	1095.8	1110.1	1114.6	1118.4	1115.9	1118.4
155°	964.6	1012.0	1053.8	1087.7	1101.2	1120.4	1134.0	1139.6	1144.2	1138.5	1144.2
157.5°	1000.5	1041.4	1077.7	1108.9	1123.4	1139.9	1152.5	1159.5	1164.0	1161.6	1164.0
160°	1022.2	1059.4	1092.2	1121.6	1135.1	1149.8	1163.4	1171.3	1175.8	1172.4	1175.8
162.5°	1040.2	1073.9	1104.9	1131.5	1143.3	1156.1	1172.4	1179.4	1183.9	1179.6	1183.9
165°	1066.2	1093.3	1120.4	1143.0	1153.2	1163.4	1180.3	1188.2	1191.6	1187.1	1191.6
167.5°	1085.9	1106.7	1128.6	1148.0	1155.5	1165.4	1182.3	1188.9	1193.2	1187.5	1193.2
170°	1096.7	1114.8	1134.0	1149.8	1155.5	1164.5	1181.4	1187.1	1190.5	1184.8	1190.5
172.5°	1105.8	1119.3	1134.9	1148.9	1151.8	1159.1	1175.1	1180.8	1183.2	1178.5	1183.2
175°	1114.8	1122.7	1134.0	1143.0	1141.9	1146.4	1160.0	1164.5	1169.0	1162.2	1169.0
177.5°	1119.1	1122.7	1126.3	1131.7	1128.1	1128.1	1138.1	1140.8	1141.7	1138.1	1141.7
180°	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2



TEST NUMBER: P1428233

CATALOG NUMBER: SQ2W-PR1-K-075U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1
2.5°	1596.6	1595.7	1595.1	1598.9	1607.0	1610.9	1602.2	1593.5	1602.2	1610.9	1607.0
5°	1606.8	1603.9	1602.4	1605.7	1613.6	1616.5	1604.2	1591.9	1604.2	1616.5	1613.6
7.5°	1633.8	1628.2	1624.0	1623.9	1628.0	1626.7	1609.1	1591.6	1609.1	1626.7	1628.0
10°	1635.2	1632.1	1631.4	1632.5	1635.4	1632.3	1611.3	1590.3	1611.3	1632.3	1635.4
12.5°	1610.6	1609.9	1611.0	1617.3	1628.9	1631.4	1606.9	1582.4	1606.9	1631.4	1628.9
15°	1573.2	1570.7	1568.5	1580.1	1605.5	1617.3	1588.3	1559.3	1588.3	1617.3	1605.5
17.5°	1551.6	1543.9	1536.1	1544.3	1568.5	1579.1	1548.8	1518.5	1548.8	1579.1	1568.5
20°	1541.2	1530.5	1520.3	1525.0	1544.6	1551.8	1522.1	1492.4	1522.1	1551.8	1544.6
22.5°	1535.8	1520.9	1506.7	1507.6	1523.7	1528.4	1498.6	1468.9	1498.6	1528.4	1523.7
25°	1534.6	1512.0	1488.1	1480.1	1488.1	1487.5	1461.4	1435.3	1461.4	1487.5	1488.1
27.5°	1529.6	1502.1	1469.8	1449.4	1441.0	1430.8	1415.5	1400.1	1415.5	1430.8	1441.0
30°	1506.7	1484.2	1456.0	1431.0	1409.2	1390.4	1380.2	1370.1	1380.2	1390.4	1409.2
32.5°	1458.2	1448.6	1433.7	1409.5	1376.2	1349.6	1343.5	1337.5	1343.5	1349.6	1376.2
35°	1363.4	1375.5	1387.1	1371.2	1327.7	1293.8	1288.7	1283.6	1288.7	1293.8	1327.7
37.5°	1237.9	1267.3	1301.2	1301.5	1268.2	1240.6	1230.1	1219.7	1230.1	1240.6	1268.2
40°	1135.6	1178.2	1228.9	1244.8	1226.0	1207.5	1190.1	1172.7	1190.1	1207.5	1226.0
42.5°	1018.4	1072.5	1137.1	1171.3	1175.1	1171.0	1143.1	1115.3	1143.1	1171.0	1175.1
45°	851.8	910.7	981.0	1036.8	1078.1	1099.7	1062.0	1024.3	1062.0	1099.7	1078.1
47.5°	706.0	758.9	821.6	886.6	953.7	994.4	955.7	917.0	955.7	994.4	953.7
50°	616.7	667.1	725.8	791.1	862.8	908.9	877.7	846.5	877.7	908.9	862.8
52.5°	533.8	583.6	642.3	705.8	774.1	819.7	797.2	774.7	797.2	819.7	774.1
55°	425.0	470.8	526.6	584.6	644.8	687.0	675.4	663.8	675.4	687.0	644.8
57.5°	343.5	382.0	429.4	481.0	536.8	576.8	569.5	562.1	569.5	576.8	536.8
60°	301.0	331.1	368.1	414.5	470.3	510.9	505.8	500.7	505.8	510.9	470.3
62.5°	265.1	288.9	318.3	359.8	413.3	452.5	448.5	444.6	448.5	452.5	413.3
65°	218.9	237.0	259.5	293.6	339.3	372.6	369.0	365.4	369.0	372.6	339.3
67.5°	181.8	196.3	214.0	241.4	278.7	306.2	304.3	302.4	304.3	306.2	278.7
70°	157.3	170.2	186.1	210.4	243.0	267.3	266.6	265.9	266.6	267.3	243.0
72.5°	136.7	147.1	160.2	181.0	209.5	231.2	232.2	233.2	232.2	231.2	209.5
75°	107.3	114.2	122.9	138.8	162.0	180.0	182.1	184.3	182.1	180.0	162.0
77.5°	82.9	85.0	87.9	98.9	118.1	133.0	135.3	137.7	135.3	133.0	118.1
80°	68.5	68.5	68.5	75.8	90.3	101.8	104.7	107.6	104.7	101.8	90.3
82.5°	52.7	52.8	52.8	56.9	65.0	72.1	76.2	80.2	76.2	72.1	65.0
85°	20.7	24.5	28.8	31.0	31.0	31.9	35.5	39.1	35.5	31.9	31.0
87.5°	8.7	8.4	8.4	9.7	11.9	13.1	12.0	11.1	12.0	12.9	12.3
90°	23.7	22.6	22.6	21.5	18.1	13.6	7.9	3.4	7.9	12.4	20.3
92.5°	28.2	28.0	26.2	24.2	19.9	19.9	19.7	12.4	21.5	30.5	43.8
95°	26.0	26.0	30.5	38.4	56.5	57.6	38.4	35.0	49.7	70.0	88.1
97.5°	70.3	83.6	102.6	106.2	100.5	75.0	71.8	66.9	91.0	111.1	140.3
100°	129.9	146.8	160.4	133.3	105.0	103.9	97.1	94.9	120.9	140.1	168.3
102.5°	203.1	208.3	161.3	145.9	139.4	134.6	124.2	122.9	148.9	175.3	199.0
105°	220.2	197.7	198.8	198.8	194.3	185.2	166.0	164.9	194.3	224.8	254.1
107.5°	259.1	262.5	268.4	267.0	261.8	237.6	215.1	209.9	236.3	272.9	305.2
110°	310.6	314.0	316.3	314.0	306.1	275.6	248.5	240.6	264.3	302.7	337.7



TEST NUMBER: P1428233

CATALOG NUMBER: SQ2W-PR1-K-075U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	360.3	362.8	367.8	361.0	347.7	312.6	281.9	270.4	294.1	333.4	369.3
115°	439.4	439.4	440.5	437.1	410.0	373.9	333.2	316.3	336.6	372.7	412.3
117.5°	517.1	518.4	513.9	504.9	473.5	431.5	385.8	358.7	374.8	412.9	453.6
120°	565.9	568.1	563.6	550.1	519.6	472.1	420.2	388.5	401.0	438.2	478.9
122.5°	616.5	616.0	610.6	595.2	559.3	510.1	459.0	420.2	425.4	459.9	499.7
125°	686.7	685.6	681.1	663.0	625.7	574.9	515.0	467.6	460.8	490.2	530.9
127.5°	753.6	751.1	744.1	722.2	684.0	635.0	569.3	515.5	500.4	518.9	556.2
130°	799.7	796.3	783.9	760.1	722.9	676.6	609.9	548.9	527.5	538.8	571.5
132.5°	843.9	834.2	823.6	798.1	763.5	715.4	647.9	584.2	554.6	559.5	585.1
135°	900.2	891.2	877.6	852.8	820.0	772.6	704.8	635.9	595.2	590.7	605.4
137.5°	949.7	940.2	924.8	903.4	870.4	828.1	763.1	690.3	639.1	623.9	629.6
140°	980.4	969.1	955.5	934.1	904.7	860.7	797.4	727.4	669.8	648.3	644.9
142.5°	1005.7	997.1	982.6	963.0	937.2	893.2	831.7	762.6	701.4	673.6	665.7
145°	1043.6	1036.9	1021.0	1003.0	981.5	937.5	881.0	812.1	751.1	715.0	698.0
147.5°	1075.7	1070.3	1057.9	1036.6	1018.6	976.3	924.8	863.8	801.3	756.5	734.6
150°	1095.6	1091.1	1078.7	1058.3	1040.2	1000.7	951.0	894.5	834.7	787.2	759.0
152.5°	1114.6	1110.1	1095.8	1075.5	1060.1	1023.3	978.1	924.4	863.6	816.2	787.0
155°	1139.6	1134.0	1120.4	1101.2	1087.7	1053.8	1012.0	964.6	912.6	862.9	830.2
157.5°	1159.5	1152.5	1139.9	1123.4	1108.9	1077.7	1041.4	1000.5	955.1	907.6	874.2
160°	1171.3	1163.4	1149.8	1135.1	1121.6	1092.2	1059.4	1022.2	980.4	937.5	901.3
162.5°	1179.4	1172.4	1156.1	1143.3	1131.5	1104.9	1073.9	1040.2	1003.0	965.5	932.0
165°	1188.2	1180.3	1163.4	1153.2	1143.0	1120.4	1093.3	1066.2	1034.6	1004.1	977.0
167.5°	1188.9	1182.3	1165.4	1155.5	1148.0	1128.6	1106.7	1085.9	1061.3	1037.3	1014.7
170°	1187.1	1181.4	1164.5	1155.5	1149.8	1134.0	1114.8	1096.7	1077.5	1057.2	1039.1
172.5°	1180.8	1175.1	1159.1	1151.8	1148.9	1134.9	1119.3	1105.8	1089.3	1074.4	1059.9
175°	1164.5	1160.0	1146.4	1141.9	1143.0	1134.0	1122.7	1114.8	1104.6	1095.6	1087.7
177.5°	1140.8	1138.1	1128.1	1128.1	1131.7	1126.3	1122.7	1119.1	1114.6	1111.9	1109.1
180°	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2



TEST NUMBER: P1428233

CATALOG NUMBER: SQ2W-PR1-K-075U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1	1600.1
2.5°	1598.9	1595.1	1595.7	1596.6	1598.3	1600.1	1598.3	1596.6	1595.7	1595.1	1598.9
5°	1605.7	1602.4	1603.9	1606.8	1614.0	1621.3	1614.0	1606.8	1603.9	1602.4	1605.7
7.5°	1623.9	1624.0	1628.2	1633.8	1643.3	1652.9	1643.3	1633.8	1628.2	1624.0	1623.9
10°	1632.5	1631.4	1632.1	1635.2	1645.4	1655.5	1645.4	1635.2	1632.1	1631.4	1632.5
12.5°	1617.3	1611.0	1609.9	1610.6	1616.1	1621.6	1616.1	1610.6	1609.9	1611.0	1617.3
15°	1580.1	1568.5	1570.7	1573.2	1576.9	1580.5	1576.9	1573.2	1570.7	1568.5	1580.1
17.5°	1544.3	1536.1	1543.9	1551.6	1558.7	1565.8	1558.7	1551.6	1543.9	1536.1	1544.3
20°	1525.0	1520.3	1530.5	1541.2	1553.5	1565.8	1553.5	1541.2	1530.5	1520.3	1525.0
22.5°	1507.6	1506.7	1520.9	1535.8	1552.8	1569.7	1552.8	1535.8	1520.9	1506.7	1507.6
25°	1480.1	1488.1	1512.0	1534.6	1553.5	1572.3	1553.5	1534.6	1512.0	1488.1	1480.1
27.5°	1449.4	1469.8	1502.1	1529.6	1542.8	1556.0	1542.8	1529.6	1502.1	1469.8	1449.4
30°	1431.0	1456.0	1484.2	1506.7	1511.8	1516.9	1511.8	1506.7	1484.2	1456.0	1431.0
32.5°	1409.5	1433.7	1448.6	1458.2	1451.6	1445.1	1451.6	1458.2	1448.6	1433.7	1409.5
35°	1371.2	1387.1	1375.5	1363.4	1349.6	1335.8	1349.6	1363.4	1375.5	1387.1	1371.2
37.5°	1301.5	1301.2	1267.3	1237.9	1222.1	1206.3	1222.1	1237.9	1267.3	1301.2	1301.5
40°	1244.8	1228.9	1178.2	1135.6	1117.4	1099.3	1117.4	1135.6	1178.2	1228.9	1244.8
42.5°	1171.3	1137.1	1072.5	1018.4	996.2	974.1	996.2	1018.4	1072.5	1137.1	1171.3
45°	1036.8	981.0	910.7	851.8	827.1	802.5	827.1	851.8	910.7	981.0	1036.8
47.5°	886.6	821.6	758.9	706.0	683.0	659.9	683.0	706.0	758.9	821.6	886.6
50°	791.1	725.8	667.1	616.7	591.3	566.0	591.3	616.7	667.1	725.8	791.1
52.5°	705.8	642.3	583.6	533.8	510.7	487.7	510.7	533.8	583.6	642.3	705.8
55°	584.6	526.6	470.8	425.0	409.0	393.1	409.0	425.0	470.8	526.6	584.6
57.5°	481.0	429.4	382.0	343.5	331.8	320.0	331.8	343.5	382.0	429.4	481.0
60°	414.5	368.1	331.1	301.0	291.6	282.2	291.6	301.0	331.1	368.1	414.5
62.5°	359.8	318.3	288.9	265.1	258.0	250.9	258.0	265.1	288.9	318.3	359.8
65°	293.6	259.5	237.0	218.9	213.8	208.8	213.8	218.9	237.0	259.5	293.6
67.5°	241.4	214.0	196.3	181.8	177.0	172.2	177.0	181.8	196.3	214.0	241.4
70°	210.4	186.1	170.2	157.3	153.7	150.1	153.7	157.3	170.2	186.1	210.4
72.5°	181.0	160.2	147.1	136.7	134.3	131.8	134.3	136.7	147.1	160.2	181.0
75°	138.8	122.9	114.2	107.3	105.8	104.4	105.8	107.3	114.2	122.9	138.8
77.5°	98.9	87.9	85.0	82.9	82.9	82.9	82.9	82.9	85.0	87.9	98.9
80°	75.8	68.5	68.5	68.5	68.5	68.5	68.5	68.5	68.5	68.5	75.8
82.5°	56.9	52.8	52.8	52.7	52.1	51.5	52.1	52.7	52.8	52.8	56.9
85°	31.0	28.8	24.5	20.7	18.5	16.3	18.5	20.7	24.5	28.8	31.0
87.5°	10.6	10.7	12.3	13.2	14.1	13.6	14.1	13.2	12.3	10.7	10.6
90°	26.0	33.9	41.8	46.3	50.8	48.6	50.8	46.3	41.8	33.9	26.0
92.5°	52.2	65.5	75.2	83.4	87.0	86.5	87.0	83.4	75.2	65.5	52.2
95°	105.0	120.9	136.7	148.0	154.7	152.5	154.7	148.0	136.7	120.9	105.0
97.5°	162.0	183.2	200.8	211.4	218.2	222.7	218.2	211.4	200.8	183.2	162.0
100°	199.9	220.2	240.6	253.0	264.3	268.8	264.3	253.0	240.6	220.2	199.9
102.5°	230.6	257.3	279.4	292.8	302.2	306.8	302.2	292.8	279.4	257.3	230.6
105°	281.2	309.5	333.2	350.1	360.3	363.7	360.3	350.1	333.2	309.5	281.2
107.5°	331.8	361.0	382.9	401.6	414.1	421.3	414.1	401.6	382.9	361.0	331.8
110°	371.6	395.3	419.0	436.0	448.4	452.9	448.4	436.0	419.0	395.3	371.6



TEST NUMBER: P1428233

CATALOG NUMBER: SQ2W-PR1-K-075U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	405.0	431.5	455.2	472.1	486.4	492.7	486.4	472.1	455.2	431.5	405.0
115°	451.8	486.8	508.3	524.1	534.2	539.9	534.2	524.1	508.3	486.8	451.8
117.5°	490.6	527.2	550.7	562.9	567.7	571.7	567.7	562.9	550.7	527.2	490.6
120°	515.0	548.9	576.0	591.8	597.5	599.8	597.5	591.8	576.0	548.9	515.0
122.5°	537.6	569.7	595.9	615.3	624.6	626.9	624.6	615.3	595.9	569.7	537.6
125°	569.3	599.8	626.9	646.1	656.2	661.9	656.2	646.1	626.9	599.8	569.3
127.5°	596.8	629.8	654.6	672.0	682.0	686.5	682.0	672.0	654.6	629.8	596.8
130°	612.2	646.1	670.9	690.1	699.1	703.7	699.1	690.1	670.9	646.1	612.2
132.5°	623.9	659.6	685.4	702.8	712.7	717.2	712.7	702.8	685.4	659.6	623.9
135°	638.2	675.4	702.5	719.5	728.5	733.0	728.5	719.5	702.5	675.4	638.2
137.5°	650.6	684.5	712.7	730.5	738.7	741.6	738.7	730.5	712.7	684.5	650.6
140°	659.6	689.0	717.2	734.2	743.2	744.3	743.2	734.2	717.2	689.0	659.6
142.5°	671.4	694.4	719.0	736.0	745.0	747.0	745.0	736.0	719.0	694.4	671.4
145°	692.4	705.9	722.9	738.7	746.6	748.8	746.6	738.7	722.9	705.9	692.4
147.5°	718.8	723.1	731.9	742.3	750.0	751.6	750.0	742.3	731.9	723.1	718.8
150°	738.7	737.5	740.9	747.7	754.5	753.4	754.5	747.7	740.9	737.5	738.7
152.5°	761.3	754.7	754.5	757.7	760.8	760.6	760.8	757.7	754.5	754.7	761.3
155°	799.7	787.2	780.5	778.2	778.2	777.1	778.2	778.2	780.5	787.2	799.7
157.5°	841.9	824.5	814.4	808.9	807.4	804.9	807.4	808.9	814.4	824.5	841.9
160°	870.8	851.6	841.5	832.4	829.0	825.6	829.0	832.4	841.5	851.6	870.8
162.5°	897.9	879.6	868.6	860.4	857.0	851.9	857.0	860.4	868.6	879.6	897.9
165°	942.0	922.8	910.4	903.6	899.1	894.5	899.1	903.6	910.4	922.8	942.0
167.5°	986.0	965.0	956.9	949.2	944.9	936.8	944.9	949.2	956.9	965.0	986.0
170°	1013.1	993.9	989.4	982.6	974.7	965.7	974.7	982.6	989.4	993.9	1013.1
172.5°	1036.6	1023.8	1019.2	1012.5	1010.0	1002.7	1010.0	1012.5	1019.2	1023.8	1036.6
175°	1070.7	1060.6	1060.6	1059.4	1056.1	1049.3	1056.1	1059.4	1060.6	1060.6	1070.7
177.5°	1099.2	1093.8	1097.4	1097.4	1096.5	1090.2	1096.5	1097.4	1097.4	1093.8	1099.2
180°	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2	1118.2



TEST NUMBER: P1428233

CATALOG NUMBER: SQ2W-PR1-K-075U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1600.1	1600.1	1600.1	1600.1
2.5°	1607.0	1610.9	1602.2	1593.5
5°	1613.6	1616.5	1604.2	1591.9
7.5°	1628.0	1626.7	1609.1	1591.6
10°	1635.4	1632.3	1611.3	1590.3
12.5°	1628.9	1631.4	1606.9	1582.4
15°	1605.5	1617.3	1588.3	1559.3
17.5°	1568.5	1579.1	1548.8	1518.5
20°	1544.6	1551.8	1522.1	1492.4
22.5°	1523.7	1528.4	1498.6	1468.9
25°	1488.1	1487.5	1461.4	1435.3
27.5°	1441.0	1430.8	1415.5	1400.1
30°	1409.2	1390.4	1380.2	1370.1
32.5°	1376.2	1349.6	1343.5	1337.5
35°	1327.7	1293.8	1288.7	1283.6
37.5°	1268.2	1240.6	1230.1	1219.7
40°	1226.0	1207.5	1190.1	1172.7
42.5°	1175.1	1171.0	1143.1	1115.3
45°	1078.1	1099.7	1062.0	1024.3
47.5°	953.7	994.4	955.7	917.0
50°	862.8	908.9	877.7	846.5
52.5°	774.1	819.7	797.2	774.7
55°	644.8	687.0	675.4	663.8
57.5°	536.8	576.8	569.5	562.1
60°	470.3	510.9	505.8	500.7
62.5°	413.3	452.5	448.5	444.6
65°	339.3	372.6	369.0	365.4
67.5°	278.7	306.2	304.3	302.4
70°	243.0	267.3	266.6	265.9
72.5°	209.5	231.2	232.2	233.2
75°	162.0	180.0	182.1	184.3
77.5°	118.1	133.0	135.3	137.7
80°	90.3	101.8	104.7	107.6
82.5°	65.0	72.1	76.2	80.2
85°	31.0	31.9	35.5	39.1
87.5°	12.3	12.9	12.0	11.1
90°	20.3	12.4	7.9	3.4
92.5°	43.8	30.5	21.5	12.4
95°	88.1	70.0	49.7	35.0
97.5°	140.3	111.1	91.0	66.9
100°	168.3	140.1	120.9	94.9
102.5°	199.0	175.3	148.9	122.9
105°	254.1	224.8	194.3	164.9
107.5°	305.2	272.9	236.3	209.9
110°	337.7	302.7	264.3	240.6



TEST NUMBER: P1428233

CATALOG NUMBER: SQ2W-PR1-K-075U-075D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	369.3	333.4	294.1	270.4
115°	412.3	372.7	336.6	316.3
117.5°	453.6	412.9	374.8	358.7
120°	478.9	438.2	401.0	388.5
122.5°	499.7	459.9	425.4	420.2
125°	530.9	490.2	460.8	467.6
127.5°	556.2	518.9	500.4	515.5
130°	571.5	538.8	527.5	548.9
132.5°	585.1	559.5	554.6	584.2
135°	605.4	590.7	595.2	635.9
137.5°	629.6	623.9	639.1	690.3
140°	644.9	648.3	669.8	727.4
142.5°	665.7	673.6	701.4	762.6
145°	698.0	715.0	751.1	812.1
147.5°	734.6	756.5	801.3	863.8
150°	759.0	787.2	834.7	894.5
152.5°	787.0	816.2	863.6	924.4
155°	830.2	862.9	912.6	964.6
157.5°	874.2	907.6	955.1	1000.5
160°	901.3	937.5	980.4	1022.2
162.5°	932.0	965.5	1003.0	1040.2
165°	977.0	1004.1	1034.6	1066.2
167.5°	1014.7	1037.3	1061.3	1085.9
170°	1039.1	1057.2	1077.5	1096.7
172.5°	1059.9	1074.4	1089.3	1105.8
175°	1087.7	1095.6	1104.6	1114.8
177.5°	1109.1	1111.9	1114.6	1119.1
180°	1118.2	1118.2	1118.2	1118.2



TEST NUMBER: P1428233
 CATALOG NUMBER: SQ2W-PR1-K-075U-075D-L830-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.35	19.20	19.28	20.14	21.36	14.72	15.57	15.65	16.51	17.73
	3H	19.55	20.32	20.50	21.27	22.51	15.88	16.64	16.82	17.59	18.83
	4H	20.04	20.76	21.00	21.72	22.96	16.34	17.06	17.30	18.02	19.27
	6H	20.34	21.00	21.30	21.96	23.22	16.68	17.35	17.65	18.31	19.57
	8H	20.44	21.07	21.41	22.05	23.30	16.82	17.45	17.80	18.43	19.69
	12H	20.48	21.08	21.46	22.05	23.33	16.85	17.45	17.83	18.42	19.70
4H	2H	18.45	19.17	19.41	20.13	21.37	15.43	16.15	16.39	17.10	18.35
	3H	19.91	20.51	20.88	21.49	22.76	16.78	17.38	17.75	18.37	19.63
	4H	20.54	21.08	21.52	22.06	23.35	17.33	17.87	18.31	18.85	20.14
	6H	20.97	21.44	21.96	22.44	23.73	17.76	18.23	18.75	19.23	20.52
	8H	21.13	21.57	22.12	22.56	23.86	17.94	18.38	18.94	19.38	20.68
	12H	21.19	21.59	22.21	22.60	23.90	17.99	18.38	19.00	19.40	20.70
8H	4H	20.56	21.00	21.56	22.00	23.30	17.66	18.09	18.65	19.09	20.39
	6H	21.10	21.46	22.11	22.49	23.79	18.20	18.56	19.21	19.59	20.89
	8H	21.33	21.65	22.36	22.67	23.99	18.46	18.78	19.48	19.80	21.12
	12H	21.45	21.73	22.48	22.75	24.11	18.55	18.83	19.58	19.85	21.21
12H	4H	20.52	20.92	21.53	21.93	23.23	17.67	18.07	18.69	19.08	20.38
	6H	21.09	21.40	22.11	22.43	23.74	18.27	18.59	19.29	19.61	20.93
	8H	21.34	21.62	22.37	22.64	24.00	18.56	18.84	19.58	19.85	21.22