

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435970

Luminaire Tested: SQ2W-FB-K-075U-100D-L930-UNV-STD-W-WM-4

Issue Date: 3/24/2026

Test Information

Test Method: LM-79-2019
Report Number: P1435970
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 3/24/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-FB-K-075U-100D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6613.5 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1435970

CATALOG NUMBER: SQ2W-FB-K-075U-100D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1435970

CATALOG NUMBER: SQ2W-FB-K-075U-100D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	99	95	91	87	92	89	85	82	77	74	72	66	64	62	56	54	53	48
2	90	82	76	71	84	77	71	67	67	62	59	57	54	51	49	46	44	40
3	82	72	64	58	76	67	60	55	58	53	49	50	46	43	43	39	37	33
4	75	63	55	49	69	59	52	46	51	46	41	44	40	36	38	34	31	28
5	68	56	48	41	63	52	45	39	46	40	35	39	35	31	33	30	27	24
6	63	50	41	35	58	47	39	34	41	35	30	35	30	27	30	26	23	20
7	58	45	37	31	54	42	35	29	37	31	26	32	27	23	27	23	20	18
8	53	41	32	27	50	38	31	26	33	27	23	29	24	20	25	21	18	16
9	50	37	29	24	46	35	28	23	30	25	20	26	22	18	23	19	16	14
10	46	34	26	21	43	32	25	20	28	22	18	24	20	16	21	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6264	6264	6264	6264
5°	6107	11095	6107	11095
10°	5718	21592	5718	21592
15°	5177	24852	5177	24852
20°	4584	26027	4584	26027
25°	4055	26453	4055	26453
30°	3581	26779	3581	26779
35°	3199	28791	3199	28791
40°	2909	30588	2909	30588
45°	2683	32030	2683	32030
50°	2529	32613	2529	32613
55°	2469	32872	2469	32872
60°	2528	32708	2528	32708
65°	2636	31785	2636	31785
70°	2729	24042	2729	24042
75°	3026	13269	3026	13269
80°	3124	12310	3124	12310
85°	3112	5187	3112	5187

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 33168 cd/sqm



TEST NUMBER: P1435970

CATALOG NUMBER: SQ2W-FB-K-075U-100D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.0	1.0
10°-20°	296.6	4.5
20°-30°	522.0	7.9
30°-40°	675.7	10.2
40°-50°	745.2	11.3
50°-60°	695.5	10.5
60°-70°	537.3	8.1
70°-80°	247.7	3.7
80°-90°	51.3	0.8
90°-100°	75.7	1.1
100°-110°	220.8	3.3
110°-120°	360.3	5.4
120°-130°	457.2	6.9
130°-140°	489.2	7.4
140°-150°	456.8	6.9
150°-160°	375.9	5.7
160°-170°	252.1	3.8
170°-180°	89.5	1.4
0°-30°	883.6	13.4
0°-40°	1559.3	23.6
0°-60°	2999.9	45.4
0°-90°	3836.2	58.0
90°-120°	656.7	9.9
90°-150°	2059.9	31.1
90°-180°	2777.0	42.0
0°-180°	6613.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	388	388	388	388	388	
5°	377	685	377	685	377	35
15°	310	1487	310	1487	310	86
25°	228	1485	228	1485	228	105
35°	162	1461	162	1461	162	102
45°	118	1403	118	1403	118	91
55°	88	1168	88	1168	88	79
65°	69	832	69	832	69	68
75°	48	213	48	213	48	50
85°	17	28	17	28	17	18
90°	3	21	3	41	3	3
95°	30	22	30	130	30	36
105°	140	225	140	309	140	149
115°	269	373	269	459	269	265
125°	398	591	398	563	398	356
135°	541	773	541	624	541	418
145°	691	892	691	637	691	432
155°	820	968	820	661	820	377
165°	907	1010	907	761	907	255
175°	948	989	948	893	948	90
180°	951	951	951	951	951	



TEST NUMBER: P1435970

CATALOG NUMBER: SQ2W-FB-K-075U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	388.0	388.0	388.0	388.0	388.0	388.0	388.0	388.0	388.0	388.0	388.0
2.5°	385.0	392.3	399.6	407.4	415.4	424.0	433.3	441.2	445.2	449.2	445.2
5°	376.8	401.7	426.6	462.6	502.4	547.6	598.2	641.5	663.1	684.6	663.1
7.5°	362.3	412.8	463.4	570.6	696.6	827.4	963.1	1075.6	1118.7	1161.8	1118.7
10°	348.8	419.3	489.8	671.6	890.5	1058.8	1176.5	1270.6	1293.8	1317.0	1293.8
12.5°	333.9	429.6	525.3	749.7	1017.0	1191.9	1274.5	1342.4	1366.3	1390.1	1366.3
15°	309.7	446.5	583.3	837.0	1129.6	1309.6	1376.7	1433.7	1460.2	1486.8	1460.2
17.5°	284.7	466.7	648.8	907.6	1192.0	1367.4	1433.9	1487.4	1501.8	1516.3	1501.8
20°	266.8	480.7	694.6	953.9	1228.3	1394.1	1451.3	1496.5	1505.6	1514.8	1505.6
22.5°	250.3	489.5	728.6	988.2	1254.7	1409.5	1452.8	1487.7	1497.5	1507.3	1497.5
25°	227.6	497.0	766.5	1025.4	1280.7	1422.1	1449.5	1471.6	1478.3	1484.9	1478.3
27.5°	205.6	490.3	775.0	1030.6	1276.5	1408.4	1426.3	1441.4	1447.9	1454.3	1447.9
30°	192.1	481.5	770.9	1024.1	1265.4	1392.7	1405.9	1418.2	1427.3	1436.4	1427.3
32.5°	180.2	470.9	761.6	1011.7	1248.3	1372.9	1385.5	1399.9	1419.7	1439.4	1419.7
35°	162.3	448.3	734.4	981.9	1216.5	1343.8	1363.7	1387.7	1424.2	1460.7	1424.2
37.5°	147.0	419.4	691.9	936.8	1172.6	1311.3	1353.0	1393.0	1428.1	1463.3	1428.1
40°	138.0	399.2	660.4	903.5	1140.6	1287.0	1342.5	1391.6	1421.5	1451.3	1421.5
42.5°	129.1	376.3	623.6	864.7	1103.8	1255.8	1320.6	1376.7	1406.6	1436.4	1406.6
45°	117.5	339.7	561.9	800.9	1045.5	1205.9	1282.2	1346.5	1374.6	1402.8	1374.6
47.5°	106.7	299.7	492.7	732.8	988.4	1156.8	1237.7	1303.5	1324.1	1344.6	1324.1
50°	100.7	273.2	445.6	686.5	950.1	1121.8	1201.4	1265.2	1281.8	1298.4	1281.8
52.5°	94.8	247.3	399.9	641.2	912.2	1085.1	1160.1	1220.1	1235.4	1250.6	1235.4
55°	87.7	212.0	336.4	575.2	852.1	1023.3	1088.8	1141.3	1154.5	1167.8	1154.5
57.5°	81.3	181.7	282.0	513.3	788.2	953.6	1009.5	1054.1	1064.9	1075.6	1064.9
60°	78.3	165.4	252.5	474.5	741.4	900.2	950.8	991.4	1002.2	1012.9	1002.2
62.5°	73.9	149.7	225.4	435.6	690.7	841.5	888.1	925.6	935.7	945.8	935.7
65°	69.0	130.4	191.7	381.2	613.3	748.9	787.8	818.7	825.4	832.0	825.4
67.5°	62.3	114.4	166.4	331.3	533.8	647.1	671.3	686.4	673.9	661.5	673.9
70°	57.8	105.9	154.0	301.0	480.9	575.0	583.3	580.6	544.9	509.3	544.9
72.5°	54.8	97.6	140.4	267.6	423.0	491.6	473.3	442.8	375.3	307.8	375.3
75°	48.5	83.3	118.1	213.9	330.0	348.2	268.6	209.3	211.0	212.7	211.0
77.5°	39.5	65.6	91.6	150.5	220.3	234.1	192.0	160.8	162.3	163.8	162.3
80°	33.6	54.3	75.0	98.2	122.3	133.5	131.8	130.8	131.6	132.4	131.6
82.5°	27.6	43.0	58.5	72.4	85.8	93.4	95.0	96.0	94.8	93.6	94.8
85°	16.8	25.9	35.0	40.4	44.6	43.3	36.7	31.3	29.6	28.0	29.6
87.5°	6.5	10.6	14.9	14.5	12.4	11.3	11.3	11.5	11.7	11.7	11.7
90°	2.9	6.7	11.5	15.4	18.3	19.2	19.2	20.2	21.1	21.1	21.1
92.5°	10.6	16.7	16.9	16.9	20.6	22.3	23.8	24.0	25.0	25.0	25.0
95°	29.8	32.7	49.0	48.0	32.7	25.9	22.1	22.1	22.1	22.1	22.1
97.5°	56.9	61.1	63.8	85.5	90.3	87.2	71.1	59.8	53.4	50.5	53.4
100°	80.7	82.6	88.4	89.4	113.4	136.4	124.9	110.5	105.7	102.8	105.7
102.5°	104.5	105.7	114.5	118.6	124.1	137.2	177.2	172.8	169.5	168.9	169.5
105°	140.3	141.2	157.6	165.3	169.1	169.1	168.1	187.4	218.1	224.8	218.1
107.5°	178.5	182.9	202.2	222.7	227.1	228.3	223.3	220.4	219.3	220.0	219.3
110°	204.7	211.4	234.4	260.4	267.1	269.0	267.1	264.2	262.3	262.3	262.3



TEST NUMBER: P1435970

CATALOG NUMBER: SQ2W-FB-K-075U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	230.0	239.8	266.0	295.7	307.1	312.8	308.6	306.5	304.6	306.1	304.6
115°	269.0	283.4	318.0	348.8	371.8	374.7	373.8	373.8	372.8	372.8	372.8
117.5°	305.2	328.2	367.0	402.8	429.5	437.2	441.0	439.9	438.7	440.6	438.7
120°	330.5	357.4	401.6	442.0	467.9	479.4	483.3	481.4	483.3	481.4	483.3
122.5°	357.4	390.5	433.9	475.8	506.3	519.4	524.0	524.4	524.8	523.6	524.8
125°	397.8	438.1	489.1	532.3	564.0	579.4	583.2	584.2	586.1	590.9	586.1
127.5°	438.5	484.2	540.2	581.9	614.3	633.0	638.9	641.0	645.1	647.2	645.1
130°	467.0	518.8	575.5	614.9	646.6	666.8	677.4	680.3	685.1	684.1	685.1
132.5°	496.9	551.1	608.6	649.5	678.9	700.6	709.7	717.9	719.6	721.0	719.6
135°	540.9	599.5	657.2	697.5	725.4	746.5	758.1	765.8	770.6	773.4	770.6
137.5°	587.2	649.1	704.5	740.4	768.5	786.7	799.8	807.8	812.8	815.1	812.8
140°	618.8	678.3	732.1	769.6	794.6	812.8	824.4	834.0	839.7	839.7	839.7
142.5°	648.7	707.5	759.8	797.3	819.2	835.9	848.2	855.5	862.0	862.0	862.0
145°	690.8	749.4	797.5	834.9	853.2	868.6	882.0	887.8	891.6	891.6	891.6
147.5°	734.8	786.7	830.5	866.5	881.8	899.9	910.5	915.1	919.9	917.8	919.9
150°	761.0	809.0	851.3	884.9	900.3	917.6	928.1	932.0	936.8	933.9	936.8
152.5°	786.3	832.1	870.5	901.8	914.9	932.2	944.3	948.1	951.4	949.3	951.4
155°	820.5	860.9	896.4	925.3	936.8	953.1	964.6	969.5	973.3	968.5	973.3
157.5°	851.1	885.9	916.8	943.3	955.6	969.6	980.4	986.4	990.2	988.1	990.2
160°	869.5	901.2	929.1	954.1	965.6	978.1	989.6	996.4	1000.2	997.3	1000.2
162.5°	884.9	913.5	939.9	962.5	972.5	983.5	997.3	1003.3	1007.1	1003.5	1007.1
165°	907.0	930.1	953.1	972.3	981.0	989.6	1004.0	1010.8	1013.7	1009.8	1013.7
167.5°	923.7	941.4	960.0	976.6	982.9	991.4	1005.8	1011.3	1015.0	1010.2	1015.0
170°	932.9	948.3	964.6	978.1	982.9	990.6	1005.0	1009.8	1012.7	1007.9	1012.7
172.5°	940.6	952.2	965.4	977.3	979.8	986.0	999.6	1004.4	1006.5	1002.5	1006.5
175°	948.3	955.0	964.6	972.3	971.4	975.2	986.7	990.6	994.4	988.7	994.4
177.5°	952.0	955.0	958.1	962.7	959.7	959.7	968.1	970.4	971.2	968.1	971.2
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1435970

CATALOG NUMBER: SQ2W-FB-K-075U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	388.0	388.0	388.0	388.0	388.0	388.0	388.0	388.0	388.0	388.0	388.0
2.5°	441.2	433.3	424.0	415.4	407.4	399.6	392.3	385.0	392.3	399.6	407.4
5°	641.5	598.2	547.6	502.4	462.6	426.6	401.7	376.8	401.7	426.6	462.6
7.5°	1075.6	963.1	827.4	696.6	570.6	463.4	412.8	362.3	412.8	463.4	570.6
10°	1270.6	1176.5	1058.8	890.5	671.6	489.8	419.3	348.8	419.3	489.8	671.6
12.5°	1342.4	1274.5	1191.9	1017.0	749.7	525.3	429.6	333.9	429.6	525.3	749.7
15°	1433.7	1376.7	1309.6	1129.6	837.0	583.3	446.5	309.7	446.5	583.3	837.0
17.5°	1487.4	1433.9	1367.4	1192.0	907.6	648.8	466.7	284.7	466.7	648.8	907.6
20°	1496.5	1451.3	1394.1	1228.3	953.9	694.6	480.7	266.8	480.7	694.6	953.9
22.5°	1487.7	1452.8	1409.5	1254.7	988.2	728.6	489.5	250.3	489.5	728.6	988.2
25°	1471.6	1449.5	1422.1	1280.7	1025.4	766.5	497.0	227.6	497.0	766.5	1025.4
27.5°	1441.4	1426.3	1408.4	1276.5	1030.6	775.0	490.3	205.6	490.3	775.0	1030.6
30°	1418.2	1405.9	1392.7	1265.4	1024.1	770.9	481.5	192.1	481.5	770.9	1024.1
32.5°	1399.9	1385.5	1372.9	1248.3	1011.7	761.6	470.9	180.2	470.9	761.6	1011.7
35°	1387.7	1363.7	1343.8	1216.5	981.9	734.4	448.3	162.3	448.3	734.4	981.9
37.5°	1393.0	1353.0	1311.3	1172.6	936.8	691.9	419.4	147.0	419.4	691.9	936.8
40°	1391.6	1342.5	1287.0	1140.6	903.5	660.4	399.2	138.0	399.2	660.4	903.5
42.5°	1376.7	1320.6	1255.8	1103.8	864.7	623.6	376.3	129.1	376.3	623.6	864.7
45°	1346.5	1282.2	1205.9	1045.5	800.9	561.9	339.7	117.5	339.7	561.9	800.9
47.5°	1303.5	1237.7	1156.8	988.4	732.8	492.7	299.7	106.7	299.7	492.7	732.8
50°	1265.2	1201.4	1121.8	950.1	686.5	445.6	273.2	100.7	273.2	445.6	686.5
52.5°	1220.1	1160.1	1085.1	912.2	641.2	399.9	247.3	94.8	247.3	399.9	641.2
55°	1141.3	1088.8	1023.3	852.1	575.2	336.4	212.0	87.7	212.0	336.4	575.2
57.5°	1054.1	1009.5	953.6	788.2	513.3	282.0	181.7	81.3	181.7	282.0	513.3
60°	991.4	950.8	900.2	741.4	474.5	252.5	165.4	78.3	165.4	252.5	474.5
62.5°	925.6	888.1	841.5	690.7	435.6	225.4	149.7	73.9	149.7	225.4	435.6
65°	818.7	787.8	748.9	613.3	381.2	191.7	130.4	69.0	130.4	191.7	381.2
67.5°	686.4	671.3	647.1	533.8	331.3	166.4	114.4	62.3	114.4	166.4	331.3
70°	580.6	583.3	575.0	480.9	301.0	154.0	105.9	57.8	105.9	154.0	301.0
72.5°	442.8	473.3	491.6	423.0	267.6	140.4	97.6	54.8	97.6	140.4	267.6
75°	209.3	268.6	348.2	330.0	213.9	118.1	83.3	48.5	83.3	118.1	213.9
77.5°	160.8	192.0	234.1	220.3	150.5	91.6	65.6	39.5	65.6	91.6	150.5
80°	130.8	131.8	133.5	122.3	98.2	75.0	54.3	33.6	54.3	75.0	98.2
82.5°	96.0	95.0	93.4	85.8	72.4	58.5	43.0	27.6	43.0	58.5	72.4
85°	31.3	36.7	43.3	44.6	40.4	35.0	25.9	16.8	25.9	35.0	40.4
87.5°	11.5	11.3	11.3	12.4	14.5	14.9	10.6	6.5	10.6	14.7	14.9
90°	20.2	19.2	19.2	18.3	15.4	11.5	6.7	2.9	6.7	10.6	17.3
92.5°	24.0	23.8	22.3	20.6	16.9	16.9	16.7	10.6	18.3	25.9	37.3
95°	22.1	22.1	25.9	32.7	48.0	49.0	32.7	29.8	42.3	59.6	74.9
97.5°	59.8	71.1	87.2	90.3	85.5	63.8	61.1	56.9	77.4	94.5	119.3
100°	110.5	124.9	136.4	113.4	89.4	88.4	82.6	80.7	102.8	119.1	143.2
102.5°	172.8	177.2	137.2	124.1	118.6	114.5	105.7	104.5	126.6	149.1	169.3
105°	187.4	168.1	169.1	169.1	165.3	157.6	141.2	140.3	165.3	191.2	216.2
107.5°	220.4	223.3	228.3	227.1	222.7	202.2	182.9	178.5	201.0	232.1	259.6
110°	264.2	267.1	269.0	267.1	260.4	234.4	211.4	204.7	224.8	257.5	287.3



TEST NUMBER: P1435970

CATALOG NUMBER: SQ2W-FB-K-075U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	306.5	308.6	312.8	307.1	295.7	266.0	239.8	230.0	250.2	283.6	314.2
115°	373.8	373.8	374.7	371.8	348.8	318.0	283.4	269.0	286.3	317.1	350.7
117.5°	439.9	441.0	437.2	429.5	402.8	367.0	328.2	305.2	318.8	351.3	385.9
120°	481.4	483.3	479.4	467.9	442.0	401.6	357.4	330.5	341.1	372.8	407.4
122.5°	524.4	524.0	519.4	506.3	475.8	433.9	390.5	357.4	361.8	391.2	425.1
125°	584.2	583.2	579.4	564.0	532.3	489.1	438.1	397.8	392.0	417.0	451.6
127.5°	641.0	638.9	633.0	614.3	581.9	540.2	484.2	438.5	425.6	441.4	473.1
130°	680.3	677.4	666.8	646.6	614.9	575.5	518.8	467.0	448.7	458.3	486.2
132.5°	717.9	709.7	700.6	678.9	649.5	608.6	551.1	496.9	471.8	476.0	497.7
135°	765.8	758.1	746.5	725.4	697.5	657.2	599.5	540.9	506.3	502.5	515.0
137.5°	807.8	799.8	786.7	768.5	740.4	704.5	649.1	587.2	543.6	530.7	535.6
140°	834.0	824.4	812.8	794.6	769.6	732.1	678.3	618.8	569.8	551.5	548.6
142.5°	855.5	848.2	835.9	819.2	797.3	759.8	707.5	648.7	596.7	573.0	566.3
145°	887.8	882.0	868.6	853.2	834.9	797.5	749.4	690.8	638.9	608.2	593.8
147.5°	915.1	910.5	899.9	881.8	866.5	830.5	786.7	734.8	681.6	643.5	624.9
150°	932.0	928.1	917.6	900.3	884.9	851.3	809.0	761.0	710.0	669.7	645.7
152.5°	948.1	944.3	932.2	914.9	901.8	870.5	832.1	786.3	734.6	694.3	669.5
155°	969.5	964.6	953.1	936.8	925.3	896.4	860.9	820.5	776.3	734.1	706.2
157.5°	986.4	980.4	969.6	955.6	943.3	916.8	885.9	851.1	812.5	772.1	743.7
160°	996.4	989.6	978.1	965.6	954.1	929.1	901.2	869.5	834.0	797.5	766.7
162.5°	1003.3	997.3	983.5	972.5	962.5	939.9	913.5	884.9	853.2	821.3	792.9
165°	1010.8	1004.0	989.6	981.0	972.3	953.1	930.1	907.0	880.1	854.2	831.1
167.5°	1011.3	1005.8	991.4	982.9	976.6	960.0	941.4	923.7	902.8	882.4	863.2
170°	1009.8	1005.0	990.6	982.9	978.1	964.6	948.3	932.9	916.6	899.3	883.9
172.5°	1004.4	999.6	986.0	979.8	977.3	965.4	952.2	940.6	926.6	913.9	901.6
175°	990.6	986.7	975.2	971.4	972.3	964.6	955.0	948.3	939.7	932.0	925.3
177.5°	970.4	968.1	959.7	959.7	962.7	958.1	955.0	952.0	948.1	945.8	943.5
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1435970

CATALOG NUMBER: SQ2W-FB-K-075U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	388.0	388.0	388.0	388.0	388.0	388.0	388.0	388.0	388.0	388.0	388.0
2.5°	415.4	424.0	433.3	441.2	445.2	449.2	445.2	441.2	433.3	424.0	415.4
5°	502.4	547.6	598.2	641.5	663.1	684.6	663.1	641.5	598.2	547.6	502.4
7.5°	696.6	827.4	963.1	1075.6	1118.7	1161.8	1118.7	1075.6	963.1	827.4	696.6
10°	890.5	1058.8	1176.5	1270.6	1293.8	1317.0	1293.8	1270.6	1176.5	1058.8	890.5
12.5°	1017.0	1191.9	1274.5	1342.4	1366.3	1390.1	1366.3	1342.4	1274.5	1191.9	1017.0
15°	1129.6	1309.6	1376.7	1433.7	1460.2	1486.8	1460.2	1433.7	1376.7	1309.6	1129.6
17.5°	1192.0	1367.4	1433.9	1487.4	1501.8	1516.3	1501.8	1487.4	1433.9	1367.4	1192.0
20°	1228.3	1394.1	1451.3	1496.5	1505.6	1514.8	1505.6	1496.5	1451.3	1394.1	1228.3
22.5°	1254.7	1409.5	1452.8	1487.7	1497.5	1507.3	1497.5	1487.7	1452.8	1409.5	1254.7
25°	1280.7	1422.1	1449.5	1471.6	1478.3	1484.9	1478.3	1471.6	1449.5	1422.1	1280.7
27.5°	1276.5	1408.4	1426.3	1441.4	1447.9	1454.3	1447.9	1441.4	1426.3	1408.4	1276.5
30°	1265.4	1392.7	1405.9	1418.2	1427.3	1436.4	1427.3	1418.2	1405.9	1392.7	1265.4
32.5°	1248.3	1372.9	1385.5	1399.9	1419.7	1439.4	1419.7	1399.9	1385.5	1372.9	1248.3
35°	1216.5	1343.8	1363.7	1387.7	1424.2	1460.7	1424.2	1387.7	1363.7	1343.8	1216.5
37.5°	1172.6	1311.3	1353.0	1393.0	1428.1	1463.3	1428.1	1393.0	1353.0	1311.3	1172.6
40°	1140.6	1287.0	1342.5	1391.6	1421.5	1451.3	1421.5	1391.6	1342.5	1287.0	1140.6
42.5°	1103.8	1255.8	1320.6	1376.7	1406.6	1436.4	1406.6	1376.7	1320.6	1255.8	1103.8
45°	1045.5	1205.9	1282.2	1346.5	1374.6	1402.8	1374.6	1346.5	1282.2	1205.9	1045.5
47.5°	988.4	1156.8	1237.7	1303.5	1324.1	1344.6	1324.1	1303.5	1237.7	1156.8	988.4
50°	950.1	1121.8	1201.4	1265.2	1281.8	1298.4	1281.8	1265.2	1201.4	1121.8	950.1
52.5°	912.2	1085.1	1160.1	1220.1	1235.4	1250.6	1235.4	1220.1	1160.1	1085.1	912.2
55°	852.1	1023.3	1088.8	1141.3	1154.5	1167.8	1154.5	1141.3	1088.8	1023.3	852.1
57.5°	788.2	953.6	1009.5	1054.1	1064.9	1075.6	1064.9	1054.1	1009.5	953.6	788.2
60°	741.4	900.2	950.8	991.4	1002.2	1012.9	1002.2	991.4	950.8	900.2	741.4
62.5°	690.7	841.5	888.1	925.6	935.7	945.8	935.7	925.6	888.1	841.5	690.7
65°	613.3	748.9	787.8	818.7	825.4	832.0	825.4	818.7	787.8	748.9	613.3
67.5°	533.8	647.1	671.3	686.4	673.9	661.5	673.9	686.4	671.3	647.1	533.8
70°	480.9	575.0	583.3	580.6	544.9	509.3	544.9	580.6	583.3	575.0	480.9
72.5°	423.0	491.6	473.3	442.8	375.3	307.8	375.3	442.8	473.3	491.6	423.0
75°	330.0	348.2	268.6	209.3	211.0	212.7	211.0	209.3	268.6	348.2	330.0
77.5°	220.3	234.1	192.0	160.8	162.3	163.8	162.3	160.8	192.0	234.1	220.3
80°	122.3	133.5	131.8	130.8	131.6	132.4	131.6	130.8	131.8	133.5	122.3
82.5°	85.8	93.4	95.0	96.0	94.8	93.6	94.8	96.0	95.0	93.4	85.8
85°	44.6	43.3	36.7	31.3	29.6	28.0	29.6	31.3	36.7	43.3	44.6
87.5°	13.2	13.2	14.6	15.3	16.1	15.7	16.1	15.3	14.6	13.2	13.2
90°	22.1	28.8	35.5	39.4	43.2	41.3	43.2	39.4	35.5	28.8	22.1
92.5°	44.4	55.7	64.0	70.9	74.0	73.6	74.0	70.9	64.0	55.7	44.4
95°	89.4	102.8	116.3	125.9	131.6	129.7	131.6	125.9	116.3	102.8	89.4
97.5°	137.8	155.8	170.8	179.9	185.6	189.5	185.6	179.9	170.8	155.8	137.8
100°	170.1	187.4	204.7	215.2	224.8	228.7	224.8	215.2	204.7	187.4	170.1
102.5°	196.2	218.9	237.7	249.0	257.1	261.0	257.1	249.0	237.7	218.9	196.2
105°	239.2	263.3	283.4	297.8	306.5	309.4	306.5	297.8	283.4	263.3	239.2
107.5°	282.3	307.1	325.7	341.7	352.2	358.4	352.2	341.7	325.7	307.1	282.3
110°	316.1	336.3	356.5	370.9	381.4	385.3	381.4	370.9	356.5	336.3	316.1



TEST NUMBER: P1435970

CATALOG NUMBER: SQ2W-FB-K-075U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	344.5	367.0	387.2	401.6	413.7	419.1	413.7	401.6	387.2	367.0	344.5
115°	384.3	414.1	432.4	445.8	454.5	459.3	454.5	445.8	432.4	414.1	384.3
117.5°	417.4	448.5	468.5	478.9	482.9	486.4	482.9	478.9	468.5	448.5	417.4
120°	438.1	467.0	490.0	503.5	508.3	510.2	508.3	490.0	467.0	438.1	
122.5°	457.3	484.6	506.9	523.4	531.3	533.2	531.3	523.4	506.9	484.6	457.3
125°	484.2	510.2	533.2	549.6	558.2	563.0	558.2	549.6	533.2	510.2	484.2
127.5°	507.7	535.7	556.9	571.7	580.1	584.0	580.1	571.7	556.9	535.7	507.7
130°	520.8	549.6	570.7	587.1	594.7	598.6	594.7	587.1	570.7	549.6	520.8
132.5°	530.7	561.1	583.0	597.8	606.3	610.1	606.3	597.8	583.0	561.1	530.7
135°	542.9	574.6	597.6	612.0	619.7	623.6	619.7	612.0	597.6	574.6	542.9
137.5°	553.4	582.2	606.3	621.4	628.4	630.9	628.4	621.4	606.3	582.2	553.4
140°	561.1	586.1	610.1	624.5	632.2	633.2	632.2	624.5	610.1	586.1	561.1
142.5°	571.1	590.7	611.6	626.1	633.7	635.5	633.7	626.1	611.6	590.7	571.1
145°	589.0	600.5	614.9	628.4	635.1	637.0	635.1	628.4	614.9	600.5	589.0
147.5°	611.5	615.1	622.6	631.4	638.0	639.3	638.0	631.4	622.6	615.1	611.5
150°	628.4	627.4	630.3	636.1	641.8	640.9	641.8	636.1	630.3	627.4	628.4
152.5°	647.6	642.0	641.8	644.5	647.2	647.0	647.2	644.5	641.8	642.0	647.6
155°	680.3	669.7	663.9	662.0	662.0	661.0	662.0	662.0	663.9	669.7	680.3
157.5°	716.2	701.4	692.7	688.1	686.8	684.7	686.8	688.1	692.7	701.4	716.2
160°	740.8	724.4	715.8	708.1	705.2	702.3	705.2	708.1	715.8	724.4	740.8
162.5°	763.8	748.3	738.9	731.9	729.1	724.6	729.1	731.9	738.9	748.3	763.8
165°	801.3	785.0	774.4	768.6	764.8	761.0	764.8	768.6	774.4	785.0	801.3
167.5°	838.8	820.9	814.0	807.5	803.8	796.9	803.8	807.5	814.0	820.9	838.8
170°	861.8	845.5	841.7	835.9	829.2	821.5	829.2	835.9	841.7	845.5	861.8
172.5°	881.8	870.9	867.0	861.3	859.2	853.0	859.2	861.3	867.0	870.9	881.8
175°	910.8	902.2	902.2	901.2	898.4	892.6	898.4	901.2	902.2	902.2	910.8
177.5°	935.1	930.4	933.5	933.5	932.8	927.4	932.8	933.5	933.5	930.4	935.1
180°	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2	951.2



TEST NUMBER: P1435970

CATALOG NUMBER: SQ2W-FB-K-075U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	388.0	388.0	388.0	388.0
2.5°	407.4	399.6	392.3	385.0
5°	462.6	426.6	401.7	376.8
7.5°	570.6	463.4	412.8	362.3
10°	671.6	489.8	419.3	348.8
12.5°	749.7	525.3	429.6	333.9
15°	837.0	583.3	446.5	309.7
17.5°	907.6	648.8	466.7	284.7
20°	953.9	694.6	480.7	266.8
22.5°	988.2	728.6	489.5	250.3
25°	1025.4	766.5	497.0	227.6
27.5°	1030.6	775.0	490.3	205.6
30°	1024.1	770.9	481.5	192.1
32.5°	1011.7	761.6	470.9	180.2
35°	981.9	734.4	448.3	162.3
37.5°	936.8	691.9	419.4	147.0
40°	903.5	660.4	399.2	138.0
42.5°	864.7	623.6	376.3	129.1
45°	800.9	561.9	339.7	117.5
47.5°	732.8	492.7	299.7	106.7
50°	686.5	445.6	273.2	100.7
52.5°	641.2	399.9	247.3	94.8
55°	575.2	336.4	212.0	87.7
57.5°	513.3	282.0	181.7	81.3
60°	474.5	252.5	165.4	78.3
62.5°	435.6	225.4	149.7	73.9
65°	381.2	191.7	130.4	69.0
67.5°	331.3	166.4	114.4	62.3
70°	301.0	154.0	105.9	57.8
72.5°	267.6	140.4	97.6	54.8
75°	213.9	118.1	83.3	48.5
77.5°	150.5	91.6	65.6	39.5
80°	98.2	75.0	54.3	33.6
82.5°	72.4	58.5	43.0	27.6
85°	40.4	35.0	25.9	16.8
87.5°	14.9	14.7	10.6	6.5
90°	17.3	10.6	6.7	2.9
92.5°	37.3	25.9	18.3	10.6
95°	74.9	59.6	42.3	29.8
97.5°	119.3	94.5	77.4	56.9
100°	143.2	119.1	102.8	80.7
102.5°	169.3	149.1	126.6	104.5
105°	216.2	191.2	165.3	140.3
107.5°	259.6	232.1	201.0	178.5
110°	287.3	257.5	224.8	204.7



TEST NUMBER: P1435970

CATALOG NUMBER: SQ2W-FB-K-075U-100D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	314.2	283.6	250.2	230.0
115°	350.7	317.1	286.3	269.0
117.5°	385.9	351.3	318.8	305.2
120°	407.4	372.8	341.1	330.5
122.5°	425.1	391.2	361.8	357.4
125°	451.6	417.0	392.0	397.8
127.5°	473.1	441.4	425.6	438.5
130°	486.2	458.3	448.7	467.0
132.5°	497.7	476.0	471.8	496.9
135°	515.0	502.5	506.3	540.9
137.5°	535.6	530.7	543.6	587.2
140°	548.6	551.5	569.8	618.8
142.5°	566.3	573.0	596.7	648.7
145°	593.8	608.2	638.9	690.8
147.5°	624.9	643.5	681.6	734.8
150°	645.7	669.7	710.0	761.0
152.5°	669.5	694.3	734.6	786.3
155°	706.2	734.1	776.3	820.5
157.5°	743.7	772.1	812.5	851.1
160°	766.7	797.5	834.0	869.5
162.5°	792.9	821.3	853.2	884.9
165°	831.1	854.2	880.1	907.0
167.5°	863.2	882.4	902.8	923.7
170°	883.9	899.3	916.6	932.9
172.5°	901.6	913.9	926.6	940.6
175°	925.3	932.0	939.7	948.3
177.5°	943.5	945.8	948.1	952.0
180°	951.2	951.2	951.2	951.2



TEST NUMBER: P1435970
 CATALOG NUMBER: SQ2W-FB-K-075U-100D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.25	14.22	14.13	15.13	16.28	22.85	23.82	23.73	24.72	25.87
	3H	14.20	15.07	15.09	15.98	17.16	24.46	25.33	25.35	26.25	27.42
	4H	14.60	15.43	15.51	16.34	17.53	24.64	25.47	25.55	26.39	27.57
	6H	14.86	15.62	15.78	16.55	17.75	24.73	25.48	25.64	26.41	27.61
	8H	14.96	15.68	15.88	16.62	17.82	24.75	25.47	25.67	26.41	27.61
	12H	15.01	15.70	15.94	16.64	17.86	24.73	25.42	25.66	26.35	27.58
4H	2H	17.98	18.81	18.90	19.73	20.91	23.23	24.05	24.14	24.97	26.15
	3H	19.12	19.81	20.05	20.76	21.96	25.12	25.81	26.05	26.76	27.96
	4H	19.41	20.04	20.35	20.98	22.21	25.35	25.98	26.29	26.92	28.15
	6H	19.55	20.09	20.50	21.06	22.29	25.49	26.03	26.44	27.00	28.22
	8H	19.59	20.10	20.55	21.06	22.30	25.54	26.04	26.49	27.01	28.24
	12H	19.60	20.06	20.57	21.04	22.28	25.52	25.98	26.50	26.96	28.21
8H	4H	20.61	21.12	21.56	22.08	23.32	25.45	25.96	26.40	26.92	28.16
	6H	20.88	21.29	21.85	22.30	23.54	25.65	26.07	26.63	27.08	28.31
	8H	20.98	21.34	21.96	22.34	23.59	25.75	26.11	26.73	27.11	28.36
	12H	21.02	21.35	22.01	22.33	23.64	25.76	26.08	26.75	27.07	28.37
12H	4H	20.64	21.10	21.61	22.08	23.32	25.41	25.86	26.38	26.84	28.09
	6H	20.98	21.35	21.97	22.35	23.60	25.64	26.01	26.63	27.00	28.26
	8H	21.13	21.45	22.12	22.44	23.74	25.74	26.07	26.74	27.05	28.36