

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428287

Luminaire Tested: SQ2W-PR1-K-125U-100D-L830-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428287
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-9)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PR1-K-125U-100D-L830-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE RIPPLE LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10725.8 lumens
Efficiency: N/A
Efficacy: 131.4 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 81.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428287

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L830-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428287

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L830-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48				48
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	49	48	47	42				42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36				36
3	82	73	66	61	75	68	62	57	58	53	49	48	45	42	39	37	35	31				31
4	75	65	57	52	69	60	54	49	51	46	42	43	40	37	36	33	31	27				27
5	69	58	50	45	64	54	47	42	46	41	37	39	35	32	32	29	27	24				24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	29	26	24	21				21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19				19
8	55	43	35	30	51	40	33	29	35	29	26	30	25	22	25	22	19	17				17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	15				15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14				14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	34734	34734	34734	34734
5°	34688	35329	34688	35329
10°	35053	36493	35053	36493
15°	35043	35520	35043	35520
20°	34477	36171	34477	36171
25°	34379	37660	34379	37660
30°	34343	38021	34343	38021
35°	34018	35399	34018	35399
40°	33231	31153	33231	31153
45°	31446	24635	31446	24635
50°	28587	19115	28587	19115
55°	25123	14877	25123	14877
60°	21738	12251	21738	12251
65°	18766	10724	18766	10724
70°	16876	9526	16876	9526
75°	15458	8752	15458	8752
80°	13454	8563	13454	8563
85°	9744	4057	9744	4057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 33759 cd/sqm



TEST NUMBER: P1428287

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L830-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.8	1.9
10°-20°	601.4	5.6
20°-30°	929.7	8.7
30°-40°	1118.0	10.4
40°-50°	1004.0	9.4
50°-60°	672.7	6.3
60°-70°	391.3	3.6
70°-80°	201.0	1.9
80°-90°	57.4	0.5
90°-100°	151.1	1.4
100°-110°	440.5	4.1
110°-120°	719.0	6.7
120°-130°	912.3	8.5
130°-140°	976.2	9.1
140°-150°	911.5	8.5
150°-160°	750.1	7.0
160°-170°	503.1	4.7
170°-180°	178.6	1.7
0°-30°	1738.9	16.2
0°-40°	2856.9	26.6
0°-60°	4533.7	42.3
0°-90°	5183.4	48.3
90°-120°	1310.6	12.2
90°-150°	4110.6	38.3
90°-180°	5542.0	51.7
0°-180°	10725.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2151	2151	2151	2151	2151	
5°	2140	2180	2140	2180	2140	204
15°	2096	2125	2096	2125	2096	589
25°	1930	2114	1930	2114	1930	890
35°	1726	1796	1726	1796	1726	1076
45°	1377	1079	1377	1079	1377	1053
55°	892	528	892	528	892	802
65°	491	281	491	281	491	497
75°	248	140	248	140	248	263
85°	53	22	53	22	53	65
90°	6	42	6	82	6	7
95°	59	44	59	259	59	72
105°	280	449	280	617	280	298
115°	537	744	537	916	537	529
125°	794	1179	794	1124	794	710
135°	1080	1544	1080	1244	1080	834
145°	1379	1779	1379	1271	1379	863
155°	1637	1933	1637	1319	1637	753
165°	1810	2015	1810	1519	1810	510
175°	1892	1973	1892	1781	1892	180
180°	1898	1898	1898	1898	1898	



TEST NUMBER: P1428287

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2151.3	2151.3	2151.3	2151.3	2151.3	2151.3	2151.3	2151.3	2151.3	2151.3	2151.3
2.5°	2142.5	2154.2	2165.9	2160.6	2149.7	2144.7	2145.4	2146.6	2149.0	2151.3	2149.0
5°	2140.3	2156.9	2173.5	2169.6	2158.8	2154.5	2156.4	2160.3	2170.1	2179.8	2170.1
7.5°	2139.9	2163.5	2187.1	2188.9	2183.4	2183.5	2189.2	2196.6	2209.5	2222.3	2209.5
10°	2138.1	2166.4	2194.7	2198.8	2194.9	2193.4	2194.4	2198.6	2212.2	2225.9	2212.2
12.5°	2127.6	2160.5	2193.5	2190.0	2174.4	2166.0	2164.6	2165.4	2172.8	2180.2	2172.8
15°	2096.5	2135.5	2174.4	2158.6	2124.5	2108.9	2111.8	2115.2	2120.1	2125.0	2120.1
17.5°	2041.6	2082.4	2123.1	2108.9	2076.3	2065.3	2075.9	2086.1	2095.7	2105.2	2095.7
20°	2006.6	2046.5	2086.5	2076.7	2050.4	2044.1	2057.7	2072.1	2088.7	2105.2	2088.7
22.5°	1975.0	2014.9	2054.9	2048.7	2027.0	2025.8	2044.9	2064.9	2087.7	2110.5	2087.7
25°	1929.8	1964.9	2000.0	2000.7	1990.0	2000.7	2032.9	2063.3	2088.7	2114.0	2088.7
27.5°	1882.4	1903.1	1923.8	1937.4	1948.7	1976.1	2019.6	2056.6	2074.3	2092.1	2074.3
30°	1842.1	1855.7	1869.4	1894.7	1924.0	1957.6	1995.6	2025.8	2032.6	2039.4	2032.6
32.5°	1798.2	1806.4	1814.6	1850.3	1895.1	1927.6	1947.6	1960.5	1951.7	1943.0	1951.7
35°	1725.9	1732.7	1739.5	1785.1	1843.5	1865.0	1849.4	1833.1	1814.5	1796.0	1814.5
37.5°	1639.9	1653.9	1668.0	1705.1	1749.9	1749.5	1703.9	1664.4	1643.2	1621.9	1643.2
40°	1576.7	1600.1	1623.5	1648.4	1673.7	1652.3	1584.0	1526.8	1502.4	1478.1	1502.4
42.5°	1499.5	1537.0	1574.4	1580.0	1574.9	1528.9	1441.9	1369.3	1339.5	1309.6	1339.5
45°	1377.2	1427.9	1478.5	1449.5	1394.0	1318.9	1224.4	1145.2	1112.1	1078.9	1112.1
47.5°	1232.9	1284.9	1337.0	1282.3	1192.0	1104.7	1020.3	949.3	918.3	887.3	918.3
50°	1138.1	1180.1	1222.0	1160.1	1063.6	975.9	896.9	829.2	795.1	761.0	795.1
52.5°	1041.7	1071.9	1102.1	1040.8	949.0	863.6	784.6	717.7	686.7	655.7	686.7
55°	892.5	908.1	923.7	866.9	786.1	708.1	633.0	571.4	549.9	528.5	549.9
57.5°	755.7	765.6	775.6	721.8	646.7	577.3	513.6	461.8	446.0	430.3	446.0
60°	673.2	680.1	686.9	632.3	557.3	494.9	445.2	404.7	392.1	379.4	392.1
62.5°	597.8	603.1	608.3	555.7	483.8	428.0	388.4	356.4	346.8	337.3	346.8
65°	491.2	496.1	501.0	456.1	394.7	348.9	318.7	294.3	287.5	280.7	287.5
67.5°	406.6	409.1	411.6	374.7	324.6	287.7	263.9	244.4	238.0	231.6	238.0
70°	357.5	358.4	359.4	326.8	282.9	250.2	228.8	211.5	206.6	201.8	206.6
72.5°	313.6	312.2	310.9	281.7	243.3	215.3	197.8	183.8	180.5	177.2	180.5
75°	247.8	244.9	242.0	217.8	186.6	165.2	153.5	144.2	142.3	140.3	142.3
77.5°	185.1	182.0	178.8	158.8	133.0	118.2	114.3	111.4	111.4	111.4	111.4
80°	144.7	140.8	136.9	121.3	101.9	92.1	92.1	92.1	92.1	92.1	92.1
82.5°	107.9	102.4	97.0	87.4	76.5	71.1	71.1	70.9	70.1	69.3	70.1
85°	52.6	47.8	42.9	41.7	41.7	38.7	32.9	27.8	24.9	21.9	24.9
87.5°	15.2	16.7	18.6	17.2	14.5	12.9	12.9	13.3	13.7	13.7	13.7
90°	5.8	13.4	23.0	30.7	36.4	38.3	38.3	40.3	42.2	42.2	42.2
92.5°	21.1	33.4	33.7	33.7	41.0	44.5	47.6	47.9	49.9	49.9	49.9
95°	59.4	65.2	97.8	95.9	65.2	51.8	44.1	44.1	44.1	44.1	44.1
97.5°	113.5	121.9	127.3	170.6	180.2	174.1	141.9	119.3	106.6	100.9	106.6
100°	161.1	164.9	176.4	178.3	226.2	272.3	249.3	220.5	210.9	205.2	210.9
102.5°	208.6	210.9	228.5	236.6	247.7	273.8	353.6	344.7	338.2	337.1	338.2
105°	279.9	281.9	314.4	329.8	337.5	337.5	335.5	373.9	435.2	448.7	435.2
107.5°	356.2	365.1	403.4	444.4	453.3	455.6	445.6	439.8	437.5	439.1	437.5
110°	408.4	421.8	467.8	519.6	533.0	536.9	533.0	527.3	523.4	523.4	523.4



TEST NUMBER: P1428287

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	459.0	478.6	530.7	590.2	612.8	624.3	615.9	611.6	607.8	610.9	607.8
115°	536.9	565.6	634.6	696.0	742.0	747.8	745.9	745.9	743.9	743.9	743.9
117.5°	609.0	655.0	732.4	803.8	857.1	872.4	880.1	877.8	875.5	879.3	875.5
120°	659.6	713.3	801.5	882.0	933.8	956.8	964.4	960.6	964.4	960.6	964.4
122.5°	713.3	779.2	865.9	949.5	1010.5	1036.5	1045.7	1046.5	1047.3	1045.0	1047.3
125°	793.8	874.3	975.9	1062.2	1125.5	1156.2	1163.8	1165.8	1169.6	1179.2	1169.6
127.5°	875.1	966.4	1077.9	1161.2	1226.0	1263.2	1275.0	1279.3	1287.3	1291.5	1287.3
130°	931.8	1035.4	1148.5	1227.1	1290.4	1330.7	1351.7	1357.5	1367.1	1365.2	1367.1
132.5°	991.7	1099.8	1214.5	1296.1	1354.8	1398.1	1416.2	1432.7	1436.1	1438.8	1436.1
135°	1079.5	1196.4	1311.5	1392.0	1447.6	1489.8	1512.8	1528.1	1537.7	1543.5	1537.7
137.5°	1171.9	1295.4	1405.8	1477.5	1533.5	1569.9	1596.0	1612.1	1622.1	1626.7	1622.1
140°	1234.8	1353.7	1461.0	1535.8	1585.7	1622.1	1645.1	1664.3	1675.8	1675.8	1675.8
142.5°	1294.6	1411.9	1516.3	1591.0	1634.7	1668.1	1692.6	1707.2	1720.3	1720.3	1720.3
145°	1378.6	1495.5	1591.4	1666.2	1702.6	1733.3	1760.1	1771.6	1779.3	1779.3	1779.3
147.5°	1466.4	1569.9	1657.4	1729.1	1759.8	1795.8	1816.9	1826.1	1835.7	1831.5	1835.7
150°	1518.6	1614.4	1698.8	1765.9	1796.6	1831.1	1852.2	1859.8	1869.4	1863.7	1869.4
152.5°	1569.2	1660.4	1737.1	1799.6	1825.7	1860.2	1884.4	1892.1	1898.6	1894.4	1898.6
155°	1637.4	1718.0	1788.9	1846.4	1869.4	1902.0	1925.0	1934.6	1942.3	1932.7	1942.3
157.5°	1698.4	1767.8	1829.5	1882.5	1907.0	1935.0	1956.5	1968.4	1976.0	1971.8	1976.0
160°	1735.2	1798.5	1854.1	1903.9	1927.0	1951.9	1974.9	1988.3	1996.0	1990.2	1996.0
162.5°	1765.9	1823.0	1875.6	1920.8	1940.8	1962.6	1990.2	2002.1	2009.8	2002.5	2009.8
165°	1810.0	1856.0	1902.0	1940.4	1957.6	1974.9	2003.6	2017.1	2022.8	2015.1	2022.8
167.5°	1843.4	1878.6	1915.8	1948.8	1961.5	1978.3	2007.1	2018.2	2025.5	2015.9	2025.5
170°	1861.8	1892.4	1925.0	1951.9	1961.5	1976.8	2005.6	2015.1	2020.9	2011.3	2020.9
172.5°	1877.1	1900.1	1926.6	1950.3	1955.3	1967.6	1994.8	2004.4	2008.6	2000.6	2008.6
175°	1892.4	1905.9	1925.0	1940.4	1938.5	1946.1	1969.1	1976.8	1984.5	1973.0	1984.5
177.5°	1899.7	1905.9	1912.0	1921.2	1915.1	1915.1	1931.9	1936.5	1938.1	1931.9	1938.1
180°	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2



TEST NUMBER: P1428287

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2151.3	2151.3	2151.3	2151.3	2151.3	2151.3	2151.3	2151.3	2151.3	2151.3	2151.3
2.5°	2146.6	2145.4	2144.7	2149.7	2160.6	2165.9	2154.2	2142.5	2154.2	2165.9	2160.6
5°	2160.3	2156.4	2154.5	2158.8	2169.6	2173.5	2156.9	2140.3	2156.9	2173.5	2169.6
7.5°	2196.6	2189.2	2183.5	2183.4	2188.9	2187.1	2163.5	2139.9	2163.5	2187.1	2188.9
10°	2198.6	2194.4	2193.4	2194.9	2198.8	2194.7	2166.4	2138.1	2166.4	2194.7	2198.8
12.5°	2165.4	2164.6	2166.0	2174.4	2190.0	2193.5	2160.5	2127.6	2160.5	2193.5	2190.0
15°	2115.2	2111.8	2108.9	2124.5	2158.6	2174.4	2135.5	2096.5	2135.5	2174.4	2158.6
17.5°	2086.1	2075.9	2065.3	2076.3	2108.9	2123.1	2082.4	2041.6	2082.4	2123.1	2108.9
20°	2072.1	2057.7	2044.1	2050.4	2076.7	2086.5	2046.5	2006.6	2046.5	2086.5	2076.7
22.5°	2064.9	2044.9	2025.8	2027.0	2048.7	2054.9	2014.9	1975.0	2014.9	2054.9	2048.7
25°	2063.3	2032.9	2000.7	1990.0	2000.7	2000.0	1964.9	1929.8	1964.9	2000.0	2000.7
27.5°	2056.6	2019.6	1976.1	1948.7	1937.4	1923.8	1903.1	1882.4	1903.1	1923.8	1937.4
30°	2025.8	1995.6	1957.6	1924.0	1894.7	1869.4	1855.7	1842.1	1855.7	1869.4	1894.7
32.5°	1960.5	1947.6	1927.6	1895.1	1850.3	1814.6	1806.4	1798.2	1806.4	1814.6	1850.3
35°	1833.1	1849.4	1865.0	1843.5	1785.1	1739.5	1732.7	1725.9	1732.7	1739.5	1785.1
37.5°	1664.4	1703.9	1749.5	1749.9	1705.1	1668.0	1653.9	1639.9	1653.9	1668.0	1705.1
40°	1526.8	1584.0	1652.3	1673.7	1648.4	1623.5	1600.1	1576.7	1600.1	1623.5	1648.4
42.5°	1369.3	1441.9	1528.9	1574.9	1580.0	1574.4	1537.0	1499.5	1537.0	1574.4	1580.0
45°	1145.2	1224.4	1318.9	1394.0	1449.5	1478.5	1427.9	1377.2	1427.9	1478.5	1449.5
47.5°	949.3	1020.3	1104.7	1192.0	1282.3	1337.0	1284.9	1232.9	1284.9	1337.0	1282.3
50°	829.2	896.9	975.9	1063.6	1160.1	1222.0	1180.1	1138.1	1180.1	1222.0	1160.1
52.5°	717.7	784.6	863.6	949.0	1040.8	1102.1	1071.9	1041.7	1071.9	1102.1	1040.8
55°	571.4	633.0	708.1	786.1	866.9	923.7	908.1	892.5	908.1	923.7	866.9
57.5°	461.8	513.6	577.3	646.7	721.8	775.6	765.6	755.7	765.6	775.6	721.8
60°	404.7	445.2	494.9	557.3	632.3	686.9	680.1	673.2	680.1	686.9	632.3
62.5°	356.4	388.4	428.0	483.8	555.7	608.3	603.1	597.8	603.1	608.3	555.7
65°	294.3	318.7	348.9	394.7	456.1	501.0	496.1	491.2	496.1	501.0	456.1
67.5°	244.4	263.9	287.7	324.6	374.7	411.6	409.1	406.6	409.1	411.6	374.7
70°	211.5	228.8	250.2	282.9	326.8	359.4	358.4	357.5	358.4	359.4	326.8
72.5°	183.8	197.8	215.3	243.3	281.7	310.9	312.2	313.6	312.2	310.9	281.7
75°	144.2	153.5	165.2	186.6	217.8	242.0	244.9	247.8	244.9	242.0	217.8
77.5°	111.4	114.3	118.2	133.0	158.8	178.8	182.0	185.1	182.0	178.8	158.8
80°	92.1	92.1	92.1	101.9	121.3	136.9	140.8	144.7	140.8	136.9	121.3
82.5°	70.9	71.1	71.1	76.5	87.4	97.0	102.4	107.9	102.4	97.0	87.4
85°	27.8	32.9	38.7	41.7	41.7	42.9	47.8	52.6	47.8	42.9	41.7
87.5°	13.3	12.9	12.9	14.5	17.2	18.6	16.7	15.2	16.7	18.3	18.0
90°	40.3	38.3	38.3	36.4	30.7	23.0	13.4	5.8	13.4	21.1	34.5
92.5°	47.9	47.6	44.5	41.0	33.7	33.7	33.4	21.1	36.4	51.8	74.4
95°	44.1	44.1	51.8	65.2	95.9	97.8	65.2	59.4	84.4	118.9	149.6
97.5°	119.3	141.9	174.1	180.2	170.6	127.3	121.9	113.5	154.5	188.7	238.1
100°	220.5	249.3	272.3	226.2	178.3	176.4	164.9	161.1	205.2	237.8	285.7
102.5°	344.7	353.6	273.8	247.7	236.6	228.5	210.9	208.6	252.7	297.6	337.8
105°	373.9	335.5	337.5	337.5	329.8	314.4	281.9	279.9	329.8	381.6	431.4
107.5°	439.8	445.6	455.6	453.3	444.4	403.4	365.1	356.2	401.1	463.2	518.1
110°	527.3	533.0	536.9	533.0	519.6	467.8	421.8	408.4	448.7	513.9	573.3



TEST NUMBER: P1428287

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	611.6	615.9	624.3	612.8	590.2	530.7	478.6	459.0	499.3	566.0	627.0
115°	745.9	745.9	747.8	742.0	696.0	634.6	565.6	536.9	571.4	632.7	699.8
117.5°	877.8	880.1	872.4	857.1	803.8	732.4	655.0	609.0	636.2	701.0	770.0
120°	960.6	964.4	956.8	933.8	882.0	801.5	713.3	659.6	680.7	743.9	813.0
122.5°	1046.5	1045.7	1036.5	1010.5	949.5	865.9	779.2	713.3	722.1	780.8	848.2
125°	1165.8	1163.8	1156.2	1125.5	1062.2	975.9	874.3	793.8	782.3	832.1	901.2
127.5°	1279.3	1275.0	1263.2	1226.0	1161.2	1077.9	966.4	875.1	849.4	880.8	944.1
130°	1357.5	1351.7	1330.7	1290.4	1227.1	1148.5	1035.4	931.8	895.4	914.6	970.2
132.5°	1432.7	1416.2	1398.1	1354.8	1296.1	1214.5	1099.8	991.7	941.4	949.9	993.2
135°	1528.1	1512.8	1489.8	1447.6	1392.0	1311.5	1196.4	1079.5	1010.5	1002.8	1027.7
137.5°	1612.1	1596.0	1569.9	1533.5	1477.5	1405.8	1295.4	1171.9	1084.8	1059.2	1068.7
140°	1664.3	1645.1	1622.1	1585.7	1535.8	1461.0	1353.7	1234.8	1137.0	1100.6	1094.8
142.5°	1707.2	1692.6	1668.1	1634.7	1591.0	1516.3	1411.9	1294.6	1190.7	1143.5	1130.1
145°	1771.6	1760.1	1733.3	1702.6	1666.2	1591.4	1495.5	1378.6	1275.0	1213.7	1184.9
147.5°	1826.1	1816.9	1795.8	1759.8	1729.1	1657.4	1569.9	1466.4	1360.2	1284.3	1247.1
150°	1859.8	1852.2	1831.1	1796.6	1765.9	1698.8	1614.4	1518.6	1416.9	1336.4	1288.5
152.5°	1892.1	1884.4	1860.2	1825.7	1799.6	1737.1	1660.4	1569.2	1466.0	1385.5	1336.0
155°	1934.6	1925.0	1902.0	1869.4	1846.4	1788.9	1718.0	1637.4	1549.2	1464.9	1409.3
157.5°	1968.4	1956.5	1935.0	1907.0	1882.5	1829.5	1767.8	1698.4	1621.3	1540.8	1484.0
160°	1988.3	1974.9	1951.9	1927.0	1903.9	1854.1	1798.5	1735.2	1664.3	1591.4	1530.1
162.5°	2002.1	1990.2	1962.6	1940.8	1920.8	1875.6	1823.0	1765.9	1702.6	1639.0	1582.2
165°	2017.1	2003.6	1974.9	1957.6	1940.4	1902.0	1856.0	1810.0	1756.3	1704.5	1658.5
167.5°	2018.2	2007.1	1978.3	1961.5	1948.8	1915.8	1878.6	1843.4	1801.6	1760.9	1722.6
170°	2015.1	2005.6	1976.8	1961.5	1951.9	1925.0	1892.4	1861.8	1829.2	1794.7	1764.0
172.5°	2004.4	1994.8	1967.6	1955.3	1950.3	1926.6	1900.1	1877.1	1849.1	1823.8	1799.3
175°	1976.8	1969.1	1946.1	1938.5	1940.4	1925.0	1905.9	1892.4	1875.2	1859.8	1846.4
177.5°	1936.5	1931.9	1915.1	1915.1	1921.2	1912.0	1905.9	1899.7	1892.1	1887.5	1882.9
180°	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2



TEST NUMBER: P1428287

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2151.3	2151.3	2151.3	2151.3	2151.3	2151.3	2151.3	2151.3	2151.3	2151.3	2151.3
2.5°	2149.7	2144.7	2145.4	2146.6	2149.0	2151.3	2149.0	2146.6	2145.4	2144.7	2149.7
5°	2158.8	2154.5	2156.4	2160.3	2170.1	2179.8	2170.1	2160.3	2156.4	2154.5	2158.8
7.5°	2183.4	2183.5	2189.2	2196.6	2209.5	2222.3	2209.5	2196.6	2189.2	2183.5	2183.4
10°	2194.9	2193.4	2194.4	2198.6	2212.2	2225.9	2212.2	2198.6	2194.4	2193.4	2194.9
12.5°	2174.4	2166.0	2164.6	2165.4	2172.8	2180.2	2172.8	2165.4	2164.6	2166.0	2174.4
15°	2124.5	2108.9	2111.8	2115.2	2120.1	2125.0	2120.1	2115.2	2111.8	2108.9	2124.5
17.5°	2076.3	2065.3	2075.9	2086.1	2095.7	2105.2	2095.7	2086.1	2075.9	2065.3	2076.3
20°	2050.4	2044.1	2057.7	2072.1	2088.7	2105.2	2088.7	2072.1	2057.7	2044.1	2050.4
22.5°	2027.0	2025.8	2044.9	2064.9	2087.7	2110.5	2087.7	2064.9	2044.9	2025.8	2027.0
25°	1990.0	2000.7	2032.9	2063.3	2088.7	2114.0	2088.7	2063.3	2032.9	2000.7	1990.0
27.5°	1948.7	1976.1	2019.6	2056.6	2074.3	2092.1	2074.3	2056.6	2019.6	1976.1	1948.7
30°	1924.0	1957.6	1995.6	2025.8	2032.6	2039.4	2032.6	2025.8	1995.6	1957.6	1924.0
32.5°	1895.1	1927.6	1947.6	1960.5	1951.7	1943.0	1951.7	1960.5	1947.6	1927.6	1895.1
35°	1843.5	1865.0	1849.4	1833.1	1814.5	1796.0	1814.5	1833.1	1849.4	1865.0	1843.5
37.5°	1749.9	1749.5	1703.9	1664.4	1643.2	1621.9	1643.2	1664.4	1703.9	1749.5	1749.9
40°	1673.7	1652.3	1584.0	1526.8	1502.4	1478.1	1502.4	1526.8	1584.0	1652.3	1673.7
42.5°	1574.9	1528.9	1441.9	1369.3	1339.5	1309.6	1339.5	1369.3	1441.9	1528.9	1574.9
45°	1394.0	1318.9	1224.4	1145.2	1112.1	1078.9	1112.1	1145.2	1224.4	1318.9	1394.0
47.5°	1192.0	1104.7	1020.3	949.3	918.3	887.3	918.3	949.3	1020.3	1104.7	1192.0
50°	1063.6	975.9	896.9	829.2	795.1	761.0	795.1	829.2	896.9	975.9	1063.6
52.5°	949.0	863.6	784.6	717.7	686.7	655.7	686.7	717.7	784.6	863.6	949.0
55°	786.1	708.1	633.0	571.4	549.9	528.5	549.9	571.4	633.0	708.1	786.1
57.5°	646.7	577.3	513.6	461.8	446.0	430.3	446.0	461.8	513.6	577.3	646.7
60°	557.3	494.9	445.2	404.7	392.1	379.4	392.1	404.7	445.2	494.9	557.3
62.5°	483.8	428.0	388.4	356.4	346.8	337.3	346.8	356.4	388.4	428.0	483.8
65°	394.7	348.9	318.7	294.3	287.5	280.7	287.5	294.3	318.7	348.9	394.7
67.5°	324.6	287.7	263.9	244.4	238.0	231.6	238.0	244.4	263.9	287.7	324.6
70°	282.9	250.2	228.8	211.5	206.6	201.8	206.6	211.5	228.8	250.2	282.9
72.5°	243.3	215.3	197.8	183.8	180.5	177.2	180.5	183.8	197.8	215.3	243.3
75°	186.6	165.2	153.5	144.2	142.3	140.3	142.3	144.2	153.5	165.2	186.6
77.5°	133.0	118.2	114.3	111.4	111.4	111.4	111.4	111.4	114.3	118.2	133.0
80°	101.9	92.1	92.1	92.1	92.1	92.1	92.1	92.1	92.1	92.1	101.9
82.5°	76.5	71.1	71.1	70.9	70.1	69.3	70.1	70.9	71.1	71.1	76.5
85°	41.7	38.7	32.9	27.8	24.9	21.9	24.9	27.8	32.9	38.7	41.7
87.5°	16.0	16.8	19.5	21.0	22.5	21.8	22.5	21.0	19.5	16.8	16.0
90°	44.1	57.5	70.9	78.6	86.3	82.4	86.3	78.6	70.9	57.5	44.1
92.5°	88.6	111.2	127.7	141.5	147.6	146.9	147.6	141.5	127.7	111.2	88.6
95°	178.3	205.2	232.0	251.2	262.7	258.8	262.7	251.2	232.0	205.2	178.3
97.5°	275.0	311.0	340.9	358.9	370.4	378.1	370.4	358.9	340.9	311.0	275.0
100°	339.4	373.9	408.4	429.5	448.7	456.3	448.7	429.5	408.4	373.9	339.4
102.5°	391.5	436.8	474.4	497.0	513.1	520.8	513.1	497.0	474.4	436.8	391.5
105°	477.4	525.4	565.6	594.4	611.6	617.4	611.6	594.4	565.6	525.4	477.4
107.5°	563.3	612.8	650.0	681.8	702.9	715.2	702.9	681.8	650.0	612.8	563.3
110°	630.8	671.1	711.3	740.1	761.2	768.9	761.2	740.1	711.3	671.1	630.8



TEST NUMBER: P1428287

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	687.6	732.4	772.7	801.5	825.6	836.4	825.6	801.5	772.7	732.4	687.6
115°	766.9	826.4	862.8	889.7	906.9	916.5	906.9	889.7	862.8	826.4	766.9
117.5°	832.9	895.0	934.9	955.6	963.7	970.6	963.7	955.6	934.9	895.0	832.9
120°	874.3	931.8	977.9	1004.7	1014.3	1018.1	1014.3	1004.7	977.9	931.8	874.3
122.5°	912.7	967.1	1011.6	1044.6	1060.3	1064.1	1060.3	1044.6	1011.6	967.1	912.7
125°	966.4	1018.1	1064.1	1096.7	1114.0	1123.6	1114.0	1096.7	1064.1	1018.1	966.4
127.5°	1013.1	1069.1	1111.3	1140.8	1157.7	1165.4	1157.7	1140.8	1111.3	1069.1	1013.1
130°	1039.2	1096.7	1138.9	1171.5	1186.8	1194.5	1186.8	1171.5	1138.9	1096.7	1039.2
132.5°	1059.2	1119.7	1163.5	1193.0	1209.9	1217.5	1209.9	1193.0	1163.5	1119.7	1059.2
135°	1083.3	1146.6	1192.6	1221.4	1236.7	1244.4	1236.7	1221.4	1192.6	1146.6	1083.3
137.5°	1104.4	1161.9	1209.9	1240.2	1254.0	1258.9	1254.0	1240.2	1209.9	1161.9	1104.4
140°	1119.7	1169.6	1217.5	1246.3	1261.6	1263.5	1261.6	1246.3	1217.5	1169.6	1119.7
142.5°	1139.7	1178.8	1220.6	1249.4	1264.7	1268.1	1264.7	1249.4	1220.6	1178.8	1139.7
145°	1175.3	1198.4	1227.1	1254.0	1267.4	1271.2	1267.4	1254.0	1227.1	1198.4	1175.3
147.5°	1220.2	1227.5	1242.5	1260.1	1273.1	1275.8	1273.1	1260.1	1242.5	1227.5	1220.2
150°	1254.0	1252.0	1257.8	1269.3	1280.8	1278.9	1280.8	1269.3	1257.8	1252.0	1254.0
152.5°	1292.3	1281.2	1280.8	1286.2	1291.5	1291.2	1291.5	1286.2	1280.8	1281.2	1292.3
155°	1357.5	1336.4	1324.9	1321.1	1321.1	1319.1	1321.1	1321.1	1324.9	1336.4	1357.5
157.5°	1429.2	1399.7	1382.4	1373.2	1370.5	1366.3	1370.5	1373.2	1382.4	1399.7	1429.2
160°	1478.3	1445.7	1428.4	1413.1	1407.3	1401.6	1407.3	1413.1	1428.4	1445.7	1478.3
162.5°	1524.3	1493.2	1474.5	1460.6	1454.9	1446.1	1454.9	1460.6	1474.5	1493.2	1524.3
165°	1599.1	1566.5	1545.4	1533.9	1526.2	1518.6	1526.2	1533.9	1545.4	1566.5	1599.1
167.5°	1673.9	1638.2	1624.4	1611.4	1604.1	1590.3	1604.1	1611.4	1624.4	1638.2	1673.9
170°	1719.9	1687.3	1679.6	1668.1	1654.7	1639.3	1654.7	1668.1	1679.6	1687.3	1719.9
172.5°	1759.8	1737.9	1730.2	1718.7	1714.5	1702.2	1714.5	1718.7	1730.2	1737.9	1759.8
175°	1817.7	1800.4	1800.4	1798.5	1792.7	1781.2	1792.7	1798.5	1800.4	1800.4	1817.7
177.5°	1866.0	1856.8	1862.9	1862.9	1861.4	1850.6	1861.4	1862.9	1862.9	1856.8	1866.0
180°	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2	1898.2



TEST NUMBER: P1428287

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2151.3	2151.3	2151.3	2151.3
2.5°	2160.6	2165.9	2154.2	2142.5
5°	2169.6	2173.5	2156.9	2140.3
7.5°	2188.9	2187.1	2163.5	2139.9
10°	2198.8	2194.7	2166.4	2138.1
12.5°	2190.0	2193.5	2160.5	2127.6
15°	2158.6	2174.4	2135.5	2096.5
17.5°	2108.9	2123.1	2082.4	2041.6
20°	2076.7	2086.5	2046.5	2006.6
22.5°	2048.7	2054.9	2014.9	1975.0
25°	2000.7	2000.0	1964.9	1929.8
27.5°	1937.4	1923.8	1903.1	1882.4
30°	1894.7	1869.4	1855.7	1842.1
32.5°	1850.3	1814.6	1806.4	1798.2
35°	1785.1	1739.5	1732.7	1725.9
37.5°	1705.1	1668.0	1653.9	1639.9
40°	1648.4	1623.5	1600.1	1576.7
42.5°	1580.0	1574.4	1537.0	1499.5
45°	1449.5	1478.5	1427.9	1377.2
47.5°	1282.3	1337.0	1284.9	1232.9
50°	1160.1	1222.0	1180.1	1138.1
52.5°	1040.8	1102.1	1071.9	1041.7
55°	866.9	923.7	908.1	892.5
57.5°	721.8	775.6	765.6	755.7
60°	632.3	686.9	680.1	673.2
62.5°	555.7	608.3	603.1	597.8
65°	456.1	501.0	496.1	491.2
67.5°	374.7	411.6	409.1	406.6
70°	326.8	359.4	358.4	357.5
72.5°	281.7	310.9	312.2	313.6
75°	217.8	242.0	244.9	247.8
77.5°	158.8	178.8	182.0	185.1
80°	121.3	136.9	140.8	144.7
82.5°	87.4	97.0	102.4	107.9
85°	41.7	42.9	47.8	52.6
87.5°	18.0	18.3	16.7	15.2
90°	34.5	21.1	13.4	5.8
92.5°	74.4	51.8	36.4	21.1
95°	149.6	118.9	84.4	59.4
97.5°	238.1	188.7	154.5	113.5
100°	285.7	237.8	205.2	161.1
102.5°	337.8	297.6	252.7	208.6
105°	431.4	381.6	329.8	279.9
107.5°	518.1	463.2	401.1	356.2
110°	573.3	513.9	448.7	408.4



TEST NUMBER: P1428287

CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L830-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	627.0	566.0	499.3	459.0
115°	699.8	632.7	571.4	536.9
117.5°	770.0	701.0	636.2	609.0
120°	813.0	743.9	680.7	659.6
122.5°	848.2	780.8	722.1	713.3
125°	901.2	832.1	782.3	793.8
127.5°	944.1	880.8	849.4	875.1
130°	970.2	914.6	895.4	931.8
132.5°	993.2	949.9	941.4	991.7
135°	1027.7	1002.8	1010.5	1079.5
137.5°	1068.7	1059.2	1084.8	1171.9
140°	1094.8	1100.6	1137.0	1234.8
142.5°	1130.1	1143.5	1190.7	1294.6
145°	1184.9	1213.7	1275.0	1378.6
147.5°	1247.1	1284.3	1360.2	1466.4
150°	1288.5	1336.4	1416.9	1518.6
152.5°	1336.0	1385.5	1466.0	1569.2
155°	1409.3	1464.9	1549.2	1637.4
157.5°	1484.0	1540.8	1621.3	1698.4
160°	1530.1	1591.4	1664.3	1735.2
162.5°	1582.2	1639.0	1702.6	1765.9
165°	1658.5	1704.5	1756.3	1810.0
167.5°	1722.6	1760.9	1801.6	1843.4
170°	1764.0	1794.7	1829.2	1861.8
172.5°	1799.3	1823.8	1849.1	1877.1
175°	1846.4	1859.8	1875.2	1892.4
177.5°	1882.9	1887.5	1892.1	1899.7
180°	1898.2	1898.2	1898.2	1898.2



TEST NUMBER: P1428287
 CATALOG NUMBER: SQ2W-PR1-K-125U-100D-L830-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.84	19.65	19.82	20.63	21.93	15.21	16.01	16.19	17.00	18.30
	3H	20.04	20.76	21.03	21.76	23.08	16.36	17.09	17.35	18.08	19.40
	4H	20.52	21.20	21.53	22.20	23.53	16.82	17.51	17.83	18.51	19.84
	6H	20.82	21.44	21.83	22.45	23.79	17.16	17.79	18.18	18.80	20.14
	8H	20.92	21.52	21.94	22.54	23.87	17.30	17.90	18.32	18.92	20.25
	12H	20.96	21.52	21.98	22.54	23.90	17.33	17.90	18.35	18.91	20.27
4H	2H	18.93	19.62	19.94	20.62	21.94	15.91	16.59	16.92	17.59	18.92
	3H	20.39	20.96	21.41	21.98	23.33	17.26	17.83	18.28	18.86	20.20
	4H	21.02	21.53	22.04	22.55	23.92	17.80	18.32	18.83	19.34	20.71
	6H	21.45	21.89	22.48	22.93	24.29	18.23	18.68	19.27	19.72	21.08
	8H	21.60	22.02	22.64	23.05	24.43	18.42	18.83	19.45	19.87	21.24
	12H	21.67	22.04	22.72	23.09	24.47	18.46	18.84	19.52	19.89	21.27
8H	4H	21.04	21.45	22.08	22.49	23.87	18.13	18.54	19.17	19.58	20.95
	6H	21.57	21.91	22.63	22.99	24.36	18.67	19.01	19.73	20.09	21.46
	8H	21.80	22.10	22.87	23.17	24.56	18.93	19.23	20.00	20.29	21.69
	12H	21.92	22.18	22.99	23.24	24.68	19.02	19.29	20.09	20.34	21.78
12H	4H	20.99	21.37	22.05	22.42	23.80	18.15	18.52	19.20	19.57	20.95
	6H	21.56	21.86	22.63	22.92	24.32	18.74	19.04	19.81	20.10	21.50
	8H	21.81	22.07	22.88	23.13	24.56	19.03	19.29	20.10	20.35	21.78