

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1436036

Luminaire Tested: SQ2W-FB-K-150U-075D-L930-UNV-STD-W-WM-4

Issue Date: 3/24/2026

Test Information

Test Method: LM-79-2019
Report Number: P1436036
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 3/24/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-FB-K-150U-075D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8450.5 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 81.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1436036

CATALOG NUMBER: SQ2W-FB-K-150U-075D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1436036

CATALOG NUMBER: SQ2W-FB-K-150U-075D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				34
1	94	90	86	82	85	81	78	75	65	63	61	50	48	47	36	35	35	28				28
2	85	78	72	67	77	71	65	61	56	53	50	44	41	39	32	30	29	23				23
3	78	68	61	55	70	62	56	51	49	45	41	38	35	33	28	26	24	19				19
4	71	60	52	46	63	54	48	42	44	39	35	34	30	27	24	22	20	16				16
5	65	53	45	39	58	48	41	36	39	34	30	30	26	23	22	19	17	14				14
6	59	47	39	34	53	43	36	31	35	29	25	27	23	20	20	17	15	12				12
7	55	43	35	29	49	39	32	27	31	26	22	24	20	18	18	15	13	10				10
8	51	38	31	25	45	35	28	23	28	23	19	22	18	15	16	14	12	9				9
9	47	35	27	22	42	32	25	21	26	21	17	20	16	14	15	12	10	8				8
10	44	32	25	20	39	29	23	18	23	19	15	18	15	12	14	11	9	7				7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4660	4660	4660	4660
5°	4543	8253	4543	8253
10°	4254	16060	4254	16060
15°	3849	18484	3849	18484
20°	3409	19357	3409	19357
25°	3016	19674	3016	19674
30°	2664	19918	2664	19918
35°	2379	21413	2379	21413
40°	2165	22752	2165	22752
45°	1996	23824	1996	23824
50°	1881	24256	1881	24256
55°	1835	24450	1835	24450
60°	1883	24328	1883	24328
65°	1960	23640	1960	23640
70°	2030	17882	2030	17882
75°	2252	9869	2252	9869
80°	2324	9158	2324	9158
85°	2316	3853	2316	3853

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 24671 cd/sqm



TEST NUMBER: P1436036

CATALOG NUMBER: SQ2W-FB-K-150U-075D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.4	0.6
10°-20°	220.6	2.6
20°-30°	388.2	4.6
30°-40°	502.5	5.9
40°-50°	554.2	6.6
50°-60°	517.3	6.1
60°-70°	399.6	4.7
70°-80°	184.2	2.2
80°-90°	43.1	0.5
90°-100°	152.4	1.8
100°-110°	444.5	5.3
110°-120°	725.4	8.6
120°-130°	920.5	10.9
130°-140°	985.0	11.7
140°-150°	919.8	10.9
150°-160°	756.8	9.0
160°-170°	507.6	6.0
170°-180°	180.2	2.1
0°-30°	657.2	7.8
0°-40°	1159.7	13.7
0°-60°	2231.2	26.4
0°-90°	2858.2	33.8
90°-120°	1322.4	15.6
90°-150°	4147.7	49.1
90°-180°	5592.0	66.2
0°-180°	8450.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	289	289	289	289	289	
5°	280	509	280	509	280	26
15°	230	1106	230	1106	230	64
25°	169	1104	169	1104	169	78
35°	121	1086	121	1086	121	76
45°	87	1043	87	1043	87	68
55°	65	869	65	869	65	59
65°	51	619	51	619	51	50
75°	36	158	36	158	36	37
85°	12	21	12	21	12	13
90°	6	43	6	83	6	5
95°	60	44	60	261	60	72
105°	282	453	282	623	282	300
115°	542	751	542	925	542	534
125°	801	1190	801	1134	801	717
135°	1089	1557	1089	1256	1089	842
145°	1391	1795	1391	1283	1391	870
155°	1652	1950	1652	1331	1652	759
165°	1826	2033	1826	1532	1826	514
175°	1910	1991	1910	1797	1910	181
180°	1915	1915	1915	1915	1915	



TEST NUMBER: P1436036

CATALOG NUMBER: SQ2W-FB-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6
2.5°	286.4	291.8	297.2	303.0	308.9	315.4	322.3	328.2	331.1	334.1	331.1
5°	280.3	298.8	317.3	344.1	373.7	407.3	444.9	477.1	493.2	509.2	493.2
7.5°	269.4	307.1	344.7	424.4	518.1	615.4	716.3	800.0	832.0	864.1	832.0
10°	259.5	311.9	364.3	499.5	662.3	787.5	875.0	945.0	962.3	979.6	962.3
12.5°	248.4	319.5	390.7	557.6	756.4	886.5	947.9	998.4	1016.2	1033.9	1016.2
15°	230.3	332.1	433.8	622.5	840.2	974.0	1024.0	1066.3	1086.1	1105.8	1086.1
17.5°	211.7	347.1	482.6	675.1	886.6	1017.0	1066.5	1106.3	1117.0	1127.7	1117.0
20°	198.4	357.5	516.6	709.5	913.6	1036.9	1079.5	1113.1	1119.8	1126.6	1119.8
22.5°	186.2	364.0	541.9	735.0	933.2	1048.4	1080.6	1106.5	1113.8	1121.1	1113.8
25°	169.3	369.7	570.1	762.6	952.6	1057.7	1078.1	1094.6	1099.5	1104.4	1099.5
27.5°	152.9	364.7	576.4	766.5	949.4	1047.5	1060.9	1072.1	1076.9	1081.7	1076.9
30°	142.9	358.1	573.3	761.7	941.2	1035.8	1045.7	1054.8	1061.6	1068.4	1061.6
32.5°	134.0	350.2	566.4	752.5	928.5	1021.1	1030.5	1041.2	1055.9	1070.6	1055.9
35°	120.7	333.5	546.2	730.3	904.8	999.4	1014.2	1032.1	1059.3	1086.4	1059.3
37.5°	109.3	312.0	514.6	696.8	872.2	975.3	1006.3	1036.0	1062.2	1088.3	1062.2
40°	102.7	296.9	491.2	672.0	848.4	957.2	998.5	1035.1	1057.3	1079.5	1057.3
42.5°	96.0	279.9	463.8	643.1	821.0	934.0	982.2	1024.0	1046.2	1068.4	1046.2
45°	87.4	252.7	417.9	595.7	777.6	896.9	953.7	1001.4	1022.4	1043.4	1022.4
47.5°	79.4	222.9	366.5	545.0	735.2	860.4	920.5	969.5	984.8	1000.1	984.8
50°	74.9	203.2	331.5	510.6	706.7	834.3	893.5	941.0	953.3	965.7	953.3
52.5°	70.5	183.9	297.4	476.9	678.4	807.1	862.8	907.5	918.8	930.2	918.8
55°	65.2	157.7	250.2	427.8	633.8	761.1	809.8	848.8	858.7	868.6	858.7
57.5°	60.5	135.1	209.7	381.7	586.2	709.2	750.8	784.0	792.0	800.0	792.0
60°	58.3	123.0	187.8	352.9	551.4	669.5	707.1	737.4	745.4	753.4	745.4
62.5°	54.9	111.3	167.7	324.0	513.7	625.9	660.5	688.4	695.9	703.4	695.9
65°	51.3	97.0	142.6	283.5	456.2	557.0	586.0	608.9	613.9	618.8	613.9
67.5°	46.3	85.1	123.8	246.4	397.0	481.3	499.3	510.5	501.2	492.0	501.2
70°	43.0	78.8	114.5	223.8	357.7	427.6	433.8	431.8	405.3	378.8	405.3
72.5°	40.8	72.6	104.4	199.1	314.6	365.6	352.0	329.3	279.1	228.9	279.1
75°	36.1	62.0	87.9	159.1	245.4	259.0	199.8	155.7	156.9	158.2	156.9
77.5°	29.4	48.8	68.1	111.9	163.8	174.1	142.8	119.6	120.7	121.8	120.7
80°	25.0	40.4	55.8	73.1	91.0	99.3	98.0	97.3	97.9	98.5	97.9
82.5°	20.5	32.0	43.5	53.8	63.8	69.4	70.7	71.4	70.5	69.7	70.5
85°	12.5	19.3	26.1	30.1	33.1	32.2	27.3	23.3	22.0	20.8	22.0
87.5°	5.6	9.6	14.0	14.7	13.9	13.3	13.3	13.7	14.1	14.1	14.1
90°	5.8	13.5	23.2	31.0	36.8	38.7	38.7	40.6	42.6	42.6	42.6
92.5°	21.3	33.7	34.0	34.0	41.4	44.9	48.0	48.4	50.3	50.3	50.3
95°	60.0	65.8	98.7	96.7	65.8	52.2	44.5	44.5	44.5	44.5	44.5
97.5°	114.5	123.0	128.5	172.2	181.9	175.7	143.2	120.3	107.6	101.8	107.6
100°	162.5	166.4	178.0	179.9	228.3	274.7	251.5	222.5	212.8	207.0	212.8
102.5°	210.5	212.8	230.6	238.7	250.0	276.3	356.7	347.8	341.3	340.1	341.3
105°	282.5	284.4	317.3	332.8	340.5	340.5	338.6	377.3	439.2	452.7	439.2
107.5°	359.5	368.4	407.0	448.4	457.3	459.7	449.6	443.8	441.5	443.0	441.5
110°	412.1	425.6	472.1	524.3	537.8	541.7	537.8	532.0	528.2	528.2	528.2



TEST NUMBER: P1436036

CATALOG NUMBER: SQ2W-FB-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	463.2	482.9	535.5	595.5	618.3	629.9	621.4	617.2	613.3	616.4	613.3
115°	541.7	570.7	640.4	702.3	748.7	754.5	752.6	752.6	750.6	750.6	750.6
117.5°	614.4	660.9	739.0	811.0	864.8	880.3	888.0	885.7	883.4	887.2	883.4
120°	665.5	719.7	808.7	889.9	942.2	965.4	973.1	969.3	973.1	969.3	973.1
122.5°	719.7	786.2	873.7	958.0	1019.6	1045.9	1055.2	1055.9	1056.7	1054.4	1056.7
125°	800.9	882.2	984.7	1071.8	1135.6	1166.6	1174.3	1176.3	1180.1	1189.8	1180.1
127.5°	883.0	975.1	1087.7	1171.6	1237.0	1274.5	1286.5	1290.8	1298.9	1303.2	1298.9
130°	940.2	1044.7	1158.8	1238.2	1302.0	1342.6	1363.9	1369.7	1379.4	1377.5	1379.4
132.5°	1000.6	1109.7	1225.4	1307.8	1367.0	1410.7	1428.9	1445.6	1449.0	1451.8	1449.0
135°	1089.2	1207.2	1323.3	1404.5	1460.7	1503.2	1526.4	1541.9	1551.6	1557.4	1551.6
137.5°	1182.5	1307.0	1418.5	1490.8	1547.3	1584.1	1610.4	1626.6	1636.7	1641.3	1636.7
140°	1245.9	1365.9	1474.2	1549.6	1599.9	1636.7	1659.9	1679.3	1690.9	1690.9	1690.9
142.5°	1306.3	1424.7	1529.9	1605.4	1649.5	1683.1	1707.9	1722.6	1735.8	1735.8	1735.8
145°	1391.0	1509.0	1605.8	1681.2	1718.0	1748.9	1776.0	1787.6	1795.3	1795.3	1795.3
147.5°	1479.6	1584.1	1672.3	1744.7	1775.6	1812.0	1833.3	1842.6	1852.2	1848.0	1852.2
150°	1532.2	1629.0	1714.1	1781.8	1812.8	1847.6	1868.9	1876.6	1886.3	1880.5	1886.3
152.5°	1583.3	1675.4	1752.8	1815.9	1842.2	1877.0	1901.4	1909.1	1915.7	1911.4	1915.7
155°	1652.2	1733.4	1805.0	1863.1	1886.3	1919.2	1942.4	1952.1	1959.8	1950.1	1959.8
157.5°	1713.7	1783.7	1846.0	1899.4	1924.2	1952.4	1974.1	1986.1	1993.8	1989.6	1993.8
160°	1750.8	1814.7	1870.8	1921.1	1944.3	1969.5	1992.7	2006.2	2014.0	2008.2	2014.0
162.5°	1781.8	1839.5	1892.5	1938.1	1958.2	1980.3	2008.2	2020.2	2027.9	2020.5	2027.9
165°	1826.3	1872.7	1919.2	1957.9	1975.3	1992.7	2021.7	2035.2	2041.0	2033.3	2041.0
167.5°	1860.0	1895.6	1933.1	1966.4	1979.1	1996.2	2025.2	2036.4	2043.8	2034.1	2043.8
170°	1878.5	1909.5	1942.4	1969.5	1979.1	1994.6	2023.6	2033.3	2039.1	2029.4	2039.1
172.5°	1894.0	1917.2	1943.9	1967.9	1972.9	1985.3	2012.8	2022.5	2026.7	2018.6	2026.7
175°	1909.5	1923.0	1942.4	1957.9	1955.9	1963.7	1986.9	1994.6	2002.4	1990.7	2002.4
177.5°	1916.8	1923.0	1929.2	1938.5	1932.3	1932.3	1949.3	1954.0	1955.5	1949.3	1955.5
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1436036

CATALOG NUMBER: SQ2W-FB-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6
2.5°	328.2	322.3	315.4	308.9	303.0	297.2	291.8	286.4	291.8	297.2	303.0
5°	477.1	444.9	407.3	373.7	344.1	317.3	298.8	280.3	298.8	317.3	344.1
7.5°	800.0	716.3	615.4	518.1	424.4	344.7	307.1	269.4	307.1	344.7	424.4
10°	945.0	875.0	787.5	662.3	499.5	364.3	311.9	259.5	311.9	364.3	499.5
12.5°	998.4	947.9	886.5	756.4	557.6	390.7	319.5	248.4	319.5	390.7	557.6
15°	1066.3	1024.0	974.0	840.2	622.5	433.8	332.1	230.3	332.1	433.8	622.5
17.5°	1106.3	1066.5	1017.0	886.6	675.1	482.6	347.1	211.7	347.1	482.6	675.1
20°	1113.1	1079.5	1036.9	913.6	709.5	516.6	357.5	198.4	357.5	516.6	709.5
22.5°	1106.5	1080.6	1048.4	933.2	735.0	541.9	364.0	186.2	364.0	541.9	735.0
25°	1094.6	1078.1	1057.7	952.6	762.6	570.1	369.7	169.3	369.7	570.1	762.6
27.5°	1072.1	1060.9	1047.5	949.4	766.5	576.4	364.7	152.9	364.7	576.4	766.5
30°	1054.8	1045.7	1035.8	941.2	761.7	573.3	358.1	142.9	358.1	573.3	761.7
32.5°	1041.2	1030.5	1021.1	928.5	752.5	566.4	350.2	134.0	350.2	566.4	752.5
35°	1032.1	1014.2	999.4	904.8	730.3	546.2	333.5	120.7	333.5	546.2	730.3
37.5°	1036.0	1006.3	975.3	872.2	696.8	514.6	312.0	109.3	312.0	514.6	696.8
40°	1035.1	998.5	957.2	848.4	672.0	491.2	296.9	102.7	296.9	491.2	672.0
42.5°	1024.0	982.2	934.0	821.0	643.1	463.8	279.9	96.0	279.9	463.8	643.1
45°	1001.4	953.7	896.9	777.6	595.7	417.9	252.7	87.4	252.7	417.9	595.7
47.5°	969.5	920.5	860.4	735.2	545.0	366.5	222.9	79.4	222.9	366.5	545.0
50°	941.0	893.5	834.3	706.7	510.6	331.5	203.2	74.9	203.2	331.5	510.6
52.5°	907.5	862.8	807.1	678.4	476.9	297.4	183.9	70.5	183.9	297.4	476.9
55°	848.8	809.8	761.1	633.8	427.8	250.2	157.7	65.2	157.7	250.2	427.8
57.5°	784.0	750.8	709.2	586.2	381.7	209.7	135.1	60.5	135.1	209.7	381.7
60°	737.4	707.1	669.5	551.4	352.9	187.8	123.0	58.3	123.0	187.8	352.9
62.5°	688.4	660.5	625.9	513.7	324.0	167.7	111.3	54.9	111.3	167.7	324.0
65°	608.9	586.0	557.0	456.2	283.5	142.6	97.0	51.3	97.0	142.6	283.5
67.5°	510.5	499.3	481.3	397.0	246.4	123.8	85.1	46.3	85.1	123.8	246.4
70°	431.8	433.8	427.6	357.7	223.8	114.5	78.8	43.0	78.8	114.5	223.8
72.5°	329.3	352.0	365.6	314.6	199.1	104.4	72.6	40.8	72.6	104.4	199.1
75°	155.7	199.8	259.0	245.4	159.1	87.9	62.0	36.1	62.0	87.9	159.1
77.5°	119.6	142.8	174.1	163.8	111.9	68.1	48.8	29.4	48.8	68.1	111.9
80°	97.3	98.0	99.3	91.0	73.1	55.8	40.4	25.0	40.4	55.8	73.1
82.5°	71.4	70.7	69.4	63.8	53.8	43.5	32.0	20.5	32.0	43.5	53.8
85°	23.3	27.3	32.2	33.1	30.1	26.1	19.3	12.5	19.3	26.1	30.1
87.5°	13.7	13.3	13.3	13.9	14.7	14.0	9.6	5.6	9.6	13.6	15.5
90°	40.6	38.7	38.7	36.8	31.0	23.2	13.5	5.8	13.5	21.3	34.8
92.5°	48.4	48.0	44.9	41.4	34.0	34.0	33.7	21.3	36.8	52.2	75.1
95°	44.5	44.5	52.2	65.8	96.7	98.7	65.8	60.0	85.1	119.9	150.9
97.5°	120.3	143.2	175.7	181.9	172.2	128.5	123.0	114.5	155.9	190.4	240.3
100°	222.5	251.5	274.7	228.3	179.9	178.0	166.4	162.5	207.0	239.9	288.3
102.5°	347.8	356.7	276.3	250.0	238.7	230.6	212.8	210.5	255.0	300.3	340.9
105°	377.3	338.6	340.5	340.5	332.8	317.3	284.4	282.5	332.8	385.0	435.3
107.5°	443.8	449.6	459.7	457.3	448.4	407.0	368.4	359.5	404.7	467.4	522.7
110°	532.0	537.8	541.7	537.8	524.3	472.1	425.6	412.1	452.7	518.5	578.5



TEST NUMBER: P1436036

CATALOG NUMBER: SQ2W-FB-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	617.2	621.4	629.9	618.3	595.5	535.5	482.9	463.2	503.8	571.1	632.6
115°	752.6	752.6	754.5	748.7	702.3	640.4	570.7	541.7	576.5	638.4	706.1
117.5°	885.7	888.0	880.3	864.8	811.0	739.0	660.9	614.4	641.9	707.3	777.0
120°	969.3	973.1	965.4	942.2	889.9	808.7	719.7	665.5	686.8	750.6	820.3
122.5°	1055.9	1055.2	1045.9	1019.6	958.0	873.7	786.2	719.7	728.6	787.8	855.9
125°	1176.3	1174.3	1166.6	1135.6	1071.8	984.7	882.2	800.9	789.3	839.6	909.3
127.5°	1290.8	1286.5	1274.5	1237.0	1171.6	1087.7	975.1	883.0	857.0	888.8	952.6
130°	1369.7	1363.9	1342.6	1302.0	1238.2	1158.8	1044.7	940.2	903.5	922.8	978.9
132.5°	1445.6	1428.9	1410.7	1367.0	1307.8	1225.4	1109.7	1000.6	949.9	958.4	1002.1
135°	1541.9	1526.4	1503.2	1460.7	1404.5	1323.3	1207.2	1089.2	1019.6	1011.8	1037.0
137.5°	1626.6	1610.4	1584.1	1547.3	1490.8	1418.5	1307.0	1182.5	1094.6	1068.7	1078.4
140°	1679.3	1659.9	1636.7	1599.9	1549.6	1474.2	1365.9	1245.9	1147.2	1110.5	1104.7
142.5°	1722.6	1707.9	1683.1	1649.5	1605.4	1529.9	1424.7	1306.3	1201.4	1153.8	1140.3
145°	1787.6	1776.0	1748.9	1718.0	1681.2	1605.8	1509.0	1391.0	1286.5	1224.6	1195.6
147.5°	1842.6	1833.3	1812.0	1775.6	1744.7	1672.3	1584.1	1479.6	1372.4	1295.8	1258.3
150°	1876.6	1868.9	1847.6	1812.8	1781.8	1714.1	1629.0	1532.2	1429.7	1348.4	1300.1
152.5°	1909.1	1901.4	1877.0	1842.2	1815.9	1752.8	1675.4	1583.3	1479.2	1398.0	1348.1
155°	1952.1	1942.4	1919.2	1886.3	1863.1	1805.0	1733.4	1652.2	1563.2	1478.1	1422.0
157.5°	1986.1	1974.1	1952.4	1924.2	1899.4	1846.0	1783.7	1713.7	1635.9	1554.7	1497.4
160°	2006.2	1992.7	1969.5	1944.3	1921.1	1870.8	1814.7	1750.8	1679.3	1605.8	1543.8
162.5°	2020.2	2008.2	1980.3	1958.2	1938.1	1892.5	1839.5	1781.8	1718.0	1653.7	1596.5
165°	2035.2	2021.7	1992.7	1975.3	1957.9	1919.2	1872.7	1826.3	1772.1	1719.9	1673.5
167.5°	2036.4	2025.2	1996.2	1979.1	1966.4	1933.1	1895.6	1860.0	1817.8	1776.8	1738.1
170°	2033.3	2023.6	1994.6	1979.1	1969.5	1942.4	1909.5	1878.5	1845.6	1810.8	1779.9
172.5°	2022.5	2012.8	1985.3	1972.9	1967.9	1943.9	1917.2	1894.0	1865.8	1840.2	1815.5
175°	1994.6	1986.9	1963.7	1955.9	1957.9	1942.4	1923.0	1909.5	1892.1	1876.6	1863.1
177.5°	1954.0	1949.3	1932.3	1932.3	1938.5	1929.2	1923.0	1916.8	1909.1	1904.5	1899.8
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1436036

CATALOG NUMBER: SQ2W-FB-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6	288.6
2.5°	308.9	315.4	322.3	328.2	331.1	334.1	331.1	328.2	322.3	315.4	308.9
5°	373.7	407.3	444.9	477.1	493.2	509.2	493.2	477.1	444.9	407.3	373.7
7.5°	518.1	615.4	716.3	800.0	832.0	864.1	832.0	800.0	716.3	615.4	518.1
10°	662.3	787.5	875.0	945.0	962.3	979.6	962.3	945.0	875.0	787.5	662.3
12.5°	756.4	886.5	947.9	998.4	1016.2	1033.9	1016.2	998.4	947.9	886.5	756.4
15°	840.2	974.0	1024.0	1066.3	1086.1	1105.8	1086.1	1066.3	1024.0	974.0	840.2
17.5°	886.6	1017.0	1066.5	1106.3	1117.0	1127.7	1117.0	1106.3	1066.5	1017.0	886.6
20°	913.6	1036.9	1079.5	1113.1	1119.8	1126.6	1119.8	1113.1	1079.5	1036.9	913.6
22.5°	933.2	1048.4	1080.6	1106.5	1113.8	1121.1	1113.8	1106.5	1080.6	1048.4	933.2
25°	952.6	1057.7	1078.1	1094.6	1099.5	1104.4	1099.5	1094.6	1078.1	1057.7	952.6
27.5°	949.4	1047.5	1060.9	1072.1	1076.9	1081.7	1076.9	1072.1	1060.9	1047.5	949.4
30°	941.2	1035.8	1045.7	1054.8	1061.6	1068.4	1061.6	1054.8	1045.7	1035.8	941.2
32.5°	928.5	1021.1	1030.5	1041.2	1055.9	1070.6	1055.9	1041.2	1030.5	1021.1	928.5
35°	904.8	999.4	1014.2	1032.1	1059.3	1086.4	1059.3	1032.1	1014.2	999.4	904.8
37.5°	872.2	975.3	1006.3	1036.0	1062.2	1088.3	1062.2	1036.0	1006.3	975.3	872.2
40°	848.4	957.2	998.5	1035.1	1057.3	1079.5	1057.3	1035.1	998.5	957.2	848.4
42.5°	821.0	934.0	982.2	1024.0	1046.2	1068.4	1046.2	1024.0	982.2	934.0	821.0
45°	777.6	896.9	953.7	1001.4	1022.4	1043.4	1022.4	1001.4	953.7	896.9	777.6
47.5°	735.2	860.4	920.5	969.5	984.8	1000.1	984.8	969.5	920.5	860.4	735.2
50°	706.7	834.3	893.5	941.0	953.3	965.7	953.3	941.0	893.5	834.3	706.7
52.5°	678.4	807.1	862.8	907.5	918.8	930.2	918.8	907.5	862.8	807.1	678.4
55°	633.8	761.1	809.8	848.8	858.7	868.6	858.7	848.8	809.8	761.1	633.8
57.5°	586.2	709.2	750.8	784.0	792.0	800.0	792.0	784.0	750.8	709.2	586.2
60°	551.4	669.5	707.1	737.4	745.4	753.4	745.4	737.4	707.1	669.5	551.4
62.5°	513.7	625.9	660.5	688.4	695.9	703.4	695.9	688.4	660.5	625.9	513.7
65°	456.2	557.0	586.0	608.9	613.9	618.8	613.9	608.9	586.0	557.0	456.2
67.5°	397.0	481.3	499.3	510.5	501.2	492.0	501.2	510.5	499.3	481.3	397.0
70°	357.7	427.6	433.8	431.8	405.3	378.8	405.3	431.8	433.8	427.6	357.7
72.5°	314.6	365.6	352.0	329.3	279.1	228.9	279.1	329.3	352.0	365.6	314.6
75°	245.4	259.0	199.8	155.7	156.9	158.2	156.9	155.7	199.8	259.0	245.4
77.5°	163.8	174.1	142.8	119.6	120.7	121.8	120.7	119.6	142.8	174.1	163.8
80°	91.0	99.3	98.0	97.3	97.9	98.5	97.9	97.3	98.0	99.3	91.0
82.5°	63.8	69.4	70.7	71.4	70.5	69.7	70.5	71.4	70.7	69.4	63.8
85°	33.1	32.2	27.3	23.3	22.0	20.8	22.0	23.3	27.3	32.2	33.1
87.5°	15.4	17.2	19.9	21.4	23.0	22.2	23.0	21.4	19.9	17.2	15.4
90°	44.5	58.0	71.6	79.3	87.1	83.2	87.1	79.3	71.6	58.0	44.5
92.5°	89.4	112.2	128.8	142.8	149.0	148.2	149.0	142.8	128.8	112.2	89.4
95°	179.9	207.0	234.1	253.4	265.0	261.2	265.0	253.4	234.1	207.0	179.9
97.5°	277.4	313.8	344.0	362.2	373.8	381.5	373.8	362.2	344.0	313.8	277.4
100°	342.4	377.3	412.1	433.4	452.7	460.4	452.7	433.4	412.1	377.3	342.4
102.5°	395.1	440.7	478.6	501.5	517.7	525.4	517.7	501.5	478.6	440.7	395.1
105°	481.7	530.1	570.7	599.7	617.2	623.0	617.2	599.7	570.7	530.1	481.7
107.5°	568.4	618.3	655.8	688.0	709.2	721.6	709.2	688.0	655.8	618.3	568.4
110°	636.5	677.1	717.8	746.8	768.1	775.8	768.1	746.8	717.8	677.1	636.5



TEST NUMBER: P1436036

CATALOG NUMBER: SQ2W-FB-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	693.8	739.0	779.7	808.7	833.1	843.9	833.1	808.7	779.7	739.0	693.8
115°	773.9	833.8	870.6	897.7	915.1	924.8	915.1	897.7	870.6	833.8	773.9
117.5°	840.4	903.1	943.3	964.2	972.4	979.3	972.4	964.2	943.3	903.1	840.4
120°	882.2	940.2	986.7	1013.8	1023.4	1027.3	1023.4	1013.8	986.7	940.2	882.2
122.5°	920.9	975.8	1020.7	1054.0	1069.9	1073.7	1069.9	1054.0	1020.7	975.8	920.9
125°	975.1	1027.3	1073.7	1106.6	1124.0	1133.7	1124.0	1106.6	1073.7	1027.3	975.1
127.5°	1022.3	1078.8	1121.3	1151.1	1168.1	1175.9	1168.1	1151.1	1121.3	1078.8	1022.3
130°	1048.6	1106.6	1149.2	1182.1	1197.5	1205.3	1197.5	1182.1	1149.2	1106.6	1048.6
132.5°	1068.7	1129.8	1173.9	1203.7	1220.8	1228.5	1220.8	1203.7	1173.9	1129.8	1068.7
135°	1093.1	1156.9	1203.3	1232.4	1247.8	1255.6	1247.8	1232.4	1203.3	1156.9	1093.1
137.5°	1114.4	1172.4	1220.8	1251.3	1265.3	1270.3	1265.3	1251.3	1220.8	1172.4	1114.4
140°	1129.8	1180.1	1228.5	1257.5	1273.0	1274.9	1273.0	1257.5	1228.5	1180.1	1129.8
142.5°	1150.0	1189.4	1231.6	1260.6	1276.1	1279.6	1276.1	1260.6	1231.6	1189.4	1150.0
145°	1185.9	1209.2	1238.2	1265.3	1278.8	1282.7	1278.8	1265.3	1238.2	1209.2	1185.9
147.5°	1231.2	1238.6	1253.6	1271.4	1284.6	1287.3	1284.6	1271.4	1253.6	1238.6	1231.2
150°	1265.3	1263.3	1269.1	1280.7	1292.3	1290.4	1292.3	1280.7	1269.1	1263.3	1265.3
152.5°	1303.9	1292.7	1292.3	1297.8	1303.2	1302.8	1303.2	1297.8	1292.3	1292.7	1303.9
155°	1369.7	1348.4	1336.8	1333.0	1333.0	1331.0	1333.0	1333.0	1336.8	1348.4	1369.7
157.5°	1442.1	1412.3	1394.9	1385.6	1382.9	1378.6	1382.9	1385.6	1394.9	1412.3	1442.1
160°	1491.6	1458.7	1441.3	1425.8	1420.0	1414.2	1420.0	1425.8	1441.3	1458.7	1491.6
162.5°	1538.0	1506.7	1487.7	1473.8	1468.0	1459.1	1468.0	1473.8	1487.7	1506.7	1538.0
165°	1613.5	1580.6	1559.3	1547.7	1540.0	1532.2	1540.0	1547.7	1559.3	1580.6	1613.5
167.5°	1688.9	1653.0	1639.0	1625.9	1618.5	1604.6	1618.5	1625.9	1639.0	1653.0	1688.9
170°	1735.4	1702.5	1694.7	1683.1	1669.6	1654.1	1669.6	1683.1	1694.7	1702.5	1735.4
172.5°	1775.6	1753.6	1745.8	1734.2	1730.0	1717.6	1730.0	1734.2	1745.8	1753.6	1775.6
175°	1834.0	1816.6	1816.6	1814.7	1808.9	1797.3	1808.9	1814.7	1816.6	1816.6	1834.0
177.5°	1882.8	1873.5	1879.7	1879.7	1878.1	1867.3	1878.1	1879.7	1879.7	1873.5	1882.8
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1436036

CATALOG NUMBER: SQ2W-FB-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	288.6	288.6	288.6	288.6
2.5°	303.0	297.2	291.8	286.4
5°	344.1	317.3	298.8	280.3
7.5°	424.4	344.7	307.1	269.4
10°	499.5	364.3	311.9	259.5
12.5°	557.6	390.7	319.5	248.4
15°	622.5	433.8	332.1	230.3
17.5°	675.1	482.6	347.1	211.7
20°	709.5	516.6	357.5	198.4
22.5°	735.0	541.9	364.0	186.2
25°	762.6	570.1	369.7	169.3
27.5°	766.5	576.4	364.7	152.9
30°	761.7	573.3	358.1	142.9
32.5°	752.5	566.4	350.2	134.0
35°	730.3	546.2	333.5	120.7
37.5°	696.8	514.6	312.0	109.3
40°	672.0	491.2	296.9	102.7
42.5°	643.1	463.8	279.9	96.0
45°	595.7	417.9	252.7	87.4
47.5°	545.0	366.5	222.9	79.4
50°	510.6	331.5	203.2	74.9
52.5°	476.9	297.4	183.9	70.5
55°	427.8	250.2	157.7	65.2
57.5°	381.7	209.7	135.1	60.5
60°	352.9	187.8	123.0	58.3
62.5°	324.0	167.7	111.3	54.9
65°	283.5	142.6	97.0	51.3
67.5°	246.4	123.8	85.1	46.3
70°	223.8	114.5	78.8	43.0
72.5°	199.1	104.4	72.6	40.8
75°	159.1	87.9	62.0	36.1
77.5°	111.9	68.1	48.8	29.4
80°	73.1	55.8	40.4	25.0
82.5°	53.8	43.5	32.0	20.5
85°	30.1	26.1	19.3	12.5
87.5°	15.5	13.6	9.6	5.6
90°	34.8	21.3	13.5	5.8
92.5°	75.1	52.2	36.8	21.3
95°	150.9	119.9	85.1	60.0
97.5°	240.3	190.4	155.9	114.5
100°	288.3	239.9	207.0	162.5
102.5°	340.9	300.3	255.0	210.5
105°	435.3	385.0	332.8	282.5
107.5°	522.7	467.4	404.7	359.5
110°	578.5	518.5	452.7	412.1



TEST NUMBER: P1436036

CATALOG NUMBER: SQ2W-FB-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	632.6	571.1	503.8	463.2
115°	706.1	638.4	576.5	541.7
117.5°	777.0	707.3	641.9	614.4
120°	820.3	750.6	686.8	665.5
122.5°	855.9	787.8	728.6	719.7
125°	909.3	839.6	789.3	800.9
127.5°	952.6	888.8	857.0	883.0
130°	978.9	922.8	903.5	940.2
132.5°	1002.1	958.4	949.9	1000.6
135°	1037.0	1011.8	1019.6	1089.2
137.5°	1078.4	1068.7	1094.6	1182.5
140°	1104.7	1110.5	1147.2	1245.9
142.5°	1140.3	1153.8	1201.4	1306.3
145°	1195.6	1224.6	1286.5	1391.0
147.5°	1258.3	1295.8	1372.4	1479.6
150°	1300.1	1348.4	1429.7	1532.2
152.5°	1348.1	1398.0	1479.2	1583.3
155°	1422.0	1478.1	1563.2	1652.2
157.5°	1497.4	1554.7	1635.9	1713.7
160°	1543.8	1605.8	1679.3	1750.8
162.5°	1596.5	1653.7	1718.0	1781.8
165°	1673.5	1719.9	1772.1	1826.3
167.5°	1738.1	1776.8	1817.8	1860.0
170°	1779.9	1810.8	1845.6	1878.5
172.5°	1815.5	1840.2	1865.8	1894.0
175°	1863.1	1876.6	1892.1	1909.5
177.5°	1899.8	1904.5	1909.1	1916.8
180°	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1436036
 CATALOG NUMBER: SQ2W-FB-K-150U-075D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.81	10.56	10.89	11.65	13.13	19.41	20.16	20.49	21.24	22.73
	3H	10.74	11.41	11.83	12.51	14.01	21.01	21.68	22.10	22.77	24.27
	4H	11.14	11.77	12.24	12.87	14.37	21.18	21.81	22.28	22.91	24.41
	6H	11.38	11.97	12.49	13.07	14.59	21.25	21.83	22.36	22.93	24.45
	8H	11.47	12.03	12.59	13.14	14.66	21.26	21.82	22.38	22.93	24.44
	12H	11.52	12.05	12.64	13.15	14.69	21.24	21.77	22.35	22.87	24.41
4H	2H	14.52	15.16	15.63	16.25	17.76	19.76	20.40	20.87	21.49	23.00
	3H	15.64	16.17	16.75	17.29	18.81	21.64	22.17	22.75	23.29	24.81
	4H	15.91	16.40	17.03	17.51	19.05	21.85	22.34	22.97	23.45	24.99
	6H	16.04	16.46	17.17	17.59	19.12	21.98	22.40	23.10	23.53	25.06
	8H	16.08	16.47	17.20	17.59	19.14	22.02	22.41	23.15	23.53	25.08
	12H	16.07	16.43	17.22	17.56	19.12	22.00	22.35	23.14	23.49	25.04
8H	4H	17.10	17.49	18.22	18.61	20.16	21.93	22.32	23.06	23.45	25.00
	6H	17.35	17.67	18.50	18.84	20.38	22.13	22.45	23.27	23.61	25.16
	8H	17.44	17.73	18.60	18.87	20.44	22.22	22.50	23.37	23.64	25.21
	12H	17.48	17.73	18.64	18.87	20.47	22.22	22.46	23.37	23.61	25.21
12H	4H	17.11	17.47	18.26	18.60	20.16	21.88	22.23	23.02	23.37	24.92
	6H	17.45	17.74	18.61	18.88	20.45	22.11	22.39	23.26	23.54	25.10
	8H	17.59	17.83	18.74	18.98	20.58	22.20	22.45	23.36	23.59	25.19