

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428383

Luminaire Tested: SQ2W-PW1-K-050U-100D-L830-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1428383  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-PW1-K-050U-100D-L830-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - PERCEIVE WAVES LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7261.4 lumens  
Efficiency: N/A  
Efficacy: 138.3 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 52.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1428383

CATALOG NUMBER: SQ2W-PW1-K-050U-100D-L830-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1428383

CATALOG NUMBER: SQ2W-PW1-K-050U-100D-L830-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70				
1	103	99	95	92	98	94	91	88	84	82	80	76	74	72	67	66	65	61				
2	95	87	82	77	89	83	78	73	75	71	67	67	64	61	60	58	56	52				
3	87	78	70	65	82	74	67	62	67	62	58	60	56	53	54	51	48	45				
4	80	69	62	56	75	66	59	54	60	54	50	54	50	46	49	45	42	39				
5	74	62	54	48	70	59	52	47	54	48	44	49	44	40	44	41	37	35				
6	68	56	48	42	65	54	46	41	49	43	38	45	40	36	41	37	33	31				
7	63	51	43	38	60	49	42	37	45	39	34	41	36	32	37	33	30	28				
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	34	30	27	25				
9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	28	25	23				
10	52	40	32	27	49	38	31	27	35	29	25	32	27	24	30	26	23	21				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	37177	37177	37177	37177
5°	36928	37568	36928	37568
10°	36996	37895	36996	37895
15°	36986	38122	36986	38122
20°	37001	37377	37001	37377
25°	36801	34730	36801	34730
30°	36550	31399	36550	31399
35°	36265	28355	36265	28355
40°	35543	25052	35543	25052
45°	34149	21881	34149	21881
50°	31782	18728	31782	18728
55°	29075	15186	29075	15186
60°	26059	13100	26059	13100
65°	22788	11644	22788	11644
70°	18632	10560	18632	10560
75°	14504	9713	14504	9713
80°	10804	8563	10804	8563
85°	7317	4872	7317	4872

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 34149 cd/sqm



TEST NUMBER: P1428383

CATALOG NUMBER: SQ2W-PW1-K-050U-100D-L830-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	219.3	3.0
10°-20°	635.3	8.7
20°-30°	934.9	12.9
30°-40°	1022.2	14.1
40°-50°	917.0	12.6
50°-60°	684.0	9.4
60°-70°	432.3	6.0
70°-80°	214.2	2.9
80°-90°	53.2	0.7
90°-100°	58.6	0.8
100°-110°	170.8	2.4
110°-120°	278.8	3.8
120°-130°	353.7	4.9
130°-140°	378.5	5.2
140°-150°	353.4	4.9
150°-160°	290.8	4.0
160°-170°	195.1	2.7
170°-180°	69.3	1.0
0°-30°	1789.5	24.6
0°-40°	2811.7	38.7
0°-60°	4412.7	60.8
0°-90°	5112.4	70.4
90°-120°	508.2	7.0
90°-150°	1593.8	21.9
90°-180°	2149.0	29.6
0°-180°	7261.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2303	2303	2303	2303	2303	
5°	2278	2318	2278	2318	2278	217
15°	2213	2281	2213	2281	2213	625
25°	2066	1950	2066	1950	2066	951
35°	1840	1439	1840	1439	1840	1147
45°	1496	958	1496	958	1496	1147
55°	1033	540	1033	540	1033	922
65°	596	305	596	305	596	591
75°	232	156	232	156	232	256
85°	40	26	40	26	40	50
90°	2	16	2	32	2	3
95°	23	17	23	100	23	28
105°	108	174	108	239	108	115
115°	208	288	208	355	208	205
125°	308	457	308	436	308	275
135°	418	598	418	482	418	323
145°	534	690	534	493	534	334
155°	635	749	635	512	635	292
165°	702	781	702	589	702	198
175°	734	765	734	691	734	70
180°	736	736	736	736	736	



TEST NUMBER: P1428383

CATALOG NUMBER: SQ2W-PW1-K-050U-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6
2.5°	2286.8	2300.1	2313.3	2310.2	2301.6	2297.7	2298.5	2299.7	2302.0	2304.4	2302.0
5°	2278.5	2295.1	2311.6	2309.2	2300.4	2296.5	2297.5	2300.4	2309.2	2318.0	2309.2
7.5°	2267.1	2283.8	2300.6	2299.8	2293.2	2291.5	2294.9	2299.5	2308.1	2316.6	2308.1
10°	2256.6	2274.1	2291.6	2291.6	2285.8	2285.3	2290.2	2295.8	2303.6	2311.4	2303.6
12.5°	2242.5	2260.8	2279.2	2280.5	2276.2	2276.9	2282.6	2288.8	2296.6	2304.4	2296.6
15°	2212.7	2232.2	2251.7	2255.8	2254.9	2257.8	2264.6	2270.9	2275.8	2280.7	2275.8
17.5°	2178.1	2197.5	2217.0	2220.9	2219.5	2219.7	2221.5	2223.4	2225.7	2228.1	2225.7
20°	2153.5	2173.0	2192.5	2195.2	2192.2	2187.4	2180.5	2175.4	2175.4	2175.4	2175.4
22.5°	2118.4	2139.5	2160.5	2160.7	2153.8	2141.2	2122.6	2107.2	2101.0	2094.7	2101.0
25°	2065.8	2086.2	2106.7	2097.2	2077.7	2049.0	2010.9	1978.8	1964.2	1949.5	1964.2
27.5°	2004.4	2020.9	2037.5	2012.7	1974.1	1927.8	1873.8	1828.2	1808.0	1787.7	1808.0
30°	1960.5	1973.2	1985.8	1946.6	1890.1	1832.1	1772.6	1723.2	1703.7	1684.2	1703.7
32.5°	1914.9	1919.8	1924.6	1872.9	1802.4	1736.2	1674.4	1622.8	1601.7	1580.7	1601.7
35°	1839.9	1831.1	1822.4	1753.6	1664.9	1589.4	1527.0	1475.6	1457.1	1438.6	1457.1
37.5°	1751.3	1725.2	1699.1	1621.6	1527.1	1447.2	1381.9	1327.8	1307.3	1286.8	1307.3
40°	1686.4	1649.4	1612.3	1529.2	1430.8	1348.9	1283.6	1229.5	1209.1	1188.6	1209.1
42.5°	1614.5	1568.1	1521.7	1436.2	1337.8	1255.9	1190.6	1136.3	1115.1	1093.8	1115.1
45°	1495.6	1441.0	1386.4	1297.5	1197.1	1115.2	1051.9	999.3	978.8	958.3	978.8
47.5°	1361.8	1307.6	1253.4	1164.8	1064.6	983.8	922.4	871.9	854.4	836.8	854.4
50°	1265.3	1212.7	1160.1	1075.3	979.8	901.3	839.9	788.5	767.0	745.6	767.0
52.5°	1167.1	1119.9	1072.7	991.1	897.9	819.8	756.9	702.3	673.1	643.9	673.1
55°	1032.9	988.1	943.2	866.2	778.5	699.6	629.4	572.6	556.0	539.5	556.0
57.5°	894.7	855.9	817.1	747.9	668.6	597.1	533.3	482.1	468.5	454.8	468.5
60°	807.0	772.9	738.8	672.5	595.5	530.2	476.6	433.0	419.3	405.7	419.3
62.5°	722.8	692.6	662.4	598.8	524.2	465.5	422.8	388.0	376.7	365.3	376.7
65°	596.5	574.1	551.7	499.3	436.9	388.2	353.1	324.3	314.6	304.8	314.6
67.5°	473.7	461.2	448.7	409.5	361.4	321.9	291.1	266.4	259.9	253.5	259.9
70°	394.7	390.8	386.9	354.5	312.6	279.0	253.7	233.4	228.6	223.7	228.6
72.5°	326.3	327.9	329.4	302.5	266.0	237.9	218.0	202.2	198.9	195.6	198.9
75°	232.5	240.3	248.0	230.3	203.9	184.0	170.3	159.6	157.6	155.7	157.6
77.5°	158.3	170.0	181.7	170.2	150.9	136.2	126.0	118.0	116.5	114.9	116.5
80°	116.2	127.9	139.6	131.6	117.0	105.7	98.0	92.1	92.1	92.1	92.1
82.5°	81.1	90.5	99.9	94.2	83.4	76.1	72.2	69.3	69.3	69.3	69.3
85°	39.5	44.3	49.2	47.5	43.6	38.7	32.9	28.3	27.3	26.3	27.3
87.5°	11.0	13.9	17.0	15.2	11.8	9.6	8.8	8.4	8.5	8.5	8.5
90°	2.2	5.2	8.9	11.9	14.1	14.9	14.9	15.6	16.4	16.4	16.4
92.5°	8.2	12.9	13.1	13.1	15.9	17.2	18.4	18.6	19.3	19.3	19.3
95°	23.0	25.3	37.9	37.2	25.3	20.1	17.1	17.1	17.1	17.1	17.1
97.5°	44.0	47.3	49.4	66.2	69.9	67.5	55.0	46.2	41.3	39.1	41.3
100°	62.4	63.9	68.4	69.1	87.7	105.6	96.6	85.5	81.8	79.5	81.8
102.5°	80.9	81.8	88.6	91.7	96.1	106.2	137.1	133.7	131.1	130.7	131.1
105°	108.5	109.3	121.9	127.9	130.8	130.8	130.1	145.0	168.8	174.0	168.8
107.5°	138.1	141.5	156.4	172.3	175.7	176.6	172.8	170.5	169.6	170.2	169.6
110°	158.3	163.6	181.4	201.5	206.7	208.2	206.7	204.4	203.0	203.0	203.0



TEST NUMBER: P1428383

CATALOG NUMBER: SQ2W-PW1-K-050U-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	178.0	185.6	205.8	228.8	237.6	242.1	238.8	237.2	235.7	236.9	235.7
115°	208.2	219.3	246.1	269.9	287.7	289.9	289.2	289.2	288.4	288.4	288.4
117.5°	236.1	254.0	284.0	311.6	332.3	338.3	341.2	340.3	339.4	340.9	339.4
120°	255.7	276.6	310.8	342.0	362.0	371.0	373.9	372.5	373.9	372.5	373.9
122.5°	276.6	302.1	335.7	368.1	391.8	401.9	405.5	405.8	406.1	405.2	406.1
125°	307.8	339.0	378.4	411.9	436.4	448.3	451.3	452.0	453.5	457.2	453.5
127.5°	339.3	374.7	418.0	450.2	475.3	489.8	494.4	496.0	499.1	500.8	499.1
130°	361.3	401.4	445.3	475.8	500.3	515.9	524.1	526.3	530.1	529.3	530.1
132.5°	384.5	426.4	470.9	502.6	525.3	542.1	549.1	555.5	556.8	557.9	556.8
135°	418.5	463.9	508.5	539.7	561.3	577.6	586.6	592.5	596.2	598.5	596.2
137.5°	454.4	502.3	545.1	572.9	594.6	608.7	618.8	625.1	628.9	630.7	628.9
140°	478.8	524.9	566.5	595.5	614.8	628.9	637.9	645.3	649.8	649.8	649.8
142.5°	502.0	547.5	587.9	616.9	633.8	646.8	656.3	661.9	667.0	667.0	667.0
145°	534.5	579.9	617.0	646.0	660.2	672.1	682.5	686.9	689.9	689.9	689.9
147.5°	568.6	608.7	642.6	670.4	682.3	696.3	704.5	708.0	711.8	710.1	711.8
150°	588.8	626.0	658.7	684.7	696.6	710.0	718.1	721.1	724.8	722.6	724.8
152.5°	608.4	643.8	673.5	697.8	707.9	721.3	730.6	733.6	736.1	734.5	736.1
155°	634.9	666.1	693.6	715.9	724.8	737.5	746.4	750.1	753.1	749.4	753.1
157.5°	658.5	685.4	709.4	729.9	739.4	750.3	758.6	763.2	766.2	764.5	766.2
160°	672.8	697.3	718.9	738.2	747.1	756.8	765.7	770.9	773.9	771.7	773.9
162.5°	684.7	706.8	727.2	744.8	752.5	761.0	771.7	776.3	779.3	776.4	779.3
165°	701.8	719.6	737.5	752.3	759.0	765.7	776.9	782.1	784.3	781.3	784.3
167.5°	714.7	728.4	742.8	755.6	760.5	767.1	778.2	782.5	785.4	781.6	785.4
170°	721.9	733.8	746.4	756.8	760.5	766.5	777.6	781.3	783.6	779.9	783.6
172.5°	727.8	736.7	747.0	756.2	758.1	762.9	773.5	777.2	778.8	775.7	778.8
175°	733.8	739.0	746.4	752.3	751.6	754.6	763.5	766.5	769.4	765.0	769.4
177.5°	736.6	739.0	741.3	744.9	742.5	742.5	749.1	750.9	751.5	749.1	751.5
180°	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0



TEST NUMBER: P1428383

CATALOG NUMBER: SQ2W-PW1-K-050U-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6
2.5°	2299.7	2298.5	2297.7	2301.6	2310.2	2313.3	2300.1	2286.8	2300.1	2313.3	2310.2
5°	2300.4	2297.5	2296.5	2300.4	2309.2	2311.6	2295.1	2278.5	2295.1	2311.6	2309.2
7.5°	2299.5	2294.9	2291.5	2293.2	2299.8	2300.6	2283.8	2267.1	2283.8	2300.6	2299.8
10°	2295.8	2290.2	2285.3	2285.8	2291.6	2291.6	2274.1	2256.6	2274.1	2291.6	2291.6
12.5°	2288.8	2282.6	2276.9	2276.2	2280.5	2279.2	2260.8	2242.5	2260.8	2279.2	2280.5
15°	2270.9	2264.6	2257.8	2254.9	2255.8	2251.7	2232.2	2212.7	2232.2	2251.7	2255.8
17.5°	2223.4	2221.5	2219.7	2219.5	2220.9	2217.0	2197.5	2178.1	2197.5	2217.0	2220.9
20°	2175.4	2180.5	2187.4	2192.2	2195.2	2192.5	2173.0	2153.5	2173.0	2192.5	2195.2
22.5°	2107.2	2122.6	2141.2	2153.8	2160.7	2160.5	2139.5	2118.4	2139.5	2160.5	2160.7
25°	1978.8	2010.9	2049.0	2077.7	2097.2	2106.7	2086.2	2065.8	2086.2	2106.7	2097.2
27.5°	1828.2	1873.8	1927.8	1974.1	2012.7	2037.5	2020.9	2004.4	2020.9	2037.5	2012.7
30°	1723.2	1772.6	1832.1	1890.1	1946.6	1985.8	1973.2	1960.5	1973.2	1985.8	1946.6
32.5°	1622.8	1674.4	1736.2	1802.4	1872.9	1924.6	1919.8	1914.9	1919.8	1924.6	1872.9
35°	1475.6	1527.0	1589.4	1664.9	1753.6	1822.4	1831.1	1839.9	1831.1	1822.4	1753.6
37.5°	1327.8	1381.9	1447.2	1527.1	1621.6	1699.1	1725.2	1751.3	1725.2	1699.1	1621.6
40°	1229.5	1283.6	1348.9	1430.8	1529.2	1612.3	1649.4	1686.4	1649.4	1612.3	1529.2
42.5°	1136.3	1190.6	1255.9	1337.8	1436.2	1521.7	1568.1	1614.5	1568.1	1521.7	1436.2
45°	999.3	1051.9	1115.2	1197.1	1297.5	1386.4	1441.0	1495.6	1441.0	1386.4	1297.5
47.5°	871.9	922.4	983.8	1064.6	1164.8	1253.4	1307.6	1361.8	1307.6	1253.4	1164.8
50°	788.5	839.9	901.3	979.8	1075.3	1160.1	1212.7	1265.3	1212.7	1160.1	1075.3
52.5°	702.3	756.9	819.8	897.9	991.1	1072.7	1119.9	1167.1	1119.9	1072.7	991.1
55°	572.6	629.4	699.6	778.5	866.2	943.2	988.1	1032.9	988.1	943.2	866.2
57.5°	482.1	533.3	597.1	668.6	747.9	817.1	855.9	894.7	855.9	817.1	747.9
60°	433.0	476.6	530.2	595.5	672.5	738.8	772.9	807.0	772.9	738.8	672.5
62.5°	388.0	422.8	465.5	524.2	598.8	662.4	692.6	722.8	692.6	662.4	598.8
65°	324.3	353.1	388.2	436.9	499.3	551.7	574.1	596.5	574.1	551.7	499.3
67.5°	266.4	291.1	321.9	361.4	409.5	448.7	461.2	473.7	461.2	448.7	409.5
70°	233.4	253.7	279.0	312.6	354.5	386.9	390.8	394.7	390.8	386.9	354.5
72.5°	202.2	218.0	237.9	266.0	302.5	329.4	327.9	326.3	327.9	329.4	302.5
75°	159.6	170.3	184.0	203.9	230.3	248.0	240.3	232.5	240.3	248.0	230.3
77.5°	118.0	126.0	136.2	150.9	170.2	181.7	170.0	158.3	170.0	181.7	170.2
80°	92.1	98.0	105.7	117.0	131.6	139.6	127.9	116.2	127.9	139.6	131.6
82.5°	69.3	72.2	76.1	83.4	94.2	99.9	90.5	81.1	90.5	99.9	94.2
85°	28.3	32.9	38.7	43.6	47.5	49.2	44.3	39.5	44.3	49.2	47.5
87.5°	8.4	8.8	9.6	11.8	15.2	17.0	13.9	11.0	13.9	16.8	15.5
90°	15.6	14.9	14.9	14.1	11.9	8.9	5.2	2.2	5.2	8.2	13.4
92.5°	18.6	18.4	17.2	15.9	13.1	13.1	12.9	8.2	14.1	20.1	28.8
95°	17.1	17.1	20.1	25.3	37.2	37.9	25.3	23.0	32.7	46.1	58.0
97.5°	46.2	55.0	67.5	69.9	66.2	49.4	47.3	44.0	59.9	73.2	92.3
100°	85.5	96.6	105.6	87.7	69.1	68.4	63.9	62.4	79.5	92.2	110.8
102.5°	133.7	137.1	106.2	96.1	91.7	88.6	81.8	80.9	98.0	115.4	131.0
105°	145.0	130.1	130.8	130.8	127.9	121.9	109.3	108.5	127.9	147.9	167.3
107.5°	170.5	172.8	176.6	175.7	172.3	156.4	141.5	138.1	155.5	179.6	200.9
110°	204.4	206.7	208.2	206.7	201.5	181.4	163.6	158.3	174.0	199.2	222.3



TEST NUMBER: P1428383

CATALOG NUMBER: SQ2W-PW1-K-050U-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	237.2	238.8	242.1	237.6	228.8	205.8	185.6	178.0	193.6	219.5	243.1
115°	289.2	289.2	289.9	287.7	269.9	246.1	219.3	208.2	221.5	245.3	271.4
117.5°	340.3	341.2	338.3	332.3	311.6	284.0	254.0	236.1	246.7	271.8	298.6
120°	372.5	373.9	371.0	362.0	342.0	310.8	276.6	255.7	263.9	288.4	315.2
122.5°	405.8	405.5	401.9	391.8	368.1	335.7	302.1	276.6	280.0	302.7	328.9
125°	452.0	451.3	448.3	436.4	411.9	378.4	339.0	307.8	303.3	322.6	349.4
127.5°	496.0	494.4	489.8	475.3	450.2	418.0	374.7	339.3	329.3	341.5	366.1
130°	526.3	524.1	515.9	500.3	475.8	445.3	401.4	361.3	347.2	354.6	376.2
132.5°	555.5	549.1	542.1	525.3	502.6	470.9	426.4	384.5	365.0	368.3	385.1
135°	592.5	586.6	577.6	561.3	539.7	508.5	463.9	418.5	391.8	388.8	398.5
137.5°	625.1	618.8	608.7	594.6	572.9	545.1	502.3	454.4	420.6	410.7	414.4
140°	645.3	637.9	628.9	614.8	595.5	566.5	524.9	478.8	440.9	426.7	424.5
142.5°	661.9	656.3	646.8	633.8	616.9	587.9	547.5	502.0	461.7	443.4	438.2
145°	686.9	682.5	672.1	660.2	646.0	617.0	579.9	534.5	494.4	470.6	459.4
147.5°	708.0	704.5	696.3	682.3	670.4	642.6	608.7	568.6	527.4	497.9	483.5
150°	721.1	718.1	710.0	696.6	684.7	658.7	626.0	588.8	549.4	518.2	499.6
152.5°	733.6	730.6	721.3	707.9	697.8	673.5	643.8	608.4	568.4	537.2	518.0
155°	750.1	746.4	737.5	724.8	715.9	693.6	666.1	634.9	600.7	568.0	546.4
157.5°	763.2	758.6	750.3	739.4	729.9	709.4	685.4	658.5	628.6	597.4	575.4
160°	770.9	765.7	756.8	747.1	738.2	718.9	697.3	672.8	645.3	617.0	593.3
162.5°	776.3	771.7	761.0	752.5	744.8	727.2	706.8	684.7	660.2	635.5	613.5
165°	782.1	776.9	765.7	759.0	752.3	737.5	719.6	701.8	681.0	660.9	643.1
167.5°	782.5	778.2	767.1	760.5	755.6	742.8	728.4	714.7	698.5	682.8	667.9
170°	781.3	777.6	766.5	760.5	756.8	746.4	733.8	721.9	709.2	695.8	684.0
172.5°	777.2	773.5	762.9	758.1	756.2	747.0	736.7	727.8	717.0	707.1	697.6
175°	766.5	763.5	754.6	751.6	752.3	746.4	739.0	733.8	727.1	721.1	715.9
177.5°	750.9	749.1	742.5	742.5	744.9	741.3	739.0	736.6	733.6	731.8	730.0
180°	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0

TEST NUMBER: P1428383

CATALOG NUMBER: SQ2W-PW1-K-050U-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6	2302.6
2.5°	2301.6	2297.7	2298.5	2299.7	2302.0	2304.4	2302.0	2299.7	2298.5	2297.7	2301.6
5°	2300.4	2296.5	2297.5	2300.4	2309.2	2318.0	2309.2	2300.4	2297.5	2296.5	2300.4
7.5°	2293.2	2291.5	2294.9	2299.5	2308.1	2316.6	2308.1	2299.5	2294.9	2291.5	2293.2
10°	2285.8	2285.3	2290.2	2295.8	2303.6	2311.4	2303.6	2295.8	2290.2	2285.3	2285.8
12.5°	2276.2	2276.9	2282.6	2288.8	2296.6	2304.4	2296.6	2288.8	2282.6	2276.9	2276.2
15°	2254.9	2257.8	2264.6	2270.9	2275.8	2280.7	2275.8	2270.9	2264.6	2257.8	2254.9
17.5°	2219.5	2219.7	2221.5	2223.4	2225.7	2228.1	2225.7	2223.4	2221.5	2219.7	2219.5
20°	2192.2	2187.4	2180.5	2175.4	2175.4	2175.4	2175.4	2175.4	2180.5	2187.4	2192.2
22.5°	2153.8	2141.2	2122.6	2107.2	2101.0	2094.7	2101.0	2107.2	2122.6	2141.2	2153.8
25°	2077.7	2049.0	2010.9	1978.8	1964.2	1949.5	1964.2	1978.8	2010.9	2049.0	2077.7
27.5°	1974.1	1927.8	1873.8	1828.2	1808.0	1787.7	1808.0	1828.2	1873.8	1927.8	1974.1
30°	1890.1	1832.1	1772.6	1723.2	1703.7	1684.2	1703.7	1723.2	1772.6	1832.1	1890.1
32.5°	1802.4	1736.2	1674.4	1622.8	1601.7	1580.7	1601.7	1622.8	1674.4	1736.2	1802.4
35°	1664.9	1589.4	1527.0	1475.6	1457.1	1438.6	1457.1	1475.6	1527.0	1589.4	1664.9
37.5°	1527.1	1447.2	1381.9	1327.8	1307.3	1286.8	1307.3	1327.8	1381.9	1447.2	1527.1
40°	1430.8	1348.9	1283.6	1229.5	1209.1	1188.6	1209.1	1229.5	1283.6	1348.9	1430.8
42.5°	1337.8	1255.9	1190.6	1136.3	1115.1	1093.8	1115.1	1136.3	1190.6	1255.9	1337.8
45°	1197.1	1115.2	1051.9	999.3	978.8	958.3	978.8	999.3	1051.9	1115.2	1197.1
47.5°	1064.6	983.8	922.4	871.9	854.4	836.8	854.4	871.9	922.4	983.8	1064.6
50°	979.8	901.3	839.9	788.5	767.0	745.6	767.0	788.5	839.9	901.3	979.8
52.5°	897.9	819.8	756.9	702.3	673.1	643.9	673.1	702.3	756.9	819.8	897.9
55°	778.5	699.6	629.4	572.6	556.0	539.5	556.0	572.6	629.4	699.6	778.5
57.5°	668.6	597.1	533.3	482.1	468.5	454.8	468.5	482.1	533.3	597.1	668.6
60°	595.5	530.2	476.6	433.0	419.3	405.7	419.3	433.0	476.6	530.2	595.5
62.5°	524.2	465.5	422.8	388.0	376.7	365.3	376.7	388.0	422.8	465.5	524.2
65°	436.9	388.2	353.1	324.3	314.6	304.8	314.6	324.3	353.1	388.2	436.9
67.5°	361.4	321.9	291.1	266.4	259.9	253.5	259.9	266.4	291.1	321.9	361.4
70°	312.6	279.0	253.7	233.4	228.6	223.7	228.6	233.4	253.7	279.0	312.6
72.5°	266.0	237.9	218.0	202.2	198.9	195.6	198.9	202.2	218.0	237.9	266.0
75°	203.9	184.0	170.3	159.6	157.6	155.7	157.6	159.6	170.3	184.0	203.9
77.5°	150.9	136.2	126.0	118.0	116.5	114.9	116.5	118.0	126.0	136.2	150.9
80°	117.0	105.7	98.0	92.1	92.1	92.1	92.1	92.1	98.0	105.7	117.0
82.5°	83.4	76.1	72.2	69.3	69.3	69.3	69.3	69.3	72.2	76.1	83.4
85°	43.6	38.7	32.9	28.3	27.3	26.3	27.3	28.3	32.9	38.7	43.6
87.5°	12.4	11.1	11.3	11.4	12.0	11.7	12.0	11.4	11.3	11.1	12.4
90°	17.1	22.3	27.5	30.5	33.5	32.0	33.5	30.5	27.5	22.3	17.1
92.5°	34.3	43.1	49.5	54.9	57.2	56.9	57.2	49.5	43.1	34.3	34.3
95°	69.1	79.5	90.0	97.4	101.8	100.4	101.8	97.4	90.0	79.5	69.1
97.5°	106.6	120.6	132.2	139.2	143.6	146.6	143.6	139.2	132.2	120.6	106.6
100°	131.6	145.0	158.3	166.5	174.0	176.9	174.0	166.5	158.3	145.0	131.6
102.5°	151.8	169.4	183.9	192.7	198.9	201.9	198.9	192.7	183.9	169.4	151.8
105°	185.1	203.7	219.3	230.5	237.2	239.4	237.2	230.5	219.3	203.7	185.1
107.5°	218.4	237.6	252.0	264.4	272.5	277.3	272.5	264.4	252.0	237.6	218.4
110°	244.6	260.2	275.8	287.0	295.1	298.1	295.1	287.0	275.8	260.2	244.6



TEST NUMBER: P1428383

CATALOG NUMBER: SQ2W-PW1-K-050U-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	266.6	284.0	299.6	310.8	320.1	324.3	320.1	310.8	299.6	284.0	266.6
115°	297.4	320.4	334.5	344.9	351.6	355.4	351.6	344.9	334.5	320.4	297.4
117.5°	322.9	347.0	362.5	370.5	373.6	376.3	373.6	370.5	362.5	347.0	322.9
120°	339.0	361.3	379.1	389.6	393.3	394.8	393.3	389.6	379.1	361.3	339.0
122.5°	353.9	375.0	392.2	405.0	411.1	412.6	411.1	405.0	392.2	375.0	353.9
125°	374.7	394.8	412.6	425.2	431.9	435.6	431.9	425.2	412.6	394.8	374.7
127.5°	392.8	414.5	430.9	442.3	448.9	451.9	448.9	442.3	430.9	414.5	392.8
130°	402.9	425.2	441.6	454.2	460.2	463.2	460.2	454.2	441.6	425.2	402.9
132.5°	410.7	434.2	451.1	462.6	469.1	472.1	469.1	462.6	451.1	434.2	410.7
135°	420.0	444.6	462.4	473.6	479.5	482.5	479.5	473.6	462.4	444.6	420.0
137.5°	428.2	450.5	469.1	480.8	486.2	488.1	486.2	480.8	469.1	450.5	428.2
140°	434.2	453.5	472.1	483.2	489.2	489.9	489.2	483.2	472.1	453.5	434.2
142.5°	441.9	457.1	473.3	484.4	490.4	491.7	490.4	484.4	473.3	457.1	441.9
145°	455.7	464.6	475.8	486.2	491.4	492.9	491.4	486.2	475.8	464.6	455.7
147.5°	473.1	475.9	481.7	488.6	493.6	494.7	493.6	488.6	481.7	475.9	473.1
150°	486.2	485.5	487.7	492.1	496.6	495.9	496.6	492.1	487.7	485.5	486.2
152.5°	501.1	496.8	496.6	498.7	500.8	500.6	500.8	498.7	496.6	496.8	501.1
155°	526.3	518.2	513.7	512.2	512.2	511.5	512.2	512.2	513.7	518.2	526.3
157.5°	554.1	542.7	536.0	532.4	531.4	529.8	531.4	532.4	536.0	542.7	554.1
160°	573.2	560.5	553.9	547.9	545.7	543.4	545.7	547.9	553.9	560.5	573.2
162.5°	591.0	579.0	571.7	566.3	564.1	560.7	564.1	566.3	571.7	579.0	591.0
165°	620.0	607.4	599.2	594.7	591.8	588.8	591.8	594.7	599.2	607.4	620.0
167.5°	649.0	635.2	629.8	624.8	621.9	616.6	621.9	624.8	629.8	635.2	649.0
170°	666.9	654.2	651.2	646.8	641.6	635.6	641.6	646.8	651.2	654.2	666.9
172.5°	682.3	673.8	670.9	666.4	664.8	660.0	664.8	666.4	670.9	673.8	682.3
175°	704.8	698.1	698.1	697.3	695.1	690.6	695.1	697.3	698.1	698.1	704.8
177.5°	723.5	719.9	722.3	722.3	721.7	717.6	721.7	722.3	722.3	719.9	723.5
180°	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0	736.0



TEST NUMBER: P1428383

CATALOG NUMBER: SQ2W-PW1-K-050U-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	2302.6	2302.6	2302.6	2302.6
2.5°	2310.2	2313.3	2300.1	2286.8
5°	2309.2	2311.6	2295.1	2278.5
7.5°	2299.8	2300.6	2283.8	2267.1
10°	2291.6	2291.6	2274.1	2256.6
12.5°	2280.5	2279.2	2260.8	2242.5
15°	2255.8	2251.7	2232.2	2212.7
17.5°	2220.9	2217.0	2197.5	2178.1
20°	2195.2	2192.5	2173.0	2153.5
22.5°	2160.7	2160.5	2139.5	2118.4
25°	2097.2	2106.7	2086.2	2065.8
27.5°	2012.7	2037.5	2020.9	2004.4
30°	1946.6	1985.8	1973.2	1960.5
32.5°	1872.9	1924.6	1919.8	1914.9
35°	1753.6	1822.4	1831.1	1839.9
37.5°	1621.6	1699.1	1725.2	1751.3
40°	1529.2	1612.3	1649.4	1686.4
42.5°	1436.2	1521.7	1568.1	1614.5
45°	1297.5	1386.4	1441.0	1495.6
47.5°	1164.8	1253.4	1307.6	1361.8
50°	1075.3	1160.1	1212.7	1265.3
52.5°	991.1	1072.7	1119.9	1167.1
55°	866.2	943.2	988.1	1032.9
57.5°	747.9	817.1	855.9	894.7
60°	672.5	738.8	772.9	807.0
62.5°	598.8	662.4	692.6	722.8
65°	499.3	551.7	574.1	596.5
67.5°	409.5	448.7	461.2	473.7
70°	354.5	386.9	390.8	394.7
72.5°	302.5	329.4	327.9	326.3
75°	230.3	248.0	240.3	232.5
77.5°	170.2	181.7	170.0	158.3
80°	131.6	139.6	127.9	116.2
82.5°	94.2	99.9	90.5	81.1
85°	47.5	49.2	44.3	39.5
87.5°	15.5	16.8	13.9	11.0
90°	13.4	8.2	5.2	2.2
92.5°	28.8	20.1	14.1	8.2
95°	58.0	46.1	32.7	23.0
97.5°	92.3	73.2	59.9	44.0
100°	110.8	92.2	79.5	62.4
102.5°	131.0	115.4	98.0	80.9
105°	167.3	147.9	127.9	108.5
107.5°	200.9	179.6	155.5	138.1
110°	222.3	199.2	174.0	158.3



TEST NUMBER: P1428383

CATALOG NUMBER: SQ2W-PW1-K-050U-100D-L830-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	243.1	219.5	193.6	178.0
115°	271.4	245.3	221.5	208.2
117.5°	298.6	271.8	246.7	236.1
120°	315.2	288.4	263.9	255.7
122.5°	328.9	302.7	280.0	276.6
125°	349.4	322.6	303.3	307.8
127.5°	366.1	341.5	329.3	339.3
130°	376.2	354.6	347.2	361.3
132.5°	385.1	368.3	365.0	384.5
135°	398.5	388.8	391.8	418.5
137.5°	414.4	410.7	420.6	454.4
140°	424.5	426.7	440.9	478.8
142.5°	438.2	443.4	461.7	502.0
145°	459.4	470.6	494.4	534.5
147.5°	483.5	497.9	527.4	568.6
150°	499.6	518.2	549.4	588.8
152.5°	518.0	537.2	568.4	608.4
155°	546.4	568.0	600.7	634.9
157.5°	575.4	597.4	628.6	658.5
160°	593.3	617.0	645.3	672.8
162.5°	613.5	635.5	660.2	684.7
165°	643.1	660.9	681.0	701.8
167.5°	667.9	682.8	698.5	714.7
170°	684.0	695.8	709.2	721.9
172.5°	697.6	707.1	717.0	727.8
175°	715.9	721.1	727.1	733.8
177.5°	730.0	731.8	733.6	736.6
180°	736.0	736.0	736.0	736.0



TEST NUMBER: P1428383

CATALOG NUMBER: SQ2W-PW1-K-050U-100D-L830-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.21	22.23	21.98	23.01	23.96	17.45	18.47	18.22	19.26	20.21
	3H	22.52	23.43	23.30	24.23	25.21	18.74	19.65	19.52	20.44	21.42
	4H	22.94	23.79	23.74	24.60	25.59	19.25	20.11	20.05	20.91	21.90
	6H	23.12	23.91	23.94	24.73	25.73	19.57	20.36	20.38	21.17	22.17
	8H	23.17	23.92	23.99	24.75	25.76	19.69	20.44	20.51	21.27	22.27
	12H	23.18	23.89	24.00	24.72	25.75	19.72	20.44	20.55	21.26	22.29
4H	2H	21.36	22.22	22.16	23.02	24.01	18.28	19.14	19.09	19.95	20.94
	3H	22.91	23.62	23.73	24.46	25.47	19.75	20.46	20.56	21.29	22.30
	4H	23.46	24.11	24.29	24.95	25.98	20.33	20.98	21.16	21.81	22.85
	6H	23.78	24.34	24.63	25.20	26.24	20.72	21.28	21.57	22.14	23.18
	8H	23.88	24.40	24.73	25.25	26.31	20.88	21.40	21.72	22.25	23.30
	12H	23.91	24.37	24.77	25.25	26.31	20.93	21.39	21.79	22.27	23.33
8H	4H	23.51	24.03	24.36	24.89	25.94	20.68	21.20	21.53	22.06	23.11
	6H	23.94	24.37	24.82	25.27	26.32	21.18	21.61	22.06	22.51	23.56
	8H	24.11	24.49	25.00	25.39	26.46	21.40	21.78	22.29	22.67	23.75
	12H	24.20	24.53	25.09	25.41	26.54	21.49	21.83	22.38	22.71	23.84
12H	4H	23.48	23.95	24.35	24.82	25.88	20.71	21.18	21.58	22.05	23.11
	6H	23.93	24.32	24.82	25.21	26.28	21.26	21.64	22.15	22.53	23.60
	8H	24.13	24.47	25.02	25.35	26.48	21.51	21.84	22.40	22.73	23.85