

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427504

Luminaire Tested: SQ2W-BBM-K-025U-125D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2024
Report Number: P1427504
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-BBM-K-025U-125D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - BLACK DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5738.0 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.17 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 57.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427504

CATALOG NUMBER: SQ2W-BBM-K-025U-125D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427504

CATALOG NUMBER: SQ2W-BBM-K-025U-125D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	115	115	115	115	111	111	111	111	102	102	102	94	94	94	87	87	87	84				
1	109	105	102	100	104	102	99	97	95	93	91	88	87	85	82	81	80	77				
2	102	96	92	88	98	93	89	85	87	84	81	82	79	77	77	75	73	70				
3	95	88	82	78	92	85	80	76	80	76	73	76	72	69	71	69	66	64				
4	89	81	74	69	86	78	72	68	74	69	65	70	66	63	66	63	60	58				
5	84	74	67	62	81	72	66	61	68	63	59	65	61	57	62	58	55	53				
6	78	68	61	56	76	66	60	55	63	58	54	60	56	52	57	53	50	49				
7	73	63	56	51	71	61	55	50	58	53	49	56	51	48	53	49	46	44				
8	69	58	51	47	67	57	50	46	54	49	45	52	47	44	50	46	43	41				
9	65	54	47	43	63	53	47	42	51	45	41	49	44	40	47	42	39	38				
10	61	50	44	39	59	49	43	39	47	42	38	45	41	37	44	39	36	35				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	51908	51908	51908	51908
5°	52315	52393	52315	52393
10°	52973	52894	52973	52894
15°	53928	52853	53928	52853
20°	53997	51896	53997	51896
25°	52662	50599	52662	50599
30°	49503	47195	49503	47195
35°	43936	42288	43936	42288
40°	36032	34102	36032	34102
45°	21484	20162	21484	20162
50°	6707	6342	6707	6342
55°	2536	2536	2536	2536
60°	155	52	155	52
65°	0	0	0	0
70°	0	0	0	0
75°	0	0	0	0
80°	0	0	0	0
85°	0	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 25151 cd/sqm



TEST NUMBER: P1427504

CATALOG NUMBER: SQ2W-BBM-K-025U-125D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	307.4	5.4
10°-20°	900.5	15.7
20°-30°	1324.8	23.1
30°-40°	1354.0	23.6
40°-50°	780.0	13.6
50°-60°	134.2	2.3
60°-70°	4.8	0.1
70°-80°	0.0	0.0
80°-90°	1.7	0.0
90°-100°	25.4	0.4
100°-110°	74.0	1.3
110°-120°	120.8	2.1
120°-130°	153.3	2.7
130°-140°	164.0	2.9
140°-150°	153.1	2.7
150°-160°	126.0	2.2
160°-170°	84.5	1.5
170°-180°	30.0	0.5
0°-30°	2532.6	44.1
0°-40°	3886.6	67.7
0°-60°	4800.9	83.7
0°-90°	4807.4	83.8
90°-120°	220.2	3.8
90°-150°	690.5	12.0
90°-180°	931.0	16.2
0°-180°	5738.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	3215	3215	3215	3215	3215	
5°	3228	3233	3228	3233	3228	308
15°	3226	3162	3226	3162	3226	908
25°	2956	2840	2956	2840	2956	1349
35°	2229	2146	2229	2146	2229	1377
45°	941	883	941	883	941	728
55°	90	90	90	90	90	95
65°	0	0	0	0	0	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	7	1	14	1	1
95°	10	7	10	44	10	12
105°	47	75	47	104	47	50
115°	90	125	90	154	90	89
125°	133	198	133	189	133	119
135°	181	259	181	209	181	140
145°	232	299	232	214	232	145
155°	275	325	275	222	275	126
165°	304	338	304	255	304	86
175°	318	331	318	299	318	30
180°	319	319	319	319	319	



TEST NUMBER: P1427504

CATALOG NUMBER: SQ2W-BBM-K-025U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0
2.5°	3229.2	3225.2	3221.2	3211.6	3200.2	3201.0	3214.2	3223.3	3220.5	3217.6	3220.5
5°	3227.9	3224.3	3220.8	3210.7	3198.6	3202.2	3221.5	3235.6	3234.2	3232.7	3234.2
7.5°	3226.0	3223.5	3221.1	3214.1	3205.5	3209.1	3225.0	3236.0	3232.4	3228.9	3232.4
10°	3231.1	3230.4	3229.7	3218.8	3204.5	3205.6	3222.0	3233.4	3229.9	3226.3	3229.9
12.5°	3233.7	3238.1	3242.6	3226.9	3204.6	3200.0	3213.0	3221.1	3214.7	3208.3	3214.7
15°	3226.3	3238.4	3250.6	3228.4	3194.8	3179.1	3181.3	3180.5	3171.3	3162.0	3171.3
17.5°	3190.3	3207.4	3224.6	3195.3	3150.6	3124.3	3116.4	3107.2	3094.1	3080.9	3094.1
20°	3142.7	3162.7	3182.7	3150.7	3101.4	3069.9	3056.3	3043.3	3031.9	3020.4	3031.9
22.5°	3075.8	3094.1	3112.4	3081.7	3034.6	3002.6	2985.6	2970.5	2961.4	2952.2	2961.4
25°	2956.1	2968.2	2980.4	2949.1	2903.4	2874.1	2861.2	2850.3	2845.3	2840.3	2845.3
27.5°	2786.6	2790.0	2793.4	2768.6	2734.3	2709.1	2693.1	2679.5	2673.0	2666.6	2673.0
30°	2655.3	2655.3	2655.3	2636.0	2610.3	2588.9	2571.7	2555.8	2543.7	2531.5	2543.7
32.5°	2502.2	2500.5	2498.8	2484.6	2466.3	2447.8	2428.9	2411.7	2399.5	2387.4	2399.5
35°	2229.1	2237.0	2244.9	2235.0	2219.3	2202.2	2183.6	2166.9	2156.2	2145.5	2156.2
37.5°	1933.5	1936.5	1939.5	1931.4	1919.5	1903.6	1883.6	1866.3	1857.3	1848.3	1857.3
40°	1709.6	1710.4	1711.1	1701.1	1687.5	1673.5	1659.3	1645.1	1631.6	1618.0	1631.6
42.5°	1448.5	1462.9	1477.3	1471.2	1458.2	1440.2	1417.4	1398.8	1393.2	1387.7	1393.2
45°	940.9	1004.5	1068.1	1091.5	1101.5	1093.7	1067.9	1030.2	956.6	883.0	956.6
47.5°	472.8	552.0	631.2	686.1	732.9	719.6	646.2	571.7	493.8	415.9	493.8
50°	267.0	314.2	361.3	434.8	517.0	503.4	394.0	305.4	279.0	252.5	279.0
52.5°	178.2	199.1	219.9	279.1	351.0	346.3	264.9	200.2	185.2	170.2	185.2
55°	90.1	95.8	101.5	127.6	160.5	159.8	125.4	98.6	94.4	90.1	94.4
57.5°	30.6	38.3	46.0	57.6	70.4	70.8	58.7	47.8	40.8	33.8	40.8
60°	4.8	12.0	19.1	28.4	38.4	37.3	25.2	14.5	8.0	1.6	8.0
62.5°	1.0	3.0	5.0	12.5	22.0	21.8	11.9	4.0	2.2	0.3	2.2
65°	0.0	0.0	0.0	0.5	1.3	1.3	0.5	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.2	0.5	0.8	1.0	1.2	1.3	1.3	1.4	1.4	1.4	1.4
90°	1.0	2.3	3.9	5.2	6.1	6.4	6.4	6.8	7.1	7.1	7.1
92.5°	3.5	5.6	5.7	5.7	6.9	7.5	8.0	8.1	8.4	8.4	8.4
95°	10.0	11.0	16.4	16.1	11.0	8.7	7.4	7.4	7.4	7.4	7.4
97.5°	19.1	20.5	21.4	28.7	30.3	29.2	23.8	20.0	17.9	16.9	17.9
100°	27.1	27.7	29.6	30.0	38.0	45.7	41.9	37.0	35.4	34.5	35.4
102.5°	35.0	35.4	38.4	39.7	41.6	46.0	59.4	57.9	56.8	56.6	56.8
105°	47.0	47.3	52.8	55.4	56.7	56.7	56.4	62.8	73.1	75.4	73.1
107.5°	59.8	61.3	67.8	74.7	76.1	76.5	74.9	73.9	73.5	73.8	73.5
110°	68.6	70.9	78.6	87.3	89.5	90.2	89.5	88.6	87.9	87.9	87.9



TEST NUMBER: P1427504

CATALOG NUMBER: SQ2W-BBM-K-025U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	77.1	80.4	89.2	99.1	102.9	104.9	103.5	102.7	102.1	102.6	102.1
115°	90.2	95.0	106.6	116.9	124.6	125.6	125.3	125.3	125.0	125.0	125.0
117.5°	102.3	110.0	123.0	135.0	144.0	146.5	147.8	147.5	147.1	147.7	147.1
120°	110.8	119.8	134.6	148.2	156.9	160.7	162.0	161.4	162.0	161.4	162.0
122.5°	119.8	130.9	145.5	159.5	169.7	174.1	175.7	175.8	175.9	175.5	175.9
125°	133.3	146.9	163.9	178.4	189.1	194.2	195.5	195.8	196.5	198.1	196.5
127.5°	147.0	162.3	181.1	195.1	205.9	212.2	214.2	214.9	216.2	217.0	216.2
130°	156.5	173.9	192.9	206.1	216.8	223.5	227.1	228.0	229.6	229.3	229.6
132.5°	166.6	184.7	204.0	217.7	227.6	234.9	237.9	240.7	241.2	241.7	241.2
135°	181.3	201.0	220.3	233.8	243.2	250.3	254.1	256.7	258.3	259.3	258.3
137.5°	196.9	217.6	236.2	248.2	257.6	263.7	268.1	270.8	272.5	273.3	272.5
140°	207.4	227.4	245.4	258.0	266.4	272.5	276.3	279.6	281.5	281.5	281.5
142.5°	217.5	237.2	254.7	267.3	274.6	280.2	284.3	286.8	289.0	289.0	289.0
145°	231.6	251.2	267.3	279.9	286.0	291.2	295.7	297.6	298.9	298.9	298.9
147.5°	246.3	263.7	278.4	290.5	295.6	301.7	305.2	306.8	308.4	307.7	308.4
150°	255.1	271.2	285.4	296.6	301.8	307.6	311.1	312.4	314.0	313.1	314.0
152.5°	263.6	278.9	291.8	302.3	306.7	312.5	316.5	317.8	318.9	318.2	318.9
155°	275.1	288.6	300.5	310.2	314.0	319.5	323.4	325.0	326.3	324.7	326.3
157.5°	285.3	297.0	307.3	316.2	320.3	325.0	328.7	330.7	331.9	331.2	331.9
160°	291.5	302.1	311.5	319.8	323.7	327.9	331.7	334.0	335.3	334.3	335.3
162.5°	296.6	306.2	315.1	322.7	326.0	329.7	334.3	336.3	337.6	336.4	337.6
165°	304.0	311.8	319.5	326.0	328.8	331.7	336.6	338.8	339.8	338.5	339.8
167.5°	309.7	315.6	321.8	327.4	329.5	332.3	337.2	339.0	340.3	338.6	340.3
170°	312.7	317.9	323.4	327.9	329.5	332.1	336.9	338.5	339.5	337.9	339.5
172.5°	315.3	319.2	323.6	327.6	328.5	330.5	335.1	336.7	337.4	336.1	337.4
175°	317.9	320.2	323.4	326.0	325.6	326.9	330.8	332.1	333.4	331.4	333.4
177.5°	319.1	320.2	321.2	322.7	321.7	321.7	324.5	325.3	325.6	324.5	325.6
180°	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9



TEST NUMBER: P1427504

CATALOG NUMBER: SQ2W-BBM-K-025U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0
2.5°	3223.3	3214.2	3201.0	3200.2	3211.6	3221.2	3225.2	3229.2	3225.2	3221.2	3211.6
5°	3235.6	3221.5	3202.2	3198.6	3210.7	3220.8	3224.3	3227.9	3224.3	3220.8	3210.7
7.5°	3236.0	3225.0	3209.1	3205.5	3214.1	3221.1	3223.5	3226.0	3223.5	3221.1	3214.1
10°	3233.4	3222.0	3205.6	3204.5	3218.8	3229.7	3230.4	3231.1	3230.4	3229.7	3218.8
12.5°	3221.1	3213.0	3200.0	3204.6	3226.9	3242.6	3238.1	3233.7	3238.1	3242.6	3226.9
15°	3180.5	3181.3	3179.1	3194.8	3228.4	3250.6	3238.4	3226.3	3238.4	3250.6	3228.4
17.5°	3107.2	3116.4	3124.3	3150.6	3195.3	3224.6	3207.4	3190.3	3207.4	3224.6	3195.3
20°	3043.3	3056.3	3069.9	3101.4	3150.7	3182.7	3162.7	3142.7	3162.7	3182.7	3150.7
22.5°	2970.5	2985.6	3002.6	3034.6	3081.7	3112.4	3094.1	3075.8	3094.1	3112.4	3081.7
25°	2850.3	2861.2	2874.1	2903.4	2949.1	2980.4	2968.2	2956.1	2968.2	2980.4	2949.1
27.5°	2679.5	2693.1	2709.1	2734.3	2768.6	2793.4	2790.0	2786.6	2790.0	2793.4	2768.6
30°	2555.8	2571.7	2588.9	2610.3	2636.0	2655.3	2655.3	2655.3	2655.3	2655.3	2636.0
32.5°	2411.7	2428.9	2447.8	2466.3	2484.6	2498.8	2500.5	2502.2	2500.5	2498.8	2484.6
35°	2166.9	2183.6	2202.2	2219.3	2235.0	2244.9	2237.0	2229.1	2237.0	2244.9	2235.0
37.5°	1866.3	1883.6	1903.6	1919.5	1931.4	1939.5	1936.5	1933.5	1936.5	1939.5	1931.4
40°	1645.1	1659.3	1673.5	1687.5	1701.1	1711.1	1710.4	1709.6	1710.4	1711.1	1701.1
42.5°	1398.8	1417.4	1440.2	1458.2	1471.2	1477.3	1462.9	1448.5	1462.9	1477.3	1471.2
45°	1030.2	1067.9	1093.7	1101.5	1091.5	1068.1	1004.5	940.9	1004.5	1068.1	1091.5
47.5°	571.7	646.2	719.6	732.9	686.1	631.2	552.0	472.8	552.0	631.2	686.1
50°	305.4	394.0	503.4	517.0	434.8	361.3	314.2	267.0	314.2	361.3	434.8
52.5°	200.2	264.9	346.3	351.0	279.1	219.9	199.1	178.2	199.1	219.9	279.1
55°	98.6	125.4	159.8	160.5	127.6	101.5	95.8	90.1	95.8	101.5	127.6
57.5°	47.8	58.7	70.8	70.4	57.6	46.0	38.3	30.6	38.3	46.0	57.6
60°	14.5	25.2	37.3	38.4	28.4	19.1	12.0	4.8	12.0	19.1	28.4
62.5°	4.0	11.9	21.8	22.0	12.5	5.0	3.0	1.0	3.0	5.0	12.5
65°	0.0	0.5	1.3	1.3	0.5	0.0	0.0	0.0	0.0	0.0	0.5
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	1.4	1.3	1.3	1.2	1.0	0.8	0.5	0.2	0.5	0.7	1.2
90°	6.8	6.4	6.4	6.1	5.2	3.9	2.3	1.0	2.3	3.5	5.8
92.5°	8.1	8.0	7.5	6.9	5.7	5.7	5.6	3.5	6.1	8.7	12.5
95°	7.4	7.4	8.7	11.0	16.1	16.4	11.0	10.0	14.2	20.0	25.1
97.5°	20.0	23.8	29.2	30.3	28.7	21.4	20.5	19.1	26.0	31.7	40.0
100°	37.0	41.9	45.7	38.0	30.0	29.6	27.7	27.1	34.5	39.9	48.0
102.5°	57.9	59.4	46.0	41.6	39.7	38.4	35.4	35.0	42.5	50.0	56.8
105°	62.8	56.4	56.7	56.7	55.4	52.8	47.3	47.0	55.4	64.1	72.5
107.5°	73.9	74.9	76.5	76.1	74.7	67.8	61.3	59.8	67.4	77.8	87.0
110°	88.6	89.5	90.2	89.5	87.3	78.6	70.9	68.6	75.4	86.3	96.3



TEST NUMBER: P1427504

CATALOG NUMBER: SQ2W-BBM-K-025U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	102.7	103.5	104.9	102.9	99.1	89.2	80.4	77.1	83.9	95.1	105.3
115°	125.3	125.3	125.6	124.6	116.9	106.6	95.0	90.2	96.0	106.3	117.6
117.5°	147.5	147.8	146.5	144.0	135.0	123.0	110.0	102.3	106.9	117.8	129.3
120°	161.4	162.0	160.7	156.9	148.2	134.6	119.8	110.8	114.3	125.0	136.6
122.5°	175.8	175.7	174.1	169.7	159.5	145.5	130.9	119.8	121.3	131.2	142.5
125°	195.8	195.5	194.2	189.1	178.4	163.9	146.9	133.3	131.4	139.8	151.4
127.5°	214.9	214.2	212.2	205.9	195.1	181.1	162.3	147.0	142.7	148.0	158.6
130°	228.0	227.1	223.5	216.8	206.1	192.9	173.9	156.5	150.4	153.6	163.0
132.5°	240.7	237.9	234.9	227.6	217.7	204.0	184.7	166.6	158.1	159.6	166.8
135°	256.7	254.1	250.3	243.2	233.8	220.3	201.0	181.3	169.7	168.5	172.6
137.5°	270.8	268.1	263.7	257.6	248.2	236.2	217.6	196.9	182.2	177.9	179.5
140°	279.6	276.3	272.5	266.4	258.0	245.4	227.4	207.4	191.0	184.9	183.9
142.5°	286.8	284.3	280.2	274.6	267.3	254.7	237.2	217.5	200.0	192.1	189.8
145°	297.6	295.7	291.2	286.0	279.9	267.3	251.2	231.6	214.2	203.9	199.0
147.5°	306.8	305.2	301.7	295.6	290.5	278.4	263.7	246.3	228.5	215.7	209.5
150°	312.4	311.1	307.6	301.8	296.6	285.4	271.2	255.1	238.0	224.5	216.4
152.5°	317.8	316.5	312.5	306.7	302.3	291.8	278.9	263.6	246.3	232.7	224.4
155°	325.0	323.4	319.5	314.0	310.2	300.5	288.6	275.1	260.2	246.1	236.7
157.5°	330.7	328.7	325.0	320.3	316.2	307.3	297.0	285.3	272.4	258.8	249.3
160°	334.0	331.7	327.9	323.7	319.8	311.5	302.1	291.5	279.6	267.3	257.0
162.5°	336.3	334.3	329.7	326.0	322.7	315.1	306.2	296.6	286.0	275.3	265.8
165°	338.8	336.6	331.7	328.8	326.0	319.5	311.8	304.0	295.0	286.3	278.6
167.5°	339.0	337.2	332.3	329.5	327.4	321.8	315.6	309.7	302.6	295.8	289.4
170°	338.5	336.9	332.1	329.5	327.9	323.4	317.9	312.7	307.3	301.5	296.3
172.5°	336.7	335.1	330.5	328.5	327.6	323.6	319.2	315.3	310.6	306.4	302.2
175°	332.1	330.8	326.9	325.6	326.0	323.4	320.2	317.9	315.0	312.4	310.2
177.5°	325.3	324.5	321.7	321.7	322.7	321.2	320.2	319.1	317.8	317.1	316.3
180°	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9



TEST NUMBER: P1427504

CATALOG NUMBER: SQ2W-BBM-K-025U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0	3215.0
2.5°	3200.2	3201.0	3214.2	3223.3	3220.5	3217.6	3220.5	3223.3	3214.2	3201.0	3200.2
5°	3198.6	3202.2	3221.5	3235.6	3234.2	3232.7	3234.2	3235.6	3221.5	3202.2	3198.6
7.5°	3205.5	3209.1	3225.0	3236.0	3232.4	3228.9	3232.4	3236.0	3225.0	3209.1	3205.5
10°	3204.5	3205.6	3222.0	3233.4	3229.9	3226.3	3229.9	3233.4	3222.0	3205.6	3204.5
12.5°	3204.6	3200.0	3213.0	3221.1	3214.7	3208.3	3214.7	3221.1	3213.0	3200.0	3204.6
15°	3194.8	3179.1	3181.3	3180.5	3171.3	3162.0	3171.3	3180.5	3181.3	3179.1	3194.8
17.5°	3150.6	3124.3	3116.4	3107.2	3094.1	3080.9	3094.1	3107.2	3116.4	3124.3	3150.6
20°	3101.4	3069.9	3056.3	3043.3	3031.9	3020.4	3031.9	3043.3	3056.3	3069.9	3101.4
22.5°	3034.6	3002.6	2985.6	2970.5	2961.4	2952.2	2961.4	2970.5	2985.6	3002.6	3034.6
25°	2903.4	2874.1	2861.2	2850.3	2845.3	2840.3	2845.3	2850.3	2861.2	2874.1	2903.4
27.5°	2734.3	2709.1	2693.1	2679.5	2673.0	2666.6	2673.0	2679.5	2693.1	2709.1	2734.3
30°	2610.3	2588.9	2571.7	2555.8	2543.7	2531.5	2543.7	2555.8	2571.7	2588.9	2610.3
32.5°	2466.3	2447.8	2428.9	2411.7	2399.5	2387.4	2399.5	2411.7	2428.9	2447.8	2466.3
35°	2219.3	2202.2	2183.6	2166.9	2156.2	2145.5	2156.2	2166.9	2183.6	2202.2	2219.3
37.5°	1919.5	1903.6	1883.6	1866.3	1857.3	1848.3	1857.3	1866.3	1883.6	1903.6	1919.5
40°	1687.5	1673.5	1659.3	1645.1	1631.6	1618.0	1631.6	1645.1	1659.3	1673.5	1687.5
42.5°	1458.2	1440.2	1417.4	1398.8	1393.2	1387.7	1393.2	1398.8	1417.4	1440.2	1458.2
45°	1101.5	1093.7	1067.9	1030.2	956.6	883.0	956.6	1030.2	1067.9	1093.7	1101.5
47.5°	732.9	719.6	646.2	571.7	493.8	415.9	493.8	571.7	646.2	719.6	732.9
50°	517.0	503.4	394.0	305.4	279.0	252.5	279.0	305.4	394.0	503.4	517.0
52.5°	351.0	346.3	264.9	200.2	185.2	170.2	185.2	200.2	264.9	346.3	351.0
55°	160.5	159.8	125.4	98.6	94.4	90.1	94.4	98.6	125.4	159.8	160.5
57.5°	70.4	70.8	58.7	47.8	40.8	33.8	40.8	47.8	58.7	70.8	70.4
60°	38.4	37.3	25.2	14.5	8.0	1.6	8.0	14.5	25.2	37.3	38.4
62.5°	22.0	21.8	11.9	4.0	2.2	0.3	2.2	4.0	11.9	21.8	22.0
65°	1.3	1.3	0.5	0.0	0.0	0.0	0.0	0.5	1.3	1.3	1.3
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	1.5	1.9	2.4	2.6	2.9	2.8	2.9	2.6	2.4	1.9	1.5
90°	7.4	9.7	11.9	13.2	14.5	13.8	14.5	13.2	11.9	9.7	7.4
92.5°	14.9	18.7	21.5	23.8	24.8	24.7	24.8	23.8	21.5	18.7	14.9
95°	30.0	34.5	39.0	42.2	44.1	43.5	44.1	42.2	39.0	34.5	30.0
97.5°	46.2	52.2	57.3	60.3	62.2	63.5	62.2	60.3	57.3	52.2	46.2
100°	57.0	62.8	68.6	72.1	75.4	76.7	75.4	72.1	68.6	62.8	57.0
102.5°	65.8	73.4	79.7	83.5	86.2	87.5	86.2	83.5	79.7	73.4	65.8
105°	80.2	88.3	95.0	99.8	102.7	103.7	102.7	99.8	95.0	88.3	80.2
107.5°	94.6	102.9	109.2	114.5	118.1	120.1	118.1	114.5	109.2	102.9	94.6
110°	106.0	112.7	119.5	124.3	127.9	129.2	127.9	124.3	119.5	112.7	106.0



TEST NUMBER: P1427504

CATALOG NUMBER: SQ2W-BBM-K-025U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	115.5	123.0	129.8	134.6	138.7	140.5	138.7	134.6	129.8	123.0	115.5
115°	128.8	138.8	144.9	149.4	152.3	154.0	152.3	149.4	144.9	138.8	128.8
117.5°	139.9	150.3	157.0	160.5	161.9	163.0	161.9	160.5	157.0	150.3	139.9
120°	146.9	156.5	164.3	168.8	170.4	171.0	170.4	168.8	164.3	156.5	146.9
122.5°	153.3	162.5	169.9	175.5	178.1	178.8	178.1	175.5	169.9	162.5	153.3
125°	162.3	171.0	178.8	184.2	187.1	188.7	187.1	184.2	178.8	171.0	162.3
127.5°	170.2	179.6	186.7	191.6	194.5	195.8	194.5	191.6	186.7	179.6	170.2
130°	174.6	184.2	191.3	196.8	199.4	200.7	199.4	196.8	191.3	184.2	174.6
132.5°	177.9	188.1	195.4	200.4	203.2	204.5	203.2	200.4	195.4	188.1	177.9
135°	182.0	192.6	200.3	205.2	207.7	209.0	207.7	205.2	200.3	192.6	182.0
137.5°	185.5	195.2	203.2	208.3	210.6	211.5	210.6	208.3	203.2	195.2	185.5
140°	188.1	196.5	204.5	209.4	211.9	212.3	211.9	209.4	204.5	196.5	188.1
142.5°	191.4	198.0	205.0	209.9	212.4	213.0	212.4	209.9	205.0	198.0	191.4
145°	197.4	201.3	206.1	210.6	212.9	213.5	212.9	210.6	206.1	201.3	197.4
147.5°	205.0	206.2	208.7	211.7	213.9	214.3	213.9	211.7	208.7	206.2	205.0
150°	210.6	210.3	211.3	213.2	215.2	214.8	215.2	213.2	211.3	210.3	210.6
152.5°	217.1	215.2	215.2	216.1	217.0	216.9	217.0	216.1	215.2	215.2	217.1
155°	228.0	224.5	222.6	221.9	221.9	221.6	221.9	221.9	222.6	224.5	228.0
157.5°	240.1	235.1	232.2	230.7	230.2	229.5	230.2	230.7	232.2	235.1	240.1
160°	248.3	242.9	240.0	237.4	236.4	235.4	236.4	237.4	240.0	242.9	248.3
162.5°	256.1	250.8	247.7	245.4	244.4	242.9	244.4	245.4	247.7	250.8	256.1
165°	268.6	263.1	259.6	257.7	256.4	255.1	256.4	257.7	259.6	263.1	268.6
167.5°	281.2	275.2	272.9	270.7	269.5	267.1	269.5	270.7	272.9	275.2	281.2
170°	288.9	283.4	282.1	280.2	278.0	275.4	278.0	280.2	282.1	283.4	288.9
172.5°	295.6	291.9	290.6	288.7	288.0	285.9	288.0	288.7	290.6	291.9	295.6
175°	305.3	302.4	302.4	302.1	301.1	299.2	301.1	302.1	302.4	302.4	305.3
177.5°	313.5	311.9	312.9	312.9	312.7	310.9	312.7	312.9	312.9	311.9	313.5
180°	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9	318.9



TEST NUMBER: P1427504

CATALOG NUMBER: SQ2W-BBM-K-025U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	3215.0	3215.0	3215.0	3215.0
2.5°	3211.6	3221.2	3225.2	3229.2
5°	3210.7	3220.8	3224.3	3227.9
7.5°	3214.1	3221.1	3223.5	3226.0
10°	3218.8	3229.7	3230.4	3231.1
12.5°	3226.9	3242.6	3238.1	3233.7
15°	3228.4	3250.6	3238.4	3226.3
17.5°	3195.3	3224.6	3207.4	3190.3
20°	3150.7	3182.7	3162.7	3142.7
22.5°	3081.7	3112.4	3094.1	3075.8
25°	2949.1	2980.4	2968.2	2956.1
27.5°	2768.6	2793.4	2790.0	2786.6
30°	2636.0	2655.3	2655.3	2655.3
32.5°	2484.6	2498.8	2500.5	2502.2
35°	2235.0	2244.9	2237.0	2229.1
37.5°	1931.4	1939.5	1936.5	1933.5
40°	1701.1	1711.1	1710.4	1709.6
42.5°	1471.2	1477.3	1462.9	1448.5
45°	1091.5	1068.1	1004.5	940.9
47.5°	686.1	631.2	552.0	472.8
50°	434.8	361.3	314.2	267.0
52.5°	279.1	219.9	199.1	178.2
55°	127.6	101.5	95.8	90.1
57.5°	57.6	46.0	38.3	30.6
60°	28.4	19.1	12.0	4.8
62.5°	12.5	5.0	3.0	1.0
65°	0.5	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
87.5°	1.2	0.7	0.5	0.2
90°	5.8	3.5	2.3	1.0
92.5°	12.5	8.7	6.1	3.5
95°	25.1	20.0	14.2	10.0
97.5°	40.0	31.7	26.0	19.1
100°	48.0	39.9	34.5	27.1
102.5°	56.8	50.0	42.5	35.0
105°	72.5	64.1	55.4	47.0
107.5°	87.0	77.8	67.4	59.8
110°	96.3	86.3	75.4	68.6



TEST NUMBER: P1427504

CATALOG NUMBER: SQ2W-BBM-K-025U-125D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	105.3	95.1	83.9	77.1
115°	117.6	106.3	96.0	90.2
117.5°	129.3	117.8	106.9	102.3
120°	136.6	125.0	114.3	110.8
122.5°	142.5	131.2	121.3	119.8
125°	151.4	139.8	131.4	133.3
127.5°	158.6	148.0	142.7	147.0
130°	163.0	153.6	150.4	156.5
132.5°	166.8	159.6	158.1	166.6
135°	172.6	168.5	169.7	181.3
137.5°	179.5	177.9	182.2	196.9
140°	183.9	184.9	191.0	207.4
142.5°	189.8	192.1	200.0	217.5
145°	199.0	203.9	214.2	231.6
147.5°	209.5	215.7	228.5	246.3
150°	216.4	224.5	238.0	255.1
152.5°	224.4	232.7	246.3	263.6
155°	236.7	246.1	260.2	275.1
157.5°	249.3	258.8	272.4	285.3
160°	257.0	267.3	279.6	291.5
162.5°	265.8	275.3	286.0	296.6
165°	278.6	286.3	295.0	304.0
167.5°	289.4	295.8	302.6	309.7
170°	296.3	301.5	307.3	312.7
172.5°	302.2	306.4	310.6	315.3
175°	310.2	312.4	315.0	317.9
177.5°	316.3	317.1	317.8	319.1
180°	318.9	318.9	318.9	318.9



TEST NUMBER: P1427504

CATALOG NUMBER: SQ2W-BBM-K-025U-125D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.26	3.19	2.89	3.81	4.51	2.48	3.42	3.12	4.03	4.73
	3H	2.08	2.90	2.73	3.53	4.27	2.30	3.12	2.95	3.75	4.49
	4H	1.98	2.74	2.65	3.38	4.14	2.21	2.97	2.88	3.61	4.37
	6H	1.88	2.57	2.56	3.23	4.00	2.10	2.80	2.78	3.46	4.22
	8H	1.82	2.48	2.51	3.15	3.92	2.05	2.71	2.74	3.38	4.15
	12H	1.76	2.39	2.46	3.06	3.85	1.99	2.62	2.69	3.28	4.08
4H	2H	1.99	2.75	2.66	3.39	4.15	2.22	2.98	2.89	3.62	4.38
	3H	1.80	2.42	2.48	3.10	3.87	2.03	2.65	2.71	3.33	4.10
	4H	1.69	2.25	2.39	2.93	3.74	1.92	2.47	2.61	3.16	3.96
	6H	1.59	2.06	2.30	2.77	3.59	1.81	2.29	2.53	3.00	3.82
	8H	1.52	1.96	2.24	2.67	3.49	1.75	2.19	2.47	2.90	3.72
	12H	1.45	1.84	2.19	2.58	3.41	1.68	2.07	2.42	2.81	3.63
8H	4H	1.52	1.96	2.24	2.67	3.49	1.75	2.19	2.47	2.90	3.72
	6H	1.40	1.76	2.15	2.51	3.34	1.63	1.99	2.38	2.74	3.57
	8H	1.33	1.65	2.10	2.41	3.25	1.56	1.88	2.32	2.64	3.48
	12H	1.27	1.55	2.03	2.29	3.20	1.50	1.78	2.26	2.52	3.43
12H	4H	1.45	1.84	2.19	2.58	3.41	1.68	2.07	2.42	2.81	3.63
	6H	1.33	1.65	2.10	2.41	3.25	1.56	1.88	2.32	2.64	3.48
	8H	1.27	1.55	2.03	2.29	3.20	1.50	1.78	2.26	2.52	3.43