

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427972

Luminaire Tested: SQ2W-PH1-K-150U-075D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427972
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-10)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PH1-K-150U-075D-L930-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE HEX LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8824.5 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 81.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427972

CATALOG NUMBER: SQ2W-PH1-K-150U-075D-L930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427972

CATALOG NUMBER: SQ2W-PH1-K-150U-075D-L930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	95	91	87	84	86	82	79	76	67	64	62	52	51	50	39	38	37	31
2	87	79	73	68	78	72	67	63	59	55	52	46	44	41	34	33	32	26
3	79	70	63	57	71	63	57	52	52	47	44	41	38	35	31	29	27	22
4	72	62	54	48	65	56	50	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	37	31	51	41	34	29	33	28	24	27	23	20	20	18	16	13
8	52	40	33	27	47	37	30	25	30	25	22	24	21	18	19	16	14	12
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23543	23543	23543	23543
5°	23679	21520	23679	21520
10°	23134	19562	23134	19562
15°	23237	19179	23237	19179
20°	22408	19333	22408	19333
25°	21998	18884	21998	18884
30°	21522	19039	21522	19039
35°	21358	22316	21358	22316
40°	21376	17692	21376	17692
45°	21383	15239	21383	15239
50°	21084	14290	21084	14290
55°	20816	13709	20816	13709
60°	20608	12858	20608	12858
65°	20248	11186	20248	11186
70°	19123	7992	19123	7992
75°	17049	6057	17049	6057
80°	13928	5672	13928	5672
85°	8744	3853	8744	3853

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21383 cd/sqm



TEST NUMBER: P1427972

CATALOG NUMBER: SQ2W-PH1-K-150U-075D-L930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.3	1.5
10°-20°	337.5	3.8
20°-30°	494.8	5.6
30°-40°	599.2	6.8
40°-50°	589.2	6.7
50°-60°	512.5	5.8
60°-70°	356.4	4.0
70°-80°	169.0	1.9
80°-90°	45.2	0.5
90°-100°	152.4	1.7
100°-110°	444.5	5.0
110°-120°	725.4	8.2
120°-130°	920.5	10.4
130°-140°	985.0	11.2
140°-150°	919.8	10.4
150°-160°	756.8	8.6
160°-170°	507.6	5.8
170°-180°	180.2	2.0
0°-30°	960.6	10.9
0°-40°	1559.8	17.7
0°-60°	2661.5	30.2
0°-90°	3232.2	36.6
90°-120°	1322.4	15.0
90°-150°	4147.7	47.0
90°-180°	5592.0	63.4
0°-180°	8824.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1458	1458	1458	1458	1458	
5°	1461	1328	1461	1328	1461	137
15°	1390	1147	1390	1147	1390	388
25°	1235	1060	1235	1060	1235	568
35°	1084	1132	1084	1132	1084	679
45°	936	667	936	667	936	720
55°	740	487	740	487	740	661
65°	530	293	530	293	530	521
75°	273	97	273	97	273	290
85°	47	21	47	21	47	63
90°	6	43	6	83	6	6
95°	60	44	60	261	60	72
105°	282	453	282	623	282	300
115°	542	751	542	925	542	534
125°	801	1190	801	1134	801	717
135°	1089	1557	1089	1256	1089	842
145°	1391	1795	1391	1283	1391	870
155°	1652	1950	1652	1331	1652	759
165°	1826	2033	1826	1532	1826	514
175°	1910	1991	1910	1797	1910	181
180°	1915	1915	1915	1915	1915	



TEST NUMBER: P1427972

CATALOG NUMBER: SQ2W-PH1-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2
2.5°	1454.9	1461.8	1468.7	1459.0	1443.7	1433.1	1427.2	1422.5	1421.5	1420.5	1421.5
5°	1461.0	1460.4	1459.8	1430.9	1392.7	1364.0	1344.9	1330.3	1329.0	1327.8	1329.0
7.5°	1434.4	1415.2	1396.1	1357.4	1312.1	1279.0	1257.9	1241.8	1240.8	1239.8	1240.8
10°	1411.1	1382.1	1353.1	1309.3	1260.6	1226.7	1207.6	1193.2	1193.2	1193.2	1193.2
12.5°	1405.5	1359.8	1314.0	1266.0	1217.3	1185.9	1171.7	1161.8	1164.7	1167.7	1164.7
15°	1390.2	1321.2	1252.1	1203.4	1161.5	1138.7	1135.0	1133.9	1140.7	1147.4	1140.7
17.5°	1339.7	1265.4	1191.0	1148.2	1115.9	1103.7	1111.5	1119.4	1127.3	1135.2	1127.3
20°	1304.2	1230.8	1157.5	1117.8	1089.5	1082.7	1097.5	1110.4	1117.8	1125.2	1117.8
22.5°	1274.3	1199.9	1125.5	1090.5	1068.5	1065.7	1081.9	1095.1	1099.1	1103.0	1099.1
25°	1234.8	1151.0	1067.1	1041.5	1035.4	1039.4	1053.6	1063.7	1061.9	1060.0	1061.9
27.5°	1187.7	1100.1	1012.5	996.1	1003.4	1011.3	1020.0	1026.7	1027.8	1028.9	1027.8
30°	1154.4	1066.8	979.2	966.1	977.9	988.0	996.7	1005.1	1013.2	1021.2	1013.2
32.5°	1122.2	1031.7	941.1	931.7	949.4	968.4	988.9	1008.8	1027.2	1045.6	1027.2
35°	1083.6	989.3	894.9	887.5	909.1	936.9	970.8	1011.3	1071.7	1132.2	1071.7
37.5°	1043.1	942.0	840.8	837.5	866.7	895.9	925.2	951.9	971.1	990.4	971.1
40°	1014.2	908.2	802.1	802.0	837.1	873.5	911.1	928.2	883.8	839.4	883.8
42.5°	983.2	877.1	771.0	767.9	799.1	839.2	888.2	906.1	831.2	756.2	831.2
45°	936.5	826.2	715.8	711.8	743.2	765.4	778.4	774.7	721.0	667.4	721.0
47.5°	881.6	776.4	671.2	670.3	704.2	706.7	677.7	650.8	629.8	608.8	629.8
50°	839.4	740.1	640.9	645.2	684.0	680.3	634.1	596.0	582.4	568.9	582.4
52.5°	798.4	704.0	609.7	621.1	667.9	660.5	598.9	550.5	541.4	532.2	541.4
55°	739.5	648.9	558.2	584.1	648.9	639.0	554.5	490.7	488.9	487.0	488.9
57.5°	677.1	591.4	505.7	523.6	576.2	565.8	492.6	438.4	441.6	444.8	441.6
60°	638.2	555.0	471.7	474.1	504.9	495.0	444.5	405.6	401.9	398.2	401.9
62.5°	597.2	517.9	438.6	427.1	438.2	426.6	392.3	365.6	361.9	358.2	361.9
65°	530.0	457.9	385.7	364.0	359.0	342.4	314.0	292.8	292.8	292.8	292.8
67.5°	456.2	393.3	330.4	306.1	294.6	278.1	256.5	236.6	221.8	207.0	221.8
70°	405.1	349.6	294.1	268.7	253.3	233.6	209.5	189.0	179.1	169.3	179.1
72.5°	350.8	303.1	255.5	229.5	210.6	191.4	171.8	154.2	142.9	131.5	142.9
75°	273.3	235.1	196.9	171.6	150.6	131.2	113.3	99.6	98.4	97.1	98.4
77.5°	197.6	169.7	141.8	121.4	103.4	89.8	80.8	74.1	74.2	74.4	74.2
80°	149.8	128.9	107.9	88.8	70.3	60.7	60.1	59.8	60.4	61.0	60.4
82.5°	105.4	89.9	74.4	62.2	51.1	45.9	46.8	47.5	47.6	47.7	47.6
85°	47.2	39.8	32.4	29.6	28.4	26.5	24.0	22.0	21.4	20.8	21.4
87.5°	11.2	12.2	13.6	14.0	13.6	13.3	13.3	13.7	14.1	14.1	14.1
90°	5.8	13.5	23.2	31.0	36.8	38.7	38.7	40.6	42.6	42.6	42.6
92.5°	21.3	33.7	34.0	34.0	41.4	44.9	48.0	48.4	50.3	50.3	50.3
95°	60.0	65.8	98.7	96.7	65.8	52.2	44.5	44.5	44.5	44.5	44.5
97.5°	114.5	123.0	128.5	172.2	181.9	175.7	143.2	120.3	107.6	101.8	107.6
100°	162.5	166.4	178.0	179.9	228.3	274.7	251.5	222.5	212.8	207.0	212.8
102.5°	210.5	212.8	230.6	238.7	250.0	276.3	356.7	347.8	341.3	340.1	341.3
105°	282.5	284.4	317.3	332.8	340.5	340.5	338.6	377.3	439.2	452.7	439.2
107.5°	359.5	368.4	407.0	448.4	457.3	459.7	449.6	443.8	441.5	443.0	441.5
110°	412.1	425.6	472.1	524.3	537.8	541.7	537.8	532.0	528.2	528.2	528.2



TEST NUMBER: P1427972

CATALOG NUMBER: SQ2W-PH1-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	463.2	482.9	535.5	595.5	618.3	629.9	621.4	617.2	613.3	616.4	613.3
115°	541.7	570.7	640.4	702.3	748.7	754.5	752.6	752.6	750.6	750.6	750.6
117.5°	614.4	660.9	739.0	811.0	864.8	880.3	888.0	885.7	883.4	887.2	883.4
120°	665.5	719.7	808.7	889.9	942.2	965.4	973.1	969.3	973.1	969.3	973.1
122.5°	719.7	786.2	873.7	958.0	1019.6	1045.9	1055.2	1055.9	1056.7	1054.4	1056.7
125°	800.9	882.2	984.7	1071.8	1135.6	1166.6	1174.3	1176.3	1180.1	1189.8	1180.1
127.5°	883.0	975.1	1087.7	1171.6	1237.0	1274.5	1286.5	1290.8	1298.9	1303.2	1298.9
130°	940.2	1044.7	1158.8	1238.2	1302.0	1342.6	1363.9	1369.7	1379.4	1377.5	1379.4
132.5°	1000.6	1109.7	1225.4	1307.8	1367.0	1410.7	1428.9	1445.6	1449.0	1451.8	1449.0
135°	1089.2	1207.2	1323.3	1404.5	1460.7	1503.2	1526.4	1541.9	1551.6	1557.4	1551.6
137.5°	1182.5	1307.0	1418.5	1490.8	1547.3	1584.1	1610.4	1626.6	1636.7	1641.3	1636.7
140°	1245.9	1365.9	1474.2	1549.6	1599.9	1636.7	1659.9	1679.3	1690.9	1690.9	1690.9
142.5°	1306.3	1424.7	1529.9	1605.4	1649.5	1683.1	1707.9	1722.6	1735.8	1735.8	1735.8
145°	1391.0	1509.0	1605.8	1681.2	1718.0	1748.9	1776.0	1787.6	1795.3	1795.3	1795.3
147.5°	1479.6	1584.1	1672.3	1744.7	1775.6	1812.0	1833.3	1842.6	1852.2	1848.0	1852.2
150°	1532.2	1629.0	1714.1	1781.8	1812.8	1847.6	1868.9	1876.6	1886.3	1880.5	1886.3
152.5°	1583.3	1675.4	1752.8	1815.9	1842.2	1877.0	1901.4	1909.1	1915.7	1911.4	1915.7
155°	1652.2	1733.4	1805.0	1863.1	1886.3	1919.2	1942.4	1952.1	1959.8	1950.1	1959.8
157.5°	1713.7	1783.7	1846.0	1899.4	1924.2	1952.4	1974.1	1986.1	1993.8	1989.6	1993.8
160°	1750.8	1814.7	1870.8	1921.1	1944.3	1969.5	1992.7	2006.2	2014.0	2008.2	2014.0
162.5°	1781.8	1839.5	1892.5	1938.1	1958.2	1980.3	2008.2	2020.2	2027.9	2020.5	2027.9
165°	1826.3	1872.7	1919.2	1957.9	1975.3	1992.7	2021.7	2035.2	2041.0	2033.3	2041.0
167.5°	1860.0	1895.6	1933.1	1966.4	1979.1	1996.2	2025.2	2036.4	2043.8	2034.1	2043.8
170°	1878.5	1909.5	1942.4	1969.5	1979.1	1994.6	2023.6	2033.3	2039.1	2029.4	2039.1
172.5°	1894.0	1917.2	1943.9	1967.9	1972.9	1985.3	2012.8	2022.5	2026.7	2018.6	2026.7
175°	1909.5	1923.0	1942.4	1957.9	1955.9	1963.7	1986.9	1994.6	2002.4	1990.7	2002.4
177.5°	1916.8	1923.0	1929.2	1938.5	1932.3	1932.3	1949.3	1954.0	1955.5	1949.3	1955.5
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1427972

CATALOG NUMBER: SQ2W-PH1-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2
2.5°	1422.5	1427.2	1433.1	1443.7	1459.0	1468.7	1461.8	1454.9	1461.8	1468.7	1459.0
5°	1330.3	1344.9	1364.0	1392.7	1430.9	1459.8	1460.4	1461.0	1460.4	1459.8	1430.9
7.5°	1241.8	1257.9	1279.0	1312.1	1357.4	1396.1	1415.2	1434.4	1415.2	1396.1	1357.4
10°	1193.2	1207.6	1226.7	1260.6	1309.3	1353.1	1382.1	1411.1	1382.1	1353.1	1309.3
12.5°	1161.8	1171.7	1185.9	1217.3	1266.0	1314.0	1359.8	1405.5	1359.8	1314.0	1266.0
15°	1133.9	1135.0	1138.7	1161.5	1203.4	1252.1	1321.2	1390.2	1321.2	1252.1	1203.4
17.5°	1119.4	1111.5	1103.7	1115.9	1148.2	1191.0	1265.4	1339.7	1265.4	1191.0	1148.2
20°	1110.4	1097.5	1082.7	1089.5	1117.8	1157.5	1230.8	1304.2	1230.8	1157.5	1117.8
22.5°	1095.1	1081.9	1065.7	1068.5	1090.5	1125.5	1199.9	1274.3	1199.9	1125.5	1090.5
25°	1063.7	1053.6	1039.4	1035.4	1041.5	1067.1	1151.0	1234.8	1151.0	1067.1	1041.5
27.5°	1026.7	1020.0	1011.3	1003.4	996.1	1012.5	1100.1	1187.7	1100.1	1012.5	996.1
30°	1005.1	996.7	988.0	977.9	966.1	979.2	1066.8	1154.4	1066.8	979.2	966.1
32.5°	1008.8	988.9	968.4	949.4	931.7	941.1	1031.7	1122.2	1031.7	941.1	931.7
35°	1011.3	970.8	936.9	909.1	887.5	894.9	989.3	1083.6	989.3	894.9	887.5
37.5°	951.9	925.2	895.9	866.7	837.5	840.8	942.0	1043.1	942.0	840.8	837.5
40°	928.2	911.1	873.5	837.1	802.0	802.1	908.2	1014.2	908.2	802.1	802.0
42.5°	906.1	888.2	839.2	799.1	767.9	771.0	877.1	983.2	877.1	771.0	767.9
45°	774.7	778.4	765.4	743.2	711.8	715.8	826.2	936.5	826.2	715.8	711.8
47.5°	650.8	677.7	706.7	704.2	670.3	671.2	776.4	881.6	776.4	671.2	670.3
50°	596.0	634.1	680.3	684.0	645.2	640.9	740.1	839.4	740.1	640.9	645.2
52.5°	550.5	598.9	660.5	667.9	621.1	609.7	704.0	798.4	704.0	609.7	621.1
55°	490.7	554.5	639.0	648.9	584.1	558.2	648.9	739.5	648.9	558.2	584.1
57.5°	438.4	492.6	565.8	576.2	523.6	505.7	591.4	677.1	591.4	505.7	523.6
60°	405.6	444.5	495.0	504.9	474.1	471.7	555.0	638.2	555.0	471.7	474.1
62.5°	365.6	392.3	426.6	438.2	427.1	438.6	517.9	597.2	517.9	438.6	427.1
65°	292.8	314.0	342.4	359.0	364.0	385.7	457.9	530.0	457.9	385.7	364.0
67.5°	236.6	256.5	278.1	294.6	306.1	330.4	393.3	456.2	393.3	330.4	306.1
70°	189.0	209.5	233.6	253.3	268.7	294.1	349.6	405.1	349.6	294.1	268.7
72.5°	154.2	171.8	191.4	210.6	229.5	255.5	303.1	350.8	303.1	255.5	229.5
75°	99.6	113.3	131.2	150.6	171.6	196.9	235.1	273.3	235.1	196.9	171.6
77.5°	74.1	80.8	89.8	103.4	121.4	141.8	169.7	197.6	169.7	141.8	121.4
80°	59.8	60.1	60.7	70.3	88.8	107.9	128.9	149.8	128.9	107.9	88.8
82.5°	47.5	46.8	45.9	51.1	62.2	74.4	89.9	105.4	89.9	74.4	62.2
85°	22.0	24.0	26.5	28.4	29.6	32.4	39.8	47.2	39.8	32.4	29.6
87.5°	13.7	13.3	13.3	13.6	14.0	13.6	12.2	11.2	12.2	13.3	14.7
90°	40.6	38.7	38.7	36.8	31.0	23.2	13.5	5.8	13.5	21.3	34.8
92.5°	48.4	48.0	44.9	41.4	34.0	34.0	33.7	21.3	36.8	52.2	75.1
95°	44.5	44.5	52.2	65.8	96.7	98.7	65.8	60.0	85.1	119.9	150.9
97.5°	120.3	143.2	175.7	181.9	172.2	128.5	123.0	114.5	155.9	190.4	240.3
100°	222.5	251.5	274.7	228.3	179.9	178.0	166.4	162.5	207.0	239.9	288.3
102.5°	347.8	356.7	276.3	250.0	238.7	230.6	212.8	210.5	255.0	300.3	340.9
105°	377.3	338.6	340.5	340.5	332.8	317.3	284.4	282.5	332.8	385.0	435.3
107.5°	443.8	449.6	459.7	457.3	448.4	407.0	368.4	359.5	404.7	467.4	522.7
110°	532.0	537.8	541.7	537.8	524.3	472.1	425.6	412.1	452.7	518.5	578.5



TEST NUMBER: P1427972

CATALOG NUMBER: SQ2W-PH1-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	617.2	621.4	629.9	618.3	595.5	535.5	482.9	463.2	503.8	571.1	632.6
115°	752.6	752.6	754.5	748.7	702.3	640.4	570.7	541.7	576.5	638.4	706.1
117.5°	885.7	888.0	880.3	864.8	811.0	739.0	660.9	614.4	641.9	707.3	777.0
120°	969.3	973.1	965.4	942.2	889.9	808.7	719.7	665.5	686.8	750.6	820.3
122.5°	1055.9	1055.2	1045.9	1019.6	958.0	873.7	786.2	719.7	728.6	787.8	855.9
125°	1176.3	1174.3	1166.6	1135.6	1071.8	984.7	882.2	800.9	789.3	839.6	909.3
127.5°	1290.8	1286.5	1274.5	1237.0	1171.6	1087.7	975.1	883.0	857.0	888.8	952.6
130°	1369.7	1363.9	1342.6	1302.0	1238.2	1158.8	1044.7	940.2	903.5	922.8	978.9
132.5°	1445.6	1428.9	1410.7	1367.0	1307.8	1225.4	1109.7	1000.6	949.9	958.4	1002.1
135°	1541.9	1526.4	1503.2	1460.7	1404.5	1323.3	1207.2	1089.2	1019.6	1011.8	1037.0
137.5°	1626.6	1610.4	1584.1	1547.3	1490.8	1418.5	1307.0	1182.5	1094.6	1068.7	1078.4
140°	1679.3	1659.9	1636.7	1599.9	1549.6	1474.2	1365.9	1245.9	1147.2	1110.5	1104.7
142.5°	1722.6	1707.9	1683.1	1649.5	1605.4	1529.9	1424.7	1306.3	1201.4	1153.8	1140.3
145°	1787.6	1776.0	1748.9	1718.0	1681.2	1605.8	1509.0	1391.0	1286.5	1224.6	1195.6
147.5°	1842.6	1833.3	1812.0	1775.6	1744.7	1672.3	1584.1	1479.6	1372.4	1295.8	1258.3
150°	1876.6	1868.9	1847.6	1812.8	1781.8	1714.1	1629.0	1532.2	1429.7	1348.4	1300.1
152.5°	1909.1	1901.4	1877.0	1842.2	1815.9	1752.8	1675.4	1583.3	1479.2	1398.0	1348.1
155°	1952.1	1942.4	1919.2	1886.3	1863.1	1805.0	1733.4	1652.2	1563.2	1478.1	1422.0
157.5°	1986.1	1974.1	1952.4	1924.2	1899.4	1846.0	1783.7	1713.7	1635.9	1554.7	1497.4
160°	2006.2	1992.7	1969.5	1944.3	1921.1	1870.8	1814.7	1750.8	1679.3	1605.8	1543.8
162.5°	2020.2	2008.2	1980.3	1958.2	1938.1	1892.5	1839.5	1781.8	1718.0	1653.7	1596.5
165°	2035.2	2021.7	1992.7	1975.3	1957.9	1919.2	1872.7	1826.3	1772.1	1719.9	1673.5
167.5°	2036.4	2025.2	1996.2	1979.1	1966.4	1933.1	1895.6	1860.0	1817.8	1776.8	1738.1
170°	2033.3	2023.6	1994.6	1979.1	1969.5	1942.4	1909.5	1878.5	1845.6	1810.8	1779.9
172.5°	2022.5	2012.8	1985.3	1972.9	1967.9	1943.9	1917.2	1894.0	1865.8	1840.2	1815.5
175°	1994.6	1986.9	1963.7	1955.9	1957.9	1942.4	1923.0	1909.5	1892.1	1876.6	1863.1
177.5°	1954.0	1949.3	1932.3	1932.3	1938.5	1929.2	1923.0	1916.8	1909.1	1904.5	1899.8
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1427972

CATALOG NUMBER: SQ2W-PH1-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2
2.5°	1443.7	1433.1	1427.2	1422.5	1421.5	1420.5	1421.5	1422.5	1427.2	1433.1	1443.7
5°	1392.7	1364.0	1344.9	1330.3	1329.0	1327.8	1329.0	1330.3	1344.9	1364.0	1392.7
7.5°	1312.1	1279.0	1257.9	1241.8	1240.8	1239.8	1240.8	1241.8	1257.9	1279.0	1312.1
10°	1260.6	1226.7	1207.6	1193.2	1193.2	1193.2	1193.2	1193.2	1207.6	1226.7	1260.6
12.5°	1217.3	1185.9	1171.7	1161.8	1164.7	1167.7	1164.7	1161.8	1171.7	1185.9	1217.3
15°	1161.5	1138.7	1135.0	1133.9	1140.7	1147.4	1140.7	1133.9	1135.0	1138.7	1161.5
17.5°	1115.9	1103.7	1111.5	1119.4	1127.3	1135.2	1127.3	1119.4	1111.5	1103.7	1115.9
20°	1089.5	1082.7	1097.5	1110.4	1117.8	1125.2	1117.8	1110.4	1097.5	1082.7	1089.5
22.5°	1068.5	1065.7	1081.9	1095.1	1099.1	1103.0	1099.1	1095.1	1081.9	1065.7	1068.5
25°	1035.4	1039.4	1053.6	1063.7	1061.9	1060.0	1061.9	1063.7	1053.6	1039.4	1035.4
27.5°	1003.4	1011.3	1020.0	1026.7	1027.8	1028.9	1027.8	1026.7	1020.0	1011.3	1003.4
30°	977.9	988.0	996.7	1005.1	1013.2	1021.2	1013.2	1005.1	996.7	988.0	977.9
32.5°	949.4	968.4	988.9	1008.8	1027.2	1045.6	1027.2	1008.8	988.9	968.4	949.4
35°	909.1	936.9	970.8	1011.3	1071.7	1132.2	1071.7	1011.3	970.8	936.9	909.1
37.5°	866.7	895.9	925.2	951.9	971.1	990.4	971.1	951.9	925.2	895.9	866.7
40°	837.1	873.5	911.1	928.2	883.8	839.4	883.8	928.2	911.1	873.5	837.1
42.5°	799.1	839.2	888.2	906.1	831.2	756.2	831.2	906.1	888.2	839.2	799.1
45°	743.2	765.4	778.4	774.7	721.0	667.4	721.0	774.7	778.4	765.4	743.2
47.5°	704.2	706.7	677.7	650.8	629.8	608.8	629.8	650.8	677.7	706.7	704.2
50°	684.0	680.3	634.1	596.0	582.4	568.9	582.4	596.0	634.1	680.3	684.0
52.5°	667.9	660.5	598.9	550.5	541.4	532.2	541.4	550.5	598.9	660.5	667.9
55°	648.9	639.0	554.5	490.7	488.9	487.0	488.9	490.7	554.5	639.0	648.9
57.5°	576.2	565.8	492.6	438.4	441.6	444.8	441.6	438.4	492.6	565.8	576.2
60°	504.9	495.0	444.5	405.6	401.9	398.2	401.9	405.6	444.5	495.0	504.9
62.5°	438.2	426.6	392.3	365.6	361.9	358.2	361.9	365.6	392.3	426.6	438.2
65°	359.0	342.4	314.0	292.8	292.8	292.8	292.8	292.8	314.0	342.4	359.0
67.5°	294.6	278.1	256.5	236.6	221.8	207.0	221.8	236.6	256.5	278.1	294.6
70°	253.3	233.6	209.5	189.0	179.1	169.3	179.1	189.0	209.5	233.6	253.3
72.5°	210.6	191.4	171.8	154.2	142.9	131.5	142.9	154.2	171.8	191.4	210.6
75°	150.6	131.2	113.3	99.6	98.4	97.1	98.4	99.6	113.3	131.2	150.6
77.5°	103.4	89.8	80.8	74.1	74.2	74.4	74.2	74.1	80.8	89.8	103.4
80°	70.3	60.7	60.1	59.8	60.4	61.0	60.4	59.8	60.1	60.7	70.3
82.5°	51.1	45.9	46.8	47.5	47.6	47.7	47.6	47.5	46.8	45.9	51.1
85°	28.4	26.5	24.0	22.0	21.4	20.8	21.4	22.0	24.0	26.5	28.4
87.5°	15.2	17.2	19.9	21.4	23.0	22.2	23.0	21.4	19.9	17.2	15.2
90°	44.5	58.0	71.6	79.3	87.1	83.2	87.1	79.3	71.6	58.0	44.5
92.5°	89.4	112.2	128.8	142.8	149.0	148.2	149.0	142.8	128.8	112.2	89.4
95°	179.9	207.0	234.1	253.4	265.0	261.2	265.0	253.4	234.1	207.0	179.9
97.5°	277.4	313.8	344.0	362.2	373.8	381.5	373.8	362.2	344.0	313.8	277.4
100°	342.4	377.3	412.1	433.4	452.7	460.4	452.7	433.4	412.1	377.3	342.4
102.5°	395.1	440.7	478.6	501.5	517.7	525.4	517.7	501.5	478.6	440.7	395.1
105°	481.7	530.1	570.7	599.7	617.2	623.0	617.2	599.7	570.7	530.1	481.7
107.5°	568.4	618.3	655.8	688.0	709.2	721.6	709.2	688.0	655.8	618.3	568.4
110°	636.5	677.1	717.8	746.8	768.1	775.8	768.1	746.8	717.8	677.1	636.5



TEST NUMBER: P1427972

CATALOG NUMBER: SQ2W-PH1-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	693.8	739.0	779.7	808.7	833.1	843.9	833.1	808.7	779.7	739.0	693.8
115°	773.9	833.8	870.6	897.7	915.1	924.8	915.1	897.7	870.6	833.8	773.9
117.5°	840.4	903.1	943.3	964.2	972.4	979.3	972.4	964.2	943.3	903.1	840.4
120°	882.2	940.2	986.7	1013.8	1023.4	1027.3	1023.4	1013.8	986.7	940.2	882.2
122.5°	920.9	975.8	1020.7	1054.0	1069.9	1073.7	1069.9	1054.0	1020.7	975.8	920.9
125°	975.1	1027.3	1073.7	1106.6	1124.0	1133.7	1124.0	1106.6	1073.7	1027.3	975.1
127.5°	1022.3	1078.8	1121.3	1151.1	1168.1	1175.9	1168.1	1151.1	1121.3	1078.8	1022.3
130°	1048.6	1106.6	1149.2	1182.1	1197.5	1205.3	1197.5	1182.1	1149.2	1106.6	1048.6
132.5°	1068.7	1129.8	1173.9	1203.7	1220.8	1228.5	1220.8	1203.7	1173.9	1129.8	1068.7
135°	1093.1	1156.9	1203.3	1232.4	1247.8	1255.6	1247.8	1232.4	1203.3	1156.9	1093.1
137.5°	1114.4	1172.4	1220.8	1251.3	1265.3	1270.3	1265.3	1251.3	1220.8	1172.4	1114.4
140°	1129.8	1180.1	1228.5	1257.5	1273.0	1274.9	1273.0	1257.5	1228.5	1180.1	1129.8
142.5°	1150.0	1189.4	1231.6	1260.6	1276.1	1279.6	1276.1	1260.6	1231.6	1189.4	1150.0
145°	1185.9	1209.2	1238.2	1265.3	1278.8	1282.7	1278.8	1265.3	1238.2	1209.2	1185.9
147.5°	1231.2	1238.6	1253.6	1271.4	1284.6	1287.3	1284.6	1271.4	1253.6	1238.6	1231.2
150°	1265.3	1263.3	1269.1	1280.7	1292.3	1290.4	1292.3	1280.7	1269.1	1263.3	1265.3
152.5°	1303.9	1292.7	1292.3	1297.8	1303.2	1302.8	1303.2	1297.8	1292.3	1292.7	1303.9
155°	1369.7	1348.4	1336.8	1333.0	1333.0	1331.0	1333.0	1333.0	1336.8	1348.4	1369.7
157.5°	1442.1	1412.3	1394.9	1385.6	1382.9	1378.6	1382.9	1385.6	1394.9	1412.3	1442.1
160°	1491.6	1458.7	1441.3	1425.8	1420.0	1414.2	1420.0	1425.8	1441.3	1458.7	1491.6
162.5°	1538.0	1506.7	1487.7	1473.8	1468.0	1459.1	1468.0	1473.8	1487.7	1506.7	1538.0
165°	1613.5	1580.6	1559.3	1547.7	1540.0	1532.2	1540.0	1547.7	1559.3	1580.6	1613.5
167.5°	1688.9	1653.0	1639.0	1625.9	1618.5	1604.6	1618.5	1625.9	1639.0	1653.0	1688.9
170°	1735.4	1702.5	1694.7	1683.1	1669.6	1654.1	1669.6	1683.1	1694.7	1702.5	1735.4
172.5°	1775.6	1753.6	1745.8	1734.2	1730.0	1717.6	1730.0	1734.2	1745.8	1753.6	1775.6
175°	1834.0	1816.6	1816.6	1814.7	1808.9	1797.3	1808.9	1814.7	1816.6	1816.6	1834.0
177.5°	1882.8	1873.5	1879.7	1879.7	1878.1	1867.3	1878.1	1879.7	1879.7	1873.5	1882.8
180°	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1427972

CATALOG NUMBER: SQ2W-PH1-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1458.2	1458.2	1458.2	1458.2
2.5°	1459.0	1468.7	1461.8	1454.9
5°	1430.9	1459.8	1460.4	1461.0
7.5°	1357.4	1396.1	1415.2	1434.4
10°	1309.3	1353.1	1382.1	1411.1
12.5°	1266.0	1314.0	1359.8	1405.5
15°	1203.4	1252.1	1321.2	1390.2
17.5°	1148.2	1191.0	1265.4	1339.7
20°	1117.8	1157.5	1230.8	1304.2
22.5°	1090.5	1125.5	1199.9	1274.3
25°	1041.5	1067.1	1151.0	1234.8
27.5°	996.1	1012.5	1100.1	1187.7
30°	966.1	979.2	1066.8	1154.4
32.5°	931.7	941.1	1031.7	1122.2
35°	887.5	894.9	989.3	1083.6
37.5°	837.5	840.8	942.0	1043.1
40°	802.0	802.1	908.2	1014.2
42.5°	767.9	771.0	877.1	983.2
45°	711.8	715.8	826.2	936.5
47.5°	670.3	671.2	776.4	881.6
50°	645.2	640.9	740.1	839.4
52.5°	621.1	609.7	704.0	798.4
55°	584.1	558.2	648.9	739.5
57.5°	523.6	505.7	591.4	677.1
60°	474.1	471.7	555.0	638.2
62.5°	427.1	438.6	517.9	597.2
65°	364.0	385.7	457.9	530.0
67.5°	306.1	330.4	393.3	456.2
70°	268.7	294.1	349.6	405.1
72.5°	229.5	255.5	303.1	350.8
75°	171.6	196.9	235.1	273.3
77.5°	121.4	141.8	169.7	197.6
80°	88.8	107.9	128.9	149.8
82.5°	62.2	74.4	89.9	105.4
85°	29.6	32.4	39.8	47.2
87.5°	14.7	13.3	12.2	11.2
90°	34.8	21.3	13.5	5.8
92.5°	75.1	52.2	36.8	21.3
95°	150.9	119.9	85.1	60.0
97.5°	240.3	190.4	155.9	114.5
100°	288.3	239.9	207.0	162.5
102.5°	340.9	300.3	255.0	210.5
105°	435.3	385.0	332.8	282.5
107.5°	522.7	467.4	404.7	359.5
110°	578.5	518.5	452.7	412.1



TEST NUMBER: P1427972

CATALOG NUMBER: SQ2W-PH1-K-150U-075D-L930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	632.6	571.1	503.8	463.2
115°	706.1	638.4	576.5	541.7
117.5°	777.0	707.3	641.9	614.4
120°	820.3	750.6	686.8	665.5
122.5°	855.9	787.8	728.6	719.7
125°	909.3	839.6	789.3	800.9
127.5°	952.6	888.8	857.0	883.0
130°	978.9	922.8	903.5	940.2
132.5°	1002.1	958.4	949.9	1000.6
135°	1037.0	1011.8	1019.6	1089.2
137.5°	1078.4	1068.7	1094.6	1182.5
140°	1104.7	1110.5	1147.2	1245.9
142.5°	1140.3	1153.8	1201.4	1306.3
145°	1195.6	1224.6	1286.5	1391.0
147.5°	1258.3	1295.8	1372.4	1479.6
150°	1300.1	1348.4	1429.7	1532.2
152.5°	1348.1	1398.0	1479.2	1583.3
155°	1422.0	1478.1	1563.2	1652.2
157.5°	1497.4	1554.7	1635.9	1713.7
160°	1543.8	1605.8	1679.3	1750.8
162.5°	1596.5	1653.7	1718.0	1781.8
165°	1673.5	1719.9	1772.1	1826.3
167.5°	1738.1	1776.8	1817.8	1860.0
170°	1779.9	1810.8	1845.6	1878.5
172.5°	1815.5	1840.2	1865.8	1894.0
175°	1863.1	1876.6	1892.1	1909.5
177.5°	1899.8	1904.5	1909.1	1916.8
180°	1915.3	1915.3	1915.3	1915.3



TEST NUMBER: P1427972
 CATALOG NUMBER: SQ2W-PH1-K-150U-075D-L930-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.47	17.21	17.53	18.28	19.73	15.29	16.04	16.36	17.11	18.56
	3H	18.63	19.30	19.71	20.38	21.84	16.33	17.00	17.41	18.08	19.55
	4H	19.44	20.07	20.52	21.15	22.63	16.57	17.21	17.66	18.29	19.76
	6H	19.90	20.48	20.99	21.56	23.05	16.71	17.29	17.80	18.37	19.86
	8H	20.05	20.60	21.15	21.70	23.18	16.76	17.32	17.86	18.42	19.90
	12H	20.10	20.63	21.21	21.72	23.23	16.77	17.30	17.87	18.39	19.89
4H	2H	16.89	17.52	17.98	18.60	20.07	15.96	16.60	17.06	17.67	19.15
	3H	19.13	19.65	20.23	20.76	22.25	17.18	17.71	18.28	18.81	20.30
	4H	19.99	20.48	21.10	21.57	23.08	17.47	17.95	18.57	19.05	20.56
	6H	20.55	20.96	21.66	22.08	23.58	17.66	18.08	18.77	19.19	20.69
	8H	20.75	21.13	21.86	22.24	23.76	17.75	18.13	18.86	19.24	20.76
	12H	20.83	21.18	21.96	22.30	23.82	17.77	18.12	18.89	19.24	20.76
8H	4H	20.01	20.40	21.12	21.50	23.02	17.69	18.08	18.80	19.18	20.70
	6H	20.63	20.95	21.77	22.10	23.62	17.95	18.27	19.08	19.42	20.94
	8H	20.89	21.17	22.03	22.31	23.84	18.10	18.38	19.24	19.51	21.04
	12H	21.02	21.27	22.16	22.40	23.97	18.16	18.40	19.30	19.53	21.10
12H	4H	19.95	20.31	21.08	21.43	22.95	17.68	18.03	18.81	19.15	20.67
	6H	20.61	20.89	21.75	22.02	23.56	17.99	18.27	19.13	19.40	20.93
	8H	20.87	21.12	22.02	22.25	23.82	18.14	18.39	19.29	19.52	21.09