

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427762

Luminaire Tested: SQ2W-F-K-100U-100D-L930-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1427762  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-F-K-100U-100D-L930-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - FROSTED CONTINUOUS ROLL LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7567.6 lumens  
Efficiency: N/A  
Efficacy: 107.0 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 70.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1427762

CATALOG NUMBER: SQ2W-F-K-100U-100D-L930-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1427762

CATALOG NUMBER: SQ2W-F-K-100U-100D-L930-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	93	89	86	90	86	83	80	73	71	68	61	59	58	50	49	48	42
2	89	81	75	70	82	75	70	65	64	60	56	53	51	48	44	42	40	35
3	81	71	64	58	74	66	60	54	56	51	47	47	43	40	39	36	34	30
4	74	63	55	49	68	58	51	46	50	44	40	42	38	34	34	31	29	25
5	68	56	48	42	62	52	45	39	45	39	34	38	33	30	31	28	25	22
6	62	50	42	36	57	47	39	34	40	34	30	34	29	26	28	25	22	19
7	58	45	37	32	53	42	35	30	36	31	26	31	26	23	26	22	20	17
8	54	41	33	28	49	38	31	26	33	27	23	28	24	20	23	20	17	15
9	50	37	30	25	46	35	28	23	30	25	21	26	21	18	22	18	16	14
10	47	34	27	22	43	32	26	21	28	22	19	24	20	16	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	22052	22052	22052	22052
5°	21917	22167	21917	22167
10°	21839	22092	21839	22092
15°	21720	21992	21720	21992
20°	21582	21797	21582	21797
25°	21349	21538	21349	21538
30°	21123	21266	21123	21266
35°	20853	20985	20853	20985
40°	20615	20676	20615	20676
45°	20315	20315	20315	20315
50°	19906	19954	19906	19954
55°	19440	19465	19440	19465
60°	18913	18913	18913	18913
65°	18300	18227	18300	18227
70°	17433	17254	17433	17254
75°	16257	15901	16257	15901
80°	14486	13770	14486	13770
85°	11578	9800	11578	9800

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 20°  
 Vertical Angle: 45°  
 Luminance: 20449 cd/sqm



TEST NUMBER: P1427762

CATALOG NUMBER: SQ2W-F-K-100U-100D-L930-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	129.2	1.7
10°-20°	369.2	4.9
20°-30°	555.8	7.3
30°-40°	664.7	8.8
40°-50°	686.3	9.1
50°-60°	619.0	8.2
60°-70°	474.2	6.3
70°-80°	274.1	3.6
80°-90°	76.5	1.0
90°-100°	101.4	1.3
100°-110°	295.6	3.9
110°-120°	482.4	6.4
120°-130°	612.1	8.1
130°-140°	655.0	8.7
140°-150°	611.6	8.1
150°-160°	503.3	6.7
160°-170°	337.5	4.5
170°-180°	119.8	1.6
0°-30°	1054.3	13.9
0°-40°	1718.9	22.7
0°-60°	3024.3	40.0
0°-90°	3849.0	50.9
90°-120°	879.3	11.6
90°-150°	2758.0	36.4
90°-180°	3719.0	49.1
0°-180°	7567.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1366	1366	1366	1366	1366	
5°	1352	1368	1352	1368	1352	128
15°	1299	1316	1299	1316	1299	366
25°	1198	1209	1198	1209	1198	552
35°	1058	1065	1058	1065	1058	662
45°	890	890	890	890	890	686
55°	691	692	691	692	691	617
65°	479	477	479	477	479	473
75°	261	255	261	255	261	276
85°	62	53	62	53	62	73
90°	4	28	4	55	4	6
95°	40	30	40	174	40	48
105°	188	301	188	414	188	200
115°	360	499	360	615	360	355
125°	533	791	533	754	533	477
135°	724	1036	724	835	724	560
145°	925	1194	925	853	925	579
155°	1099	1297	1099	885	1099	505
165°	1214	1352	1214	1019	1214	342
175°	1270	1324	1270	1195	1270	120
180°	1274	1274	1274	1274	1274	

TEST NUMBER: P1427762

CATALOG NUMBER: SQ2W-F-K-100U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1365.8	1365.8	1365.8	1365.8	1365.8	1365.8	1365.8	1365.8	1365.8	1365.8	1365.8
2.5°	1358.8	1365.3	1371.8	1369.1	1363.3	1361.1	1362.4	1363.6	1364.3	1365.0	1364.3
5°	1352.3	1360.8	1369.4	1366.4	1359.6	1356.6	1357.4	1359.1	1363.4	1367.7	1363.4
7.5°	1341.3	1349.9	1358.4	1355.7	1349.2	1346.5	1347.5	1349.4	1353.8	1358.3	1353.8
10°	1332.1	1340.6	1349.2	1346.2	1339.4	1336.8	1338.5	1340.6	1344.1	1347.5	1344.1
12.5°	1320.5	1329.1	1337.6	1335.2	1329.0	1326.4	1327.5	1329.2	1332.9	1336.7	1332.9
15°	1299.4	1307.9	1316.5	1314.1	1308.2	1305.8	1307.1	1308.9	1312.3	1315.7	1312.3
17.5°	1273.8	1281.8	1289.9	1287.7	1282.2	1280.1	1281.6	1283.4	1286.4	1289.4	1286.4
20°	1256.1	1263.8	1271.5	1269.3	1263.7	1261.1	1261.6	1262.6	1265.6	1268.6	1265.6
22.5°	1234.6	1242.3	1250.0	1248.0	1242.8	1239.7	1238.7	1238.9	1242.6	1246.3	1242.6
25°	1198.4	1206.1	1213.8	1212.2	1207.5	1204.5	1203.2	1203.0	1206.0	1209.0	1206.0
27.5°	1160.7	1167.1	1173.5	1172.2	1168.2	1165.8	1165.0	1164.9	1167.0	1169.2	1167.0
30°	1133.0	1139.4	1145.8	1144.2	1139.9	1137.4	1136.5	1136.4	1138.6	1140.7	1138.6
32.5°	1103.8	1109.8	1115.9	1113.7	1108.7	1106.2	1106.0	1106.5	1109.0	1111.5	1109.0
35°	1058.0	1063.1	1068.2	1066.0	1061.3	1059.2	1059.6	1060.4	1062.6	1064.7	1062.6
37.5°	1012.0	1015.9	1019.9	1017.6	1013.2	1011.0	1010.9	1011.3	1013.1	1014.9	1013.1
40°	978.1	982.4	986.7	984.2	979.5	977.0	976.5	976.8	978.9	981.0	978.9
42.5°	943.5	946.8	950.0	947.8	943.8	941.9	942.2	942.6	943.8	944.9	943.8
45°	889.7	892.7	895.6	893.5	889.7	887.7	887.7	888.0	888.8	889.7	888.8
47.5°	833.3	835.6	837.9	836.3	833.3	831.5	831.0	831.0	832.3	833.7	832.3
50°	792.5	795.5	798.5	797.0	794.0	792.1	791.2	791.0	792.7	794.4	792.7
52.5°	752.5	755.8	759.2	757.8	754.8	752.7	751.5	750.9	752.3	753.7	752.3
55°	690.6	694.4	698.3	697.3	694.7	692.6	690.9	689.8	690.7	691.5	690.7
57.5°	627.3	631.0	634.8	634.1	631.9	629.7	627.7	626.4	627.6	628.8	627.6
60°	585.7	589.2	592.6	591.5	588.9	586.8	585.1	584.0	584.9	585.7	584.9
62.5°	543.4	546.8	550.3	548.9	546.0	543.7	542.0	540.9	541.8	542.6	541.8
65°	479.0	482.0	485.0	483.8	481.2	479.1	477.4	476.2	476.6	477.1	476.6
67.5°	414.0	416.5	419.1	417.9	415.4	412.9	410.4	408.7	409.4	410.1	409.4
70°	369.3	371.9	374.5	373.5	371.4	369.2	367.1	365.5	365.5	365.5	365.5
72.5°	326.2	328.5	330.7	329.4	326.9	324.8	323.0	321.6	321.6	321.6	321.6
75°	260.6	261.9	263.2	262.6	261.3	259.6	257.4	255.7	255.3	254.9	255.3
77.5°	197.4	197.4	197.4	196.1	194.5	192.9	191.3	189.9	189.4	188.9	189.4
80°	155.8	155.8	155.8	154.8	153.6	152.3	151.0	149.8	149.0	148.1	149.0
82.5°	117.3	116.7	116.0	114.8	113.6	111.9	110.0	108.7	109.6	110.4	109.6
85°	62.5	61.7	60.8	59.6	58.3	56.9	55.1	53.8	53.3	52.9	53.3
87.5°	20.0	20.4	21.0	21.0	20.8	19.9	18.5	17.6	17.5	17.2	17.5
90°	3.9	9.0	15.4	20.6	24.4	25.7	25.7	27.0	28.3	28.3	28.3
92.5°	14.2	22.4	22.6	22.6	27.5	29.8	31.9	32.2	33.4	33.4	33.4
95°	39.9	43.7	65.6	64.3	43.7	34.7	29.6	29.6	29.6	29.6	29.6
97.5°	76.2	81.8	85.4	114.5	120.9	116.8	95.2	80.0	71.5	67.7	71.5
100°	108.1	110.6	118.4	119.6	151.8	182.7	167.2	147.9	141.5	137.6	141.5
102.5°	140.0	141.5	153.3	158.7	166.2	183.7	237.2	231.3	226.9	226.2	226.9
105°	187.8	189.1	211.0	221.3	226.4	226.4	225.1	250.9	292.0	301.0	292.0
107.5°	239.0	244.9	270.7	298.2	304.1	305.7	299.0	295.1	293.6	294.6	293.6
110°	274.0	283.0	313.9	348.6	357.6	360.2	357.6	353.8	351.2	351.2	351.2



TEST NUMBER: P1427762

CATALOG NUMBER: SQ2W-F-K-100U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	308.0	321.1	356.1	396.0	411.1	418.9	413.2	410.4	407.8	409.9	407.8
115°	360.2	379.5	425.8	467.0	497.9	501.7	500.4	500.4	499.1	499.1	499.1
117.5°	408.6	439.5	491.4	539.3	575.0	585.3	590.5	588.9	587.4	590.0	587.4
120°	442.5	478.6	537.7	591.8	626.5	641.9	647.1	644.5	647.1	644.5	647.1
122.5°	478.6	522.8	581.0	637.0	678.0	695.5	701.6	702.1	702.7	701.1	702.7
125°	532.6	586.6	654.8	712.7	755.1	775.7	780.9	782.2	784.7	791.2	784.7
127.5°	587.1	648.4	723.2	779.1	822.6	847.5	855.5	858.3	863.7	866.6	863.7
130°	625.2	694.7	770.6	823.3	865.8	892.8	906.9	910.8	917.2	916.0	917.2
132.5°	665.4	737.9	814.8	869.6	909.0	938.1	950.2	961.2	963.5	965.4	963.5
135°	724.3	802.7	879.9	934.0	971.3	999.6	1015.0	1025.3	1031.7	1035.6	1031.7
137.5°	786.3	869.1	943.2	991.3	1028.9	1053.3	1070.8	1081.6	1088.3	1091.4	1088.3
140°	828.5	908.2	980.3	1030.4	1063.9	1088.3	1103.8	1116.6	1124.4	1124.4	1124.4
142.5°	868.6	947.3	1017.3	1067.5	1096.8	1119.2	1135.7	1145.5	1154.2	1154.2	1154.2
145°	925.0	1003.4	1067.8	1117.9	1142.4	1162.9	1181.0	1188.7	1193.8	1193.8	1193.8
147.5°	983.9	1053.3	1112.0	1160.1	1180.7	1204.9	1219.0	1225.2	1231.6	1228.8	1231.6
150°	1018.9	1083.2	1139.8	1184.8	1205.4	1228.6	1242.7	1247.9	1254.3	1250.4	1254.3
152.5°	1052.8	1114.1	1165.5	1207.5	1225.0	1248.1	1264.3	1269.5	1273.8	1271.0	1273.8
155°	1098.6	1152.7	1200.3	1238.8	1254.3	1276.2	1291.6	1298.0	1303.2	1296.7	1303.2
157.5°	1139.5	1186.1	1227.5	1263.0	1279.5	1298.3	1312.7	1320.7	1325.8	1323.0	1325.8
160°	1164.2	1206.7	1244.0	1277.4	1292.9	1309.6	1325.0	1334.0	1339.2	1335.3	1339.2
162.5°	1184.8	1223.2	1258.4	1288.8	1302.1	1316.8	1335.3	1343.3	1348.5	1343.6	1348.5
165°	1214.4	1245.3	1276.2	1301.9	1313.5	1325.0	1344.3	1353.3	1357.2	1352.1	1357.2
167.5°	1236.8	1260.5	1285.4	1307.5	1316.0	1327.4	1346.7	1354.1	1359.0	1352.6	1359.0
170°	1249.1	1269.7	1291.6	1309.6	1316.0	1326.3	1345.6	1352.1	1355.9	1349.5	1355.9
172.5°	1259.4	1274.9	1292.6	1308.6	1311.9	1320.2	1338.4	1344.9	1347.7	1342.3	1347.7
175°	1269.7	1278.7	1291.6	1301.9	1300.6	1305.7	1321.2	1326.3	1331.5	1323.8	1331.5
177.5°	1274.6	1278.7	1282.8	1289.0	1284.9	1284.9	1296.2	1299.3	1300.3	1296.2	1300.3
180°	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6



TEST NUMBER: P1427762

CATALOG NUMBER: SQ2W-F-K-100U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1365.8	1365.8	1365.8	1365.8	1365.8	1365.8	1365.8	1365.8	1365.8	1365.8	1365.8
2.5°	1363.6	1362.4	1361.1	1363.3	1369.1	1371.8	1365.3	1358.8	1365.3	1371.8	1369.1
5°	1359.1	1357.4	1356.6	1359.6	1366.4	1369.4	1360.8	1352.3	1360.8	1369.4	1366.4
7.5°	1349.4	1347.5	1346.5	1349.2	1355.7	1358.4	1349.9	1341.3	1349.9	1358.4	1355.7
10°	1340.6	1338.5	1336.8	1339.4	1346.2	1349.2	1340.6	1332.1	1340.6	1349.2	1346.2
12.5°	1329.2	1327.5	1326.4	1329.0	1335.2	1337.6	1329.1	1320.5	1329.1	1337.6	1335.2
15°	1308.9	1307.1	1305.8	1308.2	1314.1	1316.5	1307.9	1299.4	1307.9	1316.5	1314.1
17.5°	1283.4	1281.6	1280.1	1282.2	1287.7	1289.9	1281.8	1273.8	1281.8	1289.9	1287.7
20°	1262.6	1261.6	1261.1	1263.7	1269.3	1271.5	1263.8	1256.1	1263.8	1271.5	1269.3
22.5°	1238.9	1238.7	1239.7	1242.8	1248.0	1250.0	1242.3	1234.6	1242.3	1250.0	1248.0
25°	1203.0	1203.2	1204.5	1207.5	1212.2	1213.8	1206.1	1198.4	1206.1	1213.8	1212.2
27.5°	1164.9	1165.0	1165.8	1168.2	1172.2	1173.5	1167.1	1160.7	1167.1	1173.5	1172.2
30°	1136.4	1136.5	1137.4	1139.9	1144.2	1145.8	1139.4	1133.0	1139.4	1145.8	1144.2
32.5°	1106.5	1106.0	1106.2	1108.7	1113.7	1115.9	1109.8	1103.8	1109.8	1115.9	1113.7
35°	1060.4	1059.6	1059.2	1061.3	1066.0	1068.2	1063.1	1058.0	1063.1	1068.2	1066.0
37.5°	1011.3	1010.9	1011.0	1013.2	1017.6	1019.9	1015.9	1012.0	1015.9	1019.9	1017.6
40°	976.8	976.5	977.0	979.5	984.2	986.7	982.4	978.1	982.4	986.7	984.2
42.5°	942.6	942.2	941.9	943.8	947.8	950.0	946.8	943.5	946.8	950.0	947.8
45°	888.0	887.7	887.7	889.7	893.5	895.6	892.7	889.7	892.7	895.6	893.5
47.5°	831.0	831.0	831.5	833.3	836.3	837.9	835.6	833.3	835.6	837.9	836.3
50°	791.0	791.2	792.1	794.0	797.0	798.5	795.5	792.5	795.5	798.5	797.0
52.5°	750.9	751.5	752.7	754.8	757.8	759.2	755.8	752.5	755.8	759.2	757.8
55°	689.8	690.9	692.6	694.7	697.3	698.3	694.4	690.6	694.4	698.3	697.3
57.5°	626.4	627.7	629.7	631.9	634.1	634.8	631.0	627.3	631.0	634.8	634.1
60°	584.0	585.1	586.8	588.9	591.5	592.6	589.2	585.7	589.2	592.6	591.5
62.5°	540.9	542.0	543.7	546.0	548.9	550.3	546.8	543.4	546.8	550.3	548.9
65°	476.2	477.4	479.1	481.2	483.8	485.0	482.0	479.0	482.0	485.0	483.8
67.5°	408.7	410.4	412.9	415.4	417.9	419.1	416.5	414.0	416.5	419.1	417.9
70°	365.5	367.1	369.2	371.4	373.5	374.5	371.9	369.3	371.9	374.5	373.5
72.5°	321.6	323.0	324.8	326.9	329.4	330.7	328.5	326.2	328.5	330.7	329.4
75°	255.7	257.4	259.6	261.3	262.6	263.2	261.9	260.6	261.9	263.2	262.6
77.5°	189.9	191.3	192.9	194.5	196.1	197.4	197.4	197.4	197.4	197.4	196.1
80°	149.8	151.0	152.3	153.6	154.8	155.8	155.8	155.8	155.8	155.8	154.8
82.5°	108.7	110.0	111.9	113.6	114.8	116.0	116.7	117.3	116.7	116.0	114.8
85°	53.8	55.1	56.9	58.3	59.6	60.8	61.7	62.5	61.7	60.8	59.6
87.5°	17.6	18.5	19.9	20.8	21.0	21.0	20.4	20.0	20.4	20.7	21.6
90°	27.0	25.7	25.7	24.4	20.6	15.4	9.0	3.9	9.0	14.2	23.2
92.5°	32.2	31.9	29.8	27.5	22.6	22.6	22.4	14.2	24.4	34.7	49.9
95°	29.6	29.6	34.7	43.7	64.3	65.6	43.7	39.9	56.6	79.8	100.3
97.5°	80.0	95.2	116.8	120.9	114.5	85.4	81.8	76.2	103.7	126.6	159.8
100°	147.9	167.2	182.7	151.8	119.6	118.4	110.6	108.1	137.6	159.5	191.7
102.5°	231.3	237.2	183.7	166.2	158.7	153.3	141.5	140.0	169.6	199.7	226.7
105°	250.9	225.1	226.4	226.4	221.3	211.0	189.1	187.8	221.3	256.0	289.5
107.5°	295.1	299.0	305.7	304.1	298.2	270.7	244.9	239.0	269.1	310.8	347.6
110°	353.8	357.6	360.2	357.6	348.6	313.9	283.0	274.0	301.0	344.8	384.6



TEST NUMBER: P1427762

CATALOG NUMBER: SQ2W-F-K-100U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	410.4	413.2	418.9	411.1	396.0	356.1	321.1	308.0	335.0	379.8	420.7
115°	500.4	500.4	501.7	497.9	467.0	425.8	379.5	360.2	383.4	424.5	469.6
117.5°	588.9	590.5	585.3	575.0	539.3	491.4	439.5	408.6	426.8	470.3	516.6
120°	644.5	647.1	641.9	626.5	591.8	537.7	478.6	442.5	456.7	499.1	545.5
122.5°	702.1	701.6	695.5	678.0	637.0	581.0	522.8	478.6	484.5	523.8	569.1
125°	782.2	780.9	775.7	755.1	712.7	654.8	586.6	532.6	524.9	558.3	604.6
127.5°	858.3	855.5	847.5	822.6	779.1	723.2	648.4	587.1	569.9	591.0	633.4
130°	910.8	906.9	892.8	865.8	823.3	770.6	694.7	625.2	600.8	613.6	650.9
132.5°	961.2	950.2	938.1	909.0	869.6	814.8	737.9	665.4	631.6	637.3	666.4
135°	1025.3	1015.0	999.6	971.3	934.0	879.9	802.7	724.3	678.0	672.8	689.5
137.5°	1081.6	1070.8	1053.3	1028.9	991.3	943.2	869.1	786.3	727.9	710.6	717.1
140°	1116.6	1103.8	1088.3	1063.9	1030.4	980.3	908.2	828.5	762.9	738.4	734.6
142.5°	1145.5	1135.7	1119.2	1096.8	1067.5	1017.3	947.3	868.6	798.9	767.2	758.2
145°	1188.7	1181.0	1162.9	1142.4	1117.9	1067.8	1003.4	925.0	855.5	814.3	795.0
147.5°	1225.2	1219.0	1204.9	1180.7	1160.1	1112.0	1053.3	983.9	912.6	861.7	836.7
150°	1247.9	1242.7	1228.6	1205.4	1184.8	1139.8	1083.2	1018.9	950.7	896.7	864.5
152.5°	1269.5	1264.3	1248.1	1225.0	1207.5	1165.5	1114.1	1052.8	983.6	929.6	896.4
155°	1298.0	1291.6	1276.2	1254.3	1238.8	1200.3	1152.7	1098.6	1039.4	982.8	945.5
157.5°	1320.7	1312.7	1298.3	1279.5	1263.0	1227.5	1186.1	1139.5	1087.8	1033.8	995.7
160°	1334.0	1325.0	1309.6	1292.9	1277.4	1244.0	1206.7	1164.2	1116.6	1067.8	1026.6
162.5°	1343.3	1335.3	1316.8	1302.1	1288.8	1258.4	1223.2	1184.8	1142.4	1099.7	1061.6
165°	1353.3	1344.3	1325.0	1313.5	1301.9	1276.2	1245.3	1214.4	1178.4	1143.7	1112.8
167.5°	1354.1	1346.7	1327.4	1316.0	1307.5	1285.4	1260.5	1236.8	1208.7	1181.5	1155.7
170°	1352.1	1345.6	1326.3	1316.0	1309.6	1291.6	1269.7	1249.1	1227.3	1204.1	1183.5
172.5°	1344.9	1338.4	1320.2	1311.9	1308.6	1292.6	1274.9	1259.4	1240.7	1223.7	1207.2
175°	1326.3	1321.2	1305.7	1300.6	1301.9	1291.6	1278.7	1269.7	1258.1	1247.9	1238.8
177.5°	1299.3	1296.2	1284.9	1284.9	1289.0	1282.8	1278.7	1274.6	1269.5	1266.4	1263.3
180°	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6



TEST NUMBER: P1427762

CATALOG NUMBER: SQ2W-F-K-100U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1365.8	1365.8	1365.8	1365.8	1365.8	1365.8	1365.8	1365.8	1365.8	1365.8	1365.8
2.5°	1363.3	1361.1	1362.4	1363.6	1364.3	1365.0	1364.3	1363.6	1362.4	1361.1	1363.3
5°	1359.6	1356.6	1357.4	1359.1	1363.4	1367.7	1363.4	1359.1	1357.4	1356.6	1359.6
7.5°	1349.2	1346.5	1347.5	1349.4	1353.8	1358.3	1353.8	1349.4	1347.5	1346.5	1349.2
10°	1339.4	1336.8	1338.5	1340.6	1344.1	1347.5	1344.1	1340.6	1338.5	1336.8	1339.4
12.5°	1329.0	1326.4	1327.5	1329.2	1332.9	1336.7	1332.9	1329.2	1327.5	1326.4	1329.0
15°	1308.2	1305.8	1307.1	1308.9	1312.3	1315.7	1312.3	1308.9	1307.1	1305.8	1308.2
17.5°	1282.2	1280.1	1281.6	1283.4	1286.4	1289.4	1286.4	1283.4	1281.6	1280.1	1282.2
20°	1263.7	1261.1	1261.6	1262.6	1265.6	1268.6	1265.6	1262.6	1261.6	1261.1	1263.7
22.5°	1242.8	1239.7	1238.7	1238.9	1242.6	1246.3	1242.6	1238.9	1238.7	1239.7	1242.8
25°	1207.5	1204.5	1203.2	1203.0	1206.0	1209.0	1206.0	1203.0	1203.2	1204.5	1207.5
27.5°	1168.2	1165.8	1165.0	1164.9	1167.0	1169.2	1167.0	1164.9	1165.0	1165.8	1168.2
30°	1139.9	1137.4	1136.5	1136.4	1138.6	1140.7	1138.6	1136.4	1136.5	1137.4	1139.9
32.5°	1108.7	1106.2	1106.0	1106.5	1109.0	1111.5	1109.0	1106.5	1106.0	1106.2	1108.7
35°	1061.3	1059.2	1059.6	1060.4	1062.6	1064.7	1062.6	1060.4	1059.6	1059.2	1061.3
37.5°	1013.2	1011.0	1010.9	1011.3	1013.1	1014.9	1013.1	1011.3	1010.9	1011.0	1013.2
40°	979.5	977.0	976.5	976.8	978.9	981.0	978.9	976.8	976.5	977.0	979.5
42.5°	943.8	941.9	942.2	942.6	943.8	944.9	943.8	942.6	942.2	941.9	943.8
45°	889.7	887.7	887.7	888.0	888.8	889.7	888.8	888.0	887.7	887.7	889.7
47.5°	833.3	831.5	831.0	831.0	832.3	833.7	832.3	831.0	831.0	831.5	833.3
50°	794.0	792.1	791.2	791.0	792.7	794.4	792.7	791.0	791.2	792.1	794.0
52.5°	754.8	752.7	751.5	750.9	752.3	753.7	752.3	750.9	751.5	752.7	754.8
55°	694.7	692.6	690.9	689.8	690.7	691.5	690.7	689.8	690.9	692.6	694.7
57.5°	631.9	629.7	627.7	626.4	627.6	628.8	627.6	626.4	627.7	629.7	631.9
60°	588.9	586.8	585.1	584.0	584.9	585.7	584.9	584.0	585.1	586.8	588.9
62.5°	546.0	543.7	542.0	540.9	541.8	542.6	541.8	540.9	542.0	543.7	546.0
65°	481.2	479.1	477.4	476.2	476.6	477.1	476.6	476.2	477.4	479.1	481.2
67.5°	415.4	412.9	410.4	408.7	409.4	410.1	409.4	408.7	410.4	412.9	415.4
70°	371.4	369.2	367.1	365.5	365.5	365.5	365.5	365.5	367.1	369.2	371.4
72.5°	326.9	324.8	323.0	321.6	321.6	321.6	321.6	321.6	323.0	324.8	326.9
75°	261.3	259.6	257.4	255.7	255.3	254.9	255.3	255.7	257.4	259.6	261.3
77.5°	194.5	192.9	191.3	189.9	189.4	188.9	189.4	189.9	191.3	192.9	194.5
80°	153.6	152.3	151.0	149.8	149.0	148.1	149.0	149.8	151.0	152.3	153.6
82.5°	113.6	111.9	110.0	108.7	109.6	110.4	109.6	108.7	110.0	111.9	113.6
85°	58.3	56.9	55.1	53.8	53.3	52.9	53.3	53.8	55.1	56.9	58.3
87.5°	21.8	22.4	22.9	22.8	23.5	22.6	23.5	22.8	22.9	22.4	21.8
90°	29.6	38.6	47.6	52.7	57.9	55.3	57.9	52.7	47.6	38.6	29.6
92.5°	59.4	74.6	85.7	94.9	99.1	98.5	99.1	94.9	85.7	74.6	59.4
95°	119.6	137.6	155.7	168.5	176.2	173.7	176.2	168.5	155.7	137.6	119.6
97.5°	184.5	208.7	228.7	240.8	248.5	253.7	248.5	240.8	228.7	208.7	184.5
100°	227.7	250.9	274.0	288.2	301.0	306.2	301.0	288.2	274.0	250.9	227.7
102.5°	262.7	293.1	318.3	333.4	344.3	349.4	344.3	318.3	293.1	262.7	
105°	320.3	352.5	379.5	398.8	410.4	414.2	410.4	398.8	379.5	352.5	320.3
107.5°	378.0	411.1	436.1	457.5	471.6	479.8	471.6	457.5	436.1	411.1	378.0
110°	423.2	450.3	477.3	496.6	510.7	515.9	510.7	496.6	477.3	450.3	423.2



TEST NUMBER: P1427762

CATALOG NUMBER: SQ2W-F-K-100U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	461.3	491.4	518.4	537.7	553.9	561.1	553.9	537.7	518.4	491.4	461.3
115°	514.6	554.5	578.9	596.9	608.5	614.9	608.5	596.9	578.9	554.5	514.6
117.5°	558.8	600.5	627.3	641.2	646.6	651.2	646.6	641.2	627.3	600.5	558.8
120°	586.6	625.2	656.1	674.1	680.5	683.1	680.5	674.1	656.1	625.2	586.6
122.5°	612.3	648.9	678.7	700.9	711.4	714.0	711.4	700.9	678.7	648.9	612.3
125°	648.4	683.1	714.0	735.8	747.4	753.9	747.4	735.8	714.0	683.1	648.4
127.5°	679.8	717.3	745.6	765.4	776.8	781.9	776.8	765.4	745.6	717.3	679.8
130°	697.3	735.8	764.1	786.0	796.3	801.5	796.3	786.0	764.1	735.8	697.3
132.5°	710.6	751.3	780.6	800.4	811.7	816.9	811.7	800.4	780.6	751.3	710.6
135°	726.8	769.3	800.2	819.5	829.8	834.9	829.8	819.5	800.2	769.3	726.8
137.5°	741.0	779.6	811.7	832.1	841.3	844.7	841.3	832.1	811.7	779.6	741.0
140°	751.3	784.7	816.9	836.2	846.5	847.8	846.5	836.2	816.9	784.7	751.3
142.5°	764.7	790.9	819.0	838.2	848.5	850.9	848.5	838.2	819.0	790.9	764.7
145°	788.6	804.0	823.3	841.3	850.3	852.9	850.3	841.3	823.3	804.0	788.6
147.5°	818.7	823.6	833.6	845.5	854.2	856.0	854.2	845.5	833.6	823.6	818.7
150°	841.3	840.1	843.9	851.6	859.3	858.1	859.3	851.6	843.9	840.1	841.3
152.5°	867.1	859.6	859.3	862.9	866.6	866.3	866.6	862.9	859.3	859.6	867.1
155°	910.8	896.7	888.9	886.4	886.4	885.1	886.4	886.4	888.9	896.7	910.8
157.5°	958.9	939.1	927.5	921.4	919.6	916.7	919.6	921.4	927.5	939.1	958.9
160°	991.9	970.0	958.4	948.1	944.3	940.4	944.3	948.1	958.4	970.0	991.9
162.5°	1022.7	1001.9	989.3	980.0	976.2	970.2	976.2	980.0	989.3	1001.9	1022.7
165°	1072.9	1051.0	1036.9	1029.2	1024.0	1018.9	1024.0	1029.2	1036.9	1051.0	1072.9
167.5°	1123.1	1099.1	1089.9	1081.1	1076.2	1067.0	1076.2	1081.1	1089.9	1099.1	1123.1
170°	1153.9	1132.1	1126.9	1119.2	1110.2	1099.9	1110.2	1119.2	1126.9	1132.1	1153.9
172.5°	1180.7	1166.0	1160.9	1153.2	1150.3	1142.1	1150.3	1153.2	1160.9	1166.0	1180.7
175°	1219.6	1208.0	1208.0	1206.7	1202.8	1195.1	1202.8	1206.7	1208.0	1208.0	1219.6
177.5°	1252.0	1245.8	1249.9	1249.9	1248.9	1241.7	1248.9	1249.9	1249.9	1245.8	1252.0
180°	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6	1273.6



TEST NUMBER: P1427762

CATALOG NUMBER: SQ2W-F-K-100U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	1365.8	1365.8	1365.8	1365.8
2.5°	1369.1	1371.8	1365.3	1358.8
5°	1366.4	1369.4	1360.8	1352.3
7.5°	1355.7	1358.4	1349.9	1341.3
10°	1346.2	1349.2	1340.6	1332.1
12.5°	1335.2	1337.6	1329.1	1320.5
15°	1314.1	1316.5	1307.9	1299.4
17.5°	1287.7	1289.9	1281.8	1273.8
20°	1269.3	1271.5	1263.8	1256.1
22.5°	1248.0	1250.0	1242.3	1234.6
25°	1212.2	1213.8	1206.1	1198.4
27.5°	1172.2	1173.5	1167.1	1160.7
30°	1144.2	1145.8	1139.4	1133.0
32.5°	1113.7	1115.9	1109.8	1103.8
35°	1066.0	1068.2	1063.1	1058.0
37.5°	1017.6	1019.9	1015.9	1012.0
40°	984.2	986.7	982.4	978.1
42.5°	947.8	950.0	946.8	943.5
45°	893.5	895.6	892.7	889.7
47.5°	836.3	837.9	835.6	833.3
50°	797.0	798.5	795.5	792.5
52.5°	757.8	759.2	755.8	752.5
55°	697.3	698.3	694.4	690.6
57.5°	634.1	634.8	631.0	627.3
60°	591.5	592.6	589.2	585.7
62.5°	548.9	550.3	546.8	543.4
65°	483.8	485.0	482.0	479.0
67.5°	417.9	419.1	416.5	414.0
70°	373.5	374.5	371.9	369.3
72.5°	329.4	330.7	328.5	326.2
75°	262.6	263.2	261.9	260.6
77.5°	196.1	197.4	197.4	197.4
80°	154.8	155.8	155.8	155.8
82.5°	114.8	116.0	116.7	117.3
85°	59.6	60.8	61.7	62.5
87.5°	21.6	20.7	20.4	20.0
90°	23.2	14.2	9.0	3.9
92.5°	49.9	34.7	24.4	14.2
95°	100.3	79.8	56.6	39.9
97.5°	159.8	126.6	103.7	76.2
100°	191.7	159.5	137.6	108.1
102.5°	226.7	199.7	169.6	140.0
105°	289.5	256.0	221.3	187.8
107.5°	347.6	310.8	269.1	239.0
110°	384.6	344.8	301.0	274.0



TEST NUMBER: P1427762

CATALOG NUMBER: SQ2W-F-K-100U-100D-L930-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	420.7	379.8	335.0	308.0
115°	469.6	424.5	383.4	360.2
117.5°	516.6	470.3	426.8	408.6
120°	545.5	499.1	456.7	442.5
122.5°	569.1	523.8	484.5	478.6
125°	604.6	558.3	524.9	532.6
127.5°	633.4	591.0	569.9	587.1
130°	650.9	613.6	600.8	625.2
132.5°	666.4	637.3	631.6	665.4
135°	689.5	672.8	678.0	724.3
137.5°	717.1	710.6	727.9	786.3
140°	734.6	738.4	762.9	828.5
142.5°	758.2	767.2	798.9	868.6
145°	795.0	814.3	855.5	925.0
147.5°	836.7	861.7	912.6	983.9
150°	864.5	896.7	950.7	1018.9
152.5°	896.4	929.6	983.6	1052.8
155°	945.5	982.8	1039.4	1098.6
157.5°	995.7	1033.8	1087.8	1139.5
160°	1026.6	1067.8	1116.6	1164.2
162.5°	1061.6	1099.7	1142.4	1184.8
165°	1112.8	1143.7	1178.4	1214.4
167.5°	1155.7	1181.5	1208.7	1236.8
170°	1183.5	1204.1	1227.3	1249.1
172.5°	1207.2	1223.7	1240.7	1259.4
175°	1238.8	1247.9	1258.1	1269.7
177.5°	1263.3	1266.4	1269.5	1274.6
180°	1273.6	1273.6	1273.6	1273.6



TEST NUMBER: P1427762  
 CATALOG NUMBER: SQ2W-F-K-100U-100D-L930-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.69	19.57	19.63	20.53	21.79	18.60	19.48	19.55	20.45	21.71
	3H	20.48	21.27	21.44	22.24	23.53	20.38	21.17	21.34	22.14	23.42
	4H	21.18	21.92	22.15	22.90	24.19	21.06	21.81	22.03	22.79	24.08
	6H	21.61	22.30	22.60	23.29	24.59	21.47	22.16	22.46	23.15	24.45
	8H	21.78	22.43	22.77	23.43	24.73	21.62	22.28	22.61	23.28	24.58
	12H	21.86	22.49	22.86	23.48	24.80	21.68	22.31	22.68	23.30	24.63
4H	2H	19.27	20.02	20.25	21.00	22.29	19.20	19.95	20.18	20.93	22.22
	3H	21.29	21.92	22.28	22.93	24.23	21.20	21.83	22.19	22.83	24.14
	4H	22.11	22.68	23.10	23.68	25.01	22.00	22.57	22.99	23.57	24.90
	6H	22.66	23.16	23.67	24.18	25.50	22.52	23.01	23.53	24.04	25.36
	8H	22.88	23.34	23.89	24.36	25.70	22.72	23.18	23.73	24.20	25.54
	12H	22.99	23.41	24.02	24.44	25.79	22.81	23.22	23.83	24.26	25.60
8H	4H	22.35	22.82	23.36	23.83	25.17	22.26	22.72	23.27	23.74	25.07
	6H	23.04	23.43	24.08	24.49	25.82	22.91	23.30	23.95	24.35	25.69
	8H	23.35	23.69	24.39	24.73	26.09	23.19	23.53	24.24	24.58	25.93
	12H	23.53	23.83	24.58	24.87	26.27	23.34	23.64	24.39	24.68	26.08
12H	4H	22.35	22.77	23.38	23.80	25.14	22.26	22.67	23.29	23.71	25.05
	6H	23.09	23.43	24.14	24.48	25.83	22.97	23.31	24.01	24.35	25.71
	8H	23.43	23.73	24.48	24.77	26.16	23.28	23.58	24.33	24.61	26.01